

Uni Wall Sconce

10575312



Uni Wall Mount Sconce: Urban up and down lighting
Wall Mounts applies on surface, e.g., parking garages, entrances, outdoor terrace and wall in garden.

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

Benefits

- Modern streamlined design.
- Multiple mounting option.
- Easy directly mounted over a bracket.

Applications

- Walkways
- Parks and Plazas
- Outdoor Parking areas

Versions




Uni Wall Sconce

Features

- Die – cast aluminum housing and tempered glass diffuser.
- Textured architectural bronze powder coat finish.
- Various color can be customized to meet per customer need.

Dimensional drawing



BWP410 LED NW 220V 40W WB PSU 7012

General Information

Driver included	Yes
-----------------	-----

Light Technical

Luminous Flux	5,400 lm
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	70
Light source color	740 neutral white

Operating and Electrical

Power Consumption	40 W
-------------------	------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Gray
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass

Approval and Application

CE mark	Yes
---------	-----