



Uni Wall Mount Sconce: Urban up and down lighting Wall Mounts applies on surface, e.g., parking garages, entrances, outdoor terrace and wall in garden.

Uni Wall Sconce

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

Uni Wall Sconce

Benefits

- Modern streamlined design.
- Multiple mounting option.
- Easy directly mounted over a bracket.



Features

- Die – cast aluminum housing and tempered glass diffuser.
- Textured architectural bronze powder coat finish.
- Various color can be customized to meet per customer need.

Application

- Walkways
- Parks and Plazas
- Outdoor Parking areas

Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	70
Operating and Electrical	
Power Consumption	40 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
CE mark	Yes

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401697308	BWP411 LED WW 220V 40W NB PSU 7012	730 warm white	3000 K	5,000 lm
911401697408	BWP411 LED WW 220V 40W MB PSU 7012	730 warm white	3000 K	5,000 lm
911401697508	BWP411 LED WW 220V 40W WB PSU 7012	730 warm white	3000 K	5,000 lm
911401697608	BWP411 LED NW 220V 40W NB PSU 7012	740 neutral white	4000 K	5,400 lm
911401697708	BWP411 LED NW 220V 40W MB PSU 7012	740 neutral white	4000 K	5,400 lm
911401697808	BWP411 LED NW 220V 40W WB PSU 7012	740 neutral white	4000 K	5,400 lm
911401696708	BWP410 LED WW 220V 40W NB PSU 7012	730 warm white	3000 K	5,000 lm
911401696808	BWP410 LED WW 220V 40W MB PSU 7012	730 warm white	3000 K	5,000 lm
911401696908	BWP410 LED WW 220V 40W WB PSU 7012	730 warm white	3000 K	5,000 lm

Uni Wall Sconce

Order Code	Full Product Name	Light source color	Correlated Color	
			Temperature (Nom)	Luminous Flux
911401697008	BWP410 LED NW 220V 40W NB PSU	740 neutral white	4000 K	5,400 lm
	7012			
911401697108	BWP410 LED NW 220V 40W MB PSU	740 neutral white	4000 K	5,400 lm
	7012			
911401697208	BWP410 LED NW 220V 40W WB PSU	740 neutral white	4000 K	5,400 lm
	7012			

