

Uni Wall Mount

10575320



Uni Wall Mount: Urban Wall Mount applies on surface, e.g., parking garages, entrances, outdoor terrace and wall in garden.

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. Thanks to the adjustable mounting angle, the fixture can be installed in accordance with per requirement, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount help you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount offers an affordable, energy – efficient and stable choice in wall Mounting family.

Benefits

- Modern streamlined design
- Adjustable mounting angle degree (0-90)
- Easy installation

Applications


- Walkways
- Parks and Plazas
- Outdoor Parking areas

Features

- Die – cast aluminum housing and tempered glass diffuser.

- Textured architectural bronze powder coat finish.
- Various color can be customized to meet per customer need.

Versions



Dimensional drawing



BWP420 LED NW 220V 20W WB PSU 7012

BWP421 LED WW 220V 60W WB PSU 7012

General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	70
Controls and Dimming	
Dimmable	No

Mechanical and Housing

Housing Color	Gray
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass

Approval and Application

CE mark	Yes
---------	-----

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
911401698108	BWP421 LED WW 220V 40W WB PSU 7012	5,000 lm	3000 K	730 warm white
911401698208	BWP421 LED NW 220V 40W WB PSU 7012	5,400 lm	4000 K	740 neutral white
911401698308	BWP421 LED WW 220V 60W WB PSU 7012	7,500 lm	3000 K	730 warm white
911401698408	BWP421 LED NW 220V 60W WB PSU 7012	8,200 lm	4000 K	740 neutral white
911401697908	BWP420 LED WW 220V 20W WB PSU 7012	2,500 lm	3000 K	730 warm white
911401698008	BWP420 LED NW 220V 20W WB PSU 7012	2,700 lm	4000 K	740 neutral white

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401698108	BWP421 LED WW 220V 40W WB PSU 7012	40 W
911401698208	BWP421 LED NW 220V 40W WB PSU 7012	40 W
911401698308	BWP421 LED WW 220V 60W WB PSU 7012	60 W
911401698408	BWP421 LED NW 220V 60W WB PSU 7012	60 W
911401697908	BWP420 LED WW 220V 20W WB PSU 7012	20 W
911401698008	BWP420 LED NW 220V 20W WB PSU 7012	20 W