



Uni Wall Mount: Urban Wall Mount applies on surface, e.g., parking garages, entrances, outdoor terrace and wall in garden.

Uni Wall Mount

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. Thanks to the adjustable mounting angle, the fixture can be installed in accordance with per requirement, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount help you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount offers an affordable, energy – efficient and stable choice in wall Mounting family.

Benefits

- Modern streamlined design
- Adjustable mounting angle degree (0-90)
- Easy installation

Uni Wall Mount



Features

- Die – cast aluminum housing and tempered glass diffuser.
- Textured architectural bronze powder coat finish.
- Various color can be customized to meet per customer need.

Application

- Walkways
- Parks and Plazas
- Outdoor Parking areas

Dimensional drawing



General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	70
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
CE mark	Yes

Light Technical

Order Code	Full Product Name	Light source color	Temperature (Nom)	Luminous Flux
61097599	BWP421 LED WW 220V 40W WB PSU 7012	730 warm white	3000 K	5,000 lm
61098299	BWP421 LED NW 220V 40W WB PSU 7012	740 neutral white	4000 K	5,400 lm
61099999	BWP421 LED WW 220V 60W WB PSU 7012	730 warm white	3000 K	7,500 lm
61101999	BWP421 LED NW 220V 60W WB PSU 7012	740 neutral white	4000 K	8,200 lm
61095199	BWP420 LED WW 220V 20W WB PSU 7012	730 warm white	3000 K	2,500 lm
61096899	BWP420 LED NW 220V 20W WB PSU 7012	740 neutral white	4000 K	2,700 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
61097599	BWP421 LED WW 220V 40W WB PSU 7012	40 W
61098299	BWP421 LED NW 220V 40W WB PSU 7012	40 W
61099999	BWP421 LED WW 220V 60W WB PSU 7012	60 W

Order Code	Full Product Name	Power Consumption
61101999	BWP421 LED NW 220V 60W WB PSU 7012	60 W
61095199	BWP420 LED WW 220V 20W WB PSU 7012	20 W
61096899	BWP420 LED NW 220V 20W WB PSU 7012	20 W

Uni Wall Mount



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2024, August 30 - data subject to change