



# **Uni Wall Mount: Urban Wall Mount applies on surface, e.g., parking garages, entrances, outdoor terrace and wall in garden.**

## **Uni Wall Mount**

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. Thanks to the adjustable mounting angle, the fixture can be installed in accordance with per requirement, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount help you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount offers an affordable, energy – efficient and stable choice in wall Mounting family.

### **Benefits**

- Modern streamlined design
- Adjustable mounting angle degree (0-90)
- Easy installation

## Uni Wall Mount

### Features

- Die – cast aluminum housing and tempered glass diffuser.
- Textured architectural bronze powder coat finish.
- Various color can be customized to meet per customer need.

### Application

- Walkways
- Parks and Plazas
- Outdoor Parking areas



### Versions



UNI WALL MOUNT

UNI WALL MOUNT

### Dimensional drawing



# Uni Wall Mount

General Information	
Driver included	Yes
Light Technical	
Color rendering index (CRI)	70
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Flat glass
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
CE mark	Yes

## Light Technical

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Luminous Flux
911401698108	BWP421 LED WW 220V 40W WB PSU 7012	730 warm white	3000 K	5,000 lm
911401698208	BWP421 LED NW 220V 40W WB PSU 7012	740 neutral white	4000 K	5,400 lm
911401698308	BWP421 LED WW 220V 60W WB PSU 7012	730 warm white	3000 K	7,500 lm
911401698408	BWP421 LED NW 220V 60W WB PSU 7012	740 neutral white	4000 K	8,200 lm
911401698008	BWP420 LED NW 220V 20W WB PSU 7012	740 neutral white	4000 K	2,700 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401698108	BWP421 LED WW 220V 40W WB PSU 7012	40 W
911401698208	BWP421 LED NW 220V 40W WB PSU 7012	40 W
911401698308	BWP421 LED WW 220V 60W WB PSU 7012	60 W

Order Code	Full Product Name	Power Consumption
911401698408	BWP421 LED NW 220V 60W WB PSU 7012	60 W
911401698008	BWP420 LED NW 220V 20W WB PSU 7012	20 W

