



Install smarter, finish sooner Choose long-lasting reliability and performance

CoreLine waterproof gen3

CoreLine waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. Its trusted, well-known, and appreciated architecture establishes a new standard for installation and sustainability. A fast and easy connection is enabled by an optional pre-mounted external connector, while its efficient design ensures flexibility with plug-in emergency packs and “All-in” settings, allowing on-site adjustments to better suit various application conditions. Smart architecture facilitates straightforward, toolless parts replacement, while single-material paper packaging simplifies waste management on-site. Additionally, the optional Post-Consumer Recycled (PCR) plastic housing elevates its environmentally friendly design to the next level. CoreLine waterproof provides better wide-beam light distribution for straightforward and effective lighting. It can directly replace traditional waterproof luminaires with fluorescent lamps ranging from 18W up to 58W, delivering significant energy savings. The product family also includes a range of options, such as on/off, DALI dimming, and Interact Ready option with integrated wireless communications which can be used with Interact gateways, sensors and software, is also available in this family.

CoreLine waterproof gen3

Benefits

- Hassle-free and fast installation and service
- Fulfills needs of general applications projects, with robust design (IK08) and high water and dust-proof rating (IP66)
- Design with sustainability in mind — with replaceable parts, single-paper material packaging, and access to the Signify Service Tag app with service and maintenance information at hand.
- Interact Ready connectivity for smart lighting and easy commissioning.

Features

- Long lifetime of 100,000 hours at L80 with 5 years warranty
- High efficiency: Standard versions to 160 lm/W, UltraEfficient versions of 185 lm/W
- All-in: multiple lumen packages and/or color temperatures in one luminaire (optional)
- Pre-mounted waterproof external connector (optional), long sliders, faster lock opening, toolless electrical connections, supporting ease and flexibility of installation
- Sustainability in scope: Post Consumer Recycled housing (optional) and spare parts (driver, LED boards, cover).
- Optional controls and versions: DALI dimming, integrated wireless connectivity (Interact Ready), integrated movement sensors with dimming and grouping function (MDU), Emergency Lighting (pack), through wiring 1- and 3-phase (TW1/3)

Application

- Manufacturing
- Parking Garages
- Warehouses
- General lighting

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Versions

CoreLine waterproof G3, WT120C
G3 All_in



CoreLine waterproof G3, WT120C
G3 All_in









CoreLine waterproof gen3

Versions

CoreLine waterproof G3, WT120C
G3 All_in



Dimensional drawing



CoreLine waterproof gen3

Product details




CoreLine Waterproof WT120C G2
PCU-7DPP



CoreLine waterproof WT120C G3,
toolless installation, waterproof
external connector (WEC3)



CoreLine waterproof gen3,
WT120C G3, top view



CoreLine waterproof gen3,
WT120C G3, easy driver
replacement




CoreLine Waterproof WT120C G2
PCU-10DPP




CoreLine waterproof gen3, WT120C
G3, dimmable motion sensor



CoreLine Waterproof WT120C G2
PCU-12DPP



CoreLine waterproof gen3,
WT120C G3, All_in, lumen switch



CoreLine waterproof gen3, WT120C
G3, dimmable motion sensor

CoreLine waterproof gen3


Product details




CoreLine waterproof gen3, WT120C G3, ServiceTag, QR code for easy access



CoreLine waterproof WT120C G3, toolless installation, waterproof external connector (WEC3)



CoreLine Waterproof WT120C G2 PCU-2DPP



CoreLine waterproof gen3, WT120C G3, EL pack (EM300V) placement




CoreLine waterproof gen3, WT120C G3, easy LED board replacement



CoreLine waterproof WT120C G3, toolless installation, waterproof external connector (WEC3)



CoreLine waterproof G3, WT120C G3




CoreLine waterproof gen3, WT120C G3, easy driver replacement

CoreLine waterproof gen3

Product details



CoreLine waterproof gen3, WT120C G3, easy LED board replacement



CoreLine waterproof WT120C G3, toolless installation, clic-fix push-in connector



CoreLine waterproof G3, WT120C G3



CoreLine waterproof G3, WT120C G3

General Information

| | |
|----------------------|--------|
| Driver included | Yes |
| Number of gear units | 1 unit |

Light Technical

| | |
|-----------------------------|-------------|
| Color rendering index (CRI) | >80 |
| Optic type | Symmetrical |

Operating and Electrical

| | |
|----------------------|----------------|
| Protection class IEC | Safety class I |
| Input Voltage | 220-240 V |
| Line Frequency | 0/50/60 Hz |

Mechanical and Housing

| | |
|------------------------------|------|
| Housing Color | Grey |
| Mech. impact protection code | IK08 |
| Ingress protection code | IP66 |

Approval and Application

| | |
|--|---|
| Ambient temperature range | -20 °C to 40 °C |
| CE mark | Yes |
| Flammability mark | For mounting on easily flammable surfaces |
| Glow-wire test | Temperature 850 °C, duration 30 s |
| Stroboscopic effect visibility measure (SVM) | 0.4 |

Light Technical

| Order Code | Full Product Name | All-in Type | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|------------|--|---------------------|------------------------------------|---------------------------------|---------------|
| 39005900 | WT121C G3 35_43_51_60S/840 PSU L1500 | All-in, Multi Lumen | 4000 K | 155 lm/W | 3,300 lm |
| 39013400 | WT120C G3 35_43_51_60S/830 PSU L1500 | All-in, Multi Lumen | 3000 K | 157 lm/W | 3,400 lm |
| 39015800 | WT120C G3 35_43_51_60S/865 PSU L1500 | All-in, Multi Lumen | 6500 K | 162 lm/W | 3,500 lm |
| 35977300 | WT120C G3 27S/840 PSU TW3 L1200 | - | 4000 K | 159 lm/W | 2,700 lm |
| 35978000 | WT120C G3 40S/840 PSU TW3 L1200 | - | 4000 K | 160 lm/W | 4,000 lm |
| 35983400 | WT120C G3 27S/840 PSR MDUPHW L1200 | - | 4000 K | 159 lm/W | 2,700 lm |
| 35986500 | WT120C G3 27S/840 PSR MDUPHW TW3 L1200 | - | 4000 K | 159 lm/W | 2,700 lm |
| 35988900 | WT120C G3 40S/840 PSR MDUPHW TW3 L1200 | - | 4000 K | 160 lm/W | 4,000 lm |
| 35991900 | WT120C G3 80S/840 PSD L1200 | - | 4000 K | 160 lm/W | 8,000 lm |
| 35993300 | WT120C G3 80S/840 WIA L1200 | - | 4000 K | 160 lm/W | 8,000 lm |
| 35994000 | WT120C G3 80S/840 WIA TW3 L1200 | - | 4000 K | 160 lm/W | 8,000 lm |
| 35997100 | WT120C G3 40S/840 UE PSU L1200 | - | 4000 K | 187 lm/W | 4,200 lm |
| 39000400 | WT120C G3 80S/840 UE PSD L1200 | - | 4000 K | 186 lm/W | 8,200 lm |

CoreLine waterproof gen3

| Order Code | Full Product Name | All-in Type | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|------------|---|---------------------|------------------------------------|---------------------------------|---------------|
| 39002800 | WT121C G3 40S/840 PSU L1200 | - | 4000 K | 152 lm/W | 3,800 lm |
| 39008000 | WT120C G3 40S/840 PSD TW3 L1200 | - | 4000 K | 160 lm/W | 4,000 lm |
| 39009700 | WT120C G3 80S/840 PSD TW3 L1200 | - | 4000 K | 160 lm/W | 8,000 lm |
| 39016500 | WT120C G3 40S/840 PSU ELB3 L1200 | - | 4000 K | 160 lm/W | 4,000 lm |
| 33308799 | WT120C G3 40S/840 PSU L1200 | - | 4000 K | 160 lm/W | 4,000 lm |
| 33321699 | WT120C G3 40S/840 PSU WEC3 L1200 | - | 4000 K | 160 lm/W | 4,000 lm |
| 39004200 | WT121C G3 27_33_39_46S/840 PSU L1200 | All-in, Multi Lumen | 4000 K | 158 lm/W | 2,600 lm |
| 39012700 | WT120C G3 27_33_39_46S/830 PSU L1200 | All-in, Multi Lumen | 3000 K | 156 lm/W | 2,600 lm |
| 39014100 | WT120C G3 27_33_39_46S/865 PSU L1200 | All-in, Multi Lumen | 6500 K | 163 lm/W | 2,700 lm |
| 35982700 | WT120C G3 20S/840 PSR MDUPHW L600 | - | 4000 K | 154 lm/W | 2,000 lm |
| 35990200 | WT120C G3 40S/840 PSD L600 | - | 4000 K | 160 lm/W | 4,000 lm |
| 39007300 | WT120C G3 40S/840 PSD TW1 L600 | - | 4000 K | 160 lm/W | 4,000 lm |
| 39006600 | WT120C G3 24_29_35_40S/840 PSU TW3 L600 | All-in, Multi Lumen | 4000 K | 164 lm/W | 2,400 lm |
| 35979700 | WT120C G3 34S/840 PSU TW3 L1500 | - | 4000 K | 158 lm/W | 3,400 lm |
| 35980300 | WT120C G3 60S/840 PSU TW3 L1500 | - | 4000 K | 160 lm/W | 6,000 lm |
| 35981000 | WT120C G3 80S/840 PSU TW3 L1500 | - | 4000 K | 160 lm/W | 8,000 lm |
| 35984100 | WT120C G3 34S/840 PSR MDUPHW L1500 | - | 4000 K | 158 lm/W | 3,400 lm |
| 35985800 | WT120C G3 80S/840 PSR MDUPHW L1500 | - | 4000 K | 160 lm/W | 8,000 lm |
| 35987200 | WT120C G3 34S/840 PSR MDUPHW TW3 L1500 | - | 4000 K | 158 lm/W | 3,400 lm |
| 35989600 | WT120C G3 60S/840 PSR MDUPHW TW3 L1500 | - | 4000 K | 160 lm/W | 6,000 lm |
| 35992600 | WT120C G3 120S/840 PSD L1500 | - | 4000 K | 160 lm/W | 12,000 lm |
| 35995700 | WT120C G3 80S/840 WIA TW3 L1500 | - | 4000 K | 160 lm/W | 8,000 lm |
| 35996400 | WT120C G3 80S/840 WIA L1500 | - | 4000 K | 160 lm/W | 8,000 lm |

CoreLine waterproof gen3

| Order Code | Full Product Name | All-in Type | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|------------|----------------------------------|-------------|------------------------------------|---------------------------------|---------------|
| 35998800 | WT120C G3 60S/840 UE PSU L1500 | - | 4000 K | 188 lm/W | 6,000 lm |
| 35999500 | WT120C G3 140S/840 UE PSU L1500 | - | 4000 K | 189 lm/W | 14,000 lm |
| 39001100 | WT120C G3 80S/840 UE PSD L1500 | - | 4000 K | 186 lm/W | 8,200 lm |
| 39003500 | WT121C G3 60S/840 PSU L1500 | - | 4000 K | 155 lm/W | 5,800 lm |
| 39010300 | WT120C G3 60S/840 PSD TW3 L1500 | - | 4000 K | 160 lm/W | 6,000 lm |
| 39011000 | WT120C G3 80S/840 PSD TW3 L1500 | - | 4000 K | 160 lm/W | 8,000 lm |
| 39017200 | WT120C G3 60S/840 PSU ELB3 L1500 | - | 4000 K | 160 lm/W | 6,000 lm |
| 33309499 | WT120C G3 60S/840 PSU L1500 | - | 4000 K | 160 lm/W | 6,000 lm |
| 33310099 | WT120C G3 80S/840 PSU L1500 | - | 4000 K | 160 lm/W | 8,000 lm |
| 33315599 | WT120C G3 120S/840 PSU L1500 | - | 4000 K | 160 lm/W | 12,000 lm |
| 33323099 | WT120C G3 60S/840 PSU WEC3 L1500 | - | 4000 K | 160 lm/W | 6,000 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Suitable for random switching | Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|------------|--|-------------------|--|------------|--|-------------------|--|
| 39005900 | WT121C G3 35_43_51_60S/840 PSU L1500 | 37.5 W | Yes | 35988900 | WT120C G3 40S/840 PSR MDUPHW TW3 L1200 | 25 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 39013400 | WT120C G3 35_43_51_60S/830 PSU L1500 | 37.5 W | Yes | 35991900 | WT120C G3 80S/840 PSD L1200 | 50 W | Yes |
| 39015800 | WT120C G3 35_43_51_60S/865 PSU L1500 | 37.5 W | Yes | 35993300 | WT120C G3 80S/840 WIA L1200 | 50 W | Yes |
| 35977300 | WT120C G3 27S/840 PSU TW3 L1200 | 17 W | Yes | 35994000 | WT120C G3 80S/840 WIA TW3 L1200 | 50 W | Yes |
| 35978000 | WT120C G3 40S/840 PSU TW3 L1200 | 25 W | Yes | 35997100 | WT120C G3 40S/840 UE PSU L1200 | 22.5 W | Yes |
| 35983400 | WT120C G3 27S/840 PSR MDUPHW L1200 | 17 W | Yes (relates to presence/movement detection and daylight harvesting) | 39000400 | WT120C G3 80S/840 UE PSD L1200 | 44 W | Yes |
| 35986500 | WT120C G3 27S/840 PSR MDUPHW TW3 L1200 | 17 W | Yes (relates to presence/movement detection and daylight harvesting) | 39002800 | WT121C G3 40S/840 PSU L1200 | 25 W | Yes |
| | | | | 39008000 | WT120C G3 40S/840 PSD TW3 L1200 | 25 W | Yes |
| | | | | 39009700 | WT120C G3 80S/840 PSD TW3 L1200 | 50 W | Yes |
| | | | | 39016500 | WT120C G3 40S/840 PSU ELB3 L1200 | 25 W | Yes |
| | | | | 33308799 | WT120C G3 40S/840 PSU L1200 | 25 W | Yes |

CoreLine waterproof gen3

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|------------|---|-------------------|--|
| 33321699 | WT120C G3 40S/840 PSU WEC3 L1200 | 25 W | Yes |
| 39004200 | WT121C G3 27_33_39_46S/840 PSU L1200 | 28.5 W | Yes |
| 39012700 | WT120C G3 27_33_39_46S/830 PSU L1200 | 28.5 W | Yes |
| 39014100 | WT120C G3 27_33_39_46S/865 PSU L1200 | 28.5 W | Yes |
| 35982700 | WT120C G3 20S/840 PSR MDUPHW L600 | 13 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 35990200 | WT120C G3 40S/840 PSD L600 | 25 W | Yes |
| 39007300 | WT120C G3 40S/840 PSD TW1 L600 | 25 W | Yes |
| 39006600 | WT120C G3 24_29_35_40S/840 PSU TW3 L600 | 25 W | Yes |
| 35979700 | WT120C G3 34S/840 PSU TW3 L1500 | 21.5 W | Yes |
| 35980300 | WT120C G3 60S/840 PSU TW3 L1500 | 37.5 W | Yes |
| 35981000 | WT120C G3 80S/840 PSU TW3 L1500 | 50 W | Yes |
| 35984100 | WT120C G3 34S/840 PSR MDUPHW L1500 | 21.5 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 35985800 | WT120C G3 80S/840 PSR MDUPHW L1500 | 50 W | Yes (relates to presence/movement detection and |

| Order Code | Full Product Name | Power Consumption | Suitable for random switching |
|------------|--|-------------------|--|
| | | | daylight harvesting) |
| 35987200 | WT120C G3 34S/840 PSR MDUPHW TW3 L1500 | 21.5 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 35989600 | WT120C G3 60S/840 PSR MDUPHW TW3 L1500 | 37.5 W | Yes (relates to presence/movement detection and daylight harvesting) |
| 35992600 | WT120C G3 120S/840 PSD L1500 | 75 W | Yes |
| 35995700 | WT120C G3 80S/840 WIA TW3 L1500 | 50 W | Yes |
| 35996400 | WT120C G3 80S/840 WIA L1500 | 50 W | Yes |
| 35998800 | WT120C G3 60S/840 UE PSU L1500 | 32 W | Yes |
| 35999500 | WT120C G3 140S/840 UE PSU L1500 | 74 W | Yes |
| 39001100 | WT120C G3 80S/840 UE PSD L1500 | 44 W | Yes |
| 39003500 | WT121C G3 60S/840 PSU L1500 | 37.5 W | Yes |
| 39010300 | WT120C G3 60S/840 PSD TW3 L1500 | 37.5 W | Yes |
| 39011000 | WT120C G3 80S/840 PSD TW3 L1500 | 50 W | Yes |
| 39017200 | WT120C G3 60S/840 PSU ELB3 L1500 | 37.5 W | Yes |
| 33309499 | WT120C G3 60S/840 PSU L1500 | 37.5 W | Yes |
| 33310099 | WT120C G3 80S/840 PSU L1500 | 50 W | Yes |
| 33315599 | WT120C G3 120S/840 PSU L1500 | 75 W | Yes |
| 33323099 | WT120C G3 60S/840 PSU WEC3 L1500 | 37.5 W | Yes |

Controls and Dimming

| Order Code | Full Product Name | Dimmable | Embedded control |
|------------|--------------------------------------|----------|---------------------------------|
| 39005900 | WT121C G3 35_43_51_60S/840 PSU L1500 | No | - |
| 39013400 | WT120C G3 35_43_51_60S/830 PSU L1500 | No | - |
| 39015800 | WT120C G3 35_43_51_60S/865 PSU L1500 | No | - |
| 35977300 | WT120C G3 27S/840 PSU TW3 L1200 | No | - |
| 35978000 | WT120C G3 40S/840 PSU TW3 L1200 | No | - |
| 35983400 | WT120C G3 27S/840 PSR MDUPHW L1200 | Yes | Programmable movement and light |

| Order Code | Full Product Name | Dimmable | Embedded control |
|------------|--|----------|---|
| | | | sensor with wireless grouping |
| 35986500 | WT120C G3 27S/840 PSR MDUPHW TW3 L1200 | Yes | Programmable movement and light sensor with wireless grouping |
| 35988900 | WT120C G3 40S/840 PSR MDUPHW TW3 L1200 | Yes | Programmable movement and light sensor with wireless grouping |

CoreLine waterproof gen3

| Order Code | Full Product Name | Dimmable | Embedded control |
|------------|---|----------|---|
| 35991900 | WT120C G3 80S/840 PSD L1200 | Yes | - |
| 35993300 | WT120C G3 80S/840 WIA L1200 | Yes | - |
| 35994000 | WT120C G3 80S/840 WIA TW3 L1200 | Yes | - |
| 35997100 | WT120C G3 40S/840 UE PSU L1200 | No | - |
| 39000400 | WT120C G3 80S/840 UE PSD L1200 | Yes | - |
| 39002800 | WT121C G3 40S/840 PSU L1200 | No | - |
| 39008000 | WT120C G3 40S/840 PSD TW3 L1200 | Yes | - |
| 39009700 | WT120C G3 80S/840 PSD TW3 L1200 | Yes | - |
| 39016500 | WT120C G3 40S/840 PSU ELB3 L1200 | No | - |
| 33308799 | WT120C G3 40S/840 PSU L1200 | No | - |
| 33321699 | WT120C G3 40S/840 PSU WEC3 L1200 | No | - |
| 39004200 | WT121C G3 27_33_39_46S/840 PSU L1200 | No | - |
| 39012700 | WT120C G3 27_33_39_46S/830 PSU L1200 | No | - |
| 39014100 | WT120C G3 27_33_39_46S/865 PSU L1200 | No | - |
| 35982700 | WT120C G3 20S/840 PSR MDUPHW L600 | Yes | Programmable movement and light sensor with wireless grouping |
| 35990200 | WT120C G3 40S/840 PSD L600 | Yes | - |
| 39007300 | WT120C G3 40S/840 PSD TW1 L600 | Yes | - |
| 39006600 | WT120C G3 24_29_35_40S/840 PSU TW3 L600 | No | - |
| 35979700 | WT120C G3 34S/840 PSU TW3 L1500 | No | - |
| 35980300 | WT120C G3 60S/840 PSU TW3 L1500 | No | - |
| 35981000 | WT120C G3 80S/840 PSU TW3 L1500 | No | - |
| 35984100 | WT120C G3 34S/840 PSR MDUPHW L1500 | Yes | Programmable movement and light sensor with wireless grouping |

| Order Code | Full Product Name | Dimmable | Embedded control |
|------------|--|----------|---|
| 35985800 | WT120C G3 80S/840 PSR MDUPHW L1500 | Yes | Programmable movement and light sensor with wireless grouping |
| 35987200 | WT120C G3 34S/840 PSR MDUPHW TW3 L1500 | Yes | Programmable movement and light sensor with wireless grouping |
| 35989600 | WT120C G3 60S/840 PSR MDUPHW TW3 L1500 | Yes | Programmable movement and light sensor with wireless grouping |
| 35992600 | WT120C G3 120S/840 PSD L1500 | Yes | - |
| 35995700 | WT120C G3 80S/840 WIA TW3 L1500 | Yes | - |
| 35996400 | WT120C G3 80S/840 WIA L1500 | Yes | - |
| 35998800 | WT120C G3 60S/840 UE PSU L1500 | No | - |
| 35999500 | WT120C G3 140S/840 UE PSU L1500 | No | - |
| 39001100 | WT120C G3 80S/840 UE PSD L1500 | Yes | - |
| 39003500 | WT121C G3 60S/840 PSU L1500 | No | - |
| 39010300 | WT120C G3 60S/840 PSD TW3 L1500 | Yes | - |
| 39011000 | WT120C G3 80S/840 PSD TW3 L1500 | Yes | - |
| 39017200 | WT120C G3 60S/840 PSU ELB3 L1500 | No | - |
| 33309499 | WT120C G3 60S/840 PSU L1500 | No | - |
| 33310099 | WT120C G3 80S/840 PSU L1500 | No | - |
| 33315599 | WT120C G3 120S/840 PSU L1500 | No | - |
| 33323099 | WT120C G3 60S/840 PSU WEC3 L1500 | No | - |

Emergency Operation

| Order Code | Full Product Name | Central Emergency | Emergency lighting |
|------------|--------------------------------------|-------------------|---|
| 39005900 | WT121C G3 35_43_51_60S/840 PSU L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39013400 | WT120C G3 35_43_51_60S/830 PSU L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39015800 | WT120C G3 35_43_51_60S/865 PSU L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35977300 | WT120C G3 27S/840 PSU TW3 L1200 | No | Self-contained emergency lighting is possible when used |

| Order Code | Full Product Name | Central Emergency | Emergency lighting |
|------------|--|-------------------|---|
| 35978000 | WT120C G3 40S/840 PSU TW3 L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35983400 | WT120C G3 27S/840 PSR MDUPHW L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35986500 | WT120C G3 27S/840 PSR MDUPHW TW3 L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |

CoreLine waterproof gen3

| Order Code | Full Product Name | Central | |
|------------|--|-----------|---|
| | | Emergency | Emergency lighting |
| 35988900 | WT120C G3 40S/840 PSR MDUPHW TW3 L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35991900 | WT120C G3 80S/840 PSD L1200 | Yes | DC operated central emergency lighting |
| 35993300 | WT120C G3 80S/840 WIA L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35994000 | WT120C G3 80S/840 WIA TW3 L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35997100 | WT120C G3 40S/840 UE PSU L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39000400 | WT120C G3 80S/840 UE PSD L1200 | Yes | DC operated central emergency lighting |
| 39002800 | WT121C G3 40S/840 PSU L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39008000 | WT120C G3 40S/840 PSD TW3 L1200 | Yes | DC operated central emergency lighting |
| 39009700 | WT120C G3 80S/840 PSD TW3 L1200 | Yes | DC operated central emergency lighting |
| 39016500 | WT120C G3 40S/840 PSU ELB3 L1200 | No | Emergency lighting 3 hours duration basic version |
| 33308799 | WT120C G3 40S/ 840 PSU L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 33321699 | WT120C G3 40S/840 PSU WEC3 L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39004200 | WT121C G3 27_33_39_46S/840 PSU L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39012700 | WT120C G3 27_33_39_46S/830 PSU L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39014100 | WT120C G3 27_33_39_46S/865 PSU L1200 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |

| Order Code | Full Product Name | Central | |
|------------|--|-----------|---|
| | | Emergency | Emergency lighting |
| 35982700 | WT120C G3 20S/840 PSR MDUPHW L600 | No | - |
| 35990200 | WT120C G3 40S/840 PSD L600 | Yes | DC operated central emergency lighting |
| 39007300 | WT120C G3 40S/ 840 PSD TW1 L600 | Yes | DC operated central emergency lighting |
| 39006600 | WT120C G3 24_29_35_40S/ 840 PSU TW3 L600 | No | - |
| 35979700 | WT120C G3 34S/840 PSU TW3 L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35980300 | WT120C G3 60S/840 PSU TW3 L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35981000 | WT120C G3 80S/840 PSU TW3 L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35984100 | WT120C G3 34S/840 PSR MDUPHW L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35985800 | WT120C G3 80S/840 PSR MDUPHW L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35987200 | WT120C G3 34S/840 PSR MDUPHW TW3 L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35989600 | WT120C G3 60S/840 PSR MDUPHW TW3 L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35992600 | WT120C G3 120S/840 PSD L1500 | Yes | DC operated central emergency lighting |
| 35995700 | WT120C G3 80S/840 WIA TW3 L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35996400 | WT120C G3 80S/840 WIA L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 35998800 | WT120C G3 60S/840 UE PSU L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |

CoreLine waterproof gen3

| Order Code | Full Product Name | Central | |
|------------|----------------------------------|-----------|---|
| | | Emergency | Emergency lighting |
| 35999500 | WT120C G3 140S/840 UE PSU L1500 | No | - |
| 39001100 | WT120C G3 80S/840 UE PSD L1500 | Yes | DC operated central emergency lighting |
| 39003500 | WT121C G3 60S/840 PSU L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 39010300 | WT120C G3 60S/840 PSD TW3 L1500 | Yes | DC operated central emergency lighting |
| 39011000 | WT120C G3 80S/840 PSD TW3 L1500 | Yes | DC operated central emergency lighting |
| 39017200 | WT120C G3 60S/840 PSU ELB3 L1500 | No | Emergency lighting 3 hours duration basic version |

| Order Code | Full Product Name | Central | |
|------------|----------------------------------|-----------|---|
| | | Emergency | Emergency lighting |
| 33309499 | WT120C G3 60S/840 PSU L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 33310099 | WT120C G3 80S/840 PSU L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |
| 33315599 | WT120C G3 120S/840 PSU L1500 | No | - |
| 33323099 | WT120C G3 60S/840 PSU WEC3 L1500 | No | Self-contained emergency lighting is possible when used with a compatible battery kit accessory |

Approval and Application

| Order Code | Full Product Name | ENEC mark |
|------------|--|------------------|
| 39005900 | WT121C G3 35_43_51_60S/840 PSU L1500 | ENEC mark |
| 39013400 | WT120C G3 35_43_51_60S/830 PSU L1500 | ENEC mark |
| 39015800 | WT120C G3 35_43_51_60S/865 PSU L1500 | ENEC mark |
| 35977300 | WT120C G3 27S/840 PSU TW3 L1200 | ENEC mark |
| 35978000 | WT120C G3 40S/840 PSU TW3 L1200 | ENEC mark |
| 35983400 | WT120C G3 27S/840 PSR MDUPHW L1200 | ENEC mark |
| 35986500 | WT120C G3 27S/840 PSR MDUPHW TW3 L1200 | ENEC mark |
| 35988900 | WT120C G3 40S/840 PSR MDUPHW TW3 L1200 | ENEC mark |
| 35991900 | WT120C G3 80S/840 PSD L1200 | ENEC mark |
| 35993300 | WT120C G3 80S/840 WIA L1200 | ENEC mark |
| 35994000 | WT120C G3 80S/840 WIA TW3 L1200 | ENEC mark |
| 35997100 | WT120C G3 40S/840 UE PSU L1200 | ENEC mark |
| 39000400 | WT120C G3 80S/840 UE PSD L1200 | ENEC mark |
| 39002800 | WT121C G3 40S/840 PSU L1200 | ENEC mark |
| 39008000 | WT120C G3 40S/840 PSD TW3 L1200 | ENEC mark |
| 39009700 | WT120C G3 80S/840 PSD TW3 L1200 | ENEC mark |
| 39016500 | WT120C G3 40S/840 PSU ELB3 L1200 | ENEC mark |
| 33308799 | WT120C G3 40S/840 PSU L1200 | ENEC mark |
| 33321699 | WT120C G3 40S/840 PSU WEC3 L1200 | ENEC mark |
| 39004200 | WT121C G3 27_33_39_46S/840 PSU L1200 | ENEC mark |
| 39012700 | WT120C G3 27_33_39_46S/830 PSU L1200 | ENEC mark |
| 39014100 | WT120C G3 27_33_39_46S/865 PSU L1200 | ENEC mark |
| 35982700 | WT120C G3 20S/840 PSR MDUPHW L600 | KEMA Netherlands |
| 35990200 | WT120C G3 40S/840 PSD L600 | ENEC mark |

| Order Code | Full Product Name | ENEC mark |
|------------|---|------------------|
| 39007300 | WT120C G3 40S/840 PSD TW1 L600 | KEMA Netherlands |
| 39006600 | WT120C G3 24_29_35_40S/840 PSU TW3 L600 | ENEC mark |
| 35979700 | WT120C G3 34S/840 PSU TW3 L1500 | ENEC mark |
| 35980300 | WT120C G3 60S/840 PSU TW3 L1500 | ENEC mark |
| 35981000 | WT120C G3 80S/840 PSU TW3 L1500 | ENEC mark |
| 35984100 | WT120C G3 34S/840 PSR MDUPHW L1500 | ENEC mark |
| 35985800 | WT120C G3 80S/840 PSR MDUPHW L1500 | ENEC mark |
| 35987200 | WT120C G3 34S/840 PSR MDUPHW TW3 L1500 | ENEC mark |
| 35989600 | WT120C G3 60S/840 PSR MDUPHW TW3 L1500 | ENEC mark |
| 35992600 | WT120C G3 120S/840 PSD L1500 | ENEC mark |
| 35995700 | WT120C G3 80S/840 WIA TW3 L1500 | ENEC mark |
| 35996400 | WT120C G3 80S/840 WIA L1500 | ENEC mark |
| 35998800 | WT120C G3 60S/840 UE PSU L1500 | ENEC mark |
| 35999500 | WT120C G3 140S/840 UE PSU L1500 | ENEC mark |
| 39001100 | WT120C G3 80S/840 UE PSD L1500 | ENEC mark |
| 39003500 | WT121C G3 60S/840 PSU L1500 | ENEC mark |
| 39010300 | WT120C G3 60S/840 PSD TW3 L1500 | ENEC mark |
| 39011000 | WT120C G3 80S/840 PSD TW3 L1500 | ENEC mark |
| 39017200 | WT120C G3 60S/840 PSU ELB3 L1500 | ENEC mark |
| 33309499 | WT120C G3 60S/840 PSU L1500 | ENEC mark |
| 33310099 | WT120C G3 80S/840 PSU L1500 | ENEC mark |
| 33315599 | WT120C G3 120S/840 PSU L1500 | ENEC mark |
| 33323099 | WT120C G3 60S/840 PSU WEC3 L1500 | ENEC mark |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name | Initial chromaticity | Luminous flux |
|------------|--------------------------------------|----------------------|---------------|
| | | | tolerance |
| 39005900 | WT121C G3 35_43_51_60S/840 PSU L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |

| Order Code | Full Product Name | Initial chromaticity | Luminous flux |
|------------|--------------------------------------|----------------------|---------------|
| | | | tolerance |
| 39013400 | WT120C G3 35_43_51_60S/830 PSU L1500 | (0.43, 0.40) SDCM<3 | +15%/-5% |

CoreLine waterproof gen3

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|------------|--|----------------------|-------------------------|
| 39015800 | WT120C G3 35_43_51_60S/865 PSU L1500 | (0.31, 0.32) SDCM<3 | +15%/-5% |
| 35977300 | WT120C G3 27S/840 PSU TW3 L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35978000 | WT120C G3 40S/840 PSU TW3 L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35983400 | WT120C G3 27S/840 PSR MDUPHW L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35986500 | WT120C G3 27S/840 PSR MDUPHW TW3 L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35988900 | WT120C G3 40S/840 PSR MDUPHW TW3 L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35991900 | WT120C G3 80S/840 PSD L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35993300 | WT120C G3 80S/840 WIA L1200 | (0.38; 0.37) SDCM<3 | +15%/-5% |
| 35994000 | WT120C G3 80S/840 WIA TW3 L1200 | (0.38; 0.37) SDCM<3 | +15%/-5% |
| 35997100 | WT120C G3 40S/840 UE PSU L1200 | (0.38, 0.37) SDCM<3 | -10% / +10% |
| 39000400 | WT120C G3 80S/840 UE PSD L1200 | (0.38, 0.37) SDCM<3 | -10% / +10% |
| 39002800 | WT121C G3 40S/840 PSU L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39008000 | WT120C G3 40S/840 PSD TW3 L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39009700 | WT120C G3 80S/840 PSD TW3 L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39016500 | WT120C G3 40S/840 PSU ELB3 L1200 | (0.38; 0.37) SDCM<3 | +15%/-5% |
| 33308799 | WT120C G3 40S/840 PSU L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 33321699 | WT120C G3 40S/840 PSU WEC3 L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39004200 | WT121C G3 27_33_39_46S/840 PSU L1200 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39012700 | WT120C G3 27_33_39_46S/830 PSU L1200 | (0.43, 0.40) SDCM<3 | +15%/-5% |
| 39014100 | WT120C G3 27_33_39_46S/865 PSU L1200 | (0.31, 0.32) SDCM<3 | +15%/-5% |
| 35982700 | WT120C G3 20S/840 PSR MDUPHW L600 | (0.38, 0.37) SDCM<3 | +15%/-5% |

| Order Code | Full Product Name | Initial chromaticity | Luminous flux tolerance |
|------------|---|----------------------|-------------------------|
| 35990200 | WT120C G3 40S/840 PSD L600 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39007300 | WT120C G3 40S/840 PSD TW1 L600 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39006600 | WT120C G3 24_29_35_40S/840 PSU TW3 L600 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35979700 | WT120C G3 34S/840 PSU TW3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35980300 | WT120C G3 60S/840 PSU TW3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35981000 | WT120C G3 80S/840 PSU TW3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35984100 | WT120C G3 34S/840 PSR MDUPHW L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35985800 | WT120C G3 80S/840 PSR MDUPHW L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35987200 | WT120C G3 34S/840 PSR MDUPHW TW3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35989600 | WT120C G3 60S/840 PSR MDUPHW TW3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35992600 | WT120C G3 120S/840 PSD L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 35995700 | WT120C G3 80S/840 WIA TW3 L1500 | (0.38; 0.37) SDCM<3 | +15%/-5% |
| 35996400 | WT120C G3 80S/840 WIA L1500 | (0.38; 0.37) SDCM<3 | +15%/-5% |
| 35998800 | WT120C G3 60S/840 UE PSU L1500 | (0.38, 0.37) SDCM<3 | -10% / +10% |
| 35999500 | WT120C G3 140S/840 UE PSU L1500 | (0.38, 0.37) SDCM<3 | -10% / +10% |
| 39001100 | WT120C G3 80S/840 UE PSD L1500 | (0.38, 0.37) SDCM<3 | -10% / +10% |
| 39003500 | WT121C G3 60S/840 PSU L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39010300 | WT120C G3 60S/840 PSD TW3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39011000 | WT120C G3 80S/840 PSD TW3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 39017200 | WT120C G3 60S/840 PSU ELB3 L1500 | (0.38; 0.37) SDCM<3 | +15%/-5% |
| 33309499 | WT120C G3 60S/840 PSU L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 33310099 | WT120C G3 80S/840 PSU L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 33315599 | WT120C G3 120S/840 PSU L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |
| 33323099 | WT120C G3 60S/840 PSU WEC3 L1500 | (0.38, 0.37) SDCM<3 | +15%/-5% |

Product Data

| Order Code | Full Product Name | Product family code |
|------------|--|---------------------|
| 39005900 | WT121C G3 35_43_51_60S/840 PSU L1500 | - |
| 39013400 | WT120C G3 35_43_51_60S/830 PSU L1500 | - |
| 39015800 | WT120C G3 35_43_51_60S/865 PSU L1500 | - |
| 35977300 | WT120C G3 27S/840 PSU TW3 L1200 | - |
| 35978000 | WT120C G3 40S/840 PSU TW3 L1200 | - |
| 35983400 | WT120C G3 27S/840 PSR MDUPHW L1200 | - |
| 35986500 | WT120C G3 27S/840 PSR MDUPHW TW3 L1200 | - |
| 35988900 | WT120C G3 40S/840 PSR MDUPHW TW3 L1200 | - |
| 35991900 | WT120C G3 80S/840 PSD L1200 | - |
| 35993300 | WT120C G3 80S/840 WIA L1200 | WT120C_G |
| 35994000 | WT120C G3 80S/840 WIA TW3 L1200 | WT120C_G |
| 35997100 | WT120C G3 40S/840 UE PSU L1200 | - |
| 39000400 | WT120C G3 80S/840 UE PSD L1200 | - |
| 39002800 | WT121C G3 40S/840 PSU L1200 | - |
| 39008000 | WT120C G3 40S/840 PSD TW3 L1200 | - |


| Order Code | Full Product Name | Product family code |
|------------|---|---------------------|
| 39009700 | WT120C G3 80S/840 PSD TW3 L1200 | - |
| 39016500 | WT120C G3 40S/840 PSU ELB3 L1200 | WT120C_G |
| 33308799 | WT120C G3 40S/840 PSU L1200 | - |
| 33321699 | WT120C G3 40S/840 PSU WEC3 L1200 | - |
| 39004200 | WT121C G3 27_33_39_46S/840 PSU L1200 | - |
| 39012700 | WT120C G3 27_33_39_46S/830 PSU L1200 | - |
| 39014100 | WT120C G3 27_33_39_46S/865 PSU L1200 | - |
| 35982700 | WT120C G3 20S/840 PSR MDUPHW L600 | - |
| 35990200 | WT120C G3 40S/840 PSD L600 | - |
| 39007300 | WT120C G3 40S/840 PSD TW1 L600 | - |
| 39006600 | WT120C G3 24_29_35_40S/840 PSU TW3 L600 | - |
| 35979700 | WT120C G3 34S/840 PSU TW3 L1500 | - |
| 35980300 | WT120C G3 60S/840 PSU TW3 L1500 | - |
| 35981000 | WT120C G3 80S/840 PSU TW3 L1500 | - |
| 35984100 | WT120C G3 34S/840 PSR MDUPHW L1500 | - |

CoreLine waterproof gen3


| Order Code | Full Product Name | Product family code |
|------------|--|---------------------|
| 35985800 | WT120C G3 80S/840 PSR MDUPHW L1500 | - |
| 35987200 | WT120C G3 34S/840 PSR MDUPHW TW3 L1500 | - |
| 35989600 | WT120C G3 60S/840 PSR MDUPHW TW3 L1500 | - |
| 35992600 | WT120C G3 120S/840 PSD L1500 | - |
| 35995700 | WT120C G3 80S/840 WIA TW3 L1500 | WT120C_G |
| 35996400 | WT120C G3 80S/840 WIA L1500 | WT120C_G |
| 35998800 | WT120C G3 60S/840 UE PSU L1500 | - |
| 35999500 | WT120C G3 140S/840 UE PSU L1500 | - |
| 39001100 | WT120C G3 80S/840 UE PSD L1500 | - |

| Order Code | Full Product Name | Product family code |
|------------|----------------------------------|---------------------|
| 39003500 | WT121C G3 60S/840 PSU L1500 | - |
| 39010300 | WT120C G3 60S/840 PSD TW3 L1500 | - |
| 39011000 | WT120C G3 80S/840 PSD TW3 L1500 | - |
| 39017200 | WT120C G3 60S/840 PSU ELB3 L1500 | WT120C_G |
| 33309499 | WT120C G3 60S/840 PSU L1500 | - |
| 33310099 | WT120C G3 80S/840 PSU L1500 | - |
| 33315599 | WT120C G3 120S/840 PSU L1500 | - |
| 33323099 | WT120C G3 60S/840 PSU WEC3 L1500 | - |


Polar Wide Diagrams




Polar Normal (separate) - 910505106533




Polar Normal (separate) - 910505106531




Polar Normal (separate) - 910505106532




Polar Normal (separate) - 910505106534




Polar Normal (separate) - 910505106538




Polar Normal (separate) - 910505106536



Polar Normal (separate) - 910505106543




Polar Normal (separate) - 910505106540




Polar Normal (separate) - 910505106542


Polar Wide Diagrams




Polar Normal (separate) - 910505106537




Polar Normal (separate) - 910505106535




Polar Normal (separate) - 910505106541




Polar Normal (separate) - 910505106539




Polar Normal (separate) - 910505106546




Polar Normal (separate) - WT120CN - 910505106547




Polar Normal (separate) - 910505106545




Polar Normal (separate) - 910505106565




Polar Normal (separate) - 910505106551



Polar Normal (separate) - 910505106544




Polar Normal (separate) - WT120CN - 910505106549




Polar Normal (separate) - WT120CN - 910505106550


Polar Wide Diagrams




Polar Normal (separate) - 910505106566




Polar Normal (separate) - 910505106553




Polar Normal (separate) - 910505106564




Polar Normal (separate) - WT120CN - 910505106548




Polar Normal (separate) - 910505106554




Polar Normal (separate) - 910505106560




Polar Normal (separate) - 910505106563




Polar Normal (separate) - 910505106552



Polar Normal (separate) - 910505106557




Polar Normal (separate) - 910505106555




Polar Normal (separate) - 910505106562


Polar Wide Diagrams




Polar Normal (separate) - 910505106561




Polar Normal (separate) - 910505106556




Polar Normal (separate) - 910505106558




Polar Normal (separate) - WT120CN - 910505106570




Polar Normal (separate) - 910505106569




Polar Normal (separate) - WT120CN - 910505106571




Polar Normal (separate) - 910505106567




Polar Normal (separate) - 910505106568




Polar Normal (separate) - 911401835888



Polar Normal (separate) - 911401835988




Polar Normal (separate) - 911401837088




Polar Normal (separate) - 911401835788

CoreLine waterproof gen3


Polar Wide Diagrams



Polar Normal (separate) - 911401836488



Polar Normal (separate) - 911401837288



Polar Normal (separate) - 910505106559

