



# Philips CoreLine waterproof – For every project where light really matters, easy to install and maintain.

## CoreLine waterproof gen3

CoreLine waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. Its trusted, well-known, and appreciated architecture establishes a new standard for installation and sustainability. A fast and easy connection is enabled by an optional pre-mounted external connector, while its efficient design ensures flexibility with plug-in emergency packs and “All-in” settings, allowing on-site adjustments to better suit various application conditions. Smart architecture facilitates straightforward, toolless parts replacement, while single-material paper packaging simplifies waste management on-site. Additionally, the optional Post-Consumer Recycled (PCR) plastic housing elevates its environmentally friendly design to the next level. CoreLine waterproof provides better wide-beam light distribution for straightforward and effective lighting. It can directly replace traditional waterproof luminaires with fluorescent lamps ranging from 18W up to 58W, delivering significant energy savings. The product family also includes a range of options, such as on/off, DALI dimming, and Interact Ready option with integrated wireless communications which can be used with Interact gateways, sensors and software, is also available in this family.

# CoreLine waterproof gen3

## Benefits

- Hassle-free and fast installation and service
- Fulfills needs of general applications projects, with robust design (IK08) and high water and dust-proof rating (IP66)
- Design with sustainability in mind — with replaceable parts, single-paper material packaging, and access to the Signify Service Tag app with service and maintenance information at hand.
- Interact Ready connectivity for smart lighting and easy commissioning.

## Features

- Long lifetime of 100,000 hours at L80 with 5 years warranty
- High efficiency: Standard versions to 160 lm/W, UltraEfficient versions of 185 lm/W
- All-in: multiple lumen packages and/or color temperatures in one luminaire (optional)
- Pre-mounted waterproof external connector (optional), long sliders, faster lock opening, toolless electrical connections, supporting ease and flexibility of installation
- Sustainability in scope: Post Consumer Recycled housing (optional) and spare parts (driver, LED boards, cover).
- Optional controls and versions: DALI dimming, integrated wireless connectivity (Interact Ready), integrated movement sensors with dimming and grouping function (MDU), Emergency Lighting (pack), through wiring 1- and 3-phase (TW1/3)

## Application

- Manufacturing
- Parking Garages
- Warehouses
- General lighting

## Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

## Versions

CoreLine waterproof G3, WT120C  
G3 All\_in



CoreLine waterproof G3, WT120C  
G3 All\_in



# CoreLine waterproof gen3

## Versions







CoreLine Waterproof WT120C G2  
PCU -



CoreLine waterproof G3, WT120C  
G3 All\_in





## Dimensional drawing



# CoreLine waterproof gen3

## Dimensional drawing



## Product details




CoreLine Waterproof WT120C G2  
PCU-7DPP




CoreLine waterproof WT120C G3,  
toolless installation, waterproof  
external connector (WEC3)



CoreLine waterproof gen3,  
WT120C G3, top view



CoreLine waterproof gen3,  
WT120C G3, easy driver  
replacement



CoreLine waterproof WT120C G3,  
All-in, CCT switch


# CoreLine waterproof gen3

## Product details

CoreLine Waterproof WT120C G2  
PCU-10DPP



CoreLine Waterproof WT120C G2  
PCU-12DPP




CoreLine waterproof gen3,  
WT120C G3, All\_in, lumen switch



CoreLine waterproof gen3,  
WT120C G3, ServiceTag, QR code  
for easy access



CoreLine waterproof WT120C G3,  
toolless installation, waterproof  
external connector (WEC3)



CoreLine Waterproof WT120C G2  
PCU-2DPP



CoreLine waterproof gen3,  
WT120C G3,EL pack (EM300V)  
placement



CoreLine waterproof gen3,  
WT120C G3, easy LED board  
replacement




CoreLine waterproof WT120C G3,  
toolless installation, waterproof  
external connector (WEC3)



CoreLine waterproof G3, WT120C  
G3

# CoreLine waterproof gen3


## Product details



CoreLine waterproof gen3,  
WT120C G3, easy driver  
replacement



CoreLine waterproof gen3,  
WT120C G3, easy LED board  
replacement



CoreLine waterproof WT120C G3,  
toolless installation, clic-fix push-  
in connector



CoreLine waterproof G3, WT120C  
G3



CoreLine waterproof G3, WT120C  
G3

# CoreLine waterproof gen3

## General Information

Driver included	Yes
Number of gear units	1 unit

## Light Technical

Optic type	Symmetrical
------------	-------------

## Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	0/50/60 Hz
Suitable for random switching	No

## Mechanical and Housing

Housing Color	Grey
Mech. impact protection code	IK08
Ingress protection code	IP66

## Approval and Application

Ambient temperature range	-20 °C to 40 °C
CE mark	Yes
ENEC mark	KEMA Netherlands
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Stroboscopic effect visibility measure (SVM)	0.4

## Light Technical (1/2)

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
39005900	WT121C G3 35_43_51_60S/840 PSU L1500	All-in, Multi Lumen	4000 K	>80	150 lm/W
39013400	WT120C G3 35_43_51_60S/830 PSU L1500	All-in, Multi Lumen	3000 K	>80	155 lm/W
33345299	WT120C G3 35_43_51_60S/840 PSU L1500	All-in, Multi Lumen	4000 K	>80	159 lm/W
33347699	WT120C G3 46_57_69_80S/840 PSU L1500	All-in, Multi Lumen	4000 K	>80	160 lm/W
33349099	WT120C G3 46_57_69_80S/840 PSU TW3 L1500	All-in, Multi Lumen	4000 K	>80	160 lm/W
33350699	WT120C G3 70_86_100_120S/840 PSU L1500	All-in, Multi Lumen	4000 K	>80	160 lm/W
33367499	WT120CG3 35_43_51_60S/830_40 PSUTW3L1500	All-in, Multi Color Temperature	3000 K	>80	159 lm/W
35991900	WT120C G3 80S/840 PSD L1200	-	4000 K	>80	160 lm/W
35997100	WT120C G3 40S/840 UE PSU L1200	-	4000 K	>80	187 lm/W
39000400	WT120C G3 80S/840 UE PSD L1200	-	4000 K	>80	186 lm/W
39002800	WT121C G3 40S/840 PSU L1200	-	4000 K	>80	152 lm/W
39009700	WT120C G3 80S/840 PSD TW3 L1200	-	4000 K	>80	160 lm/W
33306399	WT120C G3 27S/840 PSU L1200	-	4000 K	>80	159 lm/W
33308799	WT120C G3 40S/840 PSU L1200	-	4000 K	>80	160 lm/W
33312499	WT120C G3 60S/840 PSU L1200	-	4000 K	>80	160 lm/W
33313199	WT120C G3 80S/840 PSU L1200	-	4000 K	>80	160 lm/W
33321699	WT120C G3 40S/840 PSU WEC3 L1200	-	4000 K	>80	160 lm/W
33322399	WT120C G3 40S/840 PSU WEC3 TW1 L1200	-	4000 K	>80	160 lm/W
33336099	WT120C G3 60S/840 PSD L1200	-	4000 K	>80	160 lm/W
33366799	WT120CG3 27_33_39_46S/830_40 PSUTW3L1200	All-in, Multi Color Temperature	3000 K	>80	161 lm/W
39004200	WT121C G3 27_33_39_46S/840 PSU L1200	All-in, Multi Lumen	4000 K	>80	151 lm/W
39012700	WT120C G3 27_33_39_46S/830 PSU L1200	All-in, Multi Lumen	3000 K	>80	154 lm/W
39014100	WT120C G3 27_33_39_46S/865 PSU L1200	All-in, Multi Lumen	6500 K	80	161 lm/W
33344599	WT120C G3 27_33_39_46S/840 PSU L1200	All-in, Multi Lumen	4000 K	>80	161 lm/W

## CoreLine waterproof gen3

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
33348399	WT120C G3 27_33_39_46S/840 TW3 PSU L1200	All-in, Multi Lumen	4000 K	>80	161 lm/W
35990200	WT120C G3 40S/840 PSD L600	-	4000 K	>80	160 lm/W
39007300	WT120C G3 40S/840 PSD TW1 L600	-	4000 K	>80	160 lm/W
33305699	WT120C G3 20S/840 PSU L600	-	4000 K	>80	154 lm/W
33311799	WT120C G3 40S/840 PSU L600	-	4000 K	>80	160 lm/W
33346999	WT120C G3 24_29_35_40S/840 PSU L600	All-in, Multi Lumen	4000 K	>80	159 lm/W
35979700	WT120C G3 34S/840 PSU TW3 L1500	-	4000 K	>80	158 lm/W
35992600	WT120C G3 120S/840 PSD L1500	-	4000 K	>80	160 lm/W
35998800	WT120C G3 60S/840 UE PSU L1500	-	4000 K	>80	188 lm/W
35999500	WT120C G3 140S/840 UE PSU L1500	-	4000 K	>80	189 lm/W
39001100	WT120C G3 80S/840 UE PSD L1500	-	4000 K	>80	186 lm/W
39003500	WT121C G3 60S/840 PSU L1500	-	4000 K	>80	155 lm/W
39011000	WT120C G3 80S/840 PSD TW3 L1500	-	4000 K	>80	160 lm/W
33307099	WT120C G3 34S/840 PSU L1500	-	4000 K	>80	158 lm/W
33309499	WT120C G3 60S/840 PSU L1500	-	4000 K	>80	160 lm/W
33310099	WT120C G3 80S/840 PSU L1500	-	4000 K	>80	160 lm/W
33314899	WT120C G3 100S/840 PSU L1500	-	4000 K	>80	160 lm/W
33315599	WT120C G3 120S/840 PSU L1500	-	4000 K	>80	160 lm/W
33323099	WT120C G3 60S/840 PSU WEC3 L1500	-	4000 K	>80	160 lm/W
33324799	WT120C G3 60S/840 PSU WEC3 TW1 L1500	-	4000 K	>80	160 lm/W
33339199	WT120C G3 80S/840 PSD L1500	-	4000 K	>80	160 lm/W

### Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Order Code	Full Product Name	Luminous Flux
39005900	WT121C G3 35_43_51_60S/840 PSU L1500	3,300 lm	39000400	WT120C G3 80S/840 UE PSD L1200	8,200 lm
39013400	WT120C G3 35_43_51_60S/830 PSU L1500	3,400 lm	39002800	WT121C G3 40S/840 PSU L1200	3,800 lm
33345299	WT120C G3 35_43_51_60S/840 PSU L1500	3,500 lm	39009700	WT120C G3 80S/840 PSD TW3 L1200	8,000 lm
33347699	WT120C G3 46_57_69_80S/840 PSU L1500	4,600 lm	33306399	WT120C G3 27S/840 PSU L1200	2,700 lm
33349099	WT120C G3 46_57_69_80S/840 PSU TW3 L1500	4,600 lm	33308799	WT120C G3 40S/840 PSU L1200	4,000 lm
33350699	WT120C G3 70_86_100_120S/840 PSU L1500	7,000 lm	33312499	WT120C G3 60S/840 PSU L1200	6,000 lm
33367499	WT120CG3 35_43_51_60S/830_40 PSUTW3L1500	3,500 lm	33313199	WT120C G3 80S/840 PSU L1200	8,000 lm
35991900	WT120C G3 80S/840 PSD L1200	8,000 lm	33321699	WT120C G3 40S/840 PSU WEC3 L1200	4,000 lm
35997100	WT120C G3 40S/840 UE PSU L1200	4,200 lm	33322399	WT120C G3 40S/840 PSU WEC3 TW1 L1200	4,000 lm

## CoreLine waterproof gen3

Order Code	Full Product Name	Luminous Flux
33336099	WT120C G3 60S/840 PSD L1200	6,000 lm
33366799	WT120CG3 27_33_39_46S/830_40 PSUTW3L1200	2,700 lm
39004200	WT121C G3 27_33_39_46S/840 PSU L1200	2,600 lm
39012700	WT120C G3 27_33_39_46S/830 PSU L1200	2,600 lm
39014100	WT120C G3 27_33_39_46S/865 PSU L1200	2,700 lm
33344599	WT120C G3 27_33_39_46S/840 PSU L1200	2,700 lm
33348399	WT120C G3 27_33_39_46S/840 TW3 PSU L1200	2,700 lm
35990200	WT120C G3 40S/840 PSD L600	4,000 lm
39007300	WT120C G3 40S/840 PSD TW1 L600	4,000 lm
33305699	WT120C G3 20S/840 PSU L600	2,000 lm
33311799	WT120C G3 40S/840 PSU L600	4,000 lm
33346999	WT120C G3 24_29_35_40S/840 PSU L600	2,400 lm
35979700	WT120C G3 34S/840 PSU TW3 L1500	3,400 lm
35992600	WT120C G3 120S/840 PSD L1500	12,000 lm

Order Code	Full Product Name	Luminous Flux
35998800	WT120C G3 60S/840 UE PSU L1500	6,000 lm
35999500	WT120C G3 140S/840 UE PSU L1500	14,000 lm
39001100	WT120C G3 80S/840 UE PSD L1500	8,200 lm
39003500	WT121C G3 60S/840 PSU L1500	5,800 lm
39011000	WT120C G3 80S/840 PSD TW3 L1500	8,000 lm
33307099	WT120C G3 34S/840 PSU L1500	3,400 lm
33309499	WT120C G3 60S/840 PSU L1500	6,000 lm
33310099	WT120C G3 80S/840 PSU L1500	8,000 lm
33314899	WT120C G3 100S/840 PSU L1500	10,000 lm
33315599	WT120C G3 120S/840 PSU L1500	12,000 lm
33323099	WT120C G3 60S/840 PSU WEC3 L1500	6,000 lm
33324799	WT120C G3 60S/840 PSU WEC3 TW1 L1500	6,000 lm
33339199	WT120C G3 80S/840 PSD L1500	8,000 lm

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
39005900	WT121C G3 35_43_51_60S/840 PSU L1500	37.5 W
39013400	WT120C G3 35_43_51_60S/830 PSU L1500	37.5 W
33345299	WT120C G3 35_43_51_60S/840 PSU L1500	37.5 W
33347699	WT120C G3 46_57_69_80S/840 PSU L1500	50 W
33349099	WT120C G3 46_57_69_80S/840 PSU TW3 L1500	50 W
33350699	WT120C G3 70_86_100_120S/840 PSU L1500	75 W
33367499	WT120CG3 35_43_51_60S/830_40 PSUTW3L1500	37.5 W
35991900	WT120C G3 80S/840 PSD L1200	50 W
35997100	WT120C G3 40S/840 UE PSU L1200	22.5 W
39000400	WT120C G3 80S/840 UE PSD L1200	44 W
39002800	WT121C G3 40S/840 PSU L1200	25 W
39009700	WT120C G3 80S/840 PSD TW3 L1200	50 W
33306399	WT120C G3 27S/840 PSU L1200	17 W
33308799	WT120C G3 40S/840 PSU L1200	25 W
33312499	WT120C G3 60S/840 PSU L1200	37.5 W
33313199	WT120C G3 80S/840 PSU L1200	50 W
33321699	WT120C G3 40S/840 PSU WEC3 L1200	25 W
33322399	WT120C G3 40S/840 PSU WEC3 TW1 L1200	25 W
33336099	WT120C G3 60S/840 PSD L1200	37.5 W
33366799	WT120CG3 27_33_39_46S/830_40 PSUTW3L1200	28.5 W
39004200	WT121C G3 27_33_39_46S/840 PSU L1200	28.5 W
39012700	WT120C G3 27_33_39_46S/830 PSU L1200	28.5 W
39014100	WT120C G3 27_33_39_46S/865 PSU L1200	28.5 W

Order Code	Full Product Name	Power Consumption
33344599	WT120C G3 27_33_39_46S/840 PSU L1200	28.5 W
33348399	WT120C G3 27_33_39_46S/840 TW3 PSU L1200	28.5 W
35990200	WT120C G3 40S/840 PSD L600	25 W
39007300	WT120C G3 40S/840 PSD TW1 L600	25 W
33305699	WT120C G3 20S/840 PSU L600	13 W
33311799	WT120C G3 40S/840 PSU L600	25 W
33346999	WT120C G3 24_29_35_40S/840 PSU L600	25 W
35979700	WT120C G3 34S/840 PSU TW3 L1500	21.5 W
35992600	WT120C G3 120S/840 PSD L1500	75 W
35998800	WT120C G3 60S/840 UE PSU L1500	32 W
35999500	WT120C G3 140S/840 UE PSU L1500	74 W
39001100	WT120C G3 80S/840 UE PSD L1500	44 W
39003500	WT121C G3 60S/840 PSU L1500	37.5 W
39011000	WT120C G3 80S/840 PSD TW3 L1500	50 W
33307099	WT120C G3 34S/840 PSU L1500	21.5 W
33309499	WT120C G3 60S/840 PSU L1500	37.5 W
33310099	WT120C G3 80S/840 PSU L1500	50 W
33314899	WT120C G3 100S/840 PSU L1500	62.5 W
33315599	WT120C G3 120S/840 PSU L1500	75 W
33323099	WT120C G3 60S/840 PSU WEC3 L1500	37.5 W
33324799	WT120C G3 60S/840 PSU WEC3 TW1 L1500	37.5 W
33339199	WT120C G3 80S/840 PSD L1500	50 W

### Controls and Dimming

Order Code	Full Product Name	Dimmable
39005900	WT121C G3 35_43_51_60S/840 PSU L1500	No
39013400	WT120C G3 35_43_51_60S/830 PSU L1500	No
33345299	WT120C G3 35_43_51_60S/840 PSU L1500	No
33347699	WT120C G3 46_57_69_80S/840 PSU L1500	No
33349099	WT120C G3 46_57_69_80S/840 PSU TW3 L1500	No
33350699	WT120C G3 70_86_100_120S/840 PSU L1500	No

Order Code	Full Product Name	Dimmable
33367499	WT120CG3 35_43_51_60S/830_40 PSUTW3L1500	No
35991900	WT120C G3 80S/840 PSD L1200	Yes
35997100	WT120C G3 40S/840 UE PSU L1200	No
39000400	WT120C G3 80S/840 UE PSD L1200	Yes
39002800	WT121C G3 40S/840 PSU L1200	No
39009700	WT120C G3 80S/840 PSD TW3 L1200	Yes

## CoreLine waterproof gen3

Order Code	Full Product Name	Dimmable
33306399	WT120C G3 27S/840 PSU L1200	No
33308799	WT120C G3 40S/840 PSU L1200	No
33312499	WT120C G3 60S/840 PSU L1200	No
33313199	WT120C G3 80S/840 PSU L1200	No
33321699	WT120C G3 40S/840 PSU WEC3 L1200	No
33322399	WT120C G3 40S/840 PSU WEC3 TW1 L1200	No
33336099	WT120C G3 60S/840 PSD L1200	Yes
33366799	WT120CG3 27_33_39_46S/830_40 PSUTW3L1200	No
39004200	WT121C G3 27_33_39_46S/840 PSU L1200	No
39012700	WT120C G3 27_33_39_46S/830 PSU L1200	No
39014100	WT120C G3 27_33_39_46S/865 PSU L1200	No
33344599	WT120C G3 27_33_39_46S/840 PSU L1200	No
33348399	WT120C G3 27_33_39_46S/840 TW3 PSU L1200	No
35990200	WT120C G3 40S/840 PSD L600	Yes
39007300	WT120C G3 40S/840 PSD TW1 L600	Yes
33305699	WT120C G3 20S/840 PSU L600	No
33311799	WT120C G3 40S/840 PSU L600	No

Order Code	Full Product Name	Dimmable
33346999	WT120C G3 24_29_35_40S/840 PSU L600	No
35979700	WT120C G3 34S/840 PSU TW3 L1500	No
35992600	WT120C G3 120S/840 PSD L1500	Yes
35998800	WT120C G3 60S/840 UE PSU L1500	No
35999500	WT120C G3 140S/840 UE PSU L1500	No
39001100	WT120C G3 80S/840 UE PSD L1500	Yes
39003500	WT121C G3 60S/840 PSU L1500	No
39011000	WT120C G3 80S/840 PSD TW3 L1500	Yes
33307099	WT120C G3 34S/840 PSU L1500	No
33309499	WT120C G3 60S/840 PSU L1500	No
33310099	WT120C G3 80S/840 PSU L1500	No
33314899	WT120C G3 100S/840 PSU L1500	No
33315599	WT120C G3 120S/840 PSU L1500	No
33323099	WT120C G3 60S/840 PSU WEC3 L1500	No
33324799	WT120C G3 60S/840 PSU WEC3 TW1 L1500	No
33339199	WT120C G3 80S/840 PSD L1500	Yes

### Emergency Operation

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
39005900	WT121C G3 35_43_51_60S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
39013400	WT120C G3 35_43_51_60S/830 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33345299	WT120C G3 35_43_51_60S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33347699	WT120C G3 46_57_69_80S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33349099	WT120C G3 46_57_69_80S/840 PSU TW3 L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33350699	WT120C G3 70_86_100_120S/ 840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33367499	WT120CG3 35_43_51_60S/ 830_40 PSUTW3L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
35991900	WT120C G3 80S/840 PSD L1200	Yes	DC operated central emergency lighting

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
35997100	WT120C G3 40S/840 UE PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
39000400	WT120C G3 80S/840 UE PSD L1200	Yes	DC operated central emergency lighting
39002800	WT121C G3 40S/840 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
39009700	WT120C G3 80S/840 PSD TW3 L1200	Yes	DC operated central emergency lighting
33306399	WT120C G3 27S/ 840 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33308799	WT120C G3 40S/ 840 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33312499	WT120C G3 60S/ 840 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33313199	WT120C G3 80S/ 840 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33321699	WT120C G3 40S/840 PSU WEC3 L1200	No	Self-contained emergency lighting is possible when

## CoreLine waterproof gen3

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
			used with a compatible battery kit accessory
33322399	WT120C G3 40S/840 PSU WEC3 TW1 L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33336099	WT120C G3 60S/840 PSD L1200	Yes	DC operated central emergency lighting
33366799	WT120CG3 27_33_39_46S/830_40 PSUTW3L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
39004200	WT121C G3 27_33_39_46S/840 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
39012700	WT120C G3 27_33_39_46S/830 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
39014100	WT120C G3 27_33_39_46S/865 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33344599	WT120C G3 27_33_39_46S/840 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33348399	WT120C G3 27_33_39_46S/840 TW3 PSU L1200	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
35990200	WT120C G3 40S/840 PSD L600	Yes	DC operated central emergency lighting
39007300	WT120C G3 40S/840 PSD TW1 L600	Yes	DC operated central emergency lighting
33305699	WT120C G3 20S/840 PSU L600	No	-
33311799	WT120C G3 40S/840 PSU L600	No	-
33346999	WT120C G3 24_29_35_40S/840 PSU L600	No	-
35979700	WT120C G3 34S/840 PSU TW3 L1500	No	Self-contained emergency lighting is possible when

Order Code	Full Product Name	Central	
		Emergency	Emergency lighting
			used with a compatible battery kit accessory
35992600	WT120C G3 120S/840 PSD L1500	Yes	DC operated central emergency lighting
35998800	WT120C G3 60S/840 UE PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
35999500	WT120C G3 140S/840 UE PSU L1500	No	-
39001100	WT120C G3 80S/840 UE PSD L1500	Yes	DC operated central emergency lighting
39003500	WT121C G3 60S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
39011000	WT120C G3 80S/840 PSD TW3 L1500	Yes	DC operated central emergency lighting
33307099	WT120C G3 34S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33309499	WT120C G3 60S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33310099	WT120C G3 80S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33314899	WT120C G3 100S/840 PSU L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33315599	WT120C G3 120S/840 PSU L1500	No	-
33323099	WT120C G3 60S/840 PSU WEC3 L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33324799	WT120C G3 60S/840 PSU WEC3 TW1 L1500	No	Self-contained emergency lighting is possible when used with a compatible battery kit accessory
33339199	WT120C G3 80S/840 PSD L1500	Yes	DC operated central emergency lighting


### Initial Performance (IEC Compliant)

## CoreLine waterproof gen3


Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
39005900	WT121C G3 35_43_51_60S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
39013400	WT120C G3 35_43_51_60S/830 PSU L1500	(0.43, 0.40) SDCM<3	+15%/-5%
33345299	WT120C G3 35_43_51_60S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33347699	WT120C G3 46_57_69_80S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33349099	WT120C G3 46_57_69_80S/840 PSU TW3 L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33350699	WT120C G3 70_86_100_120S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33367499	WT120CG3 35_43_51_60S/830_40 PSUTW3L1500	(0.38, 0.37) SDCM<3; (0.43, 0.40) SDCM<3	+15%/-5%
35991900	WT120C G3 80S/840 PSD L1200	(0.38, 0.37) SDCM<3	+15%/-5%
35997100	WT120C G3 40S/840 UE PSU L1200	(0.38, 0.37) SDCM<3	-10% / +10%
39000400	WT120C G3 80S/840 UE PSD L1200	(0.38, 0.37) SDCM<3	-10% / +10%
39002800	WT121C G3 40S/840 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%
39009700	WT120C G3 80S/840 PSD TW3 L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33306399	WT120C G3 27S/840 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33308799	WT120C G3 40S/840 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33312499	WT120C G3 60S/840 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33313199	WT120C G3 80S/840 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33321699	WT120C G3 40S/840 PSU WEC3 L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33322399	WT120C G3 40S/840 PSU WEC3 TW1 L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33336099	WT120C G3 60S/840 PSD L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33366799	WT120CG3 27_33_39_46S/830_40 PSUTW3L1200	(0.38, 0.37) SDCM<3; (0.43, 0.40) SDCM<3	+15%/-5%
39004200	WT121C G3 27_33_39_46S/840 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
39012700	WT120C G3 27_33_39_46S/830 PSU L1200	(0.43, 0.40) SDCM<3	+15%/-5%
39014100	WT120C G3 27_33_39_46S/865 PSU L1200	(0.31, 0.32) SDCM<3	+15%/-5%
33344599	WT120C G3 27_33_39_46S/840 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%
33348399	WT120C G3 27_33_39_46S/840 TW3 PSU L1200	(0.38, 0.37) SDCM<3	+15%/-5%
35990200	WT120C G3 40S/840 PSD L600	(0.38, 0.37) SDCM<3	+15%/-5%
39007300	WT120C G3 40S/840 PSD TW1 L600	(0.38, 0.37) SDCM<3	+15%/-5%
33305699	WT120C G3 20S/840 PSU L600	(0.38, 0.37) SDCM<3	+15%/-5%
33311799	WT120C G3 40S/840 PSU L600	(0.38, 0.37) SDCM<3	+15%/-5%
33346999	WT120C G3 24_29_35_40S/840 PSU L600	(0.38, 0.37) SDCM<3	+15%/-5%
35979700	WT120C G3 34S/840 PSU TW3 L1500	(0.38, 0.37) SDCM<3	+15%/-5%
35992600	WT120C G3 120S/840 PSD L1500	(0.38, 0.37) SDCM<3	+15%/-5%
35998800	WT120C G3 60S/840 UE PSU L1500	(0.38, 0.37) SDCM<3	-10% / +10%
35999500	WT120C G3 140S/840 UE PSU L1500	(0.38, 0.37) SDCM<3	-10% / +10%
39001100	WT120C G3 80S/840 UE PSD L1500	(0.38, 0.37) SDCM<3	-10% / +10%
39003500	WT121C G3 60S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
39011000	WT120C G3 80S/840 PSD TW3 L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33307099	WT120C G3 34S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33309499	WT120C G3 60S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33310099	WT120C G3 80S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33314899	WT120C G3 100S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33315599	WT120C G3 120S/840 PSU L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33323099	WT120C G3 60S/840 PSU WEC3 L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33324799	WT120C G3 60S/840 PSU WEC3 TW1 L1500	(0.38, 0.37) SDCM<3	+15%/-5%
33339199	WT120C G3 80S/840 PSD L1500	(0.38, 0.37) SDCM<3	+15%/-5%


### Polar Wide Diagrams



Polar Normal (separate) - 910505106533




Polar Normal (separate) - 910505106546




Polar Normal (separate) - 910505106545


Polar Wide Diagrams




Polar Normal (separate) - 910505106565




Polar Normal (separate) - 910505106551




Polar Normal (separate) - 910505106544




Polar Normal (separate) - 910505106566




Polar Normal (separate) - 910505106553




Polar Normal (separate) - 910505106554




Polar Normal (separate) - 910505106563




Polar Normal (separate) - 910505106552




Polar Normal (separate) - 910505106557



Polar Normal (separate) - 910505106555




Polar Normal (separate) - 910505106561




Polar Normal (separate) - 910505106556


Polar Wide Diagrams




Polar Normal (separate) - 910505106558




Polar Normal (separate) - 910505106567




Polar Normal (separate) - 910505106568




Polar Normal (separate) - 911401837388




Polar Normal (separate) - 911401841688




Polar Normal (separate) - 911401839688




Polar Normal (separate) - 911401835488




Polar Normal (separate) - 911401836288




Polar Normal (separate) - 911401836088



Polar Normal (separate) - 911401835888




Polar Normal (separate) - 911401835588




Polar Normal (separate) - 911401835988


Polar Wide Diagrams




Polar Normal (separate) - 911401837088




Polar Normal (separate) - 911401838888




Polar Normal (separate) - 911401839488




Polar Normal (separate) - 911401837188




Polar Normal (separate) - 911401841588




Polar Normal (separate) - 911401839788




Polar Normal (separate) - 911401835688




Polar Normal (separate) - 911401836388




Polar Normal (separate) - 911401839988



Polar Normal (separate) - 911401839888




Polar Normal (separate) - 911401836188




Polar Normal (separate) - 911401839588

# CoreLine waterproof gen3


## Polar Wide Diagrams




Polar Normal (separate) - 911401835788




Polar Normal (separate) - 911401836488




Polar Normal (separate) - 911401837288



Polar Normal (separate) - 911401838588



Polar Normal (separate) - 911401839388



Polar Normal (separate) - 910505106559

