PHILIPS

Lighting

Higher 30K lumen with high efficacy upto 190 lm/w to optimize battery and panel, world class components combined with most durable design.

GreenVision Xceed Gen2 High Efficacy Solar

Comprehensive range of solar street lights to 30000 lumens, with upto 190 lm/w efficacy, and option of hybrid versions. Suitable for major roads, highways and parking areas. configurable dimming profile and load wattage.

Features

- High luminous efficacy upto 190lm/watt. Best in class.
- Compatible with multiple battery types (LiFePO4, GEL)
- Available in both offgrid and hybrid versions
- Configurable dimming profile and load wattage
- Pressure die-cast aluminum housing for sturdiness and excellent thermal management

GreenVision Xceed Gen2 High Efficacy Solar

Application

- Highways
- Street
- Road
- Parking

Versions



GreenVision Xceed Gen2 High Efficacy Solar

Dimensional drawing



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.