

PHILIPS

Lighting



Switch light settings without switching bulbs

SceneSwitch LED bulbs

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LEDbulbs, you can have different light settings from just one bulb. And you don't need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

Benefits

- Multiple light settings in one lamp
- Plug and play
- Built-in memory chip

Features

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Auto memory: recall your last setting automatically

Application


- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)
- Accent and general lighting (e.g. hotels, shops and offices)

SceneSwitch LED bulbs


Versions



Bulb A67 100W 1521lm 2700K E27
ND Frosted




LEDclassic SSW 60W A60 E27 WW
CL ND 1SRT




LEDbulb Classic 40W E14 B35 WW
CL ND

Dimensional drawing




Product	D	C
LEDClassic SSW 60W A60 E27WWFR ND 1PF/10	60 mm	104 mm



Product	D	C
LEDClassic SSW 40W B35 E14 WW CLND 1SRT4	35.5 mm	106 mm

SceneSwitch LED bulbs

Dimensional drawing



Product	D	C
LEDClassic SSW 60W A60 E27WWCLND RF1SRT4	60 mm	104 mm

General Information	
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
Color Code	827/825/822
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No

General Information		Cap-Base
Order Code	Full Product Name	
26396301	LEDClassic SSW 60W A60 E27WWFR ND 1PF/10	E27
77213001	LEDClassic SSW 60W A60 E27WWCLND RF1SRT4	E27
77215400	LEDClassic SSW 40W B35 E14 WW CLND 1SRT4	E14

Operating and Electrical

Order Code	Full Product Name	Power Consumption
26396301	LEDClassic SSW 60W A60 E27WWFR ND 1PF/10	7.5 W
77213001	LEDClassic SSW 60W A60 E27WWCLND RF1SRT4	7.5 W

Order Code	Full Product Name	Power Consumption
77215400	LEDClassic SSW 40W B35 E14 WW CLND 1SRT4	5 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
26396301	LEDClassic SSW 60W A60 E27WWFR ND 1PF/10	Frosted	A60
77213001	LEDClassic SSW 60W A60 E27WWCLND RF1SRT4	Clear	A60

Order Code	Full Product Name	Bulb Finish	Bulb Shape
77215400	LEDClassic SSW 40W B35 E14 WW CLND 1SRT4	Clear	B35

Approval and Application

SceneSwitch LED bulbs

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
26396301	LEDClassic SSW 60W A60 E27WWFR ND 1PF/10	8 kWh
77213001	LEDClassic SSW 60W A60 E27WWCLND RF1SRT4	8 kWh
77215400	LEDClassic SSW 40W B35 E14 WW CLND ISRT4	5 kWh

