



# For top performance and sustainability

## MASTER LED tube InstantFit HF T5

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T5 lighting tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime make these T5 LED tubes the choice for every demanding application.

### Benefits

- Absolute performance that provides a solution for every application
- Unparalleled savings with low energy consumption and long lifetime
- Robust and reliable: stands up to everyday conditions

### Features

- Retrofit existing T5 lamps with HF ballast
- Compatible with a wide range of ballasts
- > 50% energy savings compared to fluorescent tubes with up to 155lm/W
- Extra-long life up to 60,000 hours
- Ultra output up to 5600lm
- Enable implementation of HACCP, supported by product level NSF certificate
- No mercury

### Application

- Office
- Schools
- Retail


# MASTER LED tube InstantFit HF T5

## Versions



LEDtube 1200mm 17W G5

## Dimensional drawing



D1	D2	A1	A2	A3
15.5mm	18.8mm	549mm	556.1mm	563.2mm

Product	D1	D2	A1	A2	A3
MAS LEDtube HF 600mm HE 8W 840 T5 AP	15.7 mm	19 mm	549 mm	556.1 mm	563.2 mm

