

Maxos LED

4MX850



Maxos LED Industry – innovative, flexible solution delivers ideal light output

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED Industry offers best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED Industry system comprises exchangeable mid-power LED boards mounted on a standard Maxos trunking rail. A choice of wide and medium-beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: the use of our upgradable LED engine platform makes Maxos LED Industry a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven Maxos trunking system

Applications

- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers
- Showrooms


Versions

Features


- Mid-power LED boards; exchangeable LED unit
- Up to 165 lm/W efficiency
- LED gear trays for T5 and TL-D-length trunkings (high lumen output); replacement LED gear trays with same lumen packages as installed T5 and TL-D solutions (lower wattage)
- Choice of narrow, medium, double asymmetric and asymmetric lenses
- Compatible with our standard Maxos and TTX400 rails for TL5 49 W and TL-D 58 W lengths



Dimensional drawing



Maxos Led Industry - 1 unit for TL-D 58 W - LED module, system flux 4000 lm - 840 neutral white - Power supply unit with DALI interface - Wide beam - Connector with 2 additional wires for light regulation - White



MAXOS LED EM 3H3S - 1 unit for TL5 49 W - LED module, system flux 6600 lm - 840 neutral white - Power supply unit with DALI interface - Narrow beam - White - Connector with 2 additional wires for light regulation

Product details



IPDP_4MX850i_0001-Detail photo



IPDP_4MX850i_0003-Detail photo



IPDP_4MX850i_0005-Detail photo

General Information	
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	120 degree(s)
Operating and Electrical	
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polymethyl methacrylate bowl/cover

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	No

Approval and Application

Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark

General Information

Order Code	Full Product Name	Lamp family code
910500460502	4MX850 491 LED80S/840 PSD WB SI	LED80S
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	LED66S
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	LED80S
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	LED66S
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	LED80S
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	LED80S
910500460049	4MX850 491 LED80S/840 PSD VWB WH	LED80S
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	LED80S
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	LED80S
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	LED66S
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	LED66S
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	LED66S
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	LED80S
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	LED80S
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	LED80S
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	LED55S
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	LED55S
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	LED66S
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	LED55S
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	LED55S
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	LED55S
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	LED66S
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	LED66S

Order Code	Full Product Name	Lamp family code
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	LED66S
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	LED55S
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	LED66S
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	LED40S
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	-
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	-
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	LED40S
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	LED55S
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	LED40S
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	LED66S
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	LED80S
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-
910629167426	4MX850 491 LED80S/840 PSD NB WH	LED80S
910629167526	4MX850 491 LED80S/840 PSD WB WH	LED80S
910500460518	4MX850 581 LED66S/830 PSD WB SI	-
910629121026	4MX850 491 LED55S/830 PSD WB SI	LED55S
910629121126	4MX850 491 LED55S/840 PSD WB SI	LED55S
910629121426	4MX850 581 LED55S/830 PSD WB SI	LED55S
910629121526	4MX850 581 LED55S/840 PSD WB SI	LED55S
910629122426	4MX850 491 LED40S/830 PSD NB SI	LED40S
910629122526	4MX850 491 LED40S/840 PSD NB SI	LED40S
910629122626	4MX850 491 LED40S/830 PSD WB SI	LED40S
910629122726	4MX850 491 LED40S/840 PSD WB SI	LED40S
910629122826	4MX850 581 LED40S/830 PSD NB SI	LED40S
910629123026	4MX850 581 LED40S/830 PSD WB SI	LED40S
910629123126	4MX850 581 LED40S/840 PSD WB SI	LED40S
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	LED40S
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	LED40S
910629160826	4MX850 491 LED55S/830 PSD A20 SI	LED55S
910629160926	4MX850 491 LED55S/840 PSD A20 SI	LED55S
910629161126	4MX850 491 LED40S/830 PSD A20 SI	LED40S
910629161226	4MX850 491 LED40S/840 PSD A20 SI	LED40S
910629162226	4MX850 491 LED66S/840 PSD A20 SI	LED66S
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	LED55S
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	LED55S
910500457964	4MX850 581 LED80S/840 PSD NB WH	LED80S

Order Code	Full Product Name	Lamp family code
910500457965	4MX850 581 LED80S/840 PSD WB WH	LED80S
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	LED66S
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	LED80S
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	LED80S
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	LED80S
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	LED66S
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	LED66S
910500460048	4MX850 581 LED80S/840 PSD VWB WH	LED80S
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	LED40S
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	LED66S
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	LED80S
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	LED66S
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	LED80S
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	LED66S
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	LED80S
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	LED55S
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	LED55S
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	LED55S
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	LED66S
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	LED66S
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	LED55S
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	LED55S
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	LED55S
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	LED66S
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	LED66S
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	LED55S
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-
910500460477	4MX850 581 LED80S/830 PSD WB WH	-
910500460483	4MX850 581 LED80S/840 PSD A20 WH	LED80S
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	-
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	-
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	LED55S
910629120126	4MX850 491 LED55S/840 PSD NB WH	LED55S
910629120226	4MX850 491 LED55S/830 PSD WB WH	LED55S
910629120326	4MX850 491 LED55S/840 PSD WB WH	LED55S
910629120726	4MX850 581 LED55S/840 PSD WB WH	LED55S
910629121626	4MX850 491 LED40S/830 PSD NB WH	LED40S
910629121726	4MX850 491 LED40S/840 PSD NB WH	LED40S
910629121826	4MX850 491 LED40S/830 PSD WB WH	LED40S
910629121926	4MX850 491 LED40S/840 PSD WB WH	LED40S
910629122126	4MX850 581 LED40S/840 PSD NB WH	LED40S
910629122326	4MX850 581 LED40S/840 PSD WB WH	LED40S

Order Code	Full Product Name	Lamp family code
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	LED55S
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	LED55S
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	LED55S
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	LED40S
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	LED40S
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	LED66S
910629158126	4MX850 491 LED66S/840 PSD WB WH	LED66S
910629158226	4MX850 491 LED66S/840 PSD NB WH	LED66S
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	LED66S
910629160126	4MX850 491 LED66S/830 PSD WB WH	LED66S
910629160226	4MX850 491 LED66S/830 PSD NB WH	LED66S
910629160326	4MX850 581 LED66S/840 PSD WB WH	LED66S
910629160426	4MX850 581 LED66S/840 PSD NB WH	LED66S
910629160526	4MX850 491 LED40S/840 PSD A20 WH	LED40S
910629160626	4MX850 491 LED55S/840 PSD A20 WH	LED55S
910629160726	4MX850 491 LED55S/830 PSD A20 WH	LED55S
910629161026	4MX850 491 LED40S/830 PSD A20 WH	LED40S
910629162126	4MX850 491 LED66S/840 PSD A20 WH	LED66S
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	LED66S
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	LED55S
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	LED66S
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	LED55S

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910500460502	4MX850 491 LED80S/840 PSD WB SI	8,000 lm	4000 K	166 lm/W	Wide beam
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	6,600 lm	4000 K	166 lm/W	Wide beam
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	8,000 lm	4000 K	166 lm/W	Wide beam
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	6,600 lm	4000 K	166 lm/W	Narrow beam
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	8,000 lm	4000 K	166 lm/W	Narrow beam
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	8,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460049	4MX850 491 LED80S/840 PSD VWB WH	8,000 lm	4000 K	166 lm/W	Very wide beam
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	8,000 lm	4000 K	166 lm/W	Very wide beam
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	8,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	6,600 lm	4000 K	166 lm/W	Narrow beam
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	6,600 lm	4000 K	166 lm/W	Wide beam
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	8,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	8,000 lm	4000 K	166 lm/W	Narrow beam
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	8,000 lm	4000 K	166 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 20°
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	5,500 lm	4000 K	169 lm/W	Wide beam
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 20°
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	5,500 lm	4000 K	169 lm/W	Narrow beam
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	5,500 lm	4000 K	169 lm/W	Wide beam
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	6,600 lm	4000 K	166 lm/W	Narrow beam
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	6,600 lm	4000 K	166 lm/W	Wide beam
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	5,500 lm	4000 K	169 lm/W	Wide beam
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	6,600 lm	4000 K	166 lm/W	Very wide beam
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	4,000 lm	4000 K	166 lm/W	Wide beam
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	6,600 lm	4000 K	166 lm/W	Wide beam
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	6,600 lm	4000 K	166 lm/W	Wide beam
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	4,000 lm	3000 K	166 lm/W	Wide beam
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	4,000 lm	4000 K	166 lm/W	Narrow beam
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	5,500 lm	4000 K	169 lm/W	Narrow beam
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	4,000 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	6,600 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	8,000 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	4,000 lm	4000 K	166 lm/W	Narrow beam
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	4,000 lm	4000 K	166 lm/W	Wide beam
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	6,600 lm	4000 K	166 lm/W	Narrow beam
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	6,600 lm	4000 K	166 lm/W	Wide beam
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	8,000 lm	4000 K	166 lm/W	Narrow beam
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	8,000 lm	4000 K	166 lm/W	Wide beam
910629167426	4MX850 491 LED80S/840 PSD NB WH	8,000 lm	4000 K	166 lm/W	Narrow beam
910629167526	4MX850 491 LED80S/840 PSD WB WH	8,000 lm	4000 K	166 lm/W	Wide beam
910500460518	4MX850 581 LED66S/830 PSD WB SI	6,600 lm	3000 K	166 lm/W	Wide beam
910629121026	4MX850 491 LED55S/830 PSD WB SI	5,500 lm	3000 K	169 lm/W	Wide beam
910629121126	4MX850 491 LED55S/840 PSD WB SI	5,500 lm	4000 K	169 lm/W	Wide beam
910629121426	4MX850 581 LED55S/830 PSD WB SI	5,500 lm	3000 K	169 lm/W	Wide beam
910629121526	4MX850 581 LED55S/840 PSD WB SI	5,500 lm	4000 K	169 lm/W	Wide beam
910629122426	4MX850 491 LED40S/830 PSD NB SI	4,000 lm	3000 K	166 lm/W	Narrow beam
910629122526	4MX850 491 LED40S/840 PSD NB SI	4,000 lm	4000 K	166 lm/W	Narrow beam
910629122626	4MX850 491 LED40S/830 PSD WB SI	4,000 lm	3000 K	166 lm/W	Wide beam
910629122726	4MX850 491 LED40S/840 PSD WB SI	4,000 lm	4000 K	166 lm/W	Wide beam
910629122826	4MX850 581 LED40S/830 PSD NB SI	4,000 lm	3000 K	166 lm/W	Narrow beam
910629123026	4MX850 581 LED40S/830 PSD WB SI	4,000 lm	3000 K	166 lm/W	Wide beam
910629123126	4MX850 581 LED40S/840 PSD WB SI	4,000 lm	4000 K	166 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	4,000 lm	3000 K	166 lm/W	Double asymmetric optic 20°
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	4,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910629160826	4MX850 491 LED55S/830 PSD A20 SI	5,500 lm	3000 K	169 lm/W	Asymmetrical mirror axis angle 20°
910629160926	4MX850 491 LED55S/840 PSD A20 SI	5,500 lm	4000 K	169 lm/W	Asymmetrical mirror axis angle 20°
910629161126	4MX850 491 LED40S/830 PSD A20 SI	4,000 lm	3000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910629161226	4MX850 491 LED40S/840 PSD A20 SI	4,000 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910629162226	4MX850 491 LED66S/840 PSD A20 SI	6,600 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 35°
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 35°
910500457964	4MX850 581 LED80S/840 PSD NB WH	8,000 lm	4000 K	166 lm/W	Narrow beam
910500457965	4MX850 581 LED80S/840 PSD WB WH	8,000 lm	4000 K	166 lm/W	Wide beam
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	6,600 lm	4000 K	166 lm/W	Wide beam
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	8,000 lm	4000 K	166 lm/W	Wide beam
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	8,000 lm	4000 K	166 lm/W	Narrow beam
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	8,000 lm	4000 K	166 lm/W	Wide beam
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	6,600 lm	4000 K	166 lm/W	Narrow beam
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	6,600 lm	4000 K	166 lm/W	Wide beam
910500460048	4MX850 581 LED80S/840 PSD VWB WH	8,000 lm	4000 K	166 lm/W	Very wide beam
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	4,000 lm	4000 K	166 lm/W	Wide beam
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	8,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	8,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	8,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 20°
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	5,500 lm	4000 K	169 lm/W	Narrow beam
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	5,500 lm	4000 K	169 lm/W	Wide beam
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	6,600 lm	4000 K	166 lm/W	Wide beam
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 20°
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	5,500 lm	4000 K	169 lm/W	Narrow beam
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	5,500 lm	4000 K	169 lm/W	Wide beam
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	6,600 lm	4000 K	166 lm/W	Narrow beam
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	5,500 lm	4000 K	169 lm/W	Narrow beam
910500460476	4MX850 581 LED80S/830 PSD VWB WH	8,000 lm	3000 K	166 lm/W	Very wide beam
910500460477	4MX850 581 LED80S/830 PSD WB WH	8,000 lm	3000 K	166 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficiency (rated) (Nom)	Optic type
910500460483	4MX850 581 LED80S/840 PSD A20 WH	8,000 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	6,600 lm	4000 K	166 lm/W	Wide beam
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	6,600 lm	4000 K	166 lm/W	Wide beam
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	5,500 lm	4000 K	169 lm/W	Wide beam
910629120126	4MX850 491 LED55S/840 PSD NB WH	5,500 lm	4000 K	169 lm/W	Narrow beam
910629120226	4MX850 491 LED55S/830 PSD WB WH	5,500 lm	3000 K	169 lm/W	Wide beam
910629120326	4MX850 491 LED55S/840 PSD WB WH	5,500 lm	4000 K	169 lm/W	Wide beam
910629120726	4MX850 581 LED55S/840 PSD WB WH	5,500 lm	4000 K	169 lm/W	Wide beam
910629121626	4MX850 491 LED40S/830 PSD NB WH	4,000 lm	3000 K	166 lm/W	Narrow beam
910629121726	4MX850 491 LED40S/840 PSD NB WH	4,000 lm	4000 K	166 lm/W	Narrow beam
910629121826	4MX850 491 LED40S/830 PSD WB WH	4,000 lm	3000 K	166 lm/W	Wide beam
910629121926	4MX850 491 LED40S/840 PSD WB WH	4,000 lm	4000 K	166 lm/W	Wide beam
910629122126	4MX850 581 LED40S/840 PSD NB WH	4,000 lm	4000 K	166 lm/W	Narrow beam
910629122326	4MX850 581 LED40S/840 PSD WB WH	4,000 lm	4000 K	166 lm/W	Wide beam
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	5,500 lm	3000 K	169 lm/W	Double asymmetric optic 20°
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 20°
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 20°
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	4,000 lm	3000 K	166 lm/W	Double asymmetric optic 20°
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	4,000 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 20°
910629158126	4MX850 491 LED66S/840 PSD WB WH	6,600 lm	4000 K	166 lm/W	Wide beam
910629158226	4MX850 491 LED66S/840 PSD NB WH	6,600 lm	4000 K	166 lm/W	Narrow beam
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	6,600 lm	3000 K	166 lm/W	Double asymmetric optic 20°
910629160126	4MX850 491 LED66S/830 PSD WB WH	6,600 lm	3000 K	166 lm/W	Wide beam
910629160226	4MX850 491 LED66S/830 PSD NB WH	6,600 lm	3000 K	166 lm/W	Narrow beam
910629160326	4MX850 581 LED66S/840 PSD WB WH	6,600 lm	4000 K	166 lm/W	Wide beam
910629160426	4MX850 581 LED66S/840 PSD NB WH	6,600 lm	4000 K	166 lm/W	Narrow beam
910629160526	4MX850 491 LED40S/840 PSD A20 WH	4,000 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910629160626	4MX850 491 LED55S/840 PSD A20 WH	5,500 lm	4000 K	169 lm/W	Asymmetrical mirror axis angle 20°
910629160726	4MX850 491 LED55S/830 PSD A20 WH	5,500 lm	3000 K	169 lm/W	Asymmetrical mirror axis angle 20°
910629161026	4MX850 491 LED40S/830 PSD A20 WH	4,000 lm	3000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910629162126	4MX850 491 LED66S/840 PSD A20 WH	6,600 lm	4000 K	166 lm/W	Asymmetrical mirror axis angle 20°
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	6,600 lm	4000 K	166 lm/W	Wide beam
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 35°
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	6,600 lm	4000 K	166 lm/W	Double asymmetric optic 35°
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	5,500 lm	4000 K	169 lm/W	Double asymmetric optic 35°

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910500460502	4MX850 491 LED80S/840 PSD WB SI	220 to 240 V	48 W	Not applicable
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	220-240 V	39 W	Not applicable
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	220-240 V	48 W	Not applicable
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	220-240 V	39 W	Not applicable
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	220-240 V	48 W	Not applicable
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	220-240 V	48 W	Not applicable
910500460049	4MX850 491 LED80S/840 PSD VWB WH	220-240 V	48 W	Not applicable
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	220 to 240 V	48 W	Not applicable
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	220-240 V	48 W	Not applicable
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	220-240 V	39 W	Not applicable
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	220-240 V	39 W	Not applicable
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	220-240 V	39 W	Not applicable
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	220-240 V	48 W	Not applicable
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	220-240 V	48 W	Not applicable
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	220-240 V	48 W	Not applicable
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	220-240 V	36.5 W	Not applicable
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	220-240 V	36.5 W	Not applicable
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	220-240 V	43 W	Not applicable
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	220-240 V	36.5 W	Not applicable
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	220-240 V	43 W	Not applicable
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	220-240 V	43 W	Not applicable
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	220-240 V	43 W	Not applicable
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	220-240 V	32.5 W	Not applicable
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	220-240 V	39 W	Not applicable
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	220-240 V	24 W	Not applicable
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	220-240 V	43 W	Not applicable
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	220 to 240 V	43 W	Not applicable
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	220 to 240 V	24 W	Not applicable
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	220-240 V	24 W	Not applicable
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	220-240 V	32.5 W	Not applicable
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	220 to 240 V	24 W	Not applicable
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	220 to 240 V	39 W	Not applicable
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	220 to 240 V	48 W	Not applicable
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	220 to 240 V	24 W	No
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	220 to 240 V	24 W	No
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	220 to 240 V	39 W	No
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	220 to 240 V	39 W	No
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	220 to 240 V	48 W	No
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	220 to 240 V	48 W	No

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910629167426	4MX850 491 LED80S/840 PSD NB WH	220-240 V	48 W	Not applicable
910629167526	4MX850 491 LED80S/840 PSD WB WH	220-240 V	48 W	Not applicable
910500460518	4MX850 581 LED66S/830 PSD WB SI	220 to 240 V	39 W	Not applicable
910629121026	4MX850 491 LED55S/830 PSD WB SI	220-240 V	32.5 W	Not applicable
910629121126	4MX850 491 LED55S/840 PSD WB SI	220-240 V	32.5 W	Not applicable
910629121426	4MX850 581 LED55S/830 PSD WB SI	220-240 V	32.5 W	Not applicable
910629121526	4MX850 581 LED55S/840 PSD WB SI	220-240 V	32.5 W	Not applicable
910629122426	4MX850 491 LED40S/830 PSD NB SI	220-240 V	24 W	Not applicable
910629122526	4MX850 491 LED40S/840 PSD NB SI	220-240 V	24 W	Not applicable
910629122626	4MX850 491 LED40S/830 PSD WB SI	220-240 V	24 W	Not applicable
910629122726	4MX850 491 LED40S/840 PSD WB SI	220-240 V	24 W	Not applicable
910629122826	4MX850 581 LED40S/830 PSD NB SI	220-240 V	24 W	Not applicable
910629123026	4MX850 581 LED40S/830 PSD WB SI	220-240 V	24 W	Not applicable
910629123126	4MX850 581 LED40S/840 PSD WB SI	220-240 V	24 W	Not applicable
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	220-240 V	24 W	Not applicable
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	220-240 V	24 W	Not applicable
910629160826	4MX850 491 LED55S/830 PSD A20 SI	220-240 V	32.5 W	Not applicable
910629160926	4MX850 491 LED55S/840 PSD A20 SI	220-240 V	32.5 W	Not applicable
910629161126	4MX850 491 LED40S/830 PSD A20 SI	220-240 V	24 W	Not applicable
910629161226	4MX850 491 LED40S/840 PSD A20 SI	220-240 V	24 W	Not applicable
910629162226	4MX850 491 LED66S/840 PSD A20 SI	220-240 V	39 W	Not applicable
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	220-240 V	32.5 W	Not applicable
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	220-240 V	32.5 W	Not applicable
910500457964	4MX850 581 LED80S/840 PSD NB WH	220-240 V	48 W	Not applicable
910500457965	4MX850 581 LED80S/840 PSD WB WH	220-240 V	48 W	Not applicable
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	220-240 V	39 W	Not applicable
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	220-240 V	48 W	Not applicable
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	220-240 V	48 W	Not applicable
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	220-240 V	48 W	Not applicable
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	220-240 V	39 W	Not applicable
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	220-240 V	39 W	Not applicable
910500460048	4MX850 581 LED80S/840 PSD VWB WH	220-240 V	48 W	Not applicable
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	220 to 240 V	24 W	Not applicable
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	220-240 V	39 W	Not applicable
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	220-240 V	48 W	Not applicable
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	220-240 V	39 W	Not applicable
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	220-240 V	48 W	Not applicable
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	220-240 V	39 W	Not applicable
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	220-240 V	48 W	Not applicable
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	220-240 V	36.5 W	Not applicable
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	220-240 V	36.5 W	Not applicable
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	220-240 V	36.5 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	220-240 V	43 W	Not applicable
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	220-240 V	43 W	Not applicable
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	220-240 V	36.5 W	Not applicable
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	220-240 V	43 W	Not applicable
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	220-240 V	43 W	Not applicable
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	220-240 V	32.5 W	Not applicable
910500460476	4MX850 581 LED80S/830 PSD VWB WH	220 to 240 V	48 W	Not applicable
910500460477	4MX850 581 LED80S/830 PSD WB WH	220 to 240 V	48 W	Not applicable
910500460483	4MX850 581 LED80S/840 PSD A20 WH	220 to 240 V	48 W	Not applicable
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	220-240 V	43 W	Not applicable
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	220-240 V	43 W	Not applicable
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	220-240 V	32.5 W	Not applicable
910629120126	4MX850 491 LED55S/840 PSD NB WH	220-240 V	32.5 W	Not applicable
910629120226	4MX850 491 LED55S/830 PSD WB WH	220-240 V	32.5 W	Not applicable
910629120326	4MX850 491 LED55S/840 PSD WB WH	220-240 V	32.5 W	Not applicable
910629120726	4MX850 581 LED55S/840 PSD WB WH	220-240 V	32.5 W	Not applicable
910629121626	4MX850 491 LED40S/830 PSD NB WH	220-240 V	24 W	Not applicable
910629121726	4MX850 491 LED40S/840 PSD NB WH	220-240 V	24 W	Not applicable
910629121826	4MX850 491 LED40S/830 PSD WB WH	220-240 V	24 W	Not applicable
910629121926	4MX850 491 LED40S/840 PSD WB WH	220-240 V	24 W	Not applicable
910629122126	4MX850 581 LED40S/840 PSD NB WH	220-240 V	24 W	Not applicable
910629122326	4MX850 581 LED40S/840 PSD WB WH	220-240 V	24 W	Not applicable
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	220-240 V	32.5 W	Not applicable
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	220-240 V	32.5 W	Not applicable
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	220-240 V	32.5 W	Not applicable
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	220-240 V	24 W	Not applicable
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	220-240 V	24 W	Not applicable
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	220-240 V	39 W	Not applicable
910629158126	4MX850 491 LED66S/840 PSD WB WH	220-240 V	39 W	Not applicable
910629158226	4MX850 491 LED66S/840 PSD NB WH	220-240 V	39 W	Not applicable
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	220-240 V	39 W	Not applicable
910629160126	4MX850 491 LED66S/830 PSD WB WH	220-240 V	39 W	Not applicable
910629160226	4MX850 491 LED66S/830 PSD NB WH	220-240 V	39 W	Not applicable
910629160326	4MX850 581 LED66S/840 PSD WB WH	220-240 V	39 W	Not applicable
910629160426	4MX850 581 LED66S/840 PSD NB WH	220-240 V	39 W	Not applicable
910629160526	4MX850 491 LED40S/840 PSD A20 WH	220-240 V	24 W	Not applicable
910629160626	4MX850 491 LED55S/840 PSD A20 WH	220-240 V	32.5 W	Not applicable
910629160726	4MX850 491 LED55S/830 PSD A20 WH	220-240 V	32.5 W	Not applicable
910629161026	4MX850 491 LED40S/830 PSD A20 WH	220-240 V	24 W	Not applicable
910629162126	4MX850 491 LED66S/840 PSD A20 WH	220-240 V	39 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	220-240 V	43 W	Not applicable
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	220-240 V	32.5 W	Not applicable
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	220-240 V	39 W	Not applicable
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	220-240 V	32.5 W	Not applicable

Controls and Dimming

Order Code	Full Product Name	Embedded control
910500460502	4MX850 491 LED80S/840 PSD WB SI	-
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	Constant light output
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	Constant light output
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	Constant light output
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	Constant light output
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	Constant light output
910500460049	4MX850 491 LED80S/840 PSD VWB WH	-
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	-
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	-
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	-
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	-
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	-
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	-
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	-
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	-
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	-
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	-
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	-
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	-
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	-
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	-
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	-
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	-
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	-
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	-
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	-
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	-
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	-
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	-
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	-
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	-
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	-
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	-
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	-

Order Code	Full Product Name	Embedded control
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-
910629167426	4MX850 491 LED80S/840 PSD NB WH	-
910629167526	4MX850 491 LED80S/840 PSD WB WH	-
910500460518	4MX850 581 LED66S/830 PSD WB SI	-
910629121026	4MX850 491 LED55S/830 PSD WB SI	-
910629121126	4MX850 491 LED55S/840 PSD WB SI	-
910629121426	4MX850 581 LED55S/830 PSD WB SI	-
910629121526	4MX850 581 LED55S/840 PSD WB SI	-
910629122426	4MX850 491 LED40S/830 PSD NB SI	-
910629122526	4MX850 491 LED40S/840 PSD NB SI	-
910629122626	4MX850 491 LED40S/830 PSD WB SI	-
910629122726	4MX850 491 LED40S/840 PSD WB SI	-
910629122826	4MX850 581 LED40S/830 PSD NB SI	-
910629123026	4MX850 581 LED40S/830 PSD WB SI	-
910629123126	4MX850 581 LED40S/840 PSD WB SI	-
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	-
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	-
910629160826	4MX850 491 LED55S/830 PSD A20 SI	-
910629160926	4MX850 491 LED55S/840 PSD A20 SI	-
910629161126	4MX850 491 LED40S/830 PSD A20 SI	-
910629161226	4MX850 491 LED40S/840 PSD A20 SI	-
910629162226	4MX850 491 LED66S/840 PSD A20 SI	-
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	-
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	-
910500457964	4MX850 581 LED80S/840 PSD NB WH	-
910500457965	4MX850 581 LED80S/840 PSD WB WH	-
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	Constant light output
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	Constant light output
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	-
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	-
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	-
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	-
910500460048	4MX850 581 LED80S/840 PSD VWB WH	-
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	-
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	-
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	-
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	-

Order Code	Full Product Name	Embedded control
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	-
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	-
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	-
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	-
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	-
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	-
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	-
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	-
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	-
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	-
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	-
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	-
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	-
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	-
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-
910500460477	4MX850 581 LED80S/830 PSD WB WH	-
910500460483	4MX850 581 LED80S/840 PSD A20 WH	-
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	-
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	-
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	-
910629120126	4MX850 491 LED55S/840 PSD NB WH	-
910629120226	4MX850 491 LED55S/830 PSD WB WH	-
910629120326	4MX850 491 LED55S/840 PSD WB WH	-
910629120726	4MX850 581 LED55S/840 PSD WB WH	-
910629121626	4MX850 491 LED40S/830 PSD NB WH	-
910629121726	4MX850 491 LED40S/840 PSD NB WH	-
910629121826	4MX850 491 LED40S/830 PSD WB WH	-
910629121926	4MX850 491 LED40S/840 PSD WB WH	-
910629122126	4MX850 581 LED40S/840 PSD NB WH	-
910629122326	4MX850 581 LED40S/840 PSD WB WH	-
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	-
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	-
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	-
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	-
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	-
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	-
910629158126	4MX850 491 LED66S/840 PSD WB WH	-
910629158226	4MX850 491 LED66S/840 PSD NB WH	-
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	-
910629160126	4MX850 491 LED66S/830 PSD WB WH	-
910629160226	4MX850 491 LED66S/830 PSD NB WH	-
910629160326	4MX850 581 LED66S/840 PSD WB WH	-

Order Code	Full Product Name	Embedded control
910629160426	4MX850 581 LED66S/840 PSD NB WH	-
910629160526	4MX850 491 LED40S/840 PSD A20 WH	-
910629160626	4MX850 491 LED55S/840 PSD A20 WH	-
910629160726	4MX850 491 LED55S/830 PSD A20 WH	-
910629161026	4MX850 491 LED40S/830 PSD A20 WH	-
910629162126	4MX850 491 LED66S/840 PSD A20 WH	-
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	-
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	-
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	-
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910500460502	4MX850 491 LED80S/840 PSD WB SI	Silver
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	White
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	White
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	White
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	White
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	White
910500460049	4MX850 491 LED80S/840 PSD VWB WH	White
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	White
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	White
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	White
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	White
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	White
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	White
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	White
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	White
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	White
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	White
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	White
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	White
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	White
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	White
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	White
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	White
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	White
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	White
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	White
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	White
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	White
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	White

Order Code	Full Product Name	Housing Color
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	White
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	White
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	White
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	White
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	White
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	White
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	White
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	White
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	White
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	White
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	White
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	White
910629167426	4MX850 491 LED80S/840 PSD NB WH	White
910629167526	4MX850 491 LED80S/840 PSD WB WH	White
910500460518	4MX850 581 LED66S/830 PSD WB SI	Silver
910629121026	4MX850 491 LED55S/830 PSD WB SI	Silver
910629121126	4MX850 491 LED55S/840 PSD WB SI	Silver
910629121426	4MX850 581 LED55S/830 PSD WB SI	Silver
910629121526	4MX850 581 LED55S/840 PSD WB SI	Silver
910629122426	4MX850 491 LED40S/830 PSD NB SI	Silver
910629122526	4MX850 491 LED40S/840 PSD NB SI	Silver
910629122626	4MX850 491 LED40S/830 PSD WB SI	Silver
910629122726	4MX850 491 LED40S/840 PSD WB SI	Silver
910629122826	4MX850 581 LED40S/830 PSD NB SI	Silver
910629123026	4MX850 581 LED40S/830 PSD WB SI	Silver
910629123126	4MX850 581 LED40S/840 PSD WB SI	Silver
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	Silver
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	Silver
910629160826	4MX850 491 LED55S/830 PSD A20 SI	Silver
910629160926	4MX850 491 LED55S/840 PSD A20 SI	Silver
910629161126	4MX850 491 LED40S/830 PSD A20 SI	Silver
910629161226	4MX850 491 LED40S/840 PSD A20 SI	Silver
910629162226	4MX850 491 LED66S/840 PSD A20 SI	Silver
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	Silver
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	Silver
910500457964	4MX850 581 LED80S/840 PSD NB WH	White
910500457965	4MX850 581 LED80S/840 PSD WB WH	White
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	White
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	White
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	White
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	White
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	White

Order Code	Full Product Name	Housing Color
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	White
910500460048	4MX850 581 LED80S/840 PSD VWB WH	White
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	White
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	White
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	White
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	White
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	White
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	White
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	White
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	White
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	White
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	White
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	White
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	White
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	White
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	White
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	White
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	White
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	White
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	White
910500460476	4MX850 581 LED80S/830 PSD VWB WH	White
910500460477	4MX850 581 LED80S/830 PSD WB WH	White
910500460483	4MX850 581 LED80S/840 PSD A20 WH	White
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	White
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	White
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	White
910629120126	4MX850 491 LED55S/840 PSD NB WH	White
910629120226	4MX850 491 LED55S/830 PSD WB WH	White
910629120326	4MX850 491 LED55S/840 PSD WB WH	White
910629120726	4MX850 581 LED55S/840 PSD WB WH	White
910629121626	4MX850 491 LED40S/830 PSD NB WH	White
910629121726	4MX850 491 LED40S/840 PSD NB WH	White
910629121826	4MX850 491 LED40S/830 PSD WB WH	White
910629121926	4MX850 491 LED40S/840 PSD WB WH	White
910629122126	4MX850 581 LED40S/840 PSD NB WH	White
910629122326	4MX850 581 LED40S/840 PSD WB WH	White
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	White
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	White
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	White
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	White
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	White
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	White

Order Code	Full Product Name	Housing Color
910629158126	4MX850 491 LED66S/840 PSD WB WH	White
910629158226	4MX850 491 LED66S/840 PSD NB WH	White
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	White
910629160126	4MX850 491 LED66S/830 PSD WB WH	White
910629160226	4MX850 491 LED66S/830 PSD NB WH	White
910629160326	4MX850 581 LED66S/840 PSD WB WH	White
910629160426	4MX850 581 LED66S/840 PSD NB WH	White
910629160526	4MX850 491 LED40S/840 PSD A20 WH	White
910629160626	4MX850 491 LED55S/840 PSD A20 WH	White
910629160726	4MX850 491 LED55S/830 PSD A20 WH	White
910629161026	4MX850 491 LED40S/830 PSD A20 WH	White
910629162126	4MX850 491 LED66S/840 PSD A20 WH	White
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	White
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	White
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	White
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	White

Emergency Operation

Order Code	Full Product Name	Emergency lighting
910500460502	4MX850 491 LED80S/840 PSD WB SI	-
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	-
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	-
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	-
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	-
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	-
910500460049	4MX850 491 LED80S/840 PSD VWB WH	-
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	-
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	-
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	-
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	-
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	-
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	-
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	-
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	-
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version

Order Code	Full Product Name	Emergency lighting
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	-
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	-
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	-
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	Emergency lighting 3 hours duration Pro version
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	Emergency lighting 3 hours duration with DALI interface
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	-
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	-
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	-
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	-
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	-
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-
910629167426	4MX850 491 LED80S/840 PSD NB WH	-
910629167526	4MX850 491 LED80S/840 PSD WB WH	-
910500460518	4MX850 581 LED66S/830 PSD WB SI	-
910629121026	4MX850 491 LED55S/830 PSD WB SI	-
910629121126	4MX850 491 LED55S/840 PSD WB SI	-
910629121426	4MX850 581 LED55S/830 PSD WB SI	-
910629121526	4MX850 581 LED55S/840 PSD WB SI	-
910629122426	4MX850 491 LED40S/830 PSD NB SI	-
910629122526	4MX850 491 LED40S/840 PSD NB SI	-
910629122626	4MX850 491 LED40S/830 PSD WB SI	-
910629122726	4MX850 491 LED40S/840 PSD WB SI	-
910629122826	4MX850 581 LED40S/830 PSD NB SI	-
910629123026	4MX850 581 LED40S/830 PSD WB SI	-
910629123126	4MX850 581 LED40S/840 PSD WB SI	-
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	-
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	-
910629160826	4MX850 491 LED55S/830 PSD A20 SI	-
910629160926	4MX850 491 LED55S/840 PSD A20 SI	-
910629161126	4MX850 491 LED40S/830 PSD A20 SI	-
910629161226	4MX850 491 LED40S/840 PSD A20 SI	-
910629162226	4MX850 491 LED66S/840 PSD A20 SI	-
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	-
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	-
910500457964	4MX850 581 LED80S/840 PSD NB WH	-

Order Code	Full Product Name	Emergency lighting
910500457965	4MX850 581 LED80S/840 PSD WB WH	-
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	-
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	-
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	-
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	-
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	-
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	-
910500460048	4MX850 581 LED80S/840 PSD VWB WH	-
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	-
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	-
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	-
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	-
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	-
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	-
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	-
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	Emergency lighting 3 hours duration basic version
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	-
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-
910500460477	4MX850 581 LED80S/830 PSD WB WH	-
910500460483	4MX850 581 LED80S/840 PSD A20 WH	-
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	Emergency lighting 3 hours duration Pro version
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	Emergency lighting 3 hours duration with DALI interface
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	-
910629120126	4MX850 491 LED55S/840 PSD NB WH	-
910629120226	4MX850 491 LED55S/830 PSD WB WH	-
910629120326	4MX850 491 LED55S/840 PSD WB WH	-
910629120726	4MX850 581 LED55S/840 PSD WB WH	-
910629121626	4MX850 491 LED40S/830 PSD NB WH	-
910629121726	4MX850 491 LED40S/840 PSD NB WH	-
910629121826	4MX850 491 LED40S/830 PSD WB WH	-
910629121926	4MX850 491 LED40S/840 PSD WB WH	-
910629122126	4MX850 581 LED40S/840 PSD NB WH	-
910629122326	4MX850 581 LED40S/840 PSD WB WH	-

Order Code	Full Product Name	Emergency lighting
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	-
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	-
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	-
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	-
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	-
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	-
910629158126	4MX850 491 LED66S/840 PSD WB WH	-
910629158226	4MX850 491 LED66S/840 PSD NB WH	-
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	-
910629160126	4MX850 491 LED66S/830 PSD WB WH	-
910629160226	4MX850 491 LED66S/830 PSD NB WH	-
910629160326	4MX850 581 LED66S/840 PSD WB WH	-
910629160426	4MX850 581 LED66S/840 PSD NB WH	-
910629160526	4MX850 491 LED40S/840 PSD A20 WH	-
910629160626	4MX850 491 LED55S/840 PSD A20 WH	-
910629160726	4MX850 491 LED55S/830 PSD A20 WH	-
910629161026	4MX850 491 LED40S/830 PSD A20 WH	-
910629162126	4MX850 491 LED66S/840 PSD A20 WH	-
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	-
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	-
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	-

Approval and Application

Order Code	Full Product Name	Glow-wire test	Ambient temperature range
910500460502	4MX850 491 LED80S/840 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460049	4MX850 491 LED80S/840 PSD VWB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C

Order Code	Full Product Name	Glow-wire test	Ambient temperature range
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	Temperature 850 °C, duration 30 s	-20 to +35 °C
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	Temperature 650 °C, duration 30 s	0 to +35 °C
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629167426	4MX850 491 LED80S/840 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629167526	4MX850 491 LED80S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460518	4MX850 581 LED66S/830 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629121026	4MX850 491 LED55S/830 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629121126	4MX850 491 LED55S/840 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629121426	4MX850 581 LED55S/830 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629121526	4MX850 581 LED55S/840 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629122426	4MX850 491 LED40S/830 PSD NB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629122526	4MX850 491 LED40S/840 PSD NB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629122626	4MX850 491 LED40S/830 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629122726	4MX850 491 LED40S/840 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629122826	4MX850 581 LED40S/830 PSD NB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629123026	4MX850 581 LED40S/830 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629123126	4MX850 581 LED40S/840 PSD WB SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160826	4MX850 491 LED55S/830 PSD A20 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160926	4MX850 491 LED55S/840 PSD A20 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C

Order Code	Full Product Name	Glow-wire test	Ambient temperature range
910629161126	4MX850 491 LED40S/830 PSD A20 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629161226	4MX850 491 LED40S/840 PSD A20 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629162226	4MX850 491 LED66S/840 PSD A20 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500457964	4MX850 581 LED80S/840 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500457965	4MX850 581 LED80S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460048	4MX850 581 LED80S/840 PSD VWB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460476	4MX850 581 LED80S/830 PSD VWB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460477	4MX850 581 LED80S/830 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460483	4MX850 581 LED80S/840 PSD A20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	Temperature 650 °C, duration 30 s	-20 to +35 °C
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629120126	4MX850 491 LED55S/840 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629120226	4MX850 491 LED55S/830 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629120326	4MX850 491 LED55S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629120726	4MX850 581 LED55S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C

Order Code	Full Product Name	Glow-wire test	Ambient temperature range
910629121626	4MX850 491 LED40S/830 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629121726	4MX850 491 LED40S/840 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629121826	4MX850 491 LED40S/830 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629121926	4MX850 491 LED40S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629122126	4MX850 581 LED40S/840 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629122326	4MX850 581 LED40S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629158126	4MX850 491 LED66S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629158226	4MX850 491 LED66S/840 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160126	4MX850 491 LED66S/830 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160226	4MX850 491 LED66S/830 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160326	4MX850 581 LED66S/840 PSD WB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160426	4MX850 581 LED66S/840 PSD NB WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160526	4MX850 491 LED40S/840 PSD A20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160626	4MX850 491 LED55S/840 PSD A20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629160726	4MX850 491 LED55S/830 PSD A20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629161026	4MX850 491 LED40S/830 PSD A20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629162126	4MX850 491 LED66S/840 PSD A20 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	Temperature 650 °C, duration 30 s	-20 to +35 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance	Initial chromaticity
910500460502	4MX850 491 LED80S/840 PSD WB SI	+/-10%	(0.38, 0.38) SDCM <3.5
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460049	4MX850 491 LED80S/840 PSD VWB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Luminous flux tolerance	Initial chromaticity
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-10% / +10%	(0.38, 0.38) SDCM <3.5
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-10% / +10%	(0.38, 0.38) SDCM <3.5
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-10% / +10%	(0.38, 0.38) SDCM <3.5
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-10% / +10%	(0.38, 0.38) SDCM <3.5
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-10% / +10%	(0.38, 0.38) SDCM <3.5
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-10% / +10%	(0.38, 0.38) SDCM <3.5
910629167426	4MX850 491 LED80S/840 PSD NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629167526	4MX850 491 LED80S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460518	4MX850 581 LED66S/830 PSD WB SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629121026	4MX850 491 LED55S/830 PSD WB SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629121126	4MX850 491 LED55S/840 PSD WB SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629121426	4MX850 581 LED55S/830 PSD WB SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629121526	4MX850 581 LED55S/840 PSD WB SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629122426	4MX850 491 LED40S/830 PSD NB SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629122526	4MX850 491 LED40S/840 PSD NB SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629122626	4MX850 491 LED40S/830 PSD WB SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629122726	4MX850 491 LED40S/840 PSD WB SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629122826	4MX850 581 LED40S/830 PSD NB SI	+/-10%	(0.43, 0.40) SDCM <3.5

Order Code	Full Product Name	Luminous flux tolerance	Initial chromaticity
910629123026	4MX850 581 LED40S/830 PSD WB SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629123126	4MX850 581 LED40S/840 PSD WB SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629160826	4MX850 491 LED55S/830 PSD A20 SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629160926	4MX850 491 LED55S/840 PSD A20 SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629161126	4MX850 491 LED40S/830 PSD A20 SI	+/-10%	(0.43, 0.40) SDCM <3.5
910629161226	4MX850 491 LED40S/840 PSD A20 SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629162226	4MX850 491 LED66S/840 PSD A20 SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	+/-10%	(0.38, 0.38) SDCM <3.5
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	+/-10%	(0.38, 0.38) SDCM <3.5
910500457964	4MX850 581 LED80S/840 PSD NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500457965	4MX850 581 LED80S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460048	4MX850 581 LED80S/840 PSD VWB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910500460476	4MX850 581 LED80S/830 PSD VWB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460477	4MX850 581 LED80S/830 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460483	4MX850 581 LED80S/840 PSD A20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	+/-10%	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Luminous flux tolerance	Initial chromaticity
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	+/-10%	(0.38, 0.38) SDCM <3.5
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910629120126	4MX850 491 LED55S/840 PSD NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629120226	4MX850 491 LED55S/830 PSD WB WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629120326	4MX850 491 LED55S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629120726	4MX850 581 LED55S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629121626	4MX850 491 LED40S/830 PSD NB WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629121726	4MX850 491 LED40S/840 PSD NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629121826	4MX850 491 LED40S/830 PSD WB WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629121926	4MX850 491 LED40S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629122126	4MX850 581 LED40S/840 PSD NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629122326	4MX850 581 LED40S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629158126	4MX850 491 LED66S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629158226	4MX850 491 LED66S/840 PSD NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629160126	4MX850 491 LED66S/830 PSD WB WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629160226	4MX850 491 LED66S/830 PSD NB WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629160326	4MX850 581 LED66S/840 PSD WB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629160426	4MX850 581 LED66S/840 PSD NB WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629160526	4MX850 491 LED40S/840 PSD A20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629160626	4MX850 491 LED55S/840 PSD A20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629160726	4MX850 491 LED55S/830 PSD A20 WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629161026	4MX850 491 LED40S/830 PSD A20 WH	+/-10%	(0.43, 0.40) SDCM <3.5
910629162126	4MX850 491 LED66S/840 PSD A20 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	+/-10%	(0.38, 0.38) SDCM <3.5
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	+/-10%	(0.38, 0.38) SDCM <3.5
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	+/-10%	(0.38, 0.38) SDCM <3.5

Product Data


Order Code	Full Product Name	Product family code
910500460502	4MX850 491 LED80S/840 PSD WB SI	4MX850
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	4MX850
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	4MX850
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	4MX850
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	4MX850

Order Code	Full Product Name	Product family code
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	4MX850
910500460049	4MX850 491 LED80S/840 PSD VWB WH	4MX850
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	4MX850
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	4MX850
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	4MX850
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	4MX850
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	4MX850
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	4MX850
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	4MX850
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	4MX850
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	4MX883
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	4MX883
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	4MX883
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	4MX883
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	4MX883
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	4MX883
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	4MX883
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	4MX883
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	4MX883
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	4MX850
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	4MX850
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	4MX850
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	4MX883
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	4MX883
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	4MX850
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	4MX850
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	4MX850
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	4MX850
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	4MX850
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	4MX850
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	4MX850
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	4MX850
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	4MX850
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	4MX850
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	4MX850
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	4MX850
910629167426	4MX850 491 LED80S/840 PSD NB WH	4MX850
910629167526	4MX850 491 LED80S/840 PSD WB WH	4MX850
910500460518	4MX850 581 LED66S/830 PSD WB SI	4MX850
910629121026	4MX850 491 LED55S/830 PSD WB SI	4MX850
910629121126	4MX850 491 LED55S/840 PSD WB SI	4MX850
910629121426	4MX850 581 LED55S/830 PSD WB SI	4MX850


Order Code	Full Product Name	Product family code
910629121526	4MX850 581 LED55S/840 PSD WB SI	4MX850
910629122426	4MX850 491 LED40S/830 PSD NB SI	4MX850
910629122526	4MX850 491 LED40S/840 PSD NB SI	4MX850
910629122626	4MX850 491 LED40S/830 PSD WB SI	4MX850
910629122726	4MX850 491 LED40S/840 PSD WB SI	4MX850
910629122826	4MX850 581 LED40S/830 PSD NB SI	4MX850
910629123026	4MX850 581 LED40S/830 PSD WB SI	4MX850
910629123126	4MX850 581 LED40S/840 PSD WB SI	4MX850
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	4MX850
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	4MX850
910629160826	4MX850 491 LED55S/830 PSD A20 SI	4MX850
910629160926	4MX850 491 LED55S/840 PSD A20 SI	4MX850
910629161126	4MX850 491 LED40S/830 PSD A20 SI	4MX850
910629161226	4MX850 491 LED40S/840 PSD A20 SI	4MX850
910629162226	4MX850 491 LED66S/840 PSD A20 SI	4MX850
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	4MX850
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	4MX850
910500457964	4MX850 581 LED80S/840 PSD NB WH	4MX850
910500457965	4MX850 581 LED80S/840 PSD WB WH	4MX850
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	4MX850
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	4MX850
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	4MX850
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	4MX850
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	4MX850
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	4MX850
910500460048	4MX850 581 LED80S/840 PSD VWB WH	4MX850
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	4MX850
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	4MX850
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	4MX850
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	4MX850
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	4MX850
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	4MX850
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	4MX850
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	4MX883
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	4MX883
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	4MX883
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	4MX883
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	4MX883
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	4MX883
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	4MX883
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	4MX883
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	4MX883

Order Code	Full Product Name	Product family code
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	4MX883
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	4MX850
910500460476	4MX850 581 LED80S/830 PSD VWB WH	4MX850
910500460477	4MX850 581 LED80S/830 PSD WB WH	4MX850
910500460483	4MX850 581 LED80S/840 PSD A20 WH	4MX850
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	4MX883
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	4MX883
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	4MX850
910629120126	4MX850 491 LED55S/840 PSD NB WH	4MX850
910629120226	4MX850 491 LED55S/830 PSD WB WH	4MX850
910629120326	4MX850 491 LED55S/840 PSD WB WH	4MX850
910629120726	4MX850 581 LED55S/840 PSD WB WH	4MX850
910629121626	4MX850 491 LED40S/830 PSD NB WH	4MX850
910629121726	4MX850 491 LED40S/840 PSD NB WH	4MX850
910629121826	4MX850 491 LED40S/830 PSD WB WH	4MX850
910629121926	4MX850 491 LED40S/840 PSD WB WH	4MX850
910629122126	4MX850 581 LED40S/840 PSD NB WH	4MX850
910629122326	4MX850 581 LED40S/840 PSD WB WH	4MX850
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	4MX850
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	4MX850
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	4MX850
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	4MX850
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	4MX850
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	4MX850
910629158126	4MX850 491 LED66S/840 PSD WB WH	4MX850
910629158226	4MX850 491 LED66S/840 PSD NB WH	4MX850
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	4MX850
910629160126	4MX850 491 LED66S/830 PSD WB WH	4MX850
910629160226	4MX850 491 LED66S/830 PSD NB WH	4MX850
910629160326	4MX850 581 LED66S/840 PSD WB WH	4MX850
910629160426	4MX850 581 LED66S/840 PSD NB WH	4MX850
910629160526	4MX850 491 LED40S/840 PSD A20 WH	4MX850
910629160626	4MX850 491 LED55S/840 PSD A20 WH	4MX850
910629160726	4MX850 491 LED55S/830 PSD A20 WH	4MX850
910629161026	4MX850 491 LED40S/830 PSD A20 WH	4MX850
910629162126	4MX850 491 LED66S/840 PSD A20 WH	4MX850
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	4MX883
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	4MX850
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	4MX850
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	4MX850


Polar normal diagrams




4MX850I - 910500457964




4MX850I - 910500457965




4MX850I - 910500460070




4MX850I - 910500460477




4MX850I - 910500460007




4MX850I - 910500460420




4MX850I - 910500460502




4MX850I - 910500460220




4MX850I - 910629123126




4MX850I - 910629125126




4MX850I - 910629125926




4MX850I - 910629126126




4MX850I - 910629121126




4MX850I - 910629167526




4MX850I - 910629121926




4MX850I - 910629158226




4MX850I - 910629121526




4MX850I - 910629167426




4MX850I - 910629160626




4MX850I - 910629162126




4MX850I - 910629121726




4MX850I - 910629160926




4MX850I - 910629160326




4MX850I - 910629122126




4MX850I - 910629122726




4MX850I - 910629161226




4MX850I - 910629122326




4MX850I - 910629122526




4MX850I - 910629120126




4MX850I - 910629120726




4MX850I - 910629120326




4MX850I - 910629124926




4MX850I - 910629158026




4MX850I - 910629160426




4MX850I - 910629160526




4MX850I - 910629162226




4MX850I - 910500460537




4MX850I - 910500460538




4MX850I - 910500460560




4MX850I - 910500460562




4MX850I - 910500460561




4MX850I - 910500460595




4MX850I - 910500460009




4MX850I - 910500460008




4MX850I - 910500460010




4MX850I - 910500460049




4MX850I - 910500460048




4MX850I - 910500460075




4MX850I - 910500460216




4MX850I - 910500460215




4MX850I - 910500460218




4MX850I - 910500460221




4MX850I - 910500460222




4MX850I - 910500460217




4MX850I - 910500460223




4MX850I - 910500460391




4MX850I - 910500460415




4MX850I - 910500460393




4MX850I - 910500460476




4MX850I - 910500460483




4MX850I - 910500460518




4MX850I - 910500460224




4MX850I - 910500460225




4MX850I - 910500460219




4MX850I - 910505105689




4MX850I - 910505105684




4MX850I - 910505105688



4MX850I - 910505105686



4MX850I - 910505105687



4MX850I - 910505105685