



Maxos LED General Lighting – innovative, flexible solution delivers ideal light output

Maxos LED

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED General Lighting offers best-in-class energy savings while delivering high lux levels at the required colour temperatures and glare factors. The minimalistic Maxos LED General Lighting system comprises exchangeable mid-power LED boards mounted on a standard Maxos trunking rail. A choice of wide and medium-beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: the use of our upgradable LED engine platform makes Maxos LED Industry a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven Maxos trunking system

Features

- Mid-power LED boards; exchangeable LED unit
- Up to 138 lm/W efficiency
- LED gear trays for T5 and TL-D-length trunkings (high lumen output); replacement LED gear trays with same lumen packages as installed T5 and TL-D solutions (lower wattage)
- Choice of narrow, medium, double asymmetric and asymmetric lenses
- Compatible with our standard Maxos and TTX400 rails for TL5 49 W and TL-D 58 W lengths

Application


- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers
- Showrooms

Versions



Maxos LED Industry

Dimensional drawing



Maxos LED

Product details



IPDP_4MX850i_0001-Detail
photo




IPDP_4MX850i_0003-Detail
photo



IPDP_4MX850i_0005-Detail
photo

Polar Wide Diagrams



Polar Normal (separate) - 4MX850I -
910629121526

