



Maxos LED Performer – efficient and precise line lighting

Maxos LED Performer

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Benefits

- Extremely fast payback
- Breakthrough optical system for precise beam shaping
- Flexible in terms of retrofits, spots, changes, accessories

Features


- Low energy consumption compared to fluorescent
- Excellent beam shaping for less spill light and exact light distribution in horizontal and vertical planes
- Proven Philips LED engines (Fortimo)
- Can be mounted, new or retrofit, onto a Maxos rail

Application

- Supermarkets
- Warehouses
- Production facilities

Maxos LED Performer

Dimensional drawing




Product details

IPDP_4MX900i_0001-Detail photo



IPDP_4MX900i_0003-Detail photo



IPDP_4MX900i_0007-Detail photo



IPDP_4MX900i_0011-Detail photo



Maxos LED Performer

Product details



IPDP_4MX900i_0013-Detail
photo

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80

Operating and Electrical

Protection class IEC	Safety class I
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

Mechanical and Housing

Mech. impact protection code	IK02
Ingress protection code	IP40

Approval and Application

CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Lamp family code
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	50S
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	75S
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	75S
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	75S
910500460311	4MX900 581 LED40S/840 PSD WB WH	40S
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	50S
910629173126	4MX900 581 LED50S/840 PSD MB WH	LED50S
910629177026	4MX900 581 LED50S/840 PSD WB WH	LED50S
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	75S
910629132426	4MX900 LED40S/840 PSD WB WH L1200	LED40S
910629138826	4MX900 LED90S/840 PSD WB WH L1800	LED90S
910629138926	4MX900 LED90S/840 PSD MB WH L1800	LED90S
910629142026	4MX900 491 LED40S/840 PSU WB WH	LED40S
910629142126	4MX900 491 LED40S/840 PSU MB WH	LED40S
910629144426	4MX900 491 LED40S/840 PSD WB WH	LED40S
910629144526	4MX900 491 LED40S/840 PSD MB WH	LED40S
910629144626	4MX900 491 LED40S/840 PSD NB WH	LED40S
910629144826	4MX900 491 LED50S/840 PSD WB WH	LED50S
910629144926	4MX900 491 LED50S/840 PSD MB WH	LED50S
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	LED60S
910629145726	4MX900 581 LED50S/840 PSU A30 WH	LED50S
910629145826	4MX900 491 LED40S/840 PSU A30 WH	LED40S
910629145926	4MX900 491 LED50S/840 PSU A30 WH	LED50S
910629146026	4MX900 581 LED50S/840 PSU WB WH	LED50S
910629146426	4MX900 491 LED50S/840 PSU WB WH	LED50S
910629146526	4MX900 491 LED50S/840 PSU MB WH	LED50S
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	LED90S
910629148526	4MX900 491 LED75S/840 PSU A30 WH	LED75S
910629170326	4MX900 491 LED75S/840 PSU WB WH	LED75S
910629170426	4MX900 491 LED75S/840 PSU MB WH	LED75S
910629170826	4MX900 581 LED75S/840 PSU WB WH	LED75S
910629170926	4MX900 581 LED75S/840 PSU MB WH	LED75S
910629171026	4MX900 581 LED75S/840 PSU NB WH	LED75S
910629171326	4MX900 491 LED75S/840 PSD WB WH	LED75S
910629171426	4MX900 491 LED75S/840 PSD MB WH	LED75S
910629171526	4MX900 491 LED75S/840 PSD NB WH	LED75S
910629171826	4MX900 491 LED75S/840 PSD A30 WH	LED75S

Maxos LED Performer

Order Code	Full Product Name	Lamp family code
910629171926	4MX900 581 LED75S/840 PSD WB WH	LED75S
910629172026	4MX900 581 LED75S/840 PSD MB WH	LED75S
910629172126	4MX900 581 LED75S/840 PSD NB WH	LED75S
910629172426	4MX900 581 LED75S/840 PSD A30 WH	LED75S
910629131626	4MX900 LED40S/840 PSD WB SI L1200	LED40S
910629136426	4MX900 LED60S/840 PSD WB SI L1800	LED60S
910629138026	4MX900 LED90S/840 PSD WB SI L1800	LED90S
910629138126	4MX900 LED90S/840 PSD MB SI L1800	LED90S
910629141226	4MX900 491 LED40S/840 PSU WB SI	LED40S
910629141326	4MX900 491 LED40S/840 PSU MB SI	LED40S
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	LED90S
910629177526	4MX900 581 LED50S/840 PSU A30 SI	LED50S

Light Technical (1/2)

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	155 lm/W	5,000 lm	-	Wide beam
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	149 lm/W	7,500 lm	-	Wide beam
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	149 lm/W	7,500 lm	-	Wide beam
910500460311	4MX900 581 LED40S/840 PSD WB WH	158 lm/W	4,000 lm	-	Wide beam
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	155 lm/W	5,000 lm	-	Wide beam
910629173126	4MX900 581 LED50S/840 PSD MB WH	155 lm/W	5,000 lm	-	Medium beam
910629177026	4MX900 581 LED50S/840 PSD WB WH	155 lm/W	5,000 lm	-	Wide beam
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	149 lm/W	7,500 lm	1	Medium beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910629132426	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4,000 lm	1	Wide beam
910629138826	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9,000 lm	1	Wide beam
910629138926	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9,000 lm	1	Medium beam
910629142026	4MX900 491 LED40S/840 PSU WB WH	158 lm/W	4,000 lm	1	Wide beam
910629142126	4MX900 491 LED40S/840 PSU MB WH	158 lm/W	4,000 lm	1	Medium beam
910629144426	4MX900 491 LED40S/840 PSD WB WH	158 lm/W	4,000 lm	1	Wide beam
910629144526	4MX900 491 LED40S/840 PSD MB WH	158 lm/W	4,000 lm	1	Medium beam
910629144626	4MX900 491 LED40S/840 PSD NB WH	158 lm/W	4,000 lm	1	Narrow beam
910629144826	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5,000 lm	1	Wide beam
910629144926	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5,000 lm	1	Medium beam

Maxos LED Performer

Order Code	Full Product Name	Luminous Efficacy	Luminous Flux	Number of light sources	Optic type
		(rated) (Nom)			
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6,000 lm	1	Asymmetrical mirror axis angle 30°
910629145726	4MX900 581 LED50S/840 PSU A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629145826	4MX900 491 LED40S/840 PSU A30 WH	158 lm/W	4,000 lm	1	Asymmetrical mirror axis angle 30°
910629145926	4MX900 491 LED50S/840 PSU A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629146026	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	1	Wide beam
910629146426	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	1	Wide beam
910629146526	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5,000 lm	1	Medium beam
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9,000 lm	1	Asymmetrical mirror axis angle 30°
910629148526	4MX900 491 LED75S/840 PSU A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629170326	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7,500 lm	1	Wide beam
910629170426	4MX900 491 LED75S/840 PSU MB WH	149 lm/W	7,500 lm	1	Medium beam
910629170826	4MX900 581 LED75S/840 PSU WB WH	149 lm/W	7,500 lm	1	Wide beam
910629170926	4MX900 581 LED75S/840 PSU MB WH	149 lm/W	7,500 lm	1	Medium beam
910629171026	4MX900 581 LED75S/840 PSU NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629171326	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7,500 lm	1	Wide beam
910629171426	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7,500 lm	1	Medium beam

Order Code	Full Product Name	Luminous Efficacy	Luminous Flux	Number of light sources	Optic type
		(rated) (Nom)			
910629171526	4MX900 491 LED75S/840 PSD NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629171826	4MX900 491 LED75S/840 PSD A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629171926	4MX900 581 LED75S/840 PSD WB WH	149 lm/W	7,500 lm	1	Wide beam
910629172026	4MX900 581 LED75S/840 PSD MB WH	149 lm/W	7,500 lm	1	Medium beam
910629172126	4MX900 581 LED75S/840 PSD NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629172426	4MX900 581 LED75S/840 PSD A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629131626	4MX900 LED40S/840 PSD WB SI L1200	154 lm/W	4,000 lm	1	Wide beam
910629136426	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6,000 lm	1	Wide beam
910629138026	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9,000 lm	1	Wide beam
910629138126	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9,000 lm	1	Medium beam
910629141226	4MX900 491 LED40S/840 PSU WB SI	158 lm/W	4,000 lm	1	Wide beam
910629141326	4MX900 491 LED40S/840 PSU MB SI	158 lm/W	4,000 lm	1	Medium beam
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	150 lm/W	9,000 lm	1	Asymmetrical mirror axis angle 30°
910629177526	4MX900 581 LED50S/840 PSU A30 SI	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°

Maxos LED Performer

Light Technical (2/2)

Order Code	Full Product Name	Upward light output ratio
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	0
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	0
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	0
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	0
910500460311	4MX900 581 LED40S/840 PSD WB WH	0
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	0
910629173126	4MX900 581 LED50S/840 PSD MB WH	-
910629177026	4MX900 581 LED50S/840 PSD WB WH	-
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	0
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-
910629142026	4MX900 491 LED40S/840 PSU WB WH	-
910629142126	4MX900 491 LED40S/840 PSU MB WH	-
910629144426	4MX900 491 LED40S/840 PSD WB WH	-
910629144526	4MX900 491 LED40S/840 PSD MB WH	-
910629144626	4MX900 491 LED40S/840 PSD NB WH	-
910629144826	4MX900 491 LED50S/840 PSD WB WH	-
910629144926	4MX900 491 LED50S/840 PSD MB WH	-
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-
910629146026	4MX900 581 LED50S/840 PSU WB WH	-
910629146426	4MX900 491 LED50S/840 PSU WB WH	-

Order Code	Full Product Name	Upward light output ratio
910629146526	4MX900 491 LED50S/840 PSU MB WH	-
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-
910629170326	4MX900 491 LED75S/840 PSU WB WH	-
910629170426	4MX900 491 LED75S/840 PSU MB WH	-
910629170826	4MX900 581 LED75S/840 PSU WB WH	-
910629170926	4MX900 581 LED75S/840 PSU MB WH	-
910629171026	4MX900 581 LED75S/840 PSU NB WH	-
910629171326	4MX900 491 LED75S/840 PSD WB WH	-
910629171426	4MX900 491 LED75S/840 PSD MB WH	-
910629171526	4MX900 491 LED75S/840 PSD NB WH	-
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-
910629171926	4MX900 581 LED75S/840 PSD WB WH	-
910629172026	4MX900 581 LED75S/840 PSD MB WH	-
910629172126	4MX900 581 LED75S/840 PSD NB WH	-
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-
910629141226	4MX900 491 LED40S/840 PSU WB SI	-
910629141326	4MX900 491 LED40S/840 PSU MB SI	-
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-

Operating and Electrical

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	220 to 240 V	32.2 W
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	220 to 240 V	40.16 W
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	220 to 240 V	50.2 W
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	220 to 240 V	50.2 W
910500460311	4MX900 581 LED40S/840 PSD WB WH	220 to 240 V	25.2 W
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	220 to 240 V	32.2 W
910629173126	4MX900 581 LED50S/840 PSD MB WH	220 to 240 V	32.2 W
910629177026	4MX900 581 LED50S/840 PSD WB WH	220-240 V	32.2 W
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	220 to 240 V	50.2 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
910629132426	4MX900 LED40S/840 PSD WB WH L1200	220 to 240 V	25.9 W
910629138826	4MX900 LED90S/840 PSD WB WH L1800	220 to 240 V	60.1 W
910629138926	4MX900 LED90S/840 PSD MB WH L1800	220 to 240 V	60.1 W
910629142026	4MX900 491 LED40S/840 PSU WB WH	220 to 240 V	25.2 W
910629142126	4MX900 491 LED40S/840 PSU MB WH	220 to 240 V	25.2 W
910629144426	4MX900 491 LED40S/840 PSD WB WH	220 to 240 V	25.2 W
910629144526	4MX900 491 LED40S/840 PSD MB WH	220 to 240 V	25.2 W
910629144626	4MX900 491 LED40S/840 PSD NB WH	220 to 240 V	25.2 W
910629144826	4MX900 491 LED50S/840 PSD WB WH	220 to 240 V	32.2 W

Maxos LED Performer

Order Code	Full Product Name	Input Voltage	Power	
			Consumption	
910629144926	4MX900 491 LED50S/840 PSD MB WH	220 to 240 V	32.2 W	
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	220 to 240 V	37.3 W	
910629145726	4MX900 581 LED50S/840 PSU A30 WH	220 to 240 V	32.2 W	
910629145826	4MX900 491 LED40S/840 PSU A30 WH	220 to 240 V	25.2 W	
910629145926	4MX900 491 LED50S/840 PSU A30 WH	220 to 240 V	32.2 W	
910629146026	4MX900 581 LED50S/840 PSU WB WH	220 to 240 V	32.2 W	
910629146426	4MX900 491 LED50S/840 PSU WB WH	220 to 240 V	32.2 W	
910629146526	4MX900 491 LED50S/840 PSU MB WH	220 to 240 V	32.2 W	
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	220 to 240 V	60.1 W	
910629148526	4MX900 491 LED75S/840 PSU A30 WH	220 to 240 V	50.2 W	
910629170326	4MX900 491 LED75S/840 PSU WB WH	220 to 240 V	50.2 W	
910629170426	4MX900 491 LED75S/840 PSU MB WH	220 to 240 V	50.2 W	
910629170826	4MX900 581 LED75S/840 PSU WB WH	220 to 240 V	50.2 W	
910629170926	4MX900 581 LED75S/840 PSU MB WH	220 to 240 V	50.2 W	
910629171026	4MX900 581 LED75S/840 PSU NB WH	220 to 240 V	50.2 W	
910629171326	4MX900 491 LED75S/840 PSD WB WH	220 to 240 V	50.2 W	

Order Code	Full Product Name	Input Voltage	Power	
			Consumption	
910629171426	4MX900 491 LED75S/840 PSD MB WH	220 to 240 V	50.2 W	
910629171526	4MX900 491 LED75S/840 PSD NB WH	220 to 240 V	50.2 W	
910629171826	4MX900 491 LED75S/840 PSD A30 WH	220 to 240 V	50.2 W	
910629171926	4MX900 581 LED75S/840 PSD WB WH	220 to 240 V	50.2 W	
910629172026	4MX900 581 LED75S/840 PSD MB WH	220 to 240 V	50.2 W	
910629172126	4MX900 581 LED75S/840 PSD NB WH	220 to 240 V	50.2 W	
910629172426	4MX900 581 LED75S/840 PSD A30 WH	220 to 240 V	50.2 W	
910629131626	4MX900 LED40S/840 PSD WB SI L1200	220 to 240 V	25.9 W	
910629136426	4MX900 LED60S/840 PSD WB SI L1800	220 to 240 V	37.3 W	
910629138026	4MX900 LED90S/840 PSD WB SI L1800	220 to 240 V	60.1 W	
910629138126	4MX900 LED90S/840 PSD MB SI L1800	220 to 240 V	60.1 W	
910629141226	4MX900 491 LED40S/840 PSU WB SI	220 to 240 V	25.2 W	
910629141326	4MX900 491 LED40S/840 PSU MB SI	220 to 240 V	25.2 W	
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	220 to 240 V	60.1 W	
910629177526	4MX900 581 LED50S/840 PSU A30 SI	220 to 240 V	32.2 W	

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded	Maximum
			control	dim level
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	Yes	Constant light output	1%
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	Yes	Constant light output	1%
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	Yes	-	1%
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	Yes	-	1%
910500460311	4MX900 581 LED40S/840 PSD WB WH	Yes	-	1%
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	No	-	Not applicable
9106291713126	4MX900 581 LED50S/840 PSD MB WH	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded	Maximum
			control	dim level
910629177026	4MX900 581 LED50S/840 PSD WB WH	Yes	-	1%
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	Yes	Constant light output	1%
910629132426	4MX900 LED40S/840 PSD WB WH L1200	Yes	-	1%
910629138826	4MX900 LED90S/840 PSD WB WH L1800	Yes	-	1%
910629138926	4MX900 LED90S/840 PSD MB WH L1800	Yes	-	1%
910629142026	4MX900 491 LED40S/840 PSU WB WH	No	-	Not applicable
910629142126	4MX900 491 LED40S/840 PSU MB WH	No	-	Not applicable

Maxos LED Performer

Order Code	Full Product Name	Dimmable	Embedded	Maximum
			control	dim level
910629144426	4MX900 491 LED40S/840 PSD WB WH	Yes	-	1%
910629144526	4MX900 491 LED40S/840 PSD MB WH	Yes	-	1%
910629144626	4MX900 491 LED40S/840 PSD NB WH	Yes	-	1%
910629144826	4MX900 491 LED50S/840 PSD WB WH	Yes	-	1%
910629144926	4MX900 491 LED50S/840 PSD MB WH	Yes	-	1%
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	Yes	-	1%
910629145726	4MX900 581 LED50S/840 PSU A30 WH	No	-	Not applicable
910629145826	4MX900 491 LED40S/840 PSU A30 WH	No	-	Not applicable
910629145926	4MX900 491 LED50S/840 PSU A30 WH	No	-	Not applicable
910629146026	4MX900 581 LED50S/840 PSU WB WH	No	-	Not applicable
910629146426	4MX900 491 LED50S/840 PSU WB WH	No	-	Not applicable
910629146526	4MX900 491 LED50S/840 PSU MB WH	No	-	Not applicable
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	Yes	-	1%
910629148526	4MX900 491 LED75S/840 PSU A30 WH	No	-	Not applicable
910629170326	4MX900 491 LED75S/840 PSU WB WH	No	-	Not applicable
910629170426	4MX900 491 LED75S/840 PSU MB WH	No	-	Not applicable
910629170826	4MX900 581 LED75S/840 PSU WB WH	No	-	Not applicable
910629170926	4MX900 581 LED75S/840 PSU MB WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded	Maximum
			control	dim level
910629171026	4MX900 581 LED75S/840 PSU NB WH	No	-	Not applicable
910629171326	4MX900 491 LED75S/840 PSD WB WH	Yes	-	1%
910629171426	4MX900 491 LED75S/840 PSD MB WH	Yes	-	1%
910629171526	4MX900 491 LED75S/840 PSD NB WH	Yes	-	1%
910629171826	4MX900 491 LED75S/840 PSD A30 WH	Yes	-	1%
910629171926	4MX900 581 LED75S/840 PSD WB WH	Yes	-	1%
910629172026	4MX900 581 LED75S/840 PSD MB WH	Yes	-	1%
910629172126	4MX900 581 LED75S/840 PSD NB WH	Yes	-	1%
910629172426	4MX900 581 LED75S/840 PSD A30 WH	Yes	-	1%
910629131626	4MX900 LED40S/840 PSD WB SI L1200	Yes	-	1%
910629136426	4MX900 LED60S/840 PSD WB SI L1800	Yes	-	1%
910629138026	4MX900 LED90S/840 PSD WB SI L1800	Yes	-	1%
910629138126	4MX900 LED90S/840 PSD MB SI L1800	Yes	-	1%
910629141226	4MX900 491 LED40S/840 PSU WB SI	No	-	Not applicable
910629141326	4MX900 491 LED40S/840 PSU MB SI	No	-	Not applicable
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	Yes	-	1%
910629177526	4MX900 581 LED50S/840 PSU A30 SI	No	-	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing
			Color
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	Polymethyl methacrylate bowl/cover	White
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	Polymethyl methacrylate bowl/cover	White
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	Polymethyl methacrylate bowl/cover	White

Order Code	Full Product Name	Optical cover type	Housing
			Color
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460311	4MX900 581 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/cover	White
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	Polymethyl methacrylate bowl/cover	White

Maxos LED Performer

Order Code	Full Product Name	Optical cover type	Housing Color
910629173126	4MX900 581 LED50S/840 PSD MB WH	-	White
910629177026	4MX900 581 LED50S/840 PSD WB WH	-	White
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	Polymethyl methacrylate bowl/cover	White
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-	White
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-	White
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-	White
910629142026	4MX900 491 LED40S/840 PSU WB WH	-	White
910629142126	4MX900 491 LED40S/840 PSU MB WH	-	White
910629144426	4MX900 491 LED40S/840 PSD WB WH	-	White
910629144526	4MX900 491 LED40S/840 PSD MB WH	-	White
910629144626	4MX900 491 LED40S/840 PSD NB WH	-	White
910629144826	4MX900 491 LED50S/840 PSD WB WH	-	White
910629144926	4MX900 491 LED50S/840 PSD MB WH	-	White
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-	White
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-	White
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-	White
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-	White
910629146026	4MX900 581 LED50S/840 PSU WB WH	-	White
910629146426	4MX900 491 LED50S/840 PSU WB WH	-	White
910629146526	4MX900 491 LED50S/840 PSU MB WH	-	White
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-	White
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-	White

Order Code	Full Product Name	Optical cover type	Housing Color
910629170326	4MX900 491 LED75S/840 PSU WB WH	-	White
910629170426	4MX900 491 LED75S/840 PSU MB WH	-	White
910629170826	4MX900 581 LED75S/840 PSU WB WH	-	White
910629170926	4MX900 581 LED75S/840 PSU MB WH	-	White
910629171026	4MX900 581 LED75S/840 PSU NB WH	-	White
910629171326	4MX900 491 LED75S/840 PSD WB WH	-	White
910629171426	4MX900 491 LED75S/840 PSD MB WH	-	White
910629171526	4MX900 491 LED75S/840 PSD NB WH	-	White
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-	White
910629171926	4MX900 581 LED75S/840 PSD WB WH	-	White
910629172026	4MX900 581 LED75S/840 PSD MB WH	-	White
910629172126	4MX900 581 LED75S/840 PSD NB WH	-	White
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-	White
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-	Silver
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-	Silver
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-	Silver
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-	Silver
910629141226	4MX900 491 LED40S/840 PSU WB SI	-	Silver
910629141326	4MX900 491 LED40S/840 PSU MB SI	-	Silver
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-	Silver
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-	Silver

Emergency Operation (1/2)

Maxos LED Performer

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	No	-	-	-
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	No	-	-	-
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	No	-	-	-
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	No	-	-	-
910500460311	4MX900 581 LED40S/840 PSD WB WH	No	-	-	-
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910629173126	4MX900 581 LED50S/840 PSD MB WH	-	-	-	-
910629177026	4MX900 581 LED50S/840 PSD WB WH	-	-	-	-
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	No	-	-	-
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-	-	-	-
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-	-	-	-
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910629142026	4MX900 491 LED40S/840 PSU WB WH	-	-	-	-
910629142126	4MX900 491 LED40S/840 PSU MB WH	-	-	-	-
910629144426	4MX900 491 LED40S/840 PSD WB WH	-	-	-	-
910629144526	4MX900 491 LED40S/840 PSD MB WH	-	-	-	-
910629144626	4MX900 491 LED40S/840 PSD NB WH	-	-	-	-
910629144826	4MX900 491 LED50S/840 PSD WB WH	-	-	-	-
910629144926	4MX900 491 LED50S/840 PSD MB WH	-	-	-	-
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-	-	-	-
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-	-	-	-
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-	-	-	-
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-	-	-	-
910629146026	4MX900 581 LED50S/840 PSU WB WH	-	-	-	-
910629146426	4MX900 491 LED50S/840 PSU WB WH	-	-	-	-
910629146526	4MX900 491 LED50S/840 PSU MB WH	-	-	-	-
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-	-	-	-

Maxos LED Performer

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-	-	-	-
910629170326	4MX900 491 LED75S/840 PSU WB WH	-	-	-	-
910629170426	4MX900 491 LED75S/840 PSU MB WH	-	-	-	-
910629170826	4MX900 581 LED75S/840 PSU WB WH	-	-	-	-
910629170926	4MX900 581 LED75S/840 PSU MB WH	-	-	-	-
910629171026	4MX900 581 LED75S/840 PSU NB WH	-	-	-	-
910629171326	4MX900 491 LED75S/840 PSD WB WH	-	-	-	-
910629171426	4MX900 491 LED75S/840 PSD MB WH	-	-	-	-
910629171526	4MX900 491 LED75S/840 PSD NB WH	-	-	-	-
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-	-	-	-
910629171926	4MX900 581 LED75S/840 PSD WB WH	-	-	-	-
910629172026	4MX900 581 LED75S/840 PSD MB WH	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910629172126	4MX900 581 LED75S/840 PSD NB WH	-	-	-	-
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-	-	-	-
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-	-	-	-
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-	-	-	-
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-	-	-	-
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-	-	-	-
910629141226	4MX900 491 LED40S/840 PSU WB SI	-	-	-	-
910629141326	4MX900 491 LED40S/840 PSU MB SI	-	-	-	-
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-	-	-	-
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-	-	-	-

Emergency Operation (2/2)

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	-	-
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	-	-

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	-	-
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	-	-

Maxos LED Performer

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910500460311	4MX900 581 LED40S/840 PSD WB WH	-	-
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	3.4 W	3 hour(s)
910629173126	4MX900 581 LED50S/840 PSD MB WH	-	-
910629177026	4MX900 581 LED50S/840 PSD WB WH	-	-
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	-	-
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-	-
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-	-
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-	-
910629142026	4MX900 491 LED40S/840 PSU WB WH	-	-
910629142126	4MX900 491 LED40S/840 PSU MB WH	-	-
910629144426	4MX900 491 LED40S/840 PSD WB WH	-	-
910629144526	4MX900 491 LED40S/840 PSD MB WH	-	-
910629144626	4MX900 491 LED40S/840 PSD NB WH	-	-
910629144826	4MX900 491 LED50S/840 PSD WB WH	-	-
910629144926	4MX900 491 LED50S/840 PSD MB WH	-	-
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-	-
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-	-
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-	-
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-	-
910629146026	4MX900 581 LED50S/840 PSU WB WH	-	-
910629146426	4MX900 491 LED50S/840 PSU WB WH	-	-
910629146526	4MX900 491 LED50S/840 PSU MB WH	-	-
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-	-

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-	-
910629170326	4MX900 491 LED75S/840 PSU WB WH	-	-
910629170426	4MX900 491 LED75S/840 PSU MB WH	-	-
910629170826	4MX900 581 LED75S/840 PSU WB WH	-	-
910629170926	4MX900 581 LED75S/840 PSU MB WH	-	-
910629171026	4MX900 581 LED75S/840 PSU NB WH	-	-
910629171326	4MX900 491 LED75S/840 PSD WB WH	-	-
910629171426	4MX900 491 LED75S/840 PSD MB WH	-	-
910629171526	4MX900 491 LED75S/840 PSD NB WH	-	-
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-	-
910629171926	4MX900 581 LED75S/840 PSD WB WH	-	-
910629172026	4MX900 581 LED75S/840 PSD MB WH	-	-
910629172126	4MX900 581 LED75S/840 PSD NB WH	-	-
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-	-
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-	-
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-	-
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-	-
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-	-
910629141226	4MX900 491 LED40S/840 PSU WB SI	-	-
910629141326	4MX900 491 LED40S/840 PSU MB SI	-	-
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-	-
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-	-

Approval and Application

Maxos LED Performer

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500458678	4MX900 491 LED50S/840 PSD- CLO WB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460311	4MX900 581 LED40S/840 PSD WB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910629173126	4MX900 581 LED50S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629177026	4MX900 581 LED50S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629142026	4MX900 491 LED40S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629142126	4MX900 491 LED40S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144426	4MX900 491 LED40S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144526	4MX900 491 LED40S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144626	4MX900 491 LED40S/840 PSD NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144826	4MX900 491 LED50S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629144926	4MX900 491 LED50S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146026	4MX900 581 LED50S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146426	4MX900 491 LED50S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146526	4MX900 491 LED50S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629170326	4MX900 491 LED75S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629170426	4MX900 491 LED75S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629170826	4MX900 581 LED75S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629170926	4MX900 581 LED75S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171026	4MX900 581 LED75S/840 PSU NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171326	4MX900 491 LED75S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171426	4MX900 491 LED75S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s

Maxos LED Performer

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629171526	4MX900 491 LED75S/840 PSD NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171926	4MX900 581 LED75S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629172026	4MX900 581 LED75S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629172126	4MX900 581 LED75S/840 PSD NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629141226	4MX900 491 LED40S/840 PSU WB SI	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629141326	4MX900 491 LED40S/840 PSU MB SI	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-20 to +40 °C	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460311	4MX900 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	(0.38, 0.38) SDCM <3.5
910629173126	4MX900 581 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629177026	4MX900 581 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
910629132426	4MX900 LED40S/840 PSD WB WH L1200	(0.38, 0.38) SDCM <3.5
910629138826	4MX900 LED90S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
910629138926	4MX900 LED90S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
910629142026	4MX900 491 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629142126	4MX900 491 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629144426	4MX900 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629144526	4MX900 491 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629144626	4MX900 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629144826	4MX900 491 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629144926	4MX900 491 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
910629145726	4MX900 581 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145826	4MX900 491 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145926	4MX900 491 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629146026	4MX900 581 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629146426	4MX900 491 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
910629146526	4MX900 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
910629148526	4MX900 491 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629170326	4MX900 491 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629170426	4MX900 491 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629170826	4MX900 581 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629170926	4MX900 581 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629171026	4MX900 581 LED75S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
910629171326	4MX900 491 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629171426	4MX900 491 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629171526	4MX900 491 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629171826	4MX900 491 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629171926	4MX900 581 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629172026	4MX900 581 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629172126	4MX900 581 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629172426	4MX900 581 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629131626	4MX900 LED40S/840 PSD WB SI L1200	(0.38, 0.38) SDCM <3.5
910629136426	4MX900 LED60S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
910629138026	4MX900 LED90S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
910629138126	4MX900 LED90S/840 PSD MB SI L1800	(0.38, 0.38) SDCM <3.5
910629141226	4MX900 491 LED40S/840 PSU WB SI	(0.38, 0.38) SDCM <3.5
910629141326	4MX900 491 LED40S/840 PSU MB SI	(0.38, 0.38) SDCM <3
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	(0.38, 0.38) SDCM <3.5
910629177526	4MX900 581 LED50S/840 PSU A30 SI	(0.38, 0.38) SDCM <3.5


Product Data

Maxos LED Performer


Order Code	Full Product Name	Product family code
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	4MX900
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	4MX900
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	4MX900
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	4MX900
910500460311	4MX900 581 LED40S/840 PSD WB WH	4MX900
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	4MX933
910629173126	4MX900 581 LED50S/840 PSD MB WH	4MX900
910629177026	4MX900 581 LED50S/840 PSD WB WH	4MX900
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	4MX900
910629132426	4MX900 LED40S/840 PSD WB WH L1200	4MX900
910629138826	4MX900 LED90S/840 PSD WB WH L1800	4MX900
910629138926	4MX900 LED90S/840 PSD MB WH L1800	4MX900
910629142026	4MX900 491 LED40S/840 PSU WB WH	4MX900
910629142126	4MX900 491 LED40S/840 PSU MB WH	4MX900
910629144426	4MX900 491 LED40S/840 PSD WB WH	4MX900
910629144526	4MX900 491 LED40S/840 PSD MB WH	4MX900
910629144626	4MX900 491 LED40S/840 PSD NB WH	4MX900
910629144826	4MX900 491 LED50S/840 PSD WB WH	4MX900
910629144926	4MX900 491 LED50S/840 PSD MB WH	4MX900
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	4MX900
910629145726	4MX900 581 LED50S/840 PSU A30 WH	4MX900
910629145826	4MX900 491 LED40S/840 PSU A30 WH	4MX900
910629145926	4MX900 491 LED50S/840 PSU A30 WH	4MX900
910629146026	4MX900 581 LED50S/840 PSU WB WH	4MX900
910629146426	4MX900 491 LED50S/840 PSU WB WH	4MX900

Order Code	Full Product Name	Product family code
910629146526	4MX900 491 LED50S/840 PSU MB WH	4MX900
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	4MX900
910629148526	4MX900 491 LED75S/840 PSU A30 WH	4MX900
910629170326	4MX900 491 LED75S/840 PSU WB WH	4MX900
910629170426	4MX900 491 LED75S/840 PSU MB WH	4MX900
910629170826	4MX900 581 LED75S/840 PSU WB WH	4MX900
910629170926	4MX900 581 LED75S/840 PSU MB WH	4MX900
910629171026	4MX900 581 LED75S/840 PSU NB WH	4MX900
910629171326	4MX900 491 LED75S/840 PSD WB WH	4MX900
910629171426	4MX900 491 LED75S/840 PSD MB WH	4MX900
910629171526	4MX900 491 LED75S/840 PSD NB WH	4MX900
910629171826	4MX900 491 LED75S/840 PSD A30 WH	4MX900
910629171926	4MX900 581 LED75S/840 PSD WB WH	4MX900
910629172026	4MX900 581 LED75S/840 PSD MB WH	4MX900
910629172126	4MX900 581 LED75S/840 PSD NB WH	4MX900
910629172426	4MX900 581 LED75S/840 PSD A30 WH	4MX900
910629131626	4MX900 LED40S/840 PSD WB SI L1200	4MX900
910629136426	4MX900 LED60S/840 PSD WB SI L1800	4MX900
910629138026	4MX900 LED90S/840 PSD WB SI L1800	4MX900
910629138126	4MX900 LED90S/840 PSD MB SI L1800	4MX900
910629141226	4MX900 491 LED40S/840 PSU WB SI	4MX900
910629141326	4MX900 491 LED40S/840 PSU MB SI	4MX900
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	4MX900
910629177526	4MX900 581 LED50S/840 PSU A30 SI	4MX900


Polar Wide Diagrams



Polar Normal (separate) - 4MX9001 - 910629172026




Polar Normal (separate) - 4MX9001 - 910629171926




Polar Normal (separate) - 4MX9001 - 910629146026

Maxos LED Performer


Polar Wide Diagrams




Polar Normal (separate) - 4MX9001 - 910629144426




Polar Normal (separate) - 4MX9001 - 910629146426




Polar Normal (separate) - 4MX9001 - 910629144626




Polar Normal (separate) - 4MX9001 - 910629141326




Polar Normal (separate) - 4MX9001 - 910629142026




Polar Normal (separate) - 4MX9001 - 910629171826



Polar Normal (separate) - 4MX9001 - 910629145926




Polar Normal (separate) - 4MX9001 - 910629170426




Polar Normal (separate) - 4MX9001 - 910629170326

Maxos LED Performer


Polar Wide Diagrams




Polar Normal (separate) - 4MX9001 - 910629171526




Polar Normal (separate) - 4MX9001 - 910629144826




Polar Normal (separate) - 4MX9001 - 910629170826




Polar Normal (separate) - 4MX9001 - 910629171426




Polar Normal (separate) - 4MX9001 - 910629144526




Polar Normal (separate) - 4MX9001 - 910629148526



Polar Normal (separate) - 4MX9001 - 910629171026




Polar Normal (separate) - 4MX9001 - 910629172126




Polar Normal (separate) - 4MX9001 - 910629172426

Maxos LED Performer


Polar Wide Diagrams




Polar Normal (separate) - 4MX9001 - 910629177526




Polar Normal (separate) - 4MX9001 - 910629146526




Polar Normal (separate) - 4MX9001 - 910500460311




Polar Normal (separate) - 4MX9001 - 910500460307




Polar Normal (separate) - 4MX9001 - 910500460305



Polar Normal (separate) - 4MX9001 - 910500460303



Polar Normal (separate) - 4MX9001 - 910500458125



Polar Normal (separate) - 4MX9001 - 910500458678

Maxos LED Performer

