



# Maxos LED Performer – efficient and precise line lighting

## Maxos LED Performer

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

### Benefits

- Extremely fast payback
- Breakthrough optical system for precise beam shaping
- Flexible in terms of retrofits, spots, changes, accessories

### Features

- Low energy consumption compared to fluorescent
- Excellent beam shaping for less spill light and exact light distribution in horizontal and vertical planes
- Proven Philips LED engines (Fortimo)
- Can be mounted, new or retrofit, onto a Maxos rail
- Also available in a flexible panel version 4MX800 or high-efficiency version 4MX850

### Application

- Supermarkets
- Warehouses
- Production facilities


# Maxos LED Performer

## Versions



IPPR 4MX900i 0001

## Dimensional drawing




## Product details

IPDP\_4MX900i\_0001-Detail  
photo



IPDP\_4MX900i\_0003-Detail  
photo



IPDP\_4MX900i\_0007-Detail  
photo



IPDP\_4MX900i\_0011-Detail  
photo




# Maxos LED Performer

## Product details



IPDP\_4MX900i\_0013-Detail  
photo

## Polar Wide Diagrams



Polar Normal (separate) - 4MX900I -  
910629142126

