



The affordable LED Tube T8 solution

Ecofit LED tubes T8

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Benefits

- Up to 50% energy saving compared with conventional fluorescent systems
- Easy installation: retrofit replacement of existing T8 lamps improving the quality of light
- Low initial investment

Features

- Retrofit solution with Long lifetime of 15.000hs
- Up to 50% of energy saving
- Instant on, no flicker or buzz

Application

- Domestic applications
- Small offices and retailers

Ecofit LED tubes T8


Versions



LEDtube_ECO_LATAM_14W_G13-SPP

Ecofit LED tubes T8

Dimensional drawing



Product	D1	D2	A1	A2	A3		
16W (36W) G13 Cool White Non-dimmable Linear tube	25.68 mm	28 mm	1,198 mm	1,205 mm	1,212 mm	1,212 mm	27.8 mm
8W (18W) G13 Cool White Non-dimmable Linear tube	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm	602.5 mm	27.8 mm
8W (18W) G13 Cool daylight Linear tube	25.68 mm	28 mm	588.5 mm	595.5 mm	602.5 mm	602.5 mm	27.8 mm
ECOFIT E LEDtube 1200mm 14W 765 T8 CT WV	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
ECOFIT E LEDtube 1200mm 16W 740 T8 WV	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
ECOFIT E LEDtube 1200mm 16W 765 T8 WV	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
ECOFIT E LEDtube 600mm 8W 740 T8 WV	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm		
ECOFIT E LEDtube 600mm 8W 765 T8 WV	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm		
Ecofit E LEDtube 1200mm 18W 740 T8 I MY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
Ecofit E LEDtube 1200mm 18W 765 T8 I MY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
Ecofit E LEDtube 600mm 9W 740 T8 I MY	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm		
Ecofit E LEDtube 600mm 9W 765 T8 I MY	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm		
Ecofit E Mains 1200mm 16W 740 T8	25.7 mm	28 mm	1,198.2 mm	1,205 mm	1,212 mm		
Ecofit E Mains 1200mm 16W 765 T8	25.7 mm	28 mm	1,198.2 mm	1,205 mm	1,212 mm		
Ecofit E Mains 600mm 8W 740 T8	25.7 mm	28 mm	1,198.2 mm	595.5 mm	602.5 mm		
Ecofit E Mains 600mm 8W 765 T8	25.7 mm	28 mm	1,198.2 mm	595.5 mm	602.5 mm		
Ecofit LEDtube 1200mm 16W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
Ecofit LEDtube 1200mm 16W 840 T8 I	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
Ecofit LEDtube 1200mm 16W 840 T8 I	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm		
RCA							


Ecofit LED tubes T8

Dimensional drawing

Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1200mm 16W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1200mm 16W 865 T8 I	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1200mm 16W 865 T8 I RCA	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1200mm HO 18W 840 T8 S	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1200mm HO 18W 865 T8 S	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1500mm 19.5W 840 T8	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
Ecofit LEDtube 1500mm 19.5W 865 T8	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
Ecofit LEDtube 1500mm 20W 840 T8 I	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
Ecofit LEDtube 1500mm 20W 865 T8 I	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
Ecofit LEDtube 1500mm HO 23W 840 T8 S	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
Ecofit LEDtube 1500mm HO 23W 865 T8 S	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
Ecofit LEDtube 600mm 8W 840 T8 I	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube 600mm 8W 840 T8 I RCA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube 600mm 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube 600mm 8W 865 T8 I	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube 600mm 8W 865 T8 I RCA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube 600mm HO 9W 840 T8 S	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube 600mm HO 9W 865 T8 S	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Ecofit LED tubes T8



Product	D1	D2	A1	A2	A3
LEDtube 1500mm 20W 740 T8 AP SL G	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
LEDtube 1500mm 20W 765 T8 AP SL G	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
LEDtube HO 1200mm 18W 740 T8 SL ID	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
LEDtube HO 1200mm 18W 765 T8 SL ID	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
LEDtube HO 600mm 10W 740 T8 SL ID	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
LEDtube HO 600mm 10W 765 T8 SL ID	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE HO 600mm 10W 740 T8 G13	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm




Product	D1	D2	A1	A2	A3
Ledtube DE 1200mm 18.5W 830 T8 G13 TW	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
Ledtube DE 1200mm 18.5W 840 T8 G13 TW	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
Ledtube DE 1200mm 18.5W 865 T8 G13 TW	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
Ledtube DE 1200mm 19W 830 T8 G13 EG	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
Ledtube DE 1200mm 19W 840 T8 G13 EG	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
Ledtube DE 1200mm 19W 865 T8 G13 EG	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
Ledtube DE 580mm 9.5W 830 T8 G13 TW	25.7 mm	28 mm	580.1 mm	587.2 mm	594.3 mm
Ledtube DE 580mm 9.5W 840 T8 G13 TW	25.7 mm	28 mm	580.1 mm	587.2 mm	594.3 mm
Ledtube DE 580mm 9.5W 865 T8 G13 TW	25.7 mm	28 mm	580.1 mm	587.2 mm	594.3 mm
Ledtube DE 600mm 10W 830 T8 G13 EG	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 10W 840 T8 G13 EG	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 10W 865 T8 G13 EG	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Ecofit LED tubes T8


Dimensional drawing



D1	D2	A1	A2	A3
25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm



D1	D2	A1	A2	A3
25.7mm	28mm	1198mm	1205mm	1212mm



D1	D2	A1	A2	A3
25.7mm	28mm	1198mm	1205mm	1212mm

Product	D1	D2	A1	A2	A3
ECOFIT E LEDtube 1200mm 16W 740 T8 VVW	25.7 mm	28 mm	1,199.4 mm	1,206.5 mm	1,213.6 mm
ECOFIT E LEDtube 1200mm 16W 765 T8 VVW	25.7 mm	28 mm	1,199.4 mm	1,206.5 mm	1,213.6 mm
ECOFIT E LEDtube 600mm 8W 740 T8 VVW	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
ECOFIT E LEDtube 600mm 8W 765 T8 VVW	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


Product	D1	D2	A1	A2	A3
Ecofit E Mains 600mm 8W 740 T8 UY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit E Mains 600mm 8W 765 T8 UY	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Product	D1	D2	A1	A2	A3
Ledtube DE HO+ 1200mm 25W 840 T8 G13 CN	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE HO+ 1200mm 25W 865 T8 G13 CN	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1200mm HO+ 25W 840 T8 SL	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1200mm HO+ 25W 865 T8 SL	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Ecofit LED tubes T8

Dimensional drawing




Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1200mm 16W 840 T8 I TR	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1200mm 16W 865 T8 I TR	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube 1500mm 20W 840 T8 I TR	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
Ecofit LEDtube 1500mm 20W 865 T8 I TR	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm
Ecofit LEDtube 600mm 8W 840 T8 I TR	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube 600mm 8W 865 T8 I TR	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit LEDtube T8 1200mm 1600lm 16W865 I	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ecofit LEDtube T8 600mm 800lm 8W865 I	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
LEDtube E DE 600mm 8W 765 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 1200mm 18W 740 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 18W 765 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 18W 765 T8 G13 C	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 600mm 9W 740 T8 G13	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 9W 765 T8 G13	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 9W 765 T8 G13 C	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 1200mm 16W 740 T8 G13	1,198 mm	1,205 mm	1,212 mm		
Ledtube DE 1200mm 16W 765 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 16W 765 T8 G13	1,198 mm	1,205 mm	1,212 mm		
Ledtube DE 1200mm 16W 765 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 16W 765 T8 G13					
Ledtube DE 1200mm 18W 1800lm 740 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 18W 1800lm 765 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 18W 740 T8 G13 RCA	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 18W 765 T8 G13 RCA	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE 1200mm 19W 865 T8 G13					

Ecofit LED tubes T8

Dimensional drawing

Product	D1	D2	A1	A2	A3
Ledtube DE 600mm 8W 740 T8 G13	588.5 mm	595.5 mm	602.5 mm		
Ledtube DE 600mm 8W 765 T8 G13	588.5 mm	595.5 mm	602.5 mm		
Ledtube DE 600mm 8W 840 T8 G13 KSA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 8W 865 T8 G13 KSA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 9W 740 T8 G13 RCA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 9W 765 T8 G13 RCA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 9W 900lm 740 T8 G13	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE 600mm 9W 900lm 765 T8 G13	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ledtube DE E HO 1200mm 22W 740 T8	25.5 mm	28 mm	1,197 mm	1,204 mm	1,212 mm
Ledtube DE E HO 1200mm 22W 765 T8	25.5 mm	28 mm	1,197 mm	1,204 mm	1,212 mm
Ledtube DE HO 1200mm 22W 740 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE HO 1200mm 22W 765 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE HO 1200mm 22W 765 T8 G13 C	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube DE HO 1200mm 22W 765 T8G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube E DE HO 1200mm 20W 765 T8 G13	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm



D1	D2	A1	A2	A3
25.7 mm	28 mm	1198 mm	1205 mm	1212 mm

Product	D1	D2	A1	A2	A3
Ecofit E Mains 1200mm 16W 740 T8 UY	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
Ecofit E Mains 1200mm 16W 765 T8 UY	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Ecofit LED tubes T8

General Information	
Cap-Base	G13
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	T8

General Information

Order Code	Full Product Name	Rated Lifetime (Hours)	Nominal lifetime
929003662508	Ledtube DE 1200mm 18W 740 T8 G13	15,000	15,000 hour(s)
929003662608	Ledtube DE 1200mm 18W 765 T8 G13	15,000	15,000 hour(s)
929003662638	Ledtube DE 1200mm 18W 765 T8 G13 C	15,000	15,000 hour(s)
929003662708	Ledtube DE 600mm 9W 740 T8 G13	15,000	15,000 hour(s)
929003662808	Ledtube DE 600mm 9W 765 T8 G13	15,000	15,000 hour(s)
929003662838	Ledtube DE 600mm 9W 765 T8 G13 C	15,000	15,000 hour(s)
929003662908	Ledtube DE HO 1200mm 22W 740 T8 G13	15,000	15,000 hour(s)
929003663008	Ledtube DE HO 1200mm 22W 765 T8 G13	15,000	15,000 hour(s)
929003663038	Ledtube DE HO 1200mm 22W 765 T8 G13 C	15,000	15,000 hour(s)
929001276022	Ecofit LEDtube 1200mm 16W 840 T8 I	-	15,000 hour(s)
929001276122	Ecofit LEDtube 1200mm 16W 865 T8 I	-	15,000 hour(s)
929001276222	Ecofit LEDtube 600mm 8W 840 T8 I	-	15,000 hour(s)
929001276322	Ecofit LEDtube 600mm 8W 865 T8 I	-	15,000 hour(s)
929001338122	Ecofit LEDtube 1500mm 20W 840 T8 I	-	15,000 hour(s)
929001338124	Ecofit LEDtube 1500mm 20W 840 T8 I TR	-	15,000 hour(s)
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	-	15,000 hour(s)
929001338224	Ecofit LEDtube 1500mm 20W 865 T8 I TR	-	15,000 hour(s)
929002467738	Ledtube DE 1200mm 19W 830 T8 G13 EG	-	20,000 hour(s)

Order Code	Full Product Name	Rated Lifetime (Hours)	Nominal lifetime
929002467838	Ledtube DE 1200mm 19W 840 T8 G13 EG	-	20,000 hour(s)
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	-	20,000 hour(s)
929003125215	Ledtube DE 580mm 9.5W 830 T8 G13 TW	-	20,000 hour(s)
929003125315	Ledtube DE 580mm 9.5W 840 T8 G13 TW	-	20,000 hour(s)
929003125515	Ledtube DE 580mm 9.5W 865 T8 G13 TW	-	20,000 hour(s)
929003125615	Ledtube DE 1200mm 18.5W 830 T8 G13 TW	-	20,000 hour(s)
929003125715	Ledtube DE 1200mm 18.5W 840 T8 G13 TW	-	20,000 hour(s)
929003125915	Ledtube DE 1200mm 18.5W 865 T8 G13 TW	-	20,000 hour(s)
929003665238	Ledtube DE 600mm 10W 830 T8 G13 EG	-	20,000 hour(s)
929003665338	Ledtube DE 600mm 10W 840 T8 G13 EG	-	20,000 hour(s)
929003665438	Ledtube DE 600mm 10W 865 T8 G13 EG	-	20,000 hour(s)
929003560211	ECOFIT E LEDtube 1200mm 14W 765 T8 CT WV	-	15,000 hour(s)
929001184508	16W (36W) G13 Cool White Non-dimmable Linear tube	15,000	15,000 hour(s)
929001184708	8W (18W) G13 Cool White Non-dimmable Linear tube	15,000	15,000 hour(s)
929001184808	8W (18W) G13 Cool daylight Linear tube	15,000	15,000 hour(s)

Ecofit LED tubes T8

Order Code	Full Product Name	Rated Lifetime (Hours)	Nominal lifetime
929001276024	Ecofit LEDtube 1200mm 16W 840 T8 I TR	-	15,000 hour(s)
929001276037	Ecofit LEDtube 1200mm 16W 840 T8 I RCA	-	15,000 hour(s)
929001276124	Ecofit LEDtube 1200mm 16W 865 T8 I TR	-	15,000 hour(s)
929001276137	Ecofit LEDtube 1200mm 16W 865 T8 I RCA	-	15,000 hour(s)
929001276168	Ecofit LEDtube T8 1200mm 1600lm 16W865 I	-	15,000 hour(s)
929001276224	Ecofit LEDtube 600mm 8W 840 T8 I TR	-	15,000 hour(s)
929001276237	Ecofit LEDtube 600mm 8W 840 T8 I RCA	-	15,000 hour(s)
929001276324	Ecofit LEDtube 600mm 8W 865 T8 I TR	-	15,000 hour(s)
929001276337	Ecofit LEDtube 600mm 8W 865 T8 I RCA	-	15,000 hour(s)
929001276368	Ecofit LEDtube T8 600mm 800lm 8W865 I	-	15,000 hour(s)
929001277417	LEDtube HO 600mm 10W 740 T8 SL ID	-	15,000 hour(s)
929001277517	LEDtube HO 600mm 10W 765 T8 SL ID	-	15,000 hour(s)
929001940568	LEDtube 1500mm 20W 740 T8 AP SL G	-	15,000 hour(s)
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	-	15,000 hour(s)
929002351640	Ledtube DE 600mm 8W 740 T8 G13	-	15,000 hour(s)
929002351720	LEDtube E DE 600mm 8W 765 T8	-	15,000 hour(s)
929002351740	Ledtube DE 600mm 8W 765 T8 G13	-	15,000 hour(s)
929002351840	Ledtube DE 1200mm 16W 740 T8 G13	-	15,000 hour(s)
929002351912	Ledtube DE 1200mm 16W 765 T8 G13	-	15,000 hour(s)
929002351940	Ledtube DE 1200mm 16W 765 T8 G13	-	15,000 hour(s)
929002351968	Ledtube DE 1200mm 16W 765 T8 G13	-	15,000 hour(s)
929002351970	Ledtube DE 1200mm 16W 765 T8 G13	-	15,000 hour(s)
929002375108	Ledtube DE 600mm 9W 900lm 740 T8 G13	-	15,000 hour(s)
929002375208	Ledtube DE 600mm 9W 900lm 765 T8 G13	-	15,000 hour(s)
929002375308	Ledtube DE 1200mm 18W 1800lm 740 T8 G13	-	15,000 hour(s)
929002375408	Ledtube DE 1200mm 18W 1800lm 765 T8 G13	-	15,000 hour(s)
929002445702	Ecofit LEDtube 600mm HO 9W 840 T8 S	-	30,000 hour(s)
929002445802	Ecofit LEDtube 600mm HO 9W 865 T8 S	-	30,000 hour(s)
929002446002	Ecofit LEDtube 1200mm HO 18W 840 T8 S	-	30,000 hour(s)
929002446102	Ecofit LEDtube 1200mm HO 18W 865 T8 S	-	30,000 hour(s)

Order Code	Full Product Name	Rated Lifetime (Hours)	Nominal lifetime
929002446302	Ecofit LEDtube 1500mm HO 23W 840 T8 S	-	30,000 hour(s)
929002446402	Ecofit LEDtube 1500mm HO 23W 865 T8 S	-	30,000 hour(s)
929002454308	Ledtube DE 600mm 8W 840 T8 G13 KSA	-	15,000 hour(s)
929002454408	Ledtube DE 600mm 8W 865 T8 G13 KSA	-	15,000 hour(s)
929002474308	Ledtube DE 1200mm 19W 865 T8 G13	-	20,000 hour(s)
929003063408	Ledtube DE HO 1200mm 22W 765 T8G13	-	15,000 hour(s)
929003064840	Ledtube DE HO 600mm 10W 740 T8 G13	-	15,000 hour(s)
929003087311	Ecofit E Mains 600mm 8W 740 T8	-	15,000 hour(s)
929003087341	Ecofit E Mains 600mm 8W 740 T8 UY	-	15,000 hour(s)
929003087411	Ecofit E Mains 600mm 8W 765 T8	-	15,000 hour(s)
929003087441	Ecofit E Mains 600mm 8W 765 T8 UY	-	15,000 hour(s)
929003087511	Ecofit E Mains 1200mm 16W 740 T8	-	15,000 hour(s)
929003087541	Ecofit E Mains 1200mm 16W 740 T8 UY	-	15,000 hour(s)
929003087611	Ecofit E Mains 1200mm 16W 765 T8	-	15,000 hour(s)
929003087641	Ecofit E Mains 1200mm 16W 765 T8 UY	-	15,000 hour(s)
929003130402	Ecofit LEDtube 600mm 8W 865 T8	-	20,000 hour(s)
929003130502	Ecofit LEDtube 1200mm 16W 840 T8	-	20,000 hour(s)
929003130602	Ecofit LEDtube 1200mm 16W 865 T8	-	20,000 hour(s)
929003130702	Ecofit LEDtube 1500mm 19.5W 840 T8	-	20,000 hour(s)
929003130802	Ecofit LEDtube 1500mm 19.5W 865 T8	-	20,000 hour(s)
929003147037	Ledtube DE 1200mm 18W 740 T8 G13 RCA	-	15,000 hour(s)
929003147137	Ledtube DE 1200mm 18W 765 T8 G13 RCA	-	15,000 hour(s)
929003147237	Ledtube DE 600mm 9W 740 T8 G13 RCA	-	15,000 hour(s)
929003147337	Ledtube DE 600mm 9W 765 T8 G13 RCA	-	15,000 hour(s)
929003550717	LEDtube HO 1200mm 18W 740 T8 SL ID	-	15,000 hour(s)
929003550737	Ecofit E LEDtube 1200mm 18W 740 T8 I MY	-	15,000 hour(s)
929003550817	LEDtube HO 1200mm 18W 765 T8 SL ID	-	15,000 hour(s)
929003550837	Ecofit E LEDtube 1200mm 18W 765 T8 I MY	-	15,000 hour(s)
929003550937	Ecofit E LEDtube 600mm 9W 740 T8 I MY	-	15,000 hour(s)
929003551037	Ecofit E LEDtube 600mm 9W 765 T8 I MY	-	15,000 hour(s)
929003561411	ECOFIT E LEDtube 1200mm 16W 740 T8 WV	-	15,000 hour(s)
929003561511	ECOFIT E LEDtube 1200mm 16W 765 T8 WV	-	15,000 hour(s)

Ecofit LED tubes T8

Order Code	Full Product Name	Rated Lifetime (Hours)	Nominal lifetime	Order Code	Full Product Name	Rated Lifetime (Hours)	Nominal lifetime
929003561611	ECOFIT E LEDtube 600mm 8W 740 T8 WV	-	15,000 hour(s)	929004300712	ECOFIT E LEDtube 1200mm 16W 740 T8 VVW	-	15,000 hour(s)
929003561711	ECOFIT E LEDtube 600mm 8W 765 T8 WV	-	15,000 hour(s)	929004300812	ECOFIT E LEDtube 1200mm 16W 765 T8 VVW	-	15,000 hour(s)
929003576138	Ledtube DE E HO 1200mm 22W 740 T8	-	15,000 hour(s)	929004300912	ECOFIT E LEDtube 600mm 8W 740 T8 VVW	-	15,000 hour(s)
929003576210	Ledtube E DE HO 1200mm 20W 765 T8 G13	-	15,000 hour(s)	929004301012	ECOFIT E LEDtube 600mm 8W 765 T8 VVW	-	15,000 hour(s)
929003576238	Ledtube DE E HO 1200mm 22W 765 T8	-	15,000 hour(s)	929004307810	Ledtube DE HO+ 1200mm 25W 840 T8 G13 CN	-	15,000 hour(s)
929004263711	Ecofit LEDtube 1200mm HO+ 25W 840 T8 SL	-	15,000 hour(s)	929004307910	Ledtube DE HO+ 1200mm 25W 865 T8 G13 CN	-	15,000 hour(s)
929004263811	Ecofit LEDtube 1200mm HO+ 25W 865 T8 SL	-	15,000 hour(s)				

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003662508	Ledtube DE 1200mm 18W 740 T8 G13	240 degree(s)	4000 K	70	740	1,800 lm
929003662608	Ledtube DE 1200mm 18W 765 T8 G13	240 degree(s)	6500 K	70	765	1,800 lm
929003662638	Ledtube DE 1200mm 18W 765 T8 G13 C	240 degree(s)	6500 K	70	765	1,800 lm
929003662708	Ledtube DE 600mm 9W 740 T8 G13	240 degree(s)	4000 K	70	740	900 lm
929003662808	Ledtube DE 600mm 9W 765 T8 G13	240 degree(s)	6500 K	70	765	900 lm
929003662838	Ledtube DE 600mm 9W 765 T8 G13 C	240 degree(s)	6500 K	70	765	900 lm
929003662908	Ledtube DE HO 1200mm 22W 740 T8 G13	240 degree(s)	4000 K	70	740	2,300 lm
929003663008	Ledtube DE HO 1200mm 22W 765 T8 G13	240 degree(s)	6500 K	70	765	2,300 lm
929003663038	Ledtube DE HO 1200mm 22W 765 T8 G13 C	240 degree(s)	6500 K	70	765	2,300 lm
929001276022	Ecofit LEDtube 1200mm 16W 840 T8 I	240 degree(s)	4000 K	80	840	1,600 lm
929001276122	Ecofit LEDtube 1200mm 16W 865 T8 I	240 degree(s)	6500 K	80	865	1,600 lm
929001276222	Ecofit LEDtube 600mm 8W 840 T8 I	240 degree(s)	4000 K	80	840	800 lm
929001276322	Ecofit LEDtube 600mm 8W 865 T8 I	240 degree(s)	6500 K	80	865	800 lm
929001338122	Ecofit LEDtube 1500mm 20W 840 T8 I	240 degree(s)	4000 K	80	840	2,000 lm
929001338124	Ecofit LEDtube 1500mm 20W 840 T8 I TR	240 degree(s)	4000 K	80	840	2,000 lm
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	240 degree(s)	6500 K	80	865	2,000 lm
929001338224	Ecofit LEDtube 1500mm 20W 865 T8 I TR	240 degree(s)	6500 K	80	865	2,000 lm
929002467738	Ledtube DE 1200mm 19W 830 T8 G13 EG	240 degree(s)	3000 K	80	830	2,250 lm
929002467838	Ledtube DE 1200mm 19W 840 T8 G13 EG	240 degree(s)	4000 K	80	840	2,350 lm
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	240 degree(s)	6500 K	80	865	2,350 lm
929003125215	Ledtube DE 580mm 9.5W 830 T8 G13 TW	240 degree(s)	3000 K	80	830	1,150 lm
929003125315	Ledtube DE 580mm 9.5W 840 T8 G13 TW	240 degree(s)	4000 K	80	840	1,200 lm
929003125515	Ledtube DE 580mm 9.5W 865 T8 G13 TW	240 degree(s)	6500 K	80	865	1,200 lm
929003125615	Ledtube DE 1200mm 18.5W 830 T8 G13 TW	240 degree(s)	3000 K	80	830	2,250 lm
929003125715	Ledtube DE 1200mm 18.5W 840 T8 G13 TW	240 degree(s)	4000 K	80	840	2,350 lm
929003125915	Ledtube DE 1200mm 18.5W 865 T8 G13 TW	240 degree(s)	6500 K	80	865	2,350 lm
929003665238	Ledtube DE 600mm 10W 830 T8 G13 EG	240 degree(s)	3000 K	80	830	1,150 lm
929003665338	Ledtube DE 600mm 10W 840 T8 G13 EG	240 degree(s)	4000 K	80	840	1,200 lm
929003665438	Ledtube DE 600mm 10W 865 T8 G13 EG	240 degree(s)	6500 K	80	865	1,200 lm
929003560211	ECOFIT E LEDtube 1200mm 14W 765 T8 CT WV	120 degree(s)	6500 K	70	765	1,400 lm
929001184508	16W (36W) G13 Cool White Non-dimmable Linear tube	240 degree(s)	4000 K	73	740	1,600 lm
929001184708	8W (18W) G13 Cool White Non-dimmable Linear tube	240 degree(s)	4000 K	73	740	800 lm

Ecofit LED tubes T8

Order Code	Full Product Name	Correlated Color Temperature		Color rendering		Luminous Flux
		Beam Angle (Nom)	(Nom)	index (CRI)	Color Code	
929001184808	8W (18W) G13 Cool daylight Linear tube	240 degree(s)	6500 K	73	765	800 lm
929001276024	Ecofit LEDtube 1200mm 16W 840 T8 I TR	240 degree(s)	4000 K	80	840	1,600 lm
929001276037	Ecofit LEDtube 1200mm 16W 840 T8 I RCA	240 degree(s)	4000 K	80	840	1,600 lm
929001276124	Ecofit LEDtube 1200mm 16W 865 T8 I TR	240 degree(s)	6500 K	80	865	1,600 lm
929001276137	Ecofit LEDtube 1200mm 16W 865 T8 I RCA	240 degree(s)	6500 K	80	865	1,600 lm
929001276168	Ecofit LEDtube T8 1200mm 1600lm 16W865 I	240 degree(s)	6500 K	80	865	1,600 lm
929001276224	Ecofit LEDtube 600mm 8W 840 T8 I TR	240 degree(s)	4000 K	80	840	800 lm
929001276237	Ecofit LEDtube 600mm 8W 840 T8 I RCA	240 degree(s)	4000 K	80	840	800 lm
929001276324	Ecofit LEDtube 600mm 8W 865 T8 I TR	240 degree(s)	6500 K	80	865	800 lm
929001276337	Ecofit LEDtube 600mm 8W 865 T8 I RCA	240 degree(s)	6500 K	80	865	800 lm
929001276368	Ecofit LEDtube T8 600mm 800lm 8W865 I	240 degree(s)	6500 K	80	865	800 lm
929001277417	LEDtube HO 600mm 10W 740 T8 SL ID	240 degree(s)	4000 K	70	740	1,050 lm
929001277517	LEDtube HO 600mm 10W 765 T8 SL ID	240 degree(s)	6500 K	70	765	1,050 lm
929001940568	LEDtube 1500mm 20W 740 T8 AP SL G	240 degree(s)	4000 K	70	740	2,000 lm
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	240 degree(s)	6500 K	70	765	2,000 lm
929002351640	Ledtube DE 600mm 8W 740 T8 G13	240 degree(s)	4000 K	70	740	800 lm
929002351720	LEDtube E DE 600mm 8W 765 T8	240 degree(s)	6500 K	70	765	800 lm
929002351740	Ledtube DE 600mm 8W 765 T8 G13	240 degree(s)	6500 K	70	765	800 lm
929002351840	Ledtube DE 1200mm 16W 740 T8 G13	240 degree(s)	4000 K	70	740	1,600 lm
929002351912	Ledtube DE 1200mm 16W 765 T8 G13	240 degree(s)	6500 K	70	765	1,600 lm
929002351940	Ledtube DE 1200mm 16W 765 T8 G13	240 degree(s)	6500 K	70	765	1,600 lm
929002351968	Ledtube DE 1200mm 16W 765 T8 G13	240 degree(s)	6500 K	70	765	1,600 lm
929002351970	Ledtube DE 1200mm 16W 765 T8 G13	240 degree(s)	6500 K	70	765	1,600 lm
929002375108	Ledtube DE 600mm 9W 900lm 740 T8 G13	240 degree(s)	4000 K	70	740	900 lm
929002375208	Ledtube DE 600mm 9W 900lm 765 T8 G13	240 degree(s)	6500 K	70	765	900 lm
929002375308	Ledtube DE 1200mm 18W 1800lm 740 T8 G13	240 degree(s)	4000 K	70	740	1,800 lm
929002375408	Ledtube DE 1200mm 18W 1800lm 765 T8 G13	240 degree(s)	6500 K	70	765	1,800 lm
929002445702	Ecofit LEDtube 600mm HO 9W 840 T8 S	240 degree(s)	4000 K	80	840	900 lm
929002445802	Ecofit LEDtube 600mm HO 9W 865 T8 S	240 degree(s)	6500 K	80	865	900 lm
929002446002	Ecofit LEDtube 1200mm HO 18W 840 T8 S	240 degree(s)	4000 K	80	840	1,800 lm
929002446102	Ecofit LEDtube 1200mm HO 18W 865 T8 S	240 degree(s)	6500 K	80	865	1,800 lm
929002446302	Ecofit LEDtube 1500mm HO 23W 840 T8 S	240 degree(s)	4000 K	80	840	2,300 lm
929002446402	Ecofit LEDtube 1500mm HO 23W 865 T8 S	240 degree(s)	6500 K	80	865	2,300 lm
929002454308	Ledtube DE 600mm 8W 840 T8 G13 KSA	240 degree(s)	4000 K	80	840	800 lm
929002454408	Ledtube DE 600mm 8W 865 T8 G13 KSA	240 degree(s)	6500 K	80	865	800 lm
929002474308	Ledtube DE 1200mm 19W 865 T8 G13	240 degree(s)	6500 K	80	865	2,000 lm
929003063408	Ledtube DE HO 1200mm 22W 765 T8G13	240 degree(s)	6500 K	70	765	2,300 lm
929003064840	Ledtube DE HO 600mm 10W 740 T8 G13	240 degree(s)	4000 K	70	740	1,050 lm
929003087311	Ecofit E Mains 600mm 8W 740 T8	240 degree(s)	4000 K	70	740	800 lm
929003087341	Ecofit E Mains 600mm 8W 740 T8 UY	240 degree(s)	4000 K	70	740	800 lm
929003087411	Ecofit E Mains 600mm 8W 765 T8	240 degree(s)	6500 K	70	765	800 lm
929003087441	Ecofit E Mains 600mm 8W 765 T8 UY	240 degree(s)	6500 K	70	765	800 lm
929003087511	Ecofit E Mains 1200mm 16W 740 T8	240 degree(s)	4000 K	70	740	1,600 lm
929003087541	Ecofit E Mains 1200mm 16W 740 T8 UY	240 degree(s)	4000 K	70	740	1,600 lm
929003087611	Ecofit E Mains 1200mm 16W 765 T8	240 degree(s)	6500 K	70	765	1,600 lm
929003087641	Ecofit E Mains 1200mm 16W 765 T8 UY	240 degree(s)	6500 K	70	765	1,600 lm
929003130402	Ecofit LEDtube 600mm 8W 865 T8	240 degree(s)	6500 K	80	865	800 lm
929003130502	Ecofit LEDtube 1200mm 16W 840 T8	240 degree(s)	4000 K	80	840	1,600 lm
929003130602	Ecofit LEDtube 1200mm 16W 865 T8	240 degree(s)	6500 K	80	865	1,600 lm
929003130702	Ecofit LEDtube 1500mm 19.5W 840 T8	240 degree(s)	4000 K	80	840	2,000 lm
929003130802	Ecofit LEDtube 1500mm 19.5W 865 T8	240 degree(s)	6500 K	80	865	2,000 lm

Ecofit LED tubes T8

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature	Color rendering		Luminous Flux
			(Nom)	index (CRI)	Color Code	
929003147037	Ledtube DE 1200mm 18W 740 T8 G13 RCA	240 degree(s)	4000 K	70	740	1,650 lm
929003147137	Ledtube DE 1200mm 18W 765 T8 G13 RCA	240 degree(s)	6500 K	70	765	1,650 lm
929003147237	Ledtube DE 600mm 9W 740 T8 G13 RCA	240 degree(s)	4000 K	70	740	850 lm
929003147337	Ledtube DE 600mm 9W 765 T8 G13 RCA	240 degree(s)	6500 K	70	765	850 lm
929003550717	LEDtube HO 1200mm 18W 740 T8 SL ID	240 degree(s)	4000 K	70	740	1,800 lm
929003550737	Ecofit E LEDtube 1200mm 18W 740 T8 I MY	240 degree(s)	4000 K	70	740	1,800 lm
929003550817	LEDtube HO 1200mm 18W 765 T8 SL ID	240 degree(s)	6500 K	70	765	1,800 lm
929003550837	Ecofit E LEDtube 1200mm 18W 765 T8 I MY	240 degree(s)	6500 K	70	765	1,800 lm
929003550937	Ecofit E LEDtube 600mm 9W 740 T8 I MY	240 degree(s)	4000 K	70	740	900 lm
929003551037	Ecofit E LEDtube 600mm 9W 765 T8 I MY	240 degree(s)	6500 K	70	765	900 lm
929003561411	ECOFIT E LEDtube 1200mm 16W 740 T8 WV	240 degree(s)	4000 K	70	740	1,600 lm
929003561511	ECOFIT E LEDtube 1200mm 16W 765 T8 WV	240 degree(s)	6500 K	70	765	1,600 lm
929003561611	ECOFIT E LEDtube 600mm 8W 740 T8 WV	240 degree(s)	4000 K	70	740	800 lm
929003561711	ECOFIT E LEDtube 600mm 8W 765 T8 WV	240 degree(s)	6500 K	70	765	800 lm
929003576138	Ledtube DE E HO 1200mm 22W 740 T8	240 degree(s)	4000 K	70	740	2,000 lm
929003576210	Ledtube E DE HO 1200mm 20W 765 T8 G13	240 degree(s)	6500 K	70	765	2,000 lm
929003576238	Ledtube DE E HO 1200mm 22W 765 T8	240 degree(s)	6500 K	70	765	2,000 lm
929004263711	Ecofit LEDtube 1200mm HO+ 25W 840 T8 SL	240 degree(s)	4000 K	80	840	3,000 lm
929004263811	Ecofit LEDtube 1200mm HO+ 25W 865 T8 SL	240 degree(s)	6500 K	80	865	3,000 lm
929004300712	ECOFIT E LEDtube 1200mm 16W 740 T8 VWV	240 degree(s)	4000 K	70	740	1,600 lm
929004300812	ECOFIT E LEDtube 1200mm 16W 765 T8 VWV	240 degree(s)	6500 K	70	765	1,600 lm
929004300912	ECOFIT E LEDtube 600mm 8W 740 T8 VWV	240 degree(s)	4000 K	70	740	800 lm
929004301012	ECOFIT E LEDtube 600mm 8W 765 T8 VWV	240 degree(s)	6500 K	70	765	800 lm
929004307810	Ledtube DE HO+ 1200mm 25W 840 T8 G13 CN	240 degree(s)	4000 K	80	840	3,000 lm
929004307910	Ledtube DE HO+ 1200mm 25W 865 T8 G13 CN	240 degree(s)	6500 K	80	865	3,000 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003662508	Ledtube DE 1200mm 18W 740 T8 G13	-	18 W	36 W
929003662608	Ledtube DE 1200mm 18W 765 T8 G13	-	18 W	36 W
929003662638	Ledtube DE 1200mm 18W 765 T8 G13 C	-	18 W	36 W
929003662708	Ledtube DE 600mm 9W 740 T8 G13	-	9 W	18 W
929003662808	Ledtube DE 600mm 9W 765 T8 G13	-	9 W	18 W
929003662838	Ledtube DE 600mm 9W 765 T8 G13 C	-	9 W	18 W
929003662908	Ledtube DE HO 1200mm 22W 740 T8 G13	-	22 W	36 W
929003663008	Ledtube DE HO 1200mm 22W 765 T8 G13	-	22 W	36 W
929003663038	Ledtube DE HO 1200mm 22W 765 T8 G13 C	-	22 W	36 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929001276022	Ecofit LEDtube 1200mm 16W 840 T8 I	50 to 60 Hz	16 W	-
929001276122	Ecofit LEDtube 1200mm 16W 865 T8 I	50 to 60 Hz	16 W	-
929001276222	Ecofit LEDtube 600mm 8W 840 T8 I	50 to 60 Hz	8 W	-
929001276322	Ecofit LEDtube 600mm 8W 865 T8 I	50 to 60 Hz	8 W	-
929001338122	Ecofit LEDtube 1500mm 20W 840 T8 I	50 to 60 Hz	20 W	-
929001338124	Ecofit LEDtube 1500mm 20W 840 T8 I TR	-	19.5 W	54 W
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	50 to 60 Hz	20 W	-

Ecofit LED tubes T8

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929001338224	Ecofit LEDtube 1500mm 20W 865 T8 I TR	-	19.5 W	54 W
929002467738	Ledtube DE 1200mm 19W 830 T8 G13 EG	-	19 W	-
929002467838	Ledtube DE 1200mm 19W 840 T8 G13 EG	-	19 W	-
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	-	19 W	-
929003125215	Ledtube DE 580mm 9.5W 830 T8 G13 TW	-	9.5 W	-
929003125315	Ledtube DE 580mm 9.5W 840 T8 G13 TW	-	9.5 W	-
929003125515	Ledtube DE 580mm 9.5W 865 T8 G13 TW	-	9.5 W	-
929003125615	Ledtube DE 1200mm 18.5W 830 T8 G13 TW	-	18.5 W	-
929003125715	Ledtube DE 1200mm 18.5W 840 T8 G13 TW	-	18.5 W	-
929003125915	Ledtube DE 1200mm 18.5W 865 T8 G13 TW	-	18.5 W	-
929003665238	Ledtube DE 600mm 10W 830 T8 G13 EG	-	10 W	-
929003665338	Ledtube DE 600mm 10W 840 T8 G13 EG	-	10 W	-
929003665438	Ledtube DE 600mm 10W 865 T8 G13 EG	-	10 W	-
929003560211	ECOFIT E LEDtube 1200mm 14W 765 T8 CT WV	50 to 60 Hz	14 W	-
929001184508	16W (36W) G13 Cool White Non-dimmable Linear tube	50 to 60 Hz	16 W	-
929001184708	8W (18W) G13 Cool White Non-dimmable Linear tube	50 to 60 Hz	8 W	-
929001184808	8W (18W) G13 Cool daylight Linear tube	50 to 60 Hz	8 W	-
929001276024	Ecofit LEDtube 1200mm 16W 840 T8 I TR	-	16 W	36 W
929001276037	Ecofit LEDtube 1200mm 16W 840 T8 I RCA	50 to 60 Hz	16 W	-
929001276124	Ecofit LEDtube 1200mm 16W 865 T8 I TR	-	16 W	36 W
929001276137	Ecofit LEDtube 1200mm 16W 865 T8 I RCA	50 to 60 Hz	16 W	-

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929001276168	Ecofit LEDtube T8 1200mm 1600lm 16W865 I	-	16 W	36 W
929001276224	Ecofit LEDtube 600mm 8W 840 T8 I TR	-	8 W	18 W
929001276237	Ecofit LEDtube 600mm 8W 840 T8 I RCA	50 to 60 Hz	8 W	-
929001276324	Ecofit LEDtube 600mm 8W 865 T8 I TR	-	8 W	18 W
929001276337	Ecofit LEDtube 600mm 8W 865 T8 I RCA	50 to 60 Hz	8 W	-
929001276368	Ecofit LEDtube T8 600mm 800lm 8W865 I	-	8 W	18 W
929001277417	LEDtube HO 600mm 10W 740 T8 SL ID	-	10 W	18 W
929001277517	LEDtube HO 600mm 10W 765 T8 SL ID	-	10 W	18 W
929001940568	LEDtube 1500mm 20W 740 T8 AP SL G	50 to 60 Hz	20 W	-
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	50 to 60 Hz	20 W	-
929002351640	Ledtube DE 600mm 8W 740 T8 G13	50 to 60 Hz	8 W	-
929002351720	LEDtube E DE 600mm 8W 765 T8	-	8 W	18 W
929002351740	Ledtube DE 600mm 8W 765 T8 G13	50 to 60 Hz	8 W	-
929002351840	Ledtube DE 1200mm 16W 740 T8 G13	50 to 60 Hz	16 W	-
929002351912	Ledtube DE 1200mm 16W 765 T8 G13	-	16 W	36 W
929002351940	Ledtube DE 1200mm 16W 765 T8 G13	50 to 60 Hz	16 W	-
929002351968	Ledtube DE 1200mm 16W 765 T8 G13	-	16 W	36 W
929002351970	Ledtube DE 1200mm 16W 765 T8 G13	-	16 W	36 W
929002375108	Ledtube DE 600mm 9W 900lm 740 T8 G13	50 to 60 Hz	9 W	-
929002375208	Ledtube DE 600mm 9W 900lm 765 T8 G13	50 to 60 Hz	9 W	-
929002375308	Ledtube DE 1200mm 18W 1800lm 740 T8 G13	50 to 60 Hz	18 W	-

Ecofit LED tubes T8

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929002375408	Ledtube DE 1200mm 18W 1800lm 765 T8 G13	50 to 60 Hz	18 W	-
929002445702	Ecofit LEDtube 600mm HO 9W 840 T8 S	50 to 60 Hz	9 W	-
929002445802	Ecofit LEDtube 600mm HO 9W 865 T8 S	50 to 60 Hz	9 W	-
929002446002	Ecofit LEDtube 1200mm HO 18W 840 T8 S	50 to 60 Hz	17.5 W	-
929002446102	Ecofit LEDtube 1200mm HO 18W 865 T8 S	50 to 60 Hz	17.5 W	-
929002446302	Ecofit LEDtube 1500mm HO 23W 840 T8 S	50 to 60 Hz	22.3 W	-
929002446402	Ecofit LEDtube 1500mm HO 23W 865 T8 S	50 to 60 Hz	22.3 W	-
929002454308	Ledtube DE 600mm 8W 840 T8 G13 KSA	50 to 60 Hz	8 W	-
929002454408	Ledtube DE 600mm 8W 865 T8 G13 KSA	50 to 60 Hz	8 W	-
929002474308	Ledtube DE 1200mm 19W 865 T8 G13	50 to 60 Hz	19 W	-
929003063408	Ledtube DE HO 1200mm 22W 765 T8G13	-	22 W	36 W
929003064840	Ledtube DE HO 600mm 10W 740 T8 G13	-	10 W	18 W
929003087311	Ecofit E Mains 600mm 8W 740 T8	50 to 60 Hz	8 W	18 W
929003087341	Ecofit E Mains 600mm 8W 740 T8 UY	-	8 W	18 W
929003087411	Ecofit E Mains 600mm 8W 765 T8	50 to 60 Hz	8 W	18 W
929003087441	Ecofit E Mains 600mm 8W 765 T8 UY	-	8 W	18 W
929003087511	Ecofit E Mains 1200mm 16W 740 T8	50 to 60 Hz	16 W	36 W
929003087541	Ecofit E Mains 1200mm 16W 740 T8 UY	-	16 W	36 W
929003087611	Ecofit E Mains 1200mm 16W 765 T8	50 to 60 Hz	16 W	36 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003087641	Ecofit E Mains 1200mm 16W 765 T8 UY	-	16 W	36 W
929003130402	Ecofit LEDtube 600mm 8W 865 T8	50 to 60 Hz	8 W	-
929003130502	Ecofit LEDtube 1200mm 16W 840 T8	50 to 60 Hz	16 W	-
929003130602	Ecofit LEDtube 1200mm 16W 865 T8	50 to 60 Hz	16 W	-
929003130702	Ecofit LEDtube 1500mm 19.5W 840 T8	50 to 60 Hz	19.5 W	-
929003130802	Ecofit LEDtube 1500mm 19.5W 865 T8	50 to 60 Hz	19.5 W	-
929003147037	Ledtube DE 1200mm 18W 740 T8 G13 RCA	50 to 60 Hz	18 W	-
929003147137	Ledtube DE 1200mm 18W 765 T8 G13 RCA	50 to 60 Hz	18 W	-
929003147237	Ledtube DE 600mm 9W 740 T8 G13 RCA	50 to 60 Hz	9 W	-
929003147337	Ledtube DE 600mm 9W 765 T8 G13 RCA	50 to 60 Hz	9 W	-
929003550717	LEDtube HO 1200mm 18W 740 T8 SL ID	-	18 W	36 W
929003550737	Ecofit E LEDtube 1200mm 18W 740 T8 I MY	50 to 60 Hz	18 W	-
929003550817	LEDtube HO 1200mm 18W 765 T8 SL ID	-	18 W	36 W
929003550837	Ecofit E LEDtube 1200mm 18W 765 T8 I MY	50 to 60 Hz	18 W	-
929003550937	Ecofit E LEDtube 600mm 9W 740 T8 I MY	50 to 60 Hz	9 W	-
929003551037	Ecofit E LEDtube 600mm 9W 765 T8 I MY	50 to 60 Hz	9 W	-
929003561411	ECOFIT E LEDtube 1200mm 16W 740 T8 WV	50 to 60 Hz	16 W	-
929003561511	ECOFIT E LEDtube 1200mm 16W 765 T8 WV	50 to 60 Hz	16 W	-
929003561611	ECOFIT E LEDtube 600mm 8W 740 T8 WV	50 to 60 Hz	8 W	-
929003561711	ECOFIT E LEDtube 600mm 8W 765 T8 WV	50 to 60 Hz	8 W	-

Ecofit LED tubes T8

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003576138	Ledtube DE E HO 1200mm 22W 740 T8	50 to 60 Hz	22 W	-
929003576210	Ledtube E DE HO 1200mm 20W 765 T8 G13	50 to 60 Hz	20 W	36 W
929003576238	Ledtube DE E HO 1200mm 22W 765 T8	50 to 60 Hz	22 W	-
929004263711	Ecofit LEDtube 1200mm HO+ 25W 840 T8 SL	-	25 W	36 W
929004263811	Ecofit LEDtube 1200mm HO+ 25W 865 T8 SL	-	25 W	36 W
929004300712	ECOFIT E LEDtube 1200mm 16W 740 T8 VWV	-	16 W	36 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929004300812	ECOFIT E LEDtube 1200mm 16W 765 T8 VWV	-	16 W	36 W
929004300912	ECOFIT E LEDtube 600mm 8W 740 T8 VWV	-	8 W	18 W
929004301012	ECOFIT E LEDtube 600mm 8W 765 T8 VWV	-	8 W	18 W
929004307810	Ledtube DE HO+ 1200mm 25W 840 T8 G13 CN	-	25 W	36 W
929004307910	Ledtube DE HO+ 1200mm 25W 865 T8 G13 CN	-	25 W	36 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003662508	Ledtube DE 1200mm 18W 740 T8 G13	55 °C
929003662608	Ledtube DE 1200mm 18W 765 T8 G13	55 °C
929003662638	Ledtube DE 1200mm 18W 765 T8 G13 C	55 °C
929003662708	Ledtube DE 600mm 9W 740 T8 G13	55 °C
929003662808	Ledtube DE 600mm 9W 765 T8 G13	55 °C
929003662838	Ledtube DE 600mm 9W 765 T8 G13 C	55 °C
929003662908	Ledtube DE HO 1200mm 22W 740 T8 G13	55 °C
929003663008	Ledtube DE HO 1200mm 22W 765 T8 G13	55 °C
929003663038	Ledtube DE HO 1200mm 22W 765 T8 G13 C	55 °C
929001276022	Ecofit LEDtube 1200mm 16W 840 T8 I	55 °C
929001276122	Ecofit LEDtube 1200mm 16W 865 T8 I	55 °C
929001276222	Ecofit LEDtube 600mm 8W 840 T8 I	55 °C
929001276322	Ecofit LEDtube 600mm 8W 865 T8 I	55 °C
929001338122	Ecofit LEDtube 1500mm 20W 840 T8 I	60 °C
929001338124	Ecofit LEDtube 1500mm 20W 840 T8 I TR	60 °C
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	60 °C
929001338224	Ecofit LEDtube 1500mm 20W 865 T8 I TR	60 °C
929002467738	Ledtube DE 1200mm 19W 830 T8 G13 EG	50 °C
929002467838	Ledtube DE 1200mm 19W 840 T8 G13 EG	50 °C
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	50 °C
929003125215	Ledtube DE 580mm 9.5W 830 T8 G13 TW	50 °C
929003125315	Ledtube DE 580mm 9.5W 840 T8 G13 TW	50 °C
929003125515	Ledtube DE 580mm 9.5W 865 T8 G13 TW	50 °C
929003125615	Ledtube DE 1200mm 18.5W 830 T8 G13 TW	50 °C
929003125715	Ledtube DE 1200mm 18.5W 840 T8 G13 TW	50 °C
929003125915	Ledtube DE 1200mm 18.5W 865 T8 G13 TW	50 °C
929003665238	Ledtube DE 600mm 10W 830 T8 G13 EG	50 °C
929003665338	Ledtube DE 600mm 10W 840 T8 G13 EG	50 °C
929003665438	Ledtube DE 600mm 10W 865 T8 G13 EG	50 °C
929003560211	ECOFIT E LEDtube 1200mm 14W 765 T8 CT WV	60 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001184508	16W (36W) G13 Cool White Non-dimmable Linear tube	60 °C
929001184708	8W (18W) G13 Cool White Non-dimmable Linear tube	60 °C
929001184808	8W (18W) G13 Cool daylight Linear tube	60 °C
929001276024	Ecofit LEDtube 1200mm 16W 840 T8 I TR	55 °C
929001276037	Ecofit LEDtube 1200mm 16W 840 T8 I RCA	55 °C
929001276124	Ecofit LEDtube 1200mm 16W 865 T8 I TR	55 °C
929001276137	Ecofit LEDtube 1200mm 16W 865 T8 I RCA	55 °C
929001276168	Ecofit LEDtube T8 1200mm 1600lm 16W865 I	55 °C
929001276224	Ecofit LEDtube 600mm 8W 840 T8 I TR	55 °C
929001276237	Ecofit LEDtube 600mm 8W 840 T8 I RCA	55 °C
929001276324	Ecofit LEDtube 600mm 8W 865 T8 I TR	55 °C
929001276337	Ecofit LEDtube 600mm 8W 865 T8 I RCA	55 °C
929001276368	Ecofit LEDtube T8 600mm 800lm 8W865 I	55 °C
929001277417	LEDtube HO 600mm 10W 740 T8 SL ID	60 °C
929001277517	LEDtube HO 600mm 10W 765 T8 SL ID	60 °C
929001940568	LEDtube 1500mm 20W 740 T8 AP SL G	45 °C
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	45 °C
929002351640	Ledtube DE 600mm 8W 740 T8 G13	60 °C
929002351720	LEDtube E DE 600mm 8W 765 T8	50 °C
929002351740	Ledtube DE 600mm 8W 765 T8 G13	60 °C
929002351840	Ledtube DE 1200mm 16W 740 T8 G13	60 °C
929002351912	Ledtube DE 1200mm 16W 765 T8 G13	55 °C
929002351940	Ledtube DE 1200mm 16W 765 T8 G13	60 °C
929002351968	Ledtube DE 1200mm 16W 765 T8 G13	55 °C
929002351970	Ledtube DE 1200mm 16W 765 T8 G13	55 °C
929002375108	Ledtube DE 600mm 9W 900lm 740 T8 G13	60 °C
929002375208	Ledtube DE 600mm 9W 900lm 765 T8 G13	60 °C
929002375308	Ledtube DE 1200mm 18W 1800lm 740 T8 G13	60 °C

Ecofit LED tubes T8

Order Code	Full Product Name	T-Case Maximum (Nom)
929002375408	Ledtube DE 1200mm 18W 1800lm 765 T8 G13	60 °C
929002445702	Ecofit LEDtube 600mm HO 9W 840 T8 S	55 °C
929002445802	Ecofit LEDtube 600mm HO 9W 865 T8 S	55 °C
929002446002	Ecofit LEDtube 1200mm HO 18W 840 T8 S	55 °C
929002446102	Ecofit LEDtube 1200mm HO 18W 865 T8 S	55 °C
929002446302	Ecofit LEDtube 1500mm HO 23W 840 T8 S	60 °C
929002446402	Ecofit LEDtube 1500mm HO 23W 865 T8 S	60 °C
929002454308	Ledtube DE 600mm 8W 840 T8 G13 KSA	60 °C
929002454408	Ledtube DE 600mm 8W 865 T8 G13 KSA	60 °C
929002474308	Ledtube DE 1200mm 19W 865 T8 G13	60 °C
929003063408	Ledtube DE HO 1200mm 22W 765 T8G13	55 °C
929003064840	Ledtube DE HO 600mm 10W 740 T8 G13	40 °C
929003087311	Ecofit E Mains 600mm 8W 740 T8	50 °C
929003087341	Ecofit E Mains 600mm 8W 740 T8 UY	50 °C
929003087411	Ecofit E Mains 600mm 8W 765 T8	50 °C
929003087441	Ecofit E Mains 600mm 8W 765 T8 UY	50 °C
929003087511	Ecofit E Mains 1200mm 16W 740 T8	55 °C
929003087541	Ecofit E Mains 1200mm 16W 740 T8 UY	55 °C
929003087611	Ecofit E Mains 1200mm 16W 765 T8	55 °C
929003087641	Ecofit E Mains 1200mm 16W 765 T8 UY	55 °C
929003130402	Ecofit LEDtube 600mm 8W 865 T8	55 °C
929003130502	Ecofit LEDtube 1200mm 16W 840 T8	55 °C
929003130602	Ecofit LEDtube 1200mm 16W 865 T8	55 °C
929003130702	Ecofit LEDtube 1500mm 19.5W 840 T8	60 °C
929003130802	Ecofit LEDtube 1500mm 19.5W 865 T8	60 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003147037	Ledtube DE 1200mm 18W 740 T8 G13 RCA	55 °C
929003147137	Ledtube DE 1200mm 18W 765 T8 G13 RCA	55 °C
929003147237	Ledtube DE 600mm 9W 740 T8 G13 RCA	50 °C
929003147337	Ledtube DE 600mm 9W 765 T8 G13 RCA	50 °C
929003550717	LEDtube HO 1200mm 18W 740 T8 SL ID	55 °C
929003550737	Ecofit E LEDtube 1200mm 18W 740 T8 I MY	55 °C
929003550817	LEDtube HO 1200mm 18W 765 T8 SL ID	55 °C
929003550837	Ecofit E LEDtube 1200mm 18W 765 T8 I MY	55 °C
929003550937	Ecofit E LEDtube 600mm 9W 740 T8 I MY	55 °C
929003551037	Ecofit E LEDtube 600mm 9W 765 T8 I MY	55 °C
929003561411	ECOFIT E LEDtube 1200mm 16W 740 T8 WV	50 °C
929003561511	ECOFIT E LEDtube 1200mm 16W 765 T8 WV	50 °C
929003561611	ECOFIT E LEDtube 600mm 8W 740 T8 WV	50 °C
929003561711	ECOFIT E LEDtube 600mm 8W 765 T8 WV	50 °C
929003576138	Ledtube DE E HO 1200mm 22W 740 T8	60 °C
929003576210	Ledtube DE E HO 1200mm 20W 765 T8 G13	60 °C
929003576238	Ledtube DE E HO 1200mm 22W 765 T8	60 °C
929004263711	Ecofit LEDtube 1200mm HO+ 25W 840 T8 SL	60 °C
929004263811	Ecofit LEDtube 1200mm HO+ 25W 865 T8 SL	60 °C
929004300712	ECOFIT E LEDtube 1200mm 16W 740 T8 VWV	60 °C
929004300812	ECOFIT E LEDtube 1200mm 16W 765 T8 VWV	60 °C
929004300912	ECOFIT E LEDtube 600mm 8W 740 T8 VWV	60 °C
929004301012	ECOFIT E LEDtube 600mm 8W 765 T8 VWV	60 °C
929004307810	Ledtube DE HO+ 1200mm 25W 840 T8 G13 CN	60 °C
929004307910	Ledtube DE HO+ 1200mm 25W 865 T8 G13 CN	60 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929003662508	Ledtube DE 1200mm 18W 740 T8 G13	Frosted
929003662608	Ledtube DE 1200mm 18W 765 T8 G13	Frosted
929003662638	Ledtube DE 1200mm 18W 765 T8 G13 C	Frosted
929003662708	Ledtube DE 600mm 9W 740 T8 G13	Frosted
929003662808	Ledtube DE 600mm 9W 765 T8 G13	Frosted
929003662838	Ledtube DE 600mm 9W 765 T8 G13 C	Frosted
929003662908	Ledtube DE HO 1200mm 22W 740 T8 G13	Frosted
929003663008	Ledtube DE HO 1200mm 22W 765 T8 G13	Frosted
929003663038	Ledtube DE HO 1200mm 22W 765 T8 G13 C	Frosted
929001276022	Ecofit LEDtube 1200mm 16W 840 T8 I	-
929001276122	Ecofit LEDtube 1200mm 16W 865 T8 I	-
929001276222	Ecofit LEDtube 600mm 8W 840 T8 I	-
929001276322	Ecofit LEDtube 600mm 8W 865 T8 I	-
929001338122	Ecofit LEDtube 1500mm 20W 840 T8 I	-
929001338124	Ecofit LEDtube 1500mm 20W 840 T8 I TR	Frosted
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	-
929001338224	Ecofit LEDtube 1500mm 20W 865 T8 I TR	Frosted
929002467738	Ledtube DE 1200mm 19W 830 T8 G13 EG	Frosted
929002467838	Ledtube DE 1200mm 19W 840 T8 G13 EG	Frosted
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	Frosted
929003125215	Ledtube DE 580mm 9.5W 830 T8 G13 TW	Frosted
929003125315	Ledtube DE 580mm 9.5W 840 T8 G13 TW	Frosted

Order Code	Full Product Name	Bulb Finish
929003125515	Ledtube DE 580mm 9.5W 865 T8 G13 TW	Frosted
929003125615	Ledtube DE 1200mm 18.5W 830 T8 G13 TW	Frosted
929003125715	Ledtube DE 1200mm 18.5W 840 T8 G13 TW	Frosted
929003125915	Ledtube DE 1200mm 18.5W 865 T8 G13 TW	Frosted
929003665238	Ledtube DE 600mm 10W 830 T8 G13 EG	Frosted
929003665338	Ledtube DE 600mm 10W 840 T8 G13 EG	Frosted
929003665438	Ledtube DE 600mm 10W 865 T8 G13 EG	Frosted
929003560211	ECOFIT E LEDtube 1200mm 14W 765 T8 CT WV	Clear
929001184508	16W (36W) G13 Cool White Non-dimmable Linear tube	Frosted
929001184708	8W (18W) G13 Cool White Non-dimmable Linear tube	Frosted
929001184808	8W (18W) G13 Cool daylight Linear tube	Frosted
929001276024	Ecofit LEDtube 1200mm 16W 840 T8 I TR	Frosted
929001276037	Ecofit LEDtube 1200mm 16W 840 T8 I RCA	-
929001276124	Ecofit LEDtube 1200mm 16W 865 T8 I TR	Frosted
929001276137	Ecofit LEDtube 1200mm 16W 865 T8 I RCA	-
929001276168	Ecofit LEDtube T8 1200mm 1600lm 16W865 I	Frosted
929001276224	Ecofit LEDtube 600mm 8W 840 T8 I TR	Frosted
929001276237	Ecofit LEDtube 600mm 8W 840 T8 I RCA	-
929001276324	Ecofit LEDtube 600mm 8W 865 T8 I TR	Frosted
929001276337	Ecofit LEDtube 600mm 8W 865 T8 I RCA	-
929001276368	Ecofit LEDtube T8 600mm 800lm 8W865 I	Frosted
929001277417	LEDtube HO 600mm 10W 740 T8 SL ID	Frosted

Ecofit LED tubes T8

Order Code	Full Product Name	Bulb Finish
929001277517	LEDtube HO 600mm 10W 765 T8 SL ID	Frosted
929001940568	LEDtube 1500mm 20W 740 T8 AP SL G	-
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	-
929002351640	Ledtube DE 600mm 8W 740 T8 G13	-
929002351720	LEDtube E DE 600mm 8W 765 T8	Frosted
929002351740	Ledtube DE 600mm 8W 765 T8 G13	-
929002351840	Ledtube DE 1200mm 16W 740 T8 G13	-
929002351912	Ledtube DE 1200mm 16W 765 T8 G13	Frosted
929002351940	Ledtube DE 1200mm 16W 765 T8 G13	-
929002351968	Ledtube DE 1200mm 16W 765 T8 G13	Frosted
929002351970	Ledtube DE 1200mm 16W 765 T8 G13	-
929002375108	Ledtube DE 600mm 9W 900lm 740 T8 G13	Frosted
929002375208	Ledtube DE 600mm 9W 900lm 765 T8 G13	Frosted
929002375308	Ledtube DE 1200mm 18W 1800lm 740 T8 G13	Frosted
929002375408	Ledtube DE 1200mm 18W 1800lm 765 T8 G13	Frosted
929002445702	Ecofit LEDtube 600mm HO 9W 840 T8 S	Frosted
929002445802	Ecofit LEDtube 600mm HO 9W 865 T8 S	Frosted
929002446002	Ecofit LEDtube 1200mm HO 18W 840 T8 S	Frosted
929002446102	Ecofit LEDtube 1200mm HO 18W 865 T8 S	Frosted
929002446302	Ecofit LEDtube 1500mm HO 23W 840 T8 S	Frosted
929002446402	Ecofit LEDtube 1500mm HO 23W 865 T8 S	Frosted
929002454308	Ledtube DE 600mm 8W 840 T8 G13 KSA	-
929002454408	Ledtube DE 600mm 8W 865 T8 G13 KSA	-
929002474308	Ledtube DE 1200mm 19W 865 T8 G13	Frosted
929003063408	Ledtube DE HO 1200mm 22W 765 T8G13	Frosted
929003064840	Ledtube DE HO 600mm 10W 740 T8 G13	Frosted
929003087311	Ecofit E Mains 600mm 8W 740 T8	Frosted
929003087341	Ecofit E Mains 600mm 8W 740 T8 UY	Frosted
929003087411	Ecofit E Mains 600mm 8W 765 T8	Frosted
929003087441	Ecofit E Mains 600mm 8W 765 T8 UY	Frosted
929003087511	Ecofit E Mains 1200mm 16W 740 T8	Frosted
929003087541	Ecofit E Mains 1200mm 16W 740 T8 UY	Frosted

Order Code	Full Product Name	Bulb Finish
929003087611	Ecofit E Mains 1200mm 16W 765 T8	Frosted
929003087641	Ecofit E Mains 1200mm 16W 765 T8 UY	Frosted
929003130402	Ecofit LEDtube 600mm 8W 865 T8	Frosted
929003130502	Ecofit LEDtube 1200mm 16W 840 T8	Frosted
929003130602	Ecofit LEDtube 1200mm 16W 865 T8	Frosted
929003130702	Ecofit LEDtube 1500mm 19.5W 840 T8	Frosted
929003130802	Ecofit LEDtube 1500mm 19.5W 865 T8	Frosted
929003147037	Ledtube DE 1200mm 18W 740 T8 G13 RCA	-
929003147137	Ledtube DE 1200mm 18W 765 T8 G13 RCA	-
929003147237	Ledtube DE 600mm 9W 740 T8 G13 RCA	-
929003147337	Ledtube DE 600mm 9W 765 T8 G13 RCA	-
929003550717	LEDtube HO 1200mm 18W 740 T8 SL ID	Frosted
929003550737	Ecofit E LEDtube 1200mm 18W 740 T8 I MY	Frosted
929003550817	LEDtube HO 1200mm 18W 765 T8 SL ID	Frosted
929003550837	Ecofit E LEDtube 1200mm 18W 765 T8 I MY	Frosted
929003550937	Ecofit E LEDtube 600mm 9W 740 T8 I MY	Frosted
929003551037	Ecofit E LEDtube 600mm 9W 765 T8 I MY	Frosted
929003561411	ECOFIT E LEDtube 1200mm 16W 740 T8 WV	Frosted
929003561511	ECOFIT E LEDtube 1200mm 16W 765 T8 WV	Frosted
929003561611	ECOFIT E LEDtube 600mm 8W 740 T8 WV	Frosted
929003561711	ECOFIT E LEDtube 600mm 8W 765 T8 WV	Frosted
929003576138	Ledtube DE E HO 1200mm 22W 740 T8	Frosted
929003576210	Ledtube E DE HO 1200mm 20W 765 T8 G13	Frosted
929003576238	Ledtube DE E HO 1200mm 22W 765 T8	Frosted
929004263711	Ecofit LEDtube 1200mm HO+ 25W 840 T8 SL	Frosted
929004263811	Ecofit LEDtube 1200mm HO+ 25W 865 T8 SL	Frosted
929004300712	ECOFIT E LEDtube 1200mm 16W 740 T8 VVW	Frosted
929004300812	ECOFIT E LEDtube 1200mm 16W 765 T8 VVW	Frosted
929004300912	ECOFIT E LEDtube 600mm 8W 740 T8 VVW	Frosted
929004301012	ECOFIT E LEDtube 600mm 8W 765 T8 VVW	Frosted
929004307810	Ledtube DE HO+ 1200mm 25W 840 T8 G13 CN	Frosted
929004307910	Ledtube DE HO+ 1200mm 25W 865 T8 G13 CN	Frosted

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy
			Consumption kWh/1000 h
929003662508	Ledtube DE 1200mm 18W 740 T8 G13	-20 to +45 °C	-
929003662608	Ledtube DE 1200mm 18W 765 T8 G13	-20 to +45 °C	-
929003662638	Ledtube DE 1200mm 18W 765 T8 G13 C	-20 to +45 °C	-
929003662708	Ledtube DE 600mm 9W 740 T8 G13	-20 to +45 °C	-
929003662808	Ledtube DE 600mm 9W 765 T8 G13	-20 to +45 °C	-
929003662838	Ledtube DE 600mm 9W 765 T8 G13 C	-20 to +45 °C	-
929003662908	Ledtube DE HO 1200mm 22W 740 T8 G13	-20 to +45 °C	-

Order Code	Full Product Name	Ambient temperature range	Energy
			Consumption kWh/1000 h
929003663008	Ledtube DE HO 1200mm 22W 765 T8 G13	-20 to +45 °C	-
929003663038	Ledtube DE HO 1200mm 22W 765 T8 G13 C	-20 to +45 °C	-
929001276022	Ecofit LEDtube 1200mm 16W 840 T8 I	-20 °C to 45 °C	16 kWh
929001276122	Ecofit LEDtube 1200mm 16W 865 T8 I	-20 °C to 45 °C	16 kWh
929001276222	Ecofit LEDtube 600mm 8W 840 T8 I	-20 °C to 45 °C	8 kWh
929001276322	Ecofit LEDtube 600mm 8W 865 T8 I	-20 °C to 45 °C	8 kWh
929001338122	Ecofit LEDtube 1500mm 20W 840 T8 I	-20 °C to 45 °C	20 kWh

Ecofit LED tubes T8

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001338124	Ecofit LEDtube 1500mm 20W 840 T8 I TR	-20 to +45 °C	20 kWh
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	-20 °C to 45 °C	20 kWh
929001338224	Ecofit LEDtube 1500mm 20W 865 T8 I TR	-20 to +45 °C	20 kWh
929002467738	Ledtube DE 1200mm 19W 830 T8 G13 EG	-20 to +45 °C	-
929002467838	Ledtube DE 1200mm 19W 840 T8 G13 EG	-20 to +45 °C	-
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	-20 to +45 °C	-
929003125215	Ledtube DE 580mm 9.5W 830 T8 G13 TW	-20 to +45 °C	-
929003125315	Ledtube DE 580mm 9.5W 840 T8 G13 TW	-20 to +45 °C	-
929003125515	Ledtube DE 580mm 9.5W 865 T8 G13 TW	-20 to +45 °C	-
929003125615	Ledtube DE 1200mm 18.5W 830 T8 G13 TW	-20 to +45 °C	-
929003125715	Ledtube DE 1200mm 18.5W 840 T8 G13 TW	-20 to +45 °C	-
929003125915	Ledtube DE 1200mm 18.5W 865 T8 G13 TW	-20 to +45 °C	-
929003665238	Ledtube DE 600mm 10W 830 T8 G13 EG	-20 to +45 °C	-
929003665338	Ledtube DE 600mm 10W 840 T8 G13 EG	-20 to +45 °C	-
929003665438	Ledtube DE 600mm 10W 865 T8 G13 EG	-20 to +45 °C	-
929003560211	ECOFIT E LEDtube 1200mm 14W 765 T8 CT WV	-20 °C to 45 °C	-
929001184508	16W (36W) G13 Cool White Non-dimmable Linear tube	-20 °C to 45 °C	16 kWh
929001184708	8W (18W) G13 Cool White Non-dimmable Linear tube	-20 °C to 45 °C	8 kWh
929001184808	8W (18W) G13 Cool daylight Linear tube	-20 °C to 45 °C	8 kWh
929001276024	Ecofit LEDtube 1200mm 16W 840 T8 I TR	-20 to +45 °C	16 kWh
929001276037	Ecofit LEDtube 1200mm 16W 840 T8 I RCA	-20 °C to 45 °C	16 kWh
929001276124	Ecofit LEDtube 1200mm 16W 865 T8 I TR	-20 to +45 °C	16 kWh
929001276137	Ecofit LEDtube 1200mm 16W 865 T8 I RCA	-20 °C to 45 °C	16 kWh
929001276168	Ecofit LEDtube T8 1200mm 1600lm 16W865 I	-20 to +45 °C	-











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001276224	Ecofit LEDtube 600mm 8W 840 T8 I TR	-20 to +45 °C	8 kWh
929001276237	Ecofit LEDtube 600mm 8W 840 T8 I RCA	-20 °C to 45 °C	8 kWh
929001276324	Ecofit LEDtube 600mm 8W 865 T8 I TR	-20 to +45 °C	8 kWh
929001276337	Ecofit LEDtube 600mm 8W 865 T8 I RCA	-20 °C to 45 °C	8 kWh
929001276368	Ecofit LEDtube T8 600mm 800lm 8W865 I	-20 to +45 °C	-
929001277417	LEDtube HO 600mm 10W 740 T8 SL ID	-20 to +45 °C	-
929001277517	LEDtube HO 600mm 10W 765 T8 SL ID	-20 to +45 °C	-
929001940568	LEDtube 1500mm 20W 740 T8 AP SL G	-20 °C to 45 °C	20 kWh
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	-20 °C to 45 °C	20 kWh
929002351640	Ledtube DE 600mm 8W 740 T8 G13	-20 °C to 45 °C	8 kWh
929002351720	LEDtube E DE 600mm 8W 765 T8	-20 to +45 °C	-
929002351740	Ledtube DE 600mm 8W 765 T8 G13	-20 °C to 45 °C	8 kWh
929002351840	Ledtube DE 1200mm 16W 740 T8 G13	-20 °C to 45 °C	16 kWh
929002351912	Ledtube DE 1200mm 16W 765 T8 G13	-20 to +45 °C	-
929002351940	Ledtube DE 1200mm 16W 765 T8 G13	-20 °C to 45 °C	16 kWh
929002351968	Ledtube DE 1200mm 16W 765 T8 G13	-20 to +45 °C	-
929002351970	Ledtube DE 1200mm 16W 765 T8 G13	-20 to +45 °C	-
929002375108	Ledtube DE 600mm 9W 900lm 740 T8 G13	-20 °C to 45 °C	9 kWh
929002375208	Ledtube DE 600mm 9W 900lm 765 T8 G13	-20 °C to 45 °C	9 kWh
929002375308	Ledtube DE 1200mm 18W 1800lm 740 T8 G13	-20 °C to 45 °C	18 kWh
929002375408	Ledtube DE 1200mm 18W 1800lm 765 T8 G13	-20 °C to 45 °C	18 kWh
929002445702	Ecofit LEDtube 600mm HO 9W 840 T8 S	-20 °C to 45 °C	9 kWh
929002445802	Ecofit LEDtube 600mm HO 9W 865 T8 S	-20 °C to 45 °C	9 kWh
929002446002	Ecofit LEDtube 1200mm HO 18W 840 T8 S	-20 °C to 45 °C	18 kWh
929002446102	Ecofit LEDtube 1200mm HO 18W 865 T8 S	-20 °C to 45 °C	18 kWh

Ecofit LED tubes T8











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002446302	Ecofit LEDtube 1500mm HO 23W 840 T8 S	-20 °C to 45 °C	23 kWh
929002446402	Ecofit LEDtube 1500mm HO 23W 865 T8 S	-20 °C to 45 °C	23 kWh
929002454308	Ledtube DE 600mm 8W 840 T8 G13 KSA	-20 °C to 45 °C	8 kWh
929002454408	Ledtube DE 600mm 8W 865 T8 G13 KSA	-20 °C to 45 °C	8 kWh
929002474308	Ledtube DE 1200mm 19W 865 T8 G13	-20 °C to 45 °C	-
929003063408	Ledtube DE HO 1200mm 22W 765 T8G13	-20 to +45 °C	-
929003064840	Ledtube DE HO 600mm 10W 740 T8 G13	-20 to +45 °C	-
929003087311	Ecofit E Mains 600mm 8W 740 T8	-20 to +45 °C	-
929003087341	Ecofit E Mains 600mm 8W 740 T8 UY	-20 to +45 °C	8 kWh
929003087411	Ecofit E Mains 600mm 8W 765 T8	-20 to +45 °C	-
929003087441	Ecofit E Mains 600mm 8W 765 T8 UY	-20 to +45 °C	8 kWh
929003087511	Ecofit E Mains 1200mm 16W 740 T8	-20 to +45 °C	-
929003087541	Ecofit E Mains 1200mm 16W 740 T8 UY	-20 to +45 °C	16 kWh
929003087611	Ecofit E Mains 1200mm 16W 765 T8	-20 to +45 °C	-
929003087641	Ecofit E Mains 1200mm 16W 765 T8 UY	-20 to +45 °C	16 kWh
929003130402	Ecofit LEDtube 600mm 8W 865 T8	-20 °C to 45 °C	8 kWh
929003130502	Ecofit LEDtube 1200mm 16W 840 T8	-20 °C to 45 °C	16 kWh
929003130602	Ecofit LEDtube 1200mm 16W 865 T8	-20 °C to 45 °C	16 kWh
929003130702	Ecofit LEDtube 1500mm 19.5W 840 T8	-20 °C to 45 °C	20 kWh
929003130802	Ecofit LEDtube 1500mm 19.5W 865 T8	-20 °C to 45 °C	20 kWh
929003147037	Ledtube DE 1200mm 18W 740 T8 G13 RCA	-20 °C to 45 °C	18 kWh
929003147137	Ledtube DE 1200mm 18W 765 T8 G13 RCA	-20 °C to 45 °C	18 kWh
929003147237	Ledtube DE 600mm 9W 740 T8 G13 RCA	-20 °C to 45 °C	9 kWh
929003147337	Ledtube DE 600mm 9W 765 T8 G13 RCA	-20 °C to 45 °C	9 kWh
929003550717	LEDtube HO 1200mm 18W 740 T8 SL ID	-20 to +45 °C	-

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003550737	Ecofit E LEDtube 1200mm 18W 740 T8 I MY	-20 °C to 45 °C	-
929003550817	LEDtube HO 1200mm 18W 765 T8 SL ID	-20 to +45 °C	-
929003550837	Ecofit E LEDtube 1200mm 18W 765 T8 I MY	-20 °C to 45 °C	-
929003550937	Ecofit E LEDtube 600mm 9W 740 T8 I MY	-20 °C to 45 °C	-
929003551037	Ecofit E LEDtube 600mm 9W 765 T8 I MY	-20 °C to 45 °C	-
929003561411	ECOFIT E LEDtube 1200mm 16W 740 T8 WV	-20 °C to 45 °C	-
929003561511	ECOFIT E LEDtube 1200mm 16W 765 T8 WV	-20 °C to 45 °C	-
929003561611	ECOFIT E LEDtube 600mm 8W 740 T8 WV	-20 °C to 45 °C	-
929003561711	ECOFIT E LEDtube 600mm 8W 765 T8 WV	-20 °C to 45 °C	-
929003576138	Ledtube DE E HO 1200mm 22W 740 T8	-20 °C to 45 °C	-
929003576210	Ledtube E DE HO 1200mm 20W 765 T8 G13	-20 to +45 °C	-
929003576238	Ledtube DE E HO 1200mm 22W 765 T8	-20 °C to 45 °C	-
929004263711	Ecofit LEDtube 1200mm HO+ 25W 840 T8 SL	-20 to +45 °C	25 kWh
929004263811	Ecofit LEDtube 1200mm HO+ 25W 865 T8 SL	-20 to +45 °C	25 kWh
929004300712	ECOFIT E LEDtube 1200mm 16W 740 T8 VWV	-20 to +45 °C	-
929004300812	ECOFIT E LEDtube 1200mm 16W 765 T8 VWV	-20 to +45 °C	-
929004300912	ECOFIT E LEDtube 600mm 8W 740 T8 VWV	-20 to +45 °C	-
929004301012	ECOFIT E LEDtube 600mm 8W 765 T8 VWV	-20 to +45 °C	-
929004307810	Ledtube DE HO+ 1200mm 25W 840 T8 G13 CN	-20 to +45 °C	25 kWh
929004307910	Ledtube DE HO+ 1200mm 25W 865 T8 G13 CN	-20 to +45 °C	25 kWh











Ecofit LED tubes T8













Ecofit LED tubes T8



Ecofit LED tubes T8



Ecofit LED tubes T8



Ecofit LED tubes T8

