



# Classic LED filament lamps for decorative lighting

## Classic filament LED candles and lusters

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

### Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI above 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

### Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

# Classic filament LED candles and lusters

## Versions



LED classic E27 WW A60 FR ND



LEDbulb CLA A15 E27 CL



LEDclassic 40W B35 E14 CL  
WGD90 SRT4 1



LED classic 40W P45 B15 CL  
WGD90 SRT4 1



CLA LEDcandle 25W E14 827 FR  
P45



LEDbulb CLA T25L E14 CL



LED classic 40W B35 E14  
WWFRNDRF2SRT6 UK



LEDbulb CLA G16,5 E27 CL

## Classic filament LED candles and lusters

### Versions



LEDclassic 40W B35 B15 CL  
WGD90 SRT4 1



LED classic T25L E14 CL POS2



LEDbulb CLA B11 E12 CL



LEDcandle Classic 35W E14 P45  
Mirror Crown 827 CL ND



LEDbulb CLA B35 E14 TA



LEDclassic 40W P45 E27 CL  
WGD90 SRT4 1



LEDbulb 6,6BA11 PER UD CL G E12  
E26 WGD 3PF T20




LEDbulb Classic 40W E27 P45 827  
CL ND

# Classic filament LED candles and lusters

## Versions



LED classic 40W P45 B22 CL  
WGD90 SRT4 1



LEDclassic 40W B35 B22 CL  
WGD90 SRT4 1





LEDclassic 40W B35 E27 CL  
WGD90 SRT4 1



LEDclassic 40W P45 E14 WGD90  
CL SRT4 1

## Dimensional drawing







Product	D	C
LEDclassic 3.5W B35 2700K E14 D CL AU	35 mm	97 mm

Product	D	C
LED classic 40W P45 E14 WW FR ND RFSRT4	45 mm	80 mm
LEDclassic CM P45 35W WW E14 CL ND SRT4	45 mm	82 mm
LEDclassic 3.5W P45 2700K E14 D CL AU	45 mm	80 mm

## Classic filament LED candles and lusters

### Dimensional drawing



Product	D	C
CorePro LEDLusterND4.3-40W E27 827P45CLG	45 mm	82 mm
LEDclassic 3.5W P45 2700K E27 D CL AU	45 mm	78 mm





Product	D	C
LEDclassic 3.5W P45 2700K B22 D CL AU	45 mm	77 mm

Product	D	C
LEDclassic 3.5W B35 2700K B22 D CL AU	35 mm	94 mm

Product	D	C
6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	35 mm	107 mm

# Classic filament LED candles and lusters

## Dimensional drawing



Product	D	C
LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	52 mm	87 mm





Product	D	C
LEDClassic 3.5W P45 2700K B15 D CL AU	45 mm	79 mm

Product	D	C
LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	35 mm	99 mm
LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	35 mm	99 mm

Product	D	C
LEDClassic 40W B35 2700K E14 ND FR AU	35 mm	97 mm

## Classic filament LED candles and lusters

### Dimensional drawing



Product	D	C
LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	35 mm	95 mm
LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	35 mm	95 mm
LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	35 mm	95 mm





Product	D	C
LEDClassic 3.5W B35 2700K E27 D CL AU	35 mm	95 mm

Product	D	C
LED classic 25W E27 WWA60 FR ND 1PF/6	60 mm	104 mm

Product	D	C
LEDClA 25W B35 E14 825 WV ND+E27 BR/MX	35 mm	114 mm

# Classic filament LED candles and lusters

## Dimensional drawing



Product	D	C
LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	48 mm	89 mm

Product	D	C
LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	35 mm	99 mm
LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	35 mm	99 mm

Product	D	C
LEDClassic 3.5W B35 2700K B15 D CL AU	35 mm	96 mm

Product	D	C
LED classic 25W T25L E14 CL ND RF SRT4	25 mm	90 mm
LED classic 40W T25L E14 CL ND RF SRT4	25 mm	90 mm

## General Information

## Classic filament LED candles and lusters

Order Code	Full Product Name	Cap-Base	Rated			Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime				Lifetime (Hours)	Switching Cycle	Nominal lifetime
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	E27	15,000 hour(s)	20,000	15,000 hour(s)	929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	E12	-	20,000	15,000 hour(s)
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	E27	-	20,000	15,000 hour(s)	929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	E14	15,000 hour(s)	20,000	15,000 hour(s)
929003012279	LEDclassic 3.5W B35 2700K E14 D CL AU	E14	15,000 hour(s)	20,000	15,000 hour(s)	929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	E14	-	20,000	15,000 hour(s)
929003013479	LEDclassic 3.5W P45 2700K B15 D CL AU	B15	15,000 hour(s)	20,000	15,000 hour(s)	929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	E14	-	20,000	15,000 hour(s)
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	E14	15,000 hour(s)	20,000	15,000 hour(s)	929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	E14	-	20,000	15,000 hour(s)
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	E14	-	20,000	15,000 hour(s)	929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	E14	-	20,000	15,000 hour(s)
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	E14	15,000 hour(s)	15,000	15,000 hour(s)	929002000616	LEDClA 25W B35 E14 825 WV ND+E27 BR/MX	E14	-	20,000	15,000 hour(s)
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	E27	-	20,000	15,000 hour(s)	929003013279	LEDclassic 3.5W P45 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003012579	LEDclassic 3.5W B35 2700K B15 D CL AU	B15	15,000 hour(s)	20,000	15,000 hour(s)	929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	Universal	15,000 hour(s)	20,000	15,000 hour(s)
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	E27	-	20,000	15,000 hour(s)	929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	E27	-	20,000	10,000 hour(s)
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	E27	-	20,000	15,000 hour(s)	929003013379	LEDclassic 3.5W P45 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	E27	-	20,000	15,000 hour(s)	929003012479	LEDclassic 3.5W B35 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	E14	-	20,000	15,000 hour(s)	929003012379	LEDclassic 3.5W B35 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	E12	-	20,000	15,000 hour(s)	929003013179	LEDclassic 3.5W P45 2700K E14 D CL AU	E14	15,000 hour(s)	20,000	15,000 hour(s)
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	E12	-	20,000	15,000 hour(s)						
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	E12	-	20,000	15,000 hour(s)						

### Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering		LLMF At End Of Nominal Lifetime	
				index (CRI)	Color Code	(Nom)	Luminous Flux
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	-	2700 K	80	827	70 %	250 lm
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	-	5000 K	80	850	70 %	500 lm
929003012279	LEDclassic 3.5W B35 2700K E14 D CL AU	300 degree(s)	2700 K	90	927	70 %	470 lm
929003013479	LEDclassic 3.5W P45 2700K B15 D CL AU	300 degree(s)	2700 K	90	927	70 %	470 lm
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	300 degree(s)	2700 K	80	827	70 %	470 lm
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	-	2700 K	80	827	70 %	250 lm
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	-	2700 K	80	827	70 %	470 lm
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	-	2700 K	80	827	70 %	500 lm
929003012579	LEDclassic 3.5W B35 2700K B15 D CL AU	300 degree(s)	2700 K	90	927	70 %	470 lm
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	-	2700 K	80	827	70 %	500 lm
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	-	2700 K	80	827	70 %	500 lm
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	-	5000 K	80	850	70 %	500 lm

## Classic filament LED candles and lusters

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering		LLMF At End Of Nominal Lifetime		Luminous Flux
				index (CRI)	Color Code	(Nom)		
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	-	2700 K	80	827	70 %		470 lm
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	-	2700 K	80	827	70 %		500 lm
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	-	2700 K	80	827	70 %		500 lm
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	-	5000 K	80	850	70 %		500 lm
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	-	5000 K	80	850	70 %		500 lm
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	-	2700 K	80	827	70 %		397 lm
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	-	2700 K	80	827	70 %		500 lm
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	-	2700 K	80	827	70 %		500 lm
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	-	5000 K	80	850	70 %		500 lm
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	-	5000 K	80	850	70 %		500 lm
929002000616	LEDcla 25W B35 E14 825 WV ND+E27 BR/MX	280 degree(s)	2500 K	80	825	70 %		300 lm
929003013279	LEDclassic 3.5W P45 2700K E27 D CL AU	300 degree(s)	2700 K	90	927	70 %		470 lm
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	300 degree(s)	2200 K	95	922-927	0.7 %		700 lm
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	270 degree(s)	2700 K	80	827	70 %		470 lm
929003013379	LEDclassic 3.5W P45 2700K B22 D CL AU	300 degree(s)	2700 K	90	927	70 %		470 lm
929003012479	LEDclassic 3.5W B35 2700K B22 D CL AU	300 degree(s)	2700 K	90	927	70 %		470 lm
929003012379	LEDclassic 3.5W B35 2700K E27 D CL AU	300 degree(s)	2700 K	90	927	70 %		470 lm
929003013179	LEDclassic 3.5W P45 2700K E14 D CL AU	300 degree(s)	2700 K	90	927	70 %		470 lm

### Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	50 to 60 Hz	50 to 60 Hz	2.2 W	0.5 s	25 W
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003012279	LEDclassic 3.5W B35 2700K E14 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929003013479	LEDclassic 3.5W P45 2700K B15 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	50 to 60 Hz	50 to 60 Hz	4.3 W	0.5 s	40 W
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	50 to 60 Hz	-	2.1 W	0.5 s	25 W
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	50 to 60 Hz	-	3.5 W	0.4 s	40 W
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003012579	LEDclassic 3.5W B35 2700K B15 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	50 to 60 Hz	-	4.5 W	0.5 s	40 W
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	50 to 60 Hz	50 to 60 Hz	4 W	0.5 s	35 W
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002000616	LEDcla 25W B35 E14 825 WV ND+E27 BR/MX	50 to 60 Hz	50 to 60 Hz	2.7 W	0.5 s	30 W
929003013279	LEDclassic 3.5W P45 2700K E27 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	60 Hz	60 Hz	6.6 W	0.5 s	75 W
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	50 to 60 Hz	50 to 60 Hz	4.3 W	0.5 s	40 W
929003013379	LEDclassic 3.5W P45 2700K B22 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929003012479	LEDclassic 3.5W B35 2700K B22 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W

## Classic filament LED candles and lusters

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929003012379	LEDclassic 3.5W B35 2700K E27 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929003013179	LEDclassic 3.5W P45 2700K E14 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W

### Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)	Order Code	Full Product Name	T-Case Maximum (Nom)
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	30 °C	929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	55 °C
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	50 °C	929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	55 °C
929003012279	LEDclassic 3.5W B35 2700K E14 D CL AU	70 °C	929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	45 °C
929003013479	LEDclassic 3.5W P45 2700K B15 D CL AU	70 °C	929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	55 °C
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	55 °C	929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	55 °C
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	38 °C	929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	55 °C
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	55 °C	929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	55 °C
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	50 °C	929002000616	LEDClA 25W B35 E14 825 WV ND+E27 BR/MX	50 °C
929003012579	LEDclassic 3.5W B35 2700K B15 D CL AU	70 °C	929003013279	LEDclassic 3.5W P45 2700K E27 D CL AU	70 °C
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	55 °C	929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	-
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	55 °C	929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	45 °C
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	55 °C	929003013379	LEDclassic 3.5W P45 2700K B22 D CL AU	70 °C
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	57 °C	929003012479	LEDclassic 3.5W B35 2700K B22 D CL AU	70 °C
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	55 °C	929003012379	LEDclassic 3.5W B35 2700K E27 D CL AU	70 °C
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	55 °C	929003013179	LEDclassic 3.5W P45 2700K E14 D CL AU	70 °C

### Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	No	929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	No
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	No	929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	No
929003012279	LEDclassic 3.5W B35 2700K E14 D CL AU	Only with specific dimmers	929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	No
929003013479	LEDclassic 3.5W P45 2700K B15 D CL AU	Only with specific dimmers	929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	No
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	No	929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	No
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	No	929002000616	LEDClA 25W B35 E14 825 WV ND+E27 BR/MX	No
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	No	929003013279	LEDclassic 3.5W P45 2700K E27 D CL AU	Only with specific dimmers
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	No	929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	Only with specific dimmers
929003012579	LEDclassic 3.5W B35 2700K B15 D CL AU	Only with specific dimmers	929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	No
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	No	929003013379	LEDclassic 3.5W P45 2700K B22 D CL AU	Only with specific dimmers
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	No	929003012479	LEDclassic 3.5W B35 2700K B22 D CL AU	Only with specific dimmers
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	No	929003012379	LEDclassic 3.5W B35 2700K E27 D CL AU	Only with specific dimmers
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	No	929003013179	LEDclassic 3.5W P45 2700K E14 D CL AU	Only with specific dimmers
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	No			
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	No			
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	No			
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	No			

### Mechanical and Housing

## Classic filament LED candles and lusters

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	Frosted	A60
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	Clear	A15
929003012279	LEDclassic 3.5W B35 2700K E14 D CL AU	Clear	B35
929003013479	LEDclassic 3.5W P45 2700K B15 D CL AU	Clear	P45
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	Frosted	P45
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	Clear	T25
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	Frosted	B35
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	Clear	G16.5
929003012579	LEDclassic 3.5W B35 2700K B15 D CL AU	Clear	B35
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	Clear	B11
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	Clear	B11
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	Clear	B11
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	Clear	T25
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	Clear	B11
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	Clear	B11
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	Clear	B11

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	Clear	B11
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	Mirror Crown	P45
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	Clear	B11
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	Clear	B11
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	Clear	B11
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	Clear	B11
929002000616	LEDCl 25W B35 E14 825 WV ND+E27 BR/MX	Transparent amber	B35
929003013279	LEDclassic 3.5W P45 2700K E27 D CL AU	Clear	P45
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	Clear	BA11
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	Clear	P45
929003013379	LEDclassic 3.5W P45 2700K B22 D CL AU	Clear	P45
929003012479	LEDclassic 3.5W B35 2700K B22 D CL AU	Clear	B35
929003012379	LEDclassic 3.5W B35 2700K E27 D CL AU	Clear	B35
929003013179	LEDclassic 3.5W P45 2700K E14 D CL AU	Clear	P45










### Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	-20 to +45 °C	3 kWh
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	-20 to +40 °C	-
929003012279	LEDclassic 3.5W B35 2700K E14 D CL AU	-20 to +45 °C	4 kWh
929003013479	LEDclassic 3.5W P45 2700K B15 D CL AU	-20 to +45 °C	4 kWh
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	-20 °C to 45 °C	5 kWh
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	-20 to +45 °C	3 kWh
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	-20 to +45 °C	5 kWh
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	-20 to +40 °C	-
929003012579	LEDclassic 3.5W B35 2700K B15 D CL AU	-20 to +45 °C	4 kWh
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	-20 to +40 °C	-
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	-20 to +40 °C	-
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	-20 to +40 °C	-
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	-20 to +45 °C	5 kWh











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	-20 to +40 °C	-
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	-20 to +40 °C	-
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	-20 to +40 °C	-
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	-20 to +40 °C	-
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	-20 to +45 °C	4 kWh
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	-20 to +40 °C	-
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	-20 to +40 °C	-
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	-20 to +40 °C	-
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	-20 to +40 °C	-
929002000616	LEDCl 25W B35 E14 825 WV ND +E27 BR/MX	-20 to +45 °C	-
929003013279	LEDclassic 3.5W P45 2700K E27 D CL AU	-20 to +45 °C	4 kWh
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	-20 °C to 40 °C	-
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	-20 to +45 °C	5 kWh

# Classic filament LED candles and lusters

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003013379	LEDclassic 3.5W P45 2700K B22 D CL AU	-20 to +45 °C	4 kWh
929003012479	LEDclassic 3.5W B35 2700K B22 D CL AU	-20 to +45 °C	4 kWh
929003012379	LEDclassic 3.5W B35 2700K E27 D CL AU	-20 to +45 °C	4 kWh
929003013179	LEDclassic 3.5W P45 2700K E14 D CL AU	-20 to +45 °C	4 kWh



# Classic filament LED candles and lusters



## Classic filament LED candles and lusters

