



Performance within reach

Lumistreet gen2 ECO

LumiStreet gen2 Eco is available with 1 or 2 highly efficient light modules. A maximum performance is achieved by making the optics also the outer IP cover. The luminaire is ideally suited for both new build streets and areas, as well as renovation of existing installations. This affordable luminaire not only offers a clean and timeless design to blend in with the environment, but also brings high quality lighting solutions with significant energy and maintenance savings and a long operational life.

Benefits

- Easy to install in both post top and side entry application.
- Interesting total cost of ownership.
- Limited initial investment.
- Considerable reduction in energy usage and carbon footprint; further energy savings achievable when using CLO or stand-alone dimming such as Dynadim.
- Signify Service tag (unique QR identification) for maintenance, installation and spare part information.
- Optionally prepared for use of smart lighting. For example, by using an intelligent system such as Interact.

Features

- Dedicated LED luminaire in a compact and efficient design.
- One or 2 LED modules for lower or higher lumen packages, 3 optics for effective distribution.
- Wide choice of lumen packages, ranging from 800 up to 11.000 lumen.
- Long life expectancy of 100.000 operating hours.
- One flexible design to facilitate both post top and side entry application.
- Suitable for new installations or one-to-one replacement in existing installations.
- Vandal-resistant IK09 (IK 08 with Nema or SR socket), ingress protection IP66.
- Tilt regulation for side entry and post top application.

Lumistreet gen2 ECO

Application

- Road and Street
- Residential
- Walkways
- Parks and Plazas

