

Party Spot

7403286



For parties as colorful as you are

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Benefits

- Four PAR 38 colors available: Red, green, blue, yellow

Applications

- Hospitality and restaurants in patios, decks and gazebos
- Ideal for parties, festivals and holidays

Features

- Long life
- Instant on
- Ideal for any occasion – get festive for any reason
- Rated for indoor/outdoor use

Versions



LEDspots 13,5W E26 PAR38
 Yellow




LEDspots 13,5W E26 PAR38
 Red



LEDspots 13,5W E26 PAR38
 Green

Dimensional drawing



Product	D	C
13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF	122 mm	132 mm
13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF	122 mm	132 mm
13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF	122 mm	132 mm

General Information

Cap-Base	E26
Nominal lifetime	10,950 hour(s)
Switching Cycle	10,000
Rated Lifetime (Hours)	10,950 hour(s)

Light Technical

Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	13.5 W
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	65 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	PAR38

Approval and Application

Ambient temperature range	-20 °C to 45 °C
---------------------------	-----------------

Light Technical

Order Code	Full Product Name	Color Code
929001306633	13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF	Yellow
929001306863	13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF	Red
929001306763	13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF	Green