

PHILIPS

Lighting



For parties as colorful as you are

Party Spot

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.

Benefits

- Four PAR 38 colors available: Red, green, blue, yellow

Features

- Long life
- Instant on
- Ideal for any occasion – get festive for any reason
- Rated for indoor/outdoor use

Application

- Hospitality and restaurants in patios, decks and gazebos
- Ideal for parties, festivals and holidays

Party Spot

Versions



LEDspots 13,5W E26 PAR38 Yellow




LEDspots 13,5W E26 PAR38 Red



LEDspots 13,5W E26 PAR38 Green

Dimensional drawing





Product	D	C
13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF	122 mm	132 mm
13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF	122 mm	132 mm
13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF	122 mm	132 mm

Party Spot

General Information	
Cap-Base	E26
Rated Lifetime (Hours)	10,950 hour(s)
Switching Cycle	10,000
Nominal lifetime	10,950 hour(s)
Light Technical	
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Line Frequency	60 Hz
Power Consumption	13.5 W
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	PAR38
Approval and Application	
Ambient temperature range	-20 °C to 45 °C


Light Technical

Order Code	Full Product Name	Color Code
929001306633	13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF	Yellow
929001306863	13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF	Red
929001306763	13.5PAR38/PER/GREEN/G/E26/ND/ULW 3/1PF	Green




Party Spot


Accent Diagrams



Accent Diagram -
13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF




Accent Diagram - 13.5PAR38/PER/
YELLOW/G/E26/ND/ULW 3/1PF




Accent Diagram - 13.5PAR38/PER/
GREEN/G/E26/ND/ULW 3/1PF


Beam Diagrams



Beam diagram -
13.5PAR38/PER/RED/G/E26/ND/ULW 3/1PF



Beam diagram - 13.5PAR38/PER/
YELLOW/G/E26/ND/ULW 3/1PF



Beam diagram - 13.5PAR38/PER/
GREEN/G/E26/ND/ULW 3/1PF

