

LED PAR38

7403300



Everything you value in a Halogen PAR38 with the benefits of LED. Accent your merchandise or space without distraction.

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 8 to 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Applications

- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

Versions



Product standard image



PAR38 120V 17-90W 1150lm
8D 2700K E26 D



LEDspot MAS 120W E27
PAR38 830 25D ND



Product standard image



LEDspots PAR38 E26 1



LEDspots EXP NAM PAR38 E26
1



LEDspots GM 1 PAR38 E27



LEDspots BH PAR38 E26



LEDspots EXP NAM PAR38 E26




LED 10PAR38 90W DipS 5CCT
40D D P E26 T20




LEDspots MAS LATAM PAR38
E27


Dimensional drawing




Product	D	C
17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	120.7 mm	134.6 mm




Product	D	C
LEDspot 90W PAR38 827 100-277V 25D ND	120 mm	133 mm




Product	D	C
PAR38 13-120W 930 25D 120V G ULW Dim E27	122 mm	131 mm
PAR38 13-120W 950 25D 120V G ULW Dim E27	122 mm	131 mm




Product	D	C
13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	123 mm	129 mm




Product	D	C
10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	123 mm	129 mm
10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm




Product	D	C
6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	121 mm	131 mm
6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P		



Product	D	C
13PAR38/S/13W/927 40D E27 ND/G/110-277V	122 mm	137 mm



Product	D	C
14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	121 mm	132.5 mm
14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	121 mm	132.5 mm
14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	121 mm	132.5 mm
14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	121 mm	132.5 mm



Product	D	C
10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	122 mm	129 mm

General Information

Rated Lifetime (Hours) 15,000 hour(s)

Light Technical

LLMF At End Of Nominal Lifetime (Nom) 70 %

Operating and Electrical

Starting Time (Nom) 0.5 s

Mechanical and Housing

Bulb Shape PAR38

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime	Switching Cycle
929003740803	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P	E26	50,000 hour(s)	50,000
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	E26	50,000 hour(s)	50,000
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	E26	25,000 hour(s)	50,000
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	E27	25,000 hour(s)	25,000
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	E26	11,000 hour(s)	50,000
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	E26	25,000 hour(s)	50,000
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	E26	25,000 hour(s)	50,000
929003134407	13PAR38/S/13W/927 40D E27 ND/G/110-277V	E27	15,000 hour(s)	50,000
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	E26	25,000 hour(s)	50,000
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	E26	25,000 hour(s)	50,000
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	E26	25,000 hour(s)	50,000
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	E26	25,000 hour(s)	50,000
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	E26	40,000 hour(s)	50,000
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	E26	40,000 hour(s)	50,000
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	E26	40,000 hour(s)	50,000
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	E26	40,000 hour(s)	50,000
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	E26	40,000 hour(s)	50,000
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	E26	40,000 hour(s)	50,000
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	E26	25,000 hour(s)	50,000
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	E27	25,000 hour(s)	25,000
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	E27	25,000 hour(s)	25,000

Light Technical

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Luminous Intensity (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929003740803	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P	930	40 degree(s)	950 lm	1,600 cd	3000 K	90
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	930	40 degree(s)	950 lm	1,600 cd	3000 K	90
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	930	25 degree(s)	1,200 lm	6,000 cd	3000 K	90
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	827	25 degree(s)	1,250 lm	5,000 cd	2700 K	80
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	930	40 degree(s)	900 lm	1,533 cd	3000 K	90
929003736904	13PAR38/COR/927/F25/DIM/P/ULW /T20 6/1FB	927	25 degree(s)	1,300 lm	5,700 cd	2700 K	90
929003737004	13PAR38/COR/927/F40/DIM/P/ULW /T20 6/1FB	927	40 degree(s)	1,300 lm	2,450 cd	2700 K	90
929003737104	13PAR38/COR/930/F25/DIM/P/ULW /T20 6/1FB	930	25 degree(s)	1,300 lm	6,000 cd	3000 K	90
929003737204	13PAR38/COR/930/F40/DIM/P/ULW /T20 6/1FB	930	40 degree(s)	1,300 lm	2,500 cd	3000 K	90
929003737304	13PAR38/COR/940/F25/DIM/P/ULW /T20 6/1FB	940	25 degree(s)	1,300 lm	6,000 cd	4000 K	90
929003737404	13PAR38/COR/940/F40/DIM/P/ULW /T20 6/1FB	940	40 degree(s)	1,300 lm	2,500 cd	4000 K	90
929003737504	13PAR38/COR/950/F25/DIM/P/ULW /T20 6/1FB	950	25 degree(s)	1,300 lm	6,000 cd	5000 K	90
929003737604	13PAR38/COR/950/F40/DIM/P/ULW /T20 6/1FB	950	40 degree(s)	1,300 lm	2,500 cd	5000 K	90
929003737804	13PAR38/COR/935/F25/DIM/P/ULW /T20 6/1FB	935	25 degree(s)	1,300 lm	6,000 cd	3500 K	90
929003737904	10PAR38/COR/927/F25/DIM/P/ULW /T20 6/1FB	927	25 degree(s)	1,000 lm	4,100 cd	2700 K	90
929003738004	10PAR38/COR/927/F40/DIM/P/ULW /T20 6/1FB	927	40 degree(s)	1,000 lm	1,800 cd	2700 K	90
929003738104	10PAR38/COR/930/F25/DIM/P/ULW /T20 6/1FB	930	25 degree(s)	1,000 lm	4,100 cd	3000 K	90
929003738204	10PAR38/COR/930/F40/DIM/P/ULW /T20 6/1FB	930	40 degree(s)	1,000 lm	1,900 cd	3000 K	90
929003738304	10PAR38/COR/940/F40/DIM/P/ULW /T20 6/1FB	940	40 degree(s)	1,000 lm	1,900 cd	4000 K	90
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	930	25 degree(s)	1,350 lm	7,000 cd	3000 K	90
929003134407	13PAR38/S/13W/927 40D E27 ND/G/110-277V	927	40 degree(s)	1,200 lm	2,231 cd	2700 K	90
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/ T20 6/1FB	930	25 degree(s)	1,300 lm	6,000 cd	3000 K	90
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	930	8 degree(s)	1,350 lm	26,000 cd	3000 K	90

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Luminous Intensity (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	930	25 degree(s)	1,350 lm	7,000 cd	3000 K	90
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	930	40 degree(s)	1,350 lm	3,400 cd	3000 K	90
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	927	8 degree(s)	1,250 lm	24,000 cd	2700 K	95
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	927	25 degree(s)	1,250 lm	6,500 cd	2700 K	95
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	927	40 degree(s)	1,250 lm	3,000 cd	2700 K	95
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	940	8 degree(s)	1,350 lm	26,000 cd	4000 K	95
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	940	25 degree(s)	1,350 lm	7,000 cd	4000 K	95
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	940	40 degree(s)	1,350 lm	3,400 cd	4000 K	95
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	2700/3000/3500/4000/5000	40 degree(s)	900 lm	1,533 cd	2700 K 3000 K 3500 K 4000 K 5000 K	90
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	930	25 degree(s)	1,200 lm	6,000 cd	3000 K	90
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	950	25 degree(s)	1,200 lm	6,000 cd	5000 K	90

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Input Frequency	Power Consumption	Wattage Equivalent
929003740803	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P	50 to 60 Hz	50 to 60 Hz	6 W	90 W
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	-	50 to 60 Hz	6 W	90 W
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	60 Hz	60 Hz	17 W	120 W
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	50 to 60 Hz	50 to 60 Hz	14 W	90 W
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	-	50 to 60 Hz	10 W	90 W
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	-	60 Hz	13 W	120 W
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	-	60 Hz	10 W	90 W
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	-	60 Hz	10 W	90 W
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	-	60 Hz	10 W	90 W

Order Code	Full Product Name	Line Frequency	Input Frequency	Power Consumption	Wattage Equivalent
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	-	60 Hz	10 W	90 W
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	-	60 Hz	10 W	90 W
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	-	60 Hz	14 W	120 W
929003134407	13PAR38/S/13W/927 40D E27 ND/G/110-277V	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	-	60 Hz	13 W	120 W
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	-	60 Hz	14 W	120 W
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	-	60 Hz	14 W	120 W
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	-	60 Hz	14 W	120 W
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	-	60 Hz	14 W	120 W
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	-	60 Hz	14 W	120 W
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	-	60 Hz	14 W	120 W
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	-	60 Hz	14 W	120 W
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	-	60 Hz	14 W	120 W
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	-	60 Hz	14 W	120 W
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	-	60 Hz	10 W	90 W
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	50 to 60 Hz	50 to 60 Hz	13 W	120 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003740803	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P	60 °C
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	60 °C
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	90 °C
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	80 °C
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	70 °C
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	80 °C
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	80 °C
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	80 °C
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	80 °C
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	80 °C
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	73 °C
929003134407	13PAR38/S/13W/927 40D E27 ND/G/110-277V	65 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	85 °C
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	73 °C
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	73 °C
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	73 °C
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	73 °C
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	73 °C
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	73 °C
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	73 °C
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	73 °C
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	73 °C
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	75 °C
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	75 °C
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	75 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929003740803	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P	Only with specific dimmers
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	Only with specific dimmers
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	Yes
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	No
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	No
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	Only with specific dimmers
929003134407	13PAR38/S/13W/927 40D E27 ND/G/110-277V	No
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	Only with specific dimmers
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	Only with specific dimmers
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	Only with specific dimmers
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	Only with specific dimmers
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	Only with specific dimmers
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	Only with specific dimmers
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	Only with specific dimmers
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	Only with specific dimmers
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	Only with specific dimmers
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	Only with specific dimmers
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	Only with specific dimmers
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929003740803	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P	Frosted
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	Frosted
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	Clear
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	-
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	Clear
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Clear
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Clear
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Clear
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Clear
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Clear
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	Clear
929003134407	13PAR38/S/13W/927 40D E27 ND/G/110-277V	Frosted
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	Clear
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	Clear
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	Clear
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	Clear
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	Clear
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	Clear
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	Clear
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	Clear

Order Code	Full Product Name	Bulb Finish
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	Clear
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	Clear
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	Clear
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	Clear
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	Clear

Approval and Application

Order Code	Full Product Name	Ambient temperature range
929003740803	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20/2P	-40 to +45 °C
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	-40 to +45 °C
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	-20 to +45 °C
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	-20 to +45 °C
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	-20 to +45 °C
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	-20 to +45 °C
929003134407	13PAR38/S/13W/927 40D E27 ND/G/110-277V	-20 to +45 °C
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	-40 to +45 °C
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	-20 to +45 °C
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	-20 to +45 °C
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	-20 to +45 °C
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	-20 to +45 °C
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	-20 to +45 °C
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	-20 to +45 °C
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	-20 to +45 °C
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	-20 to +45 °C
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	-20 to +45 °C
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	-40 to +45 °C
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	-40 °C to 45 °C
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	-40 °C to 45 °C

