

PHILIPS

Lighting



**Everything you value
in a Halogen PAR38
with the benefits of
LED. Accent your
merchandise or space
without distraction.**

LED PAR38

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 8 to 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Features

- Lifetime of up to 40,000 hours
- Emit virtually no UV/IR light in the beam
- Up to CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

LED PAR38

Application


- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Versions




LEDspots GM 1 PAR38 E27

Dimensional drawing




Product	D	C
13PAR38/S/13W/927 40D E27 ND/G/110-277V	122 mm	137 mm



LED PAR38


Accent Diagrams



Accent Diagram - 13PAR38/S/13W/927 40D E27

ND/G/110-277V

Beam Diagrams



Beam diagram - 13PAR38/S/13W/927 40D E27

ND/G/110-277V

