



Everything you value in a Halogen PAR30 with the benefits of LED. Accent your merchandise or space without distraction.

LED PAR30 S/L

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 10 and 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

LED PAR30 S/L

Application



- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Versions



LEDspots PL PAR30S E27

Dimensional drawing






Product	D	C
8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	95 mm	117 mm

Product	D	C
10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	94 mm	91.5 mm

LED PAR30 S/L

Dimensional drawing



Product	D	C
8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	95 mm	92 mm

Product	D	C
10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	94 mm	114.5 mm

Product	D	C
LEDspot 70W PAR30S 827 100-240V 25D ND	97 mm	97 mm

General Information

Switching Cycle 50,000

Light Technical

LLMF At End Of Nominal Lifetime (Nom) 70 %

Operating and Electrical

Starting Time (Nom) 0.5 s

General Information

LED PAR30 S/L

Order Code	Full Product Name	Cap-Base	Nominal lifetime	Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	E26	25,000 hour(s)	929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	E26	25,000 hour(s)	929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	E26	25,000 hour(s)	929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	E26	40,000 hour(s)	929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	E26	40,000 hour(s)	929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	E26	40,000 hour(s)	929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	E26	25,000 hour(s)	929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	E26	25,000 hour(s)	929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	E26	25,000 hour(s)	929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	E26	40,000 hour(s)	929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	E26	40,000 hour(s)	929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	E26	40,000 hour(s)	929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)	929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	E27	25,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Color rendering index (CRI)	Color Code	Luminous Intensity	
			Temperature (Nom)				Luminous Flux	(Nom)
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	10 degree(s)	3000 K		90	930	1,000 lm	10,000 cd
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	25 degree(s)	3000 K		90	930	1,000 lm	5,000 cd
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	40 degree(s)	3000 K		90	930	1,000 lm	2,500 cd
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	40 degree(s)	2700 K		95	927	950 lm	2,000 cd
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	25 degree(s)	4000 K		95	940	1,000 lm	5,000 cd
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	40 degree(s)	4000 K		95	940	1,000 lm	2,500 cd
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	10 degree(s)	3000 K		90	930	1,000 lm	10,000 cd
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	25 degree(s)	3000 K		90	930	1,000 lm	5,000 cd
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	40 degree(s)	3000 K		90	930	1,000 lm	2,500 cd
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	25 degree(s)	2700 K		95	927	950 lm	4,500 cd
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	40 degree(s)	2700 K		95	927	950 lm	2,000 cd
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	40 degree(s)	4000 K		95	940	1,000 lm	2,500 cd
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	25 degree(s)	2700 K		90	927	850 lm	3,300 cd
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	40 degree(s)	2700 K		90	927	850 lm	1,600 cd
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	25 degree(s)	3000 K		90	930	900 lm	3,300 cd
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	40 degree(s)	3000 K		90	930	900 lm	1,600 cd
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	25 degree(s)	4000 K		90	940	900 lm	3,300 cd
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	40 degree(s)	4000 K		90	940	900 lm	1,600 cd
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	25 degree(s)	2700 K		90	927	850 lm	3,300 cd
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	40 degree(s)	2700 K		90	927	850 lm	1,600 cd

LED PAR30 S/L

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color	Color rendering	Color	Luminous Intensity	
			Temperature (Nom)	index (CRI)	Code	Luminous Flux (Nom)	(Nom)
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	25 degree(s)	3000 K	90	930	900 lm	3,300 cd
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	40 degree(s)	3000 K	90	930	900 lm	1,600 cd
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	25 degree(s)	3500 K	90	935	900 lm	3,300 cd
9290037353604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	25 degree(s)	4000 K	90	940	900 lm	3,300 cd
9290037353704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	40 degree(s)	4000 K	90	940	900 lm	1,600 cd
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	25 degree(s)	2700 K	80	827	900 lm	3,500 cd

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003754804	10PAR30L/ EXPERTCOLOR RETAIL/ S10/930/D	60 Hz	-	10 W	75 W	929003755504	10PAR30S/ EXPERTCOLOR/ F40/927/P/D/T/J A8	60 Hz	-	10 W	75 W
929003754904	10PAR30L/ EXPERTCOLOR RETAIL/ F25/930/D	60 Hz	-	10 W	75 W	929004579004	10PAR30S/ EXPERTCOLOR/ F40/940/P/D/T/ JA8	60 Hz	-	10 W	75 W
929003755004	10PAR30L/ EXPERTCOLOR RETAIL/ F40/930/D	60 Hz	-	10 W	75 W	929003738404	8.5PAR30L/COR/ 927/F25/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003755604	10PAR30L/ EXPERTCOLOR/ F40/927/P/D/T/J A8	60 Hz	-	10 W	75 W	929003738504	8.5PAR30L/COR/ 927/F40/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003755704	10PAR30L/ EXPERTCOLOR/ F25/940/P/D/T/ JA8	60 Hz	-	10 W	75 W	929003738604	8.5PAR30L/COR/ 930/F25/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003755804	10PAR30L/ EXPERTCOLOR/ F40/940/P/D/T/ JA8	60 Hz	-	10 W	75 W	929003738704	8.5PAR30L/COR/ 930/F40/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003755104	10PAR30S/ EXPERTCOLOR RETAIL/ S10/930/D	60 Hz	-	10 W	75 W	929003753404	8.5PAR30L/COR/ 940/F25/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003755204	10PAR30S/ EXPERTCOLOR RETAIL/ F25/930/D	60 Hz	-	10 W	75 W	929003753504	8.5PAR30L/COR/ 940/F40/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003755304	10PAR30S/ EXPERTCOLOR RETAIL/ F40/930/D	60 Hz	-	10 W	75 W	929003738804	8.5PAR30S/COR/ 927/F25/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003755404	10PAR30S/ EXPERTCOLOR/ F25/927/P/D/T/J A8	60 Hz	-	10 W	75 W	929003738904	8.5PAR30S/COR/ 927/F40/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
						929003739004	8.5PAR30S/COR/ 930/F25/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W
						929003739104	8.5PAR30S/COR/ 930/F40/D/P/UL W/T20 6/1FB	60 Hz	-	8.5 W	75 W

LED PAR30 S/L

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	50 to 60 Hz	50 to 60 Hz	9.5 W	70 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	73 °C
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	73 °C
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	73 °C
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	73 °C
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	73 °C
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	73 °C
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	73 °C
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	73 °C
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	73 °C
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	73 °C
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	73 °C
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	73 °C
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	85 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	85 °C
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	85 °C
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	85 °C
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	85 °C
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	85 °C
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	85 °C
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	85 °C
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	85 °C
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	85 °C
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	85 °C
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	85 °C
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	85 °C
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	70 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	Only with specific dimmers
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	Only with specific dimmers
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	Only with specific dimmers
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	Only with specific dimmers
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	Only with specific dimmers
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	Only with specific dimmers
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	Only with specific dimmers
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	Only with specific dimmers
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	Only with specific dimmers
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	Only with specific dimmers
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	Only with specific dimmers
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers

LED PAR30 S/L

Order Code	Full Product Name	Dimmable
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	No

Mechanical and Housing

Order Code	Full Product Name	Bulb	
		Finish	Bulb Shape
929003754804	10PAR30L/EXPERTCOLOR RETAIL/ S10/930/D	Clear	PAR30L
929003754904	10PAR30L/EXPERTCOLOR RETAIL/ F25/930/D	Clear	PAR30L
929003755004	10PAR30L/EXPERTCOLOR RETAIL/ F40/930/D	Clear	PAR30L
929003755604	10PAR30L/EXPERTCOLOR/ F40/927/P/D/T/JA8	Clear	PAR30L
929003755704	10PAR30L/EXPERTCOLOR/ F25/940/P/D/T/JA8	Clear	PAR30L
929003755804	10PAR30L/EXPERTCOLOR/ F40/940/P/D/T/JA8	Clear	PAR30L
929003755104	10PAR30S/EXPERTCOLOR RETAIL/ S10/930/D	Clear	PAR30S
929003755204	10PAR30S/EXPERTCOLOR RETAIL/ F25/930/D	Clear	PAR30S
929003755304	10PAR30S/EXPERTCOLOR RETAIL/ F40/930/D	Clear	PAR30S
929003755404	10PAR30S/EXPERTCOLOR/ F25/927/P/D/T/JA8	Clear	PAR30S
929003755504	10PAR30S/EXPERTCOLOR/ F40/927/P/D/T/JA8	Clear	PAR30S
929004579004	10PAR30S/EXPERTCOLOR/ F40/940/P/D/T/JA8	Clear	PAR30S
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	Clear	PAR30L

Order Code	Full Product Name	Bulb	
		Finish	Bulb Shape
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	Clear	PAR30L
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	Clear	PAR30L
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	Clear	PAR30L
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	Clear	PAR30L
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	Clear	PAR30L
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	Clear	PAR30S
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	-	PAR30S








Approval and Application

Order Code	Full Product Name	Ambient temperature range
929003754804	10PAR30L/EXPERTCOLOR RETAIL/ S10/930/D	-20 to +45 °C
929003754904	10PAR30L/EXPERTCOLOR RETAIL/ F25/930/D	-20 to +45 °C
929003755004	10PAR30L/EXPERTCOLOR RETAIL/ F40/930/D	-20 to +45 °C











Order Code	Full Product Name	Ambient temperature range
929003755604	10PAR30L/EXPERTCOLOR/ F40/927/P/D/T/JA8	-20 to +45 °C
929003755704	10PAR30L/EXPERTCOLOR/ F25/940/P/D/T/JA8	-20 to +45 °C
929003755804	10PAR30L/EXPERTCOLOR/ F40/940/P/D/T/JA8	-20 to +45 °C

LED PAR30 S/L

Order Code	Full Product Name	Ambient temperature range
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	-20 to +45 °C
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	-20 to +45 °C
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	-20 to +45 °C
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	-20 to +45 °C
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	-20 to +45 °C
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	-20 to +45 °C
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929002403212	LEDspot 70W PAR30S 827 100-240V 25D	-20 to +45 °C












LED PAR30 S/L




(cd) 0°

(cd) 0°


LED PAR30 S/L




Accent Diagrams




Accent Diagram -
8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB




Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F25/930/D




Accent Diagram -
8.5PAR30S/COR/930/F40/D/P/ULW/T20
6/1FB




Accent Diagram -
8.5PAR30S/COR/930/F25/D/P/ULW/T20
6/1FB



Accent Diagram -
8.5PAR30L/COR/927/F40/D/P/ULW/T20
6/1FB




Accent Diagram - 10PAR30S/EXPERTCOLOR/
F40/940/P/D/T/JA8




Accent Diagram -
8.5PAR30L/COR/930/F25/D/P/ULW/T20
6/1FB

LED PAR30 S/L


Accent Diagrams




Accent Diagram - 10PAR30L/EXPERTCOLOR/
F40/940/P/D/T/JA8




Accent Diagram -
8.5PAR30L/COR/940/F25/D/P/ULW/T20
6/1FB




Accent Diagram -
8.5PAR30S/COR/927/F40/D/P/ULW/T20
6/1FB




Accent Diagram -
8.5PAR30L/COR/930/F40/D/P/ULW/T20
6/1FB




Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F25/930/D



Accent Diagram - 10PAR30S/EXPERTCOLOR/
F25/927/P/D/T/JA8




Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F40/930/D




Accent Diagram -
8.5PAR30S/COR/940/F25/D/P/ULW/T20
6/1FB


Accent Diagrams




Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/S10/930/D




Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F40/930/D




Accent Diagram -
8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB




Accent Diagram -
8.5PAR30S/COR/935/F25/D/P/ULW/T20
6/1FB




Accent Diagram - 10PAR30L/EXPERTCOLOR/
F40/927/P/D/T/JA8



Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/S10/930/D




Accent Diagram -
8.5PAR30L/COR/940/F40/D/P/ULW/T20
6/1FB




Accent Diagram -
8.5PAR30S/COR/940/F40/D/P/ULW/T20
6/1FB

LED PAR30 S/L

Accent Diagrams




Accent Diagram - LEDspot 70W PAR30S 827
100-240V 25D ND




Accent Diagram - 10PAR30L/EXPERTCOLOR/
F25/940/P/D/T/JA8


Beam Diagrams




Beam diagram - 10PAR30L/EXPERTCOLOR/
F25/940/P/D/T/JA8



Beam diagram -
8.5PAR30S/COR/935/F25/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F25/930/D




Beam diagram -
8.5PAR30S/COR/930/F25/D/P/ULW/T20
6/1FB


Beam Diagrams




Beam diagram - 10PAR30L/EXPERTCOLOR/
F40/940/P/D/T/JA8




Beam diagram -
8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB




Beam diagram -
8.5PAR30S/COR/930/F40/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30S/EXPERTCOLOR/
F25/927/P/D/T/JA8



Beam diagram -
8.5PAR30S/COR/927/F40/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F40/930/D




Beam diagram -
8.5PAR30L/COR/930/F25/D/P/ULW/T20
6/1FB


Beam Diagrams




Beam diagram -
8.5PAR30L/COR/940/F40/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30L/EXPERTCOLOR/
F40/927/P/D/T/JA8




Beam diagram -
8.5PAR30L/COR/940/F25/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F25/930/D




Beam diagram -
8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB




Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/S10/930/D



Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F40/930/D




Beam diagram - LEDspot 70W PAR30S 827
100-240V 25D ND




Beam diagram -
8.5PAR30L/COR/930/F40/D/P/ULW/T20
6/1FB

LED PAR30 S/L


Beam Diagrams




Beam diagram - 10PAR30S/EXPERTCOLOR/
F40/940/P/D/T/JA8




Beam diagram - 10PAR30S/EXPERTCOLOR/
RETAIL/S10/930/D



Beam diagram -
8.5PAR30S/COR/940/F25/D/P/ULW/T20
6/1FB



Beam diagram -
8.5PAR30S/COR/940/F40/D/P/ULW/T20
6/1FB



Beam diagram -
8.5PAR30L/COR/927/F40/D/P/ULW/T20
6/1FB

