

PHILIPS

Lighting



The perfect festive touch for holidays and special occasions

LED Party Bulbs

Philips A shape party lamps provided a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays.

Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Creates a festive feel
- Adds a pop of color to any room

Features

- Available in Red, Blue, Green, Purple, Yellow and Orange
- 15,000 hour rated average life
- Instant on
- Emits virtually no UV/IR light
- No mercury for a safe environment

Application

- Hospitality
- Restaurants
- Ideal for parties, festivals and holidays in patios, decks and gazebos

LED Party Bulbs

Versions




LEDbulb Color P A19 E27 Red



LEDbulb Color P A19 E27 Yellow

Dimensional drawing



Product	D	C
8A19/LED/RED/ND 120V E27 6/1FB	60 mm	107 mm
8A19/LED/YELLOW/ND 120V E27 6/1FB	60 mm	107 mm

LED Party Bulbs

General Information	
Cap-Base	E27
Switching Cycle	20,000
Nominal lifetime	10,000 hour(s)
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Power Consumption	8 W
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	A19
Approval and Application	
Ambient temperature range	-20 to +45 °C

