



Affordable LED replacements for compact fluorescent 4-pin & 2-pin lamps

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Benefits

- Reduced lighting costs
- Excellent lighting uniformity and lumen maintenance
- Unmatched compatibility with existing ballasts

Applications

- Retail & hospitality
- Residential
- Healthcare

Features

- Excellent energy efficiency
- Horizontal lamps rotate to ensure the best possible lighting effect
- Easy installation. Plug-and-play replacement of existing CFL-ni lamps
- Conventional form factor fits into existing luminaires

Versions



SPPR_MLEDGA_0021-Product photo



SPPR_MLEDGA_0022-Product photo



LEDtube PLC 13H 5.5W G24Q
827 15D ND



LEDtube PLCT H 8W G24Q



LEDtube PLC 13V 5.5W G24Q
827 15D ND




LEDtube PLCT V 8W G24Q




LEDtube PLC 13H 5W GX23-2
827 15D ND

Dimensional drawing




Product	D1	D	A1	A2	A3
5.5PL-C/LED/13V/840/IF5/P/4P 20/1	45.7 mm	45.7 mm	24.6 mm	101.6 mm	117.6 mm

D	D1	A1	A2	A3
45.7mm	45.7mm	24.6mm	101.6mm	117.6mm




Product	D1	D	A1	A2	A3
10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	50 mm	50 mm	13 mm	110 mm	125 mm
10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	50 mm	50 mm	13 mm	110 mm	125 mm
10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	50 mm	50 mm	13 mm	110 mm	125 mm
10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	50 mm	50 mm	13 mm	110 mm	125 mm
12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	50 mm	50 mm	13 mm	110 mm	125 mm
12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	50 mm	50 mm	13 mm	110 mm	125 mm
12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	50 mm	50 mm	13 mm	110 mm	125 mm

D	D1	A1	A2	A3
50mm	50mm	13mm	110mm	125mm




Product	D1	D	A1	A2	A3
12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm
12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm
12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm
8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm
8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm
8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm
8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	34 mm	34 mm	129 mm	148 mm	164 mm

D	D1	A1	A2	A3
34mm	34mm	129mm	148mm	164mm




D	D1	A1	A2	A3
54mm	46mm	16mm	104mm	119mm

Product	D1	D	A1	A2	A3
11PL-C/T/COR/32V-3CCT/MF15/P/20/1	46 mm	54 mm	16 mm	104 mm	119 mm
8PL-C/T/COR/26V-3CCT/MF10/P/20/1	46 mm	54 mm	16 mm	104 mm	119 mm



D	D1	A1	A2	A3
27mm	27mm	91.5mm	122.4mm	137.4mm

Product	D1	D	A1	A2	A3
5.5PL-C/LED/13H/830/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/835/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/840/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/840/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm



D	D1	A1	A2	A3
42mm	32mm	82mm	135mm	150mm

Product	D1	D	A1	A2	A3
11PL-C/T/COR/32H-3CCT/MF15/P/20/1	32 mm	42 mm	82 mm	135 mm	150 mm
8PL-C/T/COR/26H-3CCT/MF10/P/20/1	32 mm	42 mm	82 mm	135 mm	150 mm

General Information

Switching Cycle 50,000

Light Technical

LLMF At End Of Nominal Lifetime (Nom) 70 %

Operating and Electrical

Starting Time (Nom) 0.5 s

Mechanical and Housing

Bulb Finish Frosted

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929001388004	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	G24q Rotatable end-cap	50,000 hour(s)
929001388104	8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	G24q Rotatable end-cap	50,000 hour(s)
929001388204	8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	G24q Rotatable end-cap	50,000 hour(s)
929001388304	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	G24q Rotatable end-cap	50,000 hour(s)
929001819804	12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	G24q Rotatable end-cap	50,000 hour(s)
929001819904	12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	G24q Rotatable end-cap	50,000 hour(s)
929001820004	12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	G24q Rotatable end-cap	50,000 hour(s)
929001388404	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	GX24q	50,000 hour(s)
929001388504	10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	GX24q	50,000 hour(s)
929001388604	10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	GX24q	50,000 hour(s)
929001388704	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	GX24q	50,000 hour(s)
929001820204	12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	GX24q	50,000 hour(s)
929001820304	12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	GX24q	50,000 hour(s)
929001820404	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	GX24q	50,000 hour(s)
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	G24q	50,000 hour(s)
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	G24q	50,000 hour(s)
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	G24q	50,000 hour(s)
929003477604	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	G24q	30,000 hour(s)
929003477804	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	G24q	30,000 hour(s)
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	G24q	50,000 hour(s)
929003477704	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	G24q	30,000 hour(s)
929003477904	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	G24q	30,000 hour(s)
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	GX23-2	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929001388004	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	827	120 degree(s)	850 lm	2700 K	82

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929001388104	8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	830	120 degree(s)	900 lm	3000 K	82
929001388204	8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	835	120 degree(s)	900 lm	3500 K	82
929001388304	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	840	120 degree(s)	950 lm	4000 K	82
929001819804	12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	830	120 degree(s)	1,350 lm	3000 K	82
929001819904	12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	835	120 degree(s)	1,400 lm	3500 K	82
929001820004	12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	840	120 degree(s)	1,450 lm	4000 K	82
929001388404	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	827	120 degree(s)	1,200 lm	2700 K	82
929001388504	10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	830	120 degree(s)	1,200 lm	3000 K	82
929001388604	10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	835	120 degree(s)	1,200 lm	3500 K	82
929001388704	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	840	120 degree(s)	1,300 lm	4000 K	82
929001820204	12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	830	120 degree(s)	1,400 lm	3000 K	82
929001820304	12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	835	120 degree(s)	1,450 lm	3500 K	82
929001820404	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	840	120 degree(s)	1,500 lm	4000 K	82
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	830	150 degree(s)	550 lm	3000 K	82
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	835	150 degree(s)	550 lm	3500 K	82
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	840	150 degree(s)	580 lm	4000 K	82
929003477604	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	3000/3500/4000	120 degree(s)	975 lm 1,000 lm 1,050 lm	Selectable 3000 K 3500 K 4000 K	83
929003477804	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	3000/3500/4000	120 degree(s)	1,425 lm 1,450 lm 1,500 lm	Selectable 3000 K 3500 K 4000 K	83
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	840	150 degree(s)	580 lm	4000 K	82
929003477704	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	3000/3500/4000	120 degree(s)	975 lm 1,000 lm 1,050 lm	Selectable 3000 K 3500 K 4000 K	83
929003477904	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	3000/3500/4000	120 degree(s)	1,425 lm 1,450 lm 1,500 lm	Selectable 3000 K 3500 K 4000 K	83
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	840	150 degree(s)	580 lm	4000 K	82

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Input Frequency	Power Consumption	Wattage Equivalent
929001388004	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	8.5 W	26 W
929001388104	8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	8.5 W	26 W
929001388204	8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	8.5 W	26 W
929001388304	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	8.5 W	26 W
929001819804	12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	12 W	32 W
929001819904	12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	12 W	32 W
929001820004	12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	12 W	32 W
929001388404	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	20000-100000 Hz	20000-100000 Hz	10.5 W	26 W
929001388504	10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	20000-100000 Hz	20000-100000 Hz	10.5 W	26 W

Order Code	Full Product Name	Line Frequency	Input Frequency	Power Consumption	Wattage Equivalent
929001388604	10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	20000-100000 Hz	20000-100000 Hz	10.5 W	26 W
929001388704	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	20000-100000 Hz	20000-100000 Hz	10.5 W	26 W
929001820204	12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	12 W	32 W
929001820304	12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	12 W	32 W
929001820404	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	20000-100000 Hz	20000-100000 Hz	12 W	32 W
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	25000-100000 Hz	25000-100000 Hz	5.5 W	13 W
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	25000-100000 Hz	25000-100000 Hz	5.5 W	13 W
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	25000-100000 Hz	25000-100000 Hz	5.5 W	13 W
929003477604	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	50 to 60 Hz	50 to 60 Hz	8 W	26 W
929003477804	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	50 to 60 Hz	50 to 60 Hz	11 W	32 W
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	25000-100000 Hz	25000-100000 Hz	5.5 W	13 W
929003477704	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	50 to 60 Hz	50 to 60 Hz	8 W	26 W
929003477904	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	50 to 60 Hz	50 to 60 Hz	11 W	32 W
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	50 to 60 Hz	50 to 60 Hz	5 W	13 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001388004	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	60 °C
929001388104	8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	60 °C
929001388204	8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	60 °C
929001388304	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	60 °C
929001819804	12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	25 °C
929001819904	12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	25 °C
929001820004	12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	25 °C
929001388404	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	60 °C
929001388504	10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	60 °C
929001388604	10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	60 °C
929001388704	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	60 °C
929001820204	12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	25 °C
929001820304	12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	25 °C
929001820404	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	25 °C
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	75 °C
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	75 °C
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	75 °C
929003477604	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	65 °C
929003477804	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	75 °C
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	70 °C
929003477704	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	65 °C
929003477904	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	75 °C
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	70 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001388004	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	Yes
929001388104	8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	Yes
929001388204	8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	Yes
929001388304	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	Yes
929001819804	12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	Yes
929001819904	12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	Yes
929001820004	12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	Yes
929001388404	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	Yes
929001388504	10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	Yes
929001388604	10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	Yes
929001388704	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	Yes
929001820204	12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	Yes
929001820304	12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	Yes
929001820404	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	Yes
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	Yes
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	Yes
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	Yes
929003477604	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	No
929003477804	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	No
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	Yes
929003477704	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	No
929003477904	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	No
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001388004	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	PL-C;PL-T
929001388104	8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	PL-C;PL-T
929001388204	8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	PL-C;PL-T
929001388304	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	PL-C;PL-T
929001819804	12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	PL-C;PL-T
929001819904	12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	PL-C;PL-T
929001820004	12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	PL-C;PL-T
929001388404	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	PL-C;PL-T
929001388504	10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	PL-C;PL-T
929001388604	10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	PL-C;PL-T
929001388704	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	PL-C;PL-T
929001820204	12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	PL-C;PL-T
929001820304	12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	PL-C;PL-T

Order Code	Full Product Name	Bulb Shape
929001820404	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	PL-C;PL-T
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	PL-C
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	PL-C
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	PL-C
929003477604	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	PL-C;PL-T
929003477804	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	PL-C;PL-T
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	PL-C
929003477704	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	PL-C;PL-T
929003477904	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	PL-C;PL-T
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	PL-C

Approval and Application

Order Code	Full Product Name	Ambient temperature range
929001388004	8.5PL-C/T/COR/26H-827/IF8/P/4P/DIM 10/1	-20 °C to 45 °C
929001388104	8.5PL-C/T/COR/26H-830/IF9/P/4P/DIM 10/1	-20 °C to 45 °C
929001388204	8.5PL-C/T/COR/26H-835/IF9/P/4P/DIM 10/1	-20 °C to 45 °C
929001388304	8.5PL-C/T/COR/26H-840/IF9/P/4P/DIM 10/1	-20 °C to 45 °C
929001819804	12PL-C/T/COR/32H-830/IF13/P/4P/DIM 10/1	-20 °C to 45 °C
929001819904	12PL-C/T/COR/32H-835/IF14/P/4P/DIM 10/1	-20 °C to 45 °C
929001820004	12PL-C/T/COR/32H-840/IF14/P/4P/DIM 10/1	-20 °C to 45 °C
929001388404	10.5PL-C/T/COR/26V-827/IF12/P/4P/DIM10/1	-20 °C to 45 °C
929001388504	10.5PL-C/T/COR/26V-830/IF13/P/4P/DIM10/1	-20 °C to 45 °C
929001388604	10.5PL-C/T/COR/26V-835/IF13/P/4P/DIM10/1	-20 °C to 45 °C
929001388704	10.5PL-C/T/COR/26V-840/IF13/P/4P/DIM10/1	-20 °C to 45 °C
929001820204	12PL-C/T/COR/32V-830/IF14/P/4P/DIM 10/1	-20 °C to 45 °C
929001820304	12PL-C/T/COR/32V-835/IF14/P/4P/DIM 10/1	-20 °C to 45 °C
929001820404	12PL-C/T/COR/32V-840/IF15/P/4P/DIM 10/1	-20 °C to 45 °C
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	-20 °C to 45 °C
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	-20 °C to 45 °C
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	-20 °C to 45 °C
929003477604	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	-20 to +45 °C
929003477804	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	-20 to +45 °C
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	-20 °C to 45 °C
929003477704	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	-20 to +45 °C
929003477904	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	-20 to +45 °C
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	-20 °C to 45 °C