


LED Designer Deco

7404039



Create a vintage or modern look while saving money with LED technology

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Benefits

- Light distribution and color which replicates the effect of standard, vintage-style incandescent lamps, or a modern sophisticated tint
- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high color rendering (CRI)

Applications

- Restaurants/Bars
- Lobbies/Reception areas

Features

- Integrated compact driver design to achieve a decorative look and feel
- Smooth Dimming
- Instant on
- 15,000 hours rated average life
- Wet location


Versions




LEDbulb CLAF NAM T10 E26
Amber



LEDbulb UFO Others E27 FR



LEDbulb NAM S14 E26 CL



LEDbulb 5,5ST19 VIN 930 E26
CL G SP D 1PF T20



UFO LEDbulb 24W E27 3000K
230V POS3




LEDbulb 6,5ST19 VIN 820 E26
Amber G SP D 1PFT20




LEDbulb UFO 125W E26
Others 865 Frosted


Dimensional drawing




Product	D	C
5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	64 mm	137 mm
6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	64 mm	137 mm



Product	D	C
26UFO/PER/830/FR/P/E26/ND 4/1PF	200 mm	77 mm
26UFO/PER/865/FR/P/E26/ND 4/1PF	200 mm	77 mm
UFO LEDBulb 15W E27 6500K 230V 1CT/6	150 mm	82 mm
UFO LEDBulb 24W E27 3000K 230V 1CT/6	200 mm	82 mm
UFO LEDBulb 24W E27 6500K 230V 1CT/6	200 mm	82 mm



Product	D	C
3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	32 mm	103 mm



Product	D	C
1S14/VIN/827/CL/G/E26/ND 1CT	45 mm	86 mm

General Information

Nominal lifetime	15,000 hour(s)
Rated Lifetime (Hours)	15,000 hour(s)

Light Technical

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical

Starting Time (Nom)	0.5 s
---------------------	-------

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	E26	20,000
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	E27	50,000
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	E26	20,000
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	E26	20,000
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	E27	50,000
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	E27	50,000
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	E26	20,000
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	E26	50,000
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	E26	50,000

Light Technical

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	820	330 degree(s)	225 lm	2000 K	80

Order Code	Full Product Name	Color Code	Beam Angle (Nom)	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	865	120 degree(s)	1,700 lm	6500 K	80
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	827	-	60 lm	2700 K	80
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	950	330 degree(s)	500 lm	5000 K	90
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	830	120 degree(s)	2,715 lm	3000 K	80
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	865	120 degree(s)	2,715 lm	6500 K	80
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	820	330 degree(s)	400 lm	2000 K	80
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	830	120 degree(s)	1,950 lm	3000 K	80
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	865	120 degree(s)	2,050 lm	6500 K	80

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Input Frequency	Power Consumption	Wattage Equivalent
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	60 Hz	60 Hz	3.5 W	25 W
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	15 W	100 W
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	50 to 60 Hz	50 to 60 Hz	1 W	10 W
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	60 Hz	60 Hz	5.5 W	60 W
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	24 W	150 W
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	24 W	150 W
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	60 Hz	60 Hz	6.5 W	60 W
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	125 W
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	125 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	-
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	72 °C
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	26 °C
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	-
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	68 °C
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	68 °C
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	-
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	72 °C
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	72 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	Only with specific dimmers
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	No
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	No

Order Code	Full Product Name	Dimmable
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	Only with specific dimmers
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	No
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	No
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	Only with specific dimmers
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	No
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	Amber	T10
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	Frosted	Others
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	Clear	S-14
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	Clear	ST19
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	Frosted	Others
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	Frosted	Others
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	Amber	ST19
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	Frosted	Others
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	Frosted	Others

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Ambient temperature range
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	-	-20 °C to 45 °C
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	15 kWh	-20 to +45 °C
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	-	-20 to +40 °C
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	-	-20 °C to 45 °C
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	24 kWh	-20 to +45 °C
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	24 kWh	-20 to +45 °C
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	-	-20 °C to 45 °C
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	-	-20 °C to 45 °C
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	-	-20 °C to 45 °C