



# Create a vintage or modern look while saving money with LED technology

## LED Designer Deco

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

### Benefits

- Light distribution and color which replicates the effect of standard, vintage-style incandescent lamps, or a modern sophisticated tint
- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high color rendering (CRI)

### Features

- Integrated compact driver design to achieve a decorative look and feel
- Smooth Dimming
- Instant on
- 15,000 hours rated average life
- Wet location

### Application

- Restaurants/Bars
- Lobbies/Reception areas

Versions




LEDbulb CLAF NAM T10 E26  
Amber



LEDbulb UFO Others E27 FR




LEDbulb NAM S14 E26 CL



LEDbulb 5,5ST19 VIN 930 E26 CL  
G SP D 1PF T20




LEDbulb UFO 75W E26 Others 865  
Frosted






LEDbulb 6,5ST19 VIN 820 E26  
Amber G SP D 1PFT20

Dimensional drawing



| Product                                 | D     | C      |
|-----------------------------------------|-------|--------|
| 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20 | 64 mm | 137 mm |
| 6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20 | 64 mm | 137 mm |

Dimensional drawing



| Product                              | D      | C     |
|--------------------------------------|--------|-------|
| 16UFO/PER/830/FR/P/E26/ND 4/1PF      | 150 mm | 77 mm |
| 26UFO/PER/830/FR/P/E26/ND 4/1PF      | 200 mm | 77 mm |
| 26UFO/PER/865/FR/P/E26/ND 4/1PF      | 200 mm | 77 mm |
| UFO LEDBulb 15W E27 6500K 230V 1CT/6 | 150 mm | 82 mm |
| UFO LEDBulb 24W E27 3000K 230V 1CT/6 | 200 mm | 82 mm |
| UFO LEDBulb 24W E27 6500K 230V 1CT/6 | 200 mm | 82 mm |

| Product                                  | D     | C      |
|------------------------------------------|-------|--------|
| 3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20 | 32 mm | 103 mm |

| Product                      | D     | C     |
|------------------------------|-------|-------|
| 1S14/VIN/827/CL/G/E26/ND 1CT | 45 mm | 86 mm |

| General Information                   |                |
|---------------------------------------|----------------|
| Nominal lifetime                      | 15,000 hour(s) |
| Light Technical                       |                |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %           |
| Operating and Electrical              |                |
| Starting Time (Nom)                   | 0.5 s          |

General Information

LED Designer Deco

| Order Code   | Full Product Name                            | Cap-Base | Rated Lifetime (Hours) | Switching Cycle |
|--------------|----------------------------------------------|----------|------------------------|-----------------|
| 929002987403 | 3.5T10/VIN/820/E26/<br>Amber/G/SP D 4/1PFT20 | E26      | -                      | 20,000          |
| 929001971571 | UFO LEDBulb 15W E27 6500K<br>230V 1CT/6      | E27      | -                      | 50,000          |
| 929003082704 | 1S14/VIN/827/CL/G/E26/ND 1CT                 | E26      | -                      | 20,000          |
| 929002988803 | 5.5ST19/VIN/950/E26/CL/G/SP<br>D 4/1PF T20   | E26      | -                      | 20,000          |
| 929002010553 | 16UFO/PER/830/FR/P/E26/ND<br>4/1PF           | E26      | 15,000<br>hour(s)      | 50,000          |
| 929001971871 | UFO LEDBulb 24W E27 3000K<br>230V 1CT/6      | E27      | -                      | 50,000          |

| Order Code   | Full Product Name                           | Cap-Base | Rated Lifetime (Hours) | Switching Cycle |
|--------------|---------------------------------------------|----------|------------------------|-----------------|
| 929001971971 | UFO LEDBulb 24W E27 6500K<br>230V 1CT/6     | E27      | -                      | 50,000          |
| 929002986903 | 6.5ST19/VIN/820/E26/<br>Amber/G/SP/D 1PFT20 | E26      | -                      | 20,000          |
| 929002010753 | 26UFO/PER/830/FR/P/E26/ND<br>4/1PF          | E26      | 15,000<br>hour(s)      | 50,000          |
| 929002010825 | 26UFO/PER/865/FR/P/E26/ND<br>4/1PF          | E26      | 15,000<br>hour(s)      | 50,000          |

Light Technical

| Order Code   | Full Product Name                        | Beam Angle (Nom) | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Color Code | Luminous Flux |
|--------------|------------------------------------------|------------------|------------------------------------|-----------------------------|------------|---------------|
| 929002987403 | 3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20 | 330 degree(s)    | 2000 K                             | 80                          | 820        | 225 lm        |
| 929001971571 | UFO LEDBulb 15W E27 6500K 230V 1CT/6     | 120 degree(s)    | 6500 K                             | 80                          | 865        | 1,700 lm      |
| 929003082704 | 1S14/VIN/827/CL/G/E26/ND 1CT             | -                | 2700 K                             | 80                          | 827        | 60 lm         |
| 929002988803 | 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20  | 330 degree(s)    | 5000 K                             | 90                          | 950        | 500 lm        |
| 929002010553 | 16UFO/PER/830/FR/P/E26/ND 4/1PF          | 120 degree(s)    | 3000 K                             | 80                          | 830        | 1,150 lm      |
| 929001971871 | UFO LEDBulb 24W E27 3000K 230V 1CT/6     | 120 degree(s)    | 3000 K                             | 80                          | 830        | 2,715 lm      |
| 929001971971 | UFO LEDBulb 24W E27 6500K 230V 1CT/6     | 120 degree(s)    | 6500 K                             | 80                          | 865        | 2,715 lm      |
| 929002986903 | 6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20  | 330 degree(s)    | 2000 K                             | 80                          | 820        | 400 lm        |
| 929002010753 | 26UFO/PER/830/FR/P/E26/ND 4/1PF          | 120 degree(s)    | 3000 K                             | 80                          | 830        | 1,950 lm      |
| 929002010825 | 26UFO/PER/865/FR/P/E26/ND 4/1PF          | 120 degree(s)    | 6500 K                             | 80                          | 865        | 2,050 lm      |

Operating and Electrical

| Order Code   | Full Product Name                               | Input Frequency | Line Frequency | Power Consumption | Wattage Equivalent |
|--------------|-------------------------------------------------|-----------------|----------------|-------------------|--------------------|
| 929002987403 | 3.5T10/VIN/820/E26/<br>Amber/G/SP<br>D 4/1PFT20 | 60 Hz           | 60 Hz          | 3.5 W             | 25 W               |
| 929001971571 | UFO LEDBulb 15W<br>E27 6500K<br>230V 1CT/6      | 50 to 60 Hz     | 50 to 60 Hz    | 15 W              | 100 W              |
| 929003082704 | 1S14/VIN/827/CL/G/E26/ND 1CT                    | 50 to 60 Hz     | 50 to 60 Hz    | 1 W               | 10 W               |
| 929002988803 | 5.5ST19/VIN/950/E26/CL/<br>G/SP D 4/1PF<br>T20  | 60 Hz           | 60 Hz          | 5.5 W             | 60 W               |
| 929002010553 | 16UFO/PER/830/FR/P/E26/ND 4/1PF                 | 50 to 60 Hz     | 50 to 60 Hz    | 16 W              | 75 W               |
| 929001971871 | UFO LEDBulb                                     | 50 to 60 Hz     | 50 to 60 Hz    | 24 W              | 150 W              |

| Order Code   | Full Product Name                               | Input Frequency | Line Frequency | Power Consumption | Wattage Equivalent |
|--------------|-------------------------------------------------|-----------------|----------------|-------------------|--------------------|
|              | 24W E27<br>3000K 230V<br>1CT/6                  |                 |                |                   |                    |
| 929001971971 | UFO LEDBulb 24W E27<br>6500K 230V<br>1CT/6      | 50 to 60 Hz     | 50 to 60 Hz    | 24 W              | 150 W              |
| 929002986903 | 6.5ST19/VIN/820/E26/<br>Amber/G/SP<br>/D 1PFT20 | 60 Hz           | 60 Hz          | 6.5 W             | 60 W               |
| 929002010753 | 26UFO/PER/830/FR/P/E26/ND 4/1PF                 | 50 to 60 Hz     | 50 to 60 Hz    | 26 W              | 125 W              |
| 929002010825 | 26UFO/PER/865/FR/P/E26/ND 4/1PF                 | 50 to 60 Hz     | 50 to 60 Hz    | 26 W              | 125 W              |

Temperature

| Order Code   | Full Product Name                        | T-Case Maximum (Nom) |
|--------------|------------------------------------------|----------------------|
| 929002987403 | 3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20 | -                    |
| 929001971571 | UFO LEDBulb 15W E27 6500K 230V 1CT/6     | 72 °C                |
| 929003082704 | 1S14/VIN/827/CL/G/E26/ND 1CT             | 26 °C                |
| 929002988803 | 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20  | -                    |
| 929002010553 | 16UFO/PER/830/FR/P/E26/ND 4/1PF          | 75 °C                |

| Order Code   | Full Product Name                       | T-Case Maximum (Nom) |
|--------------|-----------------------------------------|----------------------|
| 929001971871 | UFO LEDBulb 24W E27 3000K 230V 1CT/6    | 68 °C                |
| 929001971971 | UFO LEDBulb 24W E27 6500K 230V 1CT/6    | 68 °C                |
| 929002986903 | 6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20 | -                    |
| 929002010753 | 26UFO/PER/830/FR/P/E26/ND 4/1PF         | 72 °C                |
| 929002010825 | 26UFO/PER/865/FR/P/E26/ND 4/1PF         | 72 °C                |

Controls and Dimming

| Order Code   | Full Product Name                        | Dimmable                   |
|--------------|------------------------------------------|----------------------------|
| 929002987403 | 3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20 | Only with specific dimmers |
| 929001971571 | UFO LEDBulb 15W E27 6500K 230V 1CT/6     | No                         |
| 929003082704 | 1S14/VIN/827/CL/G/E26/ND 1CT             | No                         |
| 929002988803 | 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20  | Only with specific dimmers |
| 929002010553 | 16UFO/PER/830/FR/P/E26/ND 4/1PF          | No                         |

| Order Code   | Full Product Name                       | Dimmable                   |
|--------------|-----------------------------------------|----------------------------|
| 929001971871 | UFO LEDBulb 24W E27 3000K 230V 1CT/6    | No                         |
| 929001971971 | UFO LEDBulb 24W E27 6500K 230V 1CT/6    | No                         |
| 929002986903 | 6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20 | Only with specific dimmers |
| 929002010753 | 26UFO/PER/830/FR/P/E26/ND 4/1PF         | No                         |
| 929002010825 | 26UFO/PER/865/FR/P/E26/ND 4/1PF         | No                         |

Mechanical and Housing

| Order Code   | Full Product Name                        | Bulb        |        |
|--------------|------------------------------------------|-------------|--------|
|              |                                          | Bulb Finish | Shape  |
| 929002987403 | 3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20 | Amber       | T10    |
| 929001971571 | UFO LEDBulb 15W E27 6500K 230V 1CT/6     | Frosted     | Others |
| 929003082704 | 1S14/VIN/827/CL/G/E26/ND 1CT             | Clear       | S-14   |
| 929002988803 | 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20  | Clear       | ST19   |
| 929002010553 | 16UFO/PER/830/FR/P/E26/ND 4/1PF          | Frosted     | Others |

| Order Code   | Full Product Name                       | Bulb        |        |
|--------------|-----------------------------------------|-------------|--------|
|              |                                         | Bulb Finish | Shape  |
| 929001971871 | UFO LEDBulb 24W E27 3000K 230V 1CT/6    | Frosted     | Others |
| 929001971971 | UFO LEDBulb 24W E27 6500K 230V 1CT/6    | Frosted     | Others |
| 929002986903 | 6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20 | Amber       | ST19   |
| 929002010753 | 26UFO/PER/830/FR/P/E26/ND 4/1PF         | Frosted     | Others |
| 929002010825 | 26UFO/PER/865/FR/P/E26/ND 4/1PF         | Frosted     | Others |

Approval and Application

| Order Code   | Full Product Name                        | Ambient temperature range | Energy                 |
|--------------|------------------------------------------|---------------------------|------------------------|
|              |                                          |                           | Consumption kWh/1000 h |
| 929002987403 | 3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20 | -20 °C to 45 °C           | -                      |
| 929001971571 | UFO LEDBulb 15W E27 6500K 230V 1CT/6     | -20 to +45 °C             | 15 kWh                 |
| 929003082704 | 1S14/VIN/827/CL/G/E26/ND 1CT             | -20 to +40 °C             | -                      |
| 929002988803 | 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20  | -20 °C to 45 °C           | -                      |
| 929002010553 | 16UFO/PER/830/FR/P/E26/ND 4/1PF          | -20 °C to 45 °C           | -                      |
| 929001971871 | UFO LEDBulb 24W E27 3000K 230V 1CT/6     | -20 to +45 °C             | 24 kWh                 |
| 929001971971 | UFO LEDBulb 24W E27 6500K 230V 1CT/6     | -20 to +45 °C             | 24 kWh                 |
| 929002986903 | 6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20  | -20 °C to 45 °C           | -                      |

| Order Code   | Full Product Name               | Ambient temperature range | Energy                 |
|--------------|---------------------------------|---------------------------|------------------------|
|              |                                 |                           | Consumption kWh/1000 h |
| 929002010753 | 26UFO/PER/830/FR/P/E26/ND 4/1PF | -20 °C to 45 °C           | -                      |
| 929002010825 | 26UFO/PER/865/FR/P/E26/ND 4/1PF | -20 °C to 45 °C           | -                      |

