



Essential Smartbright waterproof is Slim and elegant, offers reliable performance in all weather conditions. It is strong, IP65 and IK06 and provides value for money.

Essential Smartbright waterproof

Essential Smartbright slim waterproof

Benefits

- Slim and Elegant
- Value for Money
- Easy installation

Essential Smartbright waterproof



Features

- Slim Design
- 20K hours life
- 2 Years warranty
- IP65, IK06
- Installation accessories included

Application

- Parking Garages
- Offices
- Residential

Dimensional drawing



Essential Smartbright waterproof

| General Information | |
|---------------------------------------|-----------------------------------|
| Driver included | Yes |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Light Technical | |
| Beam angle of light source | 120 degree(s) |
| Color rendering index (CRI) | >70 |
| Luminous Efficacy (rated) (Nom) | 90 lm/W |
| Optic type | Beam angle 120° |
| Operating and Electrical | |
| Protection class IEC | Safety class II |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Controls and Dimming | |
| Dimmable | No |
| Maximum dim level | Not applicable |
| Mechanical and Housing | |
| Optical cover type | Polycarbonate bowl/cover |
| Housing Color | White |
| Mech. impact protection code | IK06 |
| Ingress protection code | IP65 |
| Approval and Application | |
| Ambient temperature range | -20 °C to 40 °C |
| CE mark | Yes |
| ENEC mark | - |
| Flammability mark | - |
| Glow-wire test | Temperature 650 °C, duration 30 s |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Driver failure rate at 5000 h | 0.004 % |
| Median useful life L80B50 | 15,610 hour(s) |
| Median useful life L90B50 | 7,330 hour(s) |

Light Technical

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Luminous Flux |
|--------------|----------------------------------|------------------------------------|---------------|
| 911401821080 | WT035C LED15/NW PSU GM CFW L600 | 4000 K | 1,500 lm |
| 911401821180 | WT035C LED15/CW PSU GM CFW L600 | 6500 K | 1,500 lm |
| 911401821280 | WT035C LED30/NW PSU GM CFW L1200 | 4000 K | 3,000 lm |
| 911401821380 | WT035C LED30/CW PSU GM CFW L1200 | 6500 K | 3,000 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------|-------------------|
| 911401821080 | WT035C LED15/NW PSU GM CFW L600 | 15 W |
| 911401821180 | WT035C LED15/CW PSU GM CFW L600 | 15 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|----------------------------------|-------------------|
| 911401821280 | WT035C LED30/NW PSU GM CFW L1200 | 30 W |
| 911401821380 | WT035C LED30/CW PSU GM CFW L1200 | 30 W |

Initial Performance (IEC Compliant)

Essential Smartbright waterproof

| Order Code | Full Product Name | Initial chromaticity |
|--------------|---------------------------------|----------------------|
| 911401821080 | WT035C LED15/NW PSU GM CFW L600 | 0.3876 ; 0.3914 |
| 911401821180 | WT035C LED15/CW PSU GM CFW L600 | 0.323 ; 0.35 |

| Order Code | Full Product Name | Initial chromaticity |
|--------------|----------------------------------|----------------------|
| 911401821280 | WT035C LED30/NW PSU GM CFW L1200 | 0.3876 ; 0.3914 |
| 911401821380 | WT035C LED30/CW PSU GM CFW L1200 | 0.323 ; 0.35 |

