



A simple LED for everyday use

Ecohome

EcoHome LEDbulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize initial investment

Benefits

- Up to 90% energy saving compared with traditional incandescent lamps
- Lower maintenance costs
- Low initial investment


Features

- Easy retrofit with existing E27
- Long lifetime
- Non-Dimmable
- UV- and IR-free light

Application


- Domestic applications

Dimensional drawing




Product	D	C
EcoHome LEDBulb 12W E27 3000KLV 1PF/12NL	60 mm	108 mm
EcoHome LEDBulb 12W E27 3000KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 12W E27 3000KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 12W E27 6500KLV 1PF/12NL	60 mm	108 mm
EcoHome LEDBulb 12W E27 6500KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 12W E27 6500KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 12W E27 6500KLV 2PF/10CO	60 mm	109 mm
EcoHome LEDBulb 12W E27 6500KLV 3PF/12	60 mm	109 mm
EcoHome LEDBulb 14W E27 3000KLV 1PF/12MX	60 mm	108 mm
EcoHome LEDBulb 14W E27 3000KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 14W E27 3000KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 14W E27 3000KLV 3PF/12	60 mm	109 mm
EcoHome LEDBulb 14W E27 3000KLV 3PF/12MX	60 mm	108 mm
EcoHome LEDBulb 14W E27 6500KLV 1PF/12MX	60 mm	108 mm
EcoHome LEDBulb 14W E27 6500KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 14W E27 6500KLV 1PF/20	60 mm	109 mm
EcoHome LEDBulb 14W E27 6500KLV 3PF/12	60 mm	109 mm
EcoHome LEDBulb 14W E27 6500KLV 3PF/12MX	60 mm	108 mm
EcoHome LEDBulb 6W E27 3000KHV 1PF/20AR	60 mm	108 mm
EcoHome LEDBulb 6W E27 3000KHV 1PF/20UY	60 mm	108 mm
EcoHome LEDBulb 6W E27 6500KHV 1PF/20AR	60 mm	108 mm
EcoHome LEDBulb 6W E27 6500KHV 1PF/20UY	60 mm	108 mm
EcoHome LEDBulb 7W E27 6500KHV 3PF/6AR	60 mm	108 mm
EcoHome LEDBulb 8W E27 3000KHV 1PF/20AR	60 mm	108 mm
EcoHome LEDBulb 8W E27 3000KHV 1PF/20UY	60 mm	108 mm
EcoHome LEDBulb 8W E27 3000KHV 2PF/10AR	60 mm	108 mm
EcoHome LEDBulb 8W E27 3000KHV 3PF/6AR	60 mm	108 mm
EcoHome LEDBulb 8W E27 6500KHV 1PF/20AR	60 mm	108 mm
EcoHome LEDBulb 8W E27 6500KHV 1PF/20UY	60 mm	108 mm
EcoHome LEDBulb 8W E27 6500KHV 2PF/10AR	60 mm	108 mm
EcoHome LEDBulb 8W E27 6500KHV 3PF/6AR	60 mm	108 mm
EcoHome LEDBulb 9W E27 3000KHV 4PF/5AR	60 mm	108 mm
EcoHome LEDBulb 9W E27 6500KHV 4PF/5AR	60 mm	108 mm

Product	D	C
EcoHome LEDBulb 15W E27 3000KHV 1PF/20AR	60 mm	120 mm
EcoHome LEDBulb 15W E27 3000KHV 1PF/20UY	60 mm	120 mm
EcoHome LEDBulb 15W E27 6500KHV 1PF/20AR	60 mm	120 mm
EcoHome LEDBulb 15W E27 6500KHV 1PF/20UY	60 mm	120 mm



Dimensional drawing



Product	D	C
EcoHome LEDBulb 10.5WE27 3000KHV 3PF/6AR	60 mm	109 mm
EcoHome LEDBulb 10.5WE27 3000KHV1PF/20AR	60 mm	109 mm
EcoHome LEDBulb 10.5WE27 3000KHV1PF/20UY	60 mm	109 mm
EcoHome LEDBulb 10.5WE27 3000KHV2PF/10AR	60 mm	109 mm
EcoHome LEDBulb 10.5WE27 6500KHV 3PF/6AR	60 mm	109 mm
EcoHome LEDBulb 10.5WE27 6500KHV1PF/20AR	60 mm	109 mm
EcoHome LEDBulb 10.5WE27 6500KHV1PF/20UY	60 mm	109 mm
EcoHome LEDBulb 10.5WE27 6500KHV2PF/10AR	60 mm	109 mm
EcoHome LEDBulb 10W E27 3000KLV 1PF/12MX	60 mm	108 mm
EcoHome LEDBulb 10W E27 3000KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 10W E27 3000KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 10W E27 3000KLV 2PF/12	60 mm	107 mm
EcoHome LEDBulb 10W E27 3000KLV 4PF/12	60 mm	107 mm
EcoHome LEDBulb 10W E27 3000KLV 4PF/12MX	60 mm	108 mm
EcoHome LEDBulb 10W E27 6500KLV 1PF/12MX	60 mm	108 mm
EcoHome LEDBulb 10W E27 6500KLV 1PF/12NL	60 mm	108 mm
EcoHome LEDBulb 10W E27 6500KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 10W E27 6500KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 10W E27 6500KLV 2PF/10CO	60 mm	107 mm
EcoHome LEDBulb 10W E27 6500KLV 2PF/12	60 mm	107 mm
EcoHome LEDBulb 10W E27 6500KLV 3PF/12	60 mm	107 mm
EcoHome LEDBulb 10W E27 6500KLV 4PF/12	60 mm	107 mm
EcoHome LEDBulb 10W E27 6500KLV 4PF/12MX	60 mm	108 mm
EcoHome LEDBulb 13W E27 3000KHV 1PF/20AR	60 mm	109 mm
EcoHome LEDBulb 13W E27 3000KHV 1PF/20UY	60 mm	109 mm
EcoHome LEDBulb 13W E27 6500KHV 1PF/20AR	60 mm	109 mm
EcoHome LEDBulb 13W E27 6500KHV 1PF/20UY	60 mm	109 mm
EcoHome LEDBulb 13W E27 6500KHV 3PF/6AR	60 mm	109 mm
EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 5.5W E27 6500KLV 3PF/12	60 mm	107 mm
EcoHome LEDBulb 5.5W E27 6500KLV 4PF/12	60 mm	107 mm
EcoHome LEDBulb 6W E27 3000KLV 1PF/12MX	60 mm	108 mm
EcoHome LEDBulb 6W E27 6500KLV 1PF/12MX	60 mm	108 mm
EcoHome LEDBulb 8W E27 3000KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 8W E27 6500KLV 1PF/12NL	60 mm	108 mm
EcoHome LEDBulb 8W E27 6500KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 8W E27 6500KLV 1PF/20	60 mm	107 mm
EcoHome LEDBulb 8W E27 6500KLV 3PF/12	60 mm	107 mm
Ecohome LEDBulb 13W E27 3000KHV 2PF/10AR	60 mm	109 mm
Ecohome LEDBulb 13W E27 3000KHV 3PF/6AR	60 mm	109 mm
Ecohome LEDBulb 13W E27 6500KHV 2PF/10AR	60 mm	109 mm

General Information	
Cap-Base	E27
Switching Cycle	50,000
Light Technical	
Beam Angle (Nom)	150 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Nominal lifetime
929003793861	EcoHome LEDBulb 15W E27 3000KHV 1PF/20UY	15,000 hour(s)
929003793871	EcoHome LEDBulb 15W E27 3000KHV 1PF/20AR	15,000 hour(s)
929003793961	EcoHome LEDBulb 15W E27 6500KHV 1PF/20UY	15,000 hour(s)
929003793971	EcoHome LEDBulb 15W E27 6500KHV 1PF/20AR	15,000 hour(s)
929001954894	EcoHome LEDBulb 9W E27 6500KHV 4PF/5AR	10,000 hour(s)
929001955212	EcoHome LEDBulb 7W E27 6500KHV 3PF/6AR	10,000 hour(s)
929001955394	EcoHome LEDBulb 9W E27 3000KHV 4PF/5AR	10,000 hour(s)
929002312597	EcoHome LEDBulb 12W E27 3000KLV 1PF/12NL	6,000 hour(s)
929002312697	EcoHome LEDBulb 12W E27 6500KLV 1PF/12NL	6,000 hour(s)
929002312703	EcoHome LEDBulb 14W E27 3000KLV 1PF/12MX	15,000 hour(s)
929002312764	EcoHome LEDBulb 14W E27 3000KLV 3PF/12MX	15,000 hour(s)
929002312803	EcoHome LEDBulb 14W E27 6500KLV 1PF/12MX	15,000 hour(s)
929002312864	EcoHome LEDBulb 14W E27 6500KLV 3PF/12MX	15,000 hour(s)
929003793061	EcoHome LEDBulb 6W E27 3000KHV 1PF/20UY	15,000 hour(s)
929003793071	EcoHome LEDBulb 6W E27 3000KHV 1PF/20AR	15,000 hour(s)
929003793161	EcoHome LEDBulb 6W E27 6500KHV 1PF/20UY	15,000 hour(s)
929003793171	EcoHome LEDBulb 6W E27 6500KHV 1PF/20AR	15,000 hour(s)
929003793261	EcoHome LEDBulb 8W E27 3000KHV 1PF/20UY	15,000 hour(s)
929003793271	EcoHome LEDBulb 8W E27 3000KHV 1PF/20AR	15,000 hour(s)
929003793272	EcoHome LEDBulb 8W E27 3000KHV 2PF/10AR	15,000 hour(s)
929003793273	EcoHome LEDBulb 8W E27 3000KHV 3PF/6AR	15,000 hour(s)
929003793361	EcoHome LEDBulb 8W E27 6500KHV 1PF/20UY	15,000 hour(s)
929003793371	EcoHome LEDBulb 8W E27 6500KHV 1PF/20AR	15,000 hour(s)
929003793372	EcoHome LEDBulb 8W E27 6500KHV 2PF/10AR	15,000 hour(s)
929003793373	EcoHome LEDBulb 8W E27 6500KHV 3PF/6AR	15,000 hour(s)
929003797791	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	15,000 hour(s)
929003797831	EcoHome LEDBulb 12W E27 6500KLV 3PF/12	15,000 hour(s)
929003797877	EcoHome LEDBulb 12W E27 6500KLV 2PF/10CO	15,000 hour(s)
929003797891	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	15,000 hour(s)
929003797911	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	15,000 hour(s)
929003797931	EcoHome LEDBulb 14W E27 3000KLV 3PF/12	15,000 hour(s)
929003798011	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	15,000 hour(s)
929003798031	EcoHome LEDBulb 14W E27 6500KLV 3PF/12	15,000 hour(s)
929004229211	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	15,000 hour(s)
929004229311	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	15,000 hour(s)
929004266411	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	15,000 hour(s)
929004266511	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	15,000 hour(s)
929002312103	EcoHome LEDBulb 6W E27 3000KLV 1PF/12MX	15,000 hour(s)
929002312203	EcoHome LEDBulb 6W E27 6500KLV 1PF/12MX	15,000 hour(s)
929002312303	EcoHome LEDBulb 10W E27 3000KLV 1PF/12MX	15,000 hour(s)
929002312363	EcoHome LEDBulb 10W E27 3000KLV 4PF/12MX	15,000 hour(s)
929002312403	EcoHome LEDBulb 10W E27 6500KLV 1PF/12MX	15,000 hour(s)
929002312463	EcoHome LEDBulb 10W E27 6500KLV 4PF/12MX	15,000 hour(s)
929002324597	EcoHome LEDBulb 8W E27 6500KLV 1PF/12NL	6,000 hour(s)
929002386997	EcoHome LEDBulb 10W E27 6500KLV 1PF/12NL	6,000 hour(s)
929003793461	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20UY	15,000 hour(s)
929003793471	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20AR	15,000 hour(s)
929003793472	EcoHome LEDBulb 10.5WE27 3000KHV2PF/10AR	15,000 hour(s)
929003793473	EcoHome LEDBulb 10.5WE27 3000KHV 3PF/6AR	15,000 hour(s)
929003793561	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20UY	15,000 hour(s)
929003793571	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20AR	15,000 hour(s)

Order Code	Full Product Name	Nominal lifetime
929003793572	EcoHome LEDBulb 10.5WE27 6500KHV2PF/10AR	15,000 hour(s)
929003793573	EcoHome LEDBulb 10.5WE27 6500KHV 3PF/6AR	15,000 hour(s)
929003793661	EcoHome LEDBulb 13W E27 3000KHV 1PF/20UY	15,000 hour(s)
929003793671	EcoHome LEDBulb 13W E27 3000KHV 1PF/20AR	15,000 hour(s)
929003793672	EcoHome LEDBulb 13W E27 3000KHV 2PF/10AR	15,000 hour(s)
929003793673	EcoHome LEDBulb 13W E27 3000KHV 3PF/6AR	15,000 hour(s)
929003793761	EcoHome LEDBulb 13W E27 6500KHV 1PF/20UY	15,000 hour(s)
929003793771	EcoHome LEDBulb 13W E27 6500KHV 1PF/20AR	15,000 hour(s)
929003793772	EcoHome LEDBulb 13W E27 6500KHV 2PF/10AR	15,000 hour(s)
929003793773	EcoHome LEDBulb 13W E27 6500KHV 3PF/6AR	15,000 hour(s)
929003797311	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	15,000 hour(s)
929003797391	EcoHome LEDBulb 8W E27 3000KLV 1PF/20	15,000 hour(s)
929003797411	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	15,000 hour(s)
929003797431	EcoHome LEDBulb 5.5W E27 6500KLV 3PF/12	15,000 hour(s)
929003797441	EcoHome LEDBulb 5.5W E27 6500KLV 4PF/12	15,000 hour(s)
929003797471	EcoHome LEDBulb 8W E27 6500KLV 3PF/12	15,000 hour(s)
929003797491	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	15,000 hour(s)
929003797511	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	15,000 hour(s)
929003797521	EcoHome LEDBulb 10W E27 3000KLV 2PF/12	15,000 hour(s)
929003797541	EcoHome LEDBulb 10W E27 3000KLV 4PF/12	15,000 hour(s)
929003797611	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	15,000 hour(s)
929003797621	EcoHome LEDBulb 10W E27 6500KLV 2PF/12	15,000 hour(s)
929003797631	EcoHome LEDBulb 10W E27 6500KLV 3PF/12	15,000 hour(s)
929003797641	EcoHome LEDBulb 10W E27 6500KLV 4PF/12	15,000 hour(s)
929003797677	EcoHome LEDBulb 10W E27 6500KLV 2PF/10CO	15,000 hour(s)
929004228911	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	15,000 hour(s)
929004229011	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	15,000 hour(s)
929004229111	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	15,000 hour(s)
929004266211	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	15,000 hour(s)
929004266311	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	15,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003793861	EcoHome LEDBulb 15W E27 3000KHV 1PF/20UY	3000 K	830	1,300 lm
929003793871	EcoHome LEDBulb 15W E27 3000KHV 1PF/20AR	3000 K	830	1,300 lm
929003793961	EcoHome LEDBulb 15W E27 6500KHV 1PF/20UY	6500 K	865	1,300 lm
929003793971	EcoHome LEDBulb 15W E27 6500KHV 1PF/20AR	6500 K	865	1,300 lm
929001954894	EcoHome LEDBulb 9W E27 6500KHV 4PF/5AR	6500 K	865	720 lm
929001955212	EcoHome LEDBulb 7W E27 6500KHV 3PF/6AR	6500 K	865	540 lm
929001955394	EcoHome LEDBulb 9W E27 3000KHV 4PF/5AR	3000 K	830	680 lm
929002312597	EcoHome LEDBulb 12W E27 3000KLV 1PF/12NL	3000 K	830	910 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929002312697	EcoHome LEDBulb 12W E27 6500KLV 1PF/12NL	6500 K	865	910 lm
929002312703	EcoHome LEDBulb 14W E27 3000KLV 1PF/12MX	3000 K	830	1,310 lm
929002312764	EcoHome LEDBulb 14W E27 3000KLV 3PF/12MX	3000 K	830	1,310 lm
929002312803	EcoHome LEDBulb 14W E27 6500KLV 1PF/12MX	6500 K	865	1,310 lm
929002312864	EcoHome LEDBulb 14W E27 6500KLV 3PF/12MX	6500 K	865	1,310 lm
929003793061	EcoHome LEDBulb 6W E27 3000KHV 1PF/20UY	3000 K	830	520 lm
929003793071	EcoHome LEDBulb 6W E27 3000KHV 1PF/20AR	3000 K	830	520 lm
929003793161	EcoHome LEDBulb 6W E27 6500KHV 1PF/20UY	6500 K	865	520 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003793171	EcoHome LEDBulb 6W E27 6500KHV 1PF/20AR	6500 K	865	520 lm
929003793261	EcoHome LEDBulb 8W E27 3000KHV 1PF/20UY	3000 K	830	700 lm
929003793271	EcoHome LEDBulb 8W E27 3000KHV 1PF/20AR	3000 K	830	700 lm
929003793272	EcoHome LEDBulb 8W E27 3000KHV 2PF/10AR	3000 K	830	700 lm
929003793273	EcoHome LEDBulb 8W E27 3000KHV 3PF/6AR	3000 K	830	700 lm
929003793361	EcoHome LEDBulb 8W E27 6500KHV 1PF/20UY	6500 K	865	700 lm
929003793371	EcoHome LEDBulb 8W E27 6500KHV 1PF/20AR	6500 K	865	700 lm
929003793372	EcoHome LEDBulb 8W E27 6500KHV 2PF/10AR	6500 K	865	700 lm
929003793373	EcoHome LEDBulb 8W E27 6500KHV 3PF/6AR	6500 K	865	700 lm
929003797791	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	3000 K	830	910 lm
929003797831	EcoHome LEDBulb 12W E27 6500KLV 3PF/12	6500 K	865	910 lm
929003797877	EcoHome LEDBulb 12W E27 6500KLV 2PF/10CO	6500 K	865	910 lm
929003797891	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	6500 K	865	910 lm
929003797911	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	3000 K	830	1,310 lm
929003797931	EcoHome LEDBulb 14W E27 3000KLV 3PF/12	3000 K	830	1,310 lm
929003798011	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	6500 K	865	1,310 lm
929003798031	EcoHome LEDBulb 14W E27 6500KLV 3PF/12	6500 K	865	1,310 lm
929004229211	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	6500 K	865	910 lm
929004229311	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	6500 K	865	1,310 lm
929004266411	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	3000 K	830	910 lm
929004266511	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	3000 K	830	1,310 lm
929002312103	EcoHome LEDBulb 6W E27 3000KLV 1PF/12MX	3000 K	830	450 lm
929002312203	EcoHome LEDBulb 6W E27 6500KLV 1PF/12MX	6500 K	865	450 lm
929002312303	EcoHome LEDBulb 10W E27 3000KLV 1PF/12MX	3000 K	830	800 lm
929002312363	EcoHome LEDBulb 10W E27 3000KLV 4PF/12MX	3000 K	830	800 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929002312403	EcoHome LEDBulb 10W E27 6500KLV 1PF/12MX	6500 K	865	800 lm
929002312463	EcoHome LEDBulb 10W E27 6500KLV 4PF/12MX	6500 K	865	800 lm
929002324597	EcoHome LEDBulb 8W E27 6500KLV 1PF/12NL	6500 K	865	550 lm
929002386997	EcoHome LEDBulb 10W E27 6500KLV 1PF/12NL	6500 K	865	700 lm
929003793461	EcoHome LEDBulb 10.5WE27 3000KHV1PF/ 20UY	3000 K	830	900 lm
929003793471	EcoHome LEDBulb 10.5WE27 3000KHV1PF/ 20AR	3000 K	830	900 lm
929003793472	EcoHome LEDBulb 10.5WE27 3000KHV2PF/ 10AR	3000 K	830	900 lm
929003793473	EcoHome LEDBulb 10.5WE27 3000KHV 3PF/6AR	3000 K	830	900 lm
929003793561	EcoHome LEDBulb 10.5WE27 6500KHV1PF/ 20UY	6500 K	865	900 lm
929003793571	EcoHome LEDBulb 10.5WE27 6500KHV1PF/ 20AR	6500 K	865	900 lm
929003793572	EcoHome LEDBulb 10.5WE27 6500KHV2PF/ 10AR	6500 K	865	900 lm
929003793573	EcoHome LEDBulb 10.5WE27 6500KHV 3PF/6AR	6500 K	865	900 lm
929003793661	EcoHome LEDBulb 13W E27 3000KHV 1PF/20UY	3000 K	830	1,150 lm
929003793671	EcoHome LEDBulb 13W E27 3000KHV 1PF/20AR	3000 K	830	1,150 lm
929003793672	Ecohome LEDBulb 13W E27 3000KHV 2PF/10AR	3000 K	830	1,150 lm
929003793673	Ecohome LEDBulb 13W E27 3000KHV 3PF/6AR	3000 K	830	1,150 lm
929003793761	EcoHome LEDBulb 13W E27 6500KHV 1PF/20UY	6500 K	865	1,150 lm
929003793771	EcoHome LEDBulb 13W E27 6500KHV 1PF/20AR	6500 K	865	1,150 lm
929003793772	Ecohome LEDBulb 13W E27 6500KHV 2PF/10AR	6500 K	865	1,150 lm
929003793773	EcoHome LEDBulb 13W E27 6500KHV 3PF/6AR	6500 K	865	1,150 lm
929003797311	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	3000 K	830	450 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003797391	EcoHome LEDBulb 8W E27 3000KLV 1PF/20	3000 K	830	550 lm
929003797411	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	6500 K	865	450 lm
929003797431	EcoHome LEDBulb 5.5W E27 6500KLV 3PF/12	6500 K	865	550 lm
929003797441	EcoHome LEDBulb 5.5W E27 6500KLV 4PF/12	6500 K	865	550 lm
929003797471	EcoHome LEDBulb 8W E27 6500KLV 3PF/12	6500 K	865	550 lm
929003797491	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	6500 K	865	550 lm
929003797511	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	3000 K	830	800 lm
929003797521	EcoHome LEDBulb 10W E27 3000KLV 2PF/12	3000 K	830	800 lm
929003797541	EcoHome LEDBulb 10W E27 3000KLV 4PF/12	3000 K	830	800 lm
929003797611	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	6500 K	865	800 lm

Order Code	Full Product Name	Correlated Color		
		Temperature (Nom)	Color Code	Luminous Flux
929003797621	EcoHome LEDBulb 10W E27 6500KLV 2PF/12	6500 K	865	800 lm
929003797631	EcoHome LEDBulb 10W E27 6500KLV 3PF/12	6500 K	865	800 lm
929003797641	EcoHome LEDBulb 10W E27 6500KLV 4PF/12	6500 K	865	800 lm
929003797677	EcoHome LEDBulb 10W E27 6500KLV 2PF/10CO	6500 K	865	800 lm
929004228911	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	6500 K	865	450 lm
929004229011	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	6500 K	865	550 lm
929004229111	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	6500 K	865	800 lm
929004266211	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	3000 K	830	450 lm
929004266311	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	3000 K	830	800 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003793861	EcoHome LEDBulb 15W E27 3000KLV 1PF/20UY	50 to 60 Hz	-	15 W	100 W
929003793871	EcoHome LEDBulb 15W E27 3000KLV 1PF/20AR	50 to 60 Hz	-	15 W	100 W
929003793961	EcoHome LEDBulb 15W E27 6500KLV 1PF/20UY	50 to 60 Hz	-	15 W	100 W
929003793971	EcoHome LEDBulb 15W E27 6500KLV 1PF/20AR	50 to 60 Hz	-	15 W	100 W
929001954894	EcoHome LEDBulb 9W E27 6500KLV 4PF/5AR	50 to 60 Hz	50 to 60 Hz	9 W	65 W
929001955212	EcoHome LEDBulb 7W E27 6500KLV 3PF/6AR	50 to 60 Hz	50 to 60 Hz	7 W	50 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001955394	EcoHome LEDBulb 9W E27 3000KLV 4PF/5AR	50 to 60 Hz	50 to 60 Hz	9 W	65 W
929002312597	EcoHome LEDBulb 12W E27 3000KLV 1PF/12NL	50 to 60 Hz	50 to 60 Hz	12 W	75 W
929002312697	EcoHome LEDBulb 12W E27 6500KLV 1PF/12NL	50 to 60 Hz	50 to 60 Hz	12 W	75 W
929002312703	EcoHome LEDBulb 14W E27 3000KLV 1PF/12MX	50 to 60 Hz	50 to 60 Hz	14 W	100 W
929002312764	EcoHome LEDBulb 14W E27 3000KLV 3PF/12MX	50 to 60 Hz	50 to 60 Hz	14 W	100 W
929002312803	EcoHome LEDBulb 14W E27 6500KLV 1PF/12MX	50 to 60 Hz	50 to 60 Hz	14 W	100 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002312864	EcoHome LEDBulb 14W E27 6500KLV 3PF/12MX	50 to 60 Hz	50 to 60 Hz	14 W	100 W
929003793061	EcoHome LEDBulb 6W E27 3000KHV 1PF/20UY	50 to 60 Hz	-	6 W	50 W
929003793071	EcoHome LEDBulb 6W E27 3000KHV 1PF/20AR	50 to 60 Hz	-	6 W	50 W
929003793161	EcoHome LEDBulb 6W E27 6500KHV 1PF/20UY	50 to 60 Hz	-	6 W	50 W
929003793171	EcoHome LEDBulb 6W E27 6500KHV 1PF/20AR	50 to 60 Hz	-	6 W	50 W
929003793261	EcoHome LEDBulb 8W E27 3000KHV 1PF/20UY	50 to 60 Hz	-	8 W	65 W
929003793271	EcoHome LEDBulb 8W E27 3000KHV 1PF/20AR	50 to 60 Hz	-	8 W	65 W
929003793272	EcoHome LEDBulb 8W E27 3000KHV 2PF/10AR	50 to 60 Hz	-	8 W	65 W
929003793273	EcoHome LEDBulb 8W E27 3000KHV 3PF/6AR	50 to 60 Hz	-	8 W	65 W
929003793361	EcoHome LEDBulb 8W E27 6500KHV 1PF/20UY	50 to 60 Hz	-	8 W	65 W
929003793371	EcoHome LEDBulb 8W E27 6500KHV 1PF/20AR	50 to 60 Hz	-	8 W	65 W
929003793372	EcoHome LEDBulb 8W E27 6500KHV 2PF/10AR	50 to 60 Hz	-	8 W	65 W
929003793373	EcoHome LEDBulb 8W E27	50 to 60 Hz	-	8 W	65 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
	6500KHV 3PF/6AR				
929003797791	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	60 Hz	-	12 W	75 W
929003797831	EcoHome LEDBulb 12W E27 6500KLV 3PF/12	60 Hz	-	12 W	75 W
929003797877	EcoHome LEDBulb 12W E27 6500KLV 2PF/10CO	60 Hz	-	12 W	75 W
929003797891	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	60 Hz	-	12 W	75 W
929003797911	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	60 Hz	-	14 W	100 W
929003797931	EcoHome LEDBulb 14W E27 3000KLV 3PF/12	60 Hz	-	14 W	100 W
929003798011	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	60 Hz	-	14 W	100 W
929003798031	EcoHome LEDBulb 14W E27 6500KLV 3PF/12	60 Hz	-	14 W	100 W
929004229211	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	60 Hz	-	12 W	75 W
929004229311	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	60 Hz	-	14 W	100 W
929004266411	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	60 Hz	-	12 W	75 W
929004266511	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	60 Hz	-	14 W	100 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002312103	EcoHome LEDBulb 6W E27 3000KLV 1PF/12MX	50 to 60 Hz	50 to 60 Hz	6 W	40 W
929002312203	EcoHome LEDBulb 6W E27 6500KLV 1PF/12MX	50 to 60 Hz	50 to 60 Hz	6 W	40 W
929002312303	EcoHome LEDBulb 10W E27 3000KLV 1PF/12MX	50 to 60 Hz	50 to 60 Hz	10 W	60 W
929002312363	EcoHome LEDBulb 10W E27 3000KLV 4PF/12MX	50 to 60 Hz	50 to 60 Hz	10 W	60 W
929002312403	EcoHome LEDBulb 10W E27 6500KLV 1PF/12MX	50 to 60 Hz	50 to 60 Hz	10 W	60 W
929002312463	EcoHome LEDBulb 10W E27 6500KLV 4PF/12MX	50 to 60 Hz	50 to 60 Hz	10 W	60 W
929002324597	EcoHome LEDBulb 8W E27 6500KLV 1PF/12NL	50 to 60 Hz	50 to 60 Hz	8 W	50 W
929002386997	EcoHome LEDBulb 10W E27 6500KLV 1PF/12NL	50 to 60 Hz	50 to 60 Hz	10 W	60 W
929003793461	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20UY	50 to 60 Hz	-	10.5 W	80 W
929003793471	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20AR	50 to 60 Hz	-	10.5 W	80 W
929003793472	EcoHome LEDBulb 10.5WE27 3000KHV2PF/10AR	50 to 60 Hz	-	10.5 W	80 W
929003793473	EcoHome LEDBulb 10.5WE27	50 to 60 Hz	-	10.5 W	80 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
	3000KHV 3PF/6AR				
929003793561	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20UY	50 to 60 Hz	-	10.5 W	80 W
929003793571	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20AR	50 to 60 Hz	-	10.5 W	80 W
929003793572	EcoHome LEDBulb 10.5WE27 6500KHV2PF/10AR	50 to 60 Hz	-	10.5 W	80 W
929003793573	EcoHome LEDBulb 10.5WE27 6500KHV 3PF/6AR	50 to 60 Hz	-	10.5 W	80 W
929003793661	EcoHome LEDBulb 13W E27 3000KHV 1PF/20UY	50 to 60 Hz	-	13 W	95 W
929003793671	EcoHome LEDBulb 13W E27 3000KHV 1PF/20AR	50 to 60 Hz	-	13 W	95 W
929003793672	Ecohome LEDBulb 13W E27 3000KHV 2PF/10AR	50 to 60 Hz	-	13 W	95 W
929003793673	Ecohome LEDBulb 13W E27 3000KHV 3PF/6AR	50 to 60 Hz	-	13 W	95 W
929003793761	EcoHome LEDBulb 13W E27 6500KHV 1PF/20UY	50 to 60 Hz	-	13 W	95 W
929003793771	EcoHome LEDBulb 13W E27 6500KHV 1PF/20AR	50 to 60 Hz	-	13 W	95 W
929003793772	Ecohome LEDBulb 13W E27 6500KHV 2PF/10AR	50 to 60 Hz	-	13 W	95 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003793773	EcoHome LEDBulb 13W E27 6500KHV 3PF/6AR	50 to 60 Hz	-	13 W	95 W
929003797311	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	60 Hz	-	5.5 W	40 W
929003797391	EcoHome LEDBulb 8W E27 3000KLV 1PF/20	60 Hz	-	8 W	40 W
929003797411	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	60 Hz	-	5.5 W	40 W
929003797431	EcoHome LEDBulb 5.5W E27 6500KLV 3PF/12	60 Hz	-	5.5 W	40 W
929003797441	EcoHome LEDBulb 5.5W E27 6500KLV 4PF/12	60 Hz	-	5.5 W	40 W
929003797471	EcoHome LEDBulb 8W E27 6500KLV 3PF/12	60 Hz	-	8 W	40 W
929003797491	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	60 Hz	-	8 W	40 W
929003797511	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	60 Hz	-	10 W	60 W
929003797521	EcoHome LEDBulb 10W E27 3000KLV 2PF/12	60 Hz	-	10 W	60 W
929003797541	EcoHome LEDBulb 10W	60 Hz	-	10 W	60 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
	E27 3000KLV 4PF/12				
929003797611	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	60 Hz	-	10 W	60 W
929003797621	EcoHome LEDBulb 10W E27 6500KLV 2PF/12	60 Hz	-	10 W	60 W
929003797631	EcoHome LEDBulb 10W E27 6500KLV 3PF/12	60 Hz	-	10 W	60 W
929003797641	EcoHome LEDBulb 10W E27 6500KLV 4PF/12	60 Hz	-	10 W	60 W
929003797677	EcoHome LEDBulb 10W E27 6500KLV 2PF/10CO	60 Hz	-	10 W	60 W
929004228911	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	60 Hz	-	5.5 W	40 W
929004229011	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	60 Hz	-	8 W	40 W
929004229111	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	60 Hz	-	10 W	60 W
929004266211	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	60 Hz	-	5.5 W	40 W
929004266311	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	60 Hz	-	10 W	60 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003793861	EcoHome LEDBulb 15W E27 3000KHV 1PF/20UY	95 °C
929003793871	EcoHome LEDBulb 15W E27 3000KHV 1PF/20AR	95 °C
929003793961	EcoHome LEDBulb 15W E27 6500KHV 1PF/20UY	95 °C
929003793971	EcoHome LEDBulb 15W E27 6500KHV 1PF/20AR	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001954894	EcoHome LEDBulb 9W E27 6500KHV 4PF/5AR	78 °C
929001955212	EcoHome LEDBulb 7W E27 6500KHV 3PF/6AR	75 °C
929001955394	EcoHome LEDBulb 9W E27 3000KHV 4PF/5AR	78 °C
929002312597	EcoHome LEDBulb 12W E27 3000KLV 1PF/12NL	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002312697	EcoHome LEDBulb 12W E27 6500KLV 1PF/12NL	95 °C
929002312703	EcoHome LEDBulb 14W E27 3000KLV 1PF/12MX	95 °C
929002312764	EcoHome LEDBulb 14W E27 3000KLV 3PF/12MX	95 °C
929002312803	EcoHome LEDBulb 14W E27 6500KLV 1PF/12MX	95 °C
929002312864	EcoHome LEDBulb 14W E27 6500KLV 3PF/12MX	95 °C
929003793061	EcoHome LEDBulb 6W E27 3000KHV 1PF/20UY	75 °C
929003793071	EcoHome LEDBulb 6W E27 3000KHV 1PF/20AR	75 °C
929003793161	EcoHome LEDBulb 6W E27 6500KHV 1PF/20UY	75 °C
929003793171	EcoHome LEDBulb 6W E27 6500KHV 1PF/20AR	75 °C
929003793261	EcoHome LEDBulb 8W E27 3000KHV 1PF/20UY	85 °C
929003793271	EcoHome LEDBulb 8W E27 3000KHV 1PF/20AR	85 °C
929003793272	EcoHome LEDBulb 8W E27 3000KHV 2PF/10AR	85 °C
929003793273	EcoHome LEDBulb 8W E27 3000KHV 3PF/6AR	85 °C
929003793361	EcoHome LEDBulb 8W E27 6500KHV 1PF/20UY	85 °C
929003793371	EcoHome LEDBulb 8W E27 6500KHV 1PF/20AR	85 °C
929003793372	EcoHome LEDBulb 8W E27 6500KHV 2PF/10AR	85 °C
929003793373	EcoHome LEDBulb 8W E27 6500KHV 3PF/6AR	85 °C
929003797791	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	80 °C
929003797831	EcoHome LEDBulb 12W E27 6500KLV 3PF/12	80 °C
929003797877	EcoHome LEDBulb 12W E27 6500KLV 2PF/10CO	80 °C
929003797891	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	80 °C
929003797911	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	85 °C
929003797931	EcoHome LEDBulb 14W E27 3000KLV 3PF/12	85 °C
929003798011	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	85 °C
929003798031	EcoHome LEDBulb 14W E27 6500KLV 3PF/12	85 °C
929004229211	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	80 °C
929004229311	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	85 °C
929004266411	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	80 °C
929004266511	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	85 °C
929002312103	EcoHome LEDBulb 6W E27 3000KLV 1PF/12MX	85 °C
929002312203	EcoHome LEDBulb 6W E27 6500KLV 1PF/12MX	85 °C
929002312303	EcoHome LEDBulb 10W E27 3000KLV 1PF/12MX	90 °C
929002312363	EcoHome LEDBulb 10W E27 3000KLV 4PF/12MX	90 °C
929002312403	EcoHome LEDBulb 10W E27 6500KLV 1PF/12MX	90 °C
929002312463	EcoHome LEDBulb 10W E27 6500KLV 4PF/12MX	90 °C
929002324597	EcoHome LEDBulb 8W E27 6500KLV 1PF/12NL	85 °C
929002386997	EcoHome LEDBulb 10W E27 6500KLV 1PF/12NL	85 °C
929003793461	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20UY	85 °C
929003793471	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20AR	85 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003793472	EcoHome LEDBulb 10.5WE27 3000KHV2PF/10AR	85 °C
929003793473	EcoHome LEDBulb 10.5WE27 3000KHV 3PF/6AR	85 °C
929003793561	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20UY	85 °C
929003793571	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20AR	85 °C
929003793572	EcoHome LEDBulb 10.5WE27 6500KHV2PF/10AR	85 °C
929003793573	EcoHome LEDBulb 10.5WE27 6500KHV 3PF/6AR	85 °C
929003793661	EcoHome LEDBulb 13W E27 3000KHV 1PF/20UY	95 °C
929003793671	EcoHome LEDBulb 13W E27 3000KHV 1PF/20AR	95 °C
929003793672	EcoHome LEDBulb 13W E27 3000KHV 2PF/10AR	95 °C
929003793673	EcoHome LEDBulb 13W E27 3000KHV 3PF/6AR	95 °C
929003793761	EcoHome LEDBulb 13W E27 6500KHV 1PF/20UY	95 °C
929003793771	EcoHome LEDBulb 13W E27 6500KHV 1PF/20AR	95 °C
929003793772	EcoHome LEDBulb 13W E27 6500KHV 2PF/10AR	95 °C
929003793773	EcoHome LEDBulb 13W E27 6500KHV 3PF/6AR	95 °C
929003797311	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	75 °C
929003797391	EcoHome LEDBulb 8W E27 3000KLV 1PF/20	75 °C
929003797411	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	75 °C
929003797431	EcoHome LEDBulb 5.5W E27 6500KLV 3PF/12	75 °C
929003797441	EcoHome LEDBulb 5.5W E27 6500KLV 4PF/12	75 °C
929003797471	EcoHome LEDBulb 8W E27 6500KLV 3PF/12	75 °C
929003797491	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	75 °C
929003797511	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	80 °C
929003797521	EcoHome LEDBulb 10W E27 3000KLV 2PF/12	80 °C
929003797541	EcoHome LEDBulb 10W E27 3000KLV 4PF/12	80 °C
929003797611	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	80 °C
929003797621	EcoHome LEDBulb 10W E27 6500KLV 2PF/12	80 °C
929003797631	EcoHome LEDBulb 10W E27 6500KLV 3PF/12	80 °C
929003797641	EcoHome LEDBulb 10W E27 6500KLV 4PF/12	80 °C
929003797677	EcoHome LEDBulb 10W E27 6500KLV 2PF/10CO	80 °C
929004228911	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	70 °C
929004229011	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	75 °C
929004229111	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	80 °C
929004266211	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	70 °C
929004266311	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	80 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003793861	EcoHome LEDBulb 15W E27 3000KHV 1PF/20UY	A60
929003793871	EcoHome LEDBulb 15W E27 3000KHV 1PF/20AR	A60
929003793961	EcoHome LEDBulb 15W E27 6500KHV 1PF/20UY	A60
929003793971	EcoHome LEDBulb 15W E27 6500KHV 1PF/20AR	A60
929001954894	EcoHome LEDBulb 9W E27 6500KHV 4PF/5AR	A60
929001955212	EcoHome LEDBulb 7W E27 6500KHV 3PF/6AR	A60

Order Code	Full Product Name	Bulb Shape
929001955394	EcoHome LEDBulb 9W E27 3000KHV 4PF/5AR	A60
929002312597	EcoHome LEDBulb 12W E27 3000KLV 1PF/12NL	A19
929002312697	EcoHome LEDBulb 12W E27 6500KLV 1PF/12NL	A19
929002312703	EcoHome LEDBulb 14W E27 3000KLV 1PF/12MX	A19
929002312764	EcoHome LEDBulb 14W E27 3000KLV 3PF/12MX	A19
929002312803	EcoHome LEDBulb 14W E27 6500KLV 1PF/12MX	A19

Order Code	Full Product Name	Bulb Shape
929002312864	EcoHome LEDBulb 14W E27 6500KLV 3PF/12MX	A19
929003793061	EcoHome LEDBulb 6W E27 3000KHV 1PF/20UY	A60
929003793071	EcoHome LEDBulb 6W E27 3000KHV 1PF/20AR	A60
929003793161	EcoHome LEDBulb 6W E27 6500KHV 1PF/20UY	A60
929003793171	EcoHome LEDBulb 6W E27 6500KHV 1PF/20AR	A60
929003793261	EcoHome LEDBulb 8W E27 3000KHV 1PF/20UY	A60
929003793271	EcoHome LEDBulb 8W E27 3000KHV 1PF/20AR	A60
929003793272	EcoHome LEDBulb 8W E27 3000KHV 2PF/10AR	A60
929003793273	EcoHome LEDBulb 8W E27 3000KHV 3PF/6AR	A60
929003793361	EcoHome LEDBulb 8W E27 6500KHV 1PF/20UY	A60
929003793371	EcoHome LEDBulb 8W E27 6500KHV 1PF/20AR	A60
929003793372	EcoHome LEDBulb 8W E27 6500KHV 2PF/10AR	A60
929003793373	EcoHome LEDBulb 8W E27 6500KHV 3PF/6AR	A60
929003797791	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	A19
929003797831	EcoHome LEDBulb 12W E27 6500KLV 3PF/12	A19
929003797877	EcoHome LEDBulb 12W E27 6500KLV 2PF/10CO	A19
929003797891	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	A19
929003797911	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	A19
929003797931	EcoHome LEDBulb 14W E27 3000KLV 3PF/12	A19
929003798011	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	A19
929003798031	EcoHome LEDBulb 14W E27 6500KLV 3PF/12	A19
929004229211	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	A19
929004229311	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	A19
929004266411	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	A19
929004266511	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	A19
929002312103	EcoHome LEDBulb 6W E27 3000KLV 1PF/12MX	A19
929002312203	EcoHome LEDBulb 6W E27 6500KLV 1PF/12MX	A19
929002312303	EcoHome LEDBulb 10W E27 3000KLV 1PF/12MX	A19
929002312363	EcoHome LEDBulb 10W E27 3000KLV 4PF/12MX	A19
929002312403	EcoHome LEDBulb 10W E27 6500KLV 1PF/12MX	A19
929002312463	EcoHome LEDBulb 10W E27 6500KLV 4PF/12MX	A19
929002324597	EcoHome LEDBulb 8W E27 6500KLV 1PF/12NL	A19
929002386997	EcoHome LEDBulb 10W E27 6500KLV 1PF/12NL	A19
929003793461	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20UY	A60
929003793471	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20AR	A60

Order Code	Full Product Name	Bulb Shape
929003793472	EcoHome LEDBulb 10.5WE27 3000KHV2PF/10AR	A60
929003793473	EcoHome LEDBulb 10.5WE27 3000KHV 3PF/6AR	A60
929003793561	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20UY	A60
929003793571	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20AR	A60
929003793572	EcoHome LEDBulb 10.5WE27 6500KHV2PF/10AR	A60
929003793573	EcoHome LEDBulb 10.5WE27 6500KHV 3PF/6AR	A60
929003793661	EcoHome LEDBulb 13W E27 3000KHV 1PF/20UY	A60
929003793671	EcoHome LEDBulb 13W E27 3000KHV 1PF/20AR	A60
929003793672	EcoHome LEDBulb 13W E27 3000KHV 2PF/10AR	A60
929003793673	EcoHome LEDBulb 13W E27 3000KHV 3PF/6AR	A60
929003793761	EcoHome LEDBulb 13W E27 6500KHV 1PF/20UY	A60
929003793771	EcoHome LEDBulb 13W E27 6500KHV 1PF/20AR	A60
929003793772	EcoHome LEDBulb 13W E27 6500KHV 2PF/10AR	A60
929003793773	EcoHome LEDBulb 13W E27 6500KHV 3PF/6AR	A60
929003797311	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	A19
929003797391	EcoHome LEDBulb 8W E27 3000KLV 1PF/20	A19
929003797411	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	A19
929003797431	EcoHome LEDBulb 5.5W E27 6500KLV 3PF/12	A19
929003797441	EcoHome LEDBulb 5.5W E27 6500KLV 4PF/12	A19
929003797471	EcoHome LEDBulb 8W E27 6500KLV 3PF/12	A19
929003797491	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	A19
929003797511	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	A19
929003797521	EcoHome LEDBulb 10W E27 3000KLV 2PF/12	A19
929003797541	EcoHome LEDBulb 10W E27 3000KLV 4PF/12	A19
929003797611	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	A19
929003797621	EcoHome LEDBulb 10W E27 6500KLV 2PF/12	A19
929003797631	EcoHome LEDBulb 10W E27 6500KLV 3PF/12	A19
929003797641	EcoHome LEDBulb 10W E27 6500KLV 4PF/12	A19
929003797677	EcoHome LEDBulb 10W E27 6500KLV 2PF/10CO	A19
929004228911	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	A19
929004229011	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	A19
929004229111	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	A19
929004266211	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	A19
929004266311	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	A19

Approval and Application






Order Code	Full Product Name	Energy	
		Ambient temperature range	Consumption kWh/1000 h
929003793861	EcoHome LEDBulb 15W E27 3000KHV 1PF/20UY	-20 to +45 °C	-
929003793871	EcoHome LEDBulb 15W E27 3000KHV 1PF/20AR	-20 to +45 °C	-
929003793961	EcoHome LEDBulb 15W E27 6500KHV 1PF/20UY	-20 to +45 °C	-
929003793971	EcoHome LEDBulb 15W E27 6500KHV 1PF/20AR	-20 to +45 °C	-
929001954894	EcoHome LEDBulb 9W E27 6500KHV 4PF/5AR	-20 °C to 45 °C	-











Order Code	Full Product Name	Energy	
		Ambient temperature range	Consumption kWh/1000 h
929001955212	EcoHome LEDBulb 7W E27 6500KHV 3PF/6AR	-20 to +45 °C	7 kWh
929001955394	EcoHome LEDBulb 9W E27 3000KHV 4PF/5AR	-20 °C to 45 °C	-
929002312597	EcoHome LEDBulb 12W E27 3000KLV 1PF/12NL	-20 to +45 °C	-
929002312697	EcoHome LEDBulb 12W E27 6500KLV 1PF/12NL	-20 to +45 °C	-
929002312703	EcoHome LEDBulb 14W E27 3000KLV 1PF/12MX	-20 to +45 °C	-











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002312764	EcoHome LEDBulb 14W E27 3000KLV 3PF/12MX	-20 to +45 °C	-
929002312803	EcoHome LEDBulb 14W E27 6500KLV 1PF/12MX	-20 to +45 °C	-
929002312864	EcoHome LEDBulb 14W E27 6500KLV 3PF/12MX	-20 to +45 °C	-
929003793061	EcoHome LEDBulb 6W E27 3000KHV 1PF/20UY	-20 to +45 °C	-
929003793071	EcoHome LEDBulb 6W E27 3000KHV 1PF/20AR	-20 to +45 °C	-
929003793161	EcoHome LEDBulb 6W E27 6500KHV 1PF/20UY	-20 to +45 °C	-
929003793171	EcoHome LEDBulb 6W E27 6500KHV 1PF/20AR	-20 to +45 °C	-
929003793261	EcoHome LEDBulb 8W E27 3000KHV 1PF/20UY	-20 to +45 °C	-
929003793271	EcoHome LEDBulb 8W E27 3000KHV 1PF/20AR	-20 to +45 °C	-
929003793272	EcoHome LEDBulb 8W E27 3000KHV 2PF/10AR	-20 to +45 °C	-
929003793273	EcoHome LEDBulb 8W E27 3000KHV 3PF/6AR	-20 to +45 °C	-
929003793361	EcoHome LEDBulb 8W E27 6500KHV 1PF/20UY	-20 to +45 °C	-
929003793371	EcoHome LEDBulb 8W E27 6500KHV 1PF/20AR	-20 to +45 °C	-
929003793372	EcoHome LEDBulb 8W E27 6500KHV 2PF/10AR	-20 to +45 °C	-
929003793373	EcoHome LEDBulb 8W E27 6500KHV 3PF/6AR	-20 to +45 °C	-
929003797791	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	-20 to +45 °C	-
929003797831	EcoHome LEDBulb 12W E27 6500KLV 3PF/12	-20 to +45 °C	-
929003797877	EcoHome LEDBulb 12W E27 6500KLV 2PF/10CO	-20 to +45 °C	-
929003797891	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	-20 to +45 °C	-
929003797911	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	-20 to +45 °C	-
929003797931	EcoHome LEDBulb 14W E27 3000KLV 3PF/12	-20 to +45 °C	-
929003798011	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	-20 to +45 °C	-
929003798031	EcoHome LEDBulb 14W E27 6500KLV 3PF/12	-20 to +45 °C	-
929004229211	EcoHome LEDBulb 12W E27 6500KLV 1PF/20	-20 to +45 °C	-
929004229311	EcoHome LEDBulb 14W E27 6500KLV 1PF/20	-20 to +45 °C	-











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929004266411	EcoHome LEDBulb 12W E27 3000KLV 1PF/20	-20 to +45 °C	-
929004266511	EcoHome LEDBulb 14W E27 3000KLV 1PF/20	-20 to +45 °C	-
929002312103	EcoHome LEDBulb 6W E27 3000KLV 1PF/12MX	-20 to +45 °C	-
929002312203	EcoHome LEDBulb 6W E27 6500KLV 1PF/12MX	-20 to +45 °C	-
929002312303	EcoHome LEDBulb 10W E27 3000KLV 1PF/12MX	-20 to +45 °C	-
929002312363	EcoHome LEDBulb 10W E27 3000KLV 4PF/12MX	-20 to +45 °C	-
929002312403	EcoHome LEDBulb 10W E27 6500KLV 1PF/12MX	-20 to +45 °C	-
929002312463	EcoHome LEDBulb 10W E27 6500KLV 4PF/12MX	-20 to +45 °C	-
929002324597	EcoHome LEDBulb 8W E27 6500KLV 1PF/12NL	-20 to +45 °C	-
929002386997	EcoHome LEDBulb 10W E27 6500KLV 1PF/12NL	-20 to +45 °C	-
929003793461	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20UY	-20 to +45 °C	-
929003793471	EcoHome LEDBulb 10.5WE27 3000KHV1PF/20AR	-20 to +45 °C	-
929003793472	EcoHome LEDBulb 10.5WE27 3000KHV2PF/10AR	-20 to +45 °C	-
929003793473	EcoHome LEDBulb 10.5WE27 3000KHV 3PF/6AR	-20 to +45 °C	-
929003793561	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20UY	-20 to +45 °C	-
929003793571	EcoHome LEDBulb 10.5WE27 6500KHV1PF/20AR	-20 to +45 °C	-
929003793572	EcoHome LEDBulb 10.5WE27 6500KHV2PF/10AR	-20 to +45 °C	-
929003793573	EcoHome LEDBulb 10.5WE27 6500KHV 3PF/6AR	-20 to +45 °C	-
929003793661	EcoHome LEDBulb 13W E27 3000KHV 1PF/20UY	-20 to +45 °C	-
929003793671	EcoHome LEDBulb 13W E27 3000KHV 1PF/20AR	-20 to +45 °C	-
929003793672	Ecohome LEDBulb 13W E27 3000KHV 2PF/10AR	-20 to +45 °C	-
929003793673	Ecohome LEDBulb 13W E27 3000KHV 3PF/6AR	-20 to +45 °C	-
929003793761	EcoHome LEDBulb 13W E27 6500KHV 1PF/20UY	-20 to +45 °C	-
929003793771	EcoHome LEDBulb 13W E27 6500KHV 1PF/20AR	-20 to +45 °C	-
929003793772	Ecohome LEDBulb 13W E27 6500KHV 2PF/10AR	-20 to +45 °C	-

Order Code	Full Product Name	Ambient temperature range	Energy
			Consumption kWh/1000 h
929003793773	EcoHome LEDBulb 13W E27 6500KHV 3PF/6AR	-20 to +45 °C	-
929003797311	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	-20 to +45 °C	-
929003797391	EcoHome LEDBulb 8W E27 3000KLV 1PF/20	-20 to +45 °C	-
929003797411	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	-20 to +45 °C	-
929003797431	EcoHome LEDBulb 5.5W E27 6500KLV 3PF/12	-20 to +45 °C	-
929003797441	EcoHome LEDBulb 5.5W E27 6500KLV 4PF/12	-20 to +45 °C	-
929003797471	EcoHome LEDBulb 8W E27 6500KLV 3PF/12	-20 to +45 °C	-
929003797491	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	-20 to +45 °C	-
929003797511	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	-20 to +45 °C	-
929003797521	EcoHome LEDBulb 10W E27 3000KLV 2PF/12	-20 to +45 °C	-
929003797541	EcoHome LEDBulb 10W E27 3000KLV 4PF/12	-20 to +45 °C	-
929003797611	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	-20 to +45 °C	-
929003797621	EcoHome LEDBulb 10W E27 6500KLV 2PF/12	-20 to +45 °C	-
929003797631	EcoHome LEDBulb 10W E27 6500KLV 3PF/12	-20 to +45 °C	-
929003797641	EcoHome LEDBulb 10W E27 6500KLV 4PF/12	-20 to +45 °C	-
929003797677	EcoHome LEDBulb 10W E27 6500KLV 2PF/10CO	-20 to +45 °C	-
929004228911	EcoHome LEDBulb 5.5W E27 6500KLV 1PF/20	-20 to +45 °C	-
929004229011	EcoHome LEDBulb 8W E27 6500KLV 1PF/20	-20 to +45 °C	-
929004229111	EcoHome LEDBulb 10W E27 6500KLV 1PF/20	-20 to +45 °C	-
929004266211	EcoHome LEDBulb 5.5W E27 3000KLV 1PF/20	-20 to +45 °C	-
929004266311	EcoHome LEDBulb 10W E27 3000KLV 1PF/20	-20 to +45 °C	-









Ecohome

