



# Bright, stylish and slim interior module

## MyCare LED Circular

MyCare LED Ceiling Module integrates a LED light source into a module. It is specially designed to replace fluorescent circular tubes working on a G10q fitting. The module offers significant energy savings and a long lifetime.

### Benefits

- Simple, fast, installation method
- Significant energy saving
- Long lifetime

### Features

- Highly energy-efficient
- Long lifetime
- Easy installation
- High Brightness

### Application

- Home application
- Corridors & stairways
- Parking

Versions




LEDtube MOD GMGC 10W Circular



LED Circular 840 G10q AP

Dimensional drawing



Product	A1	A2	A3
LED Circular 20W 840 G10q AP	30 mm	238 mm	298 mm
LED Circular 20W 865 G10q AP	30 mm	238 mm	298 mm

Product	D1	D2	A1	A2	A3
LED MOD 14W G3 865 APR	139 mm	139 mm	18 mm	126 mm	139 mm

# MyCare LED Circular

Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Approval and Application	
Ambient temperature range	-20 to +45 °C

## General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929003765707	LED MOD 14W G3 865 APR	-	15,000	20,000 hour(s)
929002010907	LED Circular 20W 840 G10q AP	G10q	50,000	30,000 hour(s)

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929002011007	LED Circular 20W 865 G10q AP	G10q	50,000	30,000 hour(s)

## Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003765707	LED MOD 14W G3 865 APR	150 degree(s)	6500 K	83	865	1,300 lm
929002010907	LED Circular 20W 840 G10q AP	120 degree(s)	4000 K	80	840	2,000 lm
929002011007	LED Circular 20W 865 G10q AP	120 degree(s)	6500 K	80	865	2,000 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003765707	LED MOD 14W G3 865 APR	14 W	22 W
929002010907	LED Circular 20W 840 G10q AP	20 W	32 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929002011007	LED Circular 20W 865 G10q AP	20 W	32 W

## Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003765707	LED MOD 14W G3 865 APR	80 °C
929002010907	LED Circular 20W 840 G10q AP	60 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002011007	LED Circular 20W 865 G10q AP	60 °C

## Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003765707	LED MOD 14W G3 865 APR	Frosted	Others
929002010907	LED Circular 20W 840 G10q AP	-	C-T9

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002011007	LED Circular 20W 865 G10q AP	-	C-T9

## Approval and Application

MyCare LED Circular

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003765707	LED MOD 14W G3 865 APR	-
929002010907	LED Circular 20W 840 G10q AP	20 kWh
929002011007	LED Circular 20W 865 G10q AP	20 kWh

