

The professional LED HID replacement lamp, instant retrofit, instant savings.

LED Wallpack Retrofits

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Benefits

- Energy savings up to >70%
- Longer lifetime and less maintenance cost
- Adjustable light direction enable to use in a variety of applications

Features

- Standard E26/EX39 base to replace metal halide lamps and E39 options
- Available in 3000K, 4000K and 5000K CCTs
- 360o Rotatable lamp cap
- Available in ranges between 70W and 175W replacements options and upto 9,000 lumens
- 3-year limited warranty
- Surge 4KV

Application

- Design for horizontal application
- Wall packs, Shoeboxes, Post-Top fixtures
- Parking lots, public areas and office outdoor fixtures


LED Wallpack Retrofits

Versions



LEDTForce WallPack EX39

Dimensional drawing



Product	D	C
40WP/LED/850/LS EX39 G3 BB 3/1	92 mm	215 mm

