



# New generation of specialty LEDtube

## Specialty LED tube

Philips specialty LEDtube integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for relamping to serve multi-purpose usage: it meets general lighting requirements, offers significant energy savings, and special function such as Visible Light Communication.

### Benefits

- Highly energy-efficient
- Conventional form factor to fit into existing luminaires
- Easy installation
- No mercury

### Features


- Reduced operational cost thanks to lower energy consumption
- Fastest and easiest way to upgrade existing luminaires to LED technology, completely safe product and installation process
- Lower maintenance cost thanks to 2-3 times longer lifetime than conventional lamps

### Application


- Hospitality, retail, office, industrial applications

# Specialty LED tube

## Dimensional drawing



Product	D1	D2	A1	A2	A3
Sensor LEDtube 1200mm 16W 840 T8	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
Sensor LEDtube 1200mm 16W 865 T8	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm



Product	D1	D2	A1	A2	A3
Ledtube SW DE HO 1200mm 20w 12000k T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
Ledtube SW DE HO 600mm 8w 12000k T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

### General Information

Cap-Base	G13
Switching Cycle	50,000

### Light Technical

Beam Angle (Nom)	240 degree(s)
LLMF At End Of Nominal Lifetime (Nom)	70 %

### Operating and Electrical

Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

### Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	T8

### General Information

Order Code	Full Product Name	Nominal lifetime
33322200	Ledtube SW DE HO 1200mm 20w 12000k T8	15,000 hour(s)
33324600	Ledtube SW DE HO 600mm 8w 12000k T8	15,000 hour(s)
94465900	Sensor LEDtube 1200mm 16W 840 T8	30,000 hour(s)
94467300	Sensor LEDtube 1200mm 16W 865 T8	30,000 hour(s)

## Light Technical

Order Code	Full Product Name	Correlated Color	Color	Color Code	Luminous Flux
		Temperature (Nom)	rendering index (CRI)		
33322200	Ledtube SW DE HO 1200mm 20w 12000k T8	12000 K	70	7120	2,200 lm
33324600	Ledtube SW DE HO 600mm 8w 12000k T8	12000 K	70	7120	880 lm

Order Code	Full Product Name	Correlated Color	Color	Color Code	Luminous Flux
		Temperature (Nom)	rendering index (CRI)		
94465900	Sensor LEDtube 1200mm 16W 840 T8	4000 K	80	840	1,800 lm



## Specialty LED tube

