



**Philips BN058 offers exceptional value. It is Perfect for your everyday lighting installations. It provides quality light and substantial energy and maintenance savings.**

### **Essential Smartbright T5 Batten**

BN058 Batten provide flexibility to customer to choose from 3 CCT and 4 different size and lumen packages, based on their specific need.

#### **Benefits**

- Slim and trunkable, integrated design
- Polycarbonate housing with one pc extrusion process
- Slim profile: Ideal for task lighting / cove lighting applications

# Essential Smartbright T5 Batten

## Features

- 15,000 hrs life, L70/B50
- 1 Year warranty
- 4 lengths, 3 colors Increased number of options for easy application
- CRI 70, SDCM < 7, 85lm/W
- Mounting accessories included

## Application

- Hospitality
- Offices
- Residential

## Versions



Essential Smartbright T5 Batten



Essential Smartbright T5 Batten



Essential Smartbright T5 Batten

# Essential Smartbright T5 Batten

Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>70
Luminous Efficacy (rated) (Nom)	85 lm/W
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Order Code	Full Product Name	Luminous Flux
911401709562	BN058C LED9/NW L900 GM	900 lm
911401709592	BN058C LED5/NW L600 GM	600 lm
911401709532	BN058C LED11/NW L1200 GM	1,200 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401709562	BN058C LED9/NW L900 GM	9.6 W
911401709592	BN058C LED5/NW L600 GM	6.5 W

Order Code	Full Product Name	Power Consumption
911401709532	BN058C LED11/NW L1200 GM	13 W

