



# Comfortable LED ceiling light that's easy on your eyes

## Apex Ceiling light

With its EyeComfort design, Apex provides comfortable high quality LED light for home and residential project. Its long lifetime and high lumen maintenance ensures bright light level over time. With various shapes, sizes, it enables to serve from bedroom to big living room, and dining to kitchen space. Installation becomes easier with easy connector and installation bracket.

### Benefits

- Ensure comfortable LED light all around home, residential application
- Hassle free easy installation saves time and effort
- Stay bright along the long life time

### Features

- high quality LED light with EyeComfort feature, safe from Blue light hazard risk
- Easy to install with easy connector and bracket
- various models and size to fit for all rooms in residential application
- long lifetime of 20,000 hours with high lumen maintenance
- uniform light distribution

### Application

- Residential, home: living room, bedroom, dining room, kitchen



# Apex Ceiling light

## Versions





Ceiling APEX L LED 45W

## Dimensional drawing






## Product

Apex SQ LED 55W 4000K



# Apex Ceiling light

## Dimensional drawing



### Product

Apex S LED 25W 4000K

### Product

Apex RT LED 40W 4000K

## Product details



Ceiling APEX RT LED 40W ON 1-DPP



Ceiling APEX L LED 45W ON 1-DPP



Ceiling APEX S LED 25W ON 2-DPP

# Apex Ceiling light

## Product details



Ceiling APEX S LED 25W ON 1-DPP



Ceiling APEX SQ LED 55W ON 1-DPP



Ceiling APEX RT LED 40W ON 2-DPP



Ceiling APEX L LED 45W ON 2-DPP



Ceiling APEX SQ LED 55W ON 2-DPP

### General Information

Light source replaceable No

### Light Technical

Color rendering index (CRI) 80

### Operating and Electrical

Protection class IEC Safety class I

Input Voltage 220 to 240 V

Line Frequency 50 or 60 Hz

### Controls and Dimming

Dimmable No

### Mechanical and Housing

Housing Color White

Ingress protection code IP20

### Approval and Application

Ambient temperature range -20 to +40 °C

Flammability mark For mounting on normally flammable surfaces

## Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
929002612381	Apex S LED 25W 4000K	4000 K	88.00 lm/W	2,200 lm
929002612481	Apex S LED 25W 5700K	5700 K	88.00 lm/W	2,200 lm
929002612581	Apex RT LED 40W 4000K	4000 K	85.00 lm/W	3,400 lm
929002612681	Apex RT LED 40W 5700K	5700 K	85.00 lm/W	3,400 lm
929002612881	Apex L LED 45W 5700K	5700 K	88.00 lm/W	4,000 lm
929002613181	Apex SQ LED 55W 4000K	4000 K	84.00 lm/W	4,200 lm
929002613281	Apex SQ LED 55W 5700K	5700 K	84.00 lm/W	4,200 lm

## Operating and Electrical

## Apex Ceiling light

Order Code	Full Product Name	Power Consumption
929002612381	Apex S LED 25W 4000K	25 W
929002612481	Apex S LED 25W 5700K	25 W
929002612581	Apex RT LED 40W 4000K	40 W
929002612681	Apex RT LED 40W 5700K	40 W

Order Code	Full Product Name	Power Consumption
929002612881	Apex L LED 45W 5700K	45 W
929002613181	Apex SQ LED 55W 4000K	55 W
929002613281	Apex SQ LED 55W 5700K	55 W

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
929002612381	Apex S LED 25W 4000K	(ANSI4000K, 0.3818, 0.3797) 6
929002612481	Apex S LED 25W 5700K	(0.3287, 0.3425) 6
929002612581	Apex RT LED 40W 4000K	(ANSI4000K, 0.3818, 0.3797) 6
929002612681	Apex RT LED 40W 5700K	(0.3287, 0.3425) 6

Order Code	Full Product Name	Initial chromaticity
929002612881	Apex L LED 45W 5700K	(0.3287, 0.3425) 6
929002613181	Apex SQ LED 55W 4000K	(ANSI4000K, 0.3818, 0.3797) 6
929002613281	Apex SQ LED 55W 5700K	(0.3287, 0.3425) 6

