



# Comfortable LED ceiling light that's easy on your eyes

## Apex Ceiling light

With its EyeComfort design, Apex provides comfortable high quality LED light for home and residential project. Its long lifetime and high lumen maintenance ensures bright light level over time. With various shapes, sizes, it enables to serve from bedroom to big living room, and dining to kitchen space. Installation becomes easier with easy connector and installation bracket.

### Benefits

- Ensure comfortable LED light all around home, residential application
- Hassle free easy installation saves time and effort
- Stay bright along the long life time

### Features

- high quality LED light with EyeComfort feature, safe from Blue light hazard risk
- Easy to install with easy connector and bracket
- various models and size to fit for all rooms in residential application
- long lifetime of 20,000 hours with high lumen maintenance
- uniform light distribution

### Application

- Residential, home: living room, bedroom, dining room, kitchen

# Apex Ceiling light

## Versions





Ceiling APEX RT LED 40W



Ceiling APEX L LED 45W

## Dimensional drawing



## Product details



Ceiling APEX RT LED 40W ON 1-DPP



Ceiling APEX L LED 45W ON 1-DPP



Ceiling APEX RT LED 40W ON 2-DPP



Ceiling APEX L LED 45W ON 2-DPP

# Apex Ceiling light

General Information	
Light source replaceable	No
Light Technical	
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
Flammability mark	For mounting on normally flammable surfaces
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.3287, 0.3425) 6

## Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
929002612681	Apex RT LED 40W 5700K	85.00 lm/W	3,400 lm
929002612881	Apex L LED 45W 5700K	88.00 lm/W	4,000 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
929002612681	Apex RT LED 40W 5700K	40 W	929002612881	Apex L LED 45W 5700K	45 W

