



Robust, connectable luminaire with outstanding performance.

Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in parking garages and warehouses. Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency, and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency,

energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

Applications

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

Versions

Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.
- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.



Pacific LED gen5, L1800



Pacific LED gen5, ATEX 2/22, Wieland connector



Pacific LED gen5, L1200



Pacific LED gen5, L1600


Pacific LED gen5, L700




Pacific LED gen5, Wieland connector




Dimensional drawing




WT492C 64S/840 PSD WB W5 L1200




PACIFIC LED PRO - 840 neutral white - Power supply unit with DALI interface - Wide beam - Plug-in connector 5-pole Wieland/Adels compatible




PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole




WT492C 80S/840 PSU WB W5 L1800




Pacific LED gen5 - 840 neutral white - Power supply unit with DALI interface - Wide beam - Push-in connector 5-pole




PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole

Product details

Pacific LED gen5, looping connection, 2 entry on one side



Pacific LED gen5 with push in 7-pole (PI7) connector






Pacific LED gen5, Wieland connector



Pacific LED gen5 with WAGO connector



Pacific LED gen5 connection through WAGO connector side view



Pacific LED gen5 with push in 5-pole (PI5) connector



Pacific LED gen5 with Wieland connector



Pacific LED gen5 connection through WAGO connector

General Information

Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
-----------------------------	-----

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Embedded control	InterAct SC100 sensor
------------------	-----------------------

Mechanical and Housing

Housing Color	White
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Explosion hazard class	Zone 2 and 22

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	No

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC plus mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
-------------------------	-------

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
10986500	WT490C 80S/840 PSU HE NB-HRO PI5L1800	8,000 lm	4000 K	165 lm/W	Narrow beam - High-rack optic
10987200	WT490C 80S/840 PSD HE NB-HRO PI5L1800	8,000 lm	4000 K	165 lm/W	Narrow beam - High-rack optic
10988900	WT490C 80S/840 PSU HE WB TW3 PI5L1800	8,000 lm	4000 K	165 lm/W	Wide beam
10989600	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	8,000 lm	4000 K	154 lm/W	Wide beam
10990200	WT490C 80S/840 PSD HE WB PI5 L1800	8,000 lm	4000 K	165 lm/W	Wide beam
10991900	WT490C 80S/840 PSD HE WB TW3 PI7L1800	8,000 lm	4000 K	165 lm/W	Wide beam
10992600	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	8,000 lm	4000 K	154 lm/W	Wide beam
10993300	WT490C 80S/840 PSU HE VWB PI5 L1800	8,000 lm	4000 K	165 lm/W	Very wide beam
10994000	WT490C 80S/840 PSD HE VWB PI5 L1800	8,000 lm	4000 K	165 lm/W	Very wide beam
10995700	WT490C 100S/840 PSD HE WB PI5 L1800	10,000 lm	4000 K	161 lm/W	Wide beam
10996400	WT490C 120S/840 PSD HE WB PI5 L1800	12,000 lm	4000 K	158 lm/W	Wide beam
62357600	WT490C 80S/840 PSU HE WB PI5 L1800	8,000 lm	4000 K	165 lm/W	Wide beam
62358300	WT490C 100S/840 PSU HE WB PI5 L1800	10,000 lm	4000 K	161 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
62359000	WT490C 120S/840 PSU HE WB PI5 L1800	12,000 lm	4000 K	158 lm/W	Wide beam
62578500	WT490C 80S/840 SIA HE WB IA9 PI5L1800	8,000 lm	4000 K	165 lm/W	Wide beam
62758100	WT490C 80S/840 PSU HE O PI5 L1800	7,600 lm	4000 K	157 lm/W	Opal
62759800	WT490C 80S/840 PSU HE PCO PI5 L1800	6,600 lm	4000 K	136 lm/W	Opal
62761100	WT495C 80S/840 PSU HE WB PI5 L1800	8,000 lm	4000 K	157 lm/W	Wide beam
62763500	WT495C 80S/840 PSD HE WB PI5 L1800	8,000 lm	4000 K	157 lm/W	Wide beam
77195600	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L180	8,000 lm	4000 K	165 lm/W	Wide beam
77196300	WT490C 80S/840 PSD HE WB TW3x2.5PI7 L180	8,000 lm	4000 K	165 lm/W	Wide beam
77395000	WT490C 150S/840 PSD HE WB PI5 L1800	15,000 lm	4000 K	155 lm/W	Very wide beam
77399800	WT490C 150S/840 PSU HE WB PI5 L1800	15,000 lm	4000 K	155 lm/W	Very wide beam
62764200	WT492C 64S/840 PSU WB W5 L1200	6,400 lm	4000 K	160 lm/W	Wide beam
62765900	WT492C 80S/840 PSU WB W5 L1800	8,000 lm	4000 K	165 lm/W	Wide beam
62766600	WT492C 64S/840 PSD WB W5 L1200	6,400 lm	4000 K	162 lm/W	Wide beam
62767300	WT492C 80S/840 PSD WB W5 L1800	8,000 lm	4000 K	165 lm/W	Wide beam
73290200	WT490C 42S/830 PSU HE WB PI5 L1200	4,200 lm	3000 K	157 lm/W	Wide beam
10959900	WT490C 42S/840 PSD HE WB PI5 L1200	4,200 lm	4000 K	162 lm/W	Wide beam
10960500	WT490C 64S/840 PSU HE NB-HRO PI5L1200	6,400 lm	4000 K	160 lm/W	Narrow beam - High-rack optic
10961200	WT490C 64S/840 PSD HE NB-HRO PI5L1200	6,400 lm	4000 K	162 lm/W	Narrow beam - High-rack optic
10962900	WT490C 64S/840 PSU HE WB TW1 PI5L1200	6,400 lm	4000 K	160 lm/W	Wide beam
10963600	WT490C 64S/840 PSU HE WB TW3 PI5L1200	6,400 lm	4000 K	160 lm/W	Wide beam
10964300	WT490C 64S/840 PSU HE WB TC5 L1200	6,400 lm	4000 K	160 lm/W	Wide beam
10965000	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	6,400 lm	4000 K	146 lm/W	Wide beam
10966700	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	6,400 lm	4000 K	146 lm/W	Wide beam
10967400	WT490C 64S/840 PSD HE WB PI5 L1200	6,400 lm	4000 K	162 lm/W	Wide beam
10968100	WT490C 64S/840 PSD HE WB TW1 PI5L1200	6,400 lm	4000 K	162 lm/W	Wide beam
10969800	WT490C 64S/840 PSD HE WB TW3 PI7L1200	6,400 lm	4000 K	162 lm/W	Wide beam
10970400	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	6,400 lm	4000 K	147 lm/W	Wide beam
10971100	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	6,400 lm	4000 K	147 lm/W	Wide beam
10972800	WT490C 64S/840 PSU HE VWB PI5 L1200	6,400 lm	4000 K	160 lm/W	Very wide beam
10973500	WT490C 64S/840 PSD HE VWB PI5 L1200	6,400 lm	4000 K	162 lm/W	Very wide beam
10974200	WT490C 80S/840 PSU HE NB-HRO PI5L1200	8,000 lm	4000 K	157 lm/W	Narrow beam - High-rack optic
10975900	WT490C 80S/840 PSD HE NB-HRO PI5L1200	8,000 lm	4000 K	157 lm/W	Narrow beam - High-rack optic
10976600	WT490C 80S/840 PSU HE WB TW1 PI5L1200	8,000 lm	4000 K	157 lm/W	Wide beam
10977300	WT490C 80S/840 PSU HE WB TW3 PI5L1200	8,000 lm	4000 K	157 lm/W	Wide beam
10978000	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	8,000 lm	4000 K	146 lm/W	Wide beam
10979700	WT490C 80S/840 PSD HE WB PI5 L1200	8,000 lm	4000 K	157 lm/W	Wide beam
10980300	WT490C 80S/840 PSD HE WB TW1 PI5L1200	8,000 lm	4000 K	157 lm/W	Wide beam
10981000	WT490C 80S/840 PSD HE WB TW3 PI7L1200	8,000 lm	4000 K	157 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
10982700	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	8,000 lm	4000 K	146 lm/W	Wide beam
10983400	WT490C 80S/840 PSU HE VWB PI5 L1200	8,000 lm	4000 K	157 lm/W	Very wide beam
10984100	WT490C 80S/840 PSD HE VWB PI5 L1200	8,000 lm	4000 K	157 lm/W	Very wide beam
10998800	WT490C 64S/840 PSU HE NB-HRO WA7L1200	6,400 lm	4000 K	160 lm/W	Narrow beam - High-rack optic
10999500	WT490C 64S/840 PSD HE NB-HRO WA7L1200	6,400 lm	4000 K	162 lm/W	Narrow beam - High-rack optic
62312500	WT490C 64S/840 PSU HE WB WA7 L1200	6,400 lm	4000 K	160 lm/W	Wide beam
62314900	WT490C 64S/840 PSU HE WB TW3 WA7L1200	6,400 lm	4000 K	160 lm/W	Wide beam
62316300	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	6,400 lm	4000 K	146 lm/W	Wide beam
62317000	WT490C 64S/840 PSD HE WB WA7 L1200	6,400 lm	4000 K	162 lm/W	Wide beam
62318700	WT490C 64S/840 PSD HE WB TW3 WA7L1200	6,400 lm	4000 K	162 lm/W	Wide beam
62319400	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	6,400 lm	4000 K	147 lm/W	Wide beam
62320000	WT490C 64S/840 PSU HE VWB WA7 L1200	6,400 lm	4000 K	160 lm/W	Very wide beam
62321700	WT490C 64S/840 PSD HE VWB WA7 L1200	6,400 lm	4000 K	162 lm/W	Very wide beam
62322400	WT490C 80S/840 PSU HE NB-HRO WA7L1200	8,000 lm	4000 K	157 lm/W	Narrow beam - High-rack optic
62323100	WT490C 80S/840 PSD HE NB-HRO WA7L1200	8,000 lm	4000 K	157 lm/W	Narrow beam - High-rack optic
62324800	WT490C 80S/840 PSU HE WB WA7 L1200	8,000 lm	4000 K	157 lm/W	Wide beam
62325500	WT490C 80S/840 PSU HE WB TW3 WA7L1200	8,000 lm	4000 K	157 lm/W	Wide beam
62326200	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	8,000 lm	4000 K	146 lm/W	Wide beam
62327900	WT490C 80S/840 PSD HE WB WA7 L1200	8,000 lm	4000 K	157 lm/W	Wide beam
62328600	WT490C 80S/840 PSD HE WB TW3 WA7L1200	8,000 lm	4000 K	157 lm/W	Wide beam
62329300	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	8,000 lm	4000 K	146 lm/W	Wide beam
62330900	WT490C 80S/840 PSU HE VWB WA7 L1200	8,000 lm	4000 K	157 lm/W	Very wide beam
62331600	WT490C 80S/840 PSD HE VWB WA7 L1200	8,000 lm	4000 K	157 lm/W	Very wide beam
62353800	WT490C 42S/840 PSU HE WB PI5 L1200	4,200 lm	4000 K	165 lm/W	Wide beam
62354500	WT490C 64S/840 PSU HE WB PI5 L1200	6,400 lm	4000 K	160 lm/W	Wide beam
62355200	WT490C 80S/840 PSU HE WB PI5 L1200	8,000 lm	4000 K	157 lm/W	Wide beam
62571600	WT490C 42S/840 PSD HE VWB PI5 L1200	4,200 lm	4000 K	162 lm/W	Very wide beam
62752900	WT490C 35S/840 PSU HE WB PI5 L1200	3,500 lm	4000 K	159 lm/W	Wide beam
62756700	WT490C 64S/840 PSU HE O PI5 L1200	6,200 lm	4000 K	155 lm/W	Opal
62757400	WT490C 64S/840 PSU HE PCO PI5 L1200	5,300 lm	4000 K	133 lm/W	Opal
62760400	WT495C 64S/840 PSU HE WB PI5 L1200	6,400 lm	4000 K	158 lm/W	Wide beam
62762800	WT495C 64S/840 PSD HE WB PI5 L1200	6,400 lm	4000 K	158 lm/W	Wide beam
77191800	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L120	6,400 lm	4000 K	160 lm/W	Wide beam
77193200	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L120	8,000 lm	4000 K	157 lm/W	Wide beam
77200700	WT490C 42S/840 PSU HE WB TW3x2.5PI5 L120	4,200 lm	4000 K	165 lm/W	Wide beam
77394300	WT490C 100S/840 PSD HE WB PI5 L1200	10,000 lm	4000 K	152 lm/W	Very wide beam
77398100	WT490C 100S/840 PSU HE WB PI5 L1200	10,000 lm	4000 K	154 lm/W	Very wide beam
62475700	WT490C 64S/840 PSD HE WB PI5 L1600	6,400 lm	4000 K	162 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
62476400	WT490C 64S/840 PSU HE WB TW3 PI5L1600	6,400 lm	4000 K	160 lm/W	Wide beam
62477100	WT490C 64S/840 PSU HE WB PI5 L1600	6,400 lm	4000 K	160 lm/W	Wide beam
62478800	WT490C 80S/840 PSU HE WB PI5 L1600	8,000 lm	4000 K	157 lm/W	Wide beam
62481800	WT490C 64S/840 PSD HE WB WA7 L1600	6,400 lm	4000 K	162 lm/W	Wide beam
62482500	WT490C 64S/840 PSU HE WB TW3 WA7L1600	6,400 lm	4000 K	160 lm/W	Wide beam
62483200	WT490C 64S/840 PSU HE WB WA7 L1600	6,400 lm	4000 K	160 lm/W	Wide beam
77197000	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L160	6,400 lm	4000 K	160 lm/W	Wide beam
77198700	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L160	8,000 lm	4000 K	157 lm/W	Wide beam
10958200	WT490C 23S/840 PSD HE WB PI5 L700	2,300 lm	4000 K	160 lm/W	Wide beam
62352100	WT490C 23S/840 PSU HE WB PI5 L700	2,300 lm	4000 K	151 lm/W	Wide beam
62315600	WT490C 64S/840 PSU HE WB TCW5 L1200	6,400 lm	4000 K	160 lm/W	Wide beam
62572300	WT490C 64S/840 PSU HE WB W5 L1200	6,400 lm	4000 K	160 lm/W	Wide beam
62573000	WT490C 80S/840 PSU HE WB W5 L1200	8,000 lm	4000 K	157 lm/W	Wide beam
62574700	WT490C 64S/840 PSD HE WB W5 L1200	6,400 lm	4000 K	162 lm/W	Wide beam
62575400	WT490C 80S/840 PSD HE WB W5 L1200	8,000 lm	4000 K	157 lm/W	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
10986500	WT490C 80S/840 PSU HE NB-HRO PI5L1800	48.5 W
10987200	WT490C 80S/840 PSD HE NB-HRO PI5L1800	48.5 W
10988900	WT490C 80S/840 PSU HE WB TW3 PI5L1800	48.5 W
10989600	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	52 W
10990200	WT490C 80S/840 PSD HE WB PI5 L1800	48.5 W
10991900	WT490C 80S/840 PSD HE WB TW3 PI7L1800	48.5 W
10992600	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	52 W
10993300	WT490C 80S/840 PSU HE VWB PI5 L1800	48.5 W
10994000	WT490C 80S/840 PSD HE VWB PI5 L1800	48.5 W
10995700	WT490C 100S/840 PSD HE WB PI5 L1800	62 W
10996400	WT490C 120S/840 PSD HE WB PI5 L1800	76 W
62357600	WT490C 80S/840 PSU HE WB PI5 L1800	48.5 W
62358300	WT490C 100S/840 PSU HE WB PI5 L1800	62 W
62359000	WT490C 120S/840 PSU HE WB PI5 L1800	76 W
62578500	WT490C 80S/840 SIA HE WB IA9 PI5L1800	48.5 W
62758100	WT490C 80S/840 PSU HE O PI5 L1800	51 W
62759800	WT490C 80S/840 PSU HE PCO PI5 L1800	48.5 W
62761100	WT495C 80S/840 PSU HE WB PI5 L1800	49 W
62763500	WT495C 80S/840 PSD HE WB PI5 L1800	48.5 W
77195600	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L180	48.5 W
77196300	WT490C 80S/840 PSD HE WB TW3x2.5PI7 L180	48.5 W
77395000	WT490C 150S/840 PSD HE WB PI5 L1800	97 W
77399800	WT490C 150S/840 PSU HE WB PI5 L1800	97 W

Order Code	Full Product Name	Power Consumption
62764200	WT492C 64S/840 PSU WB W5 L1200	40 W
62765900	WT492C 80S/840 PSU WB W5 L1800	49 W
62766600	WT492C 64S/840 PSD WB W5 L1200	39.5 W
62767300	WT492C 80S/840 PSD WB W5 L1800	48.5 W
73290200	WT490C 42S/830 PSU HE WB PI5 L1200	25.5 W
10959900	WT490C 42S/840 PSD HE WB PI5 L1200	26 W
10960500	WT490C 64S/840 PSU HE NB-HRO PI5L1200	40 W
10961200	WT490C 64S/840 PSD HE NB-HRO PI5L1200	39.5 W
10962900	WT490C 64S/840 PSU HE WB TW1 PI5L1200	40 W
10963600	WT490C 64S/840 PSU HE WB TW3 PI5L1200	40 W
10964300	WT490C 64S/840 PSU HE WB TC5 L1200	40 W
10965000	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	44 W
10966700	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	44 W
10967400	WT490C 64S/840 PSD HE WB PI5 L1200	39.5 W
10968100	WT490C 64S/840 PSD HE WB TW1 PI5L1200	39.5 W
10969800	WT490C 64S/840 PSD HE WB TW3 PI7L1200	39.5 W
10970400	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	43.5 W
10971100	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	43.5 W
10972800	WT490C 64S/840 PSU HE VWB PI5 L1200	40 W
10973500	WT490C 64S/840 PSD HE VWB PI5 L1200	39.5 W
10974200	WT490C 80S/840 PSU HE NB-HRO PI5L1200	51 W
10975900	WT490C 80S/840 PSD HE NB-HRO PI5L1200	51 W
10976600	WT490C 80S/840 PSU HE WB TW1 PI5L1200	51 W
10977300	WT490C 80S/840 PSU HE WB TW3 PI5L1200	51 W
10978000	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	55 W
10979700	WT490C 80S/840 PSD HE WB PI5 L1200	51 W
10980300	WT490C 80S/840 PSD HE WB TW1 PI5L1200	51 W
10981000	WT490C 80S/840 PSD HE WB TW3 PI7L1200	51 W
10982700	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	55 W
10983400	WT490C 80S/840 PSU HE VWB PI5 L1200	51 W
10984100	WT490C 80S/840 PSD HE VWB PI5 L1200	51 W
10998800	WT490C 64S/840 PSU HE NB-HRO WA7L1200	40 W
10999500	WT490C 64S/840 PSD HE NB-HRO WA7L1200	39.5 W
62312500	WT490C 64S/840 PSU HE WB WA7 L1200	40 W
62314900	WT490C 64S/840 PSU HE WB TW3 WA7L1200	40 W
62316300	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	44 W
62317000	WT490C 64S/840 PSD HE WB WA7 L1200	39.5 W
62318700	WT490C 64S/840 PSD HE WB TW3 WA7L1200	39.5 W
62319400	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	43.5 W
62320000	WT490C 64S/840 PSU HE VWB WA7 L1200	40 W
62321700	WT490C 64S/840 PSD HE VWB WA7 L1200	39.5 W
62322400	WT490C 80S/840 PSU HE NB-HRO WA7L1200	51 W

Order Code	Full Product Name	Power Consumption
62323100	WT490C 80S/840 PSD HE NB-HRO WA7L1200	51 W
62324800	WT490C 80S/840 PSU HE WB WA7 L1200	51 W
62325500	WT490C 80S/840 PSU HE WB TW3 WA7L1200	51 W
62326200	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	55 W
62327900	WT490C 80S/840 PSD HE WB WA7 L1200	51 W
62328600	WT490C 80S/840 PSD HE WB TW3 WA7L1200	51 W
62329300	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	55 W
62330900	WT490C 80S/840 PSU HE VWB WA7 L1200	51 W
62331600	WT490C 80S/840 PSD HE VWB WA7 L1200	51 W
62353800	WT490C 42S/840 PSU HE WB PI5 L1200	25.5 W
62354500	WT490C 64S/840 PSU HE WB PI5 L1200	40 W
62355200	WT490C 80S/840 PSU HE WB PI5 L1200	51 W
62571600	WT490C 42S/840 PSD HE VWB PI5 L1200	26 W
62752900	WT490C 35S/840 PSU HE WB PI5 L1200	22 W
62756700	WT490C 64S/840 PSU HE O PI5 L1200	40 W
62757400	WT490C 64S/840 PSU HE PCO PI5 L1200	40 W
62760400	WT495C 64S/840 PSU HE WB PI5 L1200	40.5 W
62762800	WT495C 64S/840 PSD HE WB PI5 L1200	40.5 W
77191800	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L120	40 W
77193200	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L120	51 W
77200700	WT490C 42S/840 PSU HE WB TW3x2.5PI5 L120	25.5 W
77394300	WT490C 100S/840 PSD HE WB PI5 L1200	66 W
77398100	WT490C 100S/840 PSU HE WB PI5 L1200	65 W
62475700	WT490C 64S/840 PSD HE WB PI5 L1600	39.5 W
62476400	WT490C 64S/840 PSU HE WB TW3 PI5L1600	40 W
62477100	WT490C 64S/840 PSU HE WB PI5 L1600	40 W
62478800	WT490C 80S/840 PSU HE WB PI5 L1600	51 W
62481800	WT490C 64S/840 PSD HE WB WA7 L1600	39.5 W
62482500	WT490C 64S/840 PSU HE WB TW3 WA7L1600	40 W
62483200	WT490C 64S/840 PSU HE WB WA7 L1600	40 W
77197000	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L160	40 W
77198700	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L160	51 W
10958200	WT490C 23S/840 PSD HE WB PI5 L700	14.4 W
62352100	WT490C 23S/840 PSU HE WB PI5 L700	15.2 W
62315600	WT490C 64S/840 PSU HE WB TCW5 L1200	40 W
62572300	WT490C 64S/840 PSU HE WB W5 L1200	40 W
62573000	WT490C 80S/840 PSU HE WB W5 L1200	51 W
62574700	WT490C 64S/840 PSD HE WB W5 L1200	39.5 W
62575400	WT490C 80S/840 PSD HE WB W5 L1200	51 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
10986500	WT490C 80S/840 PSU HE NB-HRO PI5L1800	No
10987200	WT490C 80S/840 PSD HE NB-HRO PI5L1800	Yes
10988900	WT490C 80S/840 PSU HE WB TW3 PI5L1800	No
10989600	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	No
10990200	WT490C 80S/840 PSD HE WB PI5 L1800	Yes
10991900	WT490C 80S/840 PSD HE WB TW3 PI7L1800	Yes
10992600	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	Yes
10993300	WT490C 80S/840 PSU HE VWB PI5 L1800	No
10994000	WT490C 80S/840 PSD HE VWB PI5 L1800	Yes
10995700	WT490C 100S/840 PSD HE WB PI5 L1800	Yes
10996400	WT490C 120S/840 PSD HE WB PI5 L1800	Yes
62357600	WT490C 80S/840 PSU HE WB PI5 L1800	No
62358300	WT490C 100S/840 PSU HE WB PI5 L1800	No
62359000	WT490C 120S/840 PSU HE WB PI5 L1800	No
62578500	WT490C 80S/840 SIA HE WB IA9 PI5L1800	Yes
62758100	WT490C 80S/840 PSU HE O PI5 L1800	No
62759800	WT490C 80S/840 PSU HE PCO PI5 L1800	No
62761100	WT495C 80S/840 PSU HE WB PI5 L1800	No
62763500	WT495C 80S/840 PSD HE WB PI5 L1800	Yes
77195600	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L180	No
77196300	WT490C 80S/840 PSD HE WB TW3x2.5PI7 L180	Yes
77395000	WT490C 150S/840 PSD HE WB PI5 L1800	Yes
77399800	WT490C 150S/840 PSU HE WB PI5 L1800	No
62764200	WT492C 64S/840 PSU WB W5 L1200	No
62765900	WT492C 80S/840 PSU WB W5 L1800	No
62766600	WT492C 64S/840 PSD WB W5 L1200	Yes
62767300	WT492C 80S/840 PSD WB W5 L1800	Yes
73290200	WT490C 42S/830 PSU HE WB PI5 L1200	No
10959900	WT490C 42S/840 PSD HE WB PI5 L1200	Yes
10960500	WT490C 64S/840 PSU HE NB-HRO PI5L1200	No
10961200	WT490C 64S/840 PSD HE NB-HRO PI5L1200	Yes
10962900	WT490C 64S/840 PSU HE WB TW1 PI5L1200	No
10963600	WT490C 64S/840 PSU HE WB TW3 PI5L1200	No
10964300	WT490C 64S/840 PSU HE WB TC5 L1200	No
10965000	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	No
10966700	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	No
10967400	WT490C 64S/840 PSD HE WB PI5 L1200	Yes
10968100	WT490C 64S/840 PSD HE WB TW1 PI5L1200	Yes
10969800	WT490C 64S/840 PSD HE WB TW3 PI7L1200	Yes
10970400	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	Yes
10971100	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	Yes

Order Code	Full Product Name	Dimmable
10972800	WT490C 64S/840 PSU HE VWB PI5 L1200	No
10973500	WT490C 64S/840 PSD HE VWB PI5 L1200	Yes
10974200	WT490C 80S/840 PSU HE NB-HRO PI5L1200	No
10975900	WT490C 80S/840 PSD HE NB-HRO PI5L1200	Yes
10976600	WT490C 80S/840 PSU HE WB TW1 PI5L1200	No
10977300	WT490C 80S/840 PSU HE WB TW3 PI5L1200	No
10978000	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	No
10979700	WT490C 80S/840 PSD HE WB PI5 L1200	Yes
10980300	WT490C 80S/840 PSD HE WB TW1 PI5L1200	Yes
10981000	WT490C 80S/840 PSD HE WB TW3 PI7L1200	Yes
10982700	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	Yes
10983400	WT490C 80S/840 PSU HE VWB PI5 L1200	No
10984100	WT490C 80S/840 PSD HE VWB PI5 L1200	Yes
10998800	WT490C 64S/840 PSU HE NB-HRO WA7L1200	No
10999500	WT490C 64S/840 PSD HE NB-HRO WA7L1200	Yes
62312500	WT490C 64S/840 PSU HE WB WA7 L1200	No
62314900	WT490C 64S/840 PSU HE WB TW3 WA7L1200	No
62316300	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	No
62317000	WT490C 64S/840 PSD HE WB WA7 L1200	Yes
62318700	WT490C 64S/840 PSD HE WB TW3 WA7L1200	Yes
62319400	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	Yes
62320000	WT490C 64S/840 PSU HE VWB WA7 L1200	No
62321700	WT490C 64S/840 PSD HE VWB WA7 L1200	Yes
62322400	WT490C 80S/840 PSU HE NB-HRO WA7L1200	No
62323100	WT490C 80S/840 PSD HE NB-HRO WA7L1200	Yes
62324800	WT490C 80S/840 PSU HE WB WA7 L1200	No
62325500	WT490C 80S/840 PSU HE WB TW3 WA7L1200	No
62326200	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	No
62327900	WT490C 80S/840 PSD HE WB WA7 L1200	Yes
62328600	WT490C 80S/840 PSD HE WB TW3 WA7L1200	Yes
62329300	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	Yes
62330900	WT490C 80S/840 PSU HE VWB WA7 L1200	No
62331600	WT490C 80S/840 PSD HE VWB WA7 L1200	Yes
62353800	WT490C 42S/840 PSU HE WB PI5 L1200	No
62354500	WT490C 64S/840 PSU HE WB PI5 L1200	No
62355200	WT490C 80S/840 PSU HE WB PI5 L1200	No
62571600	WT490C 42S/840 PSD HE VWB PI5 L1200	Yes
62752900	WT490C 35S/840 PSU HE WB PI5 L1200	No
62756700	WT490C 64S/840 PSU HE O PI5 L1200	No
62757400	WT490C 64S/840 PSU HE PCO PI5 L1200	No
62760400	WT495C 64S/840 PSU HE WB PI5 L1200	No
62762800	WT495C 64S/840 PSD HE WB PI5 L1200	Yes

Order Code	Full Product Name	Dimmable
77191800	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L120	No
77193200	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L120	No
77200700	WT490C 42S/840 PSU HE WB TW3x2.5PI5 L120	No
77394300	WT490C 100S/840 PSD HE WB PI5 L1200	Yes
77398100	WT490C 100S/840 PSU HE WB PI5 L1200	No
62475700	WT490C 64S/840 PSD HE WB PI5 L1600	Yes
62476400	WT490C 64S/840 PSU HE WB TW3 PI5L1600	No
62477100	WT490C 64S/840 PSU HE WB PI5 L1600	No
62478800	WT490C 80S/840 PSU HE WB PI5 L1600	No
62481800	WT490C 64S/840 PSD HE WB WA7 L1600	Yes
62482500	WT490C 64S/840 PSU HE WB TW3 WA7L1600	No
62483200	WT490C 64S/840 PSU HE WB WA7 L1600	No
77197000	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L160	No
77198700	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L160	No
10958200	WT490C 23S/840 PSD HE WB PI5 L700	Yes
62352100	WT490C 23S/840 PSU HE WB PI5 L700	No
62315600	WT490C 64S/840 PSU HE WB TCW5 L1200	No
62572300	WT490C 64S/840 PSU HE WB W5 L1200	No
62573000	WT490C 80S/840 PSU HE WB W5 L1200	No
62574700	WT490C 64S/840 PSD HE WB W5 L1200	Yes
62575400	WT490C 80S/840 PSD HE WB W5 L1200	Yes

Emergency Operation

Order Code	Full Product Name	Emergency lighting
10986500	WT490C 80S/840 PSU HE NB-HRO PI5L1800	-
10987200	WT490C 80S/840 PSD HE NB-HRO PI5L1800	-
10988900	WT490C 80S/840 PSU HE WB TW3 PI5L1800	-
10989600	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	Emergency lighting 3 hours duration Pro version
10990200	WT490C 80S/840 PSD HE WB PI5 L1800	-
10991900	WT490C 80S/840 PSD HE WB TW3 PI7L1800	-
10992600	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	Emergency lighting 3 hours duration with DALI interface
10993300	WT490C 80S/840 PSU HE VWB PI5 L1800	-
10994000	WT490C 80S/840 PSD HE VWB PI5 L1800	-
10995700	WT490C 100S/840 PSD HE WB PI5 L1800	-
10996400	WT490C 120S/840 PSD HE WB PI5 L1800	-
62357600	WT490C 80S/840 PSU HE WB PI5 L1800	-
62358300	WT490C 100S/840 PSU HE WB PI5 L1800	-
62359000	WT490C 120S/840 PSU HE WB PI5 L1800	-
62578500	WT490C 80S/840 SIA HE WB IA9 PI5L1800	-
62758100	WT490C 80S/840 PSU HE O PI5 L1800	-
62759800	WT490C 80S/840 PSU HE PCO PI5 L1800	-

Order Code	Full Product Name	Emergency lighting
62761100	WT495C 80S/840 PSU HE WB PI5 L1800	-
62763500	WT495C 80S/840 PSD HE WB PI5 L1800	-
77195600	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L180	-
77196300	WT490C 80S/840 PSD HE WB TW3x2.5PI7 L180	-
77395000	WT490C 150S/840 PSD HE WB PI5 L1800	-
77399800	WT490C 150S/840 PSU HE WB PI5 L1800	-
62764200	WT492C 64S/840 PSU WB W5 L1200	-
62765900	WT492C 80S/840 PSU WB W5 L1800	-
62766600	WT492C 64S/840 PSD WB W5 L1200	-
62767300	WT492C 80S/840 PSD WB W5 L1800	-
73290200	WT490C 42S/830 PSU HE WB PI5 L1200	-
10959900	WT490C 42S/840 PSD HE WB PI5 L1200	-
10960500	WT490C 64S/840 PSU HE NB-HRO PI5L1200	-
10961200	WT490C 64S/840 PSD HE NB-HRO PI5L1200	-
10962900	WT490C 64S/840 PSU HE WB TW1 PI5L1200	-
10963600	WT490C 64S/840 PSU HE WB TW3 PI5L1200	-
10964300	WT490C 64S/840 PSU HE WB TC5 L1200	-
10965000	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version
10966700	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	Emergency lighting 3 hours duration Pro version
10967400	WT490C 64S/840 PSD HE WB PI5 L1200	-
10968100	WT490C 64S/840 PSD HE WB TW1 PI5L1200	-
10969800	WT490C 64S/840 PSD HE WB TW3 PI7L1200	-
10970400	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	Emergency lighting 3 hours duration with DALI interface
10971100	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	Emergency lighting 3 hours duration with DALI interface
10972800	WT490C 64S/840 PSU HE VWB PI5 L1200	-
10973500	WT490C 64S/840 PSD HE VWB PI5 L1200	-
10974200	WT490C 80S/840 PSU HE NB-HRO PI5L1200	-
10975900	WT490C 80S/840 PSD HE NB-HRO PI5L1200	-
10976600	WT490C 80S/840 PSU HE WB TW1 PI5L1200	-
10977300	WT490C 80S/840 PSU HE WB TW3 PI5L1200	-
10978000	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version
10979700	WT490C 80S/840 PSD HE WB PI5 L1200	-
10980300	WT490C 80S/840 PSD HE WB TW1 PI5L1200	-
10981000	WT490C 80S/840 PSD HE WB TW3 PI7L1200	-
10982700	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	Emergency lighting 3 hours duration with DALI interface
10983400	WT490C 80S/840 PSU HE VWB PI5 L1200	-
10984100	WT490C 80S/840 PSD HE VWB PI5 L1200	-
10998800	WT490C 64S/840 PSU HE NB-HRO WA7L1200	-
10999500	WT490C 64S/840 PSD HE NB-HRO WA7L1200	-
62312500	WT490C 64S/840 PSU HE WB WA7 L1200	-
62314900	WT490C 64S/840 PSU HE WB TW3 WA7L1200	-
62316300	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version

Order Code	Full Product Name	Emergency lighting
62317000	WT490C 64S/840 PSD HE WB WA7 L1200	-
62318700	WT490C 64S/840 PSD HE WB TW3 WA7L1200	-
62319400	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	Emergency lighting 3 hours duration with DALI interface
62320000	WT490C 64S/840 PSU HE VWB WA7 L1200	-
62321700	WT490C 64S/840 PSD HE VWB WA7 L1200	-
62322400	WT490C 80S/840 PSU HE NB-HRO WA7L1200	-
62323100	WT490C 80S/840 PSD HE NB-HRO WA7L1200	-
62324800	WT490C 80S/840 PSU HE WB WA7 L1200	-
62325500	WT490C 80S/840 PSU HE WB TW3 WA7L1200	-
62326200	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version
62327900	WT490C 80S/840 PSD HE WB WA7 L1200	-
62328600	WT490C 80S/840 PSD HE WB TW3 WA7L1200	-
62329300	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	Emergency lighting 3 hours duration with DALI interface
62330900	WT490C 80S/840 PSU HE VWB WA7 L1200	-
62331600	WT490C 80S/840 PSD HE VWB WA7 L1200	-
62353800	WT490C 42S/840 PSU HE WB PI5 L1200	-
62354500	WT490C 64S/840 PSU HE WB PI5 L1200	-
62355200	WT490C 80S/840 PSU HE WB PI5 L1200	-
62571600	WT490C 42S/840 PSD HE VWB PI5 L1200	-
62752900	WT490C 35S/840 PSU HE WB PI5 L1200	-
62756700	WT490C 64S/840 PSU HE O PI5 L1200	-
62757400	WT490C 64S/840 PSU HE PCO PI5 L1200	-
62760400	WT495C 64S/840 PSU HE WB PI5 L1200	-
62762800	WT495C 64S/840 PSD HE WB PI5 L1200	-
77191800	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L120	-
77193200	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L120	-
77200700	WT490C 42S/840 PSU HE WB TW3x2.5PI5 L120	-
77394300	WT490C 100S/840 PSD HE WB PI5 L1200	-
77398100	WT490C 100S/840 PSU HE WB PI5 L1200	-
62475700	WT490C 64S/840 PSD HE WB PI5 L1600	-
62476400	WT490C 64S/840 PSU HE WB TW3 PI5L1600	-
62477100	WT490C 64S/840 PSU HE WB PI5 L1600	-
62478800	WT490C 80S/840 PSU HE WB PI5 L1600	-
62481800	WT490C 64S/840 PSD HE WB WA7 L1600	-
62482500	WT490C 64S/840 PSU HE WB TW3 WA7L1600	-
62483200	WT490C 64S/840 PSU HE WB WA7 L1600	-
77197000	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L160	-
77198700	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L160	-
10958200	WT490C 23S/840 PSD HE WB PI5 L700	-
62352100	WT490C 23S/840 PSU HE WB PI5 L700	-
62315600	WT490C 64S/840 PSU HE WB TCW5 L1200	-
62572300	WT490C 64S/840 PSU HE WB W5 L1200	-

Order Code	Full Product Name	Emergency lighting
62573000	WT490C 80S/840 PSU HE WB W5 L1200	-
62574700	WT490C 64S/840 PSD HE WB W5 L1200	-
62575400	WT490C 80S/840 PSD HE WB W5 L1200	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range
10986500	WT490C 80S/840 PSU HE NB-HRO PI5L1800	-25 to +45 °C
10987200	WT490C 80S/840 PSD HE NB-HRO PI5L1800	-25 to +45 °C
10988900	WT490C 80S/840 PSU HE WB TW3 PI5L1800	-25 to +45 °C
10989600	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	0 to +30 °C
10990200	WT490C 80S/840 PSD HE WB PI5 L1800	-25 to +45 °C
10991900	WT490C 80S/840 PSD HE WB TW3 PI7L1800	-25 to +45 °C
10992600	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	0 to +30 °C
10993300	WT490C 80S/840 PSU HE VWB PI5 L1800	-25 to +45 °C
10994000	WT490C 80S/840 PSD HE VWB PI5 L1800	-25 to +45 °C
10995700	WT490C 100S/840 PSD HE WB PI5 L1800	-25 to +45 °C
10996400	WT490C 120S/840 PSD HE WB PI5 L1800	-25 to +45 °C
62357600	WT490C 80S/840 PSU HE WB PI5 L1800	-25 to +45 °C
62358300	WT490C 100S/840 PSU HE WB PI5 L1800	-25 to +45 °C
62359000	WT490C 120S/840 PSU HE WB PI5 L1800	-25 to +45 °C
62578500	WT490C 80S/840 SIA HE WB IA9 PI5L1800	-25 to +45 °C
62758100	WT490C 80S/840 PSU HE O PI5 L1800	-25 to +45 °C
62759800	WT490C 80S/840 PSU HE PCO PI5 L1800	-25 to +45 °C
62761100	WT495C 80S/840 PSU HE WB PI5 L1800	-35 to +60 °C
62763500	WT495C 80S/840 PSD HE WB PI5 L1800	-35 to +60 °C
77195600	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L180	-25 to +45 °C
77196300	WT490C 80S/840 PSD HE WB TW3x2.5PI7 L180	-25 to +45 °C
77395000	WT490C 150S/840 PSD HE WB PI5 L1800	-25 to +25 °C
77399800	WT490C 150S/840 PSU HE WB PI5 L1800	-25 to +25 °C
62764200	WT492C 64S/840 PSU WB W5 L1200	-25 to +45 °C
62765900	WT492C 80S/840 PSU WB W5 L1800	-25 to +45 °C
62766600	WT492C 64S/840 PSD WB W5 L1200	-25 to +45 °C
62767300	WT492C 80S/840 PSD WB W5 L1800	-25 to +45 °C
73290200	WT490C 42S/830 PSU HE WB PI5 L1200	-25 to +45 °C
10959900	WT490C 42S/840 PSD HE WB PI5 L1200	-25 to +45 °C
10960500	WT490C 64S/840 PSU HE NB-HRO PI5L1200	-25 to +45 °C
10961200	WT490C 64S/840 PSD HE NB-HRO PI5L1200	-25 to +45 °C
10962900	WT490C 64S/840 PSU HE WB TW1 PI5L1200	-25 to +45 °C
10963600	WT490C 64S/840 PSU HE WB TW3 PI5L1200	-25 to +45 °C
10964300	WT490C 64S/840 PSU HE WB TC5 L1200	-25 to +45 °C
10965000	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	0 to +40 °C

Order Code	Full Product Name	Ambient temperature range
10966700	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	0 to +40 °C
10967400	WT490C 64S/840 PSD HE WB PI5 L1200	-25 to +45 °C
10968100	WT490C 64S/840 PSD HE WB TW1 PI5L1200	-25 to +45 °C
10969800	WT490C 64S/840 PSD HE WB TW3 PI7L1200	-25 to +45 °C
10970400	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	0 to +40 °C
10971100	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	0 to +40 °C
10972800	WT490C 64S/840 PSU HE VWB PI5 L1200	-25 to +45 °C
10973500	WT490C 64S/840 PSD HE VWB PI5 L1200	-25 to +45 °C
10974200	WT490C 80S/840 PSU HE NB-HRO PI5L1200	-25 to +45 °C
10975900	WT490C 80S/840 PSD HE NB-HRO PI5L1200	-25 to +45 °C
10976600	WT490C 80S/840 PSU HE WB TW1 PI5L1200	-25 to +45 °C
10977300	WT490C 80S/840 PSU HE WB TW3 PI5L1200	-25 to +45 °C
10978000	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	0 to +30 °C
10979700	WT490C 80S/840 PSD HE WB PI5 L1200	-25 to +45 °C
10980300	WT490C 80S/840 PSD HE WB TW1 PI5L1200	-25 to +45 °C
10981000	WT490C 80S/840 PSD HE WB TW3 PI7L1200	-25 to +45 °C
10982700	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	0 to +30 °C
10983400	WT490C 80S/840 PSU HE VWB PI5 L1200	-25 to +45 °C
10984100	WT490C 80S/840 PSD HE VWB PI5 L1200	-25 to +45 °C
10998800	WT490C 64S/840 PSU HE NB-HRO WA7L1200	-25 to +45 °C
10999500	WT490C 64S/840 PSD HE NB-HRO WA7L1200	-25 to +45 °C
62312500	WT490C 64S/840 PSU HE WB WA7 L1200	-25 to +45 °C
62314900	WT490C 64S/840 PSU HE WB TW3 WA7L1200	-25 to +45 °C
62316300	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	0 to +40 °C
62317000	WT490C 64S/840 PSD HE WB WA7 L1200	-25 to +45 °C
62318700	WT490C 64S/840 PSD HE WB TW3 WA7L1200	-25 to +45 °C
62319400	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	0 to +40 °C
62320000	WT490C 64S/840 PSU HE VWB WA7 L1200	-25 to +45 °C
62321700	WT490C 64S/840 PSD HE VWB WA7 L1200	-25 to +45 °C
62322400	WT490C 80S/840 PSU HE NB-HRO WA7L1200	-25 to +45 °C
62323100	WT490C 80S/840 PSD HE NB-HRO WA7L1200	-25 to +45 °C
62324800	WT490C 80S/840 PSU HE WB WA7 L1200	-25 to +45 °C
62325500	WT490C 80S/840 PSU HE WB TW3 WA7L1200	-25 to +45 °C
62326200	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	0 to +30 °C
62327900	WT490C 80S/840 PSD HE WB WA7 L1200	-25 to +45 °C
62328600	WT490C 80S/840 PSD HE WB TW3 WA7L1200	-25 to +45 °C
62329300	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	0 to +30 °C
62330900	WT490C 80S/840 PSU HE VWB WA7 L1200	-25 to +45 °C
62331600	WT490C 80S/840 PSD HE VWB WA7 L1200	-25 to +45 °C
62353800	WT490C 42S/840 PSU HE WB PI5 L1200	-25 to +45 °C
62354500	WT490C 64S/840 PSU HE WB PI5 L1200	-25 to +45 °C
62355200	WT490C 80S/840 PSU HE WB PI5 L1200	-25 to +45 °C

Order Code	Full Product Name	Ambient temperature range
62571600	WT490C 42S/840 PSD HE VWB PI5 L1200	-25 to +45 °C
62752900	WT490C 35S/840 PSU HE WB PI5 L1200	-25 to +45 °C
62756700	WT490C 64S/840 PSU HE O PI5 L1200	-25 to +45 °C
62757400	WT490C 64S/840 PSU HE PCO PI5 L1200	-25 to +45 °C
62760400	WT495C 64S/840 PSU HE WB PI5 L1200	-35 to +60 °C
62762800	WT495C 64S/840 PSD HE WB PI5 L1200	-35 to +60 °C
77191800	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L120	-25 to +45 °C
77193200	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L120	-25 to +45 °C
77200700	WT490C 42S/840 PSU HE WB TW3x2.5PI5 L120	-25 to +45 °C
77394300	WT490C 100S/840 PSD HE WB PI5 L1200	-25 to +25 °C
77398100	WT490C 100S/840 PSU HE WB PI5 L1200	-25 to +25 °C
62475700	WT490C 64S/840 PSD HE WB PI5 L1600	-25 to +45 °C
62476400	WT490C 64S/840 PSU HE WB TW3 PI5L1600	-25 to +45 °C
62477100	WT490C 64S/840 PSU HE WB PI5 L1600	-25 to +45 °C
62478800	WT490C 80S/840 PSU HE WB PI5 L1600	-25 to +45 °C
62481800	WT490C 64S/840 PSD HE WB WA7 L1600	-25 to +45 °C
62482500	WT490C 64S/840 PSU HE WB TW3 WA7L1600	-25 to +45 °C
62483200	WT490C 64S/840 PSU HE WB WA7 L1600	-25 to +45 °C
77197000	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L160	-25 to +45 °C
77198700	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L160	-25 to +45 °C
10958200	WT490C 23S/840 PSD HE WB PI5 L700	-25 to +45 °C
62352100	WT490C 23S/840 PSU HE WB PI5 L700	-25 to +45 °C
62315600	WT490C 64S/840 PSU HE WB TCW5 L1200	-25 to +45 °C
62572300	WT490C 64S/840 PSU HE WB W5 L1200	-25 to +45 °C
62573000	WT490C 80S/840 PSU HE WB W5 L1200	-25 to +45 °C
62574700	WT490C 64S/840 PSD HE WB W5 L1200	-25 to +45 °C
62575400	WT490C 80S/840 PSD HE WB W5 L1200	-25 to +45 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
10986500	WT490C 80S/840 PSU HE NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
10987200	WT490C 80S/840 PSD HE NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
10988900	WT490C 80S/840 PSU HE WB TW3 PI5L1800	(0.38, 0.38) SDCM <3
10989600	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	(0.38, 0.38) SDCM <3
10990200	WT490C 80S/840 PSD HE WB PI5 L1800	(0.38, 0.38) SDCM <3
10991900	WT490C 80S/840 PSD HE WB TW3 PI7L1800	(0.38, 0.38) SDCM <3
10992600	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	(0.38, 0.38) SDCM <3
10993300	WT490C 80S/840 PSU HE VWB PI5 L1800	(0.38, 0.38) SDCM <3
10994000	WT490C 80S/840 PSD HE VWB PI5 L1800	(0.38, 0.38) SDCM <3
10995700	WT490C 100S/840 PSD HE WB PI5 L1800	(0.38, 0.38) SDCM <3
10996400	WT490C 120S/840 PSD HE WB PI5 L1800	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
62357600	WT490C 80S/840 PSU HE WB PI5 L1800	(0.38, 0.38) SDCM <3
62358300	WT490C 100S/840 PSU HE WB PI5 L1800	(0.38, 0.38) SDCM <3
62359000	WT490C 120S/840 PSU HE WB PI5 L1800	(0.38, 0.38) SDCM <3
62578500	WT490C 80S/840 SIA HE WB IA9 PI5L1800	(0.38, 0.38) SDCM <3
62758100	WT490C 80S/840 PSU HE O PI5 L1800	(0.38, 0.38) SDCM <3
62759800	WT490C 80S/840 PSU HE PCO PI5 L1800	(0.38, 0.38) SDCM <3
62761100	WT495C 80S/840 PSU HE WB PI5 L1800	(0.38, 0.38) SDCM <3
62763500	WT495C 80S/840 PSD HE WB PI5 L1800	(0.38, 0.38) SDCM <3
77195600	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L180	(0.38, 0.38) SDCM <3
77196300	WT490C 80S/840 PSD HE WB TW3x2.5PI7 L180	(0.38, 0.38) SDCM <3
77395000	WT490C 150S/840 PSD HE WB PI5 L1800	(0.38, 0.38) SDCM <3
77399800	WT490C 150S/840 PSU HE WB PI5 L1800	(0.38, 0.38) SDCM <3
62764200	WT492C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
62765900	WT492C 80S/840 PSU WB W5 L1800	(0.38, 0.38) SDCM <3
62766600	WT492C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
62767300	WT492C 80S/840 PSD WB W5 L1800	(0.38, 0.38) SDCM <3
73290200	WT490C 42S/830 PSU HE WB PI5 L1200	(0.43, 0.40) SDCM <3
10959900	WT490C 42S/840 PSD HE WB PI5 L1200	(0.38, 0.38) SDCM <3
10960500	WT490C 64S/840 PSU HE NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10961200	WT490C 64S/840 PSD HE NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10962900	WT490C 64S/840 PSU HE WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10963600	WT490C 64S/840 PSU HE WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
10964300	WT490C 64S/840 PSU HE WB TC5 L1200	(0.38, 0.38) SDCM <3
10965000	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
10966700	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	(0.38, 0.38) SDCM <3
10967400	WT490C 64S/840 PSD HE WB PI5 L1200	(0.38, 0.38) SDCM <3
10968100	WT490C 64S/840 PSD HE WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10969800	WT490C 64S/840 PSD HE WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
10970400	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
10971100	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	(0.38, 0.38) SDCM <3
10972800	WT490C 64S/840 PSU HE VWB PI5 L1200	(0.38, 0.38) SDCM <3
10973500	WT490C 64S/840 PSD HE VWB PI5 L1200	(0.38, 0.38) SDCM <3
10974200	WT490C 80S/840 PSU HE NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10975900	WT490C 80S/840 PSD HE NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10976600	WT490C 80S/840 PSU HE WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10977300	WT490C 80S/840 PSU HE WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
10978000	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
10979700	WT490C 80S/840 PSD HE WB PI5 L1200	(0.38, 0.38) SDCM <3
10980300	WT490C 80S/840 PSD HE WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10981000	WT490C 80S/840 PSD HE WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
10982700	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
10983400	WT490C 80S/840 PSU HE VWB PI5 L1200	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
10984100	WT490C 80S/840 PSD HE VWB PI5 L1200	(0.38, 0.38) SDCM <3
10998800	WT490C 64S/840 PSU HE NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
10999500	WT490C 64S/840 PSD HE NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62312500	WT490C 64S/840 PSU HE WB WA7 L1200	(0.38, 0.38) SDCM <3
62314900	WT490C 64S/840 PSU HE WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62316300	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
62317000	WT490C 64S/840 PSD HE WB WA7 L1200	(0.38, 0.38) SDCM <3
62318700	WT490C 64S/840 PSD HE WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62319400	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
62320000	WT490C 64S/840 PSU HE VWB WA7 L1200	(0.38, 0.38) SDCM <3
62321700	WT490C 64S/840 PSD HE VWB WA7 L1200	(0.38, 0.38) SDCM <3
62322400	WT490C 80S/840 PSU HE NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62323100	WT490C 80S/840 PSD HE NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62324800	WT490C 80S/840 PSU HE WB WA7 L1200	(0.38, 0.38) SDCM <3
62325500	WT490C 80S/840 PSU HE WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62326200	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
62327900	WT490C 80S/840 PSD HE WB WA7 L1200	(0.38, 0.38) SDCM <3
62328600	WT490C 80S/840 PSD HE WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62329300	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
62330900	WT490C 80S/840 PSU HE VWB WA7 L1200	(0.38, 0.38) SDCM <3
62331600	WT490C 80S/840 PSD HE VWB WA7 L1200	(0.38, 0.38) SDCM <3
62353800	WT490C 42S/840 PSU HE WB PI5 L1200	(0.38, 0.38) SDCM <3
62354500	WT490C 64S/840 PSU HE WB PI5 L1200	(0.38, 0.38) SDCM <3
62355200	WT490C 80S/840 PSU HE WB PI5 L1200	(0.38, 0.38) SDCM <3
62571600	WT490C 42S/840 PSD HE VWB PI5 L1200	(0.38, 0.38) SDCM <3
62752900	WT490C 35S/840 PSU HE WB PI5 L1200	(0.38, 0.38) SDCM <3
62756700	WT490C 64S/840 PSU HE O PI5 L1200	(0.38, 0.38) SDCM <3
62757400	WT490C 64S/840 PSU HE PCO PI5 L1200	(0.38, 0.38) SDCM <3
62760400	WT495C 64S/840 PSU HE WB PI5 L1200	(0.38, 0.38) SDCM <3
62762800	WT495C 64S/840 PSD HE WB PI5 L1200	(0.38, 0.38) SDCM <3
77191800	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L120	(0.38, 0.38) SDCM <3
77193200	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L120	(0.38, 0.38) SDCM <3
77200700	WT490C 42S/840 PSU HE WB TW3x2.5PI5 L120	(0.38, 0.38) SDCM <3
77394300	WT490C 100S/840 PSD HE WB PI5 L1200	(0.38, 0.38) SDCM <3
77398100	WT490C 100S/840 PSU HE WB PI5 L1200	(0.38, 0.38) SDCM <3
62475700	WT490C 64S/840 PSD HE WB PI5 L1600	(0.38, 0.38) SDCM <3
62476400	WT490C 64S/840 PSU HE WB TW3 PI5L1600	(0.38, 0.38) SDCM <3
62477100	WT490C 64S/840 PSU HE WB PI5 L1600	(0.38, 0.38) SDCM <3
62478800	WT490C 80S/840 PSU HE WB PI5 L1600	(0.38, 0.38) SDCM <3
62481800	WT490C 64S/840 PSD HE WB WA7 L1600	(0.38, 0.38) SDCM <3
62482500	WT490C 64S/840 PSU HE WB TW3 WA7L1600	(0.38, 0.38) SDCM <3
62483200	WT490C 64S/840 PSU HE WB WA7 L1600	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
77197000	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L160	(0.38, 0.38) SDCM <3
77198700	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L160	(0.38, 0.38) SDCM <3
10958200	WT490C 23S/840 PSD HE WB PI5 L700	(0.38, 0.38) SDCM <3
62352100	WT490C 23S/840 PSU HE WB PI5 L700	(0.38, 0.38) SDCM <3
62315600	WT490C 64S/840 PSU HE WB TCW5 L1200	(0.38, 0.38) SDCM <3
62572300	WT490C 64S/840 PSU HE WB W5 L1200	(0.38, 0.38) SDCM <3
62573000	WT490C 80S/840 PSU HE WB W5 L1200	(0.38, 0.38) SDCM <3
62574700	WT490C 64S/840 PSD HE WB W5 L1200	(0.38, 0.38) SDCM <3
62575400	WT490C 80S/840 PSD HE WB W5 L1200	(0.38, 0.38) SDCM <3


Product Data

Order Code	Full Product Name	Product family code
10986500	WT490C 80S/840 PSU HE NB-HRO PI5L1800	WT490C
10987200	WT490C 80S/840 PSD HE NB-HRO PI5L1800	WT490C
10988900	WT490C 80S/840 PSU HE WB TW3 PI5L1800	WT490C
10989600	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	WT490C
10990200	WT490C 80S/840 PSD HE WB PI5 L1800	WT490C
10991900	WT490C 80S/840 PSD HE WB TW3 PI7L1800	WT490C
10992600	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	WT490C
10993300	WT490C 80S/840 PSU HE VWB PI5 L1800	WT490C
10994000	WT490C 80S/840 PSD HE VWB PI5 L1800	WT490C
10995700	WT490C 100S/840 PSD HE WB PI5 L1800	WT490C
10996400	WT490C 120S/840 PSD HE WB PI5 L1800	WT490C
62357600	WT490C 80S/840 PSU HE WB PI5 L1800	WT490C
62358300	WT490C 100S/840 PSU HE WB PI5 L1800	WT490C
62359000	WT490C 120S/840 PSU HE WB PI5 L1800	WT490C
62578500	WT490C 80S/840 SIA HE WB IA9 PI5L1800	WT490C
62758100	WT490C 80S/840 PSU HE O PI5 L1800	WT490C
62759800	WT490C 80S/840 PSU HE PCO PI5 L1800	WT490C
62761100	WT495C 80S/840 PSU HE WB PI5 L1800	WT495C
62763500	WT495C 80S/840 PSD HE WB PI5 L1800	WT495C
77195600	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L180	WT490C
77196300	WT490C 80S/840 PSD HE WB TW3x2.5PI7 L180	WT490C
77395000	WT490C 150S/840 PSD HE WB PI5 L1800	WT490C
77399800	WT490C 150S/840 PSU HE WB PI5 L1800	WT490C
62764200	WT492C 64S/840 PSU WB W5 L1200	WT492C
62765900	WT492C 80S/840 PSU WB W5 L1800	WT492C
62766600	WT492C 64S/840 PSD WB W5 L1200	WT492C
62767300	WT492C 80S/840 PSD WB W5 L1800	WT492C
73290200	WT490C 42S/830 PSU HE WB PI5 L1200	WT490C
10959900	WT490C 42S/840 PSD HE WB PI5 L1200	WT490C


Order Code	Full Product Name	Product family code
10960500	WT490C 64S/840 PSU HE NB-HRO PI5L1200	WT490C
10961200	WT490C 64S/840 PSD HE NB-HRO PI5L1200	WT490C
10962900	WT490C 64S/840 PSU HE WB TW1 PI5L1200	WT490C
10963600	WT490C 64S/840 PSU HE WB TW3 PI5L1200	WT490C
10964300	WT490C 64S/840 PSU HE WB TC5 L1200	WT490C
10965000	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	WT490C
10966700	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	WT490C
10967400	WT490C 64S/840 PSD HE WB PI5 L1200	WT490C
10968100	WT490C 64S/840 PSD HE WB TW1 PI5L1200	WT490C
10969800	WT490C 64S/840 PSD HE WB TW3 PI7L1200	WT490C
10970400	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	WT490C
10971100	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	WT490C
10972800	WT490C 64S/840 PSU HE VWB PI5 L1200	WT490C
10973500	WT490C 64S/840 PSD HE VWB PI5 L1200	WT490C
10974200	WT490C 80S/840 PSU HE NB-HRO PI5L1200	WT490C
10975900	WT490C 80S/840 PSD HE NB-HRO PI5L1200	WT490C
10976600	WT490C 80S/840 PSU HE WB TW1 PI5L1200	WT490C
10977300	WT490C 80S/840 PSU HE WB TW3 PI5L1200	WT490C
10978000	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	WT490C
10979700	WT490C 80S/840 PSD HE WB PI5 L1200	WT490C
10980300	WT490C 80S/840 PSD HE WB TW1 PI5L1200	WT490C
10981000	WT490C 80S/840 PSD HE WB TW3 PI7L1200	WT490C
10982700	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	WT490C
10983400	WT490C 80S/840 PSU HE VWB PI5 L1200	WT490C
10984100	WT490C 80S/840 PSD HE VWB PI5 L1200	WT490C
10998800	WT490C 64S/840 PSU HE NB-HRO WA7L1200	WT490C
10999500	WT490C 64S/840 PSD HE NB-HRO WA7L1200	WT490C
62312500	WT490C 64S/840 PSU HE WB WA7 L1200	WT490C
62314900	WT490C 64S/840 PSU HE WB TW3 WA7L1200	WT490C
62316300	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	WT490C
62317000	WT490C 64S/840 PSD HE WB WA7 L1200	WT490C
62318700	WT490C 64S/840 PSD HE WB TW3 WA7L1200	WT490C
62319400	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	WT490C
62320000	WT490C 64S/840 PSU HE VWB WA7 L1200	WT490C
62321700	WT490C 64S/840 PSD HE VWB WA7 L1200	WT490C
62322400	WT490C 80S/840 PSU HE NB-HRO WA7L1200	WT490C
62323100	WT490C 80S/840 PSD HE NB-HRO WA7L1200	WT490C
62324800	WT490C 80S/840 PSU HE WB WA7 L1200	WT490C
62325500	WT490C 80S/840 PSU HE WB TW3 WA7L1200	WT490C
62326200	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	WT490C
62327900	WT490C 80S/840 PSD HE WB WA7 L1200	WT490C
62328600	WT490C 80S/840 PSD HE WB TW3 WA7L1200	WT490C

Order Code	Full Product Name	Product family code
62329300	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	WT490C
62330900	WT490C 80S/840 PSU HE VWB WA7 L1200	WT490C
62331600	WT490C 80S/840 PSD HE VWB WA7 L1200	WT490C
62353800	WT490C 42S/840 PSU HE WB PI5 L1200	WT490C
62354500	WT490C 64S/840 PSU HE WB PI5 L1200	WT490C
62355200	WT490C 80S/840 PSU HE WB PI5 L1200	WT490C
62571600	WT490C 42S/840 PSD HE VWB PI5 L1200	WT490C
62752900	WT490C 35S/840 PSU HE WB PI5 L1200	WT490C
62756700	WT490C 64S/840 PSU HE O PI5 L1200	WT490C
62757400	WT490C 64S/840 PSU HE PCO PI5 L1200	WT490C
62760400	WT495C 64S/840 PSU HE WB PI5 L1200	WT495C
62762800	WT495C 64S/840 PSD HE WB PI5 L1200	WT495C
77191800	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L120	WT490C
77193200	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L120	WT490C
77200700	WT490C 42S/840 PSU HE WB TW3x2.5PI5 L120	WT490C
77394300	WT490C 100S/840 PSD HE WB PI5 L1200	WT490C
77398100	WT490C 100S/840 PSU HE WB PI5 L1200	WT490C
62475700	WT490C 64S/840 PSD HE WB PI5 L1600	WT490C
62476400	WT490C 64S/840 PSU HE WB TW3 PI5L1600	WT490C
62477100	WT490C 64S/840 PSU HE WB PI5 L1600	WT490C
62478800	WT490C 80S/840 PSU HE WB PI5 L1600	WT490C
62481800	WT490C 64S/840 PSD HE WB WA7 L1600	WT490C
62482500	WT490C 64S/840 PSU HE WB TW3 WA7L1600	WT490C
62483200	WT490C 64S/840 PSU HE WB WA7 L1600	WT490C
77197000	WT490C 64S/840 PSU HE WB TW3x2.5PI5 L160	WT490C
77198700	WT490C 80S/840 PSU HE WB TW3x2.5PI5 L160	WT490C
10958200	WT490C 23S/840 PSD HE WB PI5 L700	WT490C
62352100	WT490C 23S/840 PSU HE WB PI5 L700	WT490C
62315600	WT490C 64S/840 PSU HE WB TCW5 L1200	WT490C
62572300	WT490C 64S/840 PSU HE WB W5 L1200	WT490C
62573000	WT490C 80S/840 PSU HE WB W5 L1200	WT490C
62574700	WT490C 64S/840 PSD HE WB W5 L1200	WT490C
62575400	WT490C 80S/840 PSD HE WB W5 L1200	WT490C


Polar normal diagrams




WT490CI - 910770229590




WT490CI - 910925868249




WT490CI - 910925868292




WT490CI - 910925868698




WT490CI - 910925868259




WT490CI - 910925868702




WT490CI - 910925868261




WT490CI - 910925868413




WT490CI - 910925868697




WT490CI - 910925868699




WT490CI - 910925868706




WT490CI - 910925868288




WT490CI - 910925868414




WT490CI - 910925868513




WT490CI - 910925868705




WT490CI - 910925868419




WT490CI - 910925868511




WT490CI - 910925868516




WT490CI - 910925868701




WT490CI - 910925868703




WT490CI - 910925868509




WT490CI - 910925867704




WT490CI - 910925867723




WT490CI - 910925867732




WT490CI - 910925867735




WT490CI - 910925867706




WT490CI - 910925867712




WT490CI - 910925867711




WT490CI - 910925867724




WT490CI - 910925867726




WT490CI - 910925867727




WT490CI - 910925867720




WT490CI - 910925867738




WT490CI - 910925867713




WT490CI - 910925867717




WT490CI - 910925867714




WT490CI - 910925867715




WT490CI - 910925867716




WT490CI - 910925867739




WT490CI - 910925867708




WT490CI - 910925867719




WT490CI - 910925867725




WT490CI - 910925867737




WT490CI - 910925867718




WT490CI - 910925867734




WT490CI - 910925867721




WT490CI - 910925867729




WT490CI - 910925868253




WT490CI - 910925868266




WT490CI - 910925868287




WT490CI - 910925868289




WT490CI - 910925868290




WT490CI - 910925868256




WT490CI - 910925868264




WT490CI - 910925868412




WT490CI - 910925868252




WT490CI - 910925868262




WT490CI - 910925868265




WT490CI - 910925868510




WT490CI - 910925867703




WT490CI - 910925867705




WT490CI - 910925867707




WT490CI - 910925867709




WT490CI - 910925867710




WT490CI - 910925867722




WT490CI - 910925867728




WT490CI - 910925867731




WT490CI - 910925867733




WT490CI - 910925867736




WT490CI - 910925867743




WT490CI - 910925867741




WT490CI - 910925867740




WT490CI - 910925867744




WT490CI - 910925868247




WT490CI - 910925868251




WT490CI - 910925868255




WT490CI - 910925868254




WT490CI - 910925868258




WT490CI - 910925868263




WT490CI - 910925868260




WT490CI - 910925868257




WT490CI - 910925868294




WT490CI - 910925868293




WT490CI - 910925868415




WT490CI - 910925868418




WT490CI - 910925868420




WT490CI - 910925868512




WT490CI - 910925868691




WT490CI - 910925868695




WT490CI - 910925868696




WT490CI - 910925868704




WT490CI - 910925868707




WT490CI - 910925869401




WT490CI - 910925869403




WT490CI - 910925869405




WT490CI - 910925869406




WT490CI - 910925869407




WT490CI - 910925869408




WT490CI - 910925869410




WT490CI - 910925868250




WT490CI - 910925869610



WT490CI - 910925869611



WT490CI - 910925869606



WT490CI - 910925869607