



Robust, connectable luminaire with outstanding performance.

Pacific LED Gen5

Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in parking garages and warehouses. Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency, and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency, energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

Pacific LED Gen5

Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.

Application

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

Warnings and Safety









- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Dimensional drawing



Pacific LED Gen5

Dimensional drawing



Pacific LED Gen5

Dimensional drawing



Product details



Pacific LED gen5, looping connection, 2 entry on one side



Pacific LED gen5 with push in 7-pole (PI7) connector



Pacific LED gen5, Wieland connector



Pacific LED gen5 with WAGO connector



Pacific LED gen5 connection through WAGO connector side view



Pacific LED gen5 with push in 5-pole (PI5) connecto



Pacific LED gen5 with Wieland connector

Pacific LED Gen5

Product details



Pacific LED gen5 connection through WAGO connector

General Information

Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
-----------------------------	-----

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK08
Ingress protection code	IP66

Approval and Application

CE mark	Yes
ENEC mark	ENEC plus mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
-------------------------	-------

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous		Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)	Luminous Flux	
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	4000 K	165 lm/W	8,000 lm	Wide beam
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
10990200	WT490C 80S/840 PSD WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	4000 K	165 lm/W	8,000 lm	Wide beam
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
10993300	WT490C 80S/840 PSU VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
10994000	WT490C 80S/840 PSD VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
10995700	WT490C 100S/840 PSD WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam
10996400	WT490C 120S/840 PSD WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
62357600	WT490C 80S/840 PSU WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
62358300	WT490C 100S/840 PSU WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam
62359000	WT490C 120S/840 PSU WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	4000 K	165 lm/W	8,000 lm	Wide beam
62758100	WT490C 80S/840 PSU O PI5 L1800	4000 K	157 lm/W	7,600 lm	Opal

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
62759800	WT490C 80S/840 PSU PCO P15 L1800	4000 K	136 lm/W	6,600 lm	Opal
62761100	WT495C 80S/840 PSU WB P15 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
62763500	WT495C 80S/840 PSD WB P15 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
77195600	WT490C 80S/840 PSU WB TW3x2.5P15 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
77196300	WT490C 80S/840 PSD WB TW3x2.5P17 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
77395000	WT490C 150S/840 PSD WB P15 L1800	4000 K	155 lm/W	15,000 lm	Very wide beam
77399800	WT490C 150S/840 PSU WB P15 L1800	4000 K	155 lm/W	15,000 lm	Very wide beam
62764200	WT492C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62765900	WT492C 80S/840 PSU WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
62766600	WT492C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
62767300	WT492C 80S/840 PSD WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
73290200	WT490C 42S/830 PSU WB P15 L1200	3000 K	157 lm/W	4,200 lm	Wide beam
10959900	WT490C 42S/840 PSD WB P15 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
10960500	WT490C 64S/840 PSU NB-HRO P15L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
10961200	WT490C 64S/840 PSD NB-HRO P15L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
10962900	WT490C 64S/840 PSU WB TW1 P15L1200	4000 K	160 lm/W	6,400 lm	Wide beam
10963600	WT490C 64S/840 PSU WB TW3 P15L1200	4000 K	160 lm/W	6,400 lm	Wide beam
10964300	WT490C 64S/840 PSU WB TCS L1200	4000 K	160 lm/W	6,400 lm	Wide beam
10965000	WT490C 64S/840 PSU WB ELP3 P15 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
10966700	WT490C 64S/840 PSU WB ELP3 TW1 P15 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
10967400	WT490C 64S/840 PSD WB P15 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
10968100	WT490C 64S/840 PSD WB TW1 P15L1200	4000 K	162 lm/W	6,400 lm	Wide beam
10969800	WT490C 64S/840 PSD WB TW3 P17L1200	4000 K	162 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
10972800	WT490C 64S/840 PSU VWB PI5 L1200	4000 K	160 lm/W	6,400 lm	Very wide beam
10973500	WT490C 64S/840 PSD VWB PI5 L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
10974200	WT490C 80S/840 PSU NB- HRO PI5L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
10975900	WT490C 80S/840 PSD NB- HRO PI5L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
10979700	WT490C 80S/840 PSD WB PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
10983400	WT490C 80S/840 PSU VWB PI5 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
10984100	WT490C 80S/840 PSD VWB PI5 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
10998800	WT490C 64S/840 PSU NB- HRO WA7L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
10999500	WT490C 64S/840 PSD NB- HRO WA7L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
62312500	WT490C 64S/840 PSU WB WA7 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
62317000	WT490C 64S/840 PSD WB WA7 L1200	4000 K	162 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	4000 K	162 lm/W	6,400 lm	Wide beam
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
62320000	WT490C 64S/840 PSU VWB WA7 L1200	4000 K	160 lm/W	6,400 lm	Very wide beam
62321700	WT490C 64S/840 PSD VWB WA7 L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
62324800	WT490C 80S/840 PSU WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
62327900	WT490C 80S/840 PSD WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
62330900	WT490C 80S/840 PSU VWB WA7 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
62331600	WT490C 80S/840 PSD VWB WA7 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
62353800	WT490C 42S/840 PSU WB P15 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
62354500	WT490C 64S/840 PSU WB P15 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62355200	WT490C 80S/840 PSU WB P15 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62571600	WT490C 42S/840 PSD VWB P15 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
62752900	WT490C 35S/840 PSU WB P15 L1200	4000 K	159 lm/W	3,500 lm	Wide beam
62756700	WT490C 64S/840 PSU O P15 L1200	4000 K	155 lm/W	6,200 lm	Opal
62757400	WT490C 64S/840 PSU PCO P15 L1200	4000 K	133 lm/W	5,300 lm	Opal
62760400	WT495C 64S/840 PSU WB P15 L1200	4000 K	158 lm/W	6,400 lm	Wide beam
62762800	WT495C 64S/840 PSD WB P15 L1200	4000 K	158 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
77394300	WT490C 100S/840 PSD WB PI5 L1200	4000 K	152 lm/W	10,000 lm	Very wide beam
77398100	WT490C 100S/840 PSU WB PI5 L1200	4000 K	154 lm/W	10,000 lm	Very wide beam
62475700	WT490C 64S/840 PSD WB PI5 L1600	4000 K	162 lm/W	6,400 lm	Wide beam
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	4000 K	160 lm/W	6,400 lm	Wide beam
62477100	WT490C 64S/840 PSU WB PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
62478800	WT490C 80S/840 PSU WB PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
62481800	WT490C 64S/840 PSD WB WA7 L1600	4000 K	162 lm/W	6,400 lm	Wide beam
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	4000 K	160 lm/W	6,400 lm	Wide beam
62483200	WT490C 64S/840 PSU WB WA7 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
10958200	WT490C 23S/840 PSD WB PI5 L700	4000 K	160 lm/W	2,300 lm	Wide beam
62352100	WT490C 23S/840 PSU WB PI5 L700	4000 K	151 lm/W	2,300 lm	Wide beam
62315600	WT490C 64S/840 PSU WB TCW5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62572300	WT490C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62573000	WT490C 80S/840 PSU WB W5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62574700	WT490C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
62575400	WT490C 80S/840 PSD WB W5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	48.5 W	10990200	WT490C 80S/840 PSD WB PI5 L1800	48.5 W
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	48.5 W	10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	48.5 W
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	48.5 W	10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	52 W
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	52 W	10993300	WT490C 80S/840 PSU VWB PI5 L1800	48.5 W

Pacific LED Gen5

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
10994000	WT490C 80S/840 PSD VWB PI5 L1800	48.5 W	62312500	WT490C 64S/840 PSU WB WA7 L1200	40 W
10995700	WT490C 100S/840 PSD WB PI5 L1800	62 W	62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	40 W
10996400	WT490C 120S/840 PSD WB PI5 L1800	76 W	62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	44 W
62357600	WT490C 80S/840 PSU WB PI5 L1800	48.5 W	62317000	WT490C 64S/840 PSD WB WA7 L1200	39.5 W
62358300	WT490C 100S/840 PSU WB PI5 L1800	62 W	62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	39.5 W
62359000	WT490C 120S/840 PSU WB PI5 L1800	76 W	62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	43.5 W
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	48.5 W	62320000	WT490C 64S/840 PSU VWB WA7 L1200	40 W
62758100	WT490C 80S/840 PSU O PI5 L1800	51 W	62321700	WT490C 64S/840 PSD VWB WA7 L1200	39.5 W
62759800	WT490C 80S/840 PSU PCO PI5 L1800	48.5 W	62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	51 W
62761100	WT495C 80S/840 PSU WB PI5 L1800	49 W	62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	51 W
62763500	WT495C 80S/840 PSD WB PI5 L1800	48.5 W	62324800	WT490C 80S/840 PSU WB WA7 L1200	51 W
77195600	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	48.5 W	62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	51 W
77196300	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	48.5 W	62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	55 W
77395000	WT490C 150S/840 PSD WB PI5 L1800	97 W	62327900	WT490C 80S/840 PSD WB WA7 L1200	51 W
77399800	WT490C 150S/840 PSU WB PI5 L1800	97 W	62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	51 W
62764200	WT492C 64S/840 PSU WB W5 L1200	40 W	62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	55 W
62765900	WT492C 80S/840 PSU WB W5 L1800	49 W	62330900	WT490C 80S/840 PSU VWB WA7 L1200	51 W
62766600	WT492C 64S/840 PSD WB W5 L1200	39.5 W	62331600	WT490C 80S/840 PSD VWB WA7 L1200	51 W
62767300	WT492C 80S/840 PSD WB W5 L1800	48.5 W	62353800	WT490C 42S/840 PSU WB PI5 L1200	25.5 W
73290200	WT490C 42S/830 PSU WB PI5 L1200	25.5 W	62354500	WT490C 64S/840 PSU WB PI5 L1200	40 W
10959900	WT490C 42S/840 PSD WB PI5 L1200	26 W	62355200	WT490C 80S/840 PSU WB PI5 L1200	51 W
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	40 W	62571600	WT490C 42S/840 PSD VWB PI5 L1200	26 W
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	39.5 W	62752900	WT490C 35S/840 PSU WB PI5 L1200	22 W
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	40 W	62756700	WT490C 64S/840 PSU O PI5 L1200	40 W
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	40 W	62757400	WT490C 64S/840 PSU PCO PI5 L1200	40 W
10964300	WT490C 64S/840 PSU WB TC5 L1200	40 W	62760400	WT495C 64S/840 PSU WB PI5 L1200	40.5 W
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	44 W	62762800	WT495C 64S/840 PSD WB PI5 L1200	40.5 W
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	44 W	77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	40 W
10967400	WT490C 64S/840 PSD WB PI5 L1200	39.5 W	77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	51 W
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	39.5 W	77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	25.5 W
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	39.5 W	77394300	WT490C 100S/840 PSD WB PI5 L1200	66 W
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	43.5 W	77398100	WT490C 100S/840 PSU WB PI5 L1200	65 W
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	43.5 W	62475700	WT490C 64S/840 PSD WB PI5 L1600	39.5 W
10972800	WT490C 64S/840 PSU VWB PI5 L1200	40 W	62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	40 W
10973500	WT490C 64S/840 PSD VWB PI5 L1200	39.5 W	62477100	WT490C 64S/840 PSU WB PI5 L1600	40 W
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	51 W	62478800	WT490C 80S/840 PSU WB PI5 L1600	51 W
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	51 W	62481800	WT490C 64S/840 PSD WB WA7 L1600	39.5 W
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	51 W	62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	40 W
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	51 W	62483200	WT490C 64S/840 PSU WB WA7 L1600	40 W
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	55 W	77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	40 W
10979700	WT490C 80S/840 PSD WB PI5 L1200	51 W	77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	51 W
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	51 W	10958200	WT490C 23S/840 PSD WB PI5 L700	14.4 W
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	51 W	62352100	WT490C 23S/840 PSU WB PI5 L700	15.2 W
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	55 W	62315600	WT490C 64S/840 PSU WB TCW5 L1200	40 W
10983400	WT490C 80S/840 PSU VWB PI5 L1200	51 W	62572300	WT490C 64S/840 PSU WB W5 L1200	40 W
10984100	WT490C 80S/840 PSD VWB PI5 L1200	51 W	62573000	WT490C 80S/840 PSU WB W5 L1200	51 W
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	40 W	62574700	WT490C 64S/840 PSD WB W5 L1200	39.5 W
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	39.5 W	62575400	WT490C 80S/840 PSD WB W5 L1200	51 W

Controls and Dimming

Pacific LED Gen5

Order Code	Full Product Name	Dimmable	Embedded
			control
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	No	-
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	Yes	-
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	No	-
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	No	-
10990200	WT490C 80S/840 PSD WB PI5 L1800	Yes	-
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	Yes	-
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Yes	-
10993300	WT490C 80S/840 PSU VWB PI5 L1800	No	-
10994000	WT490C 80S/840 PSD VWB PI5 L1800	Yes	-
10995700	WT490C 100S/840 PSD WB PI5 L1800	Yes	-
10996400	WT490C 120S/840 PSD WB PI5 L1800	Yes	-
62357600	WT490C 80S/840 PSU WB PI5 L1800	No	-
62358300	WT490C 100S/840 PSU WB PI5 L1800	No	-
62359000	WT490C 120S/840 PSU WB PI5 L1800	No	-
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	Yes	InterAct SNS410 antenna
62758100	WT490C 80S/840 PSU O PI5 L1800	No	-
62759800	WT490C 80S/840 PSU PCO PI5 L1800	No	-
62761100	WT495C 80S/840 PSU WB PI5 L1800	No	-
62763500	WT495C 80S/840 PSD WB PI5 L1800	Yes	-
77195600	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	No	-
77196300	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	Yes	-
77395000	WT490C 150S/840 PSD WB PI5 L1800	Yes	-
77399800	WT490C 150S/840 PSU WB PI5 L1800	No	-
62764200	WT492C 64S/840 PSU WB W5 L1200	No	-
62765900	WT492C 80S/840 PSU WB W5 L1800	No	-
62766600	WT492C 64S/840 PSD WB W5 L1200	Yes	-
62767300	WT492C 80S/840 PSD WB W5 L1800	Yes	-
73290200	WT490C 42S/830 PSU WB PI5 L1200	No	-
10959900	WT490C 42S/840 PSD WB PI5 L1200	Yes	-
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	No	-
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	Yes	-
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	No	-
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	No	-
10964300	WT490C 64S/840 PSU WB TC5 L1200	No	-
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	No	-
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	No	-
10967400	WT490C 64S/840 PSD WB PI5 L1200	Yes	-
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	Yes	-
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	Yes	-
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	Yes	-
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	Yes	-
10972800	WT490C 64S/840 PSU VWB PI5 L1200	No	-
10973500	WT490C 64S/840 PSD VWB PI5 L1200	Yes	-
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	No	-
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	Yes	-
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	No	-

Order Code	Full Product Name	Dimmable	Embedded
			control
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	No	-
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	No	-
10979700	WT490C 80S/840 PSD WB PI5 L1200	Yes	-
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	Yes	-
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	Yes	-
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Yes	-
10983400	WT490C 80S/840 PSU VWB PI5 L1200	No	-
10984100	WT490C 80S/840 PSD VWB PI5 L1200	Yes	-
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	No	-
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	Yes	-
62312500	WT490C 64S/840 PSU WB WA7 L1200	No	-
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	No	-
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	No	-
62317000	WT490C 64S/840 PSD WB WA7 L1200	Yes	-
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	Yes	-
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Yes	-
62320000	WT490C 64S/840 PSU VWB WA7 L1200	No	-
62321700	WT490C 64S/840 PSD VWB WA7 L1200	Yes	-
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	No	-
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	Yes	-
62324800	WT490C 80S/840 PSU WB WA7 L1200	No	-
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	No	-
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	No	-
62327900	WT490C 80S/840 PSD WB WA7 L1200	Yes	-
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	Yes	-
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Yes	-
62330900	WT490C 80S/840 PSU VWB WA7 L1200	No	-
62331600	WT490C 80S/840 PSD VWB WA7 L1200	Yes	-
62353800	WT490C 42S/840 PSU WB PI5 L1200	No	-
62354500	WT490C 64S/840 PSU WB PI5 L1200	No	-
62355200	WT490C 80S/840 PSU WB PI5 L1200	No	-
62571600	WT490C 42S/840 PSD VWB PI5 L1200	Yes	-
62752900	WT490C 35S/840 PSU WB PI5 L1200	No	-
62756700	WT490C 64S/840 PSU O PI5 L1200	No	-
62757400	WT490C 64S/840 PSU PCO PI5 L1200	No	-
62760400	WT495C 64S/840 PSU WB PI5 L1200	No	-
62762800	WT495C 64S/840 PSD WB PI5 L1200	Yes	-
77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	No	-
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	No	-
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	No	-
77394300	WT490C 100S/840 PSD WB PI5 L1200	Yes	-
77398100	WT490C 100S/840 PSU WB PI5 L1200	No	-
62475700	WT490C 64S/840 PSD WB PI5 L1600	Yes	-
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	No	-
62477100	WT490C 64S/840 PSU WB PI5 L1600	No	-
62478800	WT490C 80S/840 PSU WB PI5 L1600	No	-
62481800	WT490C 64S/840 PSD WB WA7 L1600	Yes	-
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	No	-
62483200	WT490C 64S/840 PSU WB WA7 L1600	No	-

Pacific LED Gen5

Order Code	Full Product Name	Embedded	
		Dimmable	control
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	No	-
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	No	-
10958200	WT490C 23S/840 PSD WB PI5 L700	Yes	-
62352100	WT490C 23S/840 PSU WB PI5 L700	No	-

Order Code	Full Product Name	Embedded	
		Dimmable	control
62315600	WT490C 64S/840 PSU WB TCW5 L1200	No	-
62572300	WT490C 64S/840 PSU WB W5 L1200	No	-
62573000	WT490C 80S/840 PSU WB W5 L1200	No	-
62574700	WT490C 64S/840 PSD WB W5 L1200	Yes	-
62575400	WT490C 80S/840 PSD WB W5 L1200	Yes	-

Mechanical and Housing

Order Code	Full Product Name	Explosion hazard class
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	-
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	-
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	-
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	-
10990200	WT490C 80S/840 PSD WB PI5 L1800	-
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	-
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	-
10993300	WT490C 80S/840 PSU VWB PI5 L1800	-
10994000	WT490C 80S/840 PSD VWB PI5 L1800	-
10995700	WT490C 100S/840 PSD WB PI5 L1800	-
10996400	WT490C 120S/840 PSD WB PI5 L1800	-
62357600	WT490C 80S/840 PSU WB PI5 L1800	-
62358300	WT490C 100S/840 PSU WB PI5 L1800	-
62359000	WT490C 120S/840 PSU WB PI5 L1800	-
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	-
62758100	WT490C 80S/840 PSU O PI5 L1800	-
62759800	WT490C 80S/840 PSU PCO PI5 L1800	-
62761100	WT495C 80S/840 PSU WB PI5 L1800	-
62763500	WT495C 80S/840 PSD WB PI5 L1800	-
77195600	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	-
77196300	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	-
77395000	WT490C 150S/840 PSD WB PI5 L1800	-
77399800	WT490C 150S/840 PSU WB PI5 L1800	-
62764200	WT492C 64S/840 PSU WB W5 L1200	Zone 2 and 22
62765900	WT492C 80S/840 PSU WB W5 L1800	Zone 2 and 22
62766600	WT492C 64S/840 PSD WB W5 L1200	Zone 2 and 22
62767300	WT492C 80S/840 PSD WB W5 L1800	Zone 2 and 22
73290200	WT490C 42S/830 PSU WB PI5 L1200	-
10959900	WT490C 42S/840 PSD WB PI5 L1200	-
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	-
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	-
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	-
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	-
10964300	WT490C 64S/840 PSU WB TC5 L1200	-
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	-
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	-
10967400	WT490C 64S/840 PSD WB PI5 L1200	-
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	-
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	-
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	-
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	-

Order Code	Full Product Name	Explosion hazard class
10972800	WT490C 64S/840 PSU VWB PI5 L1200	-
10973500	WT490C 64S/840 PSD VWB PI5 L1200	-
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	-
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	-
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	-
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	-
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	-
10979700	WT490C 80S/840 PSD WB PI5 L1200	-
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	-
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	-
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	-
10983400	WT490C 80S/840 PSU VWB PI5 L1200	-
10984100	WT490C 80S/840 PSD VWB PI5 L1200	-
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	-
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	-
62312500	WT490C 64S/840 PSU WB WA7 L1200	-
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	-
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	-
62317000	WT490C 64S/840 PSD WB WA7 L1200	-
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	-
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	-
62320000	WT490C 64S/840 PSU VWB WA7 L1200	-
62321700	WT490C 64S/840 PSD VWB WA7 L1200	-
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	-
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	-
62324800	WT490C 80S/840 PSU WB WA7 L1200	-
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	-
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	-
62327900	WT490C 80S/840 PSD WB WA7 L1200	-
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	-
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	-
62330900	WT490C 80S/840 PSU VWB WA7 L1200	-
62331600	WT490C 80S/840 PSD VWB WA7 L1200	-
62353800	WT490C 42S/840 PSU WB PI5 L1200	-
62354500	WT490C 64S/840 PSU WB PI5 L1200	-
62355200	WT490C 80S/840 PSU WB PI5 L1200	-
62571600	WT490C 42S/840 PSD VWB PI5 L1200	-
62752900	WT490C 35S/840 PSU WB PI5 L1200	-
62756700	WT490C 64S/840 PSU O PI5 L1200	-
62757400	WT490C 64S/840 PSU PCO PI5 L1200	-
62760400	WT495C 64S/840 PSU WB PI5 L1200	-

Pacific LED Gen5

Order Code	Full Product Name	Explosion hazard class
62762800	WT495C 64S/840 PSD WB PI5 L1200	-
77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	-
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-
77394300	WT490C 100S/840 PSD WB PI5 L1200	-
77398100	WT490C 100S/840 PSU WB PI5 L1200	-
62475700	WT490C 64S/840 PSD WB PI5 L1600	-
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	-
62477100	WT490C 64S/840 PSU WB PI5 L1600	-
62478800	WT490C 80S/840 PSU WB PI5 L1600	-
62481800	WT490C 64S/840 PSD WB WA7 L1600	-

Order Code	Full Product Name	Explosion hazard class
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	-
62483200	WT490C 64S/840 PSU WB WA7 L1600	-
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-
10958200	WT490C 23S/840 PSD WB PI5 L700	-
62352100	WT490C 23S/840 PSU WB PI5 L700	-
62315600	WT490C 64S/840 PSU WB TCW5 L1200	-
62572300	WT490C 64S/840 PSU WB W5 L1200	-
62573000	WT490C 80S/840 PSU WB W5 L1200	-
62574700	WT490C 64S/840 PSD WB W5 L1200	-
62575400	WT490C 80S/840 PSD WB W5 L1200	-

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	-	-	-
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	-	-	-
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	-	-	-
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10990200	WT490C 80S/840 PSD WB PI5 L1800	-	-	-
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	-	-	-
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10993300	WT490C 80S/840 PSU VWB PI5 L1800	-	-	-
10994000	WT490C 80S/840 PSD VWB PI5 L1800	-	-	-
10995700	WT490C 100S/840 PSD WB PI5 L1800	-	-	-
10996400	WT490C 120S/840 PSD WB PI5 L1800	-	-	-
62357600	WT490C 80S/840 PSU WB PI5 L1800	-	-	-
62358300	WT490C 100S/840 PSU WB PI5 L1800	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
62359000	WT490C 120S/840 PSU WB PI5 L1800	-	-	-
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	-	-	-
62758100	WT490C 80S/840 PSU O PI5 L1800	-	-	-
62759800	WT490C 80S/840 PSU PCO PI5 L1800	-	-	-
62761100	WT495C 80S/840 PSU WB PI5 L1800	-	-	-
62763500	WT495C 80S/840 PSD WB PI5 L1800	-	-	-
77195600	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	-	-	-
77196300	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	-	-	-
77395000	WT490C 150S/840 PSD WB PI5 L1800	-	-	-
77399800	WT490C 150S/840 PSU WB PI5 L1800	-	-	-
62764200	WT492C 64S/840 PSU WB W5 L1200	-	-	-
62765900	WT492C 80S/840 PSU WB W5 L1800	-	-	-
62766600	WT492C 64S/840 PSD WB W5 L1200	-	-	-
62767300	WT492C 80S/840 PSD WB W5 L1800	-	-	-
73290200	WT490C 42S/830 PSU WB PI5 L1200	-	-	-

Pacific LED Gen5

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10959900	WT490C 42S/840 PSD WB PI5 L1200	-	-	-
10960500	WT490C 64S/840 PSU NB- HRO PI5L1200	-	-	-
10961200	WT490C 64S/840 PSD NB- HRO PI5L1200	-	-	-
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	-	-	-
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	-	-	-
10964300	WT490C 64S/840 PSU WB TC5 L1200	-	-	-
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10967400	WT490C 64S/840 PSD WB PI5 L1200	-	-	-
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	-	-	-
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	-	-	-
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10972800	WT490C 64S/840 PSU VWB PI5 L1200	-	-	-
10973500	WT490C 64S/840 PSD VWB PI5 L1200	-	-	-
10974200	WT490C 80S/840 PSU NB- HRO PI5L1200	-	-	-
10975900	WT490C 80S/840 PSD NB- HRO PI5L1200	-	-	-
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	-	-	-
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
10979700	WT490C 80S/840 PSD WB PI5 L1200	-	-	-
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	-	-	-
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	-	-	-
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10983400	WT490C 80S/840 PSU VWB PI5 L1200	-	-	-
10984100	WT490C 80S/840 PSD VWB PI5 L1200	-	-	-
10998800	WT490C 64S/840 PSU NB- HRO WA7L1200	-	-	-
10999500	WT490C 64S/840 PSD NB- HRO WA7L1200	-	-	-
62312500	WT490C 64S/840 PSU WB WA7 L1200	-	-	-
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	-	-	-
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
62317000	WT490C 64S/840 PSD WB WA7 L1200	-	-	-
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	-	-	-
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
62320000	WT490C 64S/840 PSU VWB WA7 L1200	-	-	-
62321700	WT490C 64S/840 PSD VWB WA7 L1200	-	-	-
62322400	WT490C 80S/840 PSU NB- HRO WA7L1200	-	-	-
62323100	WT490C 80S/840 PSD NB- HRO WA7L1200	-	-	-

Pacific LED Gen5

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
62324800	WT490C 80S/840 PSU WB WA7 L1200	-	-	-
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	-	-	-
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
62327900	WT490C 80S/840 PSD WB WA7 L1200	-	-	-
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	-	-	-
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	No	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
62330900	WT490C 80S/840 PSU VWB WA7 L1200	-	-	-
62331600	WT490C 80S/840 PSD VWB WA7 L1200	-	-	-
62353800	WT490C 42S/840 PSU WB PI5 L1200	-	-	-
62354500	WT490C 64S/840 PSU WB PI5 L1200	-	-	-
62355200	WT490C 80S/840 PSU WB PI5 L1200	-	-	-
62571600	WT490C 42S/840 PSD VWB PI5 L1200	-	-	-
62752900	WT490C 35S/840 PSU WB PI5 L1200	-	-	-
62756700	WT490C 64S/840 PSU O PI5 L1200	-	-	-
62757400	WT490C 64S/840 PSU PCO PI5 L1200	-	-	-
62760400	WT495C 64S/840 PSU WB PI5 L1200	-	-	-
62762800	WT495C 64S/840 PSD WB PI5 L1200	-	-	-
77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-	-	-
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-	-	-
77394300	WT490C 100S/840 PSD WB PI5 L1200	-	-	-
77398100	WT490C 100S/840 PSU WB PI5 L1200	-	-	-
62475700	WT490C 64S/840 PSD WB PI5 L1600	-	-	-
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	-	-	-
62477100	WT490C 64S/840 PSU WB PI5 L1600	-	-	-
62478800	WT490C 80S/840 PSU WB PI5 L1600	-	-	-
62481800	WT490C 64S/840 PSD WB WA7 L1600	-	-	-
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	-	-	-
62483200	WT490C 64S/840 PSU WB WA7 L1600	-	-	-
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-	-	-
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-	-	-
10958200	WT490C 23S/840 PSD WB PI5 L700	-	-	-
62352100	WT490C 23S/840 PSU WB PI5 L700	-	-	-
62315600	WT490C 64S/840 PSU WB TCW5 L1200	-	-	-
62572300	WT490C 64S/840 PSU WB W5 L1200	-	-	-
62573000	WT490C 80S/840 PSU WB W5 L1200	-	-	-
62574700	WT490C 64S/840 PSD WB W5 L1200	-	-	-
62575400	WT490C 80S/840 PSD WB W5 L1200	-	-	-

Approval and Application

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	-25 to +45 °C	1		0.4
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	-25 to +45 °C	1		0.4
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	-25 to +45 °C	1		0.4
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	0 to +30 °C	1		0.4
10990200	WT490C 80S/840 PSD WB PI5 L1800	-25 to +45 °C	1		0.4
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	-25 to +45 °C	1		0.4
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	0 to +30 °C	1		0.4
10993300	WT490C 80S/840 PSU VWB PI5 L1800	-25 to +45 °C	1		0.4
10994000	WT490C 80S/840 PSD VWB PI5 L1800	-25 to +45 °C	1		0.4
10995700	WT490C 100S/840 PSD WB PI5 L1800	-25 to +45 °C	1		0.4
10996400	WT490C 120S/840 PSD WB PI5 L1800	-25 to +45 °C	1		0.4
62357600	WT490C 80S/840 PSU WB PI5 L1800	-25 to +45 °C	1		0.4
62358300	WT490C 100S/840 PSU WB PI5 L1800	-25 to +45 °C	1		0.4
62359000	WT490C 120S/840 PSU WB PI5 L1800	-25 to +45 °C	1		0.4
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	-25 to +45 °C	1		0.4
62758100	WT490C 80S/840 PSU O PI5 L1800	-25 to +45 °C	1		0.4
62759800	WT490C 80S/840 PSU PCO PI5 L1800	-25 to +45 °C	1		0.4
62761100	WT495C 80S/840 PSU WB PI5 L1800	-35 to +60 °C	1		0.4
62763500	WT495C 80S/840 PSD WB PI5 L1800	-35 to +60 °C	1		0.4
77195600	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	-25 to +45 °C	1		0.4
77196300	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	-25 to +45 °C	1		0.4
77395000	WT490C 150S/840 PSD WB PI5 L1800	-25 to +25 °C	-	-	-
77399800	WT490C 150S/840 PSU WB PI5 L1800	-25 to +25 °C	-	-	-

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
62764200	WT492C 64S/840 PSU WB W5 L1200	-25 to +45 °C	1		0.4
62765900	WT492C 80S/840 PSU WB W5 L1800	-25 to +45 °C	1		0.4
62766600	WT492C 64S/840 PSD WB W5 L1200	-25 to +45 °C	1		0.4
62767300	WT492C 80S/840 PSD WB W5 L1800	-25 to +45 °C	1		0.4
73290200	WT490C 42S/830 PSU WB PI5 L1200	-25 to +45 °C	1		0.4
10959900	WT490C 42S/840 PSD WB PI5 L1200	-25 to +45 °C	1		0.4
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	-25 to +45 °C	1		0.4
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	-25 to +45 °C	1		0.4
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	-25 to +45 °C	1		0.4
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	-25 to +45 °C	1		0.4
10964300	WT490C 64S/840 PSU WB TC5 L1200	-25 to +45 °C	1		0.4
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	0 to +40 °C	1		0.4
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	0 to +40 °C	1		0.4
10967400	WT490C 64S/840 PSD WB PI5 L1200	-25 to +45 °C	1		0.4
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	-25 to +45 °C	1		0.4
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	-25 to +45 °C	1		0.4
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	0 to +40 °C	1		0.4
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	0 to +40 °C	1		0.4
10972800	WT490C 64S/840 PSU VWB PI5 L1200	-25 to +45 °C	1		0.4
10973500	WT490C 64S/840 PSD VWB PI5 L1200	-25 to +45 °C	1		0.4
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	-25 to +45 °C	1		0.4
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	-25 to +45 °C	1		0.4

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	-25 to +45 °C	1		0.4
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	-25 to +45 °C	1		0.4
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	0 to +30 °C	1		0.4
10979700	WT490C 80S/840 PSD WB PI5 L1200	-25 to +45 °C	1		0.4
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	-25 to +45 °C	1		0.4
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	-25 to +45 °C	1		0.4
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	0 to +30 °C	1		0.4
10983400	WT490C 80S/840 PSU VWB PI5 L1200	-25 to +45 °C	1		0.4
10984100	WT490C 80S/840 PSD VWB PI5 L1200	-25 to +45 °C	1		0.4
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	-25 to +45 °C	1		0.4
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	-25 to +45 °C	1		0.4
62312500	WT490C 64S/840 PSU WB WA7 L1200	-25 to +45 °C	1		0.4
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	-25 to +45 °C	1		0.4
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	0 to +40 °C	1		0.4
62317000	WT490C 64S/840 PSD WB WA7 L1200	-25 to +45 °C	1		0.4
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	-25 to +45 °C	1		0.4
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	0 to +40 °C	1		0.4
62320000	WT490C 64S/840 PSU VWB WA7 L1200	-25 to +45 °C	1		0.4
62321700	WT490C 64S/840 PSD VWB WA7 L1200	-25 to +45 °C	1		0.4
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	-25 to +45 °C	1		0.4
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	-25 to +45 °C	1		0.4
62324800	WT490C 80S/840 PSU WB WA7 L1200	-25 to +45 °C	1		0.4
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	-25 to +45 °C	1		0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	0 to +30 °C	1		0.4
62327900	WT490C 80S/840 PSD WB WA7 L1200	-25 to +45 °C	1		0.4
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	-25 to +45 °C	1		0.4
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	0 to +30 °C	1		0.4
62330900	WT490C 80S/840 PSU VWB WA7 L1200	-25 to +45 °C	1		0.4
62331600	WT490C 80S/840 PSD VWB WA7 L1200	-25 to +45 °C	1		0.4
62353800	WT490C 42S/840 PSU WB PI5 L1200	-25 to +45 °C	1		0.4
62354500	WT490C 64S/840 PSU WB PI5 L1200	-25 to +45 °C	1		0.4
62355200	WT490C 80S/840 PSU WB PI5 L1200	-25 to +45 °C	1		0.4
62571600	WT490C 42S/840 PSD VWB PI5 L1200	-25 to +45 °C	1		0.4
62752900	WT490C 35S/840 PSU WB PI5 L1200	-25 to +45 °C	1		0.4
62756700	WT490C 64S/840 PSU O PI5 L1200	-25 to +45 °C	1		0.4
62757400	WT490C 64S/840 PSU PCO PI5 L1200	-25 to +45 °C	1		0.4
62760400	WT495C 64S/840 PSU WB PI5 L1200	-35 to +60 °C	1		0.4
62762800	WT495C 64S/840 PSD WB PI5 L1200	-35 to +60 °C	1		0.4
77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1		0.4
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1		0.4
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1		0.4
77394300	WT490C 100S/840 PSD WB PI5 L1200	-25 to +25 °C	-		-
77398100	WT490C 100S/840 PSU WB PI5 L1200	-25 to +25 °C	-		-
62475700	WT490C 64S/840 PSD WB PI5 L1600	-25 to +45 °C	1		0.4
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	-25 to +45 °C	1		0.4
62477100	WT490C 64S/840 PSU WB PI5 L1600	-25 to +45 °C	1		0.4

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
62478800	WT490C 80S/840 PSU WB PI5 L1600	-25 to +45 °C	1		0.4
62481800	WT490C 64S/840 PSD WB WA7 L1600	-25 to +45 °C	1		0.4
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	-25 to +45 °C	1		0.4
62483200	WT490C 64S/840 PSU WB WA7 L1600	-25 to +45 °C	1		0.4
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-25 to +45 °C	1		0.4
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-25 to +45 °C	1		0.4
10958200	WT490C 23S/840 PSD WB PI5 L700	-25 to +45 °C	1		0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
			EN 61000-3-3		
62352100	WT490C 23S/840 PSU WB PI5 L700	-25 to +45 °C	1		0.4
62315600	WT490C 64S/840 PSU WB TCW5 L1200	-25 to +45 °C	1		0.4
62572300	WT490C 64S/840 PSU WB W5 L1200	-25 to +45 °C	1		0.4
62573000	WT490C 80S/840 PSU WB W5 L1200	-25 to +45 °C	1		0.4
62574700	WT490C 64S/840 PSD WB W5 L1200	-25 to +45 °C	1		0.4
62575400	WT490C 80S/840 PSD WB W5 L1200	-25 to +45 °C	1		0.4

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	(0.38, 0.38) SDCM <3
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	(0.38, 0.38) SDCM <3
10990200	WT490C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	(0.38, 0.38) SDCM <3
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	(0.38, 0.38) SDCM <3
10993300	WT490C 80S/840 PSU VWB PI5 L1800	(0.38, 0.38) SDCM <3
10994000	WT490C 80S/840 PSD VWB PI5 L1800	(0.38, 0.38) SDCM <3
10995700	WT490C 100S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
10996400	WT490C 120S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
62357600	WT490C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62358300	WT490C 100S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62359000	WT490C 120S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	(0.38, 0.38) SDCM <3
62758100	WT490C 80S/840 PSU O PI5 L1800	(0.38, 0.38) SDCM <3
62759800	WT490C 80S/840 PSU PCO PI5 L1800	(0.38, 0.38) SDCM <3
62761100	WT495C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62763500	WT495C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
77195600	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	(0.38, 0.38) SDCM <3
77196300	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	(0.38, 0.38) SDCM <3
77395000	WT490C 150S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
77399800	WT490C 150S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62764200	WT492C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
62765900	WT492C 80S/840 PSU WB W5 L1800	(0.38, 0.38) SDCM <3
62766600	WT492C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
62767300	WT492C 80S/840 PSD WB W5 L1800	(0.38, 0.38) SDCM <3
73290200	WT490C 42S/830 PSU WB PI5 L1200	(0.43, 0.40) SDCM <3

Order Code	Full Product Name	Initial chromaticity
10959900	WT490C 42S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
10964300	WT490C 64S/840 PSU WB TC5 L1200	(0.38, 0.38) SDCM <3
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	(0.38, 0.38) SDCM <3
10967400	WT490C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	(0.38, 0.38) SDCM <3
10972800	WT490C 64S/840 PSU VWB PI5 L1200	(0.38, 0.38) SDCM <3
10973500	WT490C 64S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
10979700	WT490C 80S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
10983400	WT490C 80S/840 PSU VWB PI5 L1200	(0.38, 0.38) SDCM <3
10984100	WT490C 80S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	(0.38, 0.38) SDCM <3

Pacific LED Gen5

Order Code	Full Product Name	Initial chromaticity
62312500	WT490C 64S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
62317000	WT490C 64S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
62320000	WT490C 64S/840 PSU VWB WA7 L1200	(0.38, 0.38) SDCM <3
62321700	WT490C 64S/840 PSD VWB WA7 L1200	(0.38, 0.38) SDCM <3
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62324800	WT490C 80S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
62327900	WT490C 80S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
62330900	WT490C 80S/840 PSU VWB WA7 L1200	(0.38, 0.38) SDCM <3
62331600	WT490C 80S/840 PSD VWB WA7 L1200	(0.38, 0.38) SDCM <3
62353800	WT490C 42S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62354500	WT490C 64S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62355200	WT490C 80S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62571600	WT490C 42S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
62752900	WT490C 35S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62756700	WT490C 64S/840 PSU O PI5 L1200	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
62757400	WT490C 64S/840 PSU PCO PI5 L1200	(0.38, 0.38) SDCM <3
62760400	WT495C 64S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62762800	WT495C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
77394300	WT490C 100S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
77398100	WT490C 100S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62475700	WT490C 64S/840 PSD WB PI5 L1600	(0.38, 0.38) SDCM <3
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	(0.38, 0.38) SDCM <3
62477100	WT490C 64S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
62478800	WT490C 80S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
62481800	WT490C 64S/840 PSD WB WA7 L1600	(0.38, 0.38) SDCM <3
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	(0.38, 0.38) SDCM <3
62483200	WT490C 64S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	(0.38, 0.38) SDCM <3
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	(0.38, 0.38) SDCM <3
10958200	WT490C 23S/840 PSD WB PI5 L700	(0.38, 0.38) SDCM <3
62352100	WT490C 23S/840 PSU WB PI5 L700	(0.38, 0.38) SDCM <3
62315600	WT490C 64S/840 PSU WB TCW5 L1200	(0.38, 0.38) SDCM <3
62572300	WT490C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
62573000	WT490C 80S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
62574700	WT490C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
62575400	WT490C 80S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3

Product Data

Order Code	Full Product Name	Product family code
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	WT490C
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	WT490C
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	WT490C
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	WT490C
10990200	WT490C 80S/840 PSD WB PI5 L1800	WT490C
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	WT490C
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	WT490C
10993300	WT490C 80S/840 PSU VWB PI5 L1800	WT490C
10994000	WT490C 80S/840 PSD VWB PI5 L1800	WT490C
10995700	WT490C 100S/840 PSD WB PI5 L1800	WT490C
10996400	WT490C 120S/840 PSD WB PI5 L1800	WT490C
62357600	WT490C 80S/840 PSU WB PI5 L1800	WT490C
62358300	WT490C 100S/840 PSU WB PI5 L1800	WT490C
62359000	WT490C 120S/840 PSU WB PI5 L1800	WT490C
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	WT490C
62758100	WT490C 80S/840 PSU O PI5 L1800	WT490C
62759800	WT490C 80S/840 PSU PCO PI5 L1800	WT490C
62761100	WT495C 80S/840 PSU WB PI5 L1800	WT495C
62763500	WT495C 80S/840 PSD WB PI5 L1800	WT495C
77195600	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	WT490C
77196300	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	WT490C
77395000	WT490C 150S/840 PSD WB PI5 L1800	WT490C
77399800	WT490C 150S/840 PSU WB PI5 L1800	WT490C
62764200	WT492C 64S/840 PSU WB W5 L1200	WT492C


Order Code	Full Product Name	Product family code
62765900	WT492C 80S/840 PSU WB W5 L1800	WT492C
62766600	WT492C 64S/840 PSD WB W5 L1200	WT492C
62767300	WT492C 80S/840 PSD WB W5 L1800	WT492C
73290200	WT490C 42S/830 PSU WB PI5 L1200	WT490C
10959900	WT490C 42S/840 PSD WB PI5 L1200	WT490C
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	WT490C
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	WT490C
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	WT490C
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	WT490C
10964300	WT490C 64S/840 PSU WB TC5 L1200	WT490C
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	WT490C
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	WT490C
10967400	WT490C 64S/840 PSD WB PI5 L1200	WT490C
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	WT490C
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	WT490C
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	WT490C
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	WT490C
10972800	WT490C 64S/840 PSU VWB PI5 L1200	WT490C
10973500	WT490C 64S/840 PSD VWB PI5 L1200	WT490C
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	WT490C
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	WT490C
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	WT490C
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	WT490C
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	WT490C

Pacific LED Gen5


Order Code	Full Product Name	Product family code
10979700	WT490C 80S/840 PSD WB PI5 L1200	WT490C
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	WT490C
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	WT490C
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	WT490C
10983400	WT490C 80S/840 PSU VWB PI5 L1200	WT490C
10984100	WT490C 80S/840 PSD VWB PI5 L1200	WT490C
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	WT490C
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	WT490C
62312500	WT490C 64S/840 PSU WB WA7 L1200	WT490C
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	WT490C
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	WT490C
62317000	WT490C 64S/840 PSD WB WA7 L1200	WT490C
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	WT490C
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	WT490C
62320000	WT490C 64S/840 PSU VWB WA7 L1200	WT490C
62321700	WT490C 64S/840 PSD VWB WA7 L1200	WT490C
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	WT490C
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	WT490C
62324800	WT490C 80S/840 PSU WB WA7 L1200	WT490C
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	WT490C
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	WT490C
62327900	WT490C 80S/840 PSD WB WA7 L1200	WT490C
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	WT490C
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	WT490C
62330900	WT490C 80S/840 PSU VWB WA7 L1200	WT490C
62331600	WT490C 80S/840 PSD VWB WA7 L1200	WT490C
62353800	WT490C 42S/840 PSU WB PI5 L1200	WT490C
62354500	WT490C 64S/840 PSU WB PI5 L1200	WT490C

Order Code	Full Product Name	Product family code
62355200	WT490C 80S/840 PSU WB PI5 L1200	WT490C
62571600	WT490C 42S/840 PSD VWB PI5 L1200	WT490C
62752900	WT490C 35S/840 PSU WB PI5 L1200	WT490C
62756700	WT490C 64S/840 PSU O PI5 L1200	WT490C
62757400	WT490C 64S/840 PSU PCO PI5 L1200	WT490C
62760400	WT495C 64S/840 PSU WB PI5 L1200	WT495C
62762800	WT495C 64S/840 PSD WB PI5 L1200	WT495C
77191800	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	WT490C
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	WT490C
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	WT490C
77394300	WT490C 100S/840 PSD WB PI5 L1200	WT490C
77398100	WT490C 100S/840 PSU WB PI5 L1200	WT490C
62475700	WT490C 64S/840 PSD WB PI5 L1600	WT490C
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	WT490C
62477100	WT490C 64S/840 PSU WB PI5 L1600	WT490C
62478800	WT490C 80S/840 PSU WB PI5 L1600	WT490C
62481800	WT490C 64S/840 PSD WB WA7 L1600	WT490C
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	WT490C
62483200	WT490C 64S/840 PSU WB WA7 L1600	WT490C
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	WT490C
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	WT490C
10958200	WT490C 23S/840 PSD WB PI5 L700	WT490C
62352100	WT490C 23S/840 PSU WB PI5 L700	WT490C
62315600	WT490C 64S/840 PSU WB TCW5 L1200	WT490C
62572300	WT490C 64S/840 PSU WB W5 L1200	WT490C
62573000	WT490C 80S/840 PSU WB W5 L1200	WT490C
62574700	WT490C 64S/840 PSD WB W5 L1200	WT490C
62575400	WT490C 80S/840 PSD WB W5 L1200	WT490C


Polar Wide Diagrams



Polar Normal (separate) - WT490C1 -
910770229590




Polar Normal (separate) - WT490C1 -
910925868249




Polar Normal (separate) - WT490C1 -
910925868292


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868698




Polar Normal (separate) - WT490CI - 910925868259




Polar Normal (separate) - WT490CI - 910925868702




Polar Normal (separate) - WT490CI - 910925868261




Polar Normal (separate) - WT490CI - 910925868413




Polar Normal (separate) - WT490CI - 910925868697



Polar Normal (separate) - WT490CI - 910925868699




Polar Normal (separate) - WT490CI - 910925868706




Polar Normal (separate) - WT490CI - 910925868288


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868414




Polar Normal (separate) - WT490CI - 910925868513




Polar Normal (separate) - WT490CI - 910925868705




Polar Normal (separate) - WT490CI - 910925868419




Polar Normal (separate) - WT490CI - 910925868511




Polar Normal (separate) - WT490CI - 910925868516



Polar Normal (separate) - WT490CI - 910925868701




Polar Normal (separate) - WT490CI - 910925868703




Polar Normal (separate) - WT490CI - 910925868509


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867704




Polar Normal (separate) - WT490CI - 910925867723




Polar Normal (separate) - WT490CI - 910925867732




Polar Normal (separate) - WT490CI - 910925867735




Polar Normal (separate) - WT490CI - 910925867706




Polar Normal (separate) - WT490CI - 910925867712



Polar Normal (separate) - WT490CI - 910925867711




Polar Normal (separate) - WT490CI - 910925867724




Polar Normal (separate) - WT490CI - 910925867726


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867727




Polar Normal (separate) - WT490CI - 910925867720




Polar Normal (separate) - WT490CI - 910925867738




Polar Normal (separate) - WT490CI - 910925867713




Polar Normal (separate) - WT490CI - 910925867717




Polar Normal (separate) - WT490CI - 910925867714



Polar Normal (separate) - WT490CI - 910925867715




Polar Normal (separate) - WT490CI - 910925867716




Polar Normal (separate) - WT490CI - 910925867739


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867708




Polar Normal (separate) - WT490CI - 910925867719




Polar Normal (separate) - WT490CI - 910925867725




Polar Normal (separate) - WT490CI - 910925867737




Polar Normal (separate) - WT490CI - 910925867718




Polar Normal (separate) - WT490CI - 910925867734



Polar Normal (separate) - WT490CI - 910925867721




Polar Normal (separate) - WT490CI - 910925867729




Polar Normal (separate) - WT490CI - 910925868253


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868266




Polar Normal (separate) - WT490CI - 910925868287




Polar Normal (separate) - WT490CI - 910925868289




Polar Normal (separate) - WT490CI - 910925868290




Polar Normal (separate) - WT490CI - 910925868256




Polar Normal (separate) - WT490CI - 910925868264



Polar Normal (separate) - WT490CI - 910925868412




Polar Normal (separate) - WT490CI - 910925868252




Polar Normal (separate) - WT490CI - 910925868262


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868265




Polar Normal (separate) - WT490CI - 910925868510




Polar Normal (separate) - WT490CI - 910925867703




Polar Normal (separate) - WT490CI - 910925867705




Polar Normal (separate) - WT490CI - 910925867707




Polar Normal (separate) - WT490CI - 910925867709



Polar Normal (separate) - WT490CI - 910925867710




Polar Normal (separate) - WT490CI - 910925867722




Polar Normal (separate) - WT490CI - 910925867728


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867731




Polar Normal (separate) - WT490CI - 910925867733




Polar Normal (separate) - WT490CI - 910925867736




Polar Normal (separate) - WT490CI - 910925867743




Polar Normal (separate) - WT490CI - 910925867741




Polar Normal (separate) - WT490CI - 910925867740



Polar Normal (separate) - WT490CI - 910925867744




Polar Normal (separate) - WT490CI - 910925868247




Polar Normal (separate) - WT490CI - 910925868251


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868255




Polar Normal (separate) - WT490CI - 910925868254




Polar Normal (separate) - WT490CI - 910925868258




Polar Normal (separate) - WT490CI - 910925868263




Polar Normal (separate) - WT490CI - 910925868260




Polar Normal (separate) - WT490CI - 910925868257



Polar Normal (separate) - WT490CI - 910925868294




Polar Normal (separate) - WT490CI - 910925868293




Polar Normal (separate) - WT490CI - 910925868415


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868418




Polar Normal (separate) - WT490CI - 910925868420




Polar Normal (separate) - WT490CI - 910925868512




Polar Normal (separate) - WT490CI - 910925868691




Polar Normal (separate) - WT490CI - 910925868695




Polar Normal (separate) - WT490CI - 910925868696



Polar Normal (separate) - WT490CI - 910925868704




Polar Normal (separate) - WT490CI - 910925868707




Polar Normal (separate) - WT490CI - 910925869401


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925869403




Polar Normal (separate) - WT490CI - 910925869405




Polar Normal (separate) - WT490CI - 910925869406




Polar Normal (separate) - WT490CI - 910925869407




Polar Normal (separate) - WT490CI - 910925869408




Polar Normal (separate) - WT490CI - 910925869410



Polar Normal (separate) - WT490CI - 910925868250




Polar Normal (separate) - WT490CI - 910925869610




Polar Normal (separate) - WT490CI - 910925869611

Pacific LED Gen5

Polar Wide Diagrams



Polar Normal (separate) - WT490C1 -
910925869606



Polar Normal (separate) - WT490C1 -
910925869607

