



Robust, connectable luminaire with outstanding performance.

Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in parking garages and warehouses. Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency, and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency,

energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

Applications

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

Versions

Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.
- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.



Pacific LED gen5, L1800



Pacific LED gen5, ATEX 2/22, Wieland connector



Pacific LED gen5, L1200



Pacific LED gen5, L1600


Pacific LED gen5, L700




Pacific LED gen5, Wieland connector




Dimensional drawing




WT492C 64S/840 PSU WB W5 L1200




WT492C 80S/840 PSU WB W5 L1800




PACIFIC LED PRO - 840 neutral white - Power supply unit - Very wide beam - Push-in connector 5-pole




PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole




PACIFIC LED PRO - 840 neutral white - Power supply unit with DALI interface - Wide beam - Push-in connector 5-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit with DALI interface - Wide beam - Push-in connector 7-pole



PACIFIC LED PRO - 840 neutral white - Power supply unit - Wide beam - Push-in connector 5-pole

Product details



Pacific LED gen5, looping connection, 2 entry on one side



Pacific LED gen5 with push in 7-pole (PI7) connector



Pacific LED gen5, Wieland connector



Pacific LED gen5 with WAGO connector



Pacific LED gen5 connection through WAGO connector side view



Pacific LED gen5 with push in 5-pole (P15) connector



Pacific LED gen5 with Wieland connector



Pacific LED gen5 connection through WAGO connector

General Information

Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes

Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Embedded control	InterAct SC100 sensor
------------------	-----------------------

Mechanical and Housing

Housing Color	White
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Explosion hazard class	Zone 2 and 22

Emergency Operation

Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	No

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC plus mark
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3

Light Technical

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)	Optic type
910925867731	WT490C 80S/840 PSU HE NB-HRO PI5L1800	8,000 lm	165 lm/W	Narrow beam - High-rack optic
910925867732	WT490C 80S/840 PSD HE NB-HRO PI5L1800	8,000 lm	165 lm/W	Narrow beam - High-rack optic
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	8,000 lm	165 lm/W	Wide beam
910925867734	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	8,000 lm	154 lm/W	Wide beam
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	8,000 lm	165 lm/W	Wide beam
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	8,000 lm	165 lm/W	Wide beam
910925867737	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	8,000 lm	154 lm/W	Wide beam
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	8,000 lm	165 lm/W	Very wide beam
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	8,000 lm	165 lm/W	Very wide beam
910925867740	WT490C 100S/840 PSD HE WB PI5 L1800	10,000 lm	161 lm/W	Wide beam
910925867741	WT490C 120S/840 PSD HE WB PI5 L1800	12,000 lm	158 lm/W	Wide beam
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	8,000 lm	165 lm/W	Wide beam
910925868293	WT490C 100S/840 PSU HE WB PI5 L1800	10,000 lm	161 lm/W	Wide beam
910925868294	WT490C 120S/840 PSU HE WB PI5 L1800	12,000 lm	158 lm/W	Wide beam
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	8,000 lm	165 lm/W	Wide beam
910925868704	WT492C 64S/840 PSU WB W5 L1200	6,400 lm	160 lm/W	Wide beam
910925868705	WT492C 80S/840 PSU WB W5 L1800	8,000 lm	165 lm/W	Wide beam
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	4,200 lm	162 lm/W	Wide beam
910925867705	WT490C 64S/840 PSU HE NB-HRO PI5L1200	6,400 lm	160 lm/W	Narrow beam - High-rack optic
910925867706	WT490C 64S/840 PSD HE NB-HRO PI5L1200	6,400 lm	162 lm/W	Narrow beam - High-rack optic
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	6,400 lm	160 lm/W	Wide beam

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)	Optic type
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	6,400 lm	160 lm/W	Wide beam
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	6,400 lm	160 lm/W	Wide beam
910925867710	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	6,400 lm	146 lm/W	Wide beam
910925867711	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	6,400 lm	146 lm/W	Wide beam
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	6,400 lm	162 lm/W	Wide beam
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	6,400 lm	162 lm/W	Wide beam
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	6,400 lm	162 lm/W	Wide beam
910925867715	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	6,400 lm	147 lm/W	Wide beam
910925867716	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	6,400 lm	147 lm/W	Wide beam
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	6,400 lm	160 lm/W	Very wide beam
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	6,400 lm	162 lm/W	Very wide beam
910925867719	WT490C 80S/840 PSU HE NB-HRO PI5L1200	8,000 lm	157 lm/W	Narrow beam - High-rack optic
910925867720	WT490C 80S/840 PSD HE NB-HRO PI5L1200	8,000 lm	157 lm/W	Narrow beam - High-rack optic
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	8,000 lm	157 lm/W	Wide beam
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	8,000 lm	157 lm/W	Wide beam
910925867723	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	8,000 lm	146 lm/W	Wide beam
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	8,000 lm	157 lm/W	Wide beam
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	8,000 lm	157 lm/W	Wide beam
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	8,000 lm	157 lm/W	Wide beam
910925867727	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	8,000 lm	146 lm/W	Wide beam
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	8,000 lm	157 lm/W	Very wide beam
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	8,000 lm	157 lm/W	Very wide beam
910925867743	WT490C 64S/840 PSU HE NB-HRO WA7L1200	6,400 lm	160 lm/W	Narrow beam - High-rack optic
910925867744	WT490C 64S/840 PSD HE NB-HRO WA7L1200	6,400 lm	162 lm/W	Narrow beam - High-rack optic
910925868247	WT490C 64S/840 PSU HE WB WA7 L1200	6,400 lm	160 lm/W	Wide beam
910925868249	WT490C 64S/840 PSU HE WB TW3 WA7L1200	6,400 lm	160 lm/W	Wide beam
910925868251	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	6,400 lm	146 lm/W	Wide beam
910925868252	WT490C 64S/840 PSD HE WB WA7 L1200	6,400 lm	162 lm/W	Wide beam
910925868253	WT490C 64S/840 PSD HE WB TW3 WA7L1200	6,400 lm	162 lm/W	Wide beam
910925868254	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	6,400 lm	147 lm/W	Wide beam
910925868255	WT490C 64S/840 PSU HE VWB WA7 L1200	6,400 lm	160 lm/W	Very wide beam
910925868256	WT490C 64S/840 PSD HE VWB WA7 L1200	6,400 lm	162 lm/W	Very wide beam
910925868257	WT490C 80S/840 PSU HE NB-HRO WA7L1200	8,000 lm	157 lm/W	Narrow beam - High-rack optic
910925868258	WT490C 80S/840 PSD HE NB-HRO WA7L1200	8,000 lm	157 lm/W	Narrow beam - High-rack optic
910925868259	WT490C 80S/840 PSU HE WB WA7 L1200	8,000 lm	157 lm/W	Wide beam
910925868260	WT490C 80S/840 PSU HE WB TW3 WA7L1200	8,000 lm	157 lm/W	Wide beam
910925868261	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	8,000 lm	146 lm/W	Wide beam
910925868262	WT490C 80S/840 PSD HE WB WA7 L1200	8,000 lm	157 lm/W	Wide beam
910925868263	WT490C 80S/840 PSD HE WB TW3 WA7L1200	8,000 lm	157 lm/W	Wide beam
910925868264	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	8,000 lm	146 lm/W	Wide beam
910925868265	WT490C 80S/840 PSU HE VWB WA7 L1200	8,000 lm	157 lm/W	Very wide beam
910925868266	WT490C 80S/840 PSD HE VWB WA7 L1200	8,000 lm	157 lm/W	Very wide beam

Order Code	Full Product Name	Luminous Flux	Luminous Efficacy (rated) (Nom)	Optic type
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	4,200 lm	165 lm/W	Wide beam
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	6,400 lm	160 lm/W	Wide beam
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	8,000 lm	157 lm/W	Wide beam
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	4,200 lm	162 lm/W	Very wide beam
910925868699	WT495C 64S/840 PSU HE WB PI5 L1200	6,400 lm	158 lm/W	Wide beam
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	8,000 lm	157 lm/W	Wide beam
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	2,300 lm	160 lm/W	Wide beam
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	2,300 lm	151 lm/W	Wide beam
910925868510	WT490C 64S/840 PSU HE WB W5 L1200	6,400 lm	160 lm/W	Wide beam
910925868511	WT490C 80S/840 PSU HE WB W5 L1200	8,000 lm	157 lm/W	Wide beam
910925868512	WT490C 64S/840 PSD HE WB W5 L1200	6,400 lm	162 lm/W	Wide beam
910925868513	WT490C 80S/840 PSD HE WB W5 L1200	8,000 lm	157 lm/W	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925867731	WT490C 80S/840 PSU HE NB-HRO PI5L1800	48.5 W
910925867732	WT490C 80S/840 PSD HE NB-HRO PI5L1800	48.5 W
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	48.5 W
910925867734	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	52 W
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	48.5 W
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	48.5 W
910925867737	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	52 W
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	48.5 W
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	48.5 W
910925867740	WT490C 100S/840 PSD HE WB PI5 L1800	62 W
910925867741	WT490C 120S/840 PSD HE WB PI5 L1800	76 W
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	48.5 W
910925868293	WT490C 100S/840 PSU HE WB PI5 L1800	62 W
910925868294	WT490C 120S/840 PSU HE WB PI5 L1800	76 W
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	48.5 W
910925868704	WT492C 64S/840 PSU WB W5 L1200	40 W
910925868705	WT492C 80S/840 PSU WB W5 L1800	49 W
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	26 W
910925867705	WT490C 64S/840 PSU HE NB-HRO PI5L1200	40 W
910925867706	WT490C 64S/840 PSD HE NB-HRO PI5L1200	39.5 W
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	40 W
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	40 W
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	40 W
910925867710	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	44 W
910925867711	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	44 W
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	39.5 W
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	39.5 W

Order Code	Full Product Name	Power Consumption
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	39.5 W
910925867715	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	43.5 W
910925867716	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	43.5 W
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	40 W
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	39.5 W
910925867719	WT490C 80S/840 PSU HE NB-HRO PI5L1200	51 W
910925867720	WT490C 80S/840 PSD HE NB-HRO PI5L1200	51 W
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	51 W
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	51 W
910925867723	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	55 W
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	51 W
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	51 W
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	51 W
910925867727	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	55 W
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	51 W
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	51 W
910925867743	WT490C 64S/840 PSU HE NB-HRO WA7L1200	40 W
910925867744	WT490C 64S/840 PSD HE NB-HRO WA7L1200	39.5 W
910925868247	WT490C 64S/840 PSU HE WB WA7 L1200	40 W
910925868249	WT490C 64S/840 PSU HE WB TW3 WA7L1200	40 W
910925868251	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	44 W
910925868252	WT490C 64S/840 PSD HE WB WA7 L1200	39.5 W
910925868253	WT490C 64S/840 PSD HE WB TW3 WA7L1200	39.5 W
910925868254	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	43.5 W
910925868255	WT490C 64S/840 PSU HE VWB WA7 L1200	40 W
910925868256	WT490C 64S/840 PSD HE VWB WA7 L1200	39.5 W
910925868257	WT490C 80S/840 PSU HE NB-HRO WA7L1200	51 W
910925868258	WT490C 80S/840 PSD HE NB-HRO WA7L1200	51 W
910925868259	WT490C 80S/840 PSU HE WB WA7 L1200	51 W
910925868260	WT490C 80S/840 PSU HE WB TW3 WA7L1200	51 W
910925868261	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	55 W
910925868262	WT490C 80S/840 PSD HE WB WA7 L1200	51 W
910925868263	WT490C 80S/840 PSD HE WB TW3 WA7L1200	51 W
910925868264	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	55 W
910925868265	WT490C 80S/840 PSU HE VWB WA7 L1200	51 W
910925868266	WT490C 80S/840 PSD HE VWB WA7 L1200	51 W
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	25.5 W
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	40 W
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	51 W
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	26 W
910925868699	WT495C 64S/840 PSU HE WB PI5 L1200	40.5 W
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	51 W

Order Code	Full Product Name	Power Consumption
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	14.4 W
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	15.2 W
910925868510	WT490C 64S/840 PSU HE WB W5 L1200	40 W
910925868511	WT490C 80S/840 PSU HE WB W5 L1200	51 W
910925868512	WT490C 64S/840 PSD HE WB W5 L1200	39.5 W
910925868513	WT490C 80S/840 PSD HE WB W5 L1200	51 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925867731	WT490C 80S/840 PSU HE NB-HRO PI5L1800	No
910925867732	WT490C 80S/840 PSD HE NB-HRO PI5L1800	Yes
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	No
910925867734	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	No
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	Yes
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	Yes
910925867737	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	Yes
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	No
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	Yes
910925867740	WT490C 100S/840 PSD HE WB PI5 L1800	Yes
910925867741	WT490C 120S/840 PSD HE WB PI5 L1800	Yes
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	No
910925868293	WT490C 100S/840 PSU HE WB PI5 L1800	No
910925868294	WT490C 120S/840 PSU HE WB PI5 L1800	No
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	Yes
910925868704	WT492C 64S/840 PSU WB W5 L1200	No
910925868705	WT492C 80S/840 PSU WB W5 L1800	No
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	Yes
910925867705	WT490C 64S/840 PSU HE NB-HRO PI5L1200	No
910925867706	WT490C 64S/840 PSD HE NB-HRO PI5L1200	Yes
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	No
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	No
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	No
910925867710	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	No
910925867711	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	No
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	Yes
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	Yes
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	Yes
910925867715	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	Yes
910925867716	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	Yes
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	No
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	Yes
910925867719	WT490C 80S/840 PSU HE NB-HRO PI5L1200	No

Order Code	Full Product Name	Dimmable
910925867720	WT490C 80S/840 PSD HE NB-HRO PI5L1200	Yes
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	No
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	No
910925867723	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	No
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	Yes
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	Yes
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	Yes
910925867727	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	Yes
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	No
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	Yes
910925867743	WT490C 64S/840 PSU HE NB-HRO WA7L1200	No
910925867744	WT490C 64S/840 PSD HE NB-HRO WA7L1200	Yes
910925868247	WT490C 64S/840 PSU HE WB WA7 L1200	No
910925868249	WT490C 64S/840 PSU HE WB TW3 WA7L1200	No
910925868251	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	No
910925868252	WT490C 64S/840 PSD HE WB WA7 L1200	Yes
910925868253	WT490C 64S/840 PSD HE WB TW3 WA7L1200	Yes
910925868254	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	Yes
910925868255	WT490C 64S/840 PSU HE VWB WA7 L1200	No
910925868256	WT490C 64S/840 PSD HE VWB WA7 L1200	Yes
910925868257	WT490C 80S/840 PSU HE NB-HRO WA7L1200	No
910925868258	WT490C 80S/840 PSD HE NB-HRO WA7L1200	Yes
910925868259	WT490C 80S/840 PSU HE WB WA7 L1200	No
910925868260	WT490C 80S/840 PSU HE WB TW3 WA7L1200	No
910925868261	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	No
910925868262	WT490C 80S/840 PSD HE WB WA7 L1200	Yes
910925868263	WT490C 80S/840 PSD HE WB TW3 WA7L1200	Yes
910925868264	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	Yes
910925868265	WT490C 80S/840 PSU HE VWB WA7 L1200	No
910925868266	WT490C 80S/840 PSD HE VWB WA7 L1200	Yes
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	No
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	No
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	No
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	Yes
910925868699	WT495C 64S/840 PSU HE WB PI5 L1200	No
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	No
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	Yes
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	No
910925868510	WT490C 64S/840 PSU HE WB W5 L1200	No
910925868511	WT490C 80S/840 PSU HE WB W5 L1200	No
910925868512	WT490C 64S/840 PSD HE WB W5 L1200	Yes
910925868513	WT490C 80S/840 PSD HE WB W5 L1200	Yes

Emergency Operation

Order Code	Full Product Name	Emergency lighting
910925867731	WT490C 80S/840 PSU HE NB-HRO PI5L1800	-
910925867732	WT490C 80S/840 PSD HE NB-HRO PI5L1800	-
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	-
910925867734	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	Emergency lighting 3 hours duration Pro version
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	-
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	-
910925867737	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	Emergency lighting 3 hours duration with DALI interface
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	-
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	-
910925867740	WT490C 100S/840 PSD HE WB PI5 L1800	-
910925867741	WT490C 120S/840 PSD HE WB PI5 L1800	-
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	-
910925868293	WT490C 100S/840 PSU HE WB PI5 L1800	-
910925868294	WT490C 120S/840 PSU HE WB PI5 L1800	-
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	-
910925868704	WT492C 64S/840 PSU WB W5 L1200	-
910925868705	WT492C 80S/840 PSU WB W5 L1800	-
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	-
910925867705	WT490C 64S/840 PSU HE NB-HRO PI5L1200	-
910925867706	WT490C 64S/840 PSD HE NB-HRO PI5L1200	-
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	-
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	-
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	-
910925867710	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version
910925867711	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	Emergency lighting 3 hours duration Pro version
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	-
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	-
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	-
910925867715	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	Emergency lighting 3 hours duration with DALI interface
910925867716	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	Emergency lighting 3 hours duration with DALI interface
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	-
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	-
910925867719	WT490C 80S/840 PSU HE NB-HRO PI5L1200	-
910925867720	WT490C 80S/840 PSD HE NB-HRO PI5L1200	-
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	-
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	-
910925867723	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	-
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	-
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	-
910925867727	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	Emergency lighting 3 hours duration with DALI interface

Order Code	Full Product Name	Emergency lighting
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	-
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	-
910925867743	WT490C 64S/840 PSU HE NB-HRO WA7L1200	-
910925867744	WT490C 64S/840 PSD HE NB-HRO WA7L1200	-
910925868247	WT490C 64S/840 PSU HE WB WA7 L1200	-
910925868249	WT490C 64S/840 PSU HE WB TW3 WA7L1200	-
910925868251	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version
910925868252	WT490C 64S/840 PSD HE WB WA7 L1200	-
910925868253	WT490C 64S/840 PSD HE WB TW3 WA7L1200	-
910925868254	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	Emergency lighting 3 hours duration with DALI interface
910925868255	WT490C 64S/840 PSU HE VWB WA7 L1200	-
910925868256	WT490C 64S/840 PSD HE VWB WA7 L1200	-
910925868257	WT490C 80S/840 PSU HE NB-HRO WA7L1200	-
910925868258	WT490C 80S/840 PSD HE NB-HRO WA7L1200	-
910925868259	WT490C 80S/840 PSU HE WB WA7 L1200	-
910925868260	WT490C 80S/840 PSU HE WB TW3 WA7L1200	-
910925868261	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version
910925868262	WT490C 80S/840 PSD HE WB WA7 L1200	-
910925868263	WT490C 80S/840 PSD HE WB TW3 WA7L1200	-
910925868264	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	Emergency lighting 3 hours duration with DALI interface
910925868265	WT490C 80S/840 PSU HE VWB WA7 L1200	-
910925868266	WT490C 80S/840 PSD HE VWB WA7 L1200	-
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	-
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	-
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	-
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	-
910925868699	WT495C 64S/840 PSU HE WB PI5 L1200	-
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	-
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	-
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	-
910925868510	WT490C 64S/840 PSU HE WB W5 L1200	-
910925868511	WT490C 80S/840 PSU HE WB W5 L1200	-
910925868512	WT490C 64S/840 PSD HE WB W5 L1200	-
910925868513	WT490C 80S/840 PSD HE WB W5 L1200	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range
910925867731	WT490C 80S/840 PSU HE NB-HRO PI5L1800	-25 to +45 °C
910925867732	WT490C 80S/840 PSD HE NB-HRO PI5L1800	-25 to +45 °C
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	-25 to +45 °C
910925867734	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	0 to +30 °C
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	-25 to +45 °C

Order Code	Full Product Name	Ambient temperature range
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	-25 to +45 °C
910925867737	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	0 to +30 °C
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	-25 to +45 °C
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	-25 to +45 °C
910925867740	WT490C 100S/840 PSD HE WB PI5 L1800	-25 to +45 °C
910925867741	WT490C 120S/840 PSD HE WB PI5 L1800	-25 to +45 °C
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	-25 to +45 °C
910925868293	WT490C 100S/840 PSU HE WB PI5 L1800	-25 to +45 °C
910925868294	WT490C 120S/840 PSU HE WB PI5 L1800	-25 to +45 °C
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	-25 to +45 °C
910925868704	WT492C 64S/840 PSU WB W5 L1200	-25 to +45 °C
910925868705	WT492C 80S/840 PSU WB W5 L1800	-25 to +45 °C
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	-25 to +45 °C
910925867705	WT490C 64S/840 PSU HE NB-HRO PI5L1200	-25 to +45 °C
910925867706	WT490C 64S/840 PSD HE NB-HRO PI5L1200	-25 to +45 °C
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	-25 to +45 °C
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	-25 to +45 °C
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	-25 to +45 °C
910925867710	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	0 to +40 °C
910925867711	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	0 to +40 °C
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	-25 to +45 °C
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	-25 to +45 °C
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	-25 to +45 °C
910925867715	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	0 to +40 °C
910925867716	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	0 to +40 °C
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	-25 to +45 °C
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	-25 to +45 °C
910925867719	WT490C 80S/840 PSU HE NB-HRO PI5L1200	-25 to +45 °C
910925867720	WT490C 80S/840 PSD HE NB-HRO PI5L1200	-25 to +45 °C
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	-25 to +45 °C
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	-25 to +45 °C
910925867723	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	0 to +30 °C
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	-25 to +45 °C
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	-25 to +45 °C
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	-25 to +45 °C
910925867727	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	0 to +30 °C
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	-25 to +45 °C
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	-25 to +45 °C
910925867743	WT490C 64S/840 PSU HE NB-HRO WA7L1200	-25 to +45 °C
910925867744	WT490C 64S/840 PSD HE NB-HRO WA7L1200	-25 to +45 °C
910925868247	WT490C 64S/840 PSU HE WB WA7 L1200	-25 to +45 °C
910925868249	WT490C 64S/840 PSU HE WB TW3 WA7L1200	-25 to +45 °C

Order Code	Full Product Name	Ambient temperature range
910925868251	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	0 to +40 °C
910925868252	WT490C 64S/840 PSD HE WB WA7 L1200	-25 to +45 °C
910925868253	WT490C 64S/840 PSD HE WB TW3 WA7L1200	-25 to +45 °C
910925868254	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	0 to +40 °C
910925868255	WT490C 64S/840 PSU HE VWB WA7 L1200	-25 to +45 °C
910925868256	WT490C 64S/840 PSD HE VWB WA7 L1200	-25 to +45 °C
910925868257	WT490C 80S/840 PSU HE NB-HRO WA7L1200	-25 to +45 °C
910925868258	WT490C 80S/840 PSD HE NB-HRO WA7L1200	-25 to +45 °C
910925868259	WT490C 80S/840 PSU HE WB WA7 L1200	-25 to +45 °C
910925868260	WT490C 80S/840 PSU HE WB TW3 WA7L1200	-25 to +45 °C
910925868261	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	0 to +30 °C
910925868262	WT490C 80S/840 PSD HE WB WA7 L1200	-25 to +45 °C
910925868263	WT490C 80S/840 PSD HE WB TW3 WA7L1200	-25 to +45 °C
910925868264	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	0 to +30 °C
910925868265	WT490C 80S/840 PSU HE VWB WA7 L1200	-25 to +45 °C
910925868266	WT490C 80S/840 PSD HE VWB WA7 L1200	-25 to +45 °C
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	-25 to +45 °C
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	-25 to +45 °C
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	-25 to +45 °C
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	-25 to +45 °C
910925868699	WT495C 64S/840 PSU HE WB PI5 L1200	-35 to +60 °C
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	-25 to +45 °C
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	-25 to +45 °C
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	-25 to +45 °C
910925868510	WT490C 64S/840 PSU HE WB W5 L1200	-25 to +45 °C
910925868511	WT490C 80S/840 PSU HE WB W5 L1200	-25 to +45 °C
910925868512	WT490C 64S/840 PSD HE WB W5 L1200	-25 to +45 °C
910925868513	WT490C 80S/840 PSD HE WB W5 L1200	-25 to +45 °C


Product Data

Order Code	Full Product Name	Product family code
910925867731	WT490C 80S/840 PSU HE NB-HRO PI5L1800	WT490C
910925867732	WT490C 80S/840 PSD HE NB-HRO PI5L1800	WT490C
910925867733	WT490C 80S/840 PSU HE WB TW3 PI5L1800	WT490C
910925867734	WT490C 80S/840 PSU HE WB ELP3 PI5 L1800	WT490C
910925867735	WT490C 80S/840 PSD HE WB PI5 L1800	WT490C
910925867736	WT490C 80S/840 PSD HE WB TW3 PI7L1800	WT490C
910925867737	WT490C 80S/840 PSD HE WB ELD3 PI7 L1800	WT490C
910925867738	WT490C 80S/840 PSU HE VWB PI5 L1800	WT490C
910925867739	WT490C 80S/840 PSD HE VWB PI5 L1800	WT490C
910925867740	WT490C 100S/840 PSD HE WB PI5 L1800	WT490C
910925867741	WT490C 120S/840 PSD HE WB PI5 L1800	WT490C


Order Code	Full Product Name	Product family code
910925868292	WT490C 80S/840 PSU HE WB PI5 L1800	WT490C
910925868293	WT490C 100S/840 PSU HE WB PI5 L1800	WT490C
910925868294	WT490C 120S/840 PSU HE WB PI5 L1800	WT490C
910925868516	WT490C 80S/840 SIA HE WB IA9 PI5L1800	WT490C
910925868704	WT492C 64S/840 PSU WB W5 L1200	WT492C
910925868705	WT492C 80S/840 PSU WB W5 L1800	WT492C
910925867704	WT490C 42S/840 PSD HE WB PI5 L1200	WT490C
910925867705	WT490C 64S/840 PSU HE NB-HRO PI5L1200	WT490C
910925867706	WT490C 64S/840 PSD HE NB-HRO PI5L1200	WT490C
910925867707	WT490C 64S/840 PSU HE WB TW1 PI5L1200	WT490C
910925867708	WT490C 64S/840 PSU HE WB TW3 PI5L1200	WT490C
910925867709	WT490C 64S/840 PSU HE WB TC5 L1200	WT490C
910925867710	WT490C 64S/840 PSU HE WB ELP3 PI5 L1200	WT490C
910925867711	WT490C 64S/840 PSU HE WB ELP3 TW1 PI5 L1	WT490C
910925867712	WT490C 64S/840 PSD HE WB PI5 L1200	WT490C
910925867713	WT490C 64S/840 PSD HE WB TW1 PI5L1200	WT490C
910925867714	WT490C 64S/840 PSD HE WB TW3 PI7L1200	WT490C
910925867715	WT490C 64S/840 PSD HE WB ELD3 PI7 L1200	WT490C
910925867716	WT490C 64S/840 PSD HE WB ELD3 TW1 PI7 L1	WT490C
910925867717	WT490C 64S/840 PSU HE VWB PI5 L1200	WT490C
910925867718	WT490C 64S/840 PSD HE VWB PI5 L1200	WT490C
910925867719	WT490C 80S/840 PSU HE NB-HRO PI5L1200	WT490C
910925867720	WT490C 80S/840 PSD HE NB-HRO PI5L1200	WT490C
910925867721	WT490C 80S/840 PSU HE WB TW1 PI5L1200	WT490C
910925867722	WT490C 80S/840 PSU HE WB TW3 PI5L1200	WT490C
910925867723	WT490C 80S/840 PSU HE WB ELP3 PI5 L1200	WT490C
910925867724	WT490C 80S/840 PSD HE WB PI5 L1200	WT490C
910925867725	WT490C 80S/840 PSD HE WB TW1 PI5L1200	WT490C
910925867726	WT490C 80S/840 PSD HE WB TW3 PI7L1200	WT490C
910925867727	WT490C 80S/840 PSD HE WB ELD3 PI7 L1200	WT490C
910925867728	WT490C 80S/840 PSU HE VWB PI5 L1200	WT490C
910925867729	WT490C 80S/840 PSD HE VWB PI5 L1200	WT490C
910925867743	WT490C 64S/840 PSU HE NB-HRO WA7L1200	WT490C
910925867744	WT490C 64S/840 PSD HE NB-HRO WA7L1200	WT490C
910925868247	WT490C 64S/840 PSU HE WB WA7 L1200	WT490C
910925868249	WT490C 64S/840 PSU HE WB TW3 WA7L1200	WT490C
910925868251	WT490C 64S/840 PSU HE WB ELP3 WA7 L1200	WT490C
910925868252	WT490C 64S/840 PSD HE WB WA7 L1200	WT490C
910925868253	WT490C 64S/840 PSD HE WB TW3 WA7L1200	WT490C
910925868254	WT490C 64S/840 PSD HE WB ELD3 WA7 L1200	WT490C
910925868255	WT490C 64S/840 PSU HE VWB WA7 L1200	WT490C
910925868256	WT490C 64S/840 PSD HE VWB WA7 L1200	WT490C

Order Code	Full Product Name	Product family code
910925868257	WT490C 80S/840 PSU HE NB-HRO WA7L1200	WT490C
910925868258	WT490C 80S/840 PSD HE NB-HRO WA7L1200	WT490C
910925868259	WT490C 80S/840 PSU HE WB WA7 L1200	WT490C
910925868260	WT490C 80S/840 PSU HE WB TW3 WA7L1200	WT490C
910925868261	WT490C 80S/840 PSU HE WB ELP3 WA7 L1200	WT490C
910925868262	WT490C 80S/840 PSD HE WB WA7 L1200	WT490C
910925868263	WT490C 80S/840 PSD HE WB TW3 WA7L1200	WT490C
910925868264	WT490C 80S/840 PSD HE WB ELD3 WA7 L1200	WT490C
910925868265	WT490C 80S/840 PSU HE VWB WA7 L1200	WT490C
910925868266	WT490C 80S/840 PSD HE VWB WA7 L1200	WT490C
910925868288	WT490C 42S/840 PSU HE WB PI5 L1200	WT490C
910925868289	WT490C 64S/840 PSU HE WB PI5 L1200	WT490C
910925868290	WT490C 80S/840 PSU HE WB PI5 L1200	WT490C
910925868509	WT490C 42S/840 PSD HE VWB PI5 L1200	WT490C
910925868699	WT495C 64S/840 PSU HE WB PI5 L1200	WT495C
910925868415	WT490C 80S/840 PSU HE WB PI5 L1600	WT490C
910925867703	WT490C 23S/840 PSD HE WB PI5 L700	WT490C
910925868287	WT490C 23S/840 PSU HE WB PI5 L700	WT490C
910925868510	WT490C 64S/840 PSU HE WB W5 L1200	WT490C
910925868511	WT490C 80S/840 PSU HE WB W5 L1200	WT490C
910925868512	WT490C 64S/840 PSD HE WB W5 L1200	WT490C
910925868513	WT490C 80S/840 PSD HE WB W5 L1200	WT490C


Polar normal diagrams




WT490CI - 910925868249




WT490CI - 910925868292




WT490CI - 910925868259




WT490CI - 910925868261




WT490CI - 910925868699




WT490CI - 910925868288




WT490CI - 910925868513




WT490CI - 910925868705




WT490CI - 910925868511




WT490CI - 910925868516




WT490CI - 910925868509




WT490CI - 910925867704




WT490CI - 910925867723




WT490CI - 910925867732




WT490CI - 910925867735




WT490CI - 910925867706




WT490CI - 910925867712




WT490CI - 910925867711




WT490CI - 910925867724




WT490CI - 910925867726




WT490CI - 910925867727




WT490CI - 910925867720




WT490CI - 910925867738




WT490CI - 910925867713




WT490CI - 910925867717




WT490CI - 910925867714




WT490CI - 910925867715




WT490CI - 910925867716




WT490CI - 910925867739




WT490CI - 910925867708




WT490CI - 910925867719




WT490CI - 910925867725




WT490CI - 910925867737




WT490CI - 910925867718




WT490CI - 910925867734




WT490CI - 910925867721




WT490CI - 910925867729




WT490CI - 910925868253




WT490CI - 910925868266




WT490CI - 910925868287




WT490CI - 910925868289




WT490CI - 910925868290




WT490CI - 910925868256




WT490CI - 910925868264




WT490CI - 910925868252




WT490CI - 910925868262




WT490CI - 910925868265




WT490CI - 910925868510




WT490CI - 910925867703




WT490CI - 910925867705




WT490CI - 910925867707




WT490CI - 910925867709




WT490CI - 910925867710




WT490CI - 910925867722




WT490CI - 910925867728




WT490CI - 910925867731




WT490CI - 910925867733




WT490CI - 910925867736




WT490CI - 910925867743




WT490CI - 910925867741




WT490CI - 910925867740




WT490CI - 910925867744




WT490CI - 910925868247




WT490CI - 910925868251




WT490CI - 910925868255




WT490CI - 910925868254




WT490CI - 910925868258




WT490CI - 910925868263




WT490CI - 910925868260




WT490CI - 910925868257




WT490CI - 910925868294




WT490CI - 910925868293



WT490CI - 910925868415



WT490CI - 910925868512



WT490CI - 910925868704