



# Safe & Reliable

## Essential Smartbright Projector Gen 2

Essential SmartBright Projector ST033T is a value for money product designed for Mass market trade. It is designed to replace halogen and CDM-standard-based projectors for retail and hospitality applications. This track based luminaire supports retailers to let their products stand out, or highlight certain objects. The clean and contemporary design with integrated driver, and choice in 24 or 36 degree beam angle makes the Essential SmartBright Projector relevant to many applications. The choice of 2 colors in White and Black helps the Retailer to choose products best suited to blend into the Store Environment. Compared to its predecessor, it is not only cost effective, but also a more sleek and lighter product design. The product family includes 1M and 2M Track in Black and white color with I and L connector to support various applications.

### Benefits

- Reduced operating costs thanks to energy savings and longer lifetime, compared to conventional CDM-standard-based projectors
- Value for Money product for Mass market retail applications
- Clean, simple finish ensures Essential SmartBright Projector blends into many interior designs.

### Features

- Unobtrusive design in white or black finish
- 24 and 36 degree beam angle with Lumen output ranging from 800-2500 Lm.
- Energy-efficient: 80 lm/W
- Integrated driver and uniform track adaptor
- color temperature 3000 or 4000 K

### Application

- Fashion
- Retail
- Hospitality

# Essential Smartbright Projector Gen 2

## Versions







Essential SmartBright Projector Gen 2



Essential SmartBright Projector Gen 2

## Dimensional drawing



## Product details



Essential SmartBright Projector  
Gen 2

# Essential Smartbright Projector Gen 2

General Information	
Driver included	Yes
Gear	EB
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	90
Number of light sources	1
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Controls and Dimming	
Dimmable	-
Maximum dim level	Not applicable
Mechanical and Housing	
Optical cover type	Polycarbonate
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 °C to 45 °C
CE mark	No
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-0%,+20%

## Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401832287	STO33T G2 LED8/930 10W I MB BK GM	24 degree(s)	3000 K	80 lm/W	800 lm
911401832387	STO33T G2 LED8/930 10W I WB BK GM	36 degree(s)	3000 K	80 lm/W	800 lm
911401832487	STO33T G2 LED8/940 10W I MB BK GM	24 degree(s)	4000 K	85 lm/W	850 lm
911401832587	STO33T G2 LED8/940 10W I WB BK GM	36 degree(s)	4000 K	85 lm/W	850 lm
911401834787	STO33T G2 LED8/930 10W I MB BK CN	24 degree(s)	3000 K	80 lm/W	800 lm
911401834987	STO33T G2 LED8/940 10W I MB BK CN	24 degree(s)	4000 K	85 lm/W	850 lm
911401835187	STO33T G2 LED8/930 10W I WB BK CN	36 degree(s)	3000 K	80 lm/W	800 lm
911401835387	STO33T G2 LED8/940 10W I WB BK CN	36 degree(s)	4000 K	85 lm/W	850 lm
911401833087	STO33T G2 LED17/930 20W I MB BK GM	24 degree(s)	3000 K	80 lm/W	1,600 lm
911401833187	STO33T G2 LED17/930 20W I WB BK GM	36 degree(s)	3000 K	80 lm/W	1,600 lm
911401833287	STO33T G2 LED17/940 20W I MB BK GM	24 degree(s)	4000 K	85 lm/W	1,700 lm
911401833387	STO33T G2 LED17/940 20W I WB BK GM	36 degree(s)	4000 K	85 lm/W	1,700 lm
911401835587	STO33T G2 LED17/930 20W I MB BK CN	24 degree(s)	3000 K	80 lm/W	1,600 lm
911401835787	STO33T G2 LED17/940 20W I MB BK CN	24 degree(s)	4000 K	85 lm/W	1,700 lm
911401835987	STO33T G2 LED17/930 20W I WB BK CN	36 degree(s)	3000 K	80 lm/W	1,600 lm
911401836187	STO33T G2 LED17/940 20W I WB BK CN	36 degree(s)	4000 K	85 lm/W	1,700 lm
911401832687	STO33T G2 LED17/930 20W I MB WH GM	24 degree(s)	3000 K	80 lm/W	1,600 lm
911401832787	STO33T G2 LED17/930 20W I WB WH GM	36 degree(s)	3000 K	80 lm/W	1,600 lm
911401832887	STO33T G2 LED17/940 20W I MB WH GM	24 degree(s)	4000 K	85 lm/W	850 lm
911401832987	STO33T G2 LED17/940 20W I WB WH GM	36 degree(s)	4000 K	85 lm/W	1,700 lm
911401835487	STO33T G2 LED17/930 20W I MB WH CN	24 degree(s)	3000 K	80 lm/W	1,600 lm
911401835687	STO33T G2 LED17/940 20W I MB WH CN	24 degree(s)	4000 K	85 lm/W	1,700 lm
911401835887	STO33T G2 LED17/930 20W I WB WH CN	36 degree(s)	3000 K	80 lm/W	1,600 lm
911401836087	STO33T G2 LED17/940 20W I WB WH CN	36 degree(s)	4000 K	85 lm/W	1,700 lm

## Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401831887	ST033T G2 LED8/930 10W I MB WH GM	24 degree(s)	3000 K	80 lm/W	800 lm
911401831987	ST033T G2 LED8/930 10W I WB WH GM	36 degree(s)	3000 K	80 lm/W	800 lm
911401832087	ST033T G2 LED8/940 10W I MB WH GM	24 degree(s)	4000 K	80 lm/W	800 lm
911401832187	ST033T G2 LED8/940 10W I WB WH GM	36 degree(s)	4000 K	85 lm/W	850 lm
911401834687	ST033T G2 LED8/930 10W I MB WH CN	24 degree(s)	3000 K	80 lm/W	800 lm
911401834887	ST033T G2 LED8/940 10W I MB WH CN	24 degree(s)	4000 K	85 lm/W	850 lm
911401835087	ST033T G2 LED8/930 10W I WB WH CN	36 degree(s)	3000 K	80 lm/W	800 lm
911401835287	ST033T G2 LED8/940 10W I WB WH CN	36 degree(s)	4000 K	85 lm/W	850 lm
911401833887	ST033T G2 LED25/930 33W I MB BK GM	24 degree(s)	3000 K	80 lm/W	2,640 lm
911401833987	ST033T G2 LED25/930 33W I WB BK GM	36 degree(s)	3000 K	80 lm/W	2,640 lm
911401834087	ST033T G2 LED25/940 33W I MB BK GM	24 degree(s)	4000 K	85 lm/W	2,805 lm
911401834187	ST033T G2 LED25/940 33W I WB BK GM	36 degree(s)	4000 K	85 lm/W	2,805 lm
911401836387	ST033T G2 LED25/930 33W I MB BK CN	24 degree(s)	3000 K	80 lm/W	2,640 lm
911401836587	ST033T G2 LED25/940 33W I MB BK CN	24 degree(s)	4000 K	85 lm/W	2,805 lm
911401836787	ST033T G2 LED25/930 33W I WB BK CN	36 degree(s)	3000 K	80 lm/W	2,640 lm
911401836987	ST033T G2 LED25/940 33W I WB BK CN	36 degree(s)	4000 K	85 lm/W	2,805 lm
911401831687	ST033T G2 LED5/930 7W I WB BK GM	36 degree(s)	3000 K	85 lm/W	595 lm
911401831787	ST033T G2 LED5/940 7W I WB BK GM	36 degree(s)	4000 K	90 lm/W	640 lm
911401834287	ST033T G2 LED5/940 7W I WB BK CN	36 degree(s)	4000 K	90 lm/W	640 lm
911401834387	ST033T G2 LED5/930 7W I WB BK CN	36 degree(s)	3000 K	85 lm/W	595 lm
911401833487	ST033T G2 LED25/930 33W I MB WH GM	24 degree(s)	3000 K	80 lm/W	2,640 lm
911401833587	ST033T G2 LED25/930 33W I WB WH GM	36 degree(s)	3000 K	80 lm/W	2,640 lm
911401833687	ST033T G2 LED25/940 33W I MB WH GM	24 degree(s)	4000 K	85 lm/W	2,805 lm
911401833787	ST033T G2 LED25/940 33W I WB WH GM	36 degree(s)	4000 K	85 lm/W	2,805 lm
911401836287	ST033T G2 LED25/930 33W I MB WH CN	24 degree(s)	3000 K	80 lm/W	2,640 lm

## Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401836487	ST033T G2 LED25/940 33W I MB WH CN	24 degree(s)	4000 K	85 lm/W	2,805 lm
911401836687	ST033T G2 LED25/930 33W I WB WH CN	36 degree(s)	3000 K	80 lm/W	2,640 lm
911401836887	ST033T G2 LED25/940 33W I WB WH CN	36 degree(s)	4000 K	85 lm/W	2,805 lm
911401831487	ST033T G2 LED5/930 7W I WB WH GM	36 degree(s)	3000 K	85 lm/W	595 lm
911401831587	ST033T G2 LED5/940 7W I WB WH GM	36 degree(s)	4000 K	90 lm/W	640 lm
911401834487	ST033T G2 LED5/940 7W I WB WH CN	36 degree(s)	4000 K	90 lm/W	640 lm
911401834587	ST033T G2 LED5/930 7W I WB WH CN	36 degree(s)	3000 K	85 lm/W	595 lm

### Light Technical (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
911401832287	ST033T G2 LED8/930 10W I MB BK GM	Beam angle 24°	911401834687	ST033T G2 LED8/930 10W I MB WH CN	Beam angle 24°
911401832387	ST033T G2 LED8/930 10W I WB BK GM	Beam angle 36°	911401834887	ST033T G2 LED8/940 10W I MB WH CN	Beam angle 24°
911401832487	ST033T G2 LED8/940 10W I MB BK GM	Beam angle 24°	911401835087	ST033T G2 LED8/930 10W I WB WH CN	Beam angle 36°
911401832587	ST033T G2 LED8/940 10W I WB BK GM	Beam angle 36°	911401835287	ST033T G2 LED8/940 10W I WB WH CN	Beam angle 36°
911401834787	ST033T G2 LED8/930 10W I MB BK CN	Beam angle 24°	911401833887	ST033T G2 LED25/930 33W I MB BK GM	Beam angle 24°
911401834987	ST033T G2 LED8/940 10W I MB BK CN	Beam angle 24°	911401833987	ST033T G2 LED25/930 33W I WB BK GM	Beam angle 36°
911401835187	ST033T G2 LED8/930 10W I WB BK CN	Beam angle 36°	911401834087	ST033T G2 LED25/940 33W I MB BK GM	Beam angle 24°
911401835387	ST033T G2 LED8/940 10W I WB BK CN	Beam angle 36°	911401834187	ST033T G2 LED25/940 33W I WB BK GM	Beam angle 36°
911401833087	ST033T G2 LED17/930 20W I MB BK GM	Beam angle 24°	911401836387	ST033T G2 LED25/930 33W I MB BK CN	Beam angle 24°
911401833187	ST033T G2 LED17/930 20W I WB BK GM	Beam angle 36°	911401836587	ST033T G2 LED25/940 33W I MB BK CN	Beam angle 24°
911401833287	ST033T G2 LED17/940 20W I MB BK GM	Beam angle 24°	911401836787	ST033T G2 LED25/930 33W I WB BK CN	Beam angle 36°
911401833387	ST033T G2 LED17/940 20W I WB BK GM	Beam angle 36°	911401836987	ST033T G2 LED25/940 33W I WB BK CN	Beam angle 36°
911401835587	ST033T G2 LED17/930 20W I MB BK CN	Beam angle 24°	911401831687	ST033T G2 LED5/930 7W I WB BK GM	Beam angle 36°
911401835787	ST033T G2 LED17/940 20W I MB BK CN	Beam angle 24°	911401831787	ST033T G2 LED5/940 7W I WB BK GM	Beam angle 36°
911401835987	ST033T G2 LED17/930 20W I WB BK CN	Beam angle 36°	911401834287	ST033T G2 LED5/940 7W I WB BK CN	Beam angle 36°
911401836187	ST033T G2 LED17/940 20W I WB BK CN	Beam angle 36°	911401834387	ST033T G2 LED5/930 7W I WB BK CN	Beam angle 36°
911401832687	ST033T G2 LED17/930 20W I MB WH GM	Beam angle 24°	911401833487	ST033T G2 LED25/930 33W I MB WH GM	Beam angle 24°
911401832787	ST033T G2 LED17/930 20W I WB WH GM	Beam angle 36°	911401833587	ST033T G2 LED25/930 33W I WB WH GM	Beam angle 36°
911401832887	ST033T G2 LED17/940 20W I MB WH GM	Beam angle 24°	911401833687	ST033T G2 LED25/940 33W I MB WH GM	Beam angle 24°
911401832987	ST033T G2 LED17/940 20W I WB WH GM	Beam angle 36°	911401833787	ST033T G2 LED25/940 33W I WB WH GM	Beam angle 36°
911401835487	ST033T G2 LED17/930 20W I MB WH CN	Beam angle 24°	911401836287	ST033T G2 LED25/930 33W I MB WH CN	Beam angle 24°
911401835687	ST033T G2 LED17/940 20W I MB WH CN	Beam angle 24°	911401836487	ST033T G2 LED25/940 33W I MB WH CN	Beam angle 24°
911401835887	ST033T G2 LED17/930 20W I WB WH CN	Beam angle 36°	911401836687	ST033T G2 LED25/930 33W I WB WH CN	Beam angle 36°
911401836087	ST033T G2 LED17/940 20W I WB WH CN	Beam angle 36°	911401836887	ST033T G2 LED25/940 33W I WB WH CN	Beam angle 36°
911401831887	ST033T G2 LED8/930 10W I MB WH GM	Beam angle 24°	911401831487	ST033T G2 LED5/930 7W I WB WH GM	Beam angle 36°
911401831987	ST033T G2 LED8/930 10W I WB WH GM	Beam angle 36°	911401831587	ST033T G2 LED5/940 7W I WB WH GM	Beam angle 36°
911401832087	ST033T G2 LED8/940 10W I MB WH GM	Beam angle 24°	911401834487	ST033T G2 LED5/940 7W I WB WH CN	Beam angle 36°
911401832187	ST033T G2 LED8/940 10W I WB WH GM	Beam angle 36°	911401834587	ST033T G2 LED5/930 7W I WB WH CN	Beam angle 36°

### Operating and Electrical

## Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Power Consumption
911401832287	ST033T G2 LED8/930 10W   MB BK GM	10 W
911401832387	ST033T G2 LED8/930 10W   WB BK GM	10 W
911401832487	ST033T G2 LED8/940 10W   MB BK GM	10 W
911401832587	ST033T G2 LED8/940 10W   WB BK GM	10 W
911401834787	ST033T G2 LED8/930 10W   MB BK CN	10 W
911401834987	ST033T G2 LED8/940 10W   MB BK CN	10 W
911401835187	ST033T G2 LED8/930 10W   WB BK CN	10 W
911401835387	ST033T G2 LED8/940 10W   WB BK CN	10 W
911401833087	ST033T G2 LED17/930 20W   MB BK GM	20 W
911401833187	ST033T G2 LED17/930 20W   WB BK GM	20 W
911401833287	ST033T G2 LED17/940 20W   MB BK GM	20 W
911401833387	ST033T G2 LED17/940 20W   WB BK GM	20 W
911401835587	ST033T G2 LED17/930 20W   MB BK CN	20 W
911401835787	ST033T G2 LED17/940 20W   MB BK CN	20 W
911401835987	ST033T G2 LED17/930 20W   WB BK CN	20 W
911401836187	ST033T G2 LED17/940 20W   WB BK CN	20 W
911401832687	ST033T G2 LED17/930 20W   MB WH GM	20 W
911401832787	ST033T G2 LED17/930 20W   WB WH GM	20 W
911401832887	ST033T G2 LED17/940 20W   MB WH GM	20 W
911401832987	ST033T G2 LED17/940 20W   WB WH GM	20 W
911401835487	ST033T G2 LED17/930 20W   MB WH CN	20 W
911401835687	ST033T G2 LED17/940 20W   MB WH CN	20 W
911401835887	ST033T G2 LED17/930 20W   WB WH CN	20 W
911401836087	ST033T G2 LED17/940 20W   WB WH CN	20 W
911401831887	ST033T G2 LED8/930 10W   MB WH GM	10 W
911401831987	ST033T G2 LED8/930 10W   WB WH GM	10 W
911401832087	ST033T G2 LED8/940 10W   MB WH GM	10 W
911401832187	ST033T G2 LED8/940 10W   WB WH GM	10 W

Order Code	Full Product Name	Power Consumption
911401834687	ST033T G2 LED8/930 10W   MB WH CN	10 W
911401834887	ST033T G2 LED8/940 10W   MB WH CN	10 W
911401835087	ST033T G2 LED8/930 10W   WB WH CN	10 W
911401835287	ST033T G2 LED8/940 10W   WB WH CN	10 W
911401833887	ST033T G2 LED25/930 33W   MB BK GM	33 W
911401833987	ST033T G2 LED25/930 33W   WB BK GM	33 W
911401834087	ST033T G2 LED25/940 33W   MB BK GM	33 W
911401834187	ST033T G2 LED25/940 33W   WB BK GM	33 W
911401836387	ST033T G2 LED25/930 33W   MB BK CN	33 W
911401836587	ST033T G2 LED25/940 33W   MB BK CN	33 W
911401836787	ST033T G2 LED25/930 33W   WB BK CN	33 W
911401836987	ST033T G2 LED25/940 33W   WB BK CN	33 W
911401831687	ST033T G2 LED5/930 7W   WB BK GM	7 W
911401831787	ST033T G2 LED5/940 7W   WB BK GM	7 W
911401834287	ST033T G2 LED5/940 7W   WB BK CN	7 W
911401834387	ST033T G2 LED5/930 7W   WB BK CN	7 W
911401833487	ST033T G2 LED25/930 33W   MB WH GM	33 W
911401833587	ST033T G2 LED25/930 33W   WB WH GM	33 W
911401833687	ST033T G2 LED25/940 33W   MB WH GM	33 W
911401833787	ST033T G2 LED25/940 33W   WB WH GM	33 W
911401836287	ST033T G2 LED25/930 33W   MB WH CN	33 W
911401836487	ST033T G2 LED25/940 33W   MB WH CN	33 W
911401836687	ST033T G2 LED25/930 33W   WB WH CN	33 W
911401836887	ST033T G2 LED25/940 33W   WB WH CN	33 W
911401831487	ST033T G2 LED5/930 7W   WB WH GM	7 W
911401831587	ST033T G2 LED5/940 7W   WB WH GM	7 W
911401834487	ST033T G2 LED5/940 7W   WB WH CN	7 W
911401834587	ST033T G2 LED5/930 7W   WB WH CN	7 W

### Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401832287	ST033T G2 LED8/930 10W   MB BK GM	Black
911401832387	ST033T G2 LED8/930 10W   WB BK GM	Black
911401832487	ST033T G2 LED8/940 10W   MB BK GM	Black
911401832587	ST033T G2 LED8/940 10W   WB BK GM	Black
911401834787	ST033T G2 LED8/930 10W   MB BK CN	Black
911401834987	ST033T G2 LED8/940 10W   MB BK CN	Black
911401835187	ST033T G2 LED8/930 10W   WB BK CN	Black
911401835387	ST033T G2 LED8/940 10W   WB BK CN	Black
911401833087	ST033T G2 LED17/930 20W   MB BK GM	Black
911401833187	ST033T G2 LED17/930 20W   WB BK GM	Black
911401833287	ST033T G2 LED17/940 20W   MB BK GM	Black
911401833387	ST033T G2 LED17/940 20W   WB BK GM	Black
911401835587	ST033T G2 LED17/930 20W   MB BK CN	Black
911401835787	ST033T G2 LED17/940 20W   MB BK CN	Black
911401835987	ST033T G2 LED17/930 20W   WB BK CN	Black
911401836187	ST033T G2 LED17/940 20W   WB BK CN	Black
911401832687	ST033T G2 LED17/930 20W   MB WH GM	White RAL 9003
911401832787	ST033T G2 LED17/930 20W   WB WH GM	White RAL 9003
911401832887	ST033T G2 LED17/940 20W   MB WH GM	White RAL 9003
911401832987	ST033T G2 LED17/940 20W   WB WH GM	White RAL 9003

Order Code	Full Product Name	Housing Color
911401835487	ST033T G2 LED17/930 20W   MB WH CN	White RAL 9003
911401835687	ST033T G2 LED17/940 20W   MB WH CN	White RAL 9003
911401835887	ST033T G2 LED17/930 20W   WB WH CN	White RAL 9003
911401836087	ST033T G2 LED17/940 20W   WB WH CN	White RAL 9003
911401831887	ST033T G2 LED8/930 10W   MB WH GM	White RAL 9003
911401831987	ST033T G2 LED8/930 10W   WB WH GM	White RAL 9003
911401832087	ST033T G2 LED8/940 10W   MB WH GM	White RAL 9003
911401832187	ST033T G2 LED8/940 10W   WB WH GM	White RAL 9003
911401834687	ST033T G2 LED8/930 10W   MB WH CN	White RAL 9003
911401834887	ST033T G2 LED8/940 10W   MB WH CN	White RAL 9003
911401835087	ST033T G2 LED8/930 10W   WB WH CN	White RAL 9003
911401835287	ST033T G2 LED8/940 10W   WB WH CN	White RAL 9003
911401833887	ST033T G2 LED25/930 33W   MB BK GM	Black
911401833987	ST033T G2 LED25/930 33W   WB BK GM	Black
911401834087	ST033T G2 LED25/940 33W   MB BK GM	Black
911401834187	ST033T G2 LED25/940 33W   WB BK GM	Black
911401836387	ST033T G2 LED25/930 33W   MB BK CN	Black
911401836587	ST033T G2 LED25/940 33W   MB BK CN	Black
911401836787	ST033T G2 LED25/930 33W   WB BK CN	Black
911401836987	ST033T G2 LED25/940 33W   WB BK CN	Black

## Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Housing Color
911401831687	ST033T G2 LED5/930 7W   WB BK GM	Black
911401831787	ST033T G2 LED5/940 7W   WB BK GM	Black
911401834287	ST033T G2 LED5/940 7W   WB BK CN	Black
911401834387	ST033T G2 LED5/930 7W   WB BK CN	Black
911401833487	ST033T G2 LED25/930 33W   MB WH GM	White RAL 9003
911401833587	ST033T G2 LED25/930 33W   WB WH GM	White RAL 9003
911401833687	ST033T G2 LED25/940 33W   MB WH GM	White RAL 9003
911401833787	ST033T G2 LED25/940 33W   WB WH GM	White RAL 9003

Order Code	Full Product Name	Housing Color
911401836287	ST033T G2 LED25/930 33W   MB WH CN	White RAL 9003
911401836487	ST033T G2 LED25/940 33W   MB WH CN	White RAL 9003
911401836687	ST033T G2 LED25/930 33W   WB WH CN	White RAL 9003
911401836887	ST033T G2 LED25/940 33W   WB WH CN	White RAL 9003
911401831487	ST033T G2 LED5/930 7W   WB WH GM	White RAL 9003
911401831587	ST033T G2 LED5/940 7W   WB WH GM	White RAL 9003
911401834487	ST033T G2 LED5/940 7W   WB WH CN	White RAL 9003
911401834587	ST033T G2 LED5/930 7W   WB WH CN	White RAL 9003

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401832287	ST033T G2 LED8/930 10W   MB BK GM	(0.44,0.40) SDCM<5
911401832387	ST033T G2 LED8/930 10W   WB BK GM	(0.44,0.40) SDCM<5
911401832487	ST033T G2 LED8/940 10W   MB BK GM	(0.38,0.38) SDCM<5
911401832587	ST033T G2 LED8/940 10W   WB BK GM	(0.38,0.38) SDCM<5
911401834787	ST033T G2 LED8/930 10W   MB BK CN	(0.44,0.40) SDCM<5
911401834987	ST033T G2 LED8/940 10W   MB BK CN	(0.38,0.38) SDCM<5
911401835187	ST033T G2 LED8/930 10W   WB BK CN	(0.44,0.40) SDCM<5
911401835387	ST033T G2 LED8/940 10W   WB BK CN	(0.38,0.38) SDCM<5
911401833087	ST033T G2 LED17/930 20W   MB BK GM	(0.44,0.40) SDCM<5
911401833187	ST033T G2 LED17/930 20W   WB BK GM	(0.44,0.40) SDCM<5
911401833287	ST033T G2 LED17/940 20W   MB BK GM	(0.38,0.38) SDCM<5
911401833387	ST033T G2 LED17/940 20W   WB BK GM	(0.38,0.38) SDCM<5
911401835587	ST033T G2 LED17/930 20W   MB BK CN	(0.44,0.40) SDCM<5
911401835787	ST033T G2 LED17/940 20W   MB BK CN	(0.38,0.38) SDCM<5
911401835987	ST033T G2 LED17/930 20W   WB BK CN	(0.44,0.40) SDCM<5
911401836187	ST033T G2 LED17/940 20W   WB BK CN	(0.38,0.38) SDCM<5
911401832687	ST033T G2 LED17/930 20W   MB WH GM	(0.44,0.40) SDCM<5
911401832787	ST033T G2 LED17/930 20W   WB WH GM	(0.44,0.40) SDCM<5
911401832887	ST033T G2 LED17/940 20W   MB WH GM	(0.38,0.38) SDCM<5
911401832987	ST033T G2 LED17/940 20W   WB WH GM	(0.38,0.38) SDCM<5
911401835487	ST033T G2 LED17/930 20W   MB WH CN	(0.44,0.40) SDCM<5
911401835687	ST033T G2 LED17/940 20W   MB WH CN	(0.38,0.38) SDCM<5
911401835887	ST033T G2 LED17/930 20W   WB WH CN	(0.44,0.40) SDCM<5
911401836087	ST033T G2 LED17/940 20W   WB WH CN	(0.38,0.38) SDCM<5
911401831887	ST033T G2 LED8/930 10W   MB WH GM	(0.44,0.40) SDCM<5
911401831987	ST033T G2 LED8/930 10W   WB WH GM	(0.44,0.40) SDCM<5
911401832087	ST033T G2 LED8/940 10W   MB WH GM	(0.38,0.38) SDCM<5
911401832187	ST033T G2 LED8/940 10W   WB WH GM	(0.38,0.38) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401834687	ST033T G2 LED8/930 10W   MB WH CN	(0.44,0.40) SDCM<5
911401834887	ST033T G2 LED8/940 10W   MB WH CN	(0.38,0.38) SDCM<5
911401835087	ST033T G2 LED8/930 10W   WB WH CN	(0.44,0.40) SDCM<5
911401835287	ST033T G2 LED8/940 10W   WB WH CN	(0.38,0.38) SDCM<5
911401833887	ST033T G2 LED25/930 33W   MB BK GM	(0.44,0.40) SDCM<5
911401833987	ST033T G2 LED25/930 33W   WB BK GM	(0.44,0.40) SDCM<5
911401834087	ST033T G2 LED25/940 33W   MB BK GM	(0.38,0.38) SDCM<5
911401834187	ST033T G2 LED25/940 33W   WB BK GM	(0.38,0.38) SDCM<5
911401836387	ST033T G2 LED25/930 33W   MB BK CN	(0.44,0.40) SDCM<5
911401836587	ST033T G2 LED25/940 33W   MB BK CN	(0.38,0.38) SDCM<5
911401836787	ST033T G2 LED25/930 33W   WB BK CN	(0.44,0.40) SDCM<5
911401836987	ST033T G2 LED25/940 33W   WB BK CN	(0.38,0.38) SDCM<5
911401831687	ST033T G2 LED5/930 7W   WB BK GM	(0.44,0.40) SDCM<5
911401831787	ST033T G2 LED5/940 7W   WB BK GM	(0.38,0.38) SDCM<5
911401834287	ST033T G2 LED5/940 7W   WB BK CN	(0.38,0.38) SDCM<5
911401834387	ST033T G2 LED5/930 7W   WB BK CN	(0.44,0.40) SDCM<5
911401833487	ST033T G2 LED25/930 33W   MB WH GM	(0.44,0.40) SDCM<5
911401833587	ST033T G2 LED25/930 33W   WB WH GM	(0.44,0.40) SDCM<5
911401833687	ST033T G2 LED25/940 33W   MB WH GM	(0.38,0.38) SDCM<5
911401833787	ST033T G2 LED25/940 33W   WB WH GM	(0.38,0.38) SDCM<5
911401836287	ST033T G2 LED25/930 33W   MB WH CN	(0.44,0.40) SDCM<5
911401836487	ST033T G2 LED25/940 33W   MB WH CN	(0.38,0.38) SDCM<5
911401836687	ST033T G2 LED25/930 33W   WB WH CN	(0.44,0.40) SDCM<5
911401836887	ST033T G2 LED25/940 33W   WB WH CN	(0.38,0.38) SDCM<5
911401831487	ST033T G2 LED5/930 7W   WB WH GM	(0.44,0.40) SDCM<5
911401831587	ST033T G2 LED5/940 7W   WB WH GM	(0.38,0.38) SDCM<5
911401834487	ST033T G2 LED5/940 7W   WB WH CN	(0.38,0.38) SDCM<5
911401834587	ST033T G2 LED5/930 7W   WB WH CN	(0.44,0.40) SDCM<5

## Essential Smartbright Projector Gen 2

