



# All-in-one Solar pathway light range up-to 5000 Lumen

## Essential SmartBright All-in-one Solar Pathway

Integrated solar pathway light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Optional wall mounting arm bracket. Microwave based motion sensor for optimizing battery autonomy.

### Benefits

- Saves energy
- Environment friendly
- Easy configurability with remote
- No trenching for cabling required

### Features

- Remote control for selecting lighting profile
- Wall mounting arm Kit option available
- High Lumen efficacy of upto 160lm/W
- Microwave sensor for run time maximization

### Application

- Walkways
- Pathways
- Amenities
- Gardens

# Essential SmartBright All-in-one Solar Pathway

## Warnings and Safety

- Not recommended to install this luminaire higher than 4 meters height.
- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- It works 100% on solar energy. This luminaire does not need any external electrical connection.

## Versions



Essential SmartBright All-in-one  
Solar Pathway Light




RTP-OF-BRC010




RTP-OF-BRC010

## Dimensional drawing



TYPE	W	L	H	Ø	α
10000lm	171	371	44.5	38	15°
20000lm	203	412	44.5	45	25°
30000lm	203	412	44.5	45	25°
40000lm	228	508	44.5	48	25°


TYPE	L2	L3	W3	α3
10000lm	360	40	50	10x15
20000lm	360	40	50	10x15
30000lm	360	40	50	10x15
40000lm	360	40	50	10x15



TYPE	W	L	H	Ø
10000lm	171	371	44.5	38
20000lm	203	412	44.5	45
30000lm	203	412	44.5	45
40000lm	228	508	44.5	48

# Essential SmartBright All-in-one Solar Pathway

## Dimensional drawing



### Operating and Electrical

Battery type	LiFePO4
Battery voltage	3.2 V
Charge controller type	PWM
Grid connection type	Off grid
Panel type	Mono crystalline

### Controls and Dimming

Dimmable	Preset Dimming
Configurability	Not configurable

### Mechanical and Housing

Housing Color	Grey
Ingress protection code	IP65

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom) (CRI)	Color rendering index
911401811203	BRC010 LED50/765 kit G3	6500 K	≥70
911401811403	BRC010 LED50/765 kit Pro G3	6500 K	≥70
911401811603	BRC010 LED50/740 kit G3	4000 K	≥70
911401811803	BRC010 LED50/740 kit Pro G3	4000 K	≥70
911401812003	BRC010 LED50/730 kit G3	3000 K	≥70
911401812203	BRC010 LED50/730 kit Pro G3	3000 K	≥70
911401807603	BRC010 LED30/765 G2	6500 K	70
911401807803	BRC010 LED30/765 Pro G2	6500 K	70
911401808003	BRC010 LED30/740 G2	4000 K	70
911401808203	BRC010 LED30/730 G2	3000 K	70
911401808403	BRC010 LED30/740 Pro G2	4000 K	70
911401808603	BRC010 LED30/730 Pro G2	3000 K	70
911401809903	BRC010 LED40/MCCT kit G2	2200 K	70
911401807703	BRC010 LED30/765 kit G2	6500 K	70
911401807903	BRC010 LED30/765 kit Pro G2	6500 K	70
911401808103	BRC010 LED30/740 kit G2	4000 K	70
911401808303	BRC010 LED30/730 kit G2	3000 K	70
911401808503	BRC010 LED30/740 kit Pro G2	4000 K	70
911401808703	BRC010 LED30/730 kit Pro G2	3000 K	70
911401802203	BRC010 LED40/765 G2	6500 K	70
911401894102	BRC010 LED40/765 G2	6500 K	70
911401894702	BRC010 LED40/765 Pro G2	6500 K	70
911401896502	BRC010 LED40/740 G2	4000 K	70
911401897102	BRC010 LED40/730 G2	3000 K	70
911401897702	BRC010 LED40/740 Pro G2	4000 K	70
911401898302	BRC010 LED40/730 Pro G2	3000 K	70
911401802403	BRC010 LED10/765 G2	6500 K	70
911401893902	BRC010 LED10/765 G2	6500 K	70
911401894502	BRC010 LED10/765 Pro G2	6500 K	70
911401896302	BRC010 LED10/740 G2	4000 K	70
911401896902	BRC010 LED10/730 G2	3000 K	70
911401897502	BRC010 LED10/740 Pro G2	4000 K	70
911401898102	BRC010 LED10/730 Pro G2	3000 K	70
911401894302	BRC010 LED20/765 kit G2	6500 K	70
911401894902	BRC010 LED20/765 kit Pro G2	6500 K	70

## Essential SmartBright All-in-one Solar Pathway

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)
911401896702	BRC010 LED20/740 kit G2	4000 K	70
911401897302	BRC010 LED20/730 kit G2	3000 K	70
911401897902	BRC010 LED20/740 kit Pro G2	4000 K	70
911401898502	BRC010 LED20/730 kit Pro G2	3000 K	70
911401809803	BRC010 LED40/MCCT G2	2200 K	70
911401894202	BRC010 LED10/765 kit G2	6500 K	70
911401894802	BRC010 LED10/765 kit Pro G2	6500 K	70
911401896602	BRC010 LED10/740 kit G2	4000 K	70
911401897202	BRC010 LED10/730 kit G2	3000 K	70
911401897802	BRC010 LED10/740 kit Pro G2	4000 K	70
911401898402	BRC010 LED10/730 kit Pro G2	3000 K	70
911401802303	BRC010 LED20/765 G2	6500 K	70
911401894002	BRC010 LED20/765 G2	6500 K	70
911401894602	BRC010 LED20/765 Pro G2	6500 K	70
911401896402	BRC010 LED20/740 G2	4000 K	70
911401897002	BRC010 LED20/730 G2	3000 K	70
911401897602	BRC010 LED20/740 Pro G2	4000 K	70
911401898202	BRC010 LED20/730 Pro G2	3000 K	70
911401894402	BRC010 LED40/765 kit G2	6500 K	70
911401895002	BRC010 LED40/765 kit Pro G2	6500 K	70
911401896802	BRC010 LED40/740 kit G2	4000 K	70
911401897402	BRC010 LED40/730 kit G2	3000 K	70
911401898002	BRC010 LED40/740 kit Pro G2	4000 K	70
911401898602	BRC010 LED40/730 kit Pro G2	3000 K	70
911401811303	BRC010 LED50/765 G3	6500 K	≥70
911401811503	BRC010 LED50/765 Pro G3	6500 K	≥70
911401811703	BRC010 LED50/740 G3	4000 K	≥70
911401811903	BRC010 LED50/740 Pro G3	4000 K	≥70
911401812103	BRC010 LED50/730 G3	3000 K	≥70
911401812303	BRC010 LED50/730 Pro G3	3000 K	≥70

### Operating and Electrical

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401811203	BRC010 LED50/765 kit G3	20 Ah	500	20 W	5 V
911401811403	BRC010 LED50/765 kit Pro G3	20 Ah	1000	20 W	5 V
911401811603	BRC010 LED50/740 kit G3	20 Ah	500	20 W	5 V
911401811803	BRC010 LED50/740 kit Pro G3	20 Ah	1000	20 W	5 V
911401812003	BRC010 LED50/730 kit G3	20 Ah	500	20 W	5 V

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401812203	BRC010 LED50/730 kit Pro G3	20 Ah	1000	20 W	5 V
911401807603	BRC010 LED30/765 G2	12 Ah	500	10 W	4 V
911401807803	BRC010 LED30/765 Pro G2	12 Ah	1000	10 W	4 V
911401808003	BRC010 LED30/740 G2	12 Ah	500	10 W	4 V
911401808203	BRC010 LED30/730 G2	12 Ah	500	10 W	4 V

## Essential SmartBright All-in-one Solar Pathway

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401808403	BRC010 LED30/740 Pro G2	12 Ah	1000	10 W	4 V
911401808603	BRC010 LED30/730 Pro G2	12 Ah	1000	10 W	4 V
911401809903	BRC010 LED40/MCCT kit G2	15 Ah	500	14 W	4.5 V
911401807703	BRC010 LED30/765 kit G2	12 Ah	500	10 W	4 V
911401807903	BRC010 LED30/765 kit Pro G2	12 Ah	1000	10 W	4 V
911401808103	BRC010 LED30/740 kit G2	12 Ah	500	10 W	4 V
911401808303	BRC010 LED30/730 kit G2	12 Ah	500	10 W	4 V
911401808503	BRC010 LED30/740 kit Pro G2	12 Ah	1000	10 W	4 V
911401808703	BRC010 LED30/730 kit Pro G2	12 Ah	1000	10 W	4 V
911401802203	BRC010 LED40/765 G2	15 Ah	500	14 W	4.5 V
911401894102	BRC010 LED40/765 G2	15 Ah	500	14 W	4.5 V
911401894702	BRC010 LED40/765 Pro G2	15 Ah	1000	14 W	4.5 V
911401896502	BRC010 LED40/740 G2	15 Ah	500	14 W	4.5 V
911401897102	BRC010 LED40/730 G2	15 Ah	500	14 W	4.5 V
911401897702	BRC010 LED40/740 Pro G2	15 Ah	1000	14 W	4.5 V
911401898302	BRC010 LED40/730 Pro G2	15 Ah	1000	14 W	4.5 V
911401802403	BRC010 LED10/765 G2	5 Ah	500	6 W	5 V
911401893902	BRC010 LED10/765 G2	5 Ah	500	6 W	5 V
911401894502	BRC010 LED10/765 Pro G2	5 Ah	1000	6 W	5 V
911401896302	BRC010 LED10/740 G2	5 Ah	500	6 W	5 V

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401896902	BRC010 LED10/730 G2	5 Ah	500	6 W	5 V
911401897502	BRC010 LED10/740 Pro G2	5 Ah	1000	6 W	5 V
911401898102	BRC010 LED10/730 Pro G2	5 Ah	1000	6 W	5 V
911401894302	BRC010 LED20/765 kit G2	8 Ah	500	8 W	4.5 V
911401894902	BRC010 LED20/765 kit Pro G2	8 Ah	1000	8 W	4.5 V
911401896702	BRC010 LED20/740 kit G2	8 Ah	500	8 W	4.5 V
911401897302	BRC010 LED20/730 kit G2	8 Ah	500	8 W	4.5 V
911401897902	BRC010 LED20/740 kit Pro G2	8 Ah	1000	8 W	4.5 V
911401898502	BRC010 LED20/730 kit Pro G2	8 Ah	1000	8 W	4.5 V
911401809803	BRC010 LED40/MCCT G2	15 Ah	500	14 W	4.5 V
911401894202	BRC010 LED10/765 kit G2	5 Ah	500	6 W	5 V
911401894802	BRC010 LED10/765 kit Pro G2	5 Ah	1000	6 W	5 V
911401896602	BRC010 LED10/740 kit G2	5 Ah	500	6 W	5 V
911401897202	BRC010 LED10/730 kit G2	5 Ah	500	6 W	5 V
911401897802	BRC010 LED10/740 kit Pro G2	5 Ah	1000	6 W	5 V
911401898402	BRC010 LED10/730 kit Pro G2	5 Ah	1000	6 W	5 V
911401802303	BRC010 LED20/765 G2	8 Ah	500	8 W	4.5 V
911401894002	BRC010 LED20/765 G2	8 Ah	500	8 W	4.5 V
911401894602	BRC010 LED20/765 Pro G2	8 Ah	1000	8 W	4.5 V
911401896402	BRC010 LED20/740 G2	8 Ah	500	8 W	4.5 V
911401897002	BRC010 LED20/730 G2	8 Ah	500	8 W	4.5 V

# Essential SmartBright All-in-one Solar Pathway

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401897602	BRC010 LED20/740 Pro G2	8 Ah	1000	8 W	4.5 V
911401898202	BRC010 LED20/730 Pro G2	8 Ah	1000	8 W	4.5 V
911401894402	BRC010 LED40/765 kit G2	15 Ah	500	14 W	4.5 V
911401895002	BRC010 LED40/765 kit Pro G2	15 Ah	1000	14 W	4.5 V
911401896802	BRC010 LED40/740 kit G2	15 Ah	500	14 W	4.5 V
911401897402	BRC010 LED40/730 kit G2	15 Ah	500	14 W	4.5 V
911401898002	BRC010 LED40/740 kit Pro G2	15 Ah	1000	14 W	4.5 V

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401898602	BRC010 LED40/730 kit Pro G2	15 Ah	1000	14 W	4.5 V
911401811303	BRC010 LED50/765 G3	20 Ah	500	20 W	5 V
911401811503	BRC010 LED50/765 Pro G3	20 Ah	1000	20 W	5 V
911401811703	BRC010 LED50/740 G3	20 Ah	500	20 W	5 V
911401811903	BRC010 LED50/740 Pro G3	20 Ah	1000	20 W	5 V
911401812103	BRC010 LED50/730 G3	20 Ah	500	20 W	5 V
911401812303	BRC010 LED50/730 Pro G3	20 Ah	1000	20 W	5 V

## Controls and Dimming

Order Code	Full Product Name	Solar dimming profile
911401811203	BRC010 LED50/765 kit G3	Preset Dimming
911401811403	BRC010 LED50/765 kit Pro G3	Preset Dimming
911401811603	BRC010 LED50/740 kit G3	Preset Dimming
911401811803	BRC010 LED50/740 kit Pro G3	Preset Dimming
911401812003	BRC010 LED50/730 kit G3	Preset Dimming
911401812203	BRC010 LED50/730 kit Pro G3	Preset Dimming
911401807603	BRC010 LED30/765 G2	Preset Dimming
911401807803	BRC010 LED30/765 Pro G2	Preset Dimming
911401808003	BRC010 LED30/740 G2	Preset Dimming
911401808203	BRC010 LED30/730 G2	Preset Dimming
911401808403	BRC010 LED30/740 Pro G2	Preset Dimming
911401808603	BRC010 LED30/730 Pro G2	Preset Dimming
911401809903	BRC010 LED40/MCCT kit G2	Preset Dimming
911401807703	BRC010 LED30/765 kit G2	Preset Dimming
911401807903	BRC010 LED30/765 kit Pro G2	Preset Dimming
911401808103	BRC010 LED30/740 kit G2	Preset Dimming
911401808303	BRC010 LED30/730 kit G2	Preset Dimming
911401808503	BRC010 LED30/740 kit Pro G2	Preset Dimming
911401808703	BRC010 LED30/730 kit Pro G2	Preset Dimming
911401802203	BRC010 LED40/765 G2	Preset dimming
911401894102	BRC010 LED40/765 G2	Preset Dimming
911401894702	BRC010 LED40/765 Pro G2	Preset Dimming
911401896502	BRC010 LED40/740 G2	Preset Dimming
911401897102	BRC010 LED40/730 G2	Preset Dimming
911401897702	BRC010 LED40/740 Pro G2	Preset Dimming
911401898302	BRC010 LED40/730 Pro G2	Preset Dimming
911401802403	BRC010 LED10/765 G2	Preset dimming

Order Code	Full Product Name	Solar dimming profile
911401893902	BRC010 LED10/765 G2	Preset Dimming
911401894502	BRC010 LED10/765 Pro G2	Preset Dimming
911401896302	BRC010 LED10/740 G2	Preset Dimming
911401896902	BRC010 LED10/730 G2	Preset Dimming
911401897502	BRC010 LED10/740 Pro G2	Preset Dimming
911401898102	BRC010 LED10/730 Pro G2	Preset Dimming
911401894302	BRC010 LED20/765 kit G2	Preset Dimming
911401894902	BRC010 LED20/765 kit Pro G2	Preset Dimming
911401896702	BRC010 LED20/740 kit G2	Preset Dimming
911401897302	BRC010 LED20/730 kit G2	Preset Dimming
911401897902	BRC010 LED20/740 kit Pro G2	Preset Dimming
911401898502	BRC010 LED20/730 kit Pro G2	Preset Dimming
911401809803	BRC010 LED40/MCCT G2	Preset Dimming
911401894202	BRC010 LED10/765 kit G2	Preset Dimming
911401894802	BRC010 LED10/765 kit Pro G2	Preset Dimming
911401896602	BRC010 LED10/740 kit G2	Preset Dimming
911401897202	BRC010 LED10/730 kit G2	Preset Dimming
911401897802	BRC010 LED10/740 kit Pro G2	Preset Dimming
911401898402	BRC010 LED10/730 kit Pro G2	Preset Dimming
911401802303	BRC010 LED20/765 G2	Preset dimming
911401894002	BRC010 LED20/765 G2	Preset Dimming
911401894602	BRC010 LED20/765 Pro G2	Preset Dimming
911401896402	BRC010 LED20/740 G2	Preset Dimming
911401897002	BRC010 LED20/730 G2	Preset Dimming
911401897602	BRC010 LED20/740 Pro G2	Preset Dimming
911401898202	BRC010 LED20/730 Pro G2	Preset Dimming
911401894402	BRC010 LED40/765 kit G2	Preset Dimming

# Essential SmartBright All-in-one Solar Pathway

Order Code	Full Product Name	Solar dimming profile
911401895002	BRC010 LED40/765 kit Pro G2	Preset Dimming
911401896802	BRC010 LED40/740 kit G2	Preset Dimming
911401897402	BRC010 LED40/730 kit G2	Preset Dimming
911401898002	BRC010 LED40/740 kit Pro G2	Preset Dimming
911401898602	BRC010 LED40/730 kit Pro G2	Preset Dimming
911401811303	BRC010 LED50/765 G3	Preset Dimming

Order Code	Full Product Name	Solar dimming profile
911401811503	BRC010 LED50/765 Pro G3	Preset Dimming
911401811703	BRC010 LED50/740 G3	Preset Dimming
911401811903	BRC010 LED50/740 Pro G3	Preset Dimming
911401812103	BRC010 LED50/730 G3	Preset Dimming
911401812303	BRC010 LED50/730 Pro G3	Preset Dimming

## Mechanical and Housing

Order Code	Full Product Name	Battery location	Overall height	Overall length	Overall width
911401811203	BRC010 LED50/765 kit G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401811403	BRC010 LED50/765 kit Pro G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401811603	BRC010 LED50/740 kit G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401811803	BRC010 LED50/740 kit Pro G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401812003	BRC010 LED50/730 kit G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401812203	BRC010 LED50/730 kit Pro G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401807603	BRC010 LED30/765 G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401807803	BRC010 LED30/765 Pro G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401808003	BRC010 LED30/740 G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401808203	BRC010 LED30/730 G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401808403	BRC010 LED30/740 Pro G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401808603	BRC010 LED30/730 Pro G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401809903	BRC010 LED40/MCCT kit G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401807703	BRC010 LED30/765 kit G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401807903	BRC010 LED30/765 kit Pro G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401808103	BRC010 LED30/740 kit G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401808303	BRC010 LED30/730 kit G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401808503	BRC010 LED30/740 kit Pro G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm

Order Code	Full Product Name	Battery location	Overall height	Overall length	Overall width
911401808703	BRC010 LED30/730 kit Pro G2	Inbuilt Luminaire	44.5 mm	412 mm	203 mm
911401802203	BRC010 LED40/765 G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401894102	BRC010 LED40/765 G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401894702	BRC010 LED40/765 Pro G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401896502	BRC010 LED40/740 G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401897102	BRC010 LED40/730 G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401897702	BRC010 LED40/740 Pro G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401898302	BRC010 LED40/730 Pro G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401802403	BRC010 LED10/765 G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401893902	BRC010 LED10/765 G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401894502	BRC010 LED10/765 Pro G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401896302	BRC010 LED10/740 G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401896902	BRC010 LED10/730 G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401897502	BRC010 LED10/740 Pro G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401898102	BRC010 LED10/730 Pro G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401894302	BRC010 LED20/765 kit G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401894902	BRC010 LED20/765 kit Pro G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401896702	BRC010 LED20/740 kit G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401897302	BRC010 LED20/730 kit G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm

## Essential SmartBright All-in-one Solar Pathway

Order Code	Full Product Name	Battery location	Overall height	Overall length	Overall width
911401897902	BRC010 LED20/740 kit Pro G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401898502	BRC010 LED20/730 kit Pro G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401809803	BRC010 LED40/MCCT G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401894202	BRC010 LED10/765 kit G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401894802	BRC010 LED10/765 kit Pro G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401896602	BRC010 LED10/740 kit G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401897202	BRC010 LED10/730 kit G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401897802	BRC010 LED10/740 kit Pro G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401898402	BRC010 LED10/730 kit Pro G2	Inbuilt luminaire	44.5 mm	371 mm	171 mm
911401802303	BRC010 LED20/765 G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401894002	BRC010 LED20/765 G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401894602	BRC010 LED20/765 Pro G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401896402	BRC010 LED20/740 G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401897002	BRC010 LED20/730 G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm

Order Code	Full Product Name	Battery location	Overall height	Overall length	Overall width
911401897602	BRC010 LED20/740 Pro G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401898202	BRC010 LED20/730 Pro G2	Inbuilt luminaire	44.5 mm	412 mm	203 mm
911401894402	BRC010 LED40/765 kit G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401895002	BRC010 LED40/765 kit Pro G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401896802	BRC010 LED40/740 kit G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401897402	BRC010 LED40/730 kit G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401898002	BRC010 LED40/740 kit Pro G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401898602	BRC010 LED40/730 kit Pro G2	Inbuilt luminaire	44.5 mm	508 mm	228 mm
911401811303	BRC010 LED50/765 G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401811503	BRC010 LED50/765 Pro G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401811703	BRC010 LED50/740 G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401811903	BRC010 LED50/740 Pro G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401812103	BRC010 LED50/730 G3	Inbuilt luminaire	50 mm	638 mm	240 mm
911401812303	BRC010 LED50/730 Pro G3	Inbuilt luminaire	50 mm	638 mm	240 mm

### Approval and Application

Order Code	Full Product Name	Ambient temperature range
911401811203	BRC010 LED50/765 kit G3	0 to +45 °C
911401811403	BRC010 LED50/765 kit Pro G3	0 to +45 °C
911401811603	BRC010 LED50/740 kit G3	0 to +45 °C
911401811803	BRC010 LED50/740 kit Pro G3	0 to +45 °C
911401812003	BRC010 LED50/730 kit G3	0 to +45 °C
911401812203	BRC010 LED50/730 kit Pro G3	0 to +45 °C
911401807603	BRC010 LED30/765 G2	0 to +45 °C
911401807803	BRC010 LED30/765 Pro G2	0 to +45 °C
911401808003	BRC010 LED30/740 G2	0 to +45 °C
911401808203	BRC010 LED30/730 G2	0 to +45 °C
911401808403	BRC010 LED30/740 Pro G2	0 to +45 °C
911401808603	BRC010 LED30/730 Pro G2	0 to +45 °C
911401809903	BRC010 LED40/MCCT kit G2	0 °C to 45 °C
911401807703	BRC010 LED30/765 kit G2	0 to +45 °C

Order Code	Full Product Name	Ambient temperature range
911401807903	BRC010 LED30/765 kit Pro G2	0 to +45 °C
911401808103	BRC010 LED30/740 kit G2	0 to +45 °C
911401808303	BRC010 LED30/730 kit G2	0 to +45 °C
911401808503	BRC010 LED30/740 kit Pro G2	0 to +45 °C
911401808703	BRC010 LED30/730 kit Pro G2	0 to +45 °C
911401802203	BRC010 LED40/765 G2	0 °C to 45 °C
911401894102	BRC010 LED40/765 G2	0 to +45 °C
911401894702	BRC010 LED40/765 Pro G2	0 to +45 °C
911401896502	BRC010 LED40/740 G2	0 to +45 °C
911401897102	BRC010 LED40/730 G2	0 to +45 °C
911401897702	BRC010 LED40/740 Pro G2	0 to +45 °C
911401898302	BRC010 LED40/730 Pro G2	0 to +45 °C
911401802403	BRC010 LED10/765 G2	0 °C to 45 °C
911401893902	BRC010 LED10/765 G2	0 to +45 °C

## Essential SmartBright All-in-one Solar Pathway

Order Code	Full Product Name	Ambient temperature range
911401894502	BRC010 LED10/765 Pro G2	0 to +45 °C
911401896302	BRC010 LED10/740 G2	0 to +45 °C
911401896902	BRC010 LED10/730 G2	0 to +45 °C
911401897502	BRC010 LED10/740 Pro G2	0 to +45 °C
911401898102	BRC010 LED10/730 Pro G2	0 to +45 °C
911401894302	BRC010 LED20/765 kit G2	0 to +45 °C
911401894902	BRC010 LED20/765 kit Pro G2	0 to +45 °C
911401896702	BRC010 LED20/740 kit G2	0 to +45 °C
911401897302	BRC010 LED20/730 kit G2	0 to +45 °C
911401897902	BRC010 LED20/740 kit Pro G2	0 to +45 °C
911401898502	BRC010 LED20/730 kit Pro G2	0 to +45 °C
911401809803	BRC010 LED40/MCCT G2	0 °C to 45 °C
911401894202	BRC010 LED10/765 kit G2	0 to +45 °C
911401894802	BRC010 LED10/765 kit Pro G2	0 to +45 °C
911401896602	BRC010 LED10/740 kit G2	0 to +45 °C
911401897202	BRC010 LED10/730 kit G2	0 to +45 °C
911401897802	BRC010 LED10/740 kit Pro G2	0 to +45 °C
911401898402	BRC010 LED10/730 kit Pro G2	0 to +45 °C
911401802303	BRC010 LED20/765 G2	0 °C to 45 °C

Order Code	Full Product Name	Ambient temperature range
911401894002	BRC010 LED20/765 G2	0 to +45 °C
911401894602	BRC010 LED20/765 Pro G2	0 to +45 °C
911401896402	BRC010 LED20/740 G2	0 to +45 °C
911401897002	BRC010 LED20/730 G2	0 to +45 °C
911401897602	BRC010 LED20/740 Pro G2	0 to +45 °C
911401898202	BRC010 LED20/730 Pro G2	0 to +45 °C
911401894402	BRC010 LED40/765 kit G2	0 to +45 °C
911401895002	BRC010 LED40/765 kit Pro G2	0 to +45 °C
911401896802	BRC010 LED40/740 kit G2	0 to +45 °C
911401897402	BRC010 LED40/730 kit G2	0 to +45 °C
911401898002	BRC010 LED40/740 kit Pro G2	0 to +45 °C
911401898602	BRC010 LED40/730 kit Pro G2	0 to +45 °C
911401811303	BRC010 LED50/765 G3	0 to +45 °C
911401811503	BRC010 LED50/765 Pro G3	0 to +45 °C
911401811703	BRC010 LED50/740 G3	0 to +45 °C
911401811903	BRC010 LED50/740 Pro G3	0 to +45 °C
911401812103	BRC010 LED50/730 G3	0 to +45 °C
911401812303	BRC010 LED50/730 Pro G3	0 to +45 °C

