

MASTER LED Strip

8689244



Slim LED strip offering high quality light with diversified options in terms of brightness and light color

A complete family delivering superior light with great uniformity and safety. Choose the best fit for every projects, from 5 lumen packs/wattages, and 4 CCTs, and enjoy great reliable performance free of maintenance

Benefits

- Superior light quality: Great color rendering and extremely good color consistency
- Wide range of products: Variety in lumen/wattage and CCT combinations to cater to different applications.
- Easy installation: Slim design ensures fit in tight spaces.

Applications

- Retail
- Hospitality
- Offices

Features

- Superior light quality: CRI 90, SDCM 3
- Full product range: 500lm, 1000lm, 1500lm, 2000lm, 2500lm, 2700K, 3000K, 4000K & 6500K options
- High efficiency for energy saving: 120lm/W
- DC 24V low voltage offers superior safety
- 60,000 Life hours

Versions




LS tapetowire connector IP20-EU



LS tapetotape connector IP20-EU



MAS LEDstrip 5M




LS corner connector IP20-EU




LS mounting clips IP20-EU


Dimensional drawing




LS tape-to-wire connector IP20 50pcs EU




LS corner connector IP20 50pcs EU



MAS LEDstrip 12.5W965 1450LM/M 5M



LS tape-to-tape connector IP20 50pcs EU



LS mounting clips IP20 50pcs EU

Operating and Electrical

Input Voltage 24 V

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Ingress protection code IP20 [Finger-protected]

Approval and Application

Ambient temperature range -20 to +40 °C

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
35503300	LS tape-to-wire connector IP20 50pcs EU	-	-	-
35501900	LS tape-to-tape connector IP20 50pcs EU	-	-	-
34432700	Master LEDstrip 4.3W927 475LM/M 5M	475 lm	2700 K	90
34434100	Master LEDstrip 4.3W930 475LM/M 5M	475 lm	3000 K	>90
34436500	Master LEDstrip 4.3W940 500LM/M 5M	500 lm	4000 K	>90
34438900	Master LEDstrip 4.3W965 500LM/M 5M	500 lm	6500 K	90
34440200	Master LEDstrip 8.3W927 920LM/M 5M	920 lm	2700 K	90
34442600	Master LEDstrip 8.3W930 920LM/M 5M	920 lm	3000 K	>90
34444000	Master LEDstrip 8.3W940 1000LM/M 5M	1,000 lm	4000 K	>90
34446400	Master LEDstrip 8.3W965 950LM/M 5M	950 lm	6500 K	90
34448800	Master LEDstrip 12.5W927 1380LM/M 5M	1,380 lm	2700 K	90

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Color rendering index (CRI)
34450100	Master LEDstrip 12.5W930 1380LM/M 5M	1,380 lm	3000 K	>90
34452500	Master LEDstrip 12.5W940 1500LM/M 5M	1,500 lm	4000 K	>90
34454900	Master LEDstrip 12.5W965 1450LM/M 5M	1,450 lm	6500 K	90
34456300	Master LEDstrip 16.6W927 1830LM/M 5M	1,830 lm	2700 K	90
34458700	Master LEDstrip 16.6W930 1830LM/M 5M	1,830 lm	3000 K	>90
34460000	Master LEDstrip 16.6W940 2000LM/M 5M	2,000 lm	4000 K	>90
34462400	Master LEDstrip 16.6W965 2000LM/M 5M	2,000 lm	6500 K	90
34464800	Master LEDstrip 21.3W927 2400LM/M 5M	2,400 lm	2700 K	90
34466200	Master LEDstrip 21.3W930 2400LM/M 5M	2,400 lm	3000 K	>90
34468600	Master LEDstrip 21.3W940 2500LM/M 5M	2,500 lm	4000 K	>90
34470900	Master LEDstrip 21.3W965 2450LM/M 5M	2,450 lm	6500 K	90
35499900	LS corner connector IP20 50pcs EU	-	-	-
35497500	LS mounting clips IP20 50pcs EU	-	-	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption
35503300	LS tape-to-wire connector IP20 50pcs EU	-
35501900	LS tape-to-tape connector IP20 50pcs EU	-
34432700	Master LEDstrip 4.3W927 475LM/M 5M	19 W
34434100	Master LEDstrip 4.3W930 475LM/M 5M	19 W
34436500	Master LEDstrip 4.3W940 500LM/M 5M	19 W
34438900	Master LEDstrip 4.3W965 500LM/M 5M	19 W
34440200	Master LEDstrip 8.3W927 920LM/M 5M	37 W
34442600	Master LEDstrip 8.3W930 920LM/M 5M	37 W
34444000	Master LEDstrip 8.3W940 1000LM/M 5M	37 W
34446400	Master LEDstrip 8.3W965 950LM/M 5M	37 W
34448800	Master LEDstrip 12.5W927 1380LM/M 5M	52 W
34450100	Master LEDstrip 12.5W930 1380LM/M 5M	52 W
34452500	Master LEDstrip 12.5W940 1500LM/M 5M	52 W
34454900	Master LEDstrip 12.5W965 1450LM/M 5M	52 W
34456300	Master LEDstrip 16.6W927 1830LM/M 5M	67 W
34458700	Master LEDstrip 16.6W930 1830LM/M 5M	67 W
34460000	Master LEDstrip 16.6W940 2000LM/M 5M	67 W
34462400	Master LEDstrip 16.6W965 2000LM/M 5M	67 W
34464800	Master LEDstrip 21.3W927 2400LM/M 5M	81 W
34466200	Master LEDstrip 21.3W930 2400LM/M 5M	81 W
34468600	Master LEDstrip 21.3W940 2500LM/M 5M	81 W
34470900	Master LEDstrip 21.3W965 2450LM/M 5M	81 W
35499900	LS corner connector IP20 50pcs EU	-
35497500	LS mounting clips IP20 50pcs EU	-