



For your everyday lighting jobs, CorePro LED combines the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology

CorePro Glass LED bulbs

Featuring a classic heritage design, these filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. A very easy choice for people who are looking for a retrofit LED replacement, these CorePro LED bulbs provide 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light in a vintage style. CorePro LED lighting that offers a lifetime of 15,000 hours to reduce maintenance costs.

CorePro Glass LED bulbs

Benefits

- Saves 30% energy compared with standard Philips LED bulbs
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

Features

- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with good color rendering (CRI>80)
- Designed to be seen, they look good switched on or off
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Home
- Hospitality

Versions



LED Lamps, LEDclassic A60 E27 WW FR



CLA LEDbulb 60W E27 827 CL G93



CLA LEDbulb 60W E27 827 CL ST64



MZD LEDCLA 40W A60 E27



LED Bulb A67 E27 ND Clear







MZD LEDCLA 60W A60 E27



LEDbulb Classic 75W E27 A60 827 CL ND

CorePro Glass LED bulbs

Dimensional drawing



Product	D	C
CorePro LEDBulb7-60W E27 A60 840 FR G	60 mm	106 mm





Product	D	C
CorePro LEDBulbND 7-60W E27 A60 827FR G	60 mm	110 mm
CorePro LEDBulbND4.5-40W E27 A60 827FR G	60 mm	110 mm

Product	D	C
CorePro LEDBulbND 7-60W E27 G93 827 CL G	95 mm	140 mm

Product	D	C
CorePro LEDBulbND 4.3-40W E27 A60827 CLG	60 mm	104 mm
CorePro LEDBulbND 8.5-75W E27 A60 827CLG	60 mm	104 mm
CorePro LEDBulbND 8.5-75W E27 A60 840CLG	60 mm	104 mm

CorePro Glass LED bulbs

Dimensional drawing



Product	D	C
CorePro LEDBulbND 7-60W E27 WW A60 CL G	60 mm	104 mm

Product	D	C
CorePro LEDBulbND 7-60W E27 ST64 827CL G	64 mm	140 mm

Product	D	C
CorePro LEDBulb10.5-100W E27 A60 840 FRG	60 mm	104 mm
CorePro LEDBulb8.5-75W E27 A60 840 FR G	60 mm	104 mm
CorePro LEDBulbND 4.5-40W E27 A60830 FRG	60 mm	106 mm
CorePro LEDBulbND 7-60W E27 A60 830 FR G	60 mm	106 mm
CorePro LEDBulbND 8.5-75W E27 A60 830FRG	60 mm	104 mm
CorePro LEDBulbND10.5-100W E27A60 827FRG	60 mm	104 mm
CorePro LEDBulbND10.5-100W E27A60 830FRG	60 mm	104 mm
CorePro LEDBulbND8.5-75W E27 A60 827FR G	60 mm	104 mm

Product	D	C
CorePro LEDBulbND10.5-100W E27A60 827CLG	60 mm	104 mm
CorePro LEDBulbND10.5-100W E27A60 840CLG	60 mm	104 mm

CorePro Glass LED bulbs

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	No
Approval and Application	
Ambient temperature range	-20 to +45 °C

General Information

Order Code	Full Product Name	Switching Cycle
929001243002	CorePro LEDBulbND 7-60W E27 A60 827FR G	30,000
929001387992	CorePro LEDBulbND 7-60W E27 G93 827 CL G	20,000
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	20,000
929001242992	CorePro LEDBulbND4.5-40W E27 A60 827FR G	30,000
929001323592	CorePro LEDBulb7-60W E27 A60 840 FR G	20,000
929002025702	CorePro LEDBulbND8.5-75W E27 A60 827FR G	20,000
929002025892	CorePro LEDBulb8.5-75W E27 A60 840 FR G	20,000
929002026402	CorePro LEDBulbND10.5-100W E27A60 827FRG	20,000
929002026592	CorePro LEDBulb10.5-100W E27 A60 840 FRG	20,000
929002424992	CorePro LEDBulbND 4.5-40W E27 A60830 FRG	20,000
929002425092	CorePro LEDBulbND 7-60W E27 A60 830 FR G	20,000
929002425192	CorePro LEDBulbND 8.5-75W E27 A60 830FRG	20,000
929002425292	CorePro LEDBulbND10.5-100W E27A60 830FRG	20,000
929001890092	CorePro LEDBulbND 4.3-40W E27 A60827 CLG	20,000
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	20,000
929002026292	CorePro LEDBulbND10.5-100W E27A60 840CLG	20,000
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	20,000
929002025492	CorePro LEDBulbND 8.5-75W E27 A60 827CLG	20,000
929002025592	CorePro LEDBulbND 8.5-75W E27 A60 840CLG	20,000

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated		
			Color Temperature (Nom)	Color Code	Luminous Flux
929001243002	CorePro LEDBulbND 7-60W E27 A60 827FR G	300 degree(s)	2700 K	827	806 lm
929001387992	CorePro LEDBulbND 7-60W E27 G93 827 CL G	300 degree(s)	2700 K	827	806 lm
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	300 degree(s)	2700 K	827	806 lm
929001242992	CorePro LEDBulbND4.5-40W E27 A60 827FR G	300 degree(s)	2700 K	827	470 lm
929001323592	CorePro LEDBulb7-60W E27 A60 840 FR G	300 degree(s)	4000 K	840	806 lm
929002025702	CorePro LEDBulbND8.5-75W E27 A60 827FR G	300 degree(s)	2700 K	827	1,055 lm
929002025892	CorePro LEDBulb8.5-75W E27 A60 840 FR G	300 degree(s)	4000 K	840	1,055 lm
929002026402	CorePro LEDBulbND10.5-100W E27A60 827FRG	300 degree(s)	2700 K	827	1,521 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated		
			Color Temperature (Nom)	Color Code	Luminous Flux
929002026592	CorePro LEDBulb10.5-100W E27 A60 840 FRG	300 degree(s)	4000 K	840	1,521 lm
929002424992	CorePro LEDBulbND 4.5-40W E27 A60830 FRG	300 degree(s)	3000 K	830	470 lm
929002425092	CorePro LEDBulbND 7-60W E27 A60 830 FR G	300 degree(s)	3000 K	830	806 lm
929002425192	CorePro LEDBulbND 8.5-75W E27 A60 830FRG	300 degree(s)	3000 K	830	1,055 lm
929002425292	CorePro LEDBulbND10.5-100W E27A60 830FRG	300 degree(s)	3000 K	830	1,521 lm
929001890092	CorePro LEDBulbND 4.3-40W E27 A60827 CLG	300 degree(s)	2700 K	827	470 lm
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	300 degree(s)	2700 K	827	1,521 lm
929002026292	CorePro LEDBulbND10.5-100W E27A60 840CLG	300 degree(s)	4000 K	840	1,521 lm

CorePro Glass LED bulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	330 degree(s)	2700 K	827	806 lm
929002025492	CorePro LEDBulbND 8.5-75W E27 A60 827CLG	300 degree(s)	2700 K	827	1,055 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
929002025592	CorePro LEDBulbND 8.5-75W E27 A60 840CLG	300 degree(s)	4000 K	840	1,055 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Starting	
			Time (Nom)	Wattage Equivalent
929001243002	CorePro LEDBulbND 7-60W E27 A60 827FR G	7 W	0.5 s	60 W
929001387992	CorePro LEDBulbND 7-60W E27 G93 827 CL G	7 W	0.5 s	60 W
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	7 W	0.5 s	60 W
929001242992	CorePro LEDBulbND4.5-40W E27 A60 827FR G	4.5 W	0.5 s	40 W
929001323592	CorePro LEDBulb7-60W E27 A60 840 FR G	7 W	0.5 s	60 W
929002025702	CorePro LEDBulbND8.5-75W E27 A60 827FR G	8.5 W	0.5 s	75 W
929002025892	CorePro LEDBulb8.5-75W E27 A60 840 FR G	8.5 W	0.5 s	75 W
929002026402	CorePro LEDBulbND10.5-100W E27A60 827FRG	10.5 W	0.5 s	100 W
929002026592	CorePro LEDBulb10.5-100W E27 A60 840 FRG	10.5 W	0.4 s	100 W
929002424992	CorePro LEDBulbND 4.5-40W E27 A60830 FRG	4.5 W	0.5 s	40 W

Order Code	Full Product Name	Power Consumption	Starting	
			Time (Nom)	Wattage Equivalent
929002425092	CorePro LEDBulbND 7-60W E27 A60 830 FR G	7 W	0.5 s	60 W
929002425192	CorePro LEDBulbND 8.5-75W E27 A60 830FRG	8.5 W	0.5 s	75 W
929002425292	CorePro LEDBulbND10.5-100W E27A60 830FRG	10.5 W	0.5 s	100 W
929001890092	CorePro LEDBulbND 4.3-40W E27 A60827 CLG	4.3 W	0.5 s	40 W
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	10.5 W	0.5 s	100 W
929002026292	CorePro LEDBulbND10.5-100W E27A60 840CLG	10.5 W	0.5 s	100 W
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	7 W	0.5 s	60 W
929002025492	CorePro LEDBulbND 8.5-75W E27 A60 827CLG	8.5 W	0.5 s	75 W
929002025592	CorePro LEDBulbND 8.5-75W E27 A60 840CLG	8.5 W	0.5 s	75 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001243002	CorePro LEDBulbND 7-60W E27 A60 827FR G	50 °C
929001387992	CorePro LEDBulbND 7-60W E27 G93 827 CL G	45 °C
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	45 °C
929001242992	CorePro LEDBulbND4.5-40W E27 A60 827FR G	50 °C
929001323592	CorePro LEDBulb7-60W E27 A60 840 FR G	50 °C
929002025702	CorePro LEDBulbND8.5-75W E27 A60 827FR G	50 °C
929002025892	CorePro LEDBulb8.5-75W E27 A60 840 FR G	50 °C
929002026402	CorePro LEDBulbND10.5-100W E27A60 827FRG	55 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002026592	CorePro LEDBulb10.5-100W E27 A60 840 FRG	55 °C
929002424992	CorePro LEDBulbND 4.5-40W E27 A60830 FRG	50 °C
929002425092	CorePro LEDBulbND 7-60W E27 A60 830 FR G	50 °C
929002425192	CorePro LEDBulbND 8.5-75W E27 A60 830FRG	50 °C
929002425292	CorePro LEDBulbND10.5-100W E27A60 830FRG	55 °C
929001890092	CorePro LEDBulbND 4.3-40W E27 A60827 CLG	45 °C
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	55 °C
929002026292	CorePro LEDBulbND10.5-100W E27A60 840CLG	55 °C

CorePro Glass LED bulbs

Order Code	Full Product Name	T-Case Maximum (Nom)
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	45 °C
929002025492	CorePro LEDBulbND 8.5-75W E27 A60 827CLG	50 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002025592	CorePro LEDBulbND 8.5-75W E27 A60 840CLG	50 °C

Mechanical and Housing


Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001243002	CorePro LEDBulbND 7-60W E27 A60 827FR G	Frosted	A60
929001387992	CorePro LEDBulbND 7-60W E27 G93 827 CL G	Clear	G93
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	Clear	ST64
929001242992	CorePro LEDBulbND4.5-40W E27 A60 827FR G	Frosted	A60
929001323592	CorePro LEDBulb7-60W E27 A60 840 FR G	Frosted	A60
929002025702	CorePro LEDBulbND8.5-75W E27 A60 827FR G	Frosted	A60
929002025892	CorePro LEDBulb8.5-75W E27 A60 840 FR G	Frosted	A60
929002026402	CorePro LEDBulbND10.5-100W E27A60 827FRG	Frosted	A60
929002026592	CorePro LEDBulb10.5-100W E27 A60 840 FRG	Frosted	A60
929002424992	CorePro LEDBulbND 4.5-40W E27 A60830 FRG	Frosted	A60
929002425092	CorePro LEDBulbND 7-60W E27 A60 830 FR G	Frosted	A60

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002425192	CorePro LEDBulbND 8.5-75W E27 A60 830FRG	Frosted	A60
929002425292	CorePro LEDBulbND10.5-100W E27A60 830FRG	Frosted	A60
929001890092	CorePro LEDBulbND 4.3-40W E27 A60827 CLG	Clear	A60
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	Clear	A60
929002026292	CorePro LEDBulbND10.5-100W E27A60 840CLG	Clear	A60
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	Clear	A60
929002025492	CorePro LEDBulbND 8.5-75W E27 A60 827CLG	Clear	A60
929002025592	CorePro LEDBulbND 8.5-75W E27 A60 840CLG	Clear	A60

Approval and Application


Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001243002	CorePro LEDBulbND 7-60W E27 A60 827FR G	7 kWh
929001387992	CorePro LEDBulbND 7-60W E27 G93 827 CL G	7 kWh
929001387692	CorePro LEDBulbND 7-60W E27 ST64 827CL G	7 kWh
929001242992	CorePro LEDBulbND4.5-40W E27 A60 827FR G	5 kWh
929001323592	CorePro LEDBulb7-60W E27 A60 840 FR G	7 kWh
929002025702	CorePro LEDBulbND8.5-75W E27 A60 827FR G	9 kWh
929002025892	CorePro LEDBulb8.5-75W E27 A60 840 FR G	9 kWh
929002026402	CorePro LEDBulbND10.5-100W E27A60 827FRG	11 kWh
929002026592	CorePro LEDBulb10.5-100W E27 A60 840 FRG	11 kWh
929002424992	CorePro LEDBulbND 4.5-40W E27 A60830 FRG	5 kWh
929002425092	CorePro LEDBulbND 7-60W E27 A60 830 FR G	7 kWh
929002425192	CorePro LEDBulbND 8.5-75W E27 A60 830FRG	9 kWh
929002425292	CorePro LEDBulbND10.5-100W E27A60 830FRG	11 kWh
929001890092	CorePro LEDBulbND 4.3-40W E27 A60827 CLG	5 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002026192	CorePro LEDBulbND10.5-100W E27A60 827CLG	11 kWh
929002026292	CorePro LEDBulbND10.5-100W E27A60 840CLG	11 kWh
929001387362	CorePro LEDBulbND 7-60W E27 WW A60 CL G	7 kWh
929002025492	CorePro LEDBulbND 8.5-75W E27 A60 827CLG	9 kWh
929002025592	CorePro LEDBulbND 8.5-75W E27 A60 840CLG	9 kWh




120°


90°




(cd/1000lm) 0° L.O.R.=1.00
— 0-180° — 90-270°




(cd/1000lm) 0° 150°



(cd/1000lm) 0° 150°




(cd/1000lm) 0° 150°




(cd/1000lm) 0°

CorePro Glass LED bulbs



(cd/1000lm)



(cd/1000lm)

CorePro Glass LED bulbs

