



Dimmable glass LED candles and lusters that meet the high standard for light experience

MASTER GLASS LED candles and lusters

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent candles and lusters with the benefits of the long-lasting LED technology. It is an idea product to provide customers with cozy atmosphere. The MASTER LED candles and lusters can be dimmed for different lumen level and also for the different color temperature. MASTER Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED and provides excellent quality of light. By offering a lifetime of 25,000 hours it reduces maintenance costs.

Benefits

- energy saving, 30% less energy compared with standard Philips LED candle and luster
- Very long lifetime that reduces the need for replacement
- Easy replacement of conventional lamps

Features


- heritage design with classic shapes
- perfect fit and high quality finishing
- Very good light quality with super high color rendering (CRI>95)
- Designed to be seen, they look good on and off
- Environmentally friendly: contains no mercury or other hazardous substances

MASTER GLASS LED candles and lusters

Application

- Domestic application
- Hospitality: restaurants and hotels

Dimensional drawing



Product	D	C
MAS LEDLusterDT3.5-40W E27 927 P45CL G	45 mm	78 mm
MAS LEDLusterDT5.9-60W E27 927 P45CL G	45 mm	78 mm

General Information

Cap-Base	E27
Switching Cycle	20,000
Nominal lifetime	25,000 hour(s)

Light Technical

Correlated Color Temperature (Nom)	2200 K
Color rendering index (CRI)	90
Color Code	922-927
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	P45

Approval and Application

Ambient temperature range	-20 °C to 45 °C
---------------------------	-----------------

Light Technical

Order Code	Full Product Name	Luminous Flux
929003013282	MAS LEDLusterDT3.5-40W E27 927 P45CL G	470 lm
929003014382	MAS LEDLusterDT5.9-60W E27 927 P45CL G	806 lm

Operating and Electrical

MASTER GLASS LED candles and lusters

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929003013282	MAS LEDLusterDT3.5-40W E27 927 P45CL G	3.4 W	40 W

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929003014382	MAS LEDLusterDT5.9-60W E27 927 P45CL G	5.9 W	60 W

Approval and Application

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
929003013282	MAS LEDLusterDT3.5-40W E27 927 P45CL G	4 kWh
929003014382	MAS LEDLusterDT5.9-60W E27 927 P45CL G	6 kWh

