



# For an optimal combination of value and performance

## MASTER Value GLASS LED candles and lusters

MASTER Value Glass LED lusters features a classic heritage design, these filament LED lamps combine the familiar shapes of incandescent candles and lusters with the benefits of long-lasting LED technology. These glass LED lusters offer more energy savings than normal LED candles and lusters. At the same time, they also provide customers with a good light experience, enhanced by excellent dimming performance (dimnable LED candles). MASTER Value Glass LED lusters and lusters deliver significant energy savings, using 30% less energy compared to normal glass LED candles and provide excellent quality of light. By offering a lifetime of 15,000 hours these dimmable LED candles and lusters also reduce maintenance costs.

### Benefits

- Saves 30% energy compared with standard Philips LED candles and lusters
- Very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

### Features

- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with excellent color rendering (CRI>90)
- Designed to be seen, they look good switched on or off
- Environmentally friendly: contains no mercury or other hazardous substances

### Application

- Home
- Hospitality

# MSTER Value GLASS LED candles and lusters

## Versions



LEDlustre MAS P45 E14 CL



LEDclassic 25W B35 E14 CL  
WGD90 SRT4 1



CLA LEDcandle 25W E14 827 FR  
P45



CLA LEDcandle 25W E27 827 FR  
P45



LEDclassic 40W BA35 E14 CL  
WGD90 SRT4 1



LEDcandle MAS B35 E14 CL







LEDclassic 40W P45 E27 CL  
WGD90 SRT4 1



LEDlustre MAS P45 E27 CL

# MSTER Value GLASS LED candles and lusters

## Dimensional drawing



Product	D	C
MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	35 mm	97 mm
MAS VLE LEDCandleDT2.5-25W E14 B35CL G	35 mm	97 mm
MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	35 mm	97 mm
MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	35 mm	97 mm

Product	D	C
MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	45 mm	80 mm
MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	45 mm	80 mm

Product	D	C
MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	45 mm	78 mm
MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	45 mm	78 mm
MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	45 mm	78 mm

Product	D	C
MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	35 mm	119 mm

# MSTER Value GLASS LED candles and lusters

General Information	
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	Only with specific dimmers
Approval and Application	
Ambient temperature range	-20 to +45 °C

## General Information

Order Code	Full Product Name	Cap-Base
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	E14
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	E14
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	E14
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	E14
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	E14
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	E27
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	E14
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	E14
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	E27
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	E27

## Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated			Order Code	Full Product Name	Beam Angle (Nom)	Correlated		
			Color Temperature (Nom)	Color Code	Luminous Flux				Color Temperature (Nom)	Color Code	Luminous Flux
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	300 degree(s)	2700 K	927	470 lm	929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	300 degree(s)	2700 K	927	470 lm
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	-	2200 K	922-927	470 lm	929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	-	2200 K	922-927	470 lm
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	-	2200 K	922-927	470 lm	929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	300 degree(s)	2700 K	927	470 lm
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	-	2200 K	922-927	340 lm	929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	-	2200 K	922-927	470 lm
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	300 degree(s)	2700 K	927	470 lm	929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	300 degree(s)	2700 K	927	470 lm

## Operating and Electrical

Order Code	Full Product Name	Power		Order Code	Full Product Name	Power	
		Consumption	Wattage Equivalent			Consumption	Wattage Equivalent
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	3.4 W	40 W	929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	3.4 W	40 W
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	3.4 W	40 W	929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	2.5 W	25 W

## MSTER Value GLASS LED candles and lusters

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	3.4 W	40 W
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	3.4 W	40 W
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	3.4 W	40 W

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	3.4 W	40 W
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	3.5 W	40 W
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	3.4 W	40 W

### Temperature

Order Code	Full Product Name	T-Case Maximum
		(Nom)
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	80 °C
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	70 °C
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	70 °C
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	70 °C
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	80 °C

Order Code	Full Product Name	T-Case Maximum
		(Nom)
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	80 °C
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	70 °C
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	80 °C
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	70 °C
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	80 °C

### Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb
			Shape
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	Clear	P45
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	Clear	B35
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	Clear	B35
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	Clear	B35
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	Frosted	P45
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	Frosted	P45

Order Code	Full Product Name	Bulb Finish	Bulb
			Shape
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	Clear	BA35
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	Clear	B35
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	Clear	P45
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	Clear	P45

### Approval and Application

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
929003060002	MAS VLE LEDLusterD3.4-40W E14 P45 927CLG	4 kWh
929003012202	MAS VLE LEDCandleDT3.4-40W E14 927B35CLG	4 kWh
929003012298	MASVLE LEDCandleDT3.4-40WE14 927B35CLGUK	4 kWh
929003011902	MAS VLE LEDCandleDT2.5-25W E14 B35CL G	3 kWh
929003060202	MAS VLE LEDLusterD3.4-40W E14 P45 927FRG	4 kWh
929003060602	MAS VLE LEDLusterD3.4-40W E27 P45 927FRG	4 kWh

Order Code	Full Product Name	Energy Consumption
		kWh/1000 h
929003013002	MAS VLE LEDCandleDT3.4-40W E14927BA35CLG	4 kWh
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	4 kWh
929003013202	MAS VLE LEDLusterDT3.5-40W E27 927P45CLG	4 kWh
929003060402	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	4 kWh

# MSTER Value GLASS LED candles and lusters

