



For your everyday lighting jobs, candle LEDs feature a classic heritage design with the benefits of long-lasting LED technology

CorePro GLASS LED candles and lustres

Featuring a classic heritage design, these filament LED candles combine the familiar shapes of classic incandescent bulbs with the benefits of long-lasting LED technology. The LED candle bulb is a very easy choice for people who are looking for a retrofit LED replacement, it provides 90% energy savings compared with conventional lamps. CorePro Glass LED bulbs provide excellent quality of light for stairway lighting. The LED candle bulb offers a lifetime of 15,000 hours to reduce maintenance costs.

Benefits

- Saves 30% energy compared with standard Philips LED candles and lustres
- The LED candle bulb has very long lifetime that reduces the need for replacements
- Easy retrofit replacement for conventional lamps

CorePro GLASS LED candles and lustres

Features

- heritage design with classic shapes
- perfect fit and high-quality finish
- Very good light quality with good colour rendering (CRI>80)
- Designed to be seen, they look good switched on or off
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Home
- Hospitality

Versions



LEDluster E14 P45



LED Lamps, LEDluster ND 2-25W
P45 E27 CL



CLA LEDcandle 25W E27 827 FR
P45



LEDluster E27 P45



MZD LEDCLA 25W P45 E14



MZD LEDCLA 25W B35 E14

CorePro GLASS LED candles and lustres

Versions



LED classic 40W B35 E14
WWFRNDRF2SRT6 UK



SPPR_LEDCL_0028-Product
photo



SPPR_LEDCL_0029-Product
photo



MZD LEDCLA 40W B35 E14



MZD LEDCLA 40W P45 E14







LEDcandle E14 B35



LEDbulb Classic 40W E27 P45 827
CL ND

CorePro GLASS LED candles and lustres

Dimensional drawing



Product	D	C
CorePro LEDLusterND2-25W P45 E27 827 CLG	45 mm	78 mm





Product	D	C
CorePro LEDCandleND4.3-40W E14 827B35CLG	35 mm	97 mm

Product	D	C
CorePro LEDLuster ND 2.2-25W P45 E14 FRG	45 mm	80 mm
CorePro LEDLusterND4.3-40W E14 827P45CLG	45 mm	82 mm
CorePro LEDLusterND4.3-40W E14 827P45FRG	45 mm	80 mm
CorePro LEDLusterND6.5-60W P45 E14827FRG	45 mm	80 mm

Product	D	C
CorePro LEDLuster ND 2.2-25W P45 E27 FRG	45 mm	78 mm
CorePro LEDLusterND4.3-40W E27 827P45CLG	45 mm	82 mm
CorePro LEDLusterND4.3-40W E27 827P45FRG	45 mm	78 mm
CorePro LEDLusterND6.5-60W P45 E27827FRG	45 mm	78 mm

CorePro GLASS LED candles and lustres

Dimensional drawing



Product	D	C
CorePro LEDLusterND6.5-60W P45 E27827CLG	45 mm	78 mm




Product	D	C
CorePro LEDLusterND6.5-60W P45 E14827CLG	45 mm	80 mm

Product	D	C
CorePro LEDCandle ND 2.2-25W B35 E14 FRG	35 mm	97 mm
CorePro LEDCandleND 2-25W E14B35 827CL G	35 mm	97 mm
CorePro LEDCandleND4.3-40W E14 827B35FRG	35 mm	97 mm
CorePro LEDCandleND6.5-60W B35 E14827FRG	35 mm	97 mm

Product	D	C
CorePro LEDCandleND2-25W E14BA35 827CL G	35 mm	123 mm

CorePro GLASS LED candles and lustres

Dimensional drawing



Product	D	C
CorePro LEDCandleND2-25W ST35 E14 827CLG	35 mm	97 mm

Product	D	C
CorePro LEDLusterND2-25W P45 E14 827 CLG	45 mm	80 mm

Product	D	C
CorePro LEDCandle ND6.5-60W B35E14827CLG	35 mm	97 mm

CorePro GLASS LED candles and lustres

General Information

Switching Cycle	20,000
Nominal lifetime	15,000 h

Light Technical

Beam angle (nom.)	300 degree(s)
Correlated Colour Temperature (Nom)	2700 K
Colour rendering index (CRI)	80
Colour Code	827
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical

Input frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting time (nom.)	0.5 s

Controls and Dimming

Dimmable	No
----------	----

General Information

Order Code	Full Product Name	Cap base
929002028592	CorePro LEDLusterND6.5-60W P45 E14827CLG	E14
929001238792	CorePro LEDLusterND2-25W P45 E27 827 CLG	E27
929001345292	CorePro LEDCandle ND 2.2-25W B35 E14 FRG	E14
929002028292	CorePro LEDCandleND6.5-60W B35 E14827FRG	E14
929001345492	CorePro LEDLuster ND 2.2-25W P45 E14 FRG	E14
929001345592	CorePro LEDLusterND4.3-40W E14 827P45FRG	E14
929002028792	CorePro LEDLusterND6.5-60W P45 E14827FRG	E14
929001345692	CorePro LEDLuster ND 2.2-25W P45 E27 FRG	E27
929001345792	CorePro LEDLusterND4.3-40W E27 827P45FRG	E27
929002029292	CorePro LEDLusterND6.5-60W P45 E27827FRG	E27
929002029092	CorePro LEDLusterND6.5-60W P45 E27827CLG	E27
929001238692	CorePro LEDLusterND2-25W P45 E14 827 CLG	E14
929001238392	CorePro LEDCandleND 2-25W E14B35 827CL G	E14
929001345392	CorePro LEDCandleND4.3-40W E14 827B35FRG	E14
929001238492	CorePro LEDCandleND2-25W E14BA35 827CL G	E14
929001238592	CorePro LEDCandleND2-25W ST35 E14 827CLG	E14
929001889792	CorePro LEDCandleND4.3-40W E14 827B35CLG	E14
929001890492	CorePro LEDLusterND4.3-40W E14 827P45CLG	E14
929002028092	CorePro LEDCandle ND6.5-60W B35E14827CLG	E14
929001890592	CorePro LEDLusterND4.3-40W E27 827P45CLG	E27

Light Technical

Order Code	Full Product Name	Luminous Flux	Order Code	Full Product Name	Luminous Flux
929002028592	CorePro LEDLusterND6.5-60W P45 E14827CLG	806 lm	929002029092	CorePro LEDLusterND6.5-60W P45 E27827CLG	806 lm
929001238792	CorePro LEDLusterND2-25W P45 E27 827 CLG	250 lm	929001238692	CorePro LEDLusterND2-25W P45 E14 827 CLG	250 lm
929001345292	CorePro LEDCandle ND 2.2-25W B35 E14 FRG	250 lm	929001238392	CorePro LEDCandleND 2-25W E14B35 827CL G	250 lm
929002028292	CorePro LEDCandleND6.5-60W B35 E14827FRG	806 lm	929001345392	CorePro LEDCandleND4.3-40W E14 827B35FRG	470 lm
929001345492	CorePro LEDLuster ND 2.2-25W P45 E14 FRG	250 lm	929001238492	CorePro LEDCandleND2-25W E14BA35 827CL G	250 lm
929001345592	CorePro LEDLusterND4.3-40W E14 827P45FRG	470 lm	929001238592	CorePro LEDCandleND2-25W ST35 E14 827CLG	250 lm
929002028792	CorePro LEDLusterND6.5-60W P45 E14827FRG	806 lm	929001889792	CorePro LEDCandleND4.3-40W E14 827B35CLG	470 lm
929001345692	CorePro LEDLuster ND 2.2-25W P45 E27 FRG	250 lm	929001890492	CorePro LEDLusterND4.3-40W E14 827P45CLG	470 lm
929001345792	CorePro LEDLusterND4.3-40W E27 827P45FRG	470 lm	929002028092	CorePro LEDCandle ND6.5-60W B35E14827CLG	806 lm
929002029292	CorePro LEDLusterND6.5-60W P45 E27827FRG	806 lm	929001890592	CorePro LEDLusterND4.3-40W E27 827P45CLG	470 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage equivalent	Order Code	Full Product Name	Power Consumption	Wattage equivalent
929002028592	CorePro LEDLusterND6.5-60W P45 E14827CLG	6.5 W	60 W	929001345592	CorePro LEDLusterND4.3-40W E14 827P45FRG	4.3 W	40 W
929001238792	CorePro LEDLusterND2-25W P45 E27 827 CLG	2 W	25 W	929002028792	CorePro LEDLusterND6.5-60W P45 E14827FRG	6.5 W	60 W
929001345292	CorePro LEDCandle ND 2.2-25W B35 E14 FRG	2.2 W	25 W	929001345692	CorePro LEDLuster ND 2.2-25W P45 E27 FRG	2.2 W	25 W
929002028292	CorePro LEDCandleND6.5-60W B35 E14827FRG	6.5 W	60 W	929001345792	CorePro LEDLusterND4.3-40W E27 827P45FRG	4.3 W	40 W
929001345492	CorePro LEDLuster ND 2.2-25W P45 E14 FRG	2.2 W	25 W	929002029292	CorePro LEDLusterND6.5-60W P45 E27827FRG	6.5 W	60 W

CorePro GLASS LED candles and lustres

Order Code	Full Product Name	Power	Wattage
		Consumption	equivalent
929002029092	CorePro LEDLusterND6.5-60W P45 E27827CLG	6.5 W	60 W
929001238692	CorePro LEDLusterND2-25W P45 E14 827 CLG	2 W	25 W
929001238392	CorePro LEDCandleND 2-25W E14B35 827CL G	2 W	25 W
929001345392	CorePro LEDCandleND4.3-40W E14 827B35FRG	4.3 W	40 W
929001238492	CorePro LEDCandleND2-25W E14BA35 827CL G	2 W	25 W

Order Code	Full Product Name	Power	Wattage
		Consumption	equivalent
929001238592	CorePro LEDCandleND2-25W ST35 E14 827CLG	2 W	25 W
929001889792	CorePro LEDCandleND4.3-40W E14 827B35CLG	4.3 W	40 W
929001890492	CorePro LEDLusterND4.3-40W E14 827P45CLG	4.3 W	40 W
929002028092	CorePro LEDCandle ND6.5-60W B35E14827CLG	6.5 W	60 W
929001890592	CorePro LEDLusterND4.3-40W E27 827P45CLG	4.3 W	40 W

Temperature

Order Code	Full Product Name	T-Case maximum (nom.)
929002028592	CorePro LEDLusterND6.5-60W P45 E14827CLG	55 °C
929001238792	CorePro LEDLusterND2-25W P45 E27 827 CLG	30 °C
929001345292	CorePro LEDCandle ND 2.2-25W B35 E14 FRG	36 °C
929002028292	CorePro LEDCandleND6.5-60W B35 E14827FRG	55 °C
929001345492	CorePro LEDLuster ND 2.2-25W P45 E14 FRG	36 °C
929001345592	CorePro LEDLusterND4.3-40W E14 827P45FRG	55 °C
929002028792	CorePro LEDLusterND6.5-60W P45 E14827FRG	55 °C
929001345692	CorePro LEDLuster ND 2.2-25W P45 E27 FRG	36 °C
929001345792	CorePro LEDLusterND4.3-40W E27 827P45FRG	55 °C
929002029292	CorePro LEDLusterND6.5-60W P45 E27827FRG	55 °C

Order Code	Full Product Name	T-Case maximum (nom.)
929002029092	CorePro LEDLusterND6.5-60W P45 E27827CLG	55 °C
929001238692	CorePro LEDLusterND2-25W P45 E14 827 CLG	36 °C
929001238392	CorePro LEDCandleND 2-25W E14B35 827CL G	36 °C
929001345392	CorePro LEDCandleND4.3-40W E14 827B35FRG	55 °C
929001238492	CorePro LEDCandleND2-25W E14BA35 827CL G	36 °C
929001238592	CorePro LEDCandleND2-25W ST35 E14 827CLG	36 °C
929001889792	CorePro LEDCandleND4.3-40W E14 827B35CLG	45 °C
929001890492	CorePro LEDLusterND4.3-40W E14 827P45CLG	45 °C
929002028092	CorePro LEDCandle ND6.5-60W B35E14827CLG	55 °C
929001890592	CorePro LEDLusterND4.3-40W E27 827P45CLG	45 °C

Mechanical and Housing

Order Code	Full Product Name	Lamp Finish	Bulb
			shape
929002028592	CorePro LEDLusterND6.5-60W P45 E14827CLG	Clear	P45
929001238792	CorePro LEDLusterND2-25W P45 E27 827 CLG	Clear	P45
929001345292	CorePro LEDCandle ND 2.2-25W B35 E14 FRG	Frosted	B35
929002028292	CorePro LEDCandleND6.5-60W B35 E14827FRG	Frosted	B35
929001345492	CorePro LEDLuster ND 2.2-25W P45 E14 FRG	Frosted	P45
929001345592	CorePro LEDLusterND4.3-40W E14 827P45FRG	Frosted	P45
929002028792	CorePro LEDLusterND6.5-60W P45 E14827FRG	Frosted	P45
929001345692	CorePro LEDLuster ND 2.2-25W P45 E27 FRG	Frosted	P45
929001345792	CorePro LEDLusterND4.3-40W E27 827P45FRG	Frosted	P45
929002029292	CorePro LEDLusterND6.5-60W P45 E27827FRG	Frosted	P45

Order Code	Full Product Name	Lamp Finish	Bulb
			shape
929002029092	CorePro LEDLusterND6.5-60W P45 E27827CLG	Clear	P45
929001238692	CorePro LEDLusterND2-25W P45 E14 827 CLG	Clear	P45
929001238392	CorePro LEDCandleND 2-25W E14B35 827CL G	Clear	B35
929001345392	CorePro LEDCandleND4.3-40W E14 827B35FRG	Frosted	B35
929001238492	CorePro LEDCandleND2-25W E14BA35 827CL G	Clear	BA35
929001238592	CorePro LEDCandleND2-25W ST35 E14 827CLG	Clear	ST35
929001889792	CorePro LEDCandleND4.3-40W E14 827B35CLG	Clear	B35
929001890492	CorePro LEDLusterND4.3-40W E14 827P45CLG	Clear	P45
929002028092	CorePro LEDCandle ND6.5-60W B35E14827CLG	Clear	B35
929001890592	CorePro LEDLusterND4.3-40W E27 827P45CLG	Clear	P45

CorePro GLASS LED candles and lustres

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy consumption kWh/1,000 hours
929002028592	CorePro LEDLusterND6.5-60W P45 E14827CLG	-20 to +45 °C	7 kWh
929001238792	CorePro LEDLusterND2-25W P45 E27 827 CLG	-20 to +45 °C	2 kWh
929001345292	CorePro LEDCandle ND 2.2-25W B35 E14 FRG	-20°C to 45°C	3 kWh
929002028292	CorePro LEDCandleND6.5-60W B35 E14827FRG	-20 to +45 °C	7 kWh
929001345492	CorePro LEDLuster ND 2.2-25W P45 E14 FRG	-20 to +45 °C	3 kWh
929001345592	CorePro LEDLusterND4.3-40W E14 827P45FRG	-20 to +45 °C	5 kWh
929002028792	CorePro LEDLusterND6.5-60W P45 E14827FRG	-20 to +45 °C	7 kWh
929001345692	CorePro LEDLuster ND 2.2-25W P45 E27 FRG	-20 to +45 °C	3 kWh
929001345792	CorePro LEDLusterND4.3-40W E27 827P45FRG	-20 to +45 °C	5 kWh
929002029292	CorePro LEDLusterND6.5-60W P45 E27827FRG	-20 to +45 °C	7 kWh
929002029092	CorePro LEDLusterND6.5-60W P45 E27827CLG	-20 to +45 °C	7 kWh
929001238692	CorePro LEDLusterND2-25W P45 E14 827 CLG	-20°C to 45°C	2 kWh
929001238392	CorePro LEDCandleND 2-25W E14B35 827CL G	-20°C to 45°C	2 kWh
929001345392	CorePro LEDCandleND4.3-40W E14 827B35FRG	-20 to +45 °C	5 kWh
929001238492	CorePro LEDCandleND2-25W E14BA35 827CL G	-20°C to 45°C	2 kWh
929001238592	CorePro LEDCandleND2-25W ST35 E14 827CLG	-20°C to 45°C	2 kWh
929001889792	CorePro LEDCandleND4.3-40W E14 827B35CLG	-20 to +45 °C	5 kWh
929001890492	CorePro LEDLusterND4.3-40W E14 827P45CLG	-20 to +45 °C	5 kWh
929002028092	CorePro LEDCandle ND6.5-60W B35E14827CLG	-20 to +45 °C	7 kWh
929001890592	CorePro LEDLusterND4.3-40W E27 827P45CLG	-20 to +45 °C	5 kWh

