



Our most efficient LED bulb

MASTER UltraEfficient LED bulb

This is the most efficient LED bulb from Philips brand. 210lm/W helps to concrete the company statement of sustainability. 50000 hour lifetime helps to extend the replacement cycle to reduce the waste. This is not only the high SPEC product, but also keep the light quality of Philips brand

Benefits

- energy saving, 60% less energy comparing with standard Philips LED bulbs
- Very long lifetime that reduces the need for replacement
- Easy replacement of conventional lamps

Features

- Ultra energy efficient, with 210lm/W
- Long lifetime, more than 3 times longer lifetime than the normal LED products
- Well optimized the look and feel, without impact on the application. Easy for the installation
- Designed to be seen, they look good on and off
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Domestic application
- Hospitality: restaurants and hotels

MASTER UltraEfficient LED bulb

Versions



LED CLA 60W A60 E27 2700K CL
UE D SRT4 RTP



LED CLA 60W ST64 E27 2700K CL
UE SRT4




LED CLA 60W G95 E27 4000K CL
UE SRT4



LED CLA 40W A60 E27 2700K CL
UE SRT4 1



LEDbulb MAS EU6 A60 E27 CL



LED CLA 40W A60 E27 4000K CL
UE SRT4 1




LED CLA 100WA60 E27 4000K CL
UE SRT4



LEDbulb MAS EU6 A60 E27 FR

MASTER UltraEfficient LED bulb





Dimensional drawing



Product	D	C
5A19/UE/927/CL/G/E26/D T20 3/4CT	60 mm	105 mm
5A19/UE/927/CL/G/E26/D T20 4/1PF CA	60 mm	105 mm
5A19/UE/927/CL/G/E26/D T20 4/2PF	60 mm	105 mm
5A19/UE/927/FR/G/E26/D T20 3/4CT	60 mm	105 mm
5A19/UE/927/FR/G/E26/D T20 4/1PF CA	60 mm	105 mm
5A19/UE/950/CL/G/E26/D T20 3/4CT	60 mm	105 mm
5A19/UE/950/CL/G/E26/D T20 4/1PF CA	60 mm	105 mm
5A19/UE/950/CL/G/E26/D T20 4/2PF	60 mm	105 mm
5A19/UE/950/FR/G/E26/D T20 3/4CT	60 mm	105 mm
5A19/UE/950/FR/G/E26/D T20 4/1PF CA	60 mm	105 mm
8.9A19/UE/927/CL/G/E26/D T20 3/1PF	60 mm	105 mm
8.9A19/UE/927/CL/G/E26/D T20 4/1PF CA	60 mm	105 mm
8.9A19/UE/927/CL/G/E26/D T20 4/2PF	60 mm	105 mm
8.9A19/UE/927/FR/G/E26/D T20 4/1PF CA	60 mm	105 mm
8.9A19/UE/927/FR/G/E26/D T20 4/2PF	60 mm	105 mm
8.9A19/UE/950/CL/G/E26/D T20 3/1PF	60 mm	105 mm
8.9A19/UE/950/CL/G/E26/D T20 4/1PF CA	60 mm	105 mm
8.9A19/UE/950/CL/G/E26/D T20 4/2PF	60 mm	105 mm
8.9A19/UE/950/FR/G/E26/D T20 4/1PF CA	60 mm	105 mm
8.9A19/UE/950/FR/G/E26/D T20 4/2PF	60 mm	105 mm
LED CLA 4W A60 E27 2700K FR UE SRT6	60 mm	104 mm
LED CLA 4W A60 E27 4000K FR UE SRT6	60 mm	104 mm
LED CLA 7.3W A60 E27 2700K FR UE SRT6	60 mm	104 mm
LED CLA 7.3W A60 E27 4000K FR UE SRT6	60 mm	104 mm
MAS LEDBulb D 4-60W E27 827 A60 CL G UE	60 mm	108 mm
MAS LEDBulb D 4-60W E27 827 A60 FR G UE	60 mm	108 mm
MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND4-60W E27 827 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND4-60W E27 827 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND4-60W E27 830 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND4-60W E27 830 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND4-60W E27 840 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND4-60W E27 840 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	60 mm	104 mm
MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	60 mm	104 mm
MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	60 mm	104 mm
MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	60 mm	104 mm
MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	60 mm	104 mm
MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	60 mm	104 mm
MAS LEDBulbND7.3-100W E27 840 A60 CL GUE	60 mm	104 mm
MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	60 mm	104 mm

MASTER UltraEfficient LED bulb

Dimensional drawing



Product	D	C
LED CLA 4W A60 B22 2700K FR UE SRT6	60 mm	102 mm
LED CLA 4W A60 B22 4000K FR UE SRT6	60 mm	102 mm
LED CLA 7.3W A60 B22 2700K FR UE SRT6	60 mm	102 mm
LED CLA 7.3W A60 B22 4000K FR UE SRT6	60 mm	102 mm

Product	D	C
MAS LEDBulbND4-60W E27 827 ST64 CL G UE	64 mm	140 mm

Product	D	C
MAS LEDBulbND4-60W E27 840 G95 CL G UE	95 mm	140 mm

Product	D	C
MAS LEDBulb D 4-60W E27 827 A60 CL G UE	60 mm	123 mm
MAS LEDBulb D 4-60W E27 827 A60 FR G UE	60 mm	123 mm
MAS LEDBulb D 4-60W E27 830 A60 CL G UE	60 mm	123 mm
MAS LEDBulb D 4-60W E27 830 A60 FR G UE	60 mm	123 mm

MASTER UltraEfficient LED bulb

General Information	
Nominal lifetime	50,000 hour(s)
Light Technical	
Beam Angle (Nom)	300 degree(s)
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
929003800102	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	E27	500,000
929003623902	MAS LEDBulbND4-60W E27 840 A60 CL G UE	E27	500,000
929003624702	MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	E27	500,000
929003623502	MAS LEDBulbND4-60W E27 827 A60 CL G UE	E27	500,000
929003624302	MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	E27	500,000
929003702902	MAS LEDBulbND4-60W E27 830 A60 CL G UE	E27	500,000
929003703302	MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	E27	500,000
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	B22	50,000
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	B22	50,000
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	B22	50,000
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	B22	50,000
929003765503	8.9A19/UE/950/CL/G/E26/D T20 4/2PF	E26	100,000
929003765505	8.9A19/UE/950/CL/G/E26/D T20 4/1PF CA	E26	100,000
929003765593	8.9A19/UE/950/CL/G/E26/D T20 3/1PF	E26	100,000
929003622902	MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	E27	500,000
929003623302	MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	E27	50,000
929003623702	MAS LEDBulbND4-60W E27 827 A60 FR G UE	E27	500,000
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	E27	50,000
929003624102	MAS LEDBulbND4-60W E27 840 A60 FR G UE	E27	500,000
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	E27	50,000
929003624502	MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	E27	50,000
929003624902	MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	E27	50,000
929003625302	MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	E27	500,000
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	E27	50,000
929003625702	MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	E27	500,000
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	E27	50,000
929003702702	MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	E27	50,000
929003703102	MAS LEDBulbND4-60W E27 830 A60 FR G UE	E27	500,000

Order Code	Full Product Name	Cap-Base	Switching Cycle
929003703502	MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	E27	500,000
929003703902	MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	E27	500,000
929003800202	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	E27	500,000
929003625102	MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	E27	500,000
929003703702	MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	E27	500,000
929003642402	MAS LEDBulbND4-60W E27 827 ST64 CL G UE	E27	50,000
929003744403	5A19/UE/927/FR/G/E26/D T20 3/4CT	E26	100,000
929003744495	5A19/UE/927/FR/G/E26/D T20 4/1PF CA	E26	100,000
929003744503	5A19/UE/950/FR/G/E26/D T20 3/4CT	E26	100,000
929003744595	5A19/UE/950/FR/G/E26/D T20 4/1PF CA	E26	100,000
929004234603	8.9A19/UE/927/FR/G/E26/D T20 4/2PF	E26	100,000
929004234605	8.9A19/UE/927/FR/G/E26/D T20 4/1PF CA	E26	100,000
929004234703	8.9A19/UE/950/FR/G/E26/D T20 4/2PF	E26	100,000
929004234705	8.9A19/UE/950/FR/G/E26/D T20 4/1PF CA	E26	100,000
929003642602	MAS LEDBulbND4-60W E27 840 G95 CL G UE	E27	50,000
929003765303	8.9A19/UE/927/CL/G/E26/D T20 4/2PF	E26	100,000
929003765305	8.9A19/UE/927/CL/G/E26/D T20 4/1PF CA	E26	100,000
929003765393	8.9A19/UE/927/CL/G/E26/D T20 3/1PF	E26	100,000
929003622702	MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	E27	500,000
929003702502	MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	E27	500,000
929003765403	5A19/UE/950/CL/G/E26/D T20 3/4CT	E26	100,000
929003765493	5A19/UE/950/CL/G/E26/D T20 4/2PF	E26	100,000
929003765495	5A19/UE/950/CL/G/E26/D T20 4/1PF CA	E26	100,000
929003691502	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	E27	50,000
929003691702	MAS LEDBulb D 4-60W E27 830 A60 CL G UE	E27	50,000
929003623102	MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	E27	500,000
929003765203	5A19/UE/927/CL/G/E26/D T20 3/4CT	E26	100,000
929003765293	5A19/UE/927/CL/G/E26/D T20 4/2PF	E26	100,000
929003765295	5A19/UE/927/CL/G/E26/D T20 4/1PF CA	E26	100,000
929003625502	MAS LEDBulbND7.3-100W E27 840 A60 CL GUE	E27	500,000

MASTER UltraEfficient LED bulb

Order Code	Full Product Name	Cap-Base	Switching Cycle
929003691602	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	E27	50,000

Order Code	Full Product Name	Cap-Base	Switching Cycle
929003691802	MAS LEDBulb D 4-60W E27 830 A60 FR G UE	E27	50,000

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003800102	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	2700 K	80	827	840 lm
929003623902	MAS LEDBulbND4-60W E27 840 A60 CL G UE	4000 K	80	840	840 lm
929003624702	MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	4000 K	80	840	1,095 lm
929003623502	MAS LEDBulbND4-60W E27 827 A60 CL G UE	2700 K	80	827	840 lm
929003624302	MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	2700 K	80	827	1,095 lm
929003702902	MAS LEDBulbND4-60W E27 830 A60 CL G UE	3000 K	80	830	840 lm
929003703302	MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	3000 K	80	830	1,095 lm
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	2700 K	80	827	840 lm
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	4000 K	80	840	840 lm
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	2700 K	80	827	1,535 lm
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	4000 K	80	840	1,535 lm
929003765503	8.9A19/UE/950/CL/G/E 26/D T20 4/2PF	5000 K	90	950	1,520 lm
929003765505	8.9A19/UE/950/CL/G/E 26/D T20 4/1PF CA	5000 K	90	950	1,520 lm
929003765593	8.9A19/UE/950/CL/G/E 26/D T20 3/1PF	5000 K	90	950	1,520 lm
929003622902	MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	2700 K	80	827	485 lm
929003623302	MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	4000 K	80	840	485 lm
929003623702	MAS LEDBulbND4-60W E27 827 A60 FR G UE	2700 K	80	827	840 lm
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	2700 K	80	827	840 lm
929003624102	MAS LEDBulbND4-60W E27 840 A60 FR G UE	4000 K	80	840	840 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	4000 K	80	840	840 lm
929003624502	MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	2700 K	80	827	1,095 lm
929003624902	MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	4000 K	80	840	1,095 lm
929003625302	MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	2700 K	80	827	1,535 lm
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	2700 K	80	827	1,535 lm
929003625702	MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	4000 K	80	840	1,535 lm
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	4000 K	80	840	1,535 lm
929003702702	MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	3000 K	80	830	485 lm
929003703102	MAS LEDBulbND4-60W E27 830 A60 FR G UE	3000 K	80	830	840 lm
929003703502	MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	3000 K	80	830	1,095 lm
929003703902	MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	3000 K	80	830	1,535 lm
929003800202	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	2700 K	80	827	840 lm
929003625102	MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	2700 K	80	827	1,535 lm
929003703702	MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	3000 K	80	830	1,535 lm
929003642402	MAS LEDBulbND4-60W E27 827 ST64 CL G UE	2700 K	80	827	840 lm
929003744403	5A19/UE/927/FR/G/E26 /D T20 3/4CT	2700 K	90	927	850 lm
929003744495	5A19/UE/927/FR/G/E26 /D T20 4/1PF CA	2700 K	90	927	850 lm

MASTER UltraEfficient LED bulb

Order Code	Full Product Name	Correlated	Color	Luminous
		Color Temperature (Nom)	rendering index (CRI)	
929003744503	5A19/UE/950/FR/G/E2 6/D T20 3/4CT	5000 K	90	950 850 lm
929003744595	5A19/UE/950/FR/G/E2 6/D T20 4/1PF CA	5000 K	90	950 850 lm
929004234603	8.9A19/UE/927/FR/G/E 26/D T20 4/2PF	2700 K	90	927 1,520 lm
929004234605	8.9A19/UE/927/FR/G/E 26/D T20 4/1PF CA	2700 K	90	927 1,520 lm
929004234703	8.9A19/UE/950/FR/G/E 26/D T20 4/2PF	5000 K	90	950 1,520 lm
929004234705	8.9A19/UE/950/FR/G/E 26/D T20 4/1PF CA	5000 K	90	950 1,520 lm
929003642602	MAS LEDBulbND4-60W E27 840 G95 CL G UE	4000 K	80	840 840 lm
929003765303	8.9A19/UE/927/CL/G/E 26/D T20 4/2PF	2700 K	90	927 1,520 lm
929003765305	8.9A19/UE/927/CL/G/E 26/D T20 4/1PF CA	2700 K	90	927 1,520 lm
929003765393	8.9A19/UE/927/CL/G/E 26/D T20 3/1PF	2700 K	90	927 1,520 lm
929003622702	MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	2700 K	80	827 485 lm
929003702502	MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	3000 K	80	830 485 lm

Order Code	Full Product Name	Correlated	Color	Luminous
		Color Temperature (Nom)	rendering index (CRI)	
929003765403	5A19/UE/950/CL/G/E2 6/D T20 3/4CT	5000 K	90	950 850 lm
929003765493	5A19/UE/950/CL/G/E2 6/D T20 4/2PF	5000 K	90	950 850 lm
929003765495	5A19/UE/950/CL/G/E2 6/D T20 4/1PF CA	5000 K	90	950 850 lm
929003691502	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	2700 K	80	827 840 lm
929003691702	MAS LEDBulb D 4-60W E27 830 A60 CL G UE	3000 K	80	830 840 lm
929003623102	MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	4000 K	80	840 485 lm
929003765203	5A19/UE/927/CL/G/E26 /D T20 3/4CT	2700 K	90	927 850 lm
929003765293	5A19/UE/927/CL/G/E26 /D T20 4/2PF	2700 K	90	927 850 lm
929003765295	5A19/UE/927/CL/G/E26 /D T20 4/1PF CA	2700 K	90	927 850 lm
929003625502	MAS LEDBulbND7.3-100W E27 840 A60 CL G UE	4000 K	80	840 1,535 lm
929003691602	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	2700 K	80	827 840 lm
929003691802	MAS LEDBulb D 4-60W E27 830 A60 FR G UE	3000 K	80	830 840 lm

Operating and Electrical

Order Code	Full Product Name	Input	Line	Power	Wattage
		Frequency	Frequency	Consumption	Equivalent
929003800102	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	50 to 60 Hz	-	4 W	60 W
929003623902	MAS LEDBulbND4-60W E27 840 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003624702	MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	5.2 W	75 W
929003623502	MAS LEDBulbND4-60W E27 827 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003624302	MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	5.2 W	75 W

Order Code	Full Product Name	Input	Line	Power	Wattage
		Frequency	Frequency	Consumption	Equivalent
929003702902	MAS LEDBulbND4-60W E27 830 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003703302	MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	5.2 W	75 W
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	50 to 60 Hz	-	4 W	60 W
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	50 to 60 Hz	-	4 W	60 W
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W

MASTER UltraEfficient LED bulb

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W		E27 830 A60 FR G UE				
929003765503	8.9A19/UE/950/CL/ G/E26/D T20 4/2PF	60 Hz	-	8.9 W	100 W	929003703102	MAS LEDBulbND4-60W E27 830 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003765505	8.9A19/UE/950/CL/ G/E26/D T20 4/1PF CA	60 Hz	-	8.9 W	100 W	929003703502	MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	5.2 W	75 W
929003765593	8.9A19/UE/950/CL/ G/E26/D T20 3/1PF	60 Hz	-	8.9 W	100 W	929003703902	MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	50 to 60 Hz	50 to 60 Hz	7.3 W	100 W
929003622902	MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	2.3 W	40 W	929003800202	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	50 to 60 Hz	-	4 W	60 W
929003623302	MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	2.3 W	40 W	929003625102	MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	50 to 60 Hz	50 to 60 Hz	7.3 W	100 W
929003623702	MAS LEDBulbND4-60W E27 827 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W	929003703702	MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	50 to 60 Hz	50 to 60 Hz	7.3 W	100 W
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	50 to 60 Hz	-	4 W	60 W	929003642402	MAS LEDBulbND4-60W E27 827 ST64 CL G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003624102	MAS LEDBulbND4-60W E27 840 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W	929003744403	5A19/UE/927/FR/G/ E26/D T20 3/4CT	60 Hz	-	5 W	60 W
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	50 to 60 Hz	-	4 W	60 W	929003744495	5A19/UE/927/FR/G/ E26/D T20 4/1PF CA	60 Hz	-	5 W	60 W
929003624502	MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	5.2 W	75 W	929003744503	5A19/UE/950/FR/G/ E26/D T20 3/4CT	60 Hz	-	5 W	60 W
929003624902	MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	5.2 W	75 W	929003744595	5A19/UE/950/FR/G/ E26/D T20 4/1PF CA	60 Hz	-	5 W	60 W
929003625302	MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	50 to 60 Hz	50 to 60 Hz	7.3 W	100 W	929004234603	8.9A19/UE/927/FR/ G/E26/D T20 4/2PF	60 Hz	-	8.9 W	100 W
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W	929004234605	8.9A19/UE/927/FR/ G/E26/D T20 4/1PF CA	60 Hz	-	8.9 W	100 W
929003625702	MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	50 to 60 Hz	50 to 60 Hz	7.3 W	100 W	929004234703	8.9A19/UE/950/FR/ G/E26/D T20 4/2PF	60 Hz	-	8.9 W	100 W
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W	929004234705	8.9A19/UE/950/FR/ G/E26/D T20 4/1PF CA	60 Hz	-	8.9 W	100 W
929003702702	MAS LEDBulbND2.3-40W	50 to 60 Hz	50 to 60 Hz	2.3 W	40 W	929003642602	MAS LEDBulbND4-60W E27 840 G95 CL G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
						929003765303	8.9A19/UE/927/CL/G /E26/D T20 4/2PF	60 Hz	-	8.9 W	100 W

MASTER UltraEfficient LED bulb

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003765305	8.9A19/UE/927/CL/G/E26/D T20 4/1PF CA	60 Hz	-	8.9 W	100 W
929003765393	8.9A19/UE/927/CL/G/E26/D T20 3/1PF	60 Hz	-	8.9 W	100 W
929003622702	MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	2.3 W	40 W
929003702502	MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	2.3 W	40 W
929003765403	5A19/UE/950/CL/G/E26/D T20 3/4CT	60 Hz	-	5 W	60 W
929003765493	5A19/UE/950/CL/G/E26/D T20 4/2PF	60 Hz	-	5 W	60 W
929003765495	5A19/UE/950/CL/G/E26/D T20 4/1PF CA	60 Hz	-	5 W	60 W
929003691502	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003691702	MAS LEDBulb D 4-60W E27 830 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003623102	MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	50 to 60 Hz	50 to 60 Hz	2.3 W	40 W
929003765203	5A19/UE/927/CL/G/E26/D T20 3/4CT	60 Hz	-	5 W	60 W
929003765293	5A19/UE/927/CL/G/E26/D T20 4/2PF	60 Hz	-	5 W	60 W
929003765295	5A19/UE/927/CL/G/E26/D T20 4/1PF CA	60 Hz	-	5 W	60 W
929003625502	MAS LEDBulbND7.3-100W E27 840 A60 CL GUE	50 to 60 Hz	50 to 60 Hz	7.3 W	100 W
929003691602	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W
929003691802	MAS LEDBulb D 4-60W E27 830 A60 FR G UE	50 to 60 Hz	50 to 60 Hz	4 W	60 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003800102	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	70 °C
929003623902	MAS LEDBulbND4-60W E27 840 A60 CL G UE	70 °C
929003624702	MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	70 °C
929003623502	MAS LEDBulbND4-60W E27 827 A60 CL G UE	70 °C
929003624302	MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	70 °C
929003702902	MAS LEDBulbND4-60W E27 830 A60 CL G UE	70 °C
929003703302	MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	70 °C
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	70 °C
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	70 °C
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	70 °C
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	70 °C
929003765503	8.9A19/UE/950/CL/G/E26/D T20 4/2PF	-
929003765505	8.9A19/UE/950/CL/G/E26/D T20 4/1PF CA	-
929003765593	8.9A19/UE/950/CL/G/E26/D T20 3/1PF	-
929003622902	MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	70 °C
929003623302	MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	70 °C
929003623702	MAS LEDBulbND4-60W E27 827 A60 FR G UE	70 °C
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	70 °C
929003624102	MAS LEDBulbND4-60W E27 840 A60 FR G UE	70 °C
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	70 °C
929003624502	MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	70 °C
929003624902	MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	70 °C
929003625302	MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	70 °C
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	70 °C
929003625702	MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	70 °C
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	70 °C
929003702702	MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	70 °C
929003703102	MAS LEDBulbND4-60W E27 830 A60 FR G UE	70 °C
929003703502	MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	70 °C
929003703902	MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	70 °C
929003800202	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	70 °C
929003625102	MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	70 °C
929003703702	MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	70 °C
929003642402	MAS LEDBulbND4-60W E27 827 ST64 CL G UE	70 °C
929003744403	5A19/UE/927/FR/G/E26/D T20 3/4CT	-
929003744495	5A19/UE/927/FR/G/E26/D T20 4/1PF CA	-
929003744503	5A19/UE/950/FR/G/E26/D T20 3/4CT	-
929003744595	5A19/UE/950/FR/G/E26/D T20 4/1PF CA	-
929004234603	8.9A19/UE/927/FR/G/E26/D T20 4/2PF	-
929004234605	8.9A19/UE/927/FR/G/E26/D T20 4/1PF CA	-
929004234703	8.9A19/UE/950/FR/G/E26/D T20 4/2PF	-
929004234705	8.9A19/UE/950/FR/G/E26/D T20 4/1PF CA	-
929003642602	MAS LEDBulbND4-60W E27 840 G95 CL G UE	70 °C
929003765303	8.9A19/UE/927/CL/G/E26/D T20 4/2PF	-

MASTER UltraEfficient LED bulb

Order Code	Full Product Name	T-Case Maximum (Nom)
929003765305	8.9A19/UE/927/CL/G/E26/D T20 4/1PF CA	-
929003765393	8.9A19/UE/927/CL/G/E26/D T20 3/1PF	-
929003622702	MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	70 °C
929003702502	MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	70 °C
929003765403	5A19/UE/950/CL/G/E26/D T20 3/4CT	-
929003765493	5A19/UE/950/CL/G/E26/D T20 4/2PF	-
929003765495	5A19/UE/950/CL/G/E26/D T20 4/1PF CA	-
929003691502	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	70 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003691702	MAS LEDBulb D 4-60W E27 830 A60 CL G UE	70 °C
929003623102	MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	70 °C
929003765203	5A19/UE/927/CL/G/E26/D T20 3/4CT	-
929003765293	5A19/UE/927/CL/G/E26/D T20 4/2PF	-
929003765295	5A19/UE/927/CL/G/E26/D T20 4/1PF CA	-
929003625502	MAS LEDBulbND7.3-100W E27 840 A60 CL G UE	70 °C
929003691602	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	70 °C
929003691802	MAS LEDBulb D 4-60W E27 830 A60 FR G UE	70 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929003800102	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	Only with specific dimmers
929003623902	MAS LEDBulbND4-60W E27 840 A60 CL G UE	No
929003624702	MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	No
929003623502	MAS LEDBulbND4-60W E27 827 A60 CL G UE	No
929003624302	MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	No
929003702902	MAS LEDBulbND4-60W E27 830 A60 CL G UE	No
929003703302	MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	No
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	No
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	No
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	No
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	No
929003765503	8.9A19/UE/950/CL/G/E26/D T20 4/2PF	Only with specific dimmers
929003765505	8.9A19/UE/950/CL/G/E26/D T20 4/1PF CA	Only with specific dimmers
929003765593	8.9A19/UE/950/CL/G/E26/D T20 3/1PF	Only with specific dimmers
929003622902	MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	No
929003623302	MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	No
929003623702	MAS LEDBulbND4-60W E27 827 A60 FR G UE	No
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	No
929003624102	MAS LEDBulbND4-60W E27 840 A60 FR G UE	No
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	No
929003624502	MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	No
929003624902	MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	No
929003625302	MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	No
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	No
929003625702	MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	No
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	No
929003702702	MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	No
929003703102	MAS LEDBulbND4-60W E27 830 A60 FR G UE	No
929003703502	MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	No
929003703902	MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	No
929003800202	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	Only with specific dimmers
929003625102	MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	No
929003703702	MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	No
929003642402	MAS LEDBulbND4-60W E27 827 ST64 CL G UE	No

Order Code	Full Product Name	Dimmable
929003744403	5A19/UE/927/FR/G/E26/D T20 3/4CT	Only with specific dimmers
929003744495	5A19/UE/927/FR/G/E26/D T20 4/1PF CA	Only with specific dimmers
929003744503	5A19/UE/950/FR/G/E26/D T20 3/4CT	Only with specific dimmers
929003744595	5A19/UE/950/FR/G/E26/D T20 4/1PF CA	Only with specific dimmers
929004234603	8.9A19/UE/927/FR/G/E26/D T20 4/2PF	Only with specific dimmers
929004234605	8.9A19/UE/927/FR/G/E26/D T20 4/1PF CA	Only with specific dimmers
929004234703	8.9A19/UE/950/FR/G/E26/D T20 4/2PF	Only with specific dimmers
929004234705	8.9A19/UE/950/FR/G/E26/D T20 4/1PF CA	Only with specific dimmers
929003642602	MAS LEDBulbND4-60W E27 840 G95 CL G UE	No
929003765303	8.9A19/UE/927/CL/G/E26/D T20 4/2PF	Only with specific dimmers
929003765305	8.9A19/UE/927/CL/G/E26/D T20 4/1PF CA	Only with specific dimmers
929003765393	8.9A19/UE/927/CL/G/E26/D T20 3/1PF	Only with specific dimmers
929003622702	MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	No
929003702502	MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	No
929003765403	5A19/UE/950/CL/G/E26/D T20 3/4CT	Only with specific dimmers
929003765493	5A19/UE/950/CL/G/E26/D T20 4/2PF	Only with specific dimmers
929003765495	5A19/UE/950/CL/G/E26/D T20 4/1PF CA	Only with specific dimmers
929003691502	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	Only with specific dimmers
929003691702	MAS LEDBulb D 4-60W E27 830 A60 CL G UE	Only with specific dimmers
929003623102	MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	No
929003765203	5A19/UE/927/CL/G/E26/D T20 3/4CT	Only with specific dimmers

MASTER UltraEfficient LED bulb

Order Code	Full Product Name	Dimmable
929003765293	5A19/UE/927/CL/G/E26/D T20 4/2PF	Only with specific dimmers
929003765295	5A19/UE/927/CL/G/E26/D T20 4/1PF CA	Only with specific dimmers
929003625502	MAS LEDBulbND7.3-100W E27 840 A60 CL GUE	No

Order Code	Full Product Name	Dimmable
929003691602	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	Only with specific dimmers
929003691802	MAS LEDBulb D 4-60W E27 830 A60 FR G UE	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003800102	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	Clear	A60
929003623902	MAS LEDBulbND4-60W E27 840 A60 CL G UE	Clear	A60
929003624702	MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	Clear	A60
929003623502	MAS LEDBulbND4-60W E27 827 A60 CL G UE	Clear	A60
929003624302	MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	Clear	A60
929003702902	MAS LEDBulbND4-60W E27 830 A60 CL G UE	Clear	A60
929003703302	MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	Clear	A60
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	Frosted	A60
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	Frosted	A60
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	Frosted	A60
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	Frosted	A60
929003765503	8.9A19/UE/950/CL/G/E26/D T20 4/2PF	Clear	A19
929003765505	8.9A19/UE/950/CL/G/E26/D T20 4/1PF CA	Clear	A19
929003765593	8.9A19/UE/950/CL/G/E26/D T20 3/1PF	Clear	A19
929003622902	MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	Frosted	A60
929003623302	MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	Frosted	A60
929003623702	MAS LEDBulbND4-60W E27 827 A60 FR G UE	Frosted	A60
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	Frosted	A60
929003624102	MAS LEDBulbND4-60W E27 840 A60 FR G UE	Frosted	A60
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	Frosted	A60
929003624502	MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	Frosted	A60
929003624902	MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	Frosted	A60
929003625302	MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	Frosted	A60
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	Frosted	A60
929003625702	MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	Frosted	A60
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	Frosted	A60
929003702702	MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	Frosted	A60
929003703102	MAS LEDBulbND4-60W E27 830 A60 FR G UE	Frosted	A60
929003703502	MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	Frosted	A60
929003703902	MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	Frosted	A60

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003800202	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	Frosted	A60
929003625102	MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	Clear	A60
929003703702	MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	Clear	A60
929003642402	MAS LEDBulbND4-60W E27 827 ST64 CL G UE	Clear	ST64
929003744403	5A19/UE/927/FR/G/E26/D T20 3/4CT	Frosted	A19
929003744495	5A19/UE/927/FR/G/E26/D T20 4/1PF CA	Frosted	A19
929003744503	5A19/UE/950/FR/G/E26/D T20 3/4CT	Frosted	A19
929003744595	5A19/UE/950/FR/G/E26/D T20 4/1PF CA	Frosted	A19
929004234603	8.9A19/UE/927/FR/G/E26/D T20 4/2PF	Frosted	A19
929004234605	8.9A19/UE/927/FR/G/E26/D T20 4/1PF CA	Frosted	A19
929004234703	8.9A19/UE/950/FR/G/E26/D T20 4/2PF	Frosted	A19
929004234705	8.9A19/UE/950/FR/G/E26/D T20 4/1PF CA	Frosted	A19
929003642602	MAS LEDBulbND4-60W E27 840 G95 CL G UE	Clear	G95
929003765303	8.9A19/UE/927/CL/G/E26/D T20 4/2PF	Clear	A19
929003765305	8.9A19/UE/927/CL/G/E26/D T20 4/1PF CA	Clear	A19
929003765393	8.9A19/UE/927/CL/G/E26/D T20 3/1PF	Clear	A19
929003622702	MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	Clear	A60
929003702502	MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	Clear	A60
929003765403	5A19/UE/950/CL/G/E26/D T20 3/4CT	Clear	A19
929003765493	5A19/UE/950/CL/G/E26/D T20 4/2PF	Clear	A19
929003765495	5A19/UE/950/CL/G/E26/D T20 4/1PF CA	Clear	A19
929003691502	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	Clear	A60
929003691702	MAS LEDBulb D 4-60W E27 830 A60 CL G UE	Clear	A60
929003623102	MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	Clear	A60
929003765203	5A19/UE/927/CL/G/E26/D T20 3/4CT	Clear	A19
929003765293	5A19/UE/927/CL/G/E26/D T20 4/2PF	Clear	A19
929003765295	5A19/UE/927/CL/G/E26/D T20 4/1PF CA	Clear	A19
929003625502	MAS LEDBulbND7.3-100W E27 840 A60 CL GUE	Clear	A60
929003691602	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	Frosted	A60
929003691802	MAS LEDBulb D 4-60W E27 830 A60 FR G UE	Frosted	A60

Approval and Application









MASTER UltraEfficient LED bulb

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003800102	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	-20 to +45 °C	4 kWh
929003623902	MAS LEDBulbND4-60W E27 840 A60 CL G UE	-20 to +45 °C	4 kWh
929003624702	MAS LEDBulbND5.2-75W E27 840 A60 CL G UE	-20 to +45 °C	6 kWh
929003623502	MAS LEDBulbND4-60W E27 827 A60 CL G UE	-20 to +45 °C	4 kWh
929003624302	MAS LEDBulbND5.2-75W E27 827 A60 CL G UE	-20 to +45 °C	6 kWh
929003702902	MAS LEDBulbND4-60W E27 830 A60 CL G UE	-20 to +45 °C	4 kWh
929003703302	MAS LEDBulbND5.2-75W E27 830 A60 CL G UE	-20 to +45 °C	6 kWh
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	-20 to +45 °C	-
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	-20 to +45 °C	-
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	-20 to +45 °C	-
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	-20 to +45 °C	-
929003765503	8.9A19/UE/950/CL/G/E26/D T20 4/2PF	-20 to +40 °C	-
929003765505	8.9A19/UE/950/CL/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929003765593	8.9A19/UE/950/CL/G/E26/D T20 3/1PF	-20 to +40 °C	-
929003622902	MAS LEDBulbND2.3-40W E27 827 A60 FR G UE	-20 to +45 °C	3 kWh
929003623302	MAS LEDBulbND2.3-40W E27 840 A60 FR G UE	-20 to +45 °C	3 kWh
929003623702	MAS LEDBulbND4-60W E27 827 A60 FR G UE	-20 to +45 °C	4 kWh
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	-20 to +45 °C	-
929003624102	MAS LEDBulbND4-60W E27 840 A60 FR G UE	-20 to +45 °C	4 kWh
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	-20 to +45 °C	-
929003624502	MAS LEDBulbND5.2-75W E27 827 A60 FR G UE	-20 to +45 °C	6 kWh
929003624902	MAS LEDBulbND5.2-75W E27 840 A60 FR G UE	-20 to +45 °C	6 kWh
929003625302	MAS LEDBulbND7.3-100W E27 827 A60 FR GUE	-20 to +45 °C	8 kWh
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	-20 to +45 °C	-
929003625702	MAS LEDBulbND7.3-100W E27 840 A60 FR GUE	-20 to +45 °C	8 kWh


Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	-20 to +45 °C	-
929003702702	MAS LEDBulbND2.3-40W E27 830 A60 FR G UE	-20 to +45 °C	3 kWh
929003703102	MAS LEDBulbND4-60W E27 830 A60 FR G UE	-20 to +45 °C	4 kWh
929003703502	MAS LEDBulbND5.2-75W E27 830 A60 FR G UE	-20 to +45 °C	6 kWh
929003703902	MAS LEDBulbND7.3-100W E27 830 A60 FR GUE	-20 to +45 °C	8 kWh
929003800202	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	-20 to +45 °C	4 kWh
929003625102	MAS LEDBulbND7.3-100W E27 827 A60 CL GUE	-20 to +45 °C	8 kWh
929003703702	MAS LEDBulbND7.3-100W E27 830 A60 CL GUE	-20 to +45 °C	8 kWh
929003642402	MAS LEDBulbND4-60W E27 827 ST64 CL G UE	-20 to +45 °C	4 kWh
929003744403	5A19/UE/927/FR/G/E26/D T20 3/4CT	-20 to +40 °C	-
929003744495	5A19/UE/927/FR/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929003744503	5A19/UE/950/FR/G/E26/D T20 3/4CT	-20 to +40 °C	-
929003744595	5A19/UE/950/FR/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929004234603	8.9A19/UE/927/FR/G/E26/D T20 4/2PF	-20 to +40 °C	-
929004234605	8.9A19/UE/927/FR/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929004234703	8.9A19/UE/950/FR/G/E26/D T20 4/2PF	-20 to +40 °C	-
929004234705	8.9A19/UE/950/FR/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929003642602	MAS LEDBulbND4-60W E27 840 G95 CL G UE	-20 to +45 °C	4 kWh
929003765303	8.9A19/UE/927/CL/G/E26/D T20 4/2PF	-20 to +40 °C	-
929003765305	8.9A19/UE/927/CL/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929003765393	8.9A19/UE/927/CL/G/E26/D T20 3/1PF	-20 to +40 °C	-
929003622702	MAS LEDBulbND2.3-40W E27 827 A60 CL G UE	-20 to +45 °C	3 kWh
929003702502	MAS LEDBulbND2.3-40W E27 830 A60 CL G UE	-20 to +45 °C	3 kWh
929003765403	5A19/UE/950/CL/G/E26/D T20 3/4CT	-20 to +40 °C	-
929003765493	5A19/UE/950/CL/G/E26/D T20 4/2PF	-20 to +40 °C	-

MASTER UltraEfficient LED bulb


Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003765495	5A19/UE/950/CL/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929003691502	MAS LEDBulb D 4-60W E27 827 A60 CL G UE	-20 to +45 °C	4 kWh
929003691702	MAS LEDBulb D 4-60W E27 830 A60 CL G UE	-20 to +45 °C	4 kWh
929003623102	MAS LEDBulbND2.3-40W E27 840 A60 CL G UE	-20 to +45 °C	3 kWh
929003765203	5A19/UE/927/CL/G/E26/D T20 3/4CT	-20 to +40 °C	-
929003765293	5A19/UE/927/CL/G/E26/D T20 4/2PF	-20 to +40 °C	-
929003765295	5A19/UE/927/CL/G/E26/D T20 4/1PF CA	-20 to +40 °C	-
929003625502	MAS LEDBulbND7.3-100W E27 840 A60 CL G UE	-20 to +45 °C	8 kWh
929003691602	MAS LEDBulb D 4-60W E27 827 A60 FR G UE	-20 to +45 °C	4 kWh
929003691802	MAS LEDBulb D 4-60W E27 830 A60 FR G UE	-20 to +45 °C	4 kWh




MASTER UltraEfficient LED bulb




(cd/1000lm) 0°




(cd/1000lm) 0°




(cd/1000lm) 0°




(cd/1000lm) 0°




(cd/1000lm) 0°




(cd/1000lm) 0°




(cd/1000lm) 0°



(cd/1000lm) 0°



(cd/1000lm) 0°



(cd/1000lm) 0°

MASTER UltraEfficient LED bulb

