



Long Life, Environmentally- Responsible Lamps

T8 Slimline

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Benefits

- Sustainable lighting solution - Reduces the impact on the environment—low mercury and energy efficient.
- Reduced lamp end blackening.

Features

- Up to 15,000 hours rated average life
- T8 lamps means reduced maintenance and disposal costs.
- Environmentally Responsible—Low mercury.

Application

- Industry
- Parking

Warnings and Safety

- Lamp contains mercury.
- Manage in accord with disposal laws.


T8 Slimline

Versions



LPPR F-T8-ISP FA8 GB

Dimensional drawing



Product
F48T8/TL865/ALTO 30W 25 PK
F96T8/TL865/ALTO 60W 25PK

General Information	
Cap-Base	FA8
Light Technical	
Color Designation	6500 Kelvin
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	>81
Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Shape	T-8

Light Technical

Order Code	Full Product Name	Luminous Flux
927870986501	F48T8/TL865/ALTO 30W 25 PK	2,445 lm

Order Code	Full Product Name	Luminous Flux
927874786501	F96T8/TL865/ALTO 60W 25PK	5,365 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
927870986501	F48T8/TL865/ALTO 30W 25 PK	30 W

Order Code	Full Product Name	Power Consumption
927874786501	F96T8/TL865/ALTO 60W 25PK	60 W

Approval and Application

T8 Slimline

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
927870986501	F48T8/TL865/ALTO 30W 25 PK	3.5 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
927874786501	F96T8/TL865/ALTO 60W 25PK	4.4 mg

