

## Dipswitch LED bulb

9377853



## One choice, five colors

Not sure about the color that will best fit your application? No need to worry. Philips Dipswitch LED bulb offer 5 colors in one product and is easy-to-operate by switching the button to change the color.

### Benefits

- Enjoy 5 possible light colors in one product
- Change the color of your light easily with by switching the button on the product
- No guesswork

### Applications

- Home
- Offices
- Education

### Features

- 5 color temperatures
- Dimmable
- Change the color by switching the button
- Lifetime up to 15,000 hours
- Easy retrofit

**Versions**



LEDBulb 14W E27 DS FR DIM  
 1PF 6 AU RTP

**Dimensional drawing**



| Product                            | D     | C      |
|------------------------------------|-------|--------|
| LEDBulb 14W E27 DS FR DIM 1PF/6 AU | 60 mm | 119 mm |

**General Information**

|                  |                |
|------------------|----------------|
| Cap-Base         | E27            |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle  | 50,000         |

**Light Technical**

|                                       |                               |
|---------------------------------------|-------------------------------|
| Color Code                            | 2700K/3000K/4000K/5000K/6500K |
| Beam Angle (Nom)                      | 200 degree(s)                 |
| Luminous Flux                         | 1,400 lm                      |
| Color rendering index (CRI)           | 80                            |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %                          |

## Operating and Electrical

|                     |             |
|---------------------|-------------|
| Input Frequency     | 50 to 60 Hz |
| Power Consumption   | 14 W        |
| Wattage Equivalent  | 100 W       |
| Starting Time (Nom) | 0.5 s       |

## Temperature

|                      |       |
|----------------------|-------|
| T-Case Maximum (Nom) | 80 °C |
|----------------------|-------|

## Controls and Dimming

|          |                            |
|----------|----------------------------|
| Dimmable | Only with specific dimmers |
|----------|----------------------------|

## Mechanical and Housing

|             |         |
|-------------|---------|
| Bulb Finish | Frosted |
| Bulb Shape  | A60     |

## Approval and Application

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
|---------------------------|---------------|

## Light Technical

| Order Code   | Full Product Name                  | Correlated Color Temperature (Nom)             |
|--------------|------------------------------------|------------------------------------------------|
| 929003785419 | LEDBulb 14W E27 DS FR DIM 1PF/6 AU | 2700 K<br>3000 K<br>4000 K<br>5000 K<br>6500 K |