



GreenSpace G6: Low energy LED downlights with high visual comfort

GreenSpace G6

Philips GreenSpace G6 builds on the GreenSpace family's reputation for superb performance, extremely low energy use, and high visual comfort. This next generation of reliable LED downlights comes in a highly-compact design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. GreenSpace G6 is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 600 to 3,550 lumen, with the option to choose fixed, dimmable, or Interact Ready variants. This makes GreenSpace G6 the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Benefits

- Energy-efficient LED
- Compact design
- Visual comfort
- Option of glossy faceted (UGR19) or matte white reflector
- Durable LED quality and reliability

Features

- High system efficacy – average 120 lm/W
- Deep recessed architecture with increased reflector depth
- Spacious installation area with improved narrow rim width
- 50,000 hours lifetime @L80/B50 Ta 25°C
- DALI and wireless Interact compatible

Application

- Offices
- retail
- Hospitality
- other potential indoor open areas

Specifications







Mounting type	Recessed
Operating Temperature range	-20°C to +40°C
Light Source	LED module
Mains Voltage	220-240V / 50-60Hz
Mains connection	flying cable
Dimming	PSU: non-dimmablePSD: Dimmable via Dali protocolWIA: Wireless control
Control system input	DALI/1-10V/ WIA
Material	Housing: Die-cat Aluminium Reflector: Plastic
Main color of the luminaire	Black heat sink
Lumen maintenance at median useful life	L80 50.000h
Flicker / Pst / SVM	MD<3.2% PST<=0.5 SVM<=1
Luminous flux	4inch: 650lm-800lm, 1100lm-1150lm, 1270-1350lm 6inch: 1150-1200lm, 1700-1800lm, 1860-2000lm 8inch: 1650-1760lm, 2250-2400lm, 3450-3550lm
Power consumption	4inch: 5.8W - 12W 6inch: 9.8W - 16.6W 8inch: 14.2W - 29.3W
Luminaire efficacy	PSU: 105-124lm/W @840 PSD/WIA: 100-122lm/W @840
Correlated color temperature - CCT	3000K, 4000K, 6500

Color Rendering index - CRI	80, 90
Risk Group	RG1
Beam angle	4inch - WH reflector - 78degree 6inch - WH reflector - 82degree 8inch - WH reflector - 83degree 4/6/8inch - Aluminizing reflector - 60degree
Reflector material	WH: Plastic AL: Aluminum coated
Optic	White (WH) UGR 23-26 (NOC) based on lumen output. Aluminizing (AL) UGR<19 (OC)
Protection Class	Class II
IEC61140	
Mechanical impact protection	IK03
Ingress protection	IP20 / IP54 (light exit window)
Overall diameter	4inch: D100 6inch: D150 8inch: D200
Overall height	4inch: 69mm 6inch: 82mm 8inch: 105mm
UGR	AL coating reflector: UGR19 WH reflector: UGR 23-26
Installation	recessed Fixation by means of spring fasteners

Versions



Dimensional drawing



General Information	
Gear	-
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Optical cover type	Polycarbonate Diffuser
Mech. impact protection code	IK03
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 5 s

General Information

Order Code	Full Product Name	Driver included	Number of gear units	Service tag
911401540044	DN394X LED38/840 P29L1W D200 AL GMG2HE	No	-	-
911401540244	DN393X LED25/840 P20L1W D200 AL GMG2HE	No	-	-
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	Yes	-	Yes
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	Yes	-	Yes
911401533844	DN391B LED15/830 P11PSU D100 WH GMG2HE	Yes	-	Yes
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	Yes	-	Yes
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	Yes	-	Yes
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	Yes	-	Yes
34570799	DN390B LED7/865 P6PSU D100 WH GMG2HE	Yes	-	Yes
33626299	DN390B LED7/840 P6PSU D100 WH GMG2HE	Yes	-	Yes
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	Yes	-	Yes
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	Yes	-	Yes
911401538144	DN391X LED15/830 P12WIA D100 WH G2HE	Yes	-	Yes
911401538744	DN391X LED15/840 P12WIA D100WH G2HE	Yes	-	Yes
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	No	-	Yes
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	No	-	Yes
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	No	-	Yes
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	No	-	Yes
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	No	-	Yes
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	No	-	Yes
911401540644	DN391X LED14/840 P11L1W D100 AL GMG2HE	No	-	-
911401503645	DN392X LED16/9TNW P15PSD D150 AL WP G2	Yes	1 unit	-
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	Yes	-	Yes
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	Yes	-	Yes
911401522144	DN392B LED20/830 P16PSU D150 ALWP GMG2HE	Yes	-	Yes
33096399	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	Yes	-	Yes
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	Yes	-	Yes
911401523344	DN392B LED18/830 P14PSU D150 ALWP GMG2HE	Yes	-	Yes
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	Yes	-	Yes
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	Yes	-	Yes
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	Yes	-	Yes
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	Yes	-	Yes
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	Yes	-	Yes
911401528744	DN392B LED20/830 P16PSU D150 AL GMG2HE	Yes	-	Yes
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	Yes	-	Yes
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	Yes	-	Yes
911401531144	DN392B LED18/830 P14PSU D150 AL GMG2HE	Yes	-	Yes
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	Yes	-	Yes
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	Yes	-	Yes
911401532344	DN391B LED12/830 P10PSU D150 AL GMG2HE	Yes	-	Yes
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	Yes	-	Yes
911401537844	DN392X LED18/830 P15WIA D150 AL G2HE	Yes	-	Yes
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	Yes	-	Yes
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	No	-	Yes
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	No	-	Yes
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	No	-	Yes
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	No	-	Yes
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	No	-	Yes
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	No	-	Yes

Order Code	Full Product Name	Driver included	Number of gear units	Service tag
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	No	-	Yes
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	No	-	Yes
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	No	-	Yes
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	No	-	Yes
31731500	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	No	-	Yes
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	No	-	Yes
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	No	-	Yes
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	No	-	Yes
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	No	-	Yes
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	No	-	Yes
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	No	-	Yes
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	No	-	Yes
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	No	-	-
911401503745	DN391X LED7/9TNW P7PSD D100 AL WP G2	Yes	1 unit	-
911401524344	DN391B LED14/865 P11PSU D100 ALWP GMG2HE	Yes	-	Yes
911401524444	DN391B LED14/840 P11PSU D100 ALWP GMG2HE	Yes	-	Yes
911401524544	DN391B LED14/830 P11PSU D100 ALWP GMG2HE	Yes	-	Yes
911401524944	DN391B LED12/865 P10PSU D100 ALWP GMG2HE	Yes	-	Yes
911401525044	DN391B LED12/840 P10PSU D100 ALWP GMG2HE	Yes	-	Yes
911401525144	DN391B LED12/830 P10PSU D100 ALWP GMG2HE	Yes	-	Yes
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	Yes	-	Yes
911401525644	DN390B LED7/840 P6PSU D100 AL WP GMG2HE	Yes	-	Yes
911401525744	DN390B LED7/830 P6PSU D100 AL WP GMG2HE	Yes	-	Yes
911401533344	DN391B LED14/865 P11PSU D100 AL GMG2HE	Yes	-	Yes
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	Yes	-	Yes
911401533544	DN391B LED14/830 P11PSU D100 AL GMG2HE	Yes	-	Yes
911401534544	DN391B LED12/865 P10PSU D100 AL GMG2HE	Yes	-	Yes
911401534644	DN391B LED12/840 P10PSU D100 AL GMG2HE	Yes	-	Yes
911401534744	DN391B LED12/830 P10PSU D100 AL GMG2HE	Yes	-	Yes
911401535844	DN390B LED7/865 P6PSU D100 AL GMG2HE	Yes	-	Yes
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	Yes	-	Yes
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	Yes	-	Yes
911401537444	DN391X LED14/865 P12WIA D100 AL G2HE	Yes	-	Yes
911401538044	DN391X LED14/830 P12WIA D100 AL G2HE	Yes	-	Yes
911401538644	DN391X LED14/840 P12WIA D100 AL G2HE	Yes	-	Yes
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	No	-	Yes
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	No	-	Yes
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	No	-	Yes
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	No	-	Yes
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	No	-	Yes
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	No	-	Yes
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	No	-	Yes
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	No	-	Yes
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	No	-	Yes
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	No	-	Yes
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	No	-	Yes
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	No	-	Yes
911401503845	DN394X LED34/9TNW P27PSD D200 WH WP G2	Yes	1 unit	-
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	Yes	-	Yes
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	Yes	-	Yes
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	Yes	-	Yes

Order Code	Full Product Name	Driver included	Number of gear units	Service tag
34571499	DN393B LED26/865 P19PSU D200 WH GMG2HE	Yes	-	Yes
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	Yes	-	Yes
34330799	DN393B LED26/830 P19PSU D200 WH GMG2HE	Yes	-	Yes
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	Yes	-	Yes
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	Yes	-	Yes
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	Yes	-	Yes
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	Yes	-	Yes
911401537744	DN393X LED26/830 P20WIA D200 WH G2HE	Yes	-	Yes
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	Yes	-	Yes
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	No	-	Yes
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	No	-	Yes
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	No	-	Yes
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	No	-	Yes
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	No	-	Yes
911401573044	DN393B LED26/830 P20PSD D200 WH GMG2HE	No	-	Yes
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	No	-	Yes
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	No	-	Yes
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	No	-	Yes
911401540144	DN394X LED40/840 P29L1W D200 WH GMG2HE	No	-	-
911401540344	DN393X LED26/840 P20L1W D200 WH GMG2HE	No	-	-
911401503545	DN394X LED33/9TNW P27PSD D200 AL WP G2	Yes	1 unit	-
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	Yes	-	Yes
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	Yes	-	Yes
911401520944	DN394B LED38/830 P29PSU D200 ALWP GMG2HE	Yes	-	Yes
31158099	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	Yes	-	Yes
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	Yes	-	Yes
911401521544	DN393B LED25/830 P19PSU D200 ALWP GMG2HE	Yes	-	Yes
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	Yes	-	Yes
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	Yes	-	Yes
911401522744	DN392B LED18/830 P14PSU D200 ALWP GMG2HE	Yes	-	Yes
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	Yes	-	Yes
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	Yes	-	Yes
911401526344	DN394B LED38/830 P29PSU D200 AL GMG2HE	Yes	-	Yes
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	Yes	-	Yes
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	Yes	-	Yes
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	Yes	-	Yes
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	Yes	-	Yes
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	Yes	-	Yes
911401529944	DN392B LED18/830 P14PSU D200 AL GMG2HE	Yes	-	Yes
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	Yes	-	Yes
911401537644	DN393X LED25/830 P20WIA D200 AL G2HE	Yes	-	Yes
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	Yes	-	Yes
911401566844	DN394B LED38/865 P29PSD D200 ALWP GMG2HE	No	-	Yes

Order Code	Full Product Name	Driver included	Number of gear units	Service tag
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	No	-	Yes
911401567044	DN394B LED38/830 P29PSD D200 ALWP GMG2HE	No	-	Yes
911401567444	DN393B LED25/865 P20PSD D200 ALWP GMG2HE	No	-	Yes
31730800	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	No	-	Yes
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	No	-	Yes
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	No	-	Yes
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	No	-	Yes
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	No	-	Yes
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	No	-	Yes
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	No	-	Yes
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	No	-	Yes
911401572544	DN393B LED25/865 P20PSD D200 AL GMG2HE	No	-	Yes
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	No	-	Yes
911401572744	DN393B LED25/830 P20PSD D200 AL GMG2HE	No	-	Yes
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	No	-	Yes
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	No	-	Yes
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	No	-	Yes
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	No	-	-
911401540544	DN392X LED22/840 P17L1W D150 WH GMG2HE	No	-	-
911401503945	DN392X LED17/9TNW P15PSD D150 WH WP G2	Yes	1 unit	-
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	Yes	-	Yes
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	Yes	-	Yes
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	Yes	-	Yes
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	Yes	-	Yes
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	Yes	-	Yes
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	Yes	-	Yes
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	Yes	-	Yes
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	Yes	-	Yes
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	Yes	-	Yes
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	Yes	-	Yes
911401537944	DN392X LED20/830 P15WIA D150 WH G2HE	Yes	-	Yes
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	Yes	-	Yes
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	No	-	Yes
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	No	-	Yes
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	No	-	Yes
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	No	-	Yes
911401574144	DN392B LED23/840 P17PSD D150 WH GMG2HE	No	-	Yes
911401574244	DN392B LED23/830 P17PSD D150 WH GMG2HE	No	-	Yes
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	No	-	Yes
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	No	-	Yes
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	No	-	Yes
911401539844	DN392X LED18/840 P15L1W D150 AL GMG2HE	No	-	-
911401540444	DN392X LED20/840 P17L1W D150 AL GMG2HE	No	-	-

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401540044	DN394X LED38/840 P29LIW D200 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	125 lm/W
911401540244	DN393X LED25/840 P20LIW D200 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	125 lm/W
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	-	6500 K	>80	130 lm/W
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	-	4000 K	>80	130 lm/W
911401533844	DN391B LED15/830 P11PSU D100 WH GMG2HE	-	3000 K	>80	120 lm/W
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	-	6500 K	>80	130 lm/W
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	-	4000 K	>80	130 lm/W
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	-	3000 K	>80	120 lm/W
34570799	DN390B LED7/865 P6PSU D100 WH GMG2HE	-	6500 K	>80	130 lm/W
33626299	DN390B LED7/840 P6PSU D100 WH GMG2HE	-	4000 K	>80	130 lm/W
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	-	3000 K	>80	120 lm/W
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	-	6500 K	>80	125 lm/W
911401538144	DN391X LED15/830 P12WIA D100 WH G2HE	-	3000 K	>80	116 lm/W
911401538744	DN391X LED15/840 P12WIA D100WH G2HE	-	4000 K	>80	125 lm/W
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	125 lm/W
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	125 lm/W
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	10 or 40 degree(s)	3000 K	≥80	116 lm/W
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	125 lm/W
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	125 lm/W
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	10 or 40 degree(s)	3000 K	≥80	116 lm/W
911401540644	DN391X LED14/840 P11LIW D100 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	115 lm/W
911401503645	DN392X LED16/9TNW P15PSD D150 AL WP G2	- degree(s)	Tunable white 2700-6500 K	≥90	115 lm/W
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	-	6500 K	>80	132 lm/W
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	-	4000 K	>80	132 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401522144	DN392B LED20/830 P16PSU D150 ALWP GMG2HE	-	3000 K	>80	122 lm/W
33096399	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	-	6500 K	>80	132 lm/W
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	-	4000 K	>80	132 lm/W
911401523344	DN392B LED18/830 P14PSU D150 ALWP GMG2HE	-	3000 K	>80	122 lm/W
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	-	6500 K	>80	132 lm/W
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	-	4000 K	>80	132 lm/W
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	-	3000 K	>80	122 lm/W
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	-	6500 K	>80	132 lm/W
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	-	4000 K	>80	132 lm/W
911401528744	DN392B LED20/830 P16PSU D150 AL GMG2HE	-	3000 K	>80	122 lm/W
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	-	6500 K	>80	132 lm/W
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	-	4000 K	>80	132 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401531144	DN392B LED18/830 P14PSU D150 AL GMG2HE	-	3000 K	>80	122 lm/W
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	-	6500 K	>80	132 lm/W
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	-	4000 K	>80	132 lm/W
911401532344	DN391B LED12/830 P10PSU D150 AL GMG2HE	-	3000 K	>80	122 lm/W
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	-	6500 K	>80	130 lm/W
911401537844	DN392X LED18/830 P15WIA D150 AL G2HE	-	3000 K	>80	120 lm/W
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	-	4000 K	>80	130 lm/W
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	120 lm/W
31731500	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	111 lm/W
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	120 lm/W
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	111 lm/W
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	125 lm/W
911401503745	DN391X LED7/9TNW P7PSD D100 AL WP G2	- degree(s)	Tunable white 2700-6500 K	≥90	110 lm/W
911401524344	DN391B LED14/865 P11PSU D100 ALWP GMG2HE	-	6500 K	>80	125 lm/W
911401524444	DN391B LED14/840 P11PSU D100 ALWP GMG2HE	-	4000 K	>80	125 lm/W
911401524544	DN391B LED14/830 P11PSU D100 ALWP GMG2HE	-	3000 K	>80	118 lm/W
911401524944	DN391B LED12/865 P10PSU D100 ALWP GMG2HE	-	6500 K	>80	125 lm/W
911401525044	DN391B LED12/840 P10PSU D100 ALWP GMG2HE	-	4000 K	>80	125 lm/W
911401525144	DN391B LED12/830 P10PSU D100 ALWP GMG2HE	-	3000 K	>80	118 lm/W
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	-	6500 K	>80	125 lm/W
911401525644	DN390B LED7/840 P6PSU D100 AL WP GMG2HE	-	4000 K	>80	125 lm/W
911401525744	DN390B LED7/830 P6PSU D100 AL WP GMG2HE	-	3000 K	>80	118 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401533344	DN391B LED14/865 P11PSU D100 AL GMG2HE	-	6500 K	>80	125 lm/W
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	-	4000 K	>80	125 lm/W
911401533544	DN391B LED14/830 P11PSU D100 AL GMG2HE	-	3000 K	>80	118 lm/W
911401534544	DN391B LED12/865 P10PSU D100 AL GMG2HE	-	6500 K	>80	125 lm/W
911401534644	DN391B LED12/840 P10PSU D100 AL GMG2HE	-	4000 K	>80	125 lm/W
911401534744	DN391B LED12/830 P10PSU D100 AL GMG2HE	-	3000 K	>80	118 lm/W
911401535844	DN390B LED7/865 P6PSU D100 AL GMG2HE	-	6500 K	>80	125 lm/W
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	-	4000 K	>80	125 lm/W
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	-	3000 K	>80	118 lm/W
911401537444	DN391X LED14/865 P12WIA D100 AL G2HE	-	6500 K	>80	120 lm/W
911401538044	DN391X LED14/830 P12WIA D100 AL G2HE	-	3000 K	>80	111 lm/W
911401538644	DN391X LED14/840 P12WIA D100 AL G2HE	-	4000 K	>80	120 lm/W
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	120 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	111 lm/W
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	120 lm/W
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	111 lm/W
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	120 lm/W
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	111 lm/W
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	120 lm/W
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	111 lm/W
911401503845	DN394X LED34/9TNW P27PSD D200 WH WP G2	- degree(s)	Tunable white 2700-6500 K	≥90	125 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	-	6500 K	>80	140 lm/W
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	-	4000 K	>80	140 lm/W
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	-	3000 K	>80	130 lm/W
34571499	DN393B LED26/865 P19PSU D200 WH GMG2HE	-	6500 K	>80	140 lm/W
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	-	4000 K	>80	140 lm/W
34330799	DN393B LED26/830 P19PSU D200 WH GMG2HE	-	3000 K	>80	130 lm/W
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	-	6500 K	>80	140 lm/W
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	-	4000 K	>80	140 lm/W
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	-	3000 K	>80	130 lm/W
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	-	6500 K	>80	137 lm/W
911401537744	DN393X LED26/830 P20WIA D200 WH G2HE	-	3000 K	>80	127 lm/W
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	-	4000 K	>80	137 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	137 lm/W
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	137 lm/W
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	10 or 40 degree(s)	3000 K	≥80	127 lm/W
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	137 lm/W
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	137 lm/W
911401573044	DN393B LED26/830 P20PSD D200 WH GMG2HE	10 or 40 degree(s)	3000 K	≥80	127 lm/W
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	137 lm/W
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	137 lm/W
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	10 or 40 degree(s)	3000 K	≥80	127 lm/W
911401540144	DN394X LED40/840 P29L1W D200 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	137 lm/W
911401540344	DN393X LED26/840 P20L1W D200 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401503545	DN394X LED33/9TNW P27PSD D200 AL WP G2	- degree(s)	Tunable white 2700-6500 K	≥90	120 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	-	6500 K	>80	132 lm/W
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	-	4000 K	>80	132 lm/W
911401520944	DN394B LED38/830 P29PSU D200 ALWP GMG2HE	-	3000 K	>80	122 lm/W
31158099	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	-	6500 K	>80	132 lm/W
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	-	4000 K	>80	132 lm/W
911401521544	DN393B LED25/830 P19PSU D200 ALWP GMG2HE	-	3000 K	>80	122 lm/W
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	-	6500 K	>80	132 lm/W
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	-	4000 K	>80	132 lm/W
911401522744	DN392B LED18/830 P14PSU D200 ALWP GMG2HE	-	3000 K	>80	122 lm/W
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	-	6500 K	>80	132 lm/W
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	-	4000 K	>80	132 lm/W
911401526344	DN394B LED38/830 P29PSU D200 AL GMG2HE	-	3000 K	>80	122 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	-	6500 K	>80	132 lm/W
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	-	4000 K	>80	132 lm/W
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	-	3000 K	>80	122 lm/W
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	-	6500 K	>80	132 lm/W
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	-	4000 K	>80	132 lm/W
911401529944	DN392B LED18/830 P14PSU D200 AL GMG2HE	-	3000 K	>80	122 lm/W
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	-	6500 K	>80	130 lm/W
911401537644	DN393X LED25/830 P20WIA D200 AL G2HE	-	3000 K	>80	120 lm/W
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	-	4000 K	>80	130 lm/W
911401566844	DN394B LED38/865 P29PSD D200 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401567044	DN394B LED38/830 P29PSD D200 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401567444	DN393B LED25/865 P20PSD D200 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
31730800	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401572544	DN393B LED25/865 P20PSD D200 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401572744	DN393B LED25/830 P20PSD D200 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	10 or 40 degree(s)	6500 K	≥80	130 lm/W
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	10 or 40 degree(s)	3000 K	≥80	120 lm/W
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401540544	DN392X LED22/840 P17L1W D150 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	130 lm/W
911401503945	DN392X LED17/9TNW P15PSD D150 WH WP G2	- degree(s)	Tunable white 2700-6500 K	≥90	120 lm/W
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	-	6500 K	>80	138 lm/W
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	-	4000 K	>80	138 lm/W
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	-	3000 K	>80	130 lm/W
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	-	6500 K	>80	138 lm/W
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	-	4000 K	>80	138 lm/W
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	-	3000 K	>80	130 lm/W

		Beam	Correlated	Color	Luminous
	Full Product	angle of	Color	rendering	Efficacy
Order Code	Name	light	Temperature	index	(rated)
		source	(Nom)	(CRI)	(Nom)
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	-	6500 K	>80	138 lm/W
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	-	4000 K	>80	138 lm/W
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	-	3000 K	>80	130 lm/W
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	-	6500 K	>80	135 lm/W
911401537944	DN392X LED20/830 P15WIA D150 WH G2HE	-	3000 K	>80	125 lm/W
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	-	4000 K	>80	135 lm/W
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	135 lm/W
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	135 lm/W
911401566744	DN392B LED19/830	10 or 40 degree(s)	3000 K	≥80	125 lm/W

		Beam	Correlated	Color	Luminous
	Full Product	angle of	Color	rendering	Efficacy
Order Code	Name	light	Temperature	index	(rated)
		source	(Nom)	(CRI)	(Nom)
	P14PSD D150 WH GMG2HE				
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	135 lm/W
911401574144	DN392B LED23/840 P17PSD D150 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	135 lm/W
911401574244	DN392B LED23/830 P17PSD D150 WH GMG2HE	10 or 40 degree(s)	3000 K	≥80	125 lm/W
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	10 or 40 degree(s)	6500 K	≥80	125 lm/W
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	10 or 40 degree(s)	4000 K	≥80	125 lm/W
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	10 or 40 degree(s)	3000 K	≥80	116 lm/W
911401539844	DN392X LED18/840 P15L1W D150 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W
911401540444	DN392X LED20/840 P17L1W D150 AL GMG2HE	10 or 40 degree(s)	4000 K	≥80	120 lm/W

Light Technical (2/2)

		Luminous	Number	
	Full Product Name	Flux	of light	Optic type
Order Code			sources	
911401540044	DN394X LED38/840 P29L1W D200 AL GMG2HE	3,800 lm	78	White reflector and opal cover
911401540244	DN393X LED25/840 P20L1W D200 AL GMG2HE	2,500 lm	48	White reflector and opal cover
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	1,500 lm	1	White reflector and opal cover
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	1,500 lm	1	White reflector and opal cover

		Luminous	Number	
	Full Product Name	Flux	of light	Optic type
Order Code			sources	
911401533844	DN391B LED15/830 P11PSU D100 WH GMG2HE	1,350 lm	1	White reflector and opal cover
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	1,250 lm	1	White reflector and opal cover
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	1,250 lm	1	White reflector and opal cover
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	1,150 lm	1	White reflector and opal cover

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
34570799	DN390B LED7/865 P6PSU D100 WH GMG2HE	750 lm	1	White reflector and opal cover
33626299	DN390B LED7/840 P6PSU D100 WH GMG2HE	750 lm	1	White reflector and opal cover
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	700 lm	1	White reflector and opal cover
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	1,500 lm	1	White reflector and opal cover
911401538144	DN391X LED15/830 P12WIA D100 WH G2HE	1,500 lm	1	White reflector and opal cover
911401538744	DN391X LED15/840 P12WIA D100WH G2HE	1,500 lm	1	White reflector and opal cover
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	1,500 lm	28	White reflector and opal cover
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	1,500 lm	28	White reflector and opal cover
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	1,350 lm	28	White reflector and opal cover
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	1,200 lm	28	White reflector and opal cover
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	1,200 lm	28	White reflector and opal cover
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	1,100 lm	28	White reflector and opal cover
911401540644	DN391X LED14/840 P11L1W D100 AL GMG2HE	1,400 lm	28	White reflector and opal cover
911401503645	DN392X LED16/9TNW P15PSD D150 AL WP G2	1,650 lm	48	Facetted reflector
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	2,000 lm	1	Facetted reflector
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	2,000 lm	1	Facetted reflector
911401522144	DN392B LED20/830 P16PSU D150 ALWP GMG2HE	1,850 lm	1	Facetted reflector
33096399	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	1,850 lm	1	Facetted reflector
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	1,850 lm	1	Facetted reflector
911401523344	DN392B LED18/830 P14PSU D150 ALWP GMG2HE	1,700 lm	1	Facetted reflector
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	1,250 lm	1	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	1,250 lm	1	Facetted reflector
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	1,150 lm	1	Facetted reflector
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	2,000 lm	1	Facetted reflector
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	2,000 lm	1	Facetted reflector
911401528744	DN392B LED20/830 P16PSU D150 AL GMG2HE	1,850 lm	1	Facetted reflector
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	1,850 lm	1	Facetted reflector
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	1,850 lm	1	Facetted reflector
911401531144	DN392B LED18/830 P14PSU D150 AL GMG2HE	1,700 lm	1	Facetted reflector
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	1,250 lm	1	Facetted reflector
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	1,250 lm	1	Facetted reflector
911401532344	DN391B LED12/830 P10PSU D150 AL GMG2HE	1,150 lm	1	Facetted reflector
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	1,850 lm	1	Facetted reflector
911401537844	DN392X LED18/830 P15WIA D150 AL G2HE	1,700 lm	1	Facetted reflector
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	1,850 lm	1	Facetted reflector
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	1,800 lm	48	Facetted reflector
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	1,800 lm	48	Facetted reflector
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	1,650 lm	48	Facetted reflector
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	1,800 lm	48	Facetted reflector
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	1,800 lm	48	Facetted reflector
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	1,650 lm	48	Facetted reflector
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	2,200 lm	48	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	2,200 lm	48	Facetted reflector
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	2,000 lm	48	Facetted reflector
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	1,250 lm	24	Facetted reflector
31731500	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	1,250 lm	24	Facetted reflector
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	1,150 lm	24	Facetted reflector
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	2,200 lm	48	Facetted reflector
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	2,200 lm	48	Facetted reflector
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	2,000 lm	48	Facetted reflector
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	1,250 lm	24	Facetted reflector
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	1,250 lm	24	Facetted reflector
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	1,150 lm	24	Facetted reflector
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	1,500 lm	28	White reflector and opal cover
911401503745	DN391X LED7/9TNW P7PSD D100 AL WP G2	750 lm	20	Facetted reflector
911401524344	DN391B LED14/865 P11PSU D100 ALWP GMG2HE	1,400 lm	1	Facetted reflector
911401524444	DN391B LED14/840 P11PSU D100 ALWP GMG2HE	1,400 lm	1	Facetted reflector
911401524544	DN391B LED14/830 P11PSU D100 ALWP GMG2HE	1,300 lm	1	Facetted reflector
911401524944	DN391B LED12/865 P10PSU D100 ALWP GMG2HE	1,200 lm	1	Facetted reflector
911401525044	DN391B LED12/840 P10PSU D100 ALWP GMG2HE	1,200 lm	1	Facetted reflector
911401525144	DN391B LED12/830 P10PSU D100 ALWP GMG2HE	1,100 lm	1	Facetted reflector
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	700 lm	1	Facetted reflector
911401525644	DN390B LED7/840 P6PSU D100 AL WP GMG2HE	700 lm	1	Facetted reflector
911401525744	DN390B LED7/830 P6PSU D100 AL WP GMG2HE	650 lm	1	Facetted reflector
911401533344	DN391B LED14/865 P11PSU D100 AL GMG2HE	1,400 lm	1	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	1,400 lm	1	Facetted reflector
911401533544	DN391B LED14/830 P11PSU D100 AL GMG2HE	1,300 lm	1	Facetted reflector
911401534544	DN391B LED12/865 P10PSU D100 AL GMG2HE	1,200 lm	1	Facetted reflector
911401534644	DN391B LED12/840 P10PSU D100 AL GMG2HE	1,200 lm	1	Facetted reflector
911401534744	DN391B LED12/830 P10PSU D100 AL GMG2HE	1,100 lm	1	Facetted reflector
911401535844	DN390B LED7/865 P6PSU D100 AL GMG2HE	700 lm	1	Facetted reflector
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	700 lm	1	Facetted reflector
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	650 lm	1	Facetted reflector
911401537444	DN391X LED14/865 P12WIA D100 AL G2HE	1,400 lm	1	Facetted reflector
911401538044	DN391X LED14/830 P12WIA D100 AL G2HE	1,400 lm	1	Facetted reflector
911401538644	DN391X LED14/840 P12WIA D100 AL G2HE	1,400 lm	1	Facetted reflector
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	1,400 lm	28	Facetted reflector
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	1,400 lm	28	Facetted reflector
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	1,300 lm	28	Facetted reflector
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	1,200 lm	28	Facetted reflector
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	1,200 lm	28	Facetted reflector
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	1,100 lm	28	Facetted reflector
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	1,400 lm	28	Facetted reflector
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	1,400 lm	28	Facetted reflector
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	1,300 lm	28	Facetted reflector
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	1,200 lm	28	Facetted reflector
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	1,200 lm	28	Facetted reflector
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	1,100 lm	28	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401503845	DN394X LED34/9TNW P27PSD D200 WH WP G2	3,400 lm	96	White reflector and opal cover
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	4,000 lm	1	White reflector and opal cover
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	4,000 lm	1	White reflector and opal cover
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	3,700 lm	1	White reflector and opal cover
34571499	DN393B LED26/865 P19PSU D200 WH GMG2HE	2,600 lm	1	White reflector and opal cover
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	2,600 lm	1	White reflector and opal cover
34330799	DN393B LED26/830 P19PSU D200 WH GMG2HE	2,400 lm	1	White reflector and opal cover
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	2,000 lm	1	White reflector and opal cover
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	2,000 lm	1	White reflector and opal cover
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	1,850 lm	1	White reflector and opal cover
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	2,600 lm	1	White reflector and opal cover
911401537744	DN393X LED26/830 P20WIA D200 WH G2HE	2,400 lm	1	White reflector and opal cover
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	2,600 lm	1	White reflector and opal cover
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	4,000 lm	78	White reflector and opal cover
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	4,000 lm	78	White reflector and opal cover
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	3,700 lm	78	White reflector and opal cover
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	2,600 lm	48	White reflector and opal cover
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	2,600 lm	48	White reflector and opal cover
911401573044	DN393B LED26/830 P20PSD D200 WH GMG2HE	2,400 lm	48	White reflector and opal cover

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	1,850 lm	48	White reflector and opal cover
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	1,850 lm	48	White reflector and opal cover
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	1,700 lm	48	White reflector and opal cover
911401540144	DN394X LED40/840 P29L1W D200 WH GMG2HE	4,000 lm	78	White reflector and opal cover
911401540344	DN393X LED26/840 P20L1W D200 WH GMG2HE	2,600 lm	48	White reflector and opal cover
911401503545	DN394X LED33/9TNW P27PSD D200 AL WP G2	3,300 lm	96	Facetted reflector
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	3,800 lm	1	Facetted reflector
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	3,800 lm	1	Facetted reflector
911401520944	DN394B LED38/830 P29PSU D200 ALWP GMG2HE	3,500 lm	1	Facetted reflector
31158099	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	2,500 lm	1	Facetted reflector
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	2,500 lm	1	Facetted reflector
911401521544	DN393B LED25/830 P19PSU D200 ALWP GMG2HE	2,300 lm	1	Facetted reflector
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	1,850 lm	1	Facetted reflector
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	1,850 lm	1	Facetted reflector
911401522744	DN392B LED18/830 P14PSU D200 ALWP GMG2HE	1,700 lm	1	Facetted reflector
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	3,800 lm	1	Facetted reflector
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	3,800 lm	1	Facetted reflector
911401526344	DN394B LED38/830 P29PSU D200 AL GMG2HE	3,500 lm	1	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	2,500 lm	1	Facetted reflector
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	2,500 lm	1	Facetted reflector
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	2,300 lm	1	Facetted reflector
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	1,850 lm	1	Facetted reflector
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	1,850 lm	1	Facetted reflector
911401529944	DN392B LED18/830 P14PSU D200 AL GMG2HE	1,700 lm	1	Facetted reflector
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	2,500 lm	1	Facetted reflector
911401537644	DN393X LED25/830 P20WIA D200 AL G2HE	2,300 lm	1	Facetted reflector
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	2,500 lm	1	Facetted reflector
911401566844	DN394B LED38/865 P29PSD D200 ALWP GMG2HE	3,800 lm	78	Facetted reflector
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	3,800 lm	78	Facetted reflector
911401567044	DN394B LED38/830 P29PSD D200 ALWP GMG2HE	3,800 lm	78	Facetted reflector
911401567444	DN393B LED25/865 P20PSD D200 ALWP GMG2HE	2,500 lm	48	Facetted reflector
31730800	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	2,500 lm	48	Facetted reflector
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	2,300 lm	48	Facetted reflector
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	1,750 lm	48	Facetted reflector
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	1,750 lm	48	Facetted reflector
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	1,650 lm	48	Facetted reflector
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	3,800 lm	78	Facetted reflector
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	3,800 lm	78	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	3,500 lm	78	Facetted reflector
911401572544	DN393B LED25/865 P20PSD D200 AL GMG2HE	2,500 lm	48	Facetted reflector
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	2,500 lm	48	Facetted reflector
911401572744	DN393B LED25/830 P20PSD D200 AL GMG2HE	2,300 lm	48	Facetted reflector
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	1,850 lm	48	Facetted reflector
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	1,850 lm	48	Facetted reflector
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	1,700 lm	48	Facetted reflector
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	2,000 lm	40	White reflector and opal cover
911401540544	DN392X LED22/840 P17L1W D150 WH GMG2HE	2,200 lm	40	White reflector and opal cover
911401503945	DN392X LED17/9TNW P15PSD D150 WH WP G2	1,700 lm	48	White reflector and opal cover
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	2,200 lm	1	White reflector and opal cover
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	2,200 lm	1	White reflector and opal cover
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	2,000 lm	1	White reflector and opal cover
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	2,000 lm	1	White reflector and opal cover
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	2,000 lm	1	White reflector and opal cover
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	1,850 lm	1	White reflector and opal cover
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	1,300 lm	1	White reflector and opal cover
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	1,300 lm	1	White reflector and opal cover
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	1,200 lm	1	White reflector and opal cover
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	2,000 lm	1	White reflector and opal cover
911401537944	DN392X LED20/830 P15WIA D150 WH G2HE	1,850 lm	1	White reflector and opal cover
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	2,000 lm	1	White reflector and opal cover
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	1,900 lm	48	White reflector and opal cover
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	1,900 lm	48	White reflector and opal cover
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	1,750 lm	48	White reflector and opal cover

Order Code	Full Product Name	Luminous	Number of light sources	Optic type
		Flux		
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	2,300 lm	48	White reflector and opal cover
911401574144	DN392B LED23/840 P17PSD D150 WH GMG2HE	2,300 lm	48	White reflector and opal cover
911401574244	DN392B LED23/830 P17PSD D150 WH GMG2HE	2,100 lm	48	White reflector and opal cover
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	1,300 lm	24	White reflector and opal cover

Order Code	Full Product Name	Luminous	Number of light sources	Optic type
		Flux		
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	1,300 lm	24	White reflector and opal cover
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	1,200 lm	24	White reflector and opal cover
911401539844	DN392X LED18/840 P15L1W D150 AL GMG2HE	1,850 lm	40	White reflector and opal cover
911401540444	DN392X LED20/840 P17L1W D150 AL GMG2HE	2,000 lm	40	White reflector and opal cover

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401540044	DN394X LED38/840 P29L1W D200 AL GMG2HE	29.3 W	No
911401540244	DN393X LED25/840 P20L1W D200 AL GMG2HE	19.9 W	No
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	11.4 W	No
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	11.4 W	No
911401533844	DN391B LED15/830 P11PSU D100 WH GMG2HE	11.4 W	No
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	9.8 W	No
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	9.8 W	No
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	9.8 W	No
34570799	DN390B LED7/865 P6PSU D100 WH GMG2HE	5.8 W	No
33626299	DN390B LED7/840 P6PSU D100 WH GMG2HE	5.8 W	No
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	5.8 W	No
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	12 W	No
911401538144	DN391X LED15/830 P12WIA D100 WH G2HE	12 W	No
911401538744	DN391X LED15/840 P12WIA D100WH G2HE	12 W	No
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	12 W	No
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	12 W	No
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	12 W	No
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	10.2 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	10.2 W	No
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	10.2 W	No
911401540644	DN391X LED14/840 P11L1W D100 AL GMG2HE	12 W	No
911401503645	DN392X LED16/9TNW P15PSD D150 AL WP G2	15 W	Yes
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	16 W	No
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	16 W	No
911401522144	DN392B LED20/830 P16PSU D150 ALWP GMG2HE	16 W	No
33096399	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	14.4 W	No
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	14.4 W	No
911401523344	DN392B LED18/830 P14PSU D150 ALWP GMG2HE	14.4 W	No
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	9.8 W	No
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	9.8 W	No
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	9.8 W	No
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	16 W	No
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	16 W	No
911401528744	DN392B LED20/830 P16PSU D150 AL GMG2HE	16 W	No
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	14.4 W	No
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	14.4 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401531144	DN392B LED18/830 P14PSU D150 AL GMG2HE	14.4 W	No
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	9.8 W	No
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	9.8 W	No
911401532344	DN391B LED12/830 P10PSU D150 AL GMG2HE	9.8 W	No
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	15 W	No
911401537844	DN392X LED18/830 P15WIA D150 AL G2HE	15 W	No
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	15 W	No
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	13.4 W	No
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	13.4 W	No
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	13.4 W	No
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	13.4 W	No
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	13.4 W	No
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	13.4 W	No
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	17.3 W	No
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	17.3 W	No
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	17.3 W	No
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	10.6 W	No
31731500	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	10.6 W	No
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	10.6 W	No
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	17.3 W	No
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	17.3 W	No
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	17.3 W	No
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	10.6 W	No
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	10.6 W	No
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	10.6 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	12 W	No
911401503745	DN391X LED7/9TNW P7PSD D100 AL WP G2	7 W	Yes
911401524344	DN391B LED14/865 P11PSU D100 ALWP GMG2HE	11.4 W	No
911401524444	DN391B LED14/840 P11PSU D100 ALWP GMG2HE	11.4 W	No
911401524544	DN391B LED14/830 P11PSU D100 ALWP GMG2HE	11.4 W	No
911401524944	DN391B LED12/865 P10PSU D100 ALWP GMG2HE	9.8 W	No
911401525044	DN391B LED12/840 P10PSU D100 ALWP GMG2HE	9.8 W	No
911401525144	DN391B LED12/830 P10PSU D100 ALWP GMG2HE	9.8 W	No
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	5.8 W	No
911401525644	DN390B LED7/840 P6PSU D100 AL WP GMG2HE	5.8 W	No
911401525744	DN390B LED7/830 P6PSU D100 AL WP GMG2HE	5.8 W	No
911401533344	DN391B LED14/865 P11PSU D100 AL GMG2HE	11.4 W	No
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	11.4 W	No
911401533544	DN391B LED14/830 P11PSU D100 AL GMG2HE	11.4 W	No
911401534544	DN391B LED12/865 P10PSU D100 AL GMG2HE	9.8 W	No
911401534644	DN391B LED12/840 P10PSU D100 AL GMG2HE	9.8 W	No
911401534744	DN391B LED12/830 P10PSU D100 AL GMG2HE	9.8 W	No
911401535844	DN390B LED7/865 P6PSU D100 AL GMG2HE	5.8 W	No
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	5.8 W	No
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	5.8 W	No
911401537444	DN391X LED14/865 P12WIA D100 AL G2HE	12 W	No
911401538044	DN391X LED14/830 P12WIA D100 AL G2HE	12 W	No
911401538644	DN391X LED14/840 P12WIA D100 AL G2HE	12 W	No
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	12 W	No
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	12 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401570344	DN391B LED14/830 P10PSD D100 ALWP GMG2HE	12 W	No
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	10.2 W	No
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	10.2 W	No
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	10.2 W	No
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	12 W	No
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	12 W	No
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	12 W	No
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	10.2 W	No
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	10.2 W	No
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	10.2 W	No
911401503845	DN394X LED34/9TNW P27PSD D200 WH WP G2	27 W	Yes
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	29.3 W	No
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	29.3 W	No
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	29.3 W	No
34571499	DN393B LED26/865 P19PSU D200 WH GMG2HE	19.2 W	No
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	19.2 W	No
34330799	DN393B LED26/830 P19PSU D200 WH GMG2HE	19.2 W	No
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	14.4 W	No
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	14.4 W	No
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	14.4 W	No
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	19.9 W	No
911401537744	DN393X LED26/830 P20WIA D200 WH G2HE	19.9 W	No
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	19.9 W	No
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	29.3 W	No
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	29.3 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	29.3 W	No
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	19.9 W	No
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	19.9 W	No
911401573044	DN393B LED26/830 P20PSD D200 WH GMG2HE	19.9 W	No
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	14.2 W	No
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	14.2 W	No
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	14.2 W	No
911401540144	DN394X LED40/840 P29L1W D200 WH GMG2HE	29.3 W	No
911401540344	DN393X LED26/840 P20L1W D200 WH GMG2HE	19.9 W	No
911401503545	DN394X LED33/9TNW P27PSD D200 AL WP G2	27 W	Yes
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	29.3 W	No
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	29.3 W	No
911401520944	DN394B LED38/830 P29PSU D200 ALWP GMG2HE	29.3 W	No
31158099	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	19.2 W	No
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	19.2 W	No
911401521544	DN393B LED25/830 P19PSU D200 ALWP GMG2HE	19.2 W	No
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	14.4 W	No
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	14.4 W	No
911401522744	DN392B LED18/830 P14PSU D200 ALWP GMG2HE	14.4 W	No
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	29.3 W	No
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	29.3 W	No
911401526344	DN394B LED38/830 P29PSU D200 AL GMG2HE	29.3 W	No
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	19.2 W	No
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	19.2 W	No
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	19.2 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	14.4 W	No
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	14.4 W	No
911401529944	DN392B LED18/830 P14PSU D200 AL GMG2HE	14.4 W	No
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	19.9 W	No
911401537644	DN393X LED25/830 P20WIA D200 AL G2HE	19.9 W	No
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	19.9 W	No
911401566844	DN394B LED38/865 P29PSD D200 ALWP GMG2HE	29.3 W	No
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	29.3 W	No
911401567044	DN394B LED38/830 P29PSD D200 ALWP GMG2HE	29.3 W	No
911401567444	DN393B LED25/865 P20PSD D200 ALWP GMG2HE	19.9 W	No
31730800	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	19.9 W	No
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	19.9 W	No
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	14.2 W	No
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	14.2 W	No
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	14.2 W	No
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	29.3 W	No
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	29.3 W	No
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	29.3 W	No
911401572544	DN393B LED25/865 P20PSD D200 AL GMG2HE	19.9 W	No
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	19.9 W	No
911401572744	DN393B LED25/830 P20PSD D200 AL GMG2HE	19.9 W	No
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	14.2 W	No
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	14.2 W	No
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	14.2 W	No
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	15 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401540544	DN392X LED22/840 P17L1W D150 WH GMG2HE	16.6 W	No
911401503945	DN392X LED17/9TNW P15PSD D150 WH WP G2	15 W	Yes
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	16 W	No
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	16 W	No
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	16 W	No
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	14.4 W	No
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	14.4 W	No
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	14.4 W	No
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	9.8 W	No
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	9.8 W	No
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	9.8 W	No
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	15 W	No
911401537944	DN392X LED20/830 P15WIA D150 WH G2HE	15 W	No
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	15 W	No
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	13.4 W	No
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	13.4 W	No
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	13.4 W	No
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	17.3 W	No
911401574144	DN392B LED23/840 P17PSD D150 WH GMG2HE	17.3 W	No
911401574244	DN392B LED23/830 P17PSD D150 WH GMG2HE	17.3 W	No
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	10.6 W	No
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	10.6 W	No
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	10.6 W	No
911401539844	DN392X LED18/840 P15L1W D150 AL GMG2HE	15 W	No
911401540444	DN392X LED20/840 P17L1W D150 AL GMG2HE	16.6 W	No

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401540044	DN394X LED38/840 P29L1W D200 AL GMG2HE	DALI	1%
911401540244	DN393X LED25/840 P20L1W D200 AL GMG2HE	DALI	1%
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	No	Not applicable
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	No	Not applicable
911401533844	DN391B LED15/830 P11PSU D100 WH GMG2HE	No	Not applicable
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	No	Not applicable
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	No	Not applicable
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	No	Not applicable
34570799	DN390B LED7/865 P6PSU D100 WH GMG2HE	No	Not applicable
33626299	DN390B LED7/840 P6PSU D100 WH GMG2HE	No	Not applicable
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	No	Not applicable
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	DALI	1%
911401538144	DN391X LED15/830 P12WIA D100 WH G2HE	DALI	1%
911401538744	DN391X LED15/840 P12WIA D100WH G2HE	DALI	1%
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	DALI	1%
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	DALI	1%
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	DALI	1%
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	DALI	1%
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	DALI	1%
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	DALI	1%
911401540644	DN391X LED14/840 P11L1W D100 AL GMG2HE	DALI	1%
911401503645	DN392X LED16/9TNW P15PSD D150 AL WP G2	DALI	1%
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	No	Not applicable
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	No	Not applicable
911401522144	DN392B LED20/830 P16PSU D150 ALWP GMG2HE	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
33096399	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	No	Not applicable
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	No	Not applicable
911401523344	DN392B LED18/830 P14PSU D150 ALWP GMG2HE	No	Not applicable
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	No	Not applicable
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	No	Not applicable
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	No	Not applicable
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	No	Not applicable
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	No	Not applicable
911401528744	DN392B LED20/830 P16PSU D150 AL GMG2HE	No	Not applicable
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	No	Not applicable
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	No	Not applicable
911401531144	DN392B LED18/830 P14PSU D150 AL GMG2HE	No	Not applicable
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	No	Not applicable
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	No	Not applicable
911401532344	DN391B LED12/830 P10PSU D150 AL GMG2HE	No	Not applicable
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	DALI	1%
911401537844	DN392X LED18/830 P15WIA D150 AL G2HE	DALI	1%
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	DALI	1%
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	DALI	1%
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	DALI	1%
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	DALI	1%
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	DALI	1%
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	DALI	1%
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	DALI	1%
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	DALI	1%

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	DALI	1%
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	DALI	1%
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	DALI	1%
31731500	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	DALI	1%
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	DALI	1%
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	DALI	1%
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	DALI	1%
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	DALI	1%
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	DALI	1%
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	DALI	1%
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	DALI	1%
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	DALI	1%
911401503745	DN391X LED7/9TNW P7PSD D100 AL WP G2	DALI	1%
911401524344	DN391B LED14/865 P11PSU D100 ALWP GMG2HE	No	Not applicable
911401524444	DN391B LED14/840 P11PSU D100 ALWP GMG2HE	No	Not applicable
911401524544	DN391B LED14/830 P11PSU D100 ALWP GMG2HE	No	Not applicable
911401524944	DN391B LED12/865 P10PSU D100 ALWP GMG2HE	No	Not applicable
911401525044	DN391B LED12/840 P10PSU D100 ALWP GMG2HE	No	Not applicable
911401525144	DN391B LED12/830 P10PSU D100 ALWP GMG2HE	No	Not applicable
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	No	Not applicable
911401525644	DN390B LED7/840 P6PSU D100 AL WP GMG2HE	No	Not applicable
911401525744	DN390B LED7/830 P6PSU D100 AL WP GMG2HE	No	Not applicable
911401533344	DN391B LED14/865 P11PSU D100 AL GMG2HE	No	Not applicable
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	No	Not applicable
911401533544	DN391B LED14/830 P11PSU D100 AL GMG2HE	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401534544	DN391B LED12/865 P10PSU D100 AL GMG2HE	No	Not applicable
911401534644	DN391B LED12/840 P10PSU D100 AL GMG2HE	No	Not applicable
911401534744	DN391B LED12/830 P10PSU D100 AL GMG2HE	No	Not applicable
911401535844	DN390B LED7/865 P6PSU D100 AL GMG2HE	No	Not applicable
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	No	Not applicable
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	No	Not applicable
911401537444	DN391X LED14/865 P12WIA D100 AL G2HE	DALI	1%
911401538044	DN391X LED14/830 P12WIA D100 AL G2HE	DALI	1%
911401538644	DN391X LED14/840 P12WIA D100 AL G2HE	DALI	1%
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	DALI	1%
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	DALI	1%
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	DALI	1%
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	DALI	1%
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	DALI	1%
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	DALI	1%
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	DALI	1%
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	DALI	1%
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	DALI	1%
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	DALI	1%
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	DALI	1%
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	DALI	1%
911401503845	DN394X LED34/9TNW P27PSD D200 WH WP G2	DALI	1%
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	No	Not applicable
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	No	Not applicable
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
34571499	DN393B LED26/865 P19PSU D200 WH GMG2HE	No	Not applicable
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	No	Not applicable
34330799	DN393B LED26/830 P19PSU D200 WH GMG2HE	No	Not applicable
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	No	Not applicable
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	No	Not applicable
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	No	Not applicable
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	DALI	1%
911401537744	DN393X LED26/830 P20WIA D200 WH G2HE	DALI	1%
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	DALI	1%
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	DALI	1%
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	DALI	1%
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	DALI	1%
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	DALI	1%
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	DALI	1%
911401573044	DN393B LED26/830 P20PSD D200 WH GMG2HE	DALI	1%
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	DALI	1%
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	DALI	1%
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	DALI	1%
911401540144	DN394X LED40/840 P29L1W D200 WH GMG2HE	DALI	1%
911401540344	DN393X LED26/840 P20L1W D200 WH GMG2HE	DALI	1%
911401503545	DN394X LED33/9TNW P27PSD D200 AL WP G2	DALI	1%
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	No	Not applicable
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	No	Not applicable
911401520944	DN394B LED38/830 P29PSU D200 ALWP GMG2HE	No	Not applicable
31158099	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	No	Not applicable
911401521544	DN393B LED25/830 P19PSU D200 ALWP GMG2HE	No	Not applicable
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	No	Not applicable
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	No	Not applicable
911401522744	DN392B LED18/830 P14PSU D200 ALWP GMG2HE	No	Not applicable
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	No	Not applicable
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	No	Not applicable
911401526344	DN394B LED38/830 P29PSU D200 AL GMG2HE	No	Not applicable
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	No	Not applicable
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	No	Not applicable
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	No	Not applicable
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	No	Not applicable
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	No	Not applicable
911401529944	DN392B LED18/830 P14PSU D200 AL GMG2HE	No	Not applicable
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	DALI	1%
911401537644	DN393X LED25/830 P20WIA D200 AL G2HE	DALI	1%
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	DALI	1%
911401566844	DN394B LED38/865 P29PSD D200 ALWP GMG2HE	DALI	1%
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	DALI	1%
911401567044	DN394B LED38/830 P29PSD D200 ALWP GMG2HE	DALI	1%
911401567444	DN393B LED25/865 P20PSD D200 ALWP GMG2HE	DALI	1%
31730800	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	DALI	1%
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	DALI	1%
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	DALI	1%
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	DALI	1%

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	DALI	1%
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	DALI	1%
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	DALI	1%
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	DALI	1%
911401572544	DN393B LED25/865 P20PSD D200 AL GMG2HE	DALI	1%
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	DALI	1%
911401572744	DN393B LED25/830 P20PSD D200 AL GMG2HE	DALI	1%
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	DALI	1%
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	DALI	1%
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	DALI	1%
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	DALI	1%
911401540544	DN392X LED22/840 P17L1W D150 WH GMG2HE	DALI	1%
911401503945	DN392X LED17/9TNW P15PSD D150 WH WP G2	DALI	1%
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	No	Not applicable
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	No	Not applicable
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	No	Not applicable
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	No	Not applicable
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	No	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	No	Not applicable
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	No	Not applicable
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	No	Not applicable
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	No	Not applicable
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	DALI	1%
911401537944	DN392X LED20/830 P15WIA D150 WH G2HE	DALI	1%
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	DALI	1%
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	DALI	1%
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	DALI	1%
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	DALI	1%
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	DALI	1%
911401574144	DN392B LED23/840 P17PSD D150 WH GMG2HE	DALI	1%
911401574244	DN392B LED23/830 P17PSD D150 WH GMG2HE	DALI	1%
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	DALI	1%
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	DALI	1%
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	DALI	1%
911401539844	DN392X LED18/840 P15L1W D150 AL GMG2HE	DALI	1%
911401540444	DN392X LED20/840 P17L1W D150 AL GMG2HE	DALI	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Ingress protection
			code
911401540044	DN394X LED38/840 P29L1W D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401540244	DN393X LED25/840 P20L1W D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	Aluminum	IP20
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	Aluminum	IP20

Order Code	Full Product Name	Housing Color	Ingress protection
			code
911401533844	DN391B LED15/830 P11PSU D100 WH GMG2HE	Aluminum	IP20
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	Aluminum	IP20
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	Aluminum	IP20
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	Aluminum	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
34570799	DN390B LED7/865 P6PSU D100 WH GMG2HE	Aluminum	IP20
33626299	DN390B LED7/840 P6PSU D100 WH GMG2HE	Aluminum	IP20
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	Aluminum	IP20
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	Aluminum	IP20
911401538144	DN391X LED15/830 P12WIA D100 WH G2HE	Aluminum	IP20
911401538744	DN391X LED15/840 P12WIA D100WH G2HE	Aluminum	IP20
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401540644	DN391X LED14/840 P11L1W D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401503645	DN392X LED16/9TNPW P15PSD D150 AL WP G2	Black	IP54
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401522144	DN392B LED20/830 P16PSU D150 ALWP GMG2HE	Aluminum	IP20/54
33096399	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523344	DN392B LED18/830 P14PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	Aluminum	IP20
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	Aluminum	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401528744	DN392B LED20/830 P16PSU D150 AL GMG2HE	Aluminum	IP20
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	Aluminum	IP20
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	Aluminum	IP20
911401531144	DN392B LED18/830 P14PSU D150 AL GMG2HE	Aluminum	IP20
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	Aluminum	IP20
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	Aluminum	IP20
911401532344	DN391B LED12/830 P10PSU D150 AL GMG2HE	Aluminum	IP20
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	Aluminum	IP20
911401537844	DN392X LED18/830 P15WIA D150 AL G2HE	Aluminum	IP20
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	Aluminum	IP20
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
31731500	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401503745	DN391X LED7/9TNW P7PSD D100 AL WP G2	Black	IP54
911401524344	DN391B LED14/865 P11PSU D100 ALWP GMG2HE	Aluminum	IP20/54
911401524444	DN391B LED14/840 P11PSU D100 ALWP GMG2HE	Aluminum	IP20/54
911401524544	DN391B LED14/830 P11PSU D100 ALWP GMG2HE	Aluminum	IP20/54
911401524944	DN391B LED12/865 P10PSU D100 ALWP GMG2HE	Aluminum	IP20/54
911401525044	DN391B LED12/840 P10PSU D100 ALWP GMG2HE	Aluminum	IP20/54
911401525144	DN391B LED12/830 P10PSU D100 ALWP GMG2HE	Aluminum	IP20/54
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	Aluminum	IP20/54
911401525644	DN390B LED7/840 P6PSU D100 AL WP GMG2HE	Aluminum	IP20/54
911401525744	DN390B LED7/830 P6PSU D100 AL WP GMG2HE	Aluminum	IP20/54
911401533344	DN391B LED14/865 P11PSU D100 AL GMG2HE	Aluminum	IP20
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	Aluminum	IP20
911401533544	DN391B LED14/830 P11PSU D100 AL GMG2HE	Aluminum	IP20
911401534544	DN391B LED12/865 P10PSU D100 AL GMG2HE	Aluminum	IP20
911401534644	DN391B LED12/840 P10PSU D100 AL GMG2HE	Aluminum	IP20
911401534744	DN391B LED12/830 P10PSU D100 AL GMG2HE	Aluminum	IP20
911401535844	DN390B LED7/865 P6PSU D100 AL GMG2HE	Aluminum	IP20
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	Aluminum	IP20
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	Aluminum	IP20
911401537444	DN391X LED14/865 P12WIA D100 AL G2HE	Aluminum	IP20
911401538044	DN391X LED14/830 P12WIA D100 AL G2HE	Aluminum	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401538644	DN391X LED14/840 P12WIA D100 AL G2HE	Aluminum	IP20
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401503845	DN394X LED34/9TNW P27PSD D200 WH WP G2	Black	IP54
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	Aluminum	IP20
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	Aluminum	IP20
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	Aluminum	IP20
34571499	DN393B LED26/865 P19PSU D200 WH GMG2HE	Aluminum	IP20
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	Aluminum	IP20
34330799	DN393B LED26/830 P19PSU D200 WH GMG2HE	Aluminum	IP20
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	Aluminum	IP20
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	Aluminum	IP20
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	Aluminum	IP20
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	Aluminum	IP20
911401537744	DN393X LED26/830 P20WIA D200 WH G2HE	Aluminum	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	Aluminum	IP20
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401573044	DN393B LED26/830 P20PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401540144	DN394X LED40/840 P29L1W D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401540344	DN393X LED26/840 P20L1W D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401503545	DN394X LED33/9TNW P27PSD D200 AL WP G2	Black	IP54
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401520944	DN394B LED38/830 P29PSU D200 ALWP GMG2HE	Aluminum	IP20/54
31158099	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401521544	DN393B LED25/830 P19PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401522744	DN392B LED18/830 P14PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	Aluminum	IP20
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	Aluminum	IP20
911401526344	DN394B LED38/830 P29PSU D200 AL GMG2HE	Aluminum	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	Aluminum	IP20
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	Aluminum	IP20
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	Aluminum	IP20
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	Aluminum	IP20
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	Aluminum	IP20
911401529944	DN392B LED18/830 P14PSU D200 AL GMG2HE	Aluminum	IP20
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	Aluminum	IP20
911401537644	DN393X LED25/830 P20WIA D200 AL G2HE	Aluminum	IP20
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	Aluminum	IP20
911401566844	DN394B LED38/865 P29PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401567044	DN394B LED38/830 P29PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401567444	DN393B LED25/865 P20PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
31730800	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572544	DN393B LED25/865 P20PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572744	DN393B LED25/830 P20PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401540544	DN392X LED22/840 P17L1W D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401503945	DN392X LED17/9TNW P15PSD D150 WH WP G2	Black	IP54
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	Aluminum	IP20
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	Aluminum	IP20
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	Aluminum	IP20
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	Aluminum	IP20
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	Aluminum	IP20
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	Aluminum	IP20
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	Aluminum	IP20
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	Aluminum	IP20
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	Aluminum	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401540044	DN394X LED38/840 P29L1W D200 AL GMG2HE	-	-10% / +10%
911401540244	DN393X LED25/840 P20L1W D200 AL GMG2HE	-	-10% / +10%
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	5	+/-10%
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	5	+/-10%
911401533844	DN391B LED15/830 P11PSU D100 WH GMG2HE	5	+/-10%
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	5	+/-10%
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	5	+/-10%
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	5	+/-10%

Order Code	Full Product Name	Housing Color	Ingress protection code
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	Aluminum	IP20
911401537944	DN392X LED20/830 P15WIA D150 WH G2HE	Aluminum	IP20
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	Aluminum	IP20
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401574144	DN392B LED23/840 P17PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401574244	DN392B LED23/830 P17PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401539844	DN392X LED18/840 P15L1W D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401540444	DN392X LED20/840 P17L1W D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
34570799	DN390B LED7/865 P6PSU D100 WH GMG2HE	5	+/-10%
33626299	DN390B LED7/840 P6PSU D100 WH GMG2HE	5	+/-10%
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	5	+/-10%
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	5	+/-10%
911401538144	DN391X LED15/830 P12WIA D100 WH G2HE	5	+/-10%
911401538744	DN391X LED15/840 P12WIA D100WH G2HE	5	+/-10%
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	5	-10% / +10%
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	5	-10% / +10%
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	5	-10% / +10%
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	5	-10% / +10%
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	5	-10% / +10%
911401540644	DN391X LED14/840 P11L1W D100 AL GMG2HE	-	-10% / +10%
911401503645	DN392X LED16/9TNW P15PSD D150 AL WP G2	SDCM5	+/-10%
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	5	+/-10%
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	5	+/-10%
911401522144	DN392B LED20/830 P16PSU D150 ALWP GMG2HE	5	+/-10%
33096399	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	5	+/-10%
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	5	+/-10%
911401523344	DN392B LED18/830 P14PSU D150 ALWP GMG2HE	5	+/-10%
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	5	+/-10%
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	5	+/-10%
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	5	+/-10%
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	5	+/-10%
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	5	+/-10%
911401528744	DN392B LED20/830 P16PSU D150 AL GMG2HE	5	+/-10%
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	5	+/-10%
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	5	+/-10%
911401531144	DN392B LED18/830 P14PSU D150 AL GMG2HE	5	+/-10%
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	5	+/-10%
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	5	+/-10%
911401532344	DN391B LED12/830 P10PSU D150 AL GMG2HE	5	+/-10%
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401537844	DN392X LED18/830 P15WIA D150 AL G2HE	5	+/-10%
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	5	+/-10%
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	5	-10% / +10%
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	5	-10% / +10%
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	5	-10% / +10%
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	5	-10% / +10%
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	5	-10% / +10%
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	5	-10% / +10%
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	5	-10% / +10%
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	5	-10% / +10%
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	5	-10% / +10%
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	5	-10% / +10%
31731500	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	5	-10% / +10%
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	5	-10% / +10%
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	5	-10% / +10%
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	5	-10% / +10%
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	5	-10% / +10%
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	5	-10% / +10%
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	5	-10% / +10%
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	5	-10% / +10%
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	-	-10% / +10%
911401503745	DN391X LED7/9TNW P7PSD D100 AL WP G2	SDCM5	+/-10%
911401524344	DN391B LED14/865 P11PSU D100 ALWP GMG2HE	5	+/-10%
911401524444	DN391B LED14/840 P11PSU D100 ALWP GMG2HE	5	+/-10%
911401524544	DN391B LED14/830 P11PSU D100 ALWP GMG2HE	5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401524944	DN391B LED12/865 P10PSU D100 ALWP GMG2HE	5	+/-10%
911401525044	DN391B LED12/840 P10PSU D100 ALWP GMG2HE	5	+/-10%
911401525144	DN391B LED12/830 P10PSU D100 ALWP GMG2HE	5	+/-10%
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	5	+/-10%
911401525644	DN390B LED7/840 P6PSU D100 AL WP GMG2HE	5	+/-10%
911401525744	DN390B LED7/830 P6PSU D100 AL WP GMG2HE	5	+/-10%
911401533344	DN391B LED14/865 P11PSU D100 AL GMG2HE	5	+/-10%
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	5	+/-10%
911401533544	DN391B LED14/830 P11PSU D100 AL GMG2HE	5	+/-10%
911401534544	DN391B LED12/865 P10PSU D100 AL GMG2HE	5	+/-10%
911401534644	DN391B LED12/840 P10PSU D100 AL GMG2HE	5	+/-10%
911401534744	DN391B LED12/830 P10PSU D100 AL GMG2HE	5	+/-10%
911401535844	DN390B LED7/865 P6PSU D100 AL GMG2HE	5	+/-10%
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	5	+/-10%
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	5	+/-10%
911401537444	DN391X LED14/865 P12WIA D100 AL G2HE	5	+/-10%
911401538044	DN391X LED14/830 P12WIA D100 AL G2HE	5	+/-10%
911401538644	DN391X LED14/840 P12WIA D100 AL G2HE	5	+/-10%
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	5	-10% / +10%
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	5	-10% / +10%
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	5	-10% / +10%
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	5	-10% / +10%
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	5	-10% / +10%
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	5	-10% / +10%
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	5	-10% / +10%
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	5	-10% / +10%
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	5	-10% / +10%
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	5	-10% / +10%
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	5	-10% / +10%
911401503845	DN394X LED34/9TNW P27PSD D200 WH WP G2 SDCM5		+/-10%
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	5	+/-10%
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	5	+/-10%
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	5	+/-10%
34571499	DN393B LED26/865 P19PSU D200 WH GMG2HE	5	+/-10%
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	5	+/-10%
34330799	DN393B LED26/830 P19PSU D200 WH GMG2HE	5	+/-10%
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	5	+/-10%
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	5	+/-10%
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	5	+/-10%
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	5	+/-10%
911401537744	DN393X LED26/830 P20WIA D200 WH G2HE	5	+/-10%
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	5	+/-10%
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	5	-10% / +10%
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	5	-10% / +10%
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	5	-10% / +10%
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	5	-10% / +10%
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	5	-10% / +10%
911401573044	DN393B LED26/830 P20PSD D200 WH GMG2HE	5	-10% / +10%
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	5	-10% / +10%
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	5	-10% / +10%
911401540144	DN394X LED40/840 P29L1W D200 WH GMG2HE	-	-10% / +10%
911401540344	DN393X LED26/840 P20L1W D200 WH GMG2HE	-	-10% / +10%
911401503545	DN394X LED33/9TNW P27PSD D200 AL WP G2	SDCM5	+/-10%
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	5	+/-10%
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	5	+/-10%
911401520944	DN394B LED38/830 P29PSU D200 ALWP GMG2HE	5	+/-10%
31158099	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	5	+/-10%
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	5	+/-10%
911401521544	DN393B LED25/830 P19PSU D200 ALWP GMG2HE	5	+/-10%
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	5	+/-10%
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	5	+/-10%
911401522744	DN392B LED18/830 P14PSU D200 ALWP GMG2HE	5	+/-10%
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	5	+/-10%
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	5	+/-10%
911401526344	DN394B LED38/830 P29PSU D200 AL GMG2HE	5	+/-10%
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	5	+/-10%
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	5	+/-10%
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	5	+/-10%
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	5	+/-10%
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	5	+/-10%
911401529944	DN392B LED18/830 P14PSU D200 AL GMG2HE	5	+/-10%
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	5	+/-10%
911401537644	DN393X LED25/830 P20WIA D200 AL G2HE	5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	5	+/-10%
911401566844	DN394B LED38/865 P29PSD D200 ALWP GMG2HE	5	-10% / +10%
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	5	-10% / +10%
911401567044	DN394B LED38/830 P29PSD D200 ALWP GMG2HE	5	-10% / +10%
911401567444	DN393B LED25/865 P20PSD D200 ALWP GMG2HE	5	-10% / +10%
31730800	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	5	-10% / +10%
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	5	-10% / +10%
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	5	-10% / +10%
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	5	-10% / +10%
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	5	-10% / +10%
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	5	-10% / +10%
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	5	-10% / +10%
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	5	-10% / +10%
911401572544	DN393B LED25/865 P20PSD D200 AL GMG2HE	5	-10% / +10%
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	5	-10% / +10%
911401572744	DN393B LED25/830 P20PSD D200 AL GMG2HE	5	-10% / +10%
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	5	-10% / +10%
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	5	-10% / +10%
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	5	-10% / +10%
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	-	-10% / +10%
911401540544	DN392X LED22/840 P17L1W D150 WH GMG2HE	-	-10% / +10%
911401503945	DN392X LED17/9TNW P15PSD D150 WH WP G2	SDCM5	+/-10%
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	5	+/-10%
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	5	+/-10%
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	5	+/-10%
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	5	+/-10%
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	5	+/-10%
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	5	+/-10%
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	5	+/-10%
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	5	+/-10%
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	5	+/-10%
911401537944	DN392X LED20/830 P15WIA D150 WH G2HE	5	+/-10%
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	5	+/-10%
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	5	-10% / +10%
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	5	-10% / +10%
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	5	-10% / +10%
911401574144	DN392B LED23/840 P17PSD D150 WH GMG2HE	5	-10% / +10%
911401574244	DN392B LED23/830 P17PSD D150 WH GMG2HE	5	-10% / +10%
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	5	-10% / +10%
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	5	-10% / +10%
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	5	-10% / +10%
911401539844	DN392X LED18/840 P15L1W D150 AL GMG2HE	-	-10% / +10%
911401540444	DN392X LED20/840 P17L1W D150 AL GMG2HE	-	-10% / +10%

