



GreenSpace G6: Low energy LED downlights with high visual comfort

Philips GreenSpace G6 builds on the GreenSpace family's reputation for superb performance, extremely low energy use, and high visual comfort. This next generation of reliable LED downlights comes in a highly-compact design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. GreenSpace G6 is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 600 to 3,550 lumen, with the option to choose fixed, dimmable, or Interact Ready variants. This makes GreenSpace G6 the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Benefits

- Energy-efficient LED
- Compact design
- Visual comfort
- Option of glossy faceted (UGR19) or matte white reflector
- Durable LED quality and reliability

Applications

- Offices
- retail

- Hospitality
- other potential indoor open areas

Features

- High system efficacy - average 120 lm/W
- Deep recessed architecture with increased reflector depth
- Spacious installation area with improved narrow rim width
- 50,000 hours lifetime @L80/B50 Ta 25°C
- DALI and wireless Interact compatible

Versions



GreenSpace G6



GreenSpace G6



GreenSpace G6



GreenSpace G6



GreenSpace G6



GreenSpace G6




GreenSpace G6



GreenSpace G6


Dimensional drawing

DN391B LED12/840 PSD D150 AL GCG2HE



DN392X LED20/840 P15L1W D150 WH GMG2HE

DN391B LED15/865 P11PSU D100 WH GMG2HE



DN391X LED15/840 P11L1W D100 WH GMG2HE

DN393X LED26/865 P20WIA D200 WH G2HE

General Information

Number of gear units	-
Gear	-
Service tag	Yes

Light Technical

Beam angle of light source	10 or 40 degree(s)
----------------------------	--------------------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Protection class IEC	Safety class II

Mechanical and Housing

Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Polycarbonate Diffuser

Approval and Application

Glow-wire test	Temperature 650 °C, duration 5 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Initial chromaticity	5
----------------------	---

General Information

Order Code	Full Product Name	Driver included
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	Yes
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	Yes
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	Yes
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	Yes
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	Yes
911401536144	DN390B LED7/865 P6PSU D100 WH GMG2HE	Yes
911401536244	DN390B LED7/840 P6PSU D100 WH GMG2HE	Yes
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	Yes
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	Yes
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	No
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	No
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	No
911401578844	DN391B LED15/865 PSD D100 WH GCG2HE	No
911401578944	DN391B LED15/840 PSD D100 WH GCG2HE	No
911401579044	DN391B LED15/830 PSD D100 WH GCG2HE	No
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	No
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	No
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	No
911401580044	DN391B LED12/865 PSD D100 WH GCG2HE	No
911401580144	DN391B LED12/840 PSD D100 WH GCG2HE	No
911401580244	DN391B LED12/830 PSD D100 WH GCG2HE	No
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	Yes
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	Yes
911401523144	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	Yes
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	Yes
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	Yes
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	Yes

Order Code	Full Product Name	Driver included
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	Yes
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	Yes
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	Yes
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	Yes
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	Yes
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	Yes
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	Yes
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	Yes
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	Yes
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	No
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	No
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	No
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	No
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	No
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	No
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	No
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	No
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	No
911401568344	DN392B LED22/865 PSD D150 AL WP GCG2HE	No
911401568444	DN392B LED22/840 PSD D150 AL WP GCG2HE	No
911401568544	DN392B LED22/830 PSD D150 AL WP GCG2HE	No
911401569244	DN392B LED18/865 PSD D150 AL WP GCG2HE	No
911401569344	DN392B LED18/840 PSD D150 AL WP GCG2HE	No
911401569444	DN392B LED18/830 PSD D150 AL WP GCG2HE	No
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	No
911401569644	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	No
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	No
911401569844	DN391B LED12/865 PSD D150 AL WP GCG2HE	No
911401569944	DN391B LED12/840 PSD D150 AL WP GCG2HE	No
911401570044	DN391B LED12/830 PSD D150 AL WP GCG2HE	No
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	No
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	No
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	No
911401574344	DN392B LED22/865 PSD D150 AL GCG2HE	No
911401574444	DN392B LED22/840 PSD D150 AL GCG2HE	No
911401574544	DN392B LED22/830 PSD D150 AL GCG2HE	No
911401576144	DN392B LED18/865 PSD D150 AL GCG2HE	No
911401576244	DN392B LED18/840 PSD D150 AL GCG2HE	No
911401576344	DN392B LED18/830 PSD D150 AL GCG2HE	No
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	No
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	No
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	No

Order Code	Full Product Name	Driver included
911401577344	DN391B LED12/865 PSD D150 AL GCG2HE	No
911401577444	DN391B LED12/840 PSD D150 AL GCG2HE	No
911401577544	DN391B LED12/830 PSD D150 AL GCG2HE	No
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	No
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	Yes
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	Yes
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	Yes
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	Yes
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	No
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	No
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	No
911401570444	DN391B LED14/865 PSD D100 AL WP GCG2HE	No
911401570544	DN391B LED14/840 PSD D100 AL WP GCG2HE	No
911401570644	DN391B LED14/830 PSD D100 AL WP GCG2HE	No
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	No
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	No
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	No
911401571044	DN391B LED12/865 PSD D100 AL WP GCG2HE	No
911401571144	DN391B LED12/840 PSD D100 AL WP GCG2HE	No
911401571244	DN391B LED12/830 PSD D100 AL WP GCG2HE	No
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	No
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	No
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	No
911401578544	DN391B LED14/865 PSD D100 AL GCG2HE	No
911401578644	DN391B LED14/840 PSD D100 AL GCG2HE	No
911401578744	DN391B LED14/830 PSD D100 AL GCG2HE	No
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	No
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	No
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	No
911401579744	DN391B LED12/865 PSD D100 AL GCG2HE	No
911401579944	DN391B LED12/830 PSD D100 AL GCG2HE	No
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	Yes
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	Yes
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	Yes
911401527644	DN393B LED26/865 P19PSU D200 WH GMG2HE	Yes
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	Yes
911401527844	DN393B LED26/830 P19PSU D200 WH GMG2HE	Yes
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	Yes
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	Yes
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	Yes
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	Yes
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	Yes

Order Code	Full Product Name	Driver included
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	No
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	No
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	No
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	No
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	No
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	No
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	No
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	No
911401575844	DN392B LED18/865 PSD D200 WH GCG2HE	No
911401575944	DN392B LED18/840 PSD D200 WH GCG2HE	No
911401576044	DN392B LED18/830 PSD D200 WH GCG2HE	No
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	Yes
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	Yes
911401521344	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	Yes
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	Yes
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	Yes
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	Yes
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	Yes
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	Yes
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	Yes
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	Yes
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	Yes
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	Yes
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	Yes
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	Yes
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	Yes
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	No
911401567544	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	No
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	No
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	No
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	No
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	No
911401568944	DN392B LED18/865 PSD D200 AL WP GCG2HE	No
911401569044	DN392B LED18/840 PSD D200 AL WP GCG2HE	No
911401569144	DN392B LED18/830 PSD D200 AL WP GCG2HE	No
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	No
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	No
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	No
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	No
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	No
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	No
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	No

Order Code	Full Product Name	Driver included
911401575544	DN392B LED18/865 PSD D200 AL GCG2HE	No
911401575644	DN392B LED18/840 PSD D200 AL GCG2HE	No
911401575744	DN392B LED18/830 PSD D200 AL GCG2HE	No
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	No
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	Yes
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	Yes
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	Yes
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	Yes
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	Yes
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	Yes
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	Yes
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	Yes
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	Yes
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	Yes
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	Yes
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	No
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	No
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	No
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	No
911401576444	DN392B LED19/865 PSD D150 WH GCG2HE	No
911401576544	DN392B LED19/840 PSD D150 WH GCG2HE	No
911401576644	DN392B LED19/830 PSD D150 WH GCG2HE	No
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	No
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	No
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	No
911401577644	DN391B LED13/865 PSD D150 WH GCG2HE	No
911401577744	DN391B LED13/840 PSD D150 WH GCG2HE	No
911401577844	DN391B LED13/830 PSD D150 WH GCG2HE	No

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	1,500 lm	6500 K	130 lm/W	>80	1	White reflector and opal cover
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	1,500 lm	4000 K	130 lm/W	>80	1	White reflector and opal cover
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	1,250 lm	6500 K	130 lm/W	>80	1	White reflector and opal cover
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	1,250 lm	4000 K	130 lm/W	>80	1	White reflector and opal cover
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	1,150 lm	3000 K	120 lm/W	>80	1	White reflector and opal cover

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401536144	DN390B LED7/865 P6PSU D100 WH GMG2HE	750 lm	6500 K	130 lm/W	>80	1	White reflector and opal cover
911401536244	DN390B LED7/840 P6PSU D100 WH GMG2HE	750 lm	4000 K	130 lm/W	>80	1	White reflector and opal cover
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	700 lm	3000 K	120 lm/W	>80	1	White reflector and opal cover
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	1,500 lm	6500 K	125 lm/W	>80	1	White reflector and opal cover
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	1,500 lm	6500 K	125 lm/W	≥80	28	White reflector and opal cover
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	1,500 lm	4000 K	125 lm/W	≥80	28	White reflector and opal cover
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	1,350 lm	3000 K	116 lm/W	≥80	28	White reflector and opal cover
911401578844	DN391B LED15/865 PSD D100 WH GCG2HE	1,500 lm	6500 K	125 lm/W	≥80	28	White reflector and opal cover
911401578944	DN391B LED15/840 PSD D100 WH GCG2HE	1,500 lm	4000 K	125 lm/W	≥80	28	White reflector and opal cover
911401579044	DN391B LED15/830 PSD D100 WH GCG2HE	1,350 lm	3000 K	116 lm/W	≥80	28	White reflector and opal cover
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	1,200 lm	6500 K	125 lm/W	≥80	28	White reflector and opal cover
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	1,200 lm	4000 K	125 lm/W	≥80	28	White reflector and opal cover
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	1,100 lm	3000 K	116 lm/W	≥80	28	White reflector and opal cover
911401580044	DN391B LED12/865 PSD D100 WH GCG2HE	1,200 lm	6500 K	125 lm/W	≥80	28	White reflector and opal cover
911401580144	DN391B LED12/840 PSD D100 WH GCG2HE	1,200 lm	4000 K	125 lm/W	≥80	28	White reflector and opal cover
911401580244	DN391B LED12/830 PSD D100 WH GCG2HE	1,100 lm	3000 K	116 lm/W	≥80	28	White reflector and opal cover
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	2,000 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	2,000 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401523144	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	1,850 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	1,850 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	1,250 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	1,250 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	1,150 lm	3000 K	122 lm/W	>80	1	Facetted reflector
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	2,000 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	2,000 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	1,850 lm	6500 K	132 lm/W	>80	1	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	1,850 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	1,250 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	1,250 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	1,850 lm	6500 K	130 lm/W	>80	1	Facetted reflector
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	1,850 lm	4000 K	130 lm/W	>80	1	Facetted reflector
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	1,800 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	1,800 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	1,650 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	1,800 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	1,800 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	1,650 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	2,200 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	2,200 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	2,000 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401568344	DN392B LED22/865 PSD D150 AL WP GCG2HE	2,200 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401568444	DN392B LED22/840 PSD D150 AL WP GCG2HE	2,200 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401568544	DN392B LED22/830 PSD D150 AL WP GCG2HE	2,000 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401569244	DN392B LED18/865 PSD D150 AL WP GCG2HE	1,800 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401569344	DN392B LED18/840 PSD D150 AL WP GCG2HE	1,800 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401569444	DN392B LED18/830 PSD D150 AL WP GCG2HE	1,650 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	1,250 lm	6500 K	120 lm/W	≥80	24	Facetted reflector
911401569644	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	1,250 lm	4000 K	120 lm/W	≥80	24	Facetted reflector
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	1,150 lm	3000 K	111 lm/W	≥80	24	Facetted reflector
911401569844	DN391B LED12/865 PSD D150 AL WP GCG2HE	1,250 lm	6500 K	120 lm/W	≥80	24	Facetted reflector
911401569944	DN391B LED12/840 PSD D150 AL WP GCG2HE	1,250 lm	4000 K	120 lm/W	≥80	24	Facetted reflector
911401570044	DN391B LED12/830 PSD D150 AL WP GCG2HE	1,150 lm	3000 K	111 lm/W	≥80	24	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	2,200 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	2,200 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	2,000 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401574344	DN392B LED22/865 PSD D150 AL GCG2HE	2,200 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401574444	DN392B LED22/840 PSD D150 AL GCG2HE	2,200 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401574544	DN392B LED22/830 PSD D150 AL GCG2HE	2,000 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401576144	DN392B LED18/865 PSD D150 AL GCG2HE	1,800 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401576244	DN392B LED18/840 PSD D150 AL GCG2HE	1,800 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401576344	DN392B LED18/830 PSD D150 AL GCG2HE	1,650 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	1,250 lm	6500 K	120 lm/W	≥80	24	Facetted reflector
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	1,250 lm	4000 K	120 lm/W	≥80	24	Facetted reflector
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	1,150 lm	3000 K	111 lm/W	≥80	24	Facetted reflector
911401577344	DN391B LED12/865 PSD D150 AL GCG2HE	1,250 lm	6500 K	120 lm/W	≥80	24	Facetted reflector
911401577444	DN391B LED12/840 PSD D150 AL GCG2HE	1,250 lm	4000 K	120 lm/W	≥80	24	Facetted reflector
911401577544	DN391B LED12/830 PSD D150 AL GCG2HE	1,150 lm	3000 K	111 lm/W	≥80	24	Facetted reflector
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	1,500 lm	4000 K	125 lm/W	≥80	28	White reflector and opal cover
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	700 lm	6500 K	125 lm/W	>80	1	Facetted reflector
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	1,400 lm	4000 K	125 lm/W	>80	1	Facetted reflector
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	700 lm	4000 K	125 lm/W	>80	1	Facetted reflector
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	650 lm	3000 K	118 lm/W	>80	1	Facetted reflector
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	1,400 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	1,400 lm	4000 K	120 lm/W	≥80	28	Facetted reflector
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	1,300 lm	3000 K	111 lm/W	≥80	28	Facetted reflector
911401570444	DN391B LED14/865 PSD D100 AL WP GCG2HE	1,400 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401570544	DN391B LED14/840 PSD D100 AL WP GCG2HE	1,400 lm	4000 K	120 lm/W	≥80	28	Facetted reflector
911401570644	DN391B LED14/830 PSD D100 AL WP GCG2HE	1,300 lm	3000 K	111 lm/W	≥80	28	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	1,200 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	1,200 lm	4000 K	120 lm/W	≥80	28	Facetted reflector
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	1,100 lm	3000 K	111 lm/W	≥80	28	Facetted reflector
911401571044	DN391B LED12/865 PSD D100 AL WP GCG2HE	1,200 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401571144	DN391B LED12/840 PSD D100 AL WP GCG2HE	1,200 lm	4000 K	120 lm/W	≥80	28	Facetted reflector
911401571244	DN391B LED12/830 PSD D100 AL WP GCG2HE	1,100 lm	3000 K	111 lm/W	≥80	28	Facetted reflector
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	1,400 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	1,400 lm	4000 K	120 lm/W	≥80	28	Facetted reflector
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	1,300 lm	3000 K	111 lm/W	≥80	28	Facetted reflector
911401578544	DN391B LED14/865 PSD D100 AL GCG2HE	1,400 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401578644	DN391B LED14/840 PSD D100 AL GCG2HE	1,400 lm	4000 K	120 lm/W	≥80	28	Facetted reflector
911401578744	DN391B LED14/830 PSD D100 AL GCG2HE	1,300 lm	3000 K	111 lm/W	≥80	28	Facetted reflector
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	1,200 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	1,200 lm	4000 K	120 lm/W	≥80	28	Facetted reflector
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	1,100 lm	3000 K	111 lm/W	≥80	28	Facetted reflector
911401579744	DN391B LED12/865 PSD D100 AL GCG2HE	1,200 lm	6500 K	120 lm/W	≥80	28	Facetted reflector
911401579944	DN391B LED12/830 PSD D100 AL GCG2HE	1,100 lm	3000 K	111 lm/W	≥80	28	Facetted reflector
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	4,000 lm	6500 K	140 lm/W	>80	1	White reflector and opal cover
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	4,000 lm	4000 K	140 lm/W	>80	1	White reflector and opal cover
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	3,700 lm	3000 K	130 lm/W	>80	1	White reflector and opal cover
911401527644	DN393B LED26/865 P19PSU D200 WH GMG2HE	2,600 lm	6500 K	140 lm/W	>80	1	White reflector and opal cover
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	2,600 lm	4000 K	140 lm/W	>80	1	White reflector and opal cover
911401527844	DN393B LED26/830 P19PSU D200 WH GMG2HE	2,400 lm	3000 K	130 lm/W	>80	1	White reflector and opal cover
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	2,000 lm	6500 K	140 lm/W	>80	1	White reflector and opal cover
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	2,000 lm	4000 K	140 lm/W	>80	1	White reflector and opal cover
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	1,850 lm	3000 K	130 lm/W	>80	1	White reflector and opal cover

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	2,600 lm	6500 K	137 lm/W	>80	1	White reflector and opal cover
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	2,600 lm	4000 K	137 lm/W	>80	1	White reflector and opal cover
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	4,000 lm	6500 K	137 lm/W	≥80	78	White reflector and opal cover
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	4,000 lm	4000 K	137 lm/W	≥80	78	White reflector and opal cover
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	3,700 lm	3000 K	127 lm/W	≥80	78	White reflector and opal cover
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	2,600 lm	6500 K	137 lm/W	≥80	48	White reflector and opal cover
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	2,600 lm	4000 K	137 lm/W	≥80	48	White reflector and opal cover
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	1,850 lm	6500 K	137 lm/W	≥80	48	White reflector and opal cover
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	1,850 lm	4000 K	137 lm/W	≥80	48	White reflector and opal cover
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	1,700 lm	3000 K	127 lm/W	≥80	48	White reflector and opal cover
911401575844	DN392B LED18/865 PSD D200 WH GCG2HE	1,850 lm	6500 K	137 lm/W	≥80	48	White reflector and opal cover
911401575944	DN392B LED18/840 PSD D200 WH GCG2HE	1,850 lm	4000 K	137 lm/W	≥80	48	White reflector and opal cover
911401576044	DN392B LED18/830 PSD D200 WH GCG2HE	1,700 lm	3000 K	127 lm/W	≥80	48	White reflector and opal cover
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	3,800 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	3,800 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401521344	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	2,500 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	2,500 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	1,850 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	1,850 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	3,800 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	3,800 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	2,500 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	2,500 lm	4000 K	132 lm/W	>80	1	Facetted reflector
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	2,300 lm	3000 K	122 lm/W	>80	1	Facetted reflector
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	1,850 lm	6500 K	132 lm/W	>80	1	Facetted reflector
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	1,850 lm	4000 K	132 lm/W	>80	1	Facetted reflector

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	2,500 lm	6500 K	130 lm/W	>80	1	Facetted reflector
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	2,500 lm	4000 K	130 lm/W	>80	1	Facetted reflector
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	3,800 lm	4000 K	130 lm/W	≥80	78	Facetted reflector
911401567544	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	2,500 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	2,300 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	1,750 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	1,750 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	1,650 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401568944	DN392B LED18/865 PSD D200 AL WP GCG2HE	1,750 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401569044	DN392B LED18/840 PSD D200 AL WP GCG2HE	1,750 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401569144	DN392B LED18/830 PSD D200 AL WP GCG2HE	1,650 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	3,800 lm	6500 K	130 lm/W	≥80	78	Facetted reflector
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	3,800 lm	4000 K	130 lm/W	≥80	78	Facetted reflector
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	3,500 lm	3000 K	120 lm/W	≥80	78	Facetted reflector
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	2,500 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	1,850 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	1,850 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	1,700 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401575544	DN392B LED18/865 PSD D200 AL GCG2HE	1,750 lm	6500 K	130 lm/W	≥80	48	Facetted reflector
911401575644	DN392B LED18/840 PSD D200 AL GCG2HE	1,750 lm	4000 K	130 lm/W	≥80	48	Facetted reflector
911401575744	DN392B LED18/830 PSD D200 AL GCG2HE	1,650 lm	3000 K	120 lm/W	≥80	48	Facetted reflector
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	2,000 lm	4000 K	130 lm/W	≥80	40	White reflector and opal cover
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	2,200 lm	6500 K	138 lm/W	>80	1	White reflector and opal cover
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	2,200 lm	4000 K	138 lm/W	>80	1	White reflector and opal cover
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	2,000 lm	3000 K	130 lm/W	>80	1	White reflector and opal cover
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	2,000 lm	6500 K	138 lm/W	>80	1	White reflector and opal cover

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Color rendering index (CRI)	Number of light sources	Optic type
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	2,000 lm	4000 K	138 lm/W	>80	1	White reflector and opal cover
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	1,850 lm	3000 K	130 lm/W	>80	1	White reflector and opal cover
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	1,300 lm	6500 K	138 lm/W	>80	1	White reflector and opal cover
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	1,300 lm	4000 K	138 lm/W	>80	1	White reflector and opal cover
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	1,200 lm	3000 K	130 lm/W	>80	1	White reflector and opal cover
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	2,000 lm	6500 K	135 lm/W	>80	1	White reflector and opal cover
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	2,000 lm	4000 K	135 lm/W	>80	1	White reflector and opal cover
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	1,900 lm	6500 K	135 lm/W	≥80	48	White reflector and opal cover
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	1,900 lm	4000 K	135 lm/W	≥80	48	White reflector and opal cover
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	1,750 lm	3000 K	125 lm/W	≥80	48	White reflector and opal cover
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	2,300 lm	6500 K	135 lm/W	≥80	48	White reflector and opal cover
911401576444	DN392B LED19/865 PSD D150 WH GCG2HE	1,900 lm	6500 K	135 lm/W	≥80	48	White reflector and opal cover
911401576544	DN392B LED19/840 PSD D150 WH GCG2HE	1,900 lm	4000 K	135 lm/W	≥80	48	White reflector and opal cover
911401576644	DN392B LED19/830 PSD D150 WH GCG2HE	1,750 lm	3000 K	116 lm/W	≥80	48	White reflector and opal cover
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	1,300 lm	6500 K	125 lm/W	≥80	24	White reflector and opal cover
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	1,300 lm	4000 K	125 lm/W	≥80	24	White reflector and opal cover
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	1,200 lm	3000 K	116 lm/W	≥80	24	White reflector and opal cover
911401577644	DN391B LED13/865 PSD D150 WH GCG2HE	1,300 lm	6500 K	125 lm/W	≥80	24	White reflector and opal cover
911401577744	DN391B LED13/840 PSD D150 WH GCG2HE	1,300 lm	4000 K	125 lm/W	≥80	24	White reflector and opal cover
911401577844	DN391B LED13/830 PSD D150 WH GCG2HE	1,200 lm	3000 K	116 lm/W	≥80	24	White reflector and opal cover

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	11.4 W
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	11.4 W
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	9.8 W
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	9.8 W
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	9.8 W

Order Code	Full Product Name	Power Consumption
911401536144	DN390B LED7/865 P6PSU D100 WH GMG2HE	5.8 W
911401536244	DN390B LED7/840 P6PSU D100 WH GMG2HE	5.8 W
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	5.8 W
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	12 W
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	12 W
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	12 W
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	12 W
911401578844	DN391B LED15/865 PSD D100 WH GCG2HE	12 W
911401578944	DN391B LED15/840 PSD D100 WH GCG2HE	12 W
911401579044	DN391B LED15/830 PSD D100 WH GCG2HE	12 W
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	10.2 W
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	10.2 W
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	10.2 W
911401580044	DN391B LED12/865 PSD D100 WH GCG2HE	10.2 W
911401580144	DN391B LED12/840 PSD D100 WH GCG2HE	10.2 W
911401580244	DN391B LED12/830 PSD D100 WH GCG2HE	10.2 W
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	16 W
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	16 W
911401523144	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	14.4 W
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	14.4 W
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	9.8 W
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	9.8 W
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	9.8 W
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	16 W
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	16 W
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	14.4 W
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	14.4 W
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	9.8 W
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	9.8 W
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	15 W
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	15 W
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	13.4 W
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	13.4 W
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	13.4 W
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	13.4 W
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	13.4 W
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	13.4 W
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	17.3 W
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	17.3 W
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	17.3 W
911401568344	DN392B LED22/865 PSD D150 AL WP GCG2HE	17.3 W
911401568444	DN392B LED22/840 PSD D150 AL WP GCG2HE	17.3 W

Order Code	Full Product Name	Power Consumption
911401568544	DN392B LED22/830 PSD D150 AL WP GCG2HE	17.3 W
911401569244	DN392B LED18/865 PSD D150 AL WP GCG2HE	13.4 W
911401569344	DN392B LED18/840 PSD D150 AL WP GCG2HE	13.4 W
911401569444	DN392B LED18/830 PSD D150 AL WP GCG2HE	13.4 W
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	10.6 W
911401569644	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	10.6 W
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	10.6 W
911401569844	DN391B LED12/865 PSD D150 AL WP GCG2HE	10.6 W
911401569944	DN391B LED12/840 PSD D150 AL WP GCG2HE	10.6 W
911401570044	DN391B LED12/830 PSD D150 AL WP GCG2HE	10.6 W
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	17.3 W
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	17.3 W
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	17.3 W
911401574344	DN392B LED22/865 PSD D150 AL GCG2HE	17.3 W
911401574444	DN392B LED22/840 PSD D150 AL GCG2HE	17.3 W
911401574544	DN392B LED22/830 PSD D150 AL GCG2HE	17.3 W
911401576144	DN392B LED18/865 PSD D150 AL GCG2HE	13.4 W
911401576244	DN392B LED18/840 PSD D150 AL GCG2HE	13.4 W
911401576344	DN392B LED18/830 PSD D150 AL GCG2HE	13.4 W
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	10.6 W
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	10.6 W
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	10.6 W
911401577344	DN391B LED12/865 PSD D150 AL GCG2HE	10.6 W
911401577444	DN391B LED12/840 PSD D150 AL GCG2HE	10.6 W
911401577544	DN391B LED12/830 PSD D150 AL GCG2HE	10.6 W
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	12 W
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	5.8 W
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	11.4 W
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	5.8 W
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	5.8 W
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	12 W
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	12 W
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	12 W
911401570444	DN391B LED14/865 PSD D100 AL WP GCG2HE	12 W
911401570544	DN391B LED14/840 PSD D100 AL WP GCG2HE	12 W
911401570644	DN391B LED14/830 PSD D100 AL WP GCG2HE	12 W
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	10.2 W
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	10.2 W
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	10.2 W
911401571044	DN391B LED12/865 PSD D100 AL WP GCG2HE	10.2 W
911401571144	DN391B LED12/840 PSD D100 AL WP GCG2HE	10.2 W
911401571244	DN391B LED12/830 PSD D100 AL WP GCG2HE	10.2 W

Order Code	Full Product Name	Power Consumption
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	12 W
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	12 W
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	12 W
911401578544	DN391B LED14/865 PSD D100 AL GCG2HE	12 W
911401578644	DN391B LED14/840 PSD D100 AL GCG2HE	12 W
911401578744	DN391B LED14/830 PSD D100 AL GCG2HE	12 W
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	10.2 W
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	10.2 W
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	10.2 W
911401579744	DN391B LED12/865 PSD D100 AL GCG2HE	10.2 W
911401579944	DN391B LED12/830 PSD D100 AL GCG2HE	10.2 W
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	29.3 W
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	29.3 W
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	29.3 W
911401527644	DN393B LED26/865 P19PSU D200 WH GMG2HE	19.2 W
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	19.2 W
911401527844	DN393B LED26/830 P19PSU D200 WH GMG2HE	19.2 W
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	14.4 W
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	14.4 W
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	14.4 W
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	19.9 W
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	19.9 W
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	29.3 W
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	29.3 W
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	29.3 W
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	19.9 W
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	19.9 W
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	14.2 W
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	14.2 W
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	14.2 W
911401575844	DN392B LED18/865 PSD D200 WH GCG2HE	14.2 W
911401575944	DN392B LED18/840 PSD D200 WH GCG2HE	14.2 W
911401576044	DN392B LED18/830 PSD D200 WH GCG2HE	14.2 W
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	29.3 W
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	29.3 W
911401521344	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	19.2 W
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	19.2 W
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	14.4 W
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	14.4 W
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	29.3 W
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	29.3 W
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	19.2 W

Order Code	Full Product Name	Power Consumption
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	19.2 W
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	19.2 W
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	14.4 W
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	14.4 W
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	19.9 W
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	19.9 W
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	29.3 W
911401567544	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	19.9 W
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	19.9 W
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	14.2 W
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	14.2 W
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	14.2 W
911401568944	DN392B LED18/865 PSD D200 AL WP GCG2HE	14.2 W
911401569044	DN392B LED18/840 PSD D200 AL WP GCG2HE	14.2 W
911401569144	DN392B LED18/830 PSD D200 AL WP GCG2HE	14.2 W
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	29.3 W
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	29.3 W
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	29.3 W
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	19.9 W
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	14.2 W
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	14.2 W
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	14.2 W
911401575544	DN392B LED18/865 PSD D200 AL GCG2HE	14.2 W
911401575644	DN392B LED18/840 PSD D200 AL GCG2HE	14.2 W
911401575744	DN392B LED18/830 PSD D200 AL GCG2HE	14.2 W
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	15 W
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	16 W
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	16 W
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	16 W
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	14.4 W
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	14.4 W
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	14.4 W
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	9.8 W
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	9.8 W
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	9.8 W
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	15 W
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	15 W
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	13.4 W
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	13.4 W
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	13.4 W
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	17.3 W
911401576444	DN392B LED19/865 PSD D150 WH GCG2HE	13.4 W

Order Code	Full Product Name	Power Consumption
911401576544	DN392B LED19/840 PSD D150 WH GCG2HE	13.4 W
911401576644	DN392B LED19/830 PSD D150 WH GCG2HE	13.4 W
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	10.6 W
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	10.6 W
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	10.6 W
911401577644	DN391B LED13/865 PSD D150 WH GCG2HE	10.6 W
911401577744	DN391B LED13/840 PSD D150 WH GCG2HE	10.6 W
911401577844	DN391B LED13/830 PSD D150 WH GCG2HE	10.6 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	No	Not applicable
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	No	Not applicable
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	No	Not applicable
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	No	Not applicable
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	No	Not applicable
911401536144	DN390B LED7/865 P6PSU D100 WH GMG2HE	No	Not applicable
911401536244	DN390B LED7/840 P6PSU D100 WH GMG2HE	No	Not applicable
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	No	Not applicable
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	DALI	1%
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	DALI	1%
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	DALI	1%
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	DALI	1%
911401578844	DN391B LED15/865 PSD D100 WH GCG2HE	DALI	1%
911401578944	DN391B LED15/840 PSD D100 WH GCG2HE	DALI	1%
911401579044	DN391B LED15/830 PSD D100 WH GCG2HE	DALI	1%
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	DALI	1%
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	DALI	1%
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	DALI	1%
911401580044	DN391B LED12/865 PSD D100 WH GCG2HE	DALI	1%
911401580144	DN391B LED12/840 PSD D100 WH GCG2HE	DALI	1%
911401580244	DN391B LED12/830 PSD D100 WH GCG2HE	DALI	1%
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	No	Not applicable
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	No	Not applicable
911401523144	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	No	Not applicable
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	No	Not applicable
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	No	Not applicable
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	No	Not applicable
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	No	Not applicable
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	No	Not applicable
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	No	Not applicable
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	No	Not applicable
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	No	Not applicable
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	No	Not applicable
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	DALI	1%
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	DALI	1%
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	DALI	1%
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	DALI	1%
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	DALI	1%
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	DALI	1%
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	DALI	1%
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	DALI	1%
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	DALI	1%
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	DALI	1%
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	DALI	1%
911401568344	DN392B LED22/865 PSD D150 AL WP GCG2HE	DALI	1%
911401568444	DN392B LED22/840 PSD D150 AL WP GCG2HE	DALI	1%
911401568544	DN392B LED22/830 PSD D150 AL WP GCG2HE	DALI	1%
911401569244	DN392B LED18/865 PSD D150 AL WP GCG2HE	DALI	1%
911401569344	DN392B LED18/840 PSD D150 AL WP GCG2HE	DALI	1%
911401569444	DN392B LED18/830 PSD D150 AL WP GCG2HE	DALI	1%
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	DALI	1%
911401569644	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	DALI	1%
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	DALI	1%
911401569844	DN391B LED12/865 PSD D150 AL WP GCG2HE	DALI	1%
911401569944	DN391B LED12/840 PSD D150 AL WP GCG2HE	DALI	1%
911401570044	DN391B LED12/830 PSD D150 AL WP GCG2HE	DALI	1%
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	DALI	1%
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	DALI	1%
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	DALI	1%
911401574344	DN392B LED22/865 PSD D150 AL GCG2HE	DALI	1%
911401574444	DN392B LED22/840 PSD D150 AL GCG2HE	DALI	1%
911401574544	DN392B LED22/830 PSD D150 AL GCG2HE	DALI	1%
911401576144	DN392B LED18/865 PSD D150 AL GCG2HE	DALI	1%
911401576244	DN392B LED18/840 PSD D150 AL GCG2HE	DALI	1%
911401576344	DN392B LED18/830 PSD D150 AL GCG2HE	DALI	1%
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	DALI	1%
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	DALI	1%
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	DALI	1%
911401577344	DN391B LED12/865 PSD D150 AL GCG2HE	DALI	1%
911401577444	DN391B LED12/840 PSD D150 AL GCG2HE	DALI	1%
911401577544	DN391B LED12/830 PSD D150 AL GCG2HE	DALI	1%
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	DALI	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	No	Not applicable
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	No	Not applicable
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	No	Not applicable
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	No	Not applicable
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	DALI	1%
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	DALI	1%
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	DALI	1%
911401570444	DN391B LED14/865 PSD D100 AL WP GCG2HE	DALI	1%
911401570544	DN391B LED14/840 PSD D100 AL WP GCG2HE	DALI	1%
911401570644	DN391B LED14/830 PSD D100 AL WP GCG2HE	DALI	1%
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	DALI	1%
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	DALI	1%
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	DALI	1%
911401571044	DN391B LED12/865 PSD D100 AL WP GCG2HE	DALI	1%
911401571144	DN391B LED12/840 PSD D100 AL WP GCG2HE	DALI	1%
911401571244	DN391B LED12/830 PSD D100 AL WP GCG2HE	DALI	1%
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	DALI	1%
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	DALI	1%
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	DALI	1%
911401578544	DN391B LED14/865 PSD D100 AL GCG2HE	DALI	1%
911401578644	DN391B LED14/840 PSD D100 AL GCG2HE	DALI	1%
911401578744	DN391B LED14/830 PSD D100 AL GCG2HE	DALI	1%
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	DALI	1%
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	DALI	1%
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	DALI	1%
911401579744	DN391B LED12/865 PSD D100 AL GCG2HE	DALI	1%
911401579944	DN391B LED12/830 PSD D100 AL GCG2HE	DALI	1%
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	No	Not applicable
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	No	Not applicable
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	No	Not applicable
911401527644	DN393B LED26/865 P19PSU D200 WH GMG2HE	No	Not applicable
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	No	Not applicable
911401527844	DN393B LED26/830 P19PSU D200 WH GMG2HE	No	Not applicable
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	No	Not applicable
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	No	Not applicable
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	No	Not applicable
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	DALI	1%
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	DALI	1%
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	DALI	1%
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	DALI	1%
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	DALI	1%
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	DALI	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	DALI	1%
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	DALI	1%
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	DALI	1%
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	DALI	1%
911401575844	DN392B LED18/865 PSD D200 WH GCG2HE	DALI	1%
911401575944	DN392B LED18/840 PSD D200 WH GCG2HE	DALI	1%
911401576044	DN392B LED18/830 PSD D200 WH GCG2HE	DALI	1%
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	No	Not applicable
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	No	Not applicable
911401521344	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	No	Not applicable
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	No	Not applicable
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	No	Not applicable
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	No	Not applicable
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	No	Not applicable
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	No	Not applicable
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	No	Not applicable
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	No	Not applicable
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	No	Not applicable
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	No	Not applicable
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	No	Not applicable
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	DALI	1%
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	DALI	1%
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	DALI	1%
911401567544	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	DALI	1%
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	DALI	1%
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	DALI	1%
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	DALI	1%
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	DALI	1%
911401568944	DN392B LED18/865 PSD D200 AL WP GCG2HE	DALI	1%
911401569044	DN392B LED18/840 PSD D200 AL WP GCG2HE	DALI	1%
911401569144	DN392B LED18/830 PSD D200 AL WP GCG2HE	DALI	1%
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	DALI	1%
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	DALI	1%
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	DALI	1%
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	DALI	1%
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	DALI	1%
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	DALI	1%
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	DALI	1%
911401575544	DN392B LED18/865 PSD D200 AL GCG2HE	DALI	1%
911401575644	DN392B LED18/840 PSD D200 AL GCG2HE	DALI	1%
911401575744	DN392B LED18/830 PSD D200 AL GCG2HE	DALI	1%
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	DALI	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	No	Not applicable
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	No	Not applicable
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	No	Not applicable
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	No	Not applicable
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	No	Not applicable
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	No	Not applicable
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	No	Not applicable
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	No	Not applicable
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	No	Not applicable
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	DALI	1%
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	DALI	1%
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	DALI	1%
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	DALI	1%
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	DALI	1%
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	DALI	1%
911401576444	DN392B LED19/865 PSD D150 WH GCG2HE	DALI	1%
911401576544	DN392B LED19/840 PSD D150 WH GCG2HE	DALI	1%
911401576644	DN392B LED19/830 PSD D150 WH GCG2HE	DALI	1%
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	DALI	1%
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	DALI	1%
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	DALI	1%
911401577644	DN391B LED13/865 PSD D150 WH GCG2HE	DALI	1%
911401577744	DN391B LED13/840 PSD D150 WH GCG2HE	DALI	1%
911401577844	DN391B LED13/830 PSD D150 WH GCG2HE	DALI	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Ingress protection code
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	Aluminum	IP20
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	Aluminum	IP20
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	Aluminum	IP20
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	Aluminum	IP20
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	Aluminum	IP20
911401536144	DN390B LED7/865 P6PSU D100 WH GMG2HE	Aluminum	IP20
911401536244	DN390B LED7/840 P6PSU D100 WH GMG2HE	Aluminum	IP20
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	Aluminum	IP20
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	Aluminum	IP20
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578844	DN391B LED15/865 PSD D100 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401578944	DN391B LED15/840 PSD D100 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401579044	DN391B LED15/830 PSD D100 WH GCG2HE	Aluminum and RAL (to be defined)	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401580044	DN391B LED12/865 PSD D100 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401580144	DN391B LED12/840 PSD D100 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401580244	DN391B LED12/830 PSD D100 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523144	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	Aluminum	IP20/54
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	Aluminum	IP20
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	Aluminum	IP20
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	Aluminum	IP20
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	Aluminum	IP20
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	Aluminum	IP20
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	Aluminum	IP20
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	Aluminum	IP20
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	Aluminum	IP20
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568344	DN392B LED22/865 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568444	DN392B LED22/840 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568544	DN392B LED22/830 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569244	DN392B LED18/865 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569344	DN392B LED18/840 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569444	DN392B LED18/830 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569644	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569844	DN391B LED12/865 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569944	DN391B LED12/840 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570044	DN391B LED12/830 PSD D150 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54

Order Code	Full Product Name	Housing Color	Ingress protection code
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401574344	DN392B LED22/865 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401574444	DN392B LED22/840 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401574544	DN392B LED22/830 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401576144	DN392B LED18/865 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401576244	DN392B LED18/840 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401576344	DN392B LED18/830 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401577344	DN391B LED12/865 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401577444	DN391B LED12/840 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401577544	DN391B LED12/830 PSD D150 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	Aluminum	IP20/54
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	Aluminum	IP20
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	Aluminum	IP20
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	Aluminum	IP20
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570444	DN391B LED14/865 PSD D100 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570544	DN391B LED14/840 PSD D100 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570644	DN391B LED14/830 PSD D100 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401571044	DN391B LED12/865 PSD D100 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401571144	DN391B LED12/840 PSD D100 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401571244	DN391B LED12/830 PSD D100 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401578544	DN391B LED14/865 PSD D100 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401578644	DN391B LED14/840 PSD D100 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401578744	DN391B LED14/830 PSD D100 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401579744	DN391B LED12/865 PSD D100 AL GCG2HE	Aluminum and RAL (to be defined)	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
911401579944	DN391B LED12/830 PSD D100 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	Aluminum	IP20
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	Aluminum	IP20
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	Aluminum	IP20
911401527644	DN393B LED26/865 P19PSU D200 WH GMG2HE	Aluminum	IP20
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	Aluminum	IP20
911401527844	DN393B LED26/830 P19PSU D200 WH GMG2HE	Aluminum	IP20
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	Aluminum	IP20
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	Aluminum	IP20
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	Aluminum	IP20
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	Aluminum	IP20
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	Aluminum	IP20
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575844	DN392B LED18/865 PSD D200 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401575944	DN392B LED18/840 PSD D200 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401576044	DN392B LED18/830 PSD D200 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401521344	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	Aluminum	IP20/54
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	Aluminum	IP20
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	Aluminum	IP20
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	Aluminum	IP20
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	Aluminum	IP20
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	Aluminum	IP20
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	Aluminum	IP20
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	Aluminum	IP20
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	Aluminum	IP20
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	Aluminum	IP20
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401567544	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54

Order Code	Full Product Name	Housing Color	Ingress protection code
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	Aluminum and RAL (to be defined)	IP20/54
911401568944	DN392B LED18/865 PSD D200 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569044	DN392B LED18/840 PSD D200 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401569144	DN392B LED18/830 PSD D200 AL WP GCG2HE	Aluminum and RAL (to be defined)	IP20/54
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	Aluminum and RAL (to be defined)	IP20
911401575544	DN392B LED18/865 PSD D200 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401575644	DN392B LED18/840 PSD D200 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401575744	DN392B LED18/830 PSD D200 AL GCG2HE	Aluminum and RAL (to be defined)	IP20
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	Aluminum	IP20
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	Aluminum	IP20
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	Aluminum	IP20
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	Aluminum	IP20
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	Aluminum	IP20
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	Aluminum	IP20
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	Aluminum	IP20
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	Aluminum	IP20
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	Aluminum	IP20
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	Aluminum	IP20
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	Aluminum	IP20
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401576444	DN392B LED19/865 PSD D150 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401576544	DN392B LED19/840 PSD D150 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401576644	DN392B LED19/830 PSD D150 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	Aluminum and RAL (to be defined)	IP20
911401577644	DN391B LED13/865 PSD D150 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401577744	DN391B LED13/840 PSD D150 WH GCG2HE	Aluminum and RAL (to be defined)	IP20
911401577844	DN391B LED13/830 PSD D150 WH GCG2HE	Aluminum and RAL (to be defined)	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance
911401533644	DN391B LED15/865 P11PSU D100 WH GMG2HE	+/-10%
911401533744	DN391B LED15/840 P11PSU D100 WH GMG2HE	+/-10%
911401534844	DN391B LED12/865 P10PSU D100 WH GMG2HE	+/-10%
911401534944	DN391B LED12/840 P10PSU D100 WH GMG2HE	+/-10%
911401535044	DN391B LED12/830 P10PSU D100 WH GMG2HE	+/-10%
911401536144	DN390B LED7/865 P6PSU D100 WH GMG2HE	+/-10%
911401536244	DN390B LED7/840 P6PSU D100 WH GMG2HE	+/-10%
911401536344	DN390B LED7/830 P6PSU D100 WH GMG2HE	+/-10%
911401537544	DN391X LED15/865 P12WIA D100 WH G2HE	+/-10%
911401578244	DN391B LED15/865 P12PSD D100 WH GMG2HE	-10% / +10%
911401578344	DN391B LED15/840 P12PSD D100 WH GMG2HE	-10% / +10%
911401578444	DN391B LED15/830 P12PSD D100 WH GMG2HE	-10% / +10%
911401578844	DN391B LED15/865 PSD D100 WH GCG2HE	-10% / +10%
911401578944	DN391B LED15/840 PSD D100 WH GCG2HE	-10% / +10%
911401579044	DN391B LED15/830 PSD D100 WH GCG2HE	-10% / +10%
911401579444	DN391B LED12/865 P10PSD D100 WH GMG2HE	-10% / +10%
911401579544	DN391B LED12/840 P10PSD D100 WH GMG2HE	-10% / +10%
911401579644	DN391B LED12/830 P10PSD D100 WH GMG2HE	-10% / +10%
911401580044	DN391B LED12/865 PSD D100 WH GCG2HE	-10% / +10%
911401580144	DN391B LED12/840 PSD D100 WH GCG2HE	-10% / +10%
911401580244	DN391B LED12/830 PSD D100 WH GCG2HE	-10% / +10%
911401521944	DN392B LED20/865 P16PSU D150 ALWP GMG2HE	+/-10%
911401522044	DN392B LED20/840 P16PSU D150 ALWP GMG2HE	+/-10%
911401523144	DN392B LED18/865 P14PSU D150 ALWP GMG2HE	+/-10%
911401523244	DN392B LED18/840 P14PSU D150 ALWP GMG2HE	+/-10%
911401523744	DN391B LED12/865 P10PSU D150 ALWP GMG2HE	+/-10%
911401523844	DN391B LED12/840 P10PSU D150 ALWP GMG2HE	+/-10%
911401523944	DN391B LED12/830 P10PSU D150 ALWP GMG2HE	+/-10%
911401528544	DN392B LED20/865 P16PSU D150 AL GMG2HE	+/-10%
911401528644	DN392B LED20/840 P16PSU D150 AL GMG2HE	+/-10%
911401530944	DN392B LED18/865 P14PSU D150 AL GMG2HE	+/-10%
911401531044	DN392B LED18/840 P14PSU D150 AL GMG2HE	+/-10%
911401532144	DN391B LED12/865 P10PSU D150 AL GMG2HE	+/-10%
911401532244	DN391B LED12/840 P10PSU D150 AL GMG2HE	+/-10%
911401537244	DN392X LED18/865 P15WIA D150 AL G2HE	+/-10%
911401538444	DN392X LED18/840 P15WIA D150 AL G2HE	+/-10%
911401565944	DN392B LED18/865 P14PSD D150 ALWP GMG2HE	-10% / +10%
911401566044	DN392B LED18/840 P14PSD D150 ALWP GMG2HE	-10% / +10%
911401566144	DN392B LED18/830 P14PSD D150 ALWP GMG2HE	-10% / +10%
911401566244	DN392B LED18/865 P14PSD D150 AL GMG2HE	-10% / +10%
911401566344	DN392B LED18/840 P14PSD D150 AL GMG2HE	-10% / +10%

Order Code	Full Product Name	Luminous flux tolerance
911401566444	DN392B LED18/830 P14PSD D150 AL GMG2HE	-10% / +10%
911401568044	DN392B LED22/865 P17PSD D150 ALWP GMG2HE	-10% / +10%
911401568144	DN392B LED22/840 P17PSD D150 ALWP GMG2HE	-10% / +10%
911401568244	DN392B LED22/830 P17PSD D150 ALWP GMG2HE	-10% / +10%
911401568344	DN392B LED22/865 PSD D150 AL WP GCG2HE	-10% / +10%
911401568444	DN392B LED22/840 PSD D150 AL WP GCG2HE	-10% / +10%
911401568544	DN392B LED22/830 PSD D150 AL WP GCG2HE	-10% / +10%
911401569244	DN392B LED18/865 PSD D150 AL WP GCG2HE	-10% / +10%
911401569344	DN392B LED18/840 PSD D150 AL WP GCG2HE	-10% / +10%
911401569444	DN392B LED18/830 PSD D150 AL WP GCG2HE	-10% / +10%
911401569544	DN391B LED12/865 P11PSD D150 ALWP GMG2HE	-10% / +10%
911401569644	DN391B LED12/840 P11PSD D150 ALWP GMG2HE	-10% / +10%
911401569744	DN391B LED12/830 P11PSD D150 ALWP GMG2HE	-10% / +10%
911401569844	DN391B LED12/865 PSD D150 AL WP GCG2HE	-10% / +10%
911401569944	DN391B LED12/840 PSD D150 AL WP GCG2HE	-10% / +10%
911401570044	DN391B LED12/830 PSD D150 AL WP GCG2HE	-10% / +10%
911401573744	DN392B LED22/865 P17PSD D150 AL GMG2HE	-10% / +10%
911401573844	DN392B LED22/840 P17PSD D150 AL GMG2HE	-10% / +10%
911401573944	DN392B LED22/830 P17PSD D150 AL GMG2HE	-10% / +10%
911401574344	DN392B LED22/865 PSD D150 AL GCG2HE	-10% / +10%
911401574444	DN392B LED22/840 PSD D150 AL GCG2HE	-10% / +10%
911401574544	DN392B LED22/830 PSD D150 AL GCG2HE	-10% / +10%
911401576144	DN392B LED18/865 PSD D150 AL GCG2HE	-10% / +10%
911401576244	DN392B LED18/840 PSD D150 AL GCG2HE	-10% / +10%
911401576344	DN392B LED18/830 PSD D150 AL GCG2HE	-10% / +10%
911401576744	DN391B LED12/865 P11PSD D150 AL GMG2HE	-10% / +10%
911401576844	DN391B LED12/840 P11PSD D150 AL GMG2HE	-10% / +10%
911401576944	DN391B LED12/830 P11PSD D150 AL GMG2HE	-10% / +10%
911401577344	DN391B LED12/865 PSD D150 AL GCG2HE	-10% / +10%
911401577444	DN391B LED12/840 PSD D150 AL GCG2HE	-10% / +10%
911401577544	DN391B LED12/830 PSD D150 AL GCG2HE	-10% / +10%
911401540744	DN391X LED15/840 P11L1W D100 WH GMG2HE	-10% / +10%
911401525544	DN390B LED7/865 P6PSU D100 AL WP GMG2HE	+/-10%
911401533444	DN391B LED14/840 P11PSU D100 AL GMG2HE	+/-10%
911401535944	DN390B LED7/840 P6PSU D100 AL GMG2HE	+/-10%
911401536044	DN390B LED7/830 P6PSU D100 AL GMG2HE	+/-10%
911401570144	DN391B LED14/865 P12PSD D100 ALWP GMG2HE	-10% / +10%
911401570244	DN391B LED14/840 P12PSD D100 ALWP GMG2HE	-10% / +10%
911401570344	DN391B LED14/830 P12PSD D100 ALWP GMG2HE	-10% / +10%
911401570444	DN391B LED14/865 PSD D100 AL WP GCG2HE	-10% / +10%
911401570544	DN391B LED14/840 PSD D100 AL WP GCG2HE	-10% / +10%
911401570644	DN391B LED14/830 PSD D100 AL WP GCG2HE	-10% / +10%

Order Code	Full Product Name	Luminous flux tolerance
911401570744	DN391B LED12/865 P10PSD D100 ALWP GMG2HE	-10% / +10%
911401570844	DN391B LED12/840 P10PSD D100 ALWP GMG2HE	-10% / +10%
911401570944	DN391B LED12/830 P10PSD D100 ALWP GMG2HE	-10% / +10%
911401571044	DN391B LED12/865 PSD D100 AL WP GCG2HE	-10% / +10%
911401571144	DN391B LED12/840 PSD D100 AL WP GCG2HE	-10% / +10%
911401571244	DN391B LED12/830 PSD D100 AL WP GCG2HE	-10% / +10%
911401577944	DN391B LED14/865 P12PSD D100 AL GMG2HE	-10% / +10%
911401578044	DN391B LED14/840 P12PSD D100 AL GMG2HE	-10% / +10%
911401578144	DN391B LED14/830 P12PSD D100 AL GMG2HE	-10% / +10%
911401578544	DN391B LED14/865 PSD D100 AL GCG2HE	-10% / +10%
911401578644	DN391B LED14/840 PSD D100 AL GCG2HE	-10% / +10%
911401578744	DN391B LED14/830 PSD D100 AL GCG2HE	-10% / +10%
911401579144	DN391B LED12/865 P10PSD D100 AL GMG2HE	-10% / +10%
911401579244	DN391B LED12/840 P10PSD D100 AL GMG2HE	-10% / +10%
911401579344	DN391B LED12/830 P10PSD D100 AL GMG2HE	-10% / +10%
911401579744	DN391B LED12/865 PSD D100 AL GCG2HE	-10% / +10%
911401579944	DN391B LED12/830 PSD D100 AL GCG2HE	-10% / +10%
911401526444	DN394B LED40/865 P29PSU D200 WH GMG2HE	+/-10%
911401526544	DN394B LED40/840 P29PSU D200 WH GMG2HE	+/-10%
911401526644	DN394B LED40/830 P29PSU D200 WH GMG2HE	+/-10%
911401527644	DN393B LED26/865 P19PSU D200 WH GMG2HE	+/-10%
911401527744	DN393B LED26/840 P19PSU D200 WH GMG2HE	+/-10%
911401527844	DN393B LED26/830 P19PSU D200 WH GMG2HE	+/-10%
911401530044	DN392B LED20/865 P14PSU D200 WH GMG2HE	+/-10%
911401530144	DN392B LED20/840 P14PSU D200 WH GMG2HE	+/-10%
911401530244	DN392B LED20/830 P14PSU D200 WH GMG2HE	+/-10%
911401537144	DN393X LED26/865 P20WIA D200 WH G2HE	+/-10%
911401538344	DN393X LED26/840 P20WIA D200 WH G2HE	+/-10%
911401571644	DN394B LED40/865 P29PSD D200 WH GMG2HE	-10% / +10%
911401571744	DN394B LED40/840 P29PSD D200 WH GMG2HE	-10% / +10%
911401571844	DN394B LED40/830 P29PSD D200 WH GMG2HE	-10% / +10%
911401572844	DN393B LED26/865 P20PSD D200 WH GMG2HE	-10% / +10%
911401572944	DN393B LED26/840 P20PSD D200 WH GMG2HE	-10% / +10%
911401575244	DN392B LED18/865 P14PSD D200 WH GMG2HE	-10% / +10%
911401575344	DN392B LED18/840 P14PSD D200 WH GMG2HE	-10% / +10%
911401575444	DN392B LED18/830 P14PSD D200 WH GMG2HE	-10% / +10%
911401575844	DN392B LED18/865 PSD D200 WH GCG2HE	-10% / +10%
911401575944	DN392B LED18/840 PSD D200 WH GCG2HE	-10% / +10%
911401576044	DN392B LED18/830 PSD D200 WH GCG2HE	-10% / +10%
911401520744	DN394B LED38/865 P29PSU D200 ALWP GMG2HE	+/-10%
911401520844	DN394B LED38/840 P29PSU D200 ALWP GMG2HE	+/-10%
911401521344	DN393B LED25/865 P19PSU D200 ALWP GMG2HE	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401521444	DN393B LED25/840 P19PSU D200 ALWP GMG2HE	+/-10%
911401522544	DN392B LED18/865 P14PSU D200 ALWP GMG2HE	+/-10%
911401522644	DN392B LED18/840 P14PSU D200 ALWP GMG2HE	+/-10%
911401526144	DN394B LED38/865 P29PSU D200 AL GMG2HE	+/-10%
911401526244	DN394B LED38/840 P29PSU D200 AL GMG2HE	+/-10%
911401527344	DN393B LED25/865 P19PSU D200 AL GMG2HE	+/-10%
911401527444	DN393B LED25/840 P19PSU D200 AL GMG2HE	+/-10%
911401527544	DN393B LED25/830 P19PSU D200 AL GMG2HE	+/-10%
911401529744	DN392B LED18/865 P14PSU D200 AL GMG2HE	+/-10%
911401529844	DN392B LED18/840 P14PSU D200 AL GMG2HE	+/-10%
911401537044	DN393X LED25/865 P20WIA D200 AL G2HE	+/-10%
911401538244	DN393X LED25/840 P20WIA D200 AL G2HE	+/-10%
911401566944	DN394B LED38/840 P29PSD D200 ALWP GMG2HE	-10% / +10%
911401567544	DN393B LED25/840 P20PSD D200 ALWP GMG2HE	-10% / +10%
911401567644	DN393B LED25/830 P20PSD D200 ALWP GMG2HE	-10% / +10%
911401568644	DN392B LED18/865 P14PSD D200 ALWP GMG2HE	-10% / +10%
911401568744	DN392B LED18/840 P14PSD D200 ALWP GMG2HE	-10% / +10%
911401568844	DN392B LED18/830 P14PSD D200 ALWP GMG2HE	-10% / +10%
911401568944	DN392B LED18/865 PSD D200 AL WP GCG2HE	-10% / +10%
911401569044	DN392B LED18/840 PSD D200 AL WP GCG2HE	-10% / +10%
911401569144	DN392B LED18/830 PSD D200 AL WP GCG2HE	-10% / +10%
911401571344	DN394B LED38/865 P29PSD D200 AL GMG2HE	-10% / +10%
911401571444	DN394B LED38/840 P29PSD D200 AL GMG2HE	-10% / +10%
911401571544	DN394B LED38/830 P29PSD D200 AL GMG2HE	-10% / +10%
911401572644	DN393B LED25/840 P20PSD D200 AL GMG2HE	-10% / +10%
911401574944	DN392B LED18/865 P14PSD D200 AL GMG2HE	-10% / +10%
911401575044	DN392B LED18/840 P14PSD D200 AL GMG2HE	-10% / +10%
911401575144	DN392B LED18/830 P14PSD D200 AL GMG2HE	-10% / +10%
911401575544	DN392B LED18/865 PSD D200 AL GCG2HE	-10% / +10%
911401575644	DN392B LED18/840 PSD D200 AL GCG2HE	-10% / +10%
911401575744	DN392B LED18/830 PSD D200 AL GCG2HE	-10% / +10%
911401539944	DN392X LED20/840 P15L1W D150 WH GMG2HE	-10% / +10%
911401528844	DN392B LED22/865 P16PSU D150 WH GMG2HE	+/-10%
911401528944	DN392B LED22/840 P16PSU D150 WH GMG2HE	+/-10%
911401529044	DN392B LED22/830 P16PSU D150 WH GMG2HE	+/-10%
911401531244	DN392B LED20/865 P14PSU D150 WH GMG2HE	+/-10%
911401531344	DN392B LED20/840 P14PSU D150 WH GMG2HE	+/-10%
911401531444	DN392B LED20/830 P14PSU D150 WH GMG2HE	+/-10%
911401532444	DN391B LED13/865 P10PSU D150 WH GMG2HE	+/-10%
911401532544	DN391B LED13/840 P10PSU D150 WH GMG2HE	+/-10%
911401532644	DN391B LED13/830 P10PSU D150 WH GMG2HE	+/-10%
911401537344	DN392X LED20/865 P15WIA D150 WH G2HE	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401538544	DN392X LED20/840 P15WIA D150 WH G2HE	+/-10%
911401566544	DN392B LED19/865 P14PSD D150 WH GMG2HE	-10% / +10%
911401566644	DN392B LED19/840 P14PSD D150 WH GMG2HE	-10% / +10%
911401566744	DN392B LED19/830 P14PSD D150 WH GMG2HE	-10% / +10%
911401574044	DN392B LED23/865 P17PSD D150 WH GMG2HE	-10% / +10%
911401576444	DN392B LED19/865 PSD D150 WH GCG2HE	-10% / +10%
911401576544	DN392B LED19/840 PSD D150 WH GCG2HE	-10% / +10%
911401576644	DN392B LED19/830 PSD D150 WH GCG2HE	-10% / +10%
911401577044	DN391B LED13/865 P11PSD D150 WH GMG2HE	-10% / +10%
911401577144	DN391B LED13/840 P11PSD D150 WH GMG2HE	-10% / +10%
911401577244	DN391B LED13/830 P11PSD D150 WH GMG2HE	-10% / +10%
911401577644	DN391B LED13/865 PSD D150 WH GCG2HE	-10% / +10%
911401577744	DN391B LED13/840 PSD D150 WH GCG2HE	-10% / +10%
911401577844	DN391B LED13/830 PSD D150 WH GCG2HE	-10% / +10%