



UniStrip G4 – Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection

UniStrip G4

Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort



Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only

Dimensional drawing



Product details

159A3710 Detail Photo



159A3691 Detail Photo



159A3731 Detail Photo



General Information	
Driver included	No
Light Technical	
Light source color	Warm white
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	80
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Clear glass
Housing Color	Dark gray
Mech. impact protection code	IK06
Ingress protection code	IP66
Approval and Application	
CE mark	Yes

Light Technical

Order Code	Full Product Name	Luminous Flux
911401780062	BCP386 12LED 30K 24V A11 L30	195 lm
911401780442	BCP386 60LED 30K 24V 45 L100	975 lm
911401780502	BCP386 60LED 30K 24V 60 L100	985 lm
911401780562	BCP386 60LED 30K 24V A11 L100	960 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401780062	BCP386 12LED 30K 24V A11 L30	3 W
911401780442	BCP386 60LED 30K 24V 45 L100	15 W

Order Code	Full Product Name	Power Consumption
911401780502	BCP386 60LED 30K 24V 60 L100	15 W
911401780562	BCP386 60LED 30K 24V A11 L100	15 W

